Ref. Certif. No.

CN74633

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	AC Contactors
Name and address of the applicant	Schneider Electric Industries SAS 35 Rue Joseph Monier 92500 Rueil-Malmaison, France
Name and address of the manufacturer	Schneider Electric Industries SAS 35 Rue Joseph Monier 92500 Rueil-Malmaison, France
Name and address of the factory Note: *When more than one factory, please report on page 2*	Schneider（Shanghai）Apparatus Parts Manufacturing Co., Ltd. Putuo Branch Block A, Building 2, No.629 Suide Road, Putuo District, Shanghai,P.R.China
Ratings and principal characteristics	See the Appendix
Trademark (if any)	Schneider Electric
Customer's Testing Facility (CTF) Stage used	N/A
Model / Type Ref.	LC1D09, LC2D09, LC1D12, LC2D12, LC1D18, LC2D18;
Additional information (if necessary may also be reported on page 2)	
A sample of the product was tested and found to be in conformity with	IEC 60947-1:2020;IEC 60947-4-1:2023
As shown in the Test Report Ref. No. which forms part of this Certificate	00901-CB2025CQC-124526

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: http://www.cqc.com.cn

Date: Dec.26,2025

Signature: 谢肇煦
Xie ZhaoXu

LC1D09, LC2D09, LC1D12, LC2D12, LC1D18, LC2D18

Ui: 690V;

Uimp: 6kV;

LC1D09, LC2D09

Ith: 25A;

AC-3: Ue/Ie: 230V/8.5A, 400V/8.5A, 440V/9A, 500V/9.2A, 690V/6.7A;

AC-4: Ue/Ie: 230V/7.1A, 400V/7.1A, 440V/7.5A, 500V/7.7A, 690V/5.6A;

AC-3e: Ue/Ie: 230V/8.5A, 400V/8.5A, 440V/9A, 500V/9.2A, 690V/6.7A;

AC-1: Ue/Ie: 230V/25A, 400V/25A, 440V/25A, 500V/25A, 690V/25A;

LC1D12, LC2D12

Ith: 25A;

AC-3: Ue/Ie: 230V/11.3A, 400V/11.5A, 440V/12A, 500V/12.4A, 690V/8.9A;

AC-4: Ue/Ie: 230V/9.42A, 400V/9.6A, 440V/10A, 500V/10.34A, 690V/7.42A;

AC-3e: Ue/Ie: 230V/11.3A, 400V/11.5A, 440V/12A, 500V/12.4A, 690V/8.9A;

AC-1: Ue/Ie: 230V/25A, 400V/25A, 440V/25A, 500V/25A, 690V/25A;

LC1D18, LC2D18

Ith: 32A;

AC-3: Ue/Ie: 230V/15A, 400V/15.5A, 440V/18A, 500V/16A, 690V/11.7A;

AC-4: Ue/Ie: 230V/12.5A, 400V/12.92A, 440V/15A, 500V/13.42A, 690V/9.75A;

AC-3e: Ue/Ie: 230V/15A, 400V/15.5A, 440V/18A, 500V/16A, 690V/11.7A;

AC-1: Ue/Ie: 230V/32A, 400V/32A, 440V/32A, 500V/32A, 690V/32A;

Us: AC12V 50/60Hz, 21V 50/60Hz, 24V 50/60Hz, 32V 50/60Hz, 36V 50/60Hz,
42V 50/60Hz, 48V 50/60Hz, 60V 50/60Hz, 100V 50/60Hz, 110V 50/60Hz,
115V 50/60Hz, 120V 50/60Hz, 127V 50/60Hz, 140V 50/60Hz, 200V 50/60Hz,

Additional information (if necessary)

Date: Dec.26,2025

Signature: 谢肇煦
Xie ZhaoXu

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666
Fax: +86-10-83886282
website
http://www.cqc.com.cn

208V 50/60Hz, 220V 50/60Hz, 230V 50/60Hz, 240V 50/60Hz, 277V 50/60Hz,
380V 50/60Hz, 400V 50/60Hz, 415V 50/60Hz, 440V 50/60Hz, 480V 50/60Hz,
500V 50/60Hz, 575V 50/60Hz, 600V 50/60Hz, 660V 50/60Hz, 690V 50/60Hz;
AC480V 60Hz, 575V 60Hz, 600V 60Hz;
DC12V, 20V, 24V, 32V, 36V, 48V, 60V, 72V, 96V, 100V, 110V, 125V, 155V,
174V, 200V, 220V, 250V, 305V, 348V, 440V;DC24VLC;
3P;
Frequency: 50/60Hz;
IP20(only front face);
Auxiliary contacts (body):
Ith:10A;
AC-15: Ue/Ie: 120V/6A, 600V/1.04A;
DC-13: Ue/Ie: 125V/1.1A, 600V/0.2A;
1NO1NC;

Additional information (if necessary)

Date: Dec.26,2025

Signature: 谢肇煦
Xie ZhaoXu

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666
Fax: +86-10-83886282
website
http://www.cqc.com.cn