



Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:
LADR0

Schneider Electric
Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 877 342 5173
Email: CCC@us.schneider-electric.com

Technical Information:

Contact Rating: A600, Q600 10A
UL File/CCN: E164862 / NKCR
CSA File: LR43364 3211 04
Meets Standard: IEC 60947-5-1
Weight: 0.17 lb (0.08 kg)
Termination Method: Screw Terminal
Control Wire Size: #10 - #18 AWG
Control Terminal Torque: 15 lb-in (1.7 Nm)
Mounting Hardware: TeSys D IEC AC or DC Contactor or Control Relay

Description:
Type:

Specification:
TeSys D IEC Off-Delay Timer - Front Mount - 0.1 to 3 Sec
TeSys D IEC Contactor and Control Relay Accessory