



Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:
LADT2

Schneider Electric
Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:	
Contact Rating:	A600, Q600 10A
UL File/CCN:	E164862 / NKCR
CSA File:	LR43364 3211 04
Meets Standard:	IEC 60947-5-1
Weight:	0.17 lb (0.08 kg)
Termination Method:	Screw Terminal
Control Wire Size:	#10 - #18 AWG
Control Terminal Torque:	15 lb-in (1.7 Nm)
Mounting Hardware:	TeSys D IEC AC or DC Contactor or Control Relay

Specification:	
Description:	TeSys D IEC On-Delay Timer - Front Mount - 0.1 to 30 Sec
Type:	TeSys D IEC Contactor and Control Relay Accessory