








Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LC1D09JD

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Rating:	600V / 9A
UL File/CCN:	E164862 / NLDX
CSA File:	LR43364 3211 04
Meets Standards:	IEC 60647-4
Weight:	0.71 lb (0.32 kg)
Termination Method:	Screw Clamp
Wire Size:	Power: #10 - #18 AWG Control: #10 - #18 AWG
Terminal torque:	Power: 15 lb-in (1.7 Nm) Control: 15 lb-in (1.7 Nm)
Mounting Hwd.:	35mm DIN Rail, #8 screw

Specification:

Description	TeSys D IEC Contactor - 9A - Vdc Coil
Type	TeSys D IEC Contactor - 9A - 12Vdc Coil
Voltages Code:	JD at 12VDC
Coil Consumption:	Inrush 5.4 W Sealed 5.4 W

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
0.5 HP	1 HP	2 HP	2 HP	5 HP	7.5 HP