UNICA X

Catalog 2026



Advancing Energy Tech

Schneider Electric™



Contents

Presentation **4**

Functions **6**

Controls 7

Specialized Controls 10

Comfort Controls 11

Switched Sockets and USB Chargers 13

Communication Outlets 15

Cover Frames and Accessories 17

Technical Information **18**

Connections 19

Dimensions 22

Reference Numbers **29**

Unica X

Give your spaces a modern edge with our next-generation solution.



Enhance the allure and functionality of your living spaces with UNICA X. Our latest line of ultra-sleek switches and sockets offers distinctive ergonomic designs, advanced connectivity, and much more. UNICA X transcends the ordinary switch – it embodies excellence and luxury, tailored to complement your individual style and preferences.

Elevate your surroundings with UNICA X, and immerse yourself in a new realm of satisfaction, efficiency, innovation and safety.

Design Ultra-thin



UNICA X embodies the minimalist design ethos, effortlessly integrating into your walls.

This range of stainless-steel wiring devices boasts an unprecedented slim profile with a mere 6.5mm thickness, showcasing our meticulous, innovative, and refined craftsmanship.

Each interaction with UNICA X offers a sensory journey, elevating your space with contemporary elegance. Discover the potential of ultra-slim brilliance today.

Material and Finishing

UNICA X, with its ultra-thin profile, is meticulously crafted from premium stainless steel using a high-intensity metal forging process. Available in six exclusive colors and finishes, these luxurious switches and sockets seamlessly blend into your walls, making them the ideal choice for contemporary, minimalist interiors. The plate's edge is crafted with CNC precision machining,Giving it an exquisite touch to its overall design.







Quality

Crafted with durability in mind, the range is made using techniques like sandblasting, electroplating, painting, anodizing, and brushing. These functions are carried out in our dust-free workshops and ensures that the range boasts of a velvet-like textures.



Advanced Function

UNICA X offers a modern edge with advanced features designed to make your everyday interactions, a little better. Experience a seamless fusion of contemporary design and practical innovation, enhancing both the look and utility of your spaces.

- Motion Sensor Night Light
  No more fumbling in the dark or wasting energy with UNICA X's motion sensor night light. It illuminates as you enter andGently dims when you depart, providing enhanced convenience while promoting energy efficiency.






- Socket with USB A+C
  Streamline your charging experience with UNICA X. Its effortless plug functionality offers a seamless way to access power and cater to diverse charging requirements all at once.

Unica X Controls
Specialized controls
Comfort controls





Controls

Switches – 16 AX – 250 V AC

	1G	2G	3G	4G
				
				
1-way				
Painted White	**NUX31_1_PW**	**NUX32_1_PW**	**NUX33_1_PW**	**NUX34_1_PW**
Stainless Steel	**NUX31_1_SS**	**NUX32_1_SS**	**NUX33_1_SS**	**NUX34_1_SS**
Jet Black	**NUX31_1_JB**	**NUX32_1_JB**	**NUX33_1_JB**	**NUX34_1_JB**
DarkGrey	**NUX31_1_DG**	**NUX32_1_DG**	**NUX33_1_DG**	**NUX34_1_DG**
Dark Bronze	**NUX31_1_DB**	**NUX32_1_DB**	**NUX33_1_DB**	**NUX34_1_DB**
Antique Brass	**NUX31_1_AB**	**NUX32_1_AB**	**NUX33_1_AB**	**NUX34_1_AB**
	1G	2G	3G	4G
				
				
2-way				
Painted White	**NUX31_2_PW**	**NUX32_2_PW**	**NUX33_2_PW**	**NUX34_2_PW**
Stainless Steel	**NUX31_2_SS**	**NUX32_2_SS**	**NUX33_2_SS**	**NUX34_2_SS**
Jet Black	**NUX31_2_JB**	**NUX32_2_JB**	**NUX33_2_JB**	**NUX34_2_JB**
DarkGrey	**NUX31_2_DG**	**NUX32_2_DG**	**NUX33_2_DG**	**NUX34_2_DG**
Dark Bronze	**NUX31_2_DB**	**NUX32_2_DB**	**NUX33_2_DB**	**NUX34_2_DB**
Antique Brass	**NUX31_2_AB**	**NUX32_2_AB**	**NUX33_2_AB**	**NUX34_2_AB**
	1G	2G		
				
				
Intermediate				
Painted White	**NUX31_IM_PW**	**NUX32_IM_PW**		
Stainless Steel	**NUX31_IM_SS**	**NUX32_IM_SS**		
Jet Black	**NUX31_IM_JB**	**NUX32_IM_JB**		
DarkGrey	**NUX31_IM_DG**	**NUX32_IM_DG**		
Dark Bronze	**NUX31_IM_DB**	**NUX32_IM_DB**		
Antique Brass	**NUX31_IM_AB**	**NUX32_IM_AB**		


Controls

Switches with LED Indicator – 16 AX – 250 V AC


	1G	2G	3G	4G
				
				
1-way				
Painted White	**NUX31_1N_PW**	**NUX32_1N_PW**	**NUX33_1N_PW**	**NUX34_1N_PW**
Stainless Steel	**NUX31_1N_SS**	**NUX32_1N_SS**	**NUX33_1N_SS**	**NUX34_1N_SS**
Jet Black	**NUX31_1N_JB**	**NUX32_1N_JB**	**NUX33_1N_JB**	**NUX34_1N_JB**
DarkGrey	**NUX31_1N_DG**	**NUX32_1N_DG**	**NUX33_1N_DG**	**NUX34_1N_DG**
Dark Bronze	**NUX31_1N_DB**	**NUX32_1N_DB**	**NUX33_1N_DB**	**NUX34_1N_DB**
Antique Brass	**NUX31_1N_AB**	**NUX32_1N_AB**	**NUX33_1N_AB**	**NUX34_1N_AB**
	1G	2G	3G	4G
				
				
2-way				
Painted White	**NUX31_2N_PW**	**NUX32_2N_PW**	**NUX33_2N_PW**	**NUX34_2N_PW**
Stainless Steel	**NUX31_2N_SS**	**NUX32_2N_SS**	**NUX33_2N_SS**	**NUX34_2N_SS**
Jet Black	**NUX31_2N_JB**	**NUX32_2N_JB**	**NUX33_2N_JB**	**NUX34_2N_JB**
DarkGrey	**NUX31_2N_DG**	**NUX32_2N_DG**	**NUX33_2N_DG**	**NUX34_2N_DG**
Dark Bronze	**NUX31_2N_DB**	**NUX32_2N_DB**	**NUX33_2N_DB**	**NUX34_2N_DB**
Antique Brass	**NUX31_2N_AB**	**NUX32_2N_AB**	**NUX33_2N_AB**	**NUX34_2N_AB**

Controls

Switches with LED Indicator – 20 A – 250 V

	1G 2-pole
	
	
1-way	
Painted White	**NUX31D20N_PW**
Stainless Steel	**NUX31D20N_SS**
Jet Black	**NUX31D20N_JB**
DarkGrey	**NUX31D20N_DG**
Dark Bronze	**NUX31D20N_DB**
Antique Brass	**NUX31D20N_AB**

Switches with LED Indicator – 32 A – 250 V

	1G 2-pole
	
	
1-way	
Painted White	**NUX31D32N_PW**
Stainless Steel	**NUX31D32N_SS**
Jet Black	**NUX31D32N_JB**
DarkGrey	**NUX31D32N_DG**
Dark Bronze	**NUX31D32N_DB**
Antique Brass	**NUX31D32N_AB**

Specialized Controls

Panic Buttons with Key Reset

	1G
	
Painted White	**NUX31KPB_PW**
Stainless Steel	**NUX31KPB_SS**
Jet Black	**NUX31KPB_JB**
DarkGrey	**NUX31KPB_DG**
Dark Bronze	**NUX31KPB_DB**
Antique Brass	**NUX31KPB_AB**

Fan Control Units with Rotary Knob

	1G
	
Painted White	**NUX31FR350_PW**
Stainless Steel	**NUX31FR350_SS**
Jet Black	**NUX31FR350_JB**
DarkGrey	**NUX31FR350_DG**
Dark Bronze	**NUX31FR350_DB**
Antique Brass	**NUX31FR350_AB**

Bell Buttons – 10 A – 250 V AC

	1G
	
Painted White	**NUX31_BP_PW**
Stainless Steel	**NUX31_BP_SS**
Jet Black	**NUX31_BP_JB**
DarkGrey	**NUX31_BP_DG**
Dark Bronze	**NUX31_BP_DB**
Antique Brass	**NUX31_BP_AB**

Universal Push-button Dimmers – 250 W

	1G	2G
		
2-way		
Painted White	**NUX31RUD250_PW**	**NUX32RUD250_PW**
Stainless Steel	**NUX31RUD250_SS**	**NUX32RUD250_SS**
Jet Black	**NUX31RUD250_JB**	**NUX32RUD250_JB**
DarkGrey	**NUX31RUD250_DG**	**NUX32RUD250_DG**
Dark Bronze	**NUX31RUD250_DB**	**NUX32RUD250_DB**
Antique Brass	**NUX31RUD250_AB**	**NUX32RUD250_AB**

Comfort Controls

Shaver Sockets – 115/230 V AC

	1G (Vertical)
	
Painted White	**NUXT727V_PW**
Stainless Steel	**NUXT727V_SS**
Jet Black	**NUXT727V_JB**
DarkGrey	**NUXT727V_DG**
Dark Bronze	**NUXT727V_DB**
Antique Brass	**NUXT727V_AB**

Bell Switches with DND, PCU Indicator

	1G
	
Painted White	**NUX31BPDM_PW**
Stainless Steel	**NUX31BPDM_SS**
Jet Black	**NUX31BPDM_JB**
DarkGrey	**NUX31BPDM_DG**
Dark Bronze	**NUX31BPDM_DB**
Antique Brass	**NUX31BPDM_AB**

Night Foot Lamps with LED Indicator and PIR Sensor

	1G
	
Painted White	**NUXFLIR_PW**
Stainless Steel	**NUXFLIR_SS**
Jet Black	**NUXFLIR_JB**
DarkGrey	**NUXFLIR_DG**
Dark Bronze	**NUXFLIR_DB**
Antique Brass	**NUXFLIR_AB**

Switches with DND, PCU Symbol – 10 A – 250 V AC

	2G
	
Painted White	**NUX32DMS_PW**
Stainless Steel	**NUX32DMS_SS**
Jet Black	**NUX32DMS_JB**
DarkGrey	**NUX32DMS_DG**
Dark Bronze	**NUX32DMS_DB**
Antique Brass	**NUX32DMS_AB**

Electronic Key Card Switches – 16 A – 250 V AC

	1G
	
Painted White	**NUX31EKT_PW**
Stainless Steel	**NUX31EKT_SS**
Jet Black	**NUX31EKT_JB**
DarkGrey	**NUX31EKT_DG**
Dark Bronze	**NUX31EKT_DB**
Antique Brass	**NUX31EKT_AB**

Momentary Switches – 10 A – 250 V AC

	1G	2G
		
Painted White	**NUX31_PR_PW**	**NUX32_PR_PW**
Stainless Steel	**NUX31_PR_SS**	**NUX32_PR_SS**
Jet Black	**NUX31_PR_JB**	**NUX32_PR_JB**
DarkGrey	**NUX31_PR_DG**	**NUX32_PR_DG**
Dark Bronze	**NUX31_PR_DB**	**NUX32_PR_DB**
Antique Brass	**NUX31_PR_AB**	**NUX32_PR_AB**

Unica X Sockets and USB chargers



Switched Sockets and USB Chargers

Switched Sockets – 6 A – 250 V AC

	1G
	
Painted White	**NUX15_6_PW**
Stainless Steel	**NUX15_6_SS**
Jet Black	**NUX15_6_JB**
DarkGrey	**NUX15_6_DG**
Dark Bronze	**NUX15_6_DB**
Antique Brass	**NUX15_6_AB**

Switched Sockets – 6/16 A – 250 V AC

	1G
	
Painted White	**NUX15_616_PW**
Stainless Steel	**NUX15_616_SS**
Jet Black	**NUX15_616_JB**
DarkGrey	**NUX15_616_DG**
Dark Bronze	**NUX15_616_DB**
Antique Brass	**NUX15_616_AB**

Switched Sockets with USB Chargers – 6 A – 250 V AC, 21 W

	Type A+C
	
Painted White	**NUX15_6TSACQUS_PW**
Stainless Steel	**NUX15_6TSACQUS_SS**
Jet Black	**NUX15_6TSACQUS_JB**
DarkGrey	**NUX15_6TSACQUS_DG**
Dark Bronze	**NUX15_6TSACQUS_DB**
Antique Brass	**NUX15_6TSACQUS_AB**

USB Chargers – 45 W

	Type A+C
Painted White	**NUX32ACQUSB_PW**
Stainless Steel	**NUX32ACQUSB_SS**
Jet Black	**NUX32ACQUSB_JB**
DarkGrey	**NUX32ACQUSB_DG**
Dark Bronze	**NUX32ACQUSB_DB**
Antique Brass	**NUX32ACQUSB_AB**

Unica X Communication Outlets



Communication Outlets

Fuse Connection Units with Flex Outlet, LED Indicator – 13 A – 250 V

	1G 2-pole
	
Painted White	**NUX31DFSGN_PW**
Stainless Steel	**NUX31DFSGN_SS**
Jet Black	**NUX31DFSGN_JB**
DarkGrey	**NUX31DFSGN_DG**
Dark Bronze	**NUX31DFSGN_DB**
Antique Brass	**NUX31DFSGN_AB**

Shuttered Telephone Sockets

	1G
	
Painted White	**NUX31RJ4_PW**
Stainless Steel	**NUX31RJ4_SS**
Jet Black	**NUX31RJ4_JB**
DarkGrey	**NUX31RJ4_DG**
Dark Bronze	**NUX31RJ4_DB**
Antique Brass	**NUX31RJ4_AB**

TV Sockets – 75 Ohm

	1G
	
Painted White	**NUX31TV_PW**
Stainless Steel	**NUX31TV_SS**
Jet Black	**NUX31TV_JB**
DarkGrey	**NUX31TV_DG**
Dark Bronze	**NUX31TV_DB**
Antique Brass	**NUX31TV_AB**

Cat. 6 RJ45 Shuttered Data Sockets

	1G	2G (TV + Data)	2G (Telephone + Data)
			
Painted White	**NUX31RJ6_PW**	**NUX32TVRJ6_PW**	**NUX32TDRJ6_PW**
Stainless Steel	**NUX31RJ6_SS**	**NUX32TVRJ6_SS**	**NUX32TDRJ6_SS**
Jet Black	**NUX31RJ6_JB**	**NUX32TVRJ6_JB**	**NUX32TDRJ6_JB**
DarkGrey	**NUX31RJ6_DG**	**NUX32TVRJ6_DG**	**NUX32TDRJ6_DG**
Dark Bronze	**NUX31RJ6_DB**	**NUX32TVRJ6_DB**	**NUX32TDRJ6_DB**
Antique Brass	**NUX31RJ6_AB**	**NUX32TVRJ6_AB**	**NUX32TDRJ6_AB**

Unica X Cover frames and Accessories



Unica X

Cover Frames and Accessories

Multi Surround Plates

	2G	3G
Painted White	**NUX_21_PW**	**NUX_31_PW**
Stainless Steel	**NUX_21_SS**	**NUX_31_SS**
Jet Black	**NUX_21_JB**	**NUX_31_JB**
DarkGrey	**NUX_21_DG**	**NUX_31_DG**
Dark Bronze	**NUX_21_DB**	**NUX_31_DB**
Antique Brass	**NUX_21_AB**	**NUX_31_AB**

	4G
Painted White	**NUX_41_PW**
Stainless Steel	**NUX_41_SS**
Jet Black	**NUX_41_JB**
DarkGrey	**NUX_41_DG**
Dark Bronze	**NUX_41_DB**
Antique Brass	**NUX_41_AB**

Blank Plates


	1G	2G
Painted White	**NUX30X_PW**	**NUX30TX_PW**
Stainless Steel	**NUX30X_SS**	**NUX30TX_SS**
Jet Black	**NUX30X_JB**	**NUX30TX_JB**
DarkGrey	**NUX30X_DG**	**NUX30TX_DG**
Dark Bronze	**NUX30X_DB**	**NUX30TX_DB**
Antique Brass	**NUX30X_AB**	**NUX30TX_AB**

Unica X Technical Information




Switches


1-way Switch




2-way Switch




1-way Switch with LED Indicator




2-way Switch with LED Indicator




Intermediate Switch



1-way Switch - 4 Gang



2-way Switch - 4 Gang




Note: # represents 1/2/3/4

Technical Information


Connections

Switches


1-way Double Pole Switch




Momentary Switch



2-way Double Pole Switch




Bell Switch




Sockets

Socket




Switched Socket




USB Socket

USB Socket




Technical Information
Connections


Fan Controller



Night Foot Lamp




Bell Switch with DND, PCU Symbol




Key Card Switch

General



Application for Connect Contactor




Technical Information

Dimensions


Switches

Dimensions (mm)


1G Switch




2G Switch




3G Switch




4G Switch




1G Intermediate Switch




2G Intermediate Switch



Panic Buttons with Key Reset



Bell Switches with DND, PCU Indicator




Technical Information
Dimensions


Switches

Dimensions (mm)


Switches with DND, PCU Symbol




1G Fan Control Units with Rotary Knob




1G Universal Push Button Dimmers




2G Universal Push Button Dimmers



1G Night Foot Lamps with LED Indicator and PIR Sensor



1G Electronic Key Card Switches




Technical Information
Dimensions

Double Pole Switches


Dimensions (mm)

1G, Double Pole Switches with LED Indicator – 20 A




Sockets

Shaver Sockets




Switched Sockets and USB Chargers


1G Sockets – 6 A




1G Sockets – 6/16 A



1G Switched Sockets with USB Chargers, Type A+C – 6 A



USB Chargers, Type A+C




Technical Information
Dimensions


Communication Outlets

Dimensions (mm)


Double Pole 1G, Fuse Connection Units with LED Indicator – 13 A




1G TV Sockets




1G Cat. 6 RJ45 Shuttered Data Sockets




2G Cat. 6 RJ45 Shuttered Data Sockets (TV + Data)



2G Cat. 6 RJ45 Shuttered Data Sockets (Telephone + Data)



1G Shuttered Telephone Sockets




Dimensions

Cover Frames and Accessories


Dimensions (mm)

Multi Surround Plates


2G




3G




4G



1G Blank Plates




2G Blank Plates



Technical Information

Dimensions

Product Dimensions (mm)



Ref.	Depth (A) (mm)	Embedding Depth (B) (mm)
NUX31_1_xx	19 mm	27 mm
NUX31_1N_xx	19 mm	27 mm
NUX31_2_xx	19 mm	27 mm
NUX31_2N_xx	19 mm	27 mm
NUX32_1_xx	19 mm	27 mm
NUX32_1N_xx	19 mm	27 mm
NUX32_2_xx	19 mm	27 mm
NUX32_2N_xx	19 mm	27 mm
NUX33_1_xx	19 mm	27 mm
NUX33_1N_xx	19 mm	27 mm
NUX33_2_xx	19 mm	27 mm
NUX33_2N_xx	19 mm	27 mm
NUX34_1_xx	19 mm	27 mm
NUX34_1N_xx	19 mm	27 mm
NUX34_2_xx	19 mm	27 mm
NUX34_2N_xx	19 mm	27 mm
NUX31_BP_xx	19 mm	27 mm
NUX31_IM_xx	19 mm	27 mm
NUX32_IM_xx	19 mm	27 mm
NUX31D20N_xx	19 mm	27 mm
NUX31D32N_xx	21.4 mm	47 mm
NUX31_PR_xx	19 mm	25.5 mm
NUX32_PR_xx	19 mm	25.5 mm
NUX31KPB_xx	27.7 mm	34.3 mm

Ref.	Depth (A) (mm)	Embedding Depth (B) (mm)
NUX31BPDM_xx	28.15 mm	34.65 mm
NUX32DMS_xx	19 mm	25.5 mm
NUX31DFSGN_xx	15 mm	21.5 mm
NUX15_6_XX	20.7	27.5
NUX15_616_XX	24.6	31.1
NUX15_6TSACQUS_XX	25	31.5
NUX32ACQUSB_xx	33.9 mm	40.4 mm
NUXT727V_xx	39.9 mm	43.9 mm
NUX31RJ6_xx	32.1 mm	38.7 mm
NUX31RJ4_xx	25.5 mm	32.1 mm
NUX31TV_xx	15.8 mm	22.5 mm
NUX32TVFMM_xx	18.3 mm	25 mm
NUX32TDRJ6_xx	32.1 mm	38.7 mm
NUX32TVRJ6_xx	32.1 mm	38.7 mm
NUXFLIR_xx	29.1 mm	44.1 mm
NUX31RUD250_xx	30.4 mm	36.9 mm
NUX32RUD250_xx	30.4 mm	36.9 mm
NUX31FR350_xx	32.2 mm	55.7 mm
NUX31EKT_xx	30.2 mm	43.3 mm
NUX_21_xx	–	7.4 mm
NUX_31_xx	–	7.4 mm
NUX_41_xx	–	7.4 mm
NUX30X_xx	–	15 mm
NUX30TX_xx	–	15 mm

Unica X Reference Numbers



Reference Numbers
Overview

Ref.	Page
NUX15_6_AB	13
NUX15_6_DB	13
NUX15_6_DG	13
NUX15_6_JB	13
NUX15_6_PW	13
NUX15_6_SS	13
NUX15_6TSACQUS_AB	13
NUX15_6TSACQUS_DB	13
NUX15_6TSACQUS_DG	13
NUX15_6TSACQUS_JB	13
NUX15_6TSACQUS_PW	13
NUX15_6TSACQUS_SS	13
NUX15_616_AB	13
NUX15_616_DB	13
NUX15_616_DG	13
NUX15_616_JB	13
NUX15_616_PW	13
NUX15_616_SS	13
NUX_21_AB	17
NUX_21_DB	17
NUX_21_DG	17
NUX_21_JB	17
NUX_21_PW	17
NUX_21_SS	17
NUX30TX_AB	17
NUX30TX_DB	17
NUX30TX_DG	17
NUX30TX_JB	17
NUX30TX_PW	17
NUX30TX_SS	17
NUX30X_AB	17
NUX30X_DB	17
NUX30X_DG	17
NUX30X_JB	17
NUX30X_PW	17
NUX30X_SS	17
NUX31_1_AB	7
NUX31_1_DB	7
NUX31_1_DG	7
NUX31_1_JB	7
NUX31_1N_AB	8
NUX31_1N_DB	8
NUX31_1N_DG	8

Ref.	Page
NUX31_1N_JB	8
NUX31_1N_PW	8
NUX31_1N_SS	8
NUX31_1_PW	7
NUX31_1_SS	7
NUX31_2_AB	7
NUX31_2_DB	7
NUX31_2_DG	7
NUX31_2_JB	7
NUX31_2N_AB	8
NUX31_2N_DB	8
NUX31_2N_DG	8
NUX31_2N_JB	8
NUX31_2N_PW	8
NUX31_2N_SS	8
NUX31_2_PW	7
NUX31_2_SS	7
NUX_31_AB	17
NUX31_BP_AB	10
NUX31_BP_DB	10
NUX31_BP_DG	10
NUX31BPDM_AB	11
NUX31BPDM_DB	11
NUX31BPDM_DG	11
NUX31BPDM_JB	11
NUX31BPDM_PW	11
NUX31BPDM_SS	11
NUX31_BP_JB	10
NUX31_BP_PW	10
NUX31_BP_SS	10
NUX31D20N_AB	9
NUX31D20N_DB	9
NUX31D20N_DG	9
NUX31D20N_JB	9
NUX31D20N_PW	9
NUX31D20N_SS	9
NUX31D32N_AB	9
NUX31D32N_DB	9
NUX31D32N_DG	9
NUX31D32N_JB	9
NUX31D32N_PW	9
NUX31D32N_SS	9
NUX_31_DB	17


Ref.	Page
NUX31DFSGN_AB	15
NUX31DFSGN_DB	15
NUX31DFSGN_DG	15
NUX31DFSGN_JB	15
NUX31DFSGN_PW	15
NUX31DFSGN_SS	15
NUX_31_DG	17
NUX31EKT_AB	11
NUX31EKT_DB	11
NUX31EKT_DG	11
NUX31EKT_JB	11
NUX31EKT_PW	11
NUX31EKT_SS	11
NUX31FR350_AB	10
NUX31FR350_DB	10
NUX31FR350_DG	10
NUX31FR350_JB	10
NUX31FR350_PW	10
NUX31FR350_SS	10
NUX31_IM_AB	7
NUX31_IM_DB	7
NUX31_IM_DG	7
NUX31_IM_JB	7
NUX31_IM_PW	7
NUX31_IM_SS	7
NUX_31_JB	17
NUX31KPB_AB	10
NUX31KPB_DB	10
NUX31KPB_DG	10
NUX31KPB_JB	10
NUX31KPB_PW	10
NUX31KPB_SS	10
NUX31_PR_AB	11
NUX31_PR_DB	11
NUX31_PR_DG	11
NUX31_PR_JB	11
NUX31_PR_PW	11
NUX31_PR_SS	11
NUX_31_PW	17
NUX31RJ4_AB	15
NUX31RJ4_DB	15
NUX31RJ4_DG	15
NUX31RJ4_JB	15

Ref.	Page
NUX31RJ4_PW	15
NUX31RJ4_SS	15
NUX31RJ6_AB	15
NUX31RJ6_DB	15
NUX31RJ6_DG	15
NUX31RJ6_JB	15
NUX31RJ6_PW	15
NUX31RJ6_SS	15
NUX31RUD250_AB	10
NUX31RUD250_DB	10
NUX31RUD250_DG	10
NUX31RUD250_JB	10
NUX31RUD250_PW	10
NUX31RUD250_SS	10
NUX_31_SS	17
NUX31TV_AB	15
NUX31TV_DB	15
NUX31TV_DG	15
NUX31TV_JB	15
NUX31TV_PW	15
NUX31TV_SS	15
NUX32_1_AB	7
NUX32_1_DB	7
NUX32_1_DG	7
NUX32_1_JB	7
NUX32_1N_AB	8
NUX32_1N_DB	8
NUX32_1N_DG	8
NUX32_1N_JB	8
NUX32_1N_PW	8
NUX32_1N_SS	8
NUX32_1_PW	7
NUX32_1_SS	7
NUX32_2_AB	7
NUX32_2_DB	7
NUX32_2_DG	7
NUX32_2_JB	7
NUX32_2N_AB	8
NUX32_2N_DB	8
NUX32_2N_DG	8
NUX32_2N_JB	8
NUX32_2N_PW	8
NUX32_2N_SS	8

Reference Numbers
Overview

Ref.	Page
NUX32_2_PW	7
NUX32_2_SS	7
NUX32ACQUSB_AB	13
NUX32ACQUSB_DB	13
NUX32ACQUSB_DG	13
NUX32ACQUSB_JB	13
NUX32ACQUSB_PW	13
NUX32ACQUSB_SS	13
NUX32DMS_AB	11
NUX32DMS_DB	11
NUX32DMS_DG	11
NUX32DMS_JB	11
NUX32DMS_PW	11
NUX32DMS_SS	11
NUX32_IM_AB	7
NUX32_IM_DB	7
NUX32_IM_DG	7
NUX32_IM_JB	7
NUX32_IM_PW	7
NUX32_IM_SS	7
NUX32_PR_AB	11
NUX32_PR_DB	11
NUX32_PR_DG	11
NUX32_PR_JB	11
NUX32_PR_PW	11
NUX32_PR_SS	11
NUX32RUD250_AB	10
NUX32RUD250_DB	10
NUX32RUD250_DG	10
NUX32RUD250_JB	10
NUX32RUD250_PW	10
NUX32RUD250_SS	10
NUX32TDRJ6_AB	15
NUX32TDRJ6_DB	15
NUX32TDRJ6_DG	15
NUX32TDRJ6_JB	15
NUX32TDRJ6_PW	15
NUX32TDRJ6_SS	15
NUX32TVRJ6_AB	15
NUX32TVRJ6_DB	15
NUX32TVRJ6_DG	15
NUX32TVRJ6_JB	15
NUX32TVRJ6_PW	15
NUX32TVRJ6_SS	15
NUX33_1_AB	7
NUX33_1_DB	7
NUX33_1_DG	7
NUX33_1_JB	7
NUX33_1N_AB	8
NUX33_1N_DB	8
NUX33_1N_DG	8
NUX33_1N_JB	8
NUX33_1N_PW	8
NUX33_1N_SS	8
NUX33_1_PW	7
NUX33_1_SS	7
NUX33_2_AB	7
NUX33_2_DB	7
NUX33_2_DG	7
NUX33_2_JB	7
NUX33_2N_AB	8
NUX33_2N_DB	8
NUX33_2N_DG	8
NUX33_2N_JB	8
NUX33_2N_PW	8
NUX33_2N_SS	8
NUX33_2_PW	7
NUX33_2_SS	7
NUX34_1_AB	7
NUX34_1_DB	7
NUX34_1_DG	7
NUX34_1_JB	7
NUX34_1N_AB	8
NUX34_1N_DB	8
NUX34_1N_DG	8
NUX34_1N_JB	8
NUX34_1N_PW	8
NUX34_1N_SS	8
NUX34_1_PW	7
NUX34_1_SS	7
NUX34_2_AB	7
NUX34_2_DB	7
NUX34_2_DG	7
NUX34_2_JB	7
NUX34_2N_AB	8
NUX34_2N_DB	8
NUX34_2N_DG	8
NUX34_2N_JB	8
NUX34_2N_PW	8
NUX34_2N_SS	8
NUX34_2_PW	7
NUX34_2_SS	7
NUX_41_AB	17
NUX_41_DB	17
NUX_41_DG	17
NUX_41_JB	17
NUX_41_PW	17
NUX_41_SS	17
NUXFLIR_AB	11
NUXFLIR_DB	11
NUXFLIR_DG	11
NUXFLIR_JB	11
NUXFLIR_PW	11
NUXFLIR_SS	11
NUXT727V_AB	11
NUXT727V_DB	11
NUXT727V_DG	11
NUXT727V_JB	11
NUXT727V_PW	11
NUXT727V_SS	11

Environmental Data Program




Next-level transparency for better-informed product choices

The Environmental Data Program is a framework for how we measure, categorize, and compare the environmental attributes and footprint of our products.

Using a rigorous, fact-based methodology, the program provides environmental data from across the product lifecycle.

Five data categories across the product lifecycle



Use Better: How sustainable a product is, including environmental footprint, materials and substances, packaging, and energy efficiency.

Use Longer: How a product's life time can be effectively extended in terms of repairability and updatability.

Use Again: How a product can be reused, from dismantling and remanufacturing to recyclability and manufacturer take back.

With this transparent, verified data, customers and partners are empowered to make conscious environmental choices and accurately evaluate and report on sustainability performance.

All our hardware offers have an associated environmental data available on se.com product pages.

Learn more about the Environmental Data Program

Advancing Energy Tech

Schneider Electric Industries SAS

1884 Boulevard de la Défense
92000 Nanterre
France

RCS Nanterre 954 503 439
Capital social 928 298 512 €
www.se.com

08-2026

© 2026 - Schneider Electric. All Rights Reserved.
All trademarks are owned by Schneider Electric Industries SAS or its affiliated companies.
Document reference: LSB03225EN

This document has been
printed on recycled paper