

Step into a new low-carbon and digital reality

EcoFit™ Modernization Services

Greater sustainability

- Efficient use of natural resources by replacing active components
- Recycling of obsolete equipment
- Enabled energy efficiency monitoring

Improved efficiency

- Lifetime extension for existing switchboards
- Unleash the power of connectivity with smart sensors
- Reduced plant shutdown time from days to hours
- No change of cables and no civil work
- Improved safety of people and surrounding equipment

Resiliency with digital capabilities

- Continuous asset condition monitoring
- Remote operation ability
- Access to digital energy management solutions and connected service plans

se.com/ecofit

Benefits

- Maximizing your resiliency, efficiency and safety while minimizing waste for the Planet
- Digitization giving access to energy management
- Enhanced process dependability
- Optimized maintenance service costs
- Spare parts availability to help your repairability program

Expert help from Schneider Electric

- Worldwide support with Schneider Electric's warranty
- Skilled installation and commissioning experts available locally
- Access to the expertise of a global leader in energy management solutions

Schneider Electric

MCSet 1,2,3 up to 17.5 kV / EVOLIS with EasyPact EXE


Original brand: Merlin Gerin, Schneider Electric

EcoFit™ Life Extension Advanced for Electrical Distribution, a true extented life time

EVOLIS17
Circuit Breaker

EasyPact-EXE
Circuit Breaker





Main technical characteristics

	EVOLIS 17
Rated current (Ir)	630 A – 2500 A
Short circuit current (Isc)	31.5 kA-3s
Rated voltage Un (50/60 Hz)	17.5 kV

	EasyPact EXE
Technology	Vacuum
Rated voltage Ur (kV)	Up to 17.5
Surge withstand voltage Up (kV)	Up to 95
Nominal frequency (Hz)	50-60
Rated current Ir (A)	630-2500
Short circuit current Isc (kA)	31.5
Short circuit duration Tk (s)	3
Versions available	12kV / 1250A / 31.5kA - 570mm - 145mm Ph to Ph 17.5kV / 1250A / 31.5kA - 700mm - 185mm Ph to Ph 17.5kV / 2500A / 31.5kA - 900mm - 240mm Ph to Ph

	EasyPact EXE
Switching sequence	O-3mn-CO-3mn-CO O-0.3s-CO-3mn-CO O-0.3s-CO-15s-CO
Closing time (ms)	<65
Opening time (ms)	<50
Number of switching operations	10000
Service temperature (°C)	-25/+40

Make the most of your equipment with available add-ons



Protection Relays
Easergy Px, Sepam, MiCom

MONITORING

SUSTAINABILITY

EcoFit™ Recover
Raw material recovery



EcoFit™ Life Extension
Essential for Power
T°, Humidity, Arc Flash

DIGITAL



Schneider Electric Industries SAS
1884 Boulevard de la Défense
92000 Nanterre, France
Phone: + 00 (0) 1 41 29 70 00
www.se.com/services

SERED21064EN
© 2026 Schneider Electric SE. All rights reserved. All Schneider Electric trademarks and service marks are the property of Schneider Electric SE, its subsidiaries and affiliated companies.