設備名稱：Equipment name 無熔線斷路器 ，型號（型式）：Type designation (Type) Muti9 C60 1P 63AF 60Hz C Curve, 額定電流1A, 2A, 3A, 4A, 6A, 8A, 10A, 16A, 20A, 25A, 32A, 40A Icu:10kA at AC110V, Ics:75%Icu

系列型號：詳如附件

單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛Lead (Pb)	汞Mercury (Hg)	鎘 Cadmium (Cd)	六價鉻 Hexavalent chromium (Cr^{+6})	多溴聯苯 Polybrominated biphenyls (PBB)	多溴二苯醚 Polybrominated diphenyl ethers (PBDE)
1.電磁線圈	○	○	○	○	○	○
2.固定主接點	○	○	○	○	○	○
3.端子接點連接片	○	○	○	○	○	○
4.連動機構	○	○	○	○	○	○
5.軟銅帶	○	○	○	○	○	○
6.可動主接點	○	○	○	○	○	○
7.端子接點連接片（近線端）	○	○	○	○	○	○
8.消弧接點	○	○	○	○	○	○
9.消弧室	○	○	○	○	○	○

備考1.〝超出0.1 wt %〞及〝超出0.01 wt %〞係指限用物質之百分比含量超出百分比含量基準值。
Note 1："Exceeding 0.1 wt %" and "exceeding 0.01 wt %" indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.

備考2.〝○〞係指該項限用物質之百分比含量未超出百分比含量基準值。
Note 2："○" indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.

備考3.〝—〞係指該項限用物質為排除項目。
Note 3：The "–" indicates that the restricted substance corresponds to the exemption.

附表:

系列型式:

1. Muti9 C60 1P 63AF 60Hz D Curve,額定電流
1A,2A,3A,4A,6A,8A,10A,16A,20A,25A,32A,40A Icu:10kA at AC110V, Ics:75%Icu
2. Muti9 C60 1P 63AF 60Hz C Curve,額定電流
1A,2A,3A,4A,6A,8A,10A,16A,20A,25A,32A,40A Icu:10kA at AC220V, Ics:75%Icu
3. Muti9 C60 1P 63AF 60Hz D Curve,額定電流
1A,2A,3A,4A,6A,8A,10A,16A,20A,25A,32A,40A Icu:10kA at AC220V, Ics:75%Icu
4. Muti9 C60 1P 63AF 60Hz C Curve,額定電流
1A,2A,3A,4A,6A,8A,10A,16A,20A,25A,32A,40A Icu:10kA at AC220V, Ics:75%Icu
5. Muti9 C60 1P 63AF 60Hz D Curve,額定電流
1A,2A,3A,4A,6A,8A,10A,16A,20A,25A,32A,40A Icu:10kA at AC220V, Ics:75%Icu

(以下空白)