限用物質含有情況標示聲明書

Declaration of the Presence Condition of the Restricted Substances Marking

證書號碼／受理編號：(No.) TA102341140127 / TA103341140196 / TA104341140208 / TA104341140219

Certificate No. / Application No.

商品標籤及商品檢驗標識：(Picture)

Product Label and Commodity Inspection Mark.

Sample and its location

設備名稱：無熔絲斷路器，型號（型式）：CVS (詳細系列型號請參見次頁)

Equipment name　　Type designation (Type)

單元Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛Lead (Pb)	汞Mercury (Hg)	鎘Cadmium (Cd)	六價鉻 Hexavalent chromium (Cr^{+6})	多溴聯苯 Polybrominated biphenyls (PBB)	多溴二苯醚 Polybrominated diphenyl ethers (PBDE)
金屬零件 (metal parts)	—	O	O	O	O	O
塑膠零件 (plastic parts)	O	O	O	O	O	O
接點 (contacts)	O	O	O	O	O	O
線材和線材附件(cables & cabling accessories)	O	O	O	O	O	O

備考1.〝超出0.1 wt %〞及〝超出0.01 wt %〞係指限用物質之百分比含量超出百分比含量基準值。

Note 1：“Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.

備考2.〝○〞係指該項限用物質之百分比含量未超出百分比含量基準值。

Note 2：“○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.

備考3.〝—〞係指該項限用物質為排除項目。

Note 3：The “–” indicates that the restricted substance corresponds to the exemption.

樣張及其標示位置：(Description and Picture)

CVS250B 3P 60Hz AF:250A AT:160-200-250A
Icu=40kA@220V Icu=25kA@380V Icu=100%Ics

Easypact CVS250B 4P 60Hz 250AF 160A, 200A,250A
Icu:40kA at 220V; 25kA at 380V Ics:40kA at 220V; 25kA at380V

Easypact CVS400F 3P 60Hz 400AF 320-400AT（可調整）Icu=40kA at 200V; 36kA at 380V; 30kA at 440V Ics=40kA at 200V; 36kA at 380V; 23kA at 440V

Easypact CVS400F 4P 60Hz 400AF 320-400AT（可調整）Icu=40kA at 200V; 36kA at 380V; 30kA at 440V Ics=40kA at 200V; 36kA at 380V; 23kA at 440V

Easypact CVS630F 3P 60Hz AF:600AF 500-600AT（可調整）Icu=40kA at 200V; 36kA at 380V; 30kA at 440V Ics=40kA at 200V; 36kA at 380V; 23kA at 440V

Easypact CVS630F 4P 60Hz AF:600AF 500-600AT（可調整）Icu=40kA at 200V; 36kA at 380V; 30kA at 440V Ics=40kA at 200V; 36kA at 380V; 23kA at 440V