








Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

CA3KN22ED

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Rating:	A600, Q600 10A
UL File/CCN:	E164353 / NKCR
CSA File:	LR43364 3211 03
Meets Standards:	IEC 60647-1-1
Weight:	0.50 lb (0.19 kg)
Termination Method:	Screw Clamp
Wire Size:	#12 - #18 AWG
Terminal torque:	7 lb-in (0.8 Nm)
Mounting Hwd.:	35mm DIN Rail, 4mm screw

Specification:

Description	TeSys K IEC Control Relay - 2NO,2NC
Type	TeSys K IEC Control Relay - 10A - 48Vdc Coil
Voltages Code:	ED at 48VDC
Coil Consumption:	Inrush 3 W
	Sealed 3W