

ML2164 - Flush Metal Plate - Accessories



All additional items to be incorporated into the Medical Service Panel eg. nurse call system , gas system, data, and lighting control etc shall be based on the Clipsal 2000 Series format.

Electrical Accessories (ACC)	
Grid Plates	
2031VH	1 gang grid
2032VH	2 gang grid
2033VH	3 gang grid
2034VH	4 gang grid
2035VH	5 gang grid
2036VH	6 gang grid
Dimmers	
Dimmer Mech	Dimmer Mech - 32 Series
Dimmer	Dimmer - 2031 Series
Mechs	
30M	Switch mech
30P-ID	Circuit ID mech
30P	Plug mech
30RJ	Data and phone socket mech
30TV	TV mech
N01	Power Available Neon
Equipotential Earthing (EP)	
Studs	
ML2031VR01	Single gang, vertical, EP stud
ML2032VR02	Double gang, vertical, EP stud
ML2031R01	Single gang, horizontal, EP stud
ML2032R02	Double gang, horizontal, EP stud

Single Facias (EP Junction)	
ML2164E35	EP Junction facia 150mm(H) x 280mm(W) - Suit 3 gang wall box
Multiple Facias (EP Junction)	
ML2164E35-L	EP Junction facia 150mm(H) x 266mm(W) Left
ML2164E35-M	EP Junction facia 150mm(H) x 252mm(W) Middle
ML2164E35-R	EP Junction facia 150mm(H) x 266mm(W) Right
Gas Outlets	
ML2031GAS	2000 series gas outlet, horizontal
ML2031VGAS	2000 series gas outlet, vertical
CWGAS	Comweld Gas outlet (69mm)
CWSUC	Comweld Gas outlet (69mm) with extra hole for venturi suction
ESCOGAS	ESCO Gas outlet (51mm)
ESCOSCAV-SUC	ESCO Gas outlet (51mm) with extra hole for venturi suction
Socket Outlets (GPO-Clipsal)	
Vertical	
2015V	Single gang power outlet, vertical, 250V, 10A
2015VD	Single gang double pole power outlet, vertical, 250V, 10A
2015VXUA	Single gang power outlet, vertical, extra unused aperture, 250V, 10A
2025V	Double gang power outlet, vertical, 250V, 10A
2015D2V	Double gang double pole power outlet, vertical, 250V, 10A
2025VXUA	Double gang power outlet, vertical, extra unused aperture, 250V, 10A
Horizontal	
2015	Single gang power outlet, horizontal, 250V, 10A
2015D	Single gang double pole power outlet, horizontal, 250V, 10A
2015XUA	Single gang power outlet, horizontal, extra unused aperture, 250V, 10A
2025	Double gang power outlet, horizontal, 250V, 10A
2025XUA	Double gang power outlet, horizontal, extra unused aperture, 250V, 10A
Socket Outlets (GPO-Medilec)	
Vertical	
ML2015V	Single gang power outlet, vertical, amber power available neon, RCD label, 250V, 10A

ML2015VI	Single gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2015-15VI	Single gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 15A
ML2015VD	Single gang double pole power outlet, vertical, Isolated label, 250V, 10A Double gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2015VDI	Single gang double pole power outlet, vertical, Isolated label, circuit identification, 250V, 10A
ML2025V	Double gang power outlet, vertical, amber power available neon, RCD label, 250V, 10A
ML2025VI	Double gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2025VD	Double gang double pole power outlet, vertical, Isolated label, 250V, 10A
Horizontal	
ML2015	Single gang power outlet, horizontal, amber power available neon, RCD label, 250V, 10A
ML2015I	Single gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2015-15I	Single gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 15A
ML2015D	Single gang double pole power outlet, horizontal, power neon, Isolated label, 250V, 10A
ML2025	Double gang power outlet, horizontal, amber power available neon, RCD label, 250V, 10A
ML2025I	Double gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 10A
Metal (Single Facia)	
Facias (Standard)	
ML2164-1-F	1 gang 2000 series facia 150mm(H) x 136mm(W)
ML2164-2-F	2 gang 2000 series facia 150mm(H) x 208mm(W)
ML2164-3-F	3 gang 2000 series facia 150mm(H) x 280mm(W)
ML2164-4-F	4 gang 2000 series facia 150mm(H) x 352mm(W)
ML2164-5(1+4)-F	5 gang 2000 series facia 150mm(H) x 460mm(W)
ML2164-5(2+3)-F	5 gang 2000 series facia 150mm(H) x 460mm(W)
ML2164-5(3+2)-F	5 gang 2000 series facia 150mm(H) x 460mm(W)
ML2164-5(4+1)-F	5 gang 2000 series facia 150mm(H) x 460mm(W)
ML2164-6(2+4)-F	6 gang 2000 series facia 150mm(H) x 532mm(W)

ML2164-6(3+3)-F	6 gang 2000 series facia 150mm(H) x 532mm(W)
ML2164-6(4+2)-F	6 gang 2000 series facia 150mm(H) x 532mm(W)
ML2164-7(3+4)-F	7 gang 2000 series facia 150mm(H) x 604mm(W)
ML2164-7(4+3)-F	7 gang 2000 series facia 150mm(H) x 604mm(W)
ML2164-8(4+4)-F	8 gang 2000 series facia 150mm(H) x 676mm(W)
Facias (Gas)	
ML2164-1-GF	1 gang gas facia 150mm(H) x 136mm(W) - Suit 1 gang wall box
ML2164-2-GF	2 gang gas facia 150mm(H) x 280mm(W) - Suit 3 gang wall box
ML2164-3-GF	3 gang gas facia 150mm(H) x 352mm(W) - Suit 4 gang wall box
ML2164-4(2+2)-GF	4 gang gas facia 150mm(H) x 532mm(W)
ML2164-5(2+3)-GF	5 gang gas facia 150mm(H) x 604mm(W)
ML2164-5(3+2)-GF	5 gang gas facia 150mm(H) x 604mm(W)
ML2164-6(3+3)-GF	6 gang gas facia 150mm(H) x 676mm(W)
Metal (Multiple Facias)	
Facias (Standard)	
ML2164-1-F-L	1 gang 2000 series facia 150mm(H) x 122mm(W) Left
ML2164-1-F-M	1 gang 2000 series facia 150mm(H) x 108mm(W) Middle
ML2164-1-F-R	1 gang 2000 series facia 150mm(H) x 122mm(W) Right
ML2164-2-F-L	2 gang 2000 series facia 150mm(H) x 194mm(W) Left
ML2164-2-F-M	2 gang 2000 series facia 150mm(H) x 180mm(W) Middle
ML2164-2-F-R	2 gang 2000 series facia 150mm(H) x 194mm(W) Right
ML2164-3-F-L	3 gang 2000 series facia 150mm(H) x 266mm(W) Left
ML2164-3-F-M	3 gang 2000 series facia 150mm(H) x 252mm(W) Middle
ML2164-3-F-R	3 gang 2000 series facia 150mm(H) x 266mm(W) Right
ML2164-4-F-L	4 gang 2000 series facia 150mm(H) x 324mm(W) Left
ML2164-4-F-M	4 gang 2000 series facia 150mm(H) x 310mm(W) Middle
ML2164-4-F-R	4 gang 2000 series facia 150mm(H) x 324mm(W) Right
ML2164-5(1+4)-F-L	5 gang 2000 series facia 150mm(H) x 446mm(W) Left
ML2164-5(1+4)-F-M	5 gang 2000 series facia 150mm(H) x 432mm(W) Middle
ML2164-5(1+4)-F-R	5 gang 2000 series facia 150mm(H) x 446mm(W) Right
ML2164-5(2+3)-F-L	5 gang 2000 series facia 150mm(H) x 446mm(W) Left
ML2164-5(2+3)-F-M	5 gang 2000 series facia 150mm(H) x 432mm(W) Middle
ML2164-5(2+3)-F-R	5 gang 2000 series facia 150mm(H) x 446mm(W) Right
ML2164-5(3+2)-F-L	5 gang 2000 series facia 150mm(H) x 446mm(W) Left

ML2164-5(4+1)-F-M	5 gang 2000 series facia 150mm(H) x 432mm(W) Middle
ML2164-5(4+1)-F-R	5 gang 2000 series facia 150mm(H) x 446mm(W) Right
ML2164-6(2+4)-F-L	6 gang 2000 series facia 150mm(H) x 518mm(W) Left
ML2164-6(2+4)-F-M	6 gang 2000 series facia 150mm(H) x 504mm(W) Middle
ML2164-6(2+4)-F-R	6 gang 2000 series facia 150mm(H) x 518mm(W) Right
ML2164-6(3+3)-F-L	6 gang 2000 series facia 150mm(H) x 518mm(W) Left
ML2164-6(3+3)-F-M	6 gang 2000 series facia 150mm(H) x 504mm(W) Middle
ML2164-6(3+3)-F-R	6 gang 2000 series facia 150mm(H) x 518mm(W) Right
ML2164-6(4+2)-F-L	6 gang 2000 series facia 150mm(H) x 518mm(W) Left
ML2164-6(4+2)-F-M	6 gang 2000 series facia 150mm(H) x 504mm(W) Middle
ML2164-6(4+2)-F-R	6 gang 2000 series facia 150mm(H) x 518mm(W) Right
ML2164-7(3+4)-F-L	7 gang 2000 series facia 150mm(H) x 590mm(W) Left
ML2164-7(3+4)-F-M	7 gang 2000 series facia 150mm(H) x 576mm(W) Middle
ML2164-7(3+4)-F-R	7 gang 2000 series facia 150mm(H) x 590mm(W) Right
ML2164-7(4+3)-F-L	7 gang 2000 series facia 150mm(H) x 590mm(W) Left
ML2164-7(4+3)-F-M	7 gang 2000 series facia 150mm(H) x 576mm(W) Middle
ML2164-7(4+3)-F-R	7 gang 2000 series facia 150mm(H) x 590mm(W) Right
ML2164-8(4+4)-F-L	8 gang 2000 series facia 150mm(H) x 662mm(W) Left
ML2164-8(4+4)-F-M	8 gang 2000 series facia 150mm(H) x 648mm(W) Middle
ML2164-8(4+4)-F-R	8 gang 2000 series facia 150mm(H) x 662mm(W) Right
Facias (Gas)	
ML2164-1-GF-L	1 gang gas facia 150mm(H) x 122mm(W) Left
ML2164-1-GF-M	1 gang gas facia 150mm(H) x 108mm(W) Middle
ML2164-1-GF-R	1 gang gas facia 150mm(H) x 122mm(W) Right
ML2164-2-GF-L	2 gang gas facia 150mm(H) x 266mm(W) Left
ML2164-2-GF-M	2 gang gas facia 150mm(H) x 252mm(W) Middle
ML2164-2-GF-R	2 gang gas facia 150mm(H) x 266mm(W) Right
ML2164-3-GF-L	3 gang gas facia 150mm(H) x 324mm(W) Left
ML2164-3-GF-M	3 gang gas facia 150mm(H) x 310mm(W) Middle
ML2164-3-GF-R	3 gang gas facia 150mm(H) x 324mm(W) Right
ML2164-4(2+2)-GF-L	4 gang gas facia 150mm(H) x 518mm(W) Left
ML2164-4(2+2)-GF-M	4 gang gas facia 150mm(H) x 504mm(W) Middle
ML2164-4(2+2)-GF-R	4 gang gas facia 150mm(H) x 518mm(W) Right
ML2164-5(2+3)-GF-L	5 gang gas facia 150mm(H) x 590mm(W) Left

ML2164-5(2+3)-GF-M	5 gang gas facia 150mm(H) x 576mm(W) Middle
ML2164-5(2+3)-GF-R	5 gang gas facia 150mm(H) x 590mm(W) Right
ML2164-5(3+2)-GF-L	5 gang gas facia 150mm(H) x 590mm(W) Left
ML2164-5(3+2)-GF-M	5 gang gas facia 150mm(H) x 576mm(W) Middle
ML2164-5(3+2)-GF-R	5 gang gas facia 150mm(H) x 590mm(W) Right
ML2164-6(3+3)-GF-L	6 gang gas facia 150mm(H) x 662mm(W) Left
ML2164-6(3+3)-GF-M	6 gang gas facia 150mm(H) x 648mm(W) Middle
ML2164-6(3+3)-GF-R	6 gang gas facia 150mm(H) x 662mm(W) Left
Nurse Call	
Vertical	
ML2031VC	Call point - vertical
ML2031VEC	Emergency call point - vertical
ML2031VSA	Staff Assist call point - vertical
ML2031VP	Pendant outlet - vertical
ML2031VENT	Entertainment outlet - vertical
Horizontal	
ML2031C	Call point - horizontal
ML2031EC	Emergency call point - horizontal
ML2031SA	Staff Assist call point - horizontal
ML2031P	Pendant outlet - horizontal
ML2031ENT	Entertainment outlet - horizontal
RCD	
ML2031VRC10	Single gang double pole, vertical, 250V, 20A, 10mA RCD
ML2031RC10	Single gang double pole, horizontal, 250V, 20A, 10mA RCD
Tech items	
ML2164JT	Wall box joining tray 2400mm
ML2164S	Segregation (2 part) for Wallbox & Grid
Example Panels	
ML2164-A	RCD, Double Switched Socket, Light Switch, Dimmer, Nurse Call
ML2164-B	3 x Gas Outlets
ML2164-C	RCD, Audible Alarm, 2 x Double Switched Sockets, Light Switch, Dimmer, Data Outlet, Blank, 2 x Gas outlet