
CODE (1)	CONTACTS	TIMING RANGE	TYPE	VOLTAGE (V)
2E	SPDT	1 TO 30 SEC,	ON-DELAY	24 TO 48V a.c. OR d.c.
2U	SPDT	1 TO 30 SEC.	ON-DELAY	110 TO 240V a.c.

Relay outputs, with single pole double throw contact, 240V ac/dc, 2 A maximum
Control voltage, from 0.85 to 1.1 Uc.
Maximum switching capacity 250 VA / 150 W
Operating temperature: -10 to +60 C (14 to 140 F)
Reset time: 1.5 s during time delay, 0.5 after time delay

Direct mounting on the mini-contactor



Catalog Number: LA2 KT(1)
Ratings: SEE CHART
UL File/Guide: -
CSA File/Guide: -
Meets Standards: -
Weight: -
Wire Size: SEE CHART
Terminal torque: -
Mounting Hwd.: CLIP-ON FRONT MOUNTING

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

DO NOT SCALE DRAWING
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION

TOLERANCES
UNLESS OTHERWISE SPECIFIED
2 PLACE DECIMALS ± .01

IEC AUX TIME DELAY BLOCK (K-LINE)
LA2 KT(1)

SQUARE D COMPANY

DWG# NO. E0211101-01