

Carcass / Floor outlet box

INS62045


Earthing

Ensure continuity of the earth is maintained throughout the installation.


All metal parts must be earthed according to AS/NZS3000 wiring regulations.




Fix the Carcass into the floor




Fix the Module and Metal Caddy into Carcass





Fix the Socket Module and Plastic Box into Carcass




Fix the Data-Socket Module and Plastic Box into Carcass



Remove





1/ 80g high quality uncoated paper (white).

2/ Double side printing.



Tolerance Standard		
For unspecification dimension on artwork		
Dimension	Value	Tolerance
00.00		± 0.05
00.0	$a \leq 3.0$	± 0.3
	$3.0 \leq a \leq 10.0$	± 0.5
	$10.0 \leq a \leq 800.0$	± 0.8
	$800.0 \leq a$	± 1.5

ECN201504495	Content change, 2015/07/14	Givi.Li	02
DECN201413184	▲01x0, Content change, 2014/11/20	Givi.Li	01
DECN201411814	Initial Release, 2014/02/25	Givi.Li	00
DECN/ECN/TCAN	DESCRIPTION	DRN	REV

	Scale :	Tolerancing Standard :	Units of measure :	
	FREE	N/A	Millimeter	
	MANUAL: Optiline 70, Carcass			
	Number :		Revision :	Sheet :
EAV5537901		02	1 / 1	

The information is highly confidential and is the exclusive property of Schneider Electric Group copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing. This drawing must be returned to the owners when the purpose has ceased.

State :