






Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:
LC1D40AD7

Schneider Electric
Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 40A
UL File/CCN: E164862 / NLDX
CSA File: LR43364 3211 04
Meets Standards: IEC 60647-4
Weight: 2.28 lb (0.850 kg)
Termination Method: Screw Clamp
Wire Size: Power: #2 - #16 AWG
Control: #12 - #20 AWG
Terminal torque: Power: 70 lb-in (8 Nm)
Control: 8 lb-in (0.9 Nm)
Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor New Type with Everlink® - 40A - Vac Coil
Type: TeSys D IEC Contactor - 40A - 42Vac Coil
Voltages Code: D7 at 42Vac 50/60 Hz

Coil Consumption: Inrush 160 VA
Sealed 15 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
3 HP	5 HP	10 HP	10 HP	30 HP	30 HP