





Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

# LC1D40AQ7

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

## Technical Information:

| | |
|---|---|
| Rating: | 600V / 40A |
| UL File/CCN: | E164862 / NLDX |
| CSA File: | LR43364 3211 04 |
| Meets Standards: | IEC 60647-4 |
| Weight: | 2.28 lb (0.850 kg) |
| Termination Method: | Screw Clamp |
| Wire Size: | Power: #2 - #16 AWG<br>Control: #12 - #20 AWG |
| Terminal torque: | Power: 70 lb-in (8 Nm)<br>Control: 8 lb-in (0.9 Nm) |
| Mounting Hwd.: | 35mm DIN Rail, #8 screw |

## Specification:

| | |
|---|---|
| Description | TeSys D IEC Contactor New Type with Everlink® - 40A - Vac Coil |
| Type | TeSys D IEC Contactor - 40A - 380Vac Coil |
| Voltages Code: | Q7 at 380Vac 50/60 Hz |
| Coil Consumption: | Inrush 160 VA<br>Sealed 15 VA |

| Single Phase | | Three Phase | | | |
|---|---|---|---|---|---|
| 115V | 230V | 200V | 230V | 460V | 575V |
| 3 HP | 5 HP | 10 HP | 10 HP | 30 HP | 30 HP |