








Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LC1D40AR7

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Rating:	600V / 40A
UL File/CCN:	E164862 / NLDX
CSA File:	LR43364 3211 04
Meets Standards:	IEC 60647-4
Weight:	2.28 lb (0.850 kg)
Termination Method:	Screw Clamp
Wire Size:	Power: #2 - #16 AWG Control: #12 - #20 AWG
Terminal torque:	Power: 70 lb-in (8 Nm) Control: 8 lb-in (0.9 Nm)
Mounting Hwd.:	35mm DIN Rail, #8 screw

Specification:

Description	TeSys D IEC Contactor New Type with Everlink® - 40A - Vac Coil
Type	TeSys D IEC Contactor - 40A - 440Vac Coil
Voltages Code:	R7 at 440Vac 50/60 Hz
Coil Consumption:	Inrush 160 VA Sealed 15 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
3 HP	5 HP	10 HP	10 HP	30 HP	30 HP