

UK DECLARATION OF CONFORMITY



We: **Manufacturer**
Schneider Electric Japan Holdings Ltd.
Subsidiary of SCHNEIDER ELECTRIC INDUSTRIES SAS (1884 Bd de la Défense, FR-92000 Nanterre)
4-4-9 Kitahama, Chuo-ku, Osaka, 541-0041 Japan

UK Representative
Schneider Electric Limited
Stafford Park 5
Telford, TF3 SBL - United Kingdom

Hereby declare under our sole responsibility that the products:

Trademark	Pro-face 
Product, Type, Function	Human Machine Interface / Industrial Controller
Models	PS6000 Basic, see detailed list of references
Serial Number	PPYYWWZZZZZ (PP = Plant Code; YY = Year; WW = Week; ZZZZZ = digits from 0 to 9)


are in conformity with the requirements of the following directives and conformity was checked in accordance with the following standards:

Regulation	Designated standard / Notified body reference
Electromagnetic compatibility regulation (EMC) SI 2016 No.1091	EN 61131-2:2007 Programmable controllers - Part 2: Equipment requirements and tests Other standard considered: IEC 61131-2:2017
RoHS regulation SI 2012 No. 3032	EN IEC 63000:2018 Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions, user manual and to accepted rules of the art.

Issued at:
Telford – United Kingdom: September 1st, 2026

Name:

Signed by:

A578D60923D7459...
David WILLIAMS
VP Marketing UK&I – Zone UK & Ireland

UK DECLARATION OF CONFORMITY

List of references

Digit	1-5	6	7	8	9	10	11	12	13	14	15	16	17	18
Range	PFXP6													
CPU	Atom 2 Core	A												
	Atom 2 Core	B												
	Atom 4 Core	D												
Display	None (Box Module)	B												
	12"	6												
	15"	7												
	10" Wide	D												
	12" Wide	E												
	15" Wide	F												
	15" Wide (FHD)	K												
	19" Wide	G												
	22" Wide	A												
Power	12-24 Vdc		B											
Slot	None				0									
Fan	None					N								
Main storage	See user manual. "*" Any letter or number						*							
Secondary storage	None							0						
	See user manual. "*" Any letter or number						*							
Memory	See user manual. "*" Any letter or number								*					
Options	None									N				
	RS-232C isolated x 2									H				
	RS-422/485 isolated x 2									J				
	Ethernet (GbE IEEE 1588) x 1									K				
OS	See user manual. "*" Any letter or number										*			
Software	See user manual. "*" Any letter or number											*		
Reserved	"*" Any letter or number												*	*

List of options and accessories

Commercial Reference	Description
Interface	
PFXYP6M2R23P2	RS-232C isolated x 2
PFXYP6M2R42P2	RS422/485 isolated x 2
PFXYP6M2ETH	Ethernet (GbE IEEE 1588)
PFXYP6M24GW	4G Cellular for Global
PFXYP6M2WF	WiFi/Bluetooth
Storage	
PFXYP6M2128L	M.2 SSD 128 GB (Standard Endurance)
PFXYP6M2128	M.2 SSD 128 GB (High Endurance)
PFXYP6M2256	M.2 SSD 256 GB (High Endurance)
PFXYP6M2512	M.2 SSD 512 GB (High Endurance)
PFXYP6SD64GCX	SD Memory Card 64 GB
Memory	
PFXYP6DM4	DIMM 4 GB

UK DECLARATION OF CONFORMITY



PFXYP6DM8	DIMM 8 GB
PFXYP6DM16	DIMM 16 GB
Cable	
PFXYP6CB4G3M	4G Cellularh extended antenna cable 3 m (2 pcs)
PFXYP6CBWF3M	WiFi/Bluetooth extended antenna cable 3 m (2 pcs)
PFXFPCBDPDV5M	DP-DVI Cable 5m
CA5-USBEXT-01	USB Front Cable
PFXYP6CVUSAU	USB Audio Cable
Others	
PFXYP6HSM2B	M.2 cooling kit
PFXYP6RUSW10B	Recovery USB for Windows 10