








Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

# CAD50MD

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

## Technical Information:

| | |
|---|---|
| Rating: | A600, Q600 10A |
| UL File/CCN: | E164862 / NKCR |
| CSA File: | LR43364 3211 03 |
| Meets Standards: | IEC 60647-5 |
| Weight: | 1.28 lb (0.58 kg) |
| Termination Method: | Screw Clamp |
| Wire Size: | #10 - #18 AWG |
| Terminal torque: | 15 lb-in (1.7 Nm) |
| Mounting Hwd.: | 35mm DIN Rail, #8 screw |

## Specification:

| | |
|---|---|
| Description | TeSys D IEC Control Relay - 5NO - Vdc Coil |
| Type | TeSys D IEC Control Relay - 5NO - 220Vdc Coil |
| Voltages Code: | MD at 220Vdc |
| Coil Consumption: | Inrush 5.4 W |
| | Sealed 5.4 W |