
Optiline 70 Posts



Post

1. Base profile
2. Partition profile
3. Front cover
4. Floor fixing
5. Gasket ring
6. Stop end
7. Power/data shroud
8. Earthing kit

Floor feeding system

9. Floor fixing with slot for aluminium floor feeder
10. Aluminium floor feeder
    10a. Base profile
    10b. Cover
11. Floor fixing with slot for PVC floor feeder
12. PVC Floor feeder
    12a. Base profile
    12b. Cover
13. Floor feeder jointing piece
14. Corner feeder piece

■ Items provided in base unit

OptiLine 70 Posts Cable Capacity

Compartment	Max. Ø mm	Cross section area mm²	Cable capacity* mm²			
			40%	50%	60%	
One-sided post						
1	21	1418	567	709	851	
2	26	905	362	452	543	
3	36	2207	883	1103	1324	
Two-sided post						
1	42	4980	1992	2490	2988	
2	23	1471	588	735	883	
3	26	900	360	450	540	
4	38	2253	901	1126	1352	

*We recommend a 40% utilisation of the cable capacity.









OptiLine 70 Posts	OptiLine 70 Posts (Single Sided)		OptiLine 70 Posts (Double Sided)	
Height 333mm. Anodised.	ISM20600		ISM20606	
Height 613mm. Anodised.		ISM20603		ISM20609
Accessories				
OptiLine 70 Partition Profile	ISM20555 (White. 49x50x500mm. 10 per pack)			
Floor fixing, w. floor feeder slot	ISM20650 (For 18x91mm floor feeder)		ISM20651 (For 18x91mm floor feeder)	
Floor fixing, w. floor feeder slot	ISM20652 (For 18x75mm floor feeder)		ISM20653 (For 18x75mm floor feeder)	
OptiLine 70 Poles Front Cover	ISM11950 (2.0m length, 12 per pack)			
OptiLine 70 Power/Data Shroud	MDEOLSPTD			
OptiLine 70 Decorative Stripe	(5.0m length, 1 per pack)			
Grey	ISM200822			
White	ISM200823			
Orange	ISM200824			
OptiLine Earthing Clamp	ISM10952 (20 per pack)			
OptiLine Earthing Kit - 200mm	ISM10953 (10 per pack)			
OptiLine Earthing Kit - 300mm	ISM10954 (10 per pack)			
OptiLine Al. Floor Feeder	ISM20660 (Anodised. 18x91x2500mm. 1 per pack)			
OptiLine Al. Floor Feeder	ISM20857 (Anodised. 18x75x2000mm. 4 per pack)			
OptiLine PVC Floor Feeder	ISM20817 (Grey. 18x75x2000mm. 14 per pack)			
OptiLine PVC Floor Feeder Joint	ISM20818 (Grey. 20x50x78mm. 10 per pack)			
OptiLine PVC Corner Feeder Pce	ISM20819 (Grey. 20x120x120mm. 10 per pack)			

Clipsal Cable Management invites Architects and Engineers to avail themselves of our obligation free advisory and design drafting service to assist with planning the most economical and functional duct system suitable for a particular project. Any infringements to patents or registered designs applied for or granted will be liable to prosecution.