Technical Data Sheet

CLIPSAL by Schneider Electric

ML2025VD Medilec Twin Vertical Double Pole Socket

Specifications

250Vac input
10A per socket
Double pole



The ML2000 range of socket outlets are based on the Clipsal 2000 range of socket outlets with modifications to suit the requirements of AS/NZS3003. The ML2025VD twin sockets feature double pole mechanisms and marking to make them suitable for installation linked with isolated power supplies. These power supplies may be normal (white sockets), essential (red sockets) or backed by UPS (blue sockets).

Applications

Specifically designed for application in Cardiac Protected Areas as required by AS/NZS3003:2011 Electrical Installations – Patient Areas of Hospitals, Medical and Dental Practices and Dialyzing Locations. They can be used as standalone sockets, included in medical panels or embedded in medical pendants.

Features


- Based on standard 2000 series footprint
- Double pole as required in Cardiac Protected Areas in AS/NZS3003
- Available in White, Red and Dark Blue colours
- 10A rating per socket
- Pre-labelled with “Isolating Transformer Protected” as required under AS/NZS3003

Ordering Details

Catalogue No.	Description
ML2025VD-WE	2000 Series Twin Vertical Double Pole GPO in white
ML2025VD-RD	2000 Series Twin Vertical Double Pole GPO in red
ML2025VD-DB	2000 Series Twin Vertical Double Pole GPO in dark blue

Socket Specifications

General	
Voltage Rating	250V a.c. 50Hz
Current Rating	10A per socket
Dimensions	116mm x 76mm x 28mm
Mounting Centres	84mm
Safety Approval	AS/NZS3112 Approval and Test: Specifications: Plugs and Socket Outlets Can be used in an AS/NZS3003:2011 Compliant Installation
Operational Temperature	0C to 40C
Operational Humidity	10% - 95% RH Non-Condensing
Storage Temperature	0C to 60C
Storage Humidity	10% - 95% RH Non-Condensing



Schneider Electric (Australia) Pty Ltd

33-37 Port Wakefield Road, Gepps Cross,
South Australia 5094

PO Box 132, Enfield Plaza,
South Australia 5085

National Customer Care Enquiries:
1300 2025 25

clipsal.com

Schneider Electric (Australia) Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this document are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© 2015 Schneider Electric. All Rights Reserved.

Trademarks are owned by Schneider Electric Industries SAS or its affiliated companies.