



Ref. Certif. No.

FR_712221/A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Circuit-breaker for overcurrent protection for household and similar installations

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendes France, Eybens
38050 GRENOBLE Cedex 9
FRANCE

Name and address of the manufacturer

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendes France, Eybens
38050 GRENOBLE Cedex 9
FRANCE

Name and address of the factory

Schneider Electric India Pvt. Ltd.
Plot No - 172, Poonamallee Bye Pass Road, Poonamallee,
Tamil Nadu
600056 CHENNAI
INDIA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

CLIPSAL

Customer's Testing Facility (CTF) Stage used

CTF2

Model / Type Ref.

MAX9

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_712221 dated 2021/09/03. Editorial Correction

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60898-1:2015 +A1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

171846-763258-C-V01

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature:
Julien GAUTHIER
Certification Officer


Date: 21/09/2021

ANNEX

New Range name	Brand	MAX9 Generic Reference	Breaking Capacity	Pole description	Rated current	Curve
MAX9	Clipsal	MX9C60N1C0,5	6000A	1P	0,5	C
MAX9	Clipsal	MX9C60N1C1	6000A	1P	1	C
MAX9	Clipsal	MX9C60N1C2	6000A	1P	2	C
MAX9	Clipsal	MX9C60N1C3	6000A	1P	3	C
MAX9	Clipsal	MX9C60N1C4	6000A	1P	4	C
MAX9	Clipsal	MX9C60N1C6	6000A	1P	6	C
MAX9	Clipsal	MX9C60N1C10	6000A	1P	10	C
MAX9	Clipsal	MX9C60N1C13	6000A	1P	13	C
MAX9	Clipsal	MX9C60N1C16	6000A	1P	16	C
MAX9	Clipsal	MX9C60N1C20	6000A	1P	20	C
MAX9	Clipsal	MX9C60N1C25	6000A	1P	25	C
MAX9	Clipsal	MX9C60N1C32	6000A	1P	32	C
MAX9	Clipsal	MX9C60N1C40	6000A	1P	40	C
MAX9	Clipsal	MX9C60N1C50	6000A	1P	50	C
MAX9	Clipsal	MX9C60N1C63	6000A	1P	63	C
MAX9	Clipsal	MX9C60N1C63R*	6000A	1P	63	C
MAX9	Clipsal	MX9C60N2C0,5	6000A	2P	0,5	C
MAX9	Clipsal	MX9C60N2C1	6000A	2P	1	C
MAX9	Clipsal	MX9C60N2C2	6000A	2P	2	C
MAX9	Clipsal	MX9C60N2C3	6000A	2P	3	C
MAX9	Clipsal	MX9C60N2C4	6000A	2P	4	C
MAX9	Clipsal	MX9C60N2C6	6000A	2P	6	C
MAX9	Clipsal	MX9C60N2C10	6000A	2P	10	C
MAX9	Clipsal	MX9C60N2C13	6000A	2P	13	C
MAX9	Clipsal	MX9C60N2C16	6000A	2P	16	C
MAX9	Clipsal	MX9C60N2C20	6000A	2P	20	C
MAX9	Clipsal	MX9C60N2C25	6000A	2P	25	C
MAX9	Clipsal	MX9C60N2C32	6000A	2P	32	C
MAX9	Clipsal	MX9C60N2C40	6000A	2P	40	C



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: **Julien GAUTHIER**
 Certification Officer

Date: 21/09/2021

ANNEX


New Range name	Brand	MAX9 Generic Reference	Breaking Capacity	Pole description	Rated current	Curve
MAX9	Clipsal	MX9C60N2C50	6000A	2P	50	C
MAX9	Clipsal	MX9C60N2C63	6000A	2P	63	C
MAX9	Clipsal	MX9C60N2C63R *	6000A	2P	63	C
MAX9	Clipsal	MX9C60N3C0,5	6000A	3P	0,5	C
MAX9	Clipsal	MX9C60N3C1	6000A	3P	1	C
MAX9	Clipsal	MX9C60N3C2	6000A	3P	2	C
MAX9	Clipsal	MX9C60N3C3	6000A	3P	3	C
MAX9	Clipsal	MX9C60N3C4	6000A	3P	4	C
MAX9	Clipsal	MX9C60N3C6	6000A	3P	6	C
MAX9	Clipsal	MX9C60N3C10	6000A	3P	10	C
MAX9	Clipsal	MX9C60N3C13	6000A	3P	13	C
MAX9	Clipsal	MX9C60N3C16	6000A	3P	16	C
MAX9	Clipsal	MX9C60N3C20	6000A	3P	20	C
MAX9	Clipsal	MX9C60N3C25	6000A	3P	25	C
MAX9	Clipsal	MX9C60N3C32	6000A	3P	32	C
MAX9	Clipsal	MX9C60N3C40	6000A	3P	40	C
MAX9	Clipsal	MX9C60N3C50	6000A	3P	50	C
MAX9	Clipsal	MX9C60N3C63	6000A	3P	63	C
MAX9	Clipsal	MX9C60N3C63R *	6000A	3P	63	C

*With Red handle



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/09/2021



Signature: **Julien GAUTHIER**
 Certification Officer


Rated operational voltage U_e : (V)	1P : 230/400,240/415 2P, 3P : 400/415
Rated current I_n : (A)	C : 0.5, 1, 2, 3, 4, 6, 10, 13, 16, 20, 25, 32, 40, 50, 63
Rated frequency : (Hz)	50/60
Nature of supply :	~
Total number of poles :	1, 2, 3
Number of protected poles :	Tous / all
Rated insulation voltage U_i : (V)	500
Rated impulse withstand voltage U_{imp} : (V)	4000
Instantaneous tripping current :	C
Reference ambient calibration air temperature : (°C)	30
Rated short-circuit capacity I_{cn} : (A)	6000
Rated making and breaking capacity on one pole separately I_{cn1} : (A)	6000
Energy limiting class (I^2t) : according to EN 60898-1	3
Grid distance (short-circuit tests) :	45mm from 0,5A up to 40A 65mm for 50A and 63A
Protection against external influences :	Fermé / enclosed
Protection degree :	IP20
Material group :	II
Method of mounting :	panel board/distribution board, on rail
Method of electrical connection	not associated with the mechanical-mounting
Type of terminals :	pillar terminals
Nominal diameter of thread : (mm)	5,0 from 0,5A up to 25A 6,5 from 32A up to 63A
Operating means	lever



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 21/09/2021



Signature: **Julien GAUTHIER**
Certification Officer