




PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 63 A



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
Acti9/Multi9					
Circuit breakers					
iC60/iK60/DT60	Top	✓	-	-	-
	Bottom	✓	-	-	-
iC60 (double terminal)	Top	-	-	-	✓
	Bottom	-	-	-	✓
iC40	Top	-	✓	-	-
	Bottom	-	✓	-	-
DT40/iDPN/C40	Top	-	✓	-	-
	Bottom	-	✓	-	-
C120 ≤ 63 A NG125 ≤ 63 A	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
iC65N-K (China) iC65 (China)	Top	✓	-	-	-
	Bottom	✓	-	-	-
iDPN (China)	Top	-	✓	-	-
	Bottom	-	✓	-	-
iKQ	Top	NA	-	-	-
	Bottom	✓	-	-	-
N40	Top	-	✓	-	-
	Bottom	-	✓	-	-
Reflex iC60	Top	✓	-	-	-
	Bottom	✓	-	-	-
Reflex XC40	Top	✓	-	-	-
	Bottom	-	-	-	✓ (1)
Multi9 OEM (C60BP/C60BPR/ C60SP) 3P 480VAC only	Top	-	-	-	✓ A9MEM1575 (UL/IEC)
	Bottom	-	-	-	-
Multi9 OEM (C60N/H/L)	Top	✓	-	-	-
	Bottom	✓	-	-	-
C32/C45/C60/C65/K60/T60	Top	✓	-	-	-
	Bottom	✓	-	-	-

(1) You may need to change the voltage measurement cable terminals of the PowerTag Energy F63 by other cable ends (wire AWG22/0.33 mm²) for a more suitable connection to this product.
 (2) Product usually associated with a comb busbar

(*) Refer to the product catalog for technical characteristics




PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 63 A



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
Acti9/Multi9					
Circuit breakers equipped with Vigi module					
iC60/iC65/iC60/iC65N-K with Vigi module	Top	☑ (CB)	-	-	-
	Bottom	-	-	-	☑ (1) (Vigi)
iC40 with Vigi iCG40	Top CB	-	☑ (CB)	-	-
	Top (Vigi)	-	☑ (2) (Vigi 1P+N)	-	-
	Bottom (Vigi)	-	-	-	☑ (Vigi 3P+N)
iC40 with "outgoer" Vigi module	Top	-	☑ (CB)	-	-
	Bottom	-	-	-	☑ (Vigi)
DT40/DPN/C40 with "group feeder" Vigi module	Top CB	-	☑ (CB)	-	-
	Top Vigi	-	☑ (Vigi 1P+N)	-	☑ (Vigi 3P+N)
DT40/DPN/C40 with "outgoer" Vigi module	Top	-	☑ (CB)	-	-
	Bottom	-	-	-	☑ (Vigi)
DT60 with Vigi TG60	Top CB	☑ (CB) only A9MEM1541	-	-	-
	Top Vigi	-	-	-	☑ (1) (Vigi)
C120 ≤ 63 A NG125 ≤ 63 A with Vigi module	Top	-	-	-	☑ (1) (CB)
	Bottom	-	-	-	☑ (1) (Vigi)
Circuit breakers equipped with Arc fault detection unit					
iC60 with ARC unit	Top	☑ (CB)	-	-	-
	Bottom	-	-	-	☑ (add-on block)
iC40 with ARC unit	Top	-	☑ (CB)	-	-
	Bottom	-	-	-	☑ (add-on block)
Arc fault detection devices					
iC40N ARC / iCV40N VigiARC	Top	☑	-	-	-
	Bottom	☑	-	-	-

(1) You may need to change the voltage measurement cable terminals of the PowerTag Energy F63 by other cable ends (wire AWG22/0.33 mm²) for a more suitable connection to this product.

(2) Product usually associated with a comb busbar

(*) Refer to the product catalog for technical characteristics




PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 63 A



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
Acti9/Multi9					
Residual current devices					
iCVm40	Top	-	☑	-	☑
	Bottom	-	☑	-	☑
iID/iID K	Top	☑	-	-	-
	Bottom	☑	-	-	-
iID (double terminal)	Top	-	-	-	☑
	Bottom	-	-	-	☑
iID40	Top	-	☑ (2) (1P+N)	-	☑ (2) (3P+N)
	Bottom	☑	-	-	-
iDPN Vigi "outgoer" 1P+N	Top	-	☑	-	-
	Bottom	-	☑	-	-
iC60H RCBO/iC60H2 RCBO/ IKQE RCBO	Top	NA (fishbone)	-	-	-
	Bottom	-	-	☑	-
iC60 RCBO	Top	☑	-	-	-
	Bottom	☑	-	-	-
iCV40 "outgoer" 1P+N	Top	-	☑	-	-
	Bottom	-	☑	-	-
iCV40 "outgoer" 3P+N	Top	-	☑	-	-
	Bottom	-	-	-	☑
DPN Vigi/DT40 Vigi/C40 Vigi "outgoer" 1P+N	Top	-	☑	-	-
	Bottom	-	☑	-	-
DPN Vigi/DT40 Vigi/C40 Vigi/ iDPN Vigi "outgoer" 3P+N	Top	-	☑	-	-
	Bottom	-	-	-	☑
DPN Vigi K	Top	-	-	-	☑ (1)
	Bottom	-	-	-	☑ (1)
N40 Vigi "outgoer"	Top	-	☑	-	-
	Bottom	-	☑	-	-
iDc/ITG40/C40	Top Left	-	☑	-	-
	Top Right	-	☑	-	-
DCP Vigi	Top	☑	-	-	-
	Bottom	☑	-	-	-
C60H RCBO (Multi9)	Top	NA (fishbone)	-	-	-
	Bottom	-	-	☑	-
ID ≤ 63 A/iD K biconnect/ ID Type B ≤ 63 A	Top	☑	-	-	-
	Bottom	☑	-	-	-
RED/REds/REDTest	Top	-	-	-	☑ (1)
	Bottom	-	-	-	☑ (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag Energy F63 by other cable ends (wire AWG22/0.33 mm²) for a more suitable connection to this product.

(2) Product usually associated with a comb busbar

(*) Refer to the product catalog for technical characteristics




PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 63 A



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
Acti9/Multi9					
Switches					
iSW ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
iSW-NA ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
iSW 20/32 A	Top	-	-	-	✓
	Bottom	-	-	-	✓
i-NA ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
NG125 NA ≤ 63 A	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
Fuse disconnectors					
STI	Top	-	-	-	✓
	Bottom	-	-	-	✓
SBI 14x51/SBI 22x58 ≤ 63 A	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
D01/D02	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag Energy F63 by other cable ends (wire AWG22/0.33 mm²) for a more suitable connection to this product.

(*) Refer to the product catalog for technical characteristics




PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 63 A



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
TeSys					
Motor circuit breakers					
GV2	Top	-	-	-	☑ (1) (2)
	Bottom	-	-	-	☑ (1) (2)
GV3 ≤ 63 A	Top	-	-	-	☑ (1) (2)
	Bottom	-	-	-	☑ (1) (2)
Contactors					
TeSys D ≤ 63 A	Top	-	-	-	☑ Upstream only (1)
	Bottom	-	-	-	-
TeSys K	Top	-	-	-	☑ Upstream only (1)
	Bottom	-	-	-	-
Motor starter					
TeSys U	Top	-	-	-	☑ Upstream only (1)
	Bottom	-	-	-	-

(1) You may need to change the voltage measurement cable terminals of the PowerTag Energy F63 by other cable ends (wire AWG22/0.33 mm²) for a more suitable connection to this product.
 (2) PowerTag Energy sensors withstand motor starting in-rush currents. Environmental mission profile : Buildings as per 60721-3-3.

(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 160 A



Products (AC network)		Mounting position	F160 3P / 3P+N
Acti9			
Circuit breakers			
C120 (with or without Vigi module)	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
NG125 (with or without Vigi module)	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
Residual current devices			
iID > 63 A	3P+N	Top / Bottom	<input checked="" type="checkbox"/>
RCCB-ID 125 A	3P+N	Top / Bottom	<input checked="" type="checkbox"/>
Fuse disconnectors			
SBI > 63 A	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
Switches			
NG125 NA	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
iSW > 63 A	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
iSW NA > 63 A	3P+N	Top / Bottom	<input checked="" type="checkbox"/>
ComPact			
Circuit breakers			
NSXm	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/> (5)
Switches			
NSXm NA	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/> (5)
INS 80/100/125/160	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/>
PowerPact			
Circuit breakers			
B	3P / 3P+N	Top / Bottom	<input checked="" type="checkbox"/> (6)
TeSys			
Motor circuit breakers			
GV3 > 65 A	3P	Top / Bottom	<input checked="" type="checkbox"/>
GV4	3P	Top / Bottom	<input checked="" type="checkbox"/>
Contactors			
63 A < TeSys D ≤ 160 A	3P / 3P+N	Top	<input checked="" type="checkbox"/> Upstream only
TeSys F ≤ 160 A	3P / 3P+N	Top	<input checked="" type="checkbox"/> Upstream only

(5) It is advised to use EverLink connectors with control wire terminal (LV426970 for 3P / LV426971 for 4P)

(6) It is advised to use EverLink connectors with control wire terminal (LV426974 for 3P / LV426975 for 4P)

(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy 250 A

PowerTag Energy 630 A



Products (AC network)	Mounting position		M250 3P	M250 3P+N	M630 3P	M630 3P+N
ComPact						
Circuit breakers						
NSX100/160/250 B/F/N/H/S/L/R/NA Fixed	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
NSX400/630 F/N/H/S/L/R/NA Fixed	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
NSX100/160/250 B/F/N/H/S/L/R/NA Plug-In (mounted on the base)	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
NSX400/630 F/N/H/S/L/R/NA Plug-In (mounted on the base)	3P	Top / Bottom	-	-	☑ (4)	-
	4P	Top / Bottom	-	-	-	☑ (3) (4)
NS100/160/250 N/SX/H/L/NA Fixed	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
NS400/630 N/H/L/NA Fixed	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
NS100/160/250 N/SX/H/L/NA Plug-In (mounted on the base)	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
NS400/630 N/H/L/NA Plug-In (mounted on the base)	3P	Top / Bottom	-	-	☑ (4)	-
	4P	Top / Bottom	-	-	-	☑ (3) (4)
Circuit breakers equipped with Vigi block						
NSX100/160/250 B/F/N/H/S/L/R/NA Fixed	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
NSX400/630 F/N/H/S/L/R/NA Fixed	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
NSX100/160/250 B/F/N/H/S/L/R/NA Plug-In (mounted on the base)	3P	Top	☑	-	-	-
NSX400/630 F/N/H/S/L/R/NA Plug-In (mounted on the base)	3P	Top	-	-	☑ (4)	-
Switches						
INS250/INV - 100/160/200/250	3P	Bottom	-	☑	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
INS/INV - 320/400/500/630	3P	Bottom	-	-	-	☑
	4P	Top / Bottom	-	-	-	☑ (3)
TeSys						
Motor circuit breakers						
GV5, GV7	3P	Bottom	☑	-	-	-
GV6	3P	Bottom	-	-	☑	-
EasyPact						
Circuit breakers						
CVS100-250	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
CVS400-630	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑

(3) neutral on the right when mounted on top side

(4) when plate mounted, need to add a 4 mm intercalary under the PowerTag module (see ComPact NSX catalog)

(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for product compatibility*

(Compatibility for terminal not equipped with comb busbar)

PowerTag Energy Rope



Products (AC network)	Mounting position	R200 3P / 3P+N	R600 3P / 3P+N	R1000 3P / 3P+N	R2000 3P / 3P+N
ComPact					
Circuit breakers					
NS 630b	3P / 3P+N	Top / Bottom	-	☑	-
NS 800/1000	3P / 3P+N	Top / Bottom	-	-	☑
NS 1250/1600/1600b/2000	3P / 3P+N	Top / Bottom	-	-	☑
Switches					
INS/INV 630b	3P / 3P+N	Top / Bottom	-	☑	-
INS/INV 800/1000	3P / 3P+N	Top / Bottom	-	-	☑
INS/INV 1250/1600/2000	3P / 3P+N	Top / Bottom	-	-	☑
NS 630b NA	3P / 3P+N	Top / Bottom	-	☑	-
NS 800/1000 NA	3P / 3P+N	Top / Bottom	-	-	☑
NS 1250/1600/1600b/2000 NA	3P / 3P+N	Top / Bottom	-	-	☑
MasterPact					
Circuit breakers					
NT 06	3P / 3P+N	Top / Bottom	-	☑	-
NT 08/10	3P / 3P+N	Top / Bottom	-	-	☑
NT 12/16	3P / 3P+N	Top / Bottom	-	-	☑
NW 08/10	3P / 3P+N	Top / Bottom	-	-	☑
NW 12/16/20	3P / 3P+N	Top / Bottom	-	-	☑
Switches					
NT 06 HA	3P / 3P+N	Top / Bottom	-	☑	-
NT 08/10 HA	3P / 3P+N	Top / Bottom	-	-	☑
NT 12/16 HA	3P / 3P+N	Top / Bottom	-	-	☑
NW 08/10 NA/HA/HF	3P / 3P+N	Top / Bottom	-	-	☑
NW 12/16/20 NA/HA/HF	3P / 3P+N	Top / Bottom	-	-	☑
MTZ1 06 HA	3P / 3P+N	Top / Bottom	-	☑	-
MTZ1 08/10 HA	3P / 3P+N	Top / Bottom	-	-	☑
MTZ1 12/16 HA	3P / 3P+N	Top / Bottom	-	-	☑
MTZ2 08/10 NA/HA/HA10	3P / 3P+N	Top / Bottom	-	-	☑
MTZ2 12/16/20 NA/HA/HA10	3P / 3P+N	Top / Bottom	-	-	☑
TeSys					
Contactors					
TeSys D > 160 A	3P / 3P+N	Top	☑ Upstream only	-	-
160 A < TeSys F ≤ 2000 A	3P / 3P+N	Top	☑ Upstream only	☑ Upstream only	☑ Upstream only
Others					
Circuit breakers / Switches / Motor circuit breakers					
All products below 200 A	3P / 3P+N	Top / Bottom	☑	-	-
All products between 200 A and 600 A	3P / 3P+N	Top / Bottom	-	☑	-
All products between 600 A and 1000 A	3P / 3P+N	Top / Bottom	-	-	☑
All products between 1000 A and 2000 A	3P / 3P+N	Top / Bottom	-	-	☑










(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for concentrators / gateways compatibility*

Concentrators / gateways

				
	EcoStruxure™ Panel Server Entry, Universal and Advanced PAS400, PAS600/600L, PAS800	Harmony Hub ZBRN1, ZBRN2, ZBRN32	Smartlink SI B A9XMZA08, Smartlink SI D A9XMWA20	PowerTag Link A9XMWD20, PowerTag Link HD A9XMWD100
PowerTag Energy M63				
	A9MEM1520	✓	-	✓
	A9MEM1521	✓	-	✓
	A9MEM1522	✓	-	✓
	A9MEM1540	✓	-	✓
	A9MEM1541	✓	-	✓
	A9MEM1542	✓	-	✓
	A9MEM1543	✓	-	✓
PowerTag Energy M63 Resi9				
	R9M20	-	-	-
	R9M21	-	-	-
	R9M22	-	-	-
	R9M40	-	-	-
	R9M41	-	-	-
	R9M42	-	-	-
	R9M43	-	-	-
PowerTag Energy P63				
	A9MEM1561	✓	-	✓
	A9MEM1562	✓	-	✓
	A9MEM1563	✓	-	✓
	A9MEM1571	✓	-	✓
	A9MEM1572	✓	-	✓
PowerTag Energy F63				
	A9MEM1560	✓	✓	✓
	A9MEM1564	✓	-	✓
	A9MEM1570	✓	✓	✓
	A9MEM1573	✓	✓	-
	A9MEM1574	✓	-	-
	A9MEM1575	✓ (1)	-	-
PowerTag Energy F63 Resi9				
	R9M60	-	-	-
	R9M70	-	-	-

(1) From firmware release 2.4








(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for concentrators / gateways compatibility*

Concentrators / gateways

			
		Wiser Home Hub CCT501801	Wiser Hub CCT501901
PowerTag Energy M63			
	A9MEM1520	<input checked="" type="checkbox"/>	-
	A9MEM1521	<input checked="" type="checkbox"/>	-
	A9MEM1522	<input checked="" type="checkbox"/>	-
	A9MEM1540	<input checked="" type="checkbox"/>	-
	A9MEM1541	<input checked="" type="checkbox"/>	-
	A9MEM1542	<input checked="" type="checkbox"/>	-
	A9MEM1543	<input checked="" type="checkbox"/>	-
PowerTag Energy M63 Resi9			
	R9M20	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M21	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M22	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M40	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M41	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M42	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M43	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
PowerTag Energy P63			
	A9MEM1561	<input checked="" type="checkbox"/>	-
	A9MEM1562	<input checked="" type="checkbox"/>	-
	A9MEM1563	<input checked="" type="checkbox"/>	-
	A9MEM1571	<input checked="" type="checkbox"/>	-
	A9MEM1572	<input checked="" type="checkbox"/>	-
PowerTag Energy F63			
	A9MEM1560	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	A9MEM1564	-	-
	A9MEM1570	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	A9MEM1573	-	-
	A9MEM1574	-	-
	A9MEM1575	-	-
PowerTag Energy F63 Resi9			
	R9M60	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	R9M70	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>







(*) Refer to the product catalog for technical characteristics



PowerLogic™ PowerTag Energy

Selection guide for concentrators / gateways compatibility*

Concentrators / gateways







				
	EcoStruxure™ Panel Server Entry, Universal and Advanced PAS400, PAS600/600L, PAS800●	Harmony Hub ZBRN1 ZBRN2 ZBRN32	Smartlink SI B A9XMZA08 Smartlink SI D A9XMWA20	PowerLogic HU250 EMS59000 + EMS59156 +EMS59155 (4G optional)
PowerTag Energy F160				
	A9MEM1580	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-
PowerTag Energy M250-M630				
	LV434020	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	LV434021	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	LV434022	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
	LV434023	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
PowerTag Energy R200-R600-R1000-R2000				
	A9MEM1590	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-
	A9MEM1591	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-
	A9MEM1592	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-
	A9MEM1593	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-



PowerLogic™ PowerTag Energy

Selection guide for concentrators / gateways compatibility*

Concentrators / gateways

				
		Wiser Home Hub CCT501801	Wiser Hub CCT501901	PowerTag Link A9XMWD20 PowerTag Link HD A9XMWD100
PowerTag Energy F160				
	A9MEM1580	-	-	☑
PowerTag Energy M250-M630				
	LV434020	-	-	☑
	LV434021	-	-	☑
	LV434022	-	-	☑
	LV434023	-	-	☑
PowerTag Energy R200-R600-R1000-R2000				
	A9MEM1590	-	-	☑
	A9MEM1591	-	-	☑
	A9MEM1592	-	-	☑
	A9MEM1593	-	-	☑