Australia and New Zealand Certificate of Conformity/Approval-addendum

Certificate
ULL-103519 -A1

Issue date
2025-09-16

Expiration date
2029-08-23

This is to acknowledge that

SCHNEIDER ELECTRIC AUSTRALIA PTY LTD

33-37 PORT WAKEFIELD RD, GEPPS CROSS, South Australia 5094 Australia

has had

PLUG

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS/NZS 3112:2017, Amd 1:2021; AS/NZS 3100:2022, Amd 1: 2023, Amd 2: 2024

Certificate of Conformity issued under Queensland Government's Recognised External Certification Scheme (RECS)
Certificate of Approval issued under NSW Government's Recognised External Approval Scheme (REAS)
ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2025 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Conformity/Approval-addendum

Certificate No: ULL-103519 -A1
Original Date of Certification: 2024-08-23
Date of Issue/Revision: 2025-09-16

Trade Name or Trademark: CLIPSAL: 56P210, PDL: PDL56P315, PDL: PDL56P320F, SCHNEIDER ELECTRIC: EY56P310, SCHNEIDER ELECTRIC: EY56P315, SCHNEIDER ELECTRIC: S56P320F, CLIPSAL: 56P3/110, CLIPSAL: 56P310, CLIPSAL: 56P310RP, CLIPSAL: 56P310SL, CLIPSAL: 56P315, CLIPSAL: 56P320F, PDL: PDL56P310, PDL: PDL56P310R

Risk Class / NSW Declared Class: LEVEL 3 - Plug

Certification Marking: The RCM mark must be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled
The product approval mark ULL-103519-EA shall be placed on declared articles offered for sale in New South Wales and New Zealand

Additional Certification Conditions: WSNZ test report conditions in NZ Gazette notices 2022-au3179 and 2022-au3180 verified.

Model Details:

Model Name	Marked Input Voltage	Marked Input Frequency	Marked Input Current
PDL56P310	230/240 Va.c.	50 Hz	10 A IP66
EY56P315	230/240 Va.c.	50 Hz	15 A IP66
PDL56P315	230/240 Va.c.	50 Hz	15 A IP66
56P315	230/240 Va.c.	50 Hz	15 A IP66
56P210	125 Va.c.	50 Hz	10 A IP66
S56P320F	230/240 Va.c.	50 Hz	20 A IP66
EY56P310	230/240 Va.c.	50 Hz	10 A IP66
PDL56P310R	230/240 Va.c.	50 Hz	10 A IP66
56P320F	230/240 Va.c.	50 Hz	20 A IP66
PDL56P320F	230/240 Va.c.	50 Hz	20 A IP66
56P310	230/240 Va.c.	50 Hz	10 A IP66
56P310SL	230/240 Va.c.	50 Hz	10 A IP66
56P310RP	230/240 Va.c.	50 Hz	10 A IP66
56P3/110	110 Va.c.	50 Hz	10 A IP66

Additional Information:

Details of addendum:
- Alternative plug pin insulation added.

The WorkSafe NZ test report acceptance conditions outlined in NZ Gazette notices 2022-au3179 and 2022-au3180 have been verified.

© 2025 UL LLC. All rights reserved.