

**IEC****IECEE**

®

™

Ref. Certif. No.

CN48440-M3

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

AC Contactors

Name and address of the applicant

Schneider Shanghai Industrial Control Co., Ltd.  
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the manufacturer

Schneider Electric Industries SAS  
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

*Note: When more than one factory, please report on page 2*SCHNEIDER ELECTRIC INDIA PVT LTD  
SY NO 99/1, MAMIDIPALLY, Mamidipalle, Balapur,  
Rangareddy - 500108

Ratings and principal characteristics

See the Appendix

Trademark (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

LC1E32..., LC1E38..., LC1E40B...;

Additional information (if necessary may also be reported on page 2)

The latest CB certificate No. is CN48440-M2, dated 2023-01-09. The M3 certificate has been issued to change parameters.

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018;IEC 60947-1:2007;IEC 60947-1:2007/AMD1:2010;IEC 60947-1:2007/AMD2:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2019CQC-088502-M3

**CHINA QUALITY CERTIFICATION CENTRE CO., LTD.**

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: <http://www.cqc.com.cn>

Date: Sep.25,2024

Signature:

谢肇煦

Xie ZhaoXu



LC1E32..., LC1E38..., LC1E40B...

Ui: 690V;

Uimp: 6kV;

Ith: 50A;

LC1E32...:

AC-3: Ue/Ie: 220/230V/32A, 380V/32A, 400/415V/32A, 440V/ 32A;

AC-3e: Ue/Ie: 220/230V/32A, 380V/32A, 400/415V/32A, 440V/ 32A;

AC-4: Ue/Ie: 220/230V/26.7A, 380V/26.7A, 400/415V/26.7A, 440V/26.7A;

AC-1: Ue/Ie: 220/230V/50A, 380V/50A, 400/415V/50A, 440V/50A;

LC1E38...:

AC-3: Ue/Ie: 220/230V/38A, 380V/38A, 400/415V/38A, 440V/38A;

AC-3e: Ue/Ie: 220/230V/38A, 380V/38A, 400/415V/38A, 440V/38A;

AC-4: Ue/IeV: 220/230V/31.7A, 380V/31.7A, 400/415V/31.7A, 440V/31.7A;

AC-1: Ue/ Ie: 220/230V/50A, 380V/50A, 400/415V/50A, 440V/50A;

LC1E40B...:

AC-3: Ue/ Ie: 220/230V/40A, 380V/40A, 400/415V/40A, 440V/40A;

AC-3e: Ue/ Ie: 220/230V/40A, 380V/40A, 400/415V/40A, 440V/40A;

AC-4: Ue/ Ie: 220/230V/33.3A, 380V/33.3A, 400/415V/33.3A, 440V/33.3A;

AC-1: Ue/ Ie: 220/230V/50A, 380V/50A, 400/415V/50A, 440V/50A;

Us: AC50Hz: 24V, 36V, 48V, 110V, 220V, 240V, 380V, 415V, 440V;

AC60Hz: 24V, 110V, 220V, 380V, 440V;

AC50/60Hz: 24V, 48V, 110V, 220V, 230V, 380V;

AC50Hz (70%~120%Us): 220V, 415V;

Additional information (if necessary)

Date:

Sep.25,2024

Signature:

谢肇煦

Xie ZhaoXu

IEC

IECEE

®

™

Ref. Certif. No.

CN48440-M3

Poles: 3P;  
Frequency: 50/60Hz;  
IP20(from front face only);  
Auxiliary contacts: (body)  
Ith:10A;  
AC-15: Ue/Ie:380V/1.3A, 660V/0.75A;  
DC-13: Ue/Ie:220V/0.3A;  
1NO, 1NC;

Page 2 of 2

Additional information (if necessary)

Date:

Sep.25,2024

Signature:

谢肇煦

Xie ZhaoXu