



...featuring on the big screen

C-Bus®
MK II
Black & White
TOUCH SCREEN


The new C-Bus® MKII Black and White Touch Screen builds on the success of the C-Bus MKI Black and White Touch Screen, with many enhancements made in this new ground-up product developed by Clipsal engineers.

- Bigger screen
- Enhanced contrast
- Superior backlighting
- Wide range of fascia styles
- Available with or without C-Bus logic engine
- RS-232 port for third party device integration*
- USB programming port accessible from the front of the unit.

Installer Benefits

To ensure the unit is quicker, easier and more flexible to install and commission, the following features have been included in the MKII unit:

- Programmed via a standard USB port on the unit
- The USB programming port is accessible from the front of the unit by simply removing the fascia
- The USB port can be used as a PC interface to a C-Bus System
- A separate RS-232 port is included on the rear of the unit for third party device integration*
- Compatible with Version 4 of Clipsal's Windows® based drag and drop programming software (PICED)
- Available with or without C-Bus Logic Engine features.




USB programming port accessible by removing the fascia.

User Benefits

To provide the user with an improved interface, the following have been included:

- The unit includes a new, larger LCD screen. This has 50% more screen area than the MKI model LCD screen
- Improved, adjustable LCD screen backlighting with ambient light compensation
- The super bright LCD uses white on black technology to enhance clarity
- A wide range of fascia colours and styles are available.



Super bright LCD screen with 50% more screen area than MKI.

Parameter	Description
Screen Size	119mm (Diagonal) 4.7 inches (Diagonal) W 100mm x H 75mm
Resolution	QVGA (320 pixels x 240 pixels)
Control Functions	• Load switching and dimming • Logic (Versions with Logic Engine only) • Scenes • Schedules
Power Supply	Powered directly from C-Bus15-36V DC @ 65mA required for normal operation. Does not provide current to the C-Bus Network.
Maximum number of controlled loads	255 Group Addresses on each of 10 C-Bus Applications
Maximum number of C-Touch Units on a single C-Bus Network	10
C-Bus Connection	Loop-in / Loop-out Removable Terminal block for C-Bus
Third party interface	RS-232 port (supported by the version with C-Bus Logic Engine only)
Programming Port	USB Type B (under front fascia)
Overall dimensions	Plastic Fascia Version W = 193mm H = 134mm D = 41mm Saturn™ Fascia Version W = 195mm H = 136mm D = 47mm Neo™ Fascia Version W = 192mm H = 137mm D = 45mm Stainless Steel Fascia Version W = 193mm H = 134mm D = 45mm
Operating Temperature Range	10 - 45°C
Operating Humidity Range	10 - 90% R.H.
Fascia Styles	Saturn™, Neo™, Stainless Steel, Plastic
Accessories	RS-232 lead (only required for integrating to third party devices) Part Number 5000CT2RS232 Wall Box Part Number 5000CT2WB (External Dimensions 179.5 x 122.5 x 55mm)

SATURN™



5080CT2,GF - without Logic Engine
5080CTL2,GF - with Logic Engine



5080CT2-3 - without Logic Engine
5080CTL2-3 - with Logic Engine



5080CT2-7 - without Logic Engine
5080CTL2-7 - with Logic Engine



5080CT2-6 - without Logic Engine
5080CTL2-6 - with Logic Engine

NEO™



5050CT2,GB - without Logic Engine
5050CTL2,GB - with Logic Engine



5050CT2,WE - without Logic Engine
5050CTL2,WE - with Logic Engine



5050CT2-28 - without Logic Engine
5050CTL2-28 - with Logic Engine



5050CT2,BK - without Logic Engine
5050CTL2,BK - with Logic Engine

STAINLESS STEEL



BS5000CT2 - without Logic Engine
BS5000CTL2 - with Logic Engine



SC5000CT2,WE - without Logic Engine
SC5000CTL2,WE - with Logic Engine



SC5000CT2,CM - without Logic Engine
SC5000CTL2,CM - with Logic Engine



SC5000CT2,BK - without Logic Engine
SC5000CTL2,BK - with Logic Engine

PLASTIC

Clipsal Australia Pty Ltd
A member of Schneider Electric
Head Office

 33-37 Port Wakefield Road,
 Gepps Cross, South Australia 5094

CIS Technical Support Hotline:

Australia	1300 722 247
New Zealand	0800 888 219
Northern Asia	+852 2484 4157 (Hong Kong)
South Africa	011 314 5200
Southern Asia	+603 7665 3555 x236 or 242
United Kingdom	+44 870 608 8 608
Technical Support Email	cis_support@clipsal.com.au

National Customer Care Enquiries:
1300 2025 25
National Customer Care Facsimile:
1300 2025 56
New Zealand

Schneider Electric (NZ) Ltd Tel +64 9 576 3403

Malaysia

Clipsal Integrated Systems (M) Sdn Bhd Tel +60 3 7665 3555

Singapore

Clipsal Integrated Systems Pte Ltd Tel +65 6415 3232/3233

China

Clipsal China Limited Tel +86 755 8237 5959

Greece

Schneider Electric AE Tel +30 69 4646 3200

Hong Kong

Clipsal Integrated Systems (HK) Limited Tel +852 2487 0261

India

Schneider Electric India Pvt Ltd Tel +91 11 5159 0000

Indonesia

PT Clipsal Graha Nusa Tel +62 21 630 6430

Korea

Clipsal Korea Co. Ltd Tel +82 549 5550

Pakistan

Clipsal Pakistan (Pvt) Ltd Tel +92 21 506 7278

Philippines

Clipsal Philippines Inc. Tel +632 683 0275-78

South Africa

Clipsal South Africa (Pty) Ltd Tel +27 11 314 5200

Taiwan

Clipsal (Taiwan) Co Ltd Tel +886 2 2558 3456

Thailand

Clipsal Thailand Ltd Tel +66 2 952 5338-42

United Arab Emirates

Clipsal Middle East Tel +971 6 5570 777

United Kingdom

 Clipsal Integrated Systems
 c/o Schneider Electric Tel +44 870 608 8 608

Vietnam

Clipsal - VTEC Tel +848 856 3002

 You can find this datasheet and many others online in
 PDF format at: clipsal.com
clipsal.com/cis

Clipsal Australia Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this catalogue are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© Clipsal Australia Pty Ltd

This material is copyright under Australian and international laws. Except as permitted under the relevant law, no part of this work may be reproduced by any process without prior written permission of and acknowledgement to Clipsal Australia Pty Ltd. The identified trademarks and copyrights are the property of Clipsal Australia Pty Ltd unless otherwise noted.

