

IEC**IECEE**

®

™

Ref. Certif. No.

CN49896-M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

AC Contactor

Name and address of the applicant

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the manufacturer

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the factory

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China*Note: When more than one factory, please report on page 2*

Ratings and principal characteristics

See the Appendix

Trademark (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

LC1E120...N, LC1E160...N, LC1E120..., LC1E160...,
LC1E105...NS260;

Additional information (if necessary may also be reported on page 2)

The latest CB certificate No. is CN49896-M1, dated 2023-09-06. The issuance of the M2 certificate is to change parameters.

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018;IEC 60947-1:2007;IEC 60947-1:2007/AMD1:2010;IEC 60947-1:2007/AMD2:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2020CQC-090858-M2

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: <http://www.cqc.com.cn>

Date: Mar.19,2024

Signature:

谢肇煦

Xie ZhaoXu



LC1E120...N, LC1E160...N, LC1E120..., LC1E160..., LC1E105...NS260

LC1E120...N, LC1E120...:

Ui: 690V;

Uimp:8kV;

Ith: 150A;

AC-3: Ue/Ie: 220V/230V/120A, 380V/400V/120A, 415V/440V/120A, 660V/690V/85.4A;

AC-3e: Ue/Ie: 220V/230V/96A, 380V/400V/96A, 415V/440V/96A, 660V/690V/80A;

AC-4: Ue/Ie: 220V/230V/100A, 380V/400V/100A, 415V/440V/100A, 660V/690V/71.2A;

LC1E160...N, LC1E160...:

Ui: 690V;

Uimp:8kV;

Ith: 200A;

AC-3: Ue/Ie: 220V/230V/160A, 380V/400V/160A, 415V/440V/160A, 660V/690V/107.8A;

AC-3e: Ue/Ie: 220V/230V/100.3A, 380V/400V/100.3A, 415V/440V/100.3A, 660V/690V/86A;

AC-4: Ue/Ie: 220V/230V/133.4A, 380V/400V/133.4A, 415V/440V/133.4A,

660V/690V/89.9A;

LC1E105...NS260:

Ui: 1000V;

Uimp:8kV;

Ith: 105A;

AC-1: Ue/Ie: 220V/230V/105A, 380V/400V/105A, 415V/440V/105A, 690V/105A;

Page 1 of 2

Additional information (if necessary)

Date:

Mar.19,2024

Signature:

谢肇煦

Xie ZhaoXu

Us: AC24V, 48V, 110V, 220V, 240V, 380V, 415V, 440V 50Hz;

AC24V, 110V, 220V, 380V, 440V 60Hz;

AC24V, 48V, 110V, 220V, 230V, 240V, 380V, 415V, 440V 50/60Hz;

Poles: 3P;

Frequency: 50/60Hz;

Auxiliary contact: (body, Only applicable for LC1E120...N, LC1E160...N, LC1E120..., LC1E160...)

1NC1NO;

Ith: 8A;

AC-15: Ue/Ie: 380V/1.3A, 660V/0.75A;

DC-13: Ue/Ie:220V/0.3A

Page 2 of 2

Additional information (if necessary)

Date:

Mar.19,2024

Signature:

谢肇煦

Xie ZhaoXu