Ref. Certif. No.

FR_724317

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	**Circuit-breaker** Miniature Circuit-breaker
Name and address of the applicant	**Schneider Electric Industries SAS** 1884 Boulevard de la Défense, 92000 Nanterre - France
Name and address of the manufacturer	**Schneider Electric Industries SAS** 1884 Boulevard de la Défense, 92000 Nanterre - France
Name and address of the factory	**Schneider Electric India Pvt. Ltd.** Plot No - 172, Poonamallee Bye Pass Road, Poonamallee, Tamil Nadu,600056 CHENNAI - India
Note: *When more than one factory, please report on page 2*	☐ Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark / Brand (if any)	CLIPSAL
Customer's Testing Facility (CTF) Stage used	CTF2
Model / Type Ref.	MCB4 Series
Additional information (if necessary may also be reported on page 2)	☐ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60898-1:2015 +A1:2019
As shown in the Test Report Ref. No. which forms part of this Certificate	B260033

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 28/09/2026

Signature: **Julien GAUTHIER**
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
33 avenue du Général Leclerc
FONTENAY AUX ROSES

ANNEX

Product References:

Rated operational voltage Ue : (V)	240V~
Rated current In : (A)	1;2;3;4;6;8;10;13;16;20;25;32;40;50;63A
Rated frequency : (Hz)	50/60Hz
Nature of supply :	AC
Total number of poles :	1P
Number of protected poles :	1P
Rated insulation voltage Ui : (V)	500V
Rated impulse withstand voltage Uimp : (kV)	4kV
Instantaneous tripping current :	C
Reference ambient calibration air temperature : (°C)	30°C
Rated short-circuit capacity Icn : (A)	4500A
Rated making and breaking capacity on one pole separately Icn1: (A)	4500A
Energy limiting class I^2t :	Class 3 (for In ≤40A) (according to EN 60898-1)
Grid distance (short-circuit tests) :	35mm (rating 1A to 40A), 55mm (rating 50A to 63A
Protection against external influences :	Enclosed
Protection degree :	IP20
Material group :	II
Method of mounting :	On rail
Method of electrical connection	
not associated with the mechanical-mounting	
Type of terminals :	Pillar terminal
Nominal diameter of thread : (mm)	5 mm (rating 1A to 25A) 6,5 mm (rating 32A to 63A)
Operating means :	Lever

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 28/09/2026

Signature: **Julien GAUTHIER**
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
Capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92260 FONTENAY AUX ROSES

ANNEX

Product references list:

Product Name	Rated short-circuit capacity Icn(A)	Voltage (V)	Poles	Rating (A)	Curve	Generic Reference
MCB4	4500	240	1	1	C	MCB4-101
MCB4	4500	240	1	2	C	MCB4-102
MCB4	4500	240	1	3	C	MCB4-103
MCB4	4500	240	1	4	C	MCB4-104
MCB4	4500	240	1	6	C	MCB4-106
MCB4	4500	240	1	8	C	MCB4-108
MCB4	4500	240	1	10	C	MCB4-110
MCB4	4500	240	1	13	C	MCB4-113
MCB4	4500	240	1	16	C	MCB4-116
MCB4	4500	240	1	20	C	MCB4-120
MCB4	4500	240	1	25	C	MCB4-125
MCB4	4500	240	1	32	C	MCB4-132
MCB4	4500	240	1	40	C	MCB4-140
MCB4	4500	240	1	50	C	MCB4-150
MCB4	4500	240	1	63	C	MCB4-163

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 28/09/2026

Signature: **Julien GAUTHIER**
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
Capital de 15.745.984 €
Rcs Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92260 FONTENAY AUX ROSES