

EU DECLARATION OF CONFORMITY

We: **Schneider Electric Japan Holdings Ltd.**
Subsidiary of SCHNEIDER ELECTRIC INDUSTRIES SAS (1884 Bd de la Défense, FR-92000 Nanterre)
4-4-9 Kitahama, Chuo-ku, Osaka, 541-0041 Japan

Hereby declare under our sole responsibility that the products:

Trademark	Pro-face 
Product, Type, Function	Human Machine Interface / Industrial Controller / Industrial Display
Models	PS6000, FP6000, see detailed list of references
Serial Number	PPYYWWZZZZZ (PP = Plant Code; YY = Year; WW = Week; ZZZZZ = digits from 0 to 9)


are in conformity with the requirements of the following directives and conformity was checked in accordance with the following standards:

Directive	Harmonized standard / Notified body reference
Electromagnetic compatibility directive (EMC) 2014/30/EU For DC input models	EN 61131-2:2007 Programmable controllers - Part 2: Equipment requirements and tests Other standard considered: IEC 61131-2:2017
Low voltage directive (LVD) 2014/35/EU For AC input models	EN 61131-2:2007 Programmable controllers – Part 2: Equipment requirements and tests Other standard considered: IEC 61010-1:2017
Equipment for explosive atmospheres directive (ATEX) 2014/34/EU For FP6000 series only	EN IEC 60079-0:2018 Explosive atmospheres - Equipment - General requirements EN IEC 60079-7:2015/A1:2018 Explosive atmospheres - Equipment protection by increased safety "e" EN 60079-15:2010 Explosive atmospheres - Equipment protection by increased safety "n" EN 60079-31:2014 Explosive atmospheres - Equipment dust ignition protection by enclosure "t" Type examination certificate INERIS 22ATEX3005X  II 3 GD (Written attestation of conformity) issued by INERIS - Parc Technologique Alata, 60550 Verneuil en Halatte, France (See certificate for list of ATEX references)
RoHS directive 2011/65/EU, (EU) 2015/863	EN IEC 63000:2018 Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions, user manual and to accepted rules of the art.

Issued at:
Vienna – AUSTRIA: September 1st, 2026

Name(*):

DocuSigned by:

4CE4DB3D073F4BF...
Christian LINSBAUER
Industrial Control & Drives
Customer Satisfaction & Quality - Director

(*) Name and title of the signatory empowered to bind the manufacturer or his authorized representative.

EU DECLARATION OF CONFORMITY

List of references for PS6000 series

Digit	1-5	6	7	8	9	10	11	12	13	14	15	16	17	18
Range	PFXP6													
CPU	Core i7 (Advanced Box)	7												
	Core i5 (Advanced Box)	5												
	Celeron (Advanced Box)	C												
	Core i3 (Standard Box)	3												
Display	None (Box Module)		B											
	12"		6											
	15"		7											
	10" Wide		D											
	12" Wide		E											
	15" Wide		F											
	15" Wide (FHD)		K											
	19" Wide		G											
	22" Wide		A											
Power	24 Vdc for Advanced Box			D										
	100–240 Vac for Advanced Box			A										
	24 Vdc for Standard Box			1										
	100–240 Vac for Standard Box			2										
Slot	None				0									
	PCI x 1 + PCIe x 1				M									
	PCIe x 2				E									
	PCI x 2				P									
Fan	None					N								
	With FAN kit					F								
Main storage	None						0							
	M.2 SSD 128 GB						1							
	M.2 SSD 128 GB						2							
	M.2 SSD 256 GB						3							
	M.2 SSD 512 GB						4							
	SSD 128 GB						5							
	SSD 256 GB						6							
	SSD 512 GB						7							
	HDD 1 TB						8							
Secondary storage	None							0						
	SSD 128 GB							5						
	SSD 256 GB							6						
	SSD 512 GB							7						
	HDD 1 TB							8						
Memory	DIMM 4 GB (4 GB x 1) (Celeron only)								4					

EU DECLARATION OF CONFORMITY

Pro-face™

by Schneider Electric

	DIMM 8 GB (4 GB x 2)	8					
	DIMM 16 GB (8 GB x 2)	A					
	DIMM 32 GB (16 GB x 2) (i7, i5 and i3 only)	B					
Options	None	N					
	RS-232C isolated x 2	B					
	RS-232C x 4	C					
	RS-422/485 isolated x 2	D					
	Ethernet (GbE IEEE 1588) x 1	E					
	Audio (Mic-IN, Line-IN, Line-OUT)	F					
	EtherCAT (Master)	G					
OS	See user manual. “*” Any letter or number		*				
Software	See user manual. “*” Any letter or number			*			
Reserved	“*” Any letter or number					*	*

List of references for FP6000 series

Digit	1-3	4-5	6	7	8-9	10	11	12
	PFX	model	series	size	type	display	Touch panel	power
		FP	6	5: 10" 6: 12" 7: 15" 8: 19" 9: 21"	00: Standard 10: 15W FHD	T: 4:3 TFT W: Wide TFT	M: Analog multi touch C: Capacitive multi touch	D: DC

List of options and accessories for PS6000 series

Commercial Reference	Description
Interface	
PFXYP6MPR23P2	RS-232C isolated x 2
PFXYP6MPR23P4	RS-232C x 4
PFXYP6MPR42P2	RS422/485 isolated x 2
PFXYP6MPETH	Ethernet (GbE IEEE 1588)
PFXYP6MPAU	Audio (Mic-IN, Line-IN, Line-OUT)
PFXYP6MPECAT	EtherCAT (Controller)
PFXYP6MPX16Y8	16DI / 8DO
Storage	
PFXYP6M2128L	M.2 SSD 128 GB
PFXYP6M2128	M.2 SSD 128 GB
PFXYP6M2256	M.2 SSD 256 GB
PFXYP6M2512	M.2 SSD 512 GB
PFXYP6SSD128	SSD 128 GB
PFXYP6SSD256	SSD 256 GB
PFXYP6SSD512	SSD 512 GB
PFXYP6HDD1T	HDD 1 TB
Memory	
PFXYP6DM4	DIMM 4 GB
PFXYP6DM8	DIMM 8 GB
PFXYP6DM16	DIMM 16 GB
Cable	
CA5-USBEXT-01	USB Front Cable
PFXYP6CVUSAU	USB Audio Cable
PFXYP6PCBDPDV5M	DP-DVI cable 5 m
PFXZP6PCBDPDV32	DP-DVI cable 3 m

EU DECLARATION OF CONFORMITY

Adapter	
PFXZPBADCVPDV2	DP-DVI Adapter
Others	
PFXYP6RUSW10*	Recovery USB for Windows 10 “*” Any letter or number
PFXYP6FAN	FAN kit with filter (5 pieces/set)

List of options and accessories for FP6000 series

Commercial Reference	Description
Cable	
FP-US00	USB cable 5 m
PFXYFPCBDPDV5M	DP-DVI cable 5 m
PFXZPBCBDPDV32	DP-DVI cable 3 m
FP-DV01-50	DVI cable 5m
Adapter	
PFXZPBADCVPDV2	DP to DVI-D adapter

List of Maintenance Accessories for PS6000 Series

Commercial Reference	Description
Display Module	
PFXDM6600TM	12-inch Display Module
PFXDM6700TM	15-inch Display Module
PFXDM6500WC	10-inch Wide Display Module
PFXDM6600WC	12-inch Wide Display Module
PFXDM6700WC	15-inch Wide Display Module
PFXDM6710WC	15-inch Wide FHD Display Module
PFXDM6800WC	19-inch Wide Display Module
PFXDM6900WC	22-inch Wide Display Module