

**IEC****IECEE**

Ref. Certif. No.

**FR\_715156**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

**AC electric vehicle conductive charging station**  
EVlink Home, EVlink Home Smart

Name and address of the applicant

**SCHNEIDER ELECTRIC INDUSTRIES SAS**  
35, rue Joseph Monier  
92500 RUEIL-MALMAISON- FRANCE

Name and address of the manufacturer

**SCHNEIDER ELECTRIC INDUSTRIES SAS**  
31 rue Pierre Mendès-France  
38320 EYBENS- France

Name and address of the factory

**WANBANG DIGITAL ENERGY Co., Ltd.**  
No.39 Longhui Road, Wujin District,  
Changzhou, Jiangsu - China

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61851-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

22HAS01P06D31-00028

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE[www.lcie.fr](http://www.lcie.fr)

Date: 04/08/2022

LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES  
S.A.S au capital de 15.745.984 €  
RCS Nanterre B 408 263 124  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSESSignature:   
**Julien GAUTHIER**  
Certification Officer

## ANNEX

### References, ratings and main characteristics:

Model name	Input and output ratings	Connection method	Radio functions	Protection class	Mass
EVH4S03N2	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S07N2	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S11N2	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S03NC	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	NO	IP55 Class I	5.2kg
EVH4S07NC	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case C Cable length:5m	NO	IP55 Class I	5.2kg
EVH4S11NC	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	NO	IP55 Class I	5.2kg
EVH4A03N2	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A07N2	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A11N2	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A03NC	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg
EVH4A07NC	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg
EVH4A11NC	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE

[www.lcie.fr](http://www.lcie.fr)



Signature: **Julien GAUTHIER**  
Certification Officer

Date: 04/08/2022