Universal Enclosures and Thermal Management

Catalog **2026/2027**



PanelSeT, ClimaSys

More than 60 years contributing
to equipment protection

se.com/enclosures

Schneider Electric™

Introduction

What's New? 5
Choosing the right Enclosure for your needs 6
Addressing Industry-Specific Challenges 7
Digital Tools for Every Step of Your Enclosure Project 8
Offer Overview and Selection Table 10

1 PanelSeT Steel Enclosures 12

Steel Boxes 14
Steel Wall-Mounted Enclosures 26
Steel Floor-Standing Enclosures 58

2 PanelSeT Stainless-Steel Enclosures 82

How to Select the Right Stainless-Steel Enclosures 84
Stainless-Steel Industrial Boxes 86
Stainless-Steel Wall-Mounted Enclosures 96
Stainless-Steel Floor-Standing Enclosures 106

3 PanelSeT Insulated Enclosures 118

Insulated Boxes 120
Insulated Wall-Mounted Enclosures 144
Insulated Floor-Standing Enclosures 156

4 Specific Applications Enclosures 168

5 ClimaSys Thermal Management System 390

6 Accessories 456

7 Spare Parts 576

8 Useful Technical Information 592

9 Index of References 604

Low-Carbon Emission Steel

PanelSeT SFN

Manufactured with a minimum of 50% low carbon emission steel



PanelSeT SM

Manufactured with a minimum of 50% low carbon emission steel



Low-Carbon Emission Stainless-Steel



PanelSeT SBX

Manufactured with a minimum of 90% low carbon emission steel

Recycled Polyester and Plastic

PanelSeT TBS

Manufactured with a minimum of 45% recycled content ABS



PanelSeT PLM

Manufactured with a minimum of 37% recycled content



Low Global Warming Potential Refrigerants



ClimaSys CU

IMPACT Company

We are committed to building a lower-carbon future, from sourcing to delivery

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU Cooling Units



- **ClimaSys cooling units comply with current F-gas regulations,** using refrigerants with **lower Global Warming Potential** (GWP), such as R513A (GWP ≈ 629), in line with established market expectations.
- The **ClimaSys portfolio is structured to address evolving European regulatory requirements** through the progressive introduction of cooling units using R1234yf refrigerant (GWP ≈ 4).
- This positioning enables alignment with stricter GWP thresholds (≤ 150) while maintaining consistency across the product range.
- As a result, **the ClimaSys cooling unit offer is structured to support compliance with current regulations and facilitate the transition toward lower-GWP refrigerant solutions,** helping reduce environmental impact and support long-term sustainability objectives.

New **Certifications**



- **PrismaSeT HD 800 V / 1000 V AC**
  The new certification for PrismaSeT HD significantly increases its relevance for solar plants, microgrids, and modern industrial systems operating at 800-1000 V AC for higher energy-transport efficiency. Built on IEC 61439 compliance, IP55 protection, and IK10 mechanical robustness, it helps ensure safe and reliable performance in demanding environments.

- **PanelSeT SFN MCC 4000 A for Drives and Starters**
  This certification position PanelSeT SFN as a fully compliant compartmentalized MCC for integrating build on IEC 61439 compliance, up to IP55 protection rating and IK10 mechanical robustness. It is constructed using durable low-carbon emission steel. It helps deliver the reliability and safety required for industries such as water, mining, oil and gas, manufacturing, and energy.

- **PanelSeT PLA for Electrical Distribution and EV**
  A specific architecture of PanelSeT PLA suitable for applications as EV charging station has been certified with IEC 61439-1 and 2 for 630 A and 1600 A.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Choosing the right Enclosure for your needs

Enclosure Materials – Key Benefits and Applications

	Steel	Stainless-steel	Polyester
Key Benefits	• Very high mechanical strength • Durability and long lifetime • Cost/performance ratio • Wide range of sizes, accessories and customization • Suitable for heavy and complex assemblies • Available in low carbon emission steel versions	• Very strong corrosion resistance • Hygiene and cleanability • Very high IP and IK ratings • Suitable for harsh chemicals and humidity	• Corrosion free material • Lightweight and easy to install • Electrical insulation (Class II) • Very good outdoor resistance (UV, humidity, chemicals) • Very high IP ratings • Available with recycled material content
Limitations	• Sensitive to corrosion in aggressive environments (unless treated) • Heavier than polyester solutions • Requires grounding	• Higher cost than polyester solutions • Heavier material • Overspecification for standard environments	• Lower mechanical strength than steel • Size limitations for very large assemblies • Not suited for very heavy equipment
Typical Applications	• Industrial automation and control panels • Machinery OEM • Power distribution switchboards • Manufacturing plants (indoor, nonclean) • Infrastructure technical rooms	• Food and beverage processing • Pharmaceutical and biotech • Chemical and petrochemical plants • Marine and coastal environments • Water treatment (corrosive zones)	• Outdoor infrastructure (solar, EV charging, transport) • Water and wastewater networks • Telecommunications • Renewable energy installations • Public and residential environments

Enclosure Materials Comparison

✓ = Strong fit
◐ = Suitable / depends on conditions
— = Not recommended


	Steel	Stainless-steel	Polyester
Mechanical Strength	✓✓✓ Very high protection IK08 - IK10	✓✓✓ Very high protection IK08 - IK10	◐ Medium to high protection IK07 - IK10
Corrosion Resistance	◐ Requires treatment / Mainly indoor	✓✓✓ Very high corrosion resistance	✓✓✓ Naturally corrosion-free
Cleanability	— Low fit	✓✓✓ Strong fit	◐ Suitable (no hygiene constraints)
Outdoor Exposure	◐ Possible with protection coating	✓✓✓ High corrosion resistant	✓✓✓ High UV and weather resistance
Electrical Insulation	— No insulation	— No insulation	✓✓✓ Class II insulation
Weight and Handling	◐ Heavy	◐ Heavy	✓✓✓ Lightweight and easy to handle
Customization and Scalability	✓✓✓ Very high customization options	✓✓ High customization options	✓✓ Modular options
Sustainability Potential	✓✓ Low-carbon emission steel options	✓✓ Low-carbon emission stainless-steel options	✓✓ Recycled material options

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Addressing Industry-Specific Challenges

Every industry has its own set of environmental, operational, and regulatory challenges. At Schneider Electric, we understand that a one-size-its-all approach does not work when it comes to protecting electrical and electronic equipment.
That's why enclosures and thermal management solutions are designed to meet the specific needs of diverse sectors, helping ensure performance, safety, and compliance in the most demanding conditions.

Transportation and mobility




- Heavy-duty polyester, steel (extra coating) and stainless-steel enclosures
- Custom plinths, cut-outs, and shock-resistance
- IP/IK ratings following needs

eMobility



- Plug-and-play kits
- Pre-certified PLA and PLM enclosures with IP66 and UV resistance
- Integrated cooling

IT, Data centers and Networks



- Steel enclosures
- Optimized airflow and active cooling integration
- Reinforced 19 racks for IT equipment
- EMC compliant designs

Industrial Manufacturing



- Wide range of steel, stainless-steel and polyester enclosures
- IP/IK ratings following needs

Water and Marine



- Polyester and stainless-steel enclosures with marine-grade coatings
- IP/IK ratings following needs
- Condensation prevention systems and DNV GL/Bureau Veritas certifications

Heavy Industries



- Certified material with traceability and compliance
- Enclosures designed with explosion containment and arc-flash considerations
- Thermal systems and pressure relief options

Nuclear



- S3D and SFN qualified for seismic performances
- S3D and SFN qualified for nuclear performances
- Manufacturing process with hight level of quality monitoring

Power and Grid



- Wide range of enclosures for indoor/ outdoor
- IP/IK ratings following needs
- Modular kits for fast deployments
- MCC compartmentalized Offer

Solar



- Solar (PV infrastructures, solar farms, BESS)
- Solution: PanelSeT PLM / PLA for external PV strings or main panels, PrismaSeT HD/6300 with 800 and 1000 VAC
- Certification for Electrical Distribution, SFN IT for BESS


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Digital Tools for Every Step of Your Enclosure Project

We support every stage of your enclosure design journey from selecting the right products to configuring complete solutions with confidence.

SPECIFY

Identify the right enclosure and compatible components



Product Selectors

Quickly identify the right enclosure, components, and accessories. Access complete compatibility recommendations in just a few clicks.
Ideal for first sizing, quick reference checks, fast BOM creation.

> **Free compatibility recommendations in just a few clicks**


DESIGN

Build your mechanical and electrical concept

SEE Electrical 3D Panel+ by ETAP

Create accurate 3D panel layouts and validate equipment positioning, clearances, and mounting using real PanelSeT enclosure data. Helps ensure a suitable fit from early design to assembly.
Leverage the Custom Enclosure Configurator (CEC) to export your enclosure directly into SEE electrical 3D Panel+ for a seamless and ready-to-use 3D assembly.





Technical Drawings Library (CAD Files and Macros)

Download 2D/3D CAD models, electrical schematic macros, and technical data for direct integration into your engineering tools. Go to the range or commercial reference you want to use to access the 3D/3D CAD models.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Digital Tools for Every Step of Your Enclosure Project

CONFIGURE

Build your complete enclosure or LV switchboard

Custom Enclosure Configurator (CEC)

Time Savings
Delivered pre-cut and pre-painted: no additional machining or finishing

Streamlined Logistics
- Flexible delivery options, e.g., scheduled deliveries for recurring orders
- Special packaging

Simplified Installation
Delivered ready-to-install with all required cut-outs


Ergonomic Design
Customized project dedicated to your personal requirements

Increased Life-Time
- Cut-outs made before panting help ensure corrosion protection and reliable sealing
- Painting service for better protection

Superior Quality
- No burrs on edges of cut-outs
- Help guaranty manufacturing tolerances

Improved Aesthetics
- Large choice of colors
- No scratches in external surfaces

Boosted Performance
- Adapted thermal management
- High-grade stainless-steel



> **Custom Enclosure Configurator (CEC)**

> **Watch the video**

Available in France, Spain, Germany, Netherland and UK since 2023.

EcoSet Config

EcoSet Config (progressively replacing the Rapsody software) streamlines LV switchboard configuration by guiding you through compatible architectures, devices, and accessories, including PanelSeT and PrismaSeT offers, for complete and consistent electrical project design.


> **These tools help you order easily with your preferred distributor or Schneider Electric**

OPTIMIZE

Enhance performance through thermal management

ProClima

Design an optimized thermal management system for your panels and safeguard equipment inside PanelSeT and PrismaSeT enclosures. Fully compatible with SEE Electrical software for an integrated workflow.



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Offer Overview and Selection Table

PanelSeT Enclosures - **Standard Applications**

Previously Spacial and Thalassa ranges

	Floor-standing	Wall-mounted	Box
Steel **Indoor industrial environments**	 **SFN** - Low-carbon Emission Steel Modular  **SM** - Low-carbon Emission Monobloc	 **S3D** - Wall-mounted  **CRN** - Wall-mounted	 **SDB** - Junction Box  **SBM** - Industrial Box
Stainless-Steel **Hygiene and corrosion-resistance**	 **SFX** - Modular  **SMX** - Monobloc	 **S3X** - Wall-Mounted	 **SBX** - Industrial Box
Insulating Material **Outdoor infrastructure and industry**	 **PLA** - GRP	 **PLM** - GRP	 **PLS** GRP  **TBS** Recycled ABS  **TBP** Polycarbonate

PanelSeT Enclosures - **Specific Applications**

Previously Spacial and Thalassa ranges

	Floor-standing	Wall-mounted
Electrical Distribution	 **PrismaSeT HD and 6300** Power Distribution Switchboards up to 6300 A	 **S3DM** - For Modular Switchgear  **S3DB** - For Terminal Blocks
Motor Control Center	 **SFN MCC** - Compartmentalized Enclosure	
Human Machine Interface	 **SFN PC** - Suitable Control PC Rack  **SD** - Control Desk	 **S3CM** - Control Enclosure with Suspension System
Network and Server	 **SFN IT** - Procured in Kit	 **Wall-mounted Racks**  **Actassi OPB and KDB** For commercial building
Severe Outdoor	 **SFN HD**  **PHD** - GRP	 **S3HD**
Seismic and Nuclear Ready Environments	 **SFN 3G/6G**  **SFN 6G Nuclear**	 **S3D 6G**
Explosive Atmosphere		 **S3DEX**
Electro Magnetic Compatibility	 **SFN HF**	 **S3HF**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Offer Overview and Selection Table

ClimaSys - **Thermal Management**

Cooling


Natural Airing


Smart Ventilation System


Forced Ventilation



Air-to-Water Exchangers



Air-to-Air Exchangers


Cooling Units

Heating


Resistance Heaters


Aluminum PTC Heater


Ultra Thin Resistance Heater

Controlling


Smart Thermal Controllers


Thermal Controllers

ProClima Web
Designing the suitable thermal solution for your control panels.
Fully integrated into SEE Electrical from ETAP




Accessories and Spare parts

Installation
Enclosures composition and installation


Canopy and Roofs


Panels - Side, Partition, Coupling


Floor Accessories


Fixing Accessories



Lifting


Cable Management
Outside and inside the enclosure


Cable Entries


Cable Holding

Mounting
For components assembly


Assembly - Mounting Plates, Cross Rails, Uprights, Chassis…


Electrical Distribution
Modular Chassis Busbar…


Door - Door Switch, Internal Doors Hinge and Closing…


Maintenance
Paint, Lighting

Spare Part


Cable Gland Plate


Doors - Doors + Accessories


Fixing Devices


Roof Accessories

Online Product Selector
Find accessories that suit your enclosure



PanelSeT Customization Services

Customization Services




Machining
Drilling, Miling, Deburring


Painting
Finishing


Accessories
Fitting


Expert Support for Advanced Projects

Custom Enclosure Configurator
Online customization, price quote and delivery lead time



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Steel Enclosures

Steel Boxes



Steel Wall-Mounted Enclosures



Steel Floor-Standing Enclosures



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Content

Steel Boxes	**14**
Steel Wall-Mounted Enclosures	**26**
Steel Floor-Standing Enclosures	**58**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Boxes

Panel**SeT** SDB: Junction Boxes

PB503350_61



Panel**SeT** SBM: Industrial Boxes

PB500237_38



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SDB: Junction Boxes

Introduction	16
Characteristics	18
Selection Table	18
Accessories	18
Dimensions	18

Panel**SeT** SBM: Industrial Boxes

Introduction	16
Characteristics	19
Selection Table	20
Accessories	22
Dimensions	24

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SDB and SBM

Introduction



Discover our boxes for industrial application and junction.

- PanelSeT SDB junction boxes are designed to suit transport infrastructures such as underground parking.
- PanelSeT SBM industrial boxes are simple, ergonomic and versatile industrial boxes to help protect electrical equipment in small control applications.
  Moreover, PanelSeT SBM can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SDB: Junction Boxes



Wide Range of Products
- Several dimensions
- Two versions: with or without knock outs



Easy Installation
- Holes heightened for internal fixation of accessories
- Maximal space inside




Designed for Robustness
- Simple and rounded design
- Ingress protection rating

PanelSeT SBM: Industrial Boxes



Large Dimension Choice
- 28 sizes available



Easy Installation
- Direct mounting through the rear
- Mounting with versatile external lugs



Added Value to your Work
- Quality and aesthetics
- Mechanical protection rating
- Ingress protection rating

For PanelSeT SBM only

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SDB: Junction Boxes

Characteristics

- PVC sealing gasket for sizes up to 206 x 156 mm and a rubber gasket for sizes > 256 x 206 mm.
- Back ready for threaded drill holes for fixing equipment.
  From size 155 x 105 mm and up, there are four M4 threaded holes fitted with removable plugs for direct fixing of the mounting plate.
- Including low cover.
- The SDB series consists of 2 basic models:
  - Without knock-outs: **NSYDB●●●**
  - With knock-outs: **NSYDB●●●M**
- Material: steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK07 according to IEC 62262
- Indoor Installation: Wall-mounted with drill holes fitted with plastic plugs for sealing, in compliance with IEC 62208 standards for UV radiation (see §9.12) and corrosion resistance test (see §9.13).

Selection Table

Low Cover Models without Knock-Outs


NSYDBN1510

External dimensions (mm)			Dimensions (mm)			Weight	References
Height (A)	Width (B)	Depth (C)	D	E	F	(kg)	
85	85	49	58	58	-	0.18	**NSYDBN88**
105	105	49	76	76	-	0.25	**NSYDBN1010**
155	105	61	124	74	56	0.38	**NSYDBN1510**
206	156	83	172	122	78	1.00	**NSYDBN2015**
256	206	93	220	170	88	1.5	**NSYDBN2520**
307	257	116	268	218	110	3.3	**NSYDBN3025**

Low Cover Models with Knock-Outs


NSYDB2015M

External dimensions (mm)			Dimensions (mm)			Knock-outs		Weight	References
Height (A)	Width (B)	Depth (C)	D	E	F	Height (A)	Width (B)	(kg)	
85	85	49	58	58	-	1 n° 1	1 n° 1	0.18	**NSYDB88M**
105	105	49	76	76	-	2 n° 1	1 n° 1	0.25	**NSYDB1010M**
155	105	61	124	74	56	3 n° 1	1 n° 1	0.38	**NSYDB1510M**
206	156	83	172	122	78	3 n° 2	2 n° 2	1.00	**NSYDB2015M**


Accessories

Plain Mounting Plates for SDB Junction Boxes


for models without knock-outs	for models with knock-outs	References
NSYDBN1510	NSYDB1510M	**NSYPMD1510**
NSYDBN2015	NSYDB2015M	**NSYPMD2015**
NSYDBN2520	-	**NSYPMD2520**
NSYDBN3025	-	**NSYPMD3025**

Dimensions


Group n° 1




Group n° 2



NSYDB●●●M



NSYDBN●●●



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SBM: Industrial Boxes

Characteristics

Characteristics	PanelSeT SBM - Flat box with plain cover
	PB502069_40_nb 
Box body	Single-piece body (cross-shaped structure). Front design incorporating folded gutters. Flat rear. 2 (or 3 for width 800 mm) drilled profiles for installing mounting plates and DIN rails, with a mounting hole spacing of 12.5 mm.
Box cover	Equipped with 4 or 6 half-turn thread screws, according to the version (6 screws for width greater than 400 mm) to help ensure maximum watertightness. Polyurethane sealing gasket.
Protection of personnel	Ground connection mandatory for all boxes: PanelSeT SBM steel boxes are equipped with a M6 x 16 ground stud welded in the cover, to be linked with the body for equipotential connection. Grounding strap to be ordered separately (Ø 6.4 mm terminal).
Material	Steel
Finish	Structured finish, epoxy polyester powder
Color	RAL 7035 gray
Ingress protection rating	IP66 according to IEC 60529
Mechanical protection rating	IK10 according to IEC 62262
Standard	Compliance with enclosure standard IEC 62208, and RoHS and REACH directives
Certifications **(see page 594)**	• UL (cULus), DNV • Types 4, 4X according to UL50E
Installation	Indoor. Direct wall-mounted (4 x Ø 10 mm holes) or with mounting lugs installed from the outside (to be ordered separately, see specific accessory pages).
Maximum load	Loading capacity on the body: 50 kg/m²
Vibration constraints	Specific construction of the PanelSeT SBM - single-piece body (rectangular structure). The rear is flat without added parts - this helps ensure compliance with certain vibration constraints.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SBM: Industrial Boxes

Selection Table

				PanelSeT SBM			
							
Dimensions (mm)			Cover screws	Flat box	Mounting plate without screws	DIN rail 10 rails, supplied without screws	Post mounting
Height	Width	Depth					
150	150	80	4	NSYSBM15158	NSYMM11SB	NSYAMRD15357SB	-
150	150	120	4	NSYSBM151512	NSYMM11SB	NSYAMRD15357SB	-
150	200	80	4	NSYSBM15208	NSYMM12SB	NSYAMRD20357SB	-
150	200	120	4	NSYSBM152012	NSYMM12SB	NSYAMRD20357SB	-
150	300	80	4	NSYSBM15308	NSYMM13SB	NSYAMRD30357SB	NSYSFPSC30
150	300	120	4	NSYSBM153012	NSYMM13SB	NSYAMRD30357SB	NSYSFPSC30
150	400	80	4	NSYSBM15408	NSYMM14SB	NSYAMRD40357SB	NSYSFPSC40
150	400	120	4	NSYSBM154012	NSYMM14SB	NSYAMRD40357SB	NSYSFPSC40
200	200	80	4	NSYSBM20208	NSYMM22SB	NSYAMRD20357SB	-
200	200	120	4	NSYSBM202012	NSYMM22SB	NSYAMRD20357SB	-
200	300	80	4	NSYSBM20308	NSYMM23SB	NSYAMRD30357SB	NSYSFPSC30
200	300	120	4	NSYSBM203012	NSYMM23SB	NSYAMRD30357SB	NSYSFPSC30
200	400	80	4	NSYSBM20408	NSYMM24SB	NSYAMRD40357SB	NSYSFPSC40
200	400	120	4	NSYSBM204012	NSYMM24SB	NSYAMRD40357SB	NSYSFPSC40
200	500	80	6	NSYSBM20508	NSYMM25SB	NSYAMRD50357SB	NSYSFPSC50
200	500	120	6	NSYSBM205012	NSYMM25SB	NSYAMRD50357SB	NSYSFPSC50
200	600	80	6	NSYSBM20608	NSYMM26SB	NSYAMRD60357SB	NSYSFPSC60
200	600	120	6	NSYSBM206012	NSYMM26SB	NSYAMRD60357SB	NSYSFPSC60
200	800	120	6	NSYSBM208012	NSYMM28SB	NSYAMRD80357SB	NSYSFPSC80
300	300	120	4	NSYSBM303012	NSYMM33SB	NSYAMRD30357SB	NSYSFPSC30
300	400	120	4	NSYSBM304012	NSYMM34SB	NSYAMRD40357SB	NSYSFPSC40
300	500	120	6	NSYSBM305012	NSYMM35SB	NSYAMRD50357SB	NSYSFPSC50
300	600	120	6	NSYSBM306012	NSYMM36SB	NSYAMRD60357SB	NSYSFPSC60
300	800	120	6	NSYSBM308012	NSYMM38SB	NSYAMRD80357SB	NSYSFPSC80
400	400	120	4	NSYSBM404012	NSYMM44SB	NSYAMRD40357SB	NSYSFPSC40
400	500	120	6	NSYSBM405012	NSYMM45SB	NSYAMRD50357SB	NSYSFPSC50
400	600	120	6	NSYSBM406012	NSYMM46SB	NSYAMRD60357SB	NSYSFPSC60
400	800	120	6	NSYSBM408012	NSYMM48SB	NSYAMRD80357SB	NSYSFPSC80

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SBM: Industrial Boxes


Selection Table

				Head screws			
							
	Mounting lugs	Self-tapping screws	Hinges	Double-bar shaped head screw	Triangular shaped head screw	Sealing kit	Dimensions (mm)
							Height / Width / Depth
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 150 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 150 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 200 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 200 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 300 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 300 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 400 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	150 / 400 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 200 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 200 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 300 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 300 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 400 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 400 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 500 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 500 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 600 / 80
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 600 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	200 / 800 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	300 / 300 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	300 / 400 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	300 / 500 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	300 / 600 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	300 / 800 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	400 / 400 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	400 / 500 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	400 / 600 / 120
	NSYAEFPFSB	NSYAMFSB	NSYAEDHSB	NSYAEDSBSB	NSYAEDSTSB	NSYPPSB	400 / 800 / 120

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SBM: Industrial Boxes

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Fixing Accessories

1



Mounting lugs

See details p. 477

2



Post fixing device

See details p. 480

Mounting Accessories

Equipment Assembly Accessories

3



Mounting plates

See details p. 508

4



Symetrical DIN rails

See details p. 528

5



Self-tapping screws

See details p. 541

6



Earthing

See details p. 540

Door Accessories


7



Hinges

See details p. 555

8



Head screws

See details p. 564

9



Sealing kit

See details p. 541

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SBM: Industrial Boxes

Dimensions


External Mounting of the Box and Mounting Accessories

Box		Mounting								
Height	Width	Ah	Bh	Bw	C	D	E	F	G	H
150 mm	150 mm	20.5 mm	109 mm	109 mm	125 mm	-	12.5 mm	85 mm	85 mm	-
	200 mm	20.5 mm	109 mm	159 mm	175 mm	-	12.5 mm	85 mm	135 mm	-
	300 mm	20.5 mm	109 mm	259 mm	275 mm	-	12.5 mm	85 mm	235 mm	-
	400 mm	20.5 mm	109 mm	359 mm	375 mm	-	12.5 mm	85 mm	335 mm	-
200 mm	200 mm	20.5 mm	159 mm	159 mm	175 mm	-	12.5 mm	135 mm	135 mm	-
	300 mm	20.5 mm	159 mm	259 mm	275 mm	-	12.5 mm	135 mm	235 mm	-
	400 mm	20.5 mm	159 mm	359 mm	375 mm	-	12.5 mm	135 mm	335 mm	-
	500 mm	20.5 mm	159 mm	459 mm	475 mm	-	12.5 mm	135 mm	435 mm	200 mm
	600 mm	20.5 mm	159 mm	559 mm	575 mm	-	12.5 mm	135 mm	535 mm	250 mm
	800 mm	20.5 mm	159 mm	759 mm	775 mm	387.5 mm	12.5 mm	135 mm	735 mm	350 mm
300 mm	300 mm	20.5 mm	259 mm	259 mm	275 mm	-	12.5 mm	235 mm	235 mm	-
	400 mm	20.5 mm	259 mm	359 mm	375 mm	-	12.5 mm	235 mm	335 mm	-
	500 mm	20.5 mm	259 mm	459 mm	475 mm	-	12.5 mm	235 mm	435 mm	200 mm
	600 mm	20.5 mm	259 mm	559 mm	575 mm	-	12.5 mm	235 mm	535 mm	250 mm
	800 mm	20.5 mm	259 mm	759 mm	775 mm	387.5 mm	12.5 mm	235 mm	735 mm	350 mm
400 mm	400 mm	20.5 mm	359 mm	359 mm	375 mm	-	12.5 mm	335 mm	335 mm	-
	500 mm	20.5 mm	359 mm	459 mm	475 mm	-	12.5 mm	335 mm	435 mm	200 mm
	600 mm	20.5 mm	359 mm	559 mm	575 mm	-	12.5 mm	335 mm	535 mm	250 mm
	800 mm	20.5 mm	359 mm	759 mm	775 mm	387.5 mm	12.5 mm	335 mm	735 mm	350 mm

Section A-A



Section B-B



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Steel Enclosures

Steel Wall-Mounted Enclosures

Panel**SeT** CRN

PB600369_68



Panel**SeT** S3D

PB600199_48_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** CRN

Introduction 28
Characteristics 30
Selection Table 32
Accessories 38
Dimensions 40

Panel**SeT** S3D

Introduction 42
Characteristics 44
Selection Table 46
Accessories 52
Dimensions 54
Mounting Options 56

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT CRN

Introduction



The PanelSeT CRN Steel Wall-Mounting Enclosure is developed for indoor, non-clean industrial environments. It has a wide range of sizes suitable for use in industrial automation and control, electrical distribution, electronics, and industrial networks.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Built to Last
- Industrial welding process
- Epoxy-polyester painting
- Polyurethane gasket
- Front folded gutter

These features help ensure quality as well as water and dust tightness over time.



Enhanced Safety
For people:
- Two welded M6 x 15 earth studs welded to the back and one M6 x 15 stud on the door

For your installation:
- Water and dust tightness
- Mechanical protection to help protect your components from external impact
- Concealed hinges to help prevent removal of the door




Smart
- Welded door reinforcement profile allowing the fixing of equipment in models from 500 mm in height



Flexible
- Optional version with glazed door including tempered glass



Ready to Assemble
- 4 or 6 welded M8 x 15 back studs with 10-mm collar for direct installation of mounting plate



Convenient
- Large embedded cable-entry plate with a neoprene gasket, flush with the back of the enclosure
- Two fixing options: direct or using the outside brackets

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT CRN

Characteristics

Characteristics	PanelSeT CRN
	PB500369_68 
	Available in 56 dimensions, including 14 versions equipped with a three-point locking system. The rear panel is connected to the side panels using a spacial profile that forming a sealed enclosure.
Material	Steel
Finish	Structured finish, epoxy-polyester powder
Color	RAL 7035 gray
Ingress protection rating	• IP66 for one-door enclosures according to IEC 60529 • IP55 for two-door enclosures according to IEC 60529
Mechanical protection rating	• IK10 for plain door • IK08 for glazed door according to IEC 62262
Standard	Compliance with enclosure standard IEC 62208, and RoHS and REACH directives
Certifications (see page 594)	• UL (cULus), CUL: Single-door: types 1, 2, 3, 3R, 4, 5, 12 and 13 Double-door: types 1, 12 and 13
Installation	• Given their strength, metal enclosures are particularly well suited to indoor areas where they may experience impacts
Supply	**Body** • 4 holes for direct fixing • Wall-fixing drill holes sealed with plastic plugs to help ensure the degree of protection (supplied as standard) • Wall-fixing bracket fixed from outside (brackets to be ordered separately) • Direct cable entry • Built-in cable-entry plate, flush with the back of the enclosure (without foamed-in gasket to facilitate machining) • Insulated cable entries with knock-outs, available as an accessory • Easy to equip with 4 or 6 welded back studs shouldered 10 mm **Door** • 3-mm double-bar lock as standard. (Wide choice of inserts as accessories and three-point locking system for heights from 1200 mm and widths from 1000 mm with standard 5-mm double-bar lock. Door-centering piece on two-door enclosures to help ensure proper door alignment) • Foamed-in polyurethane gasket on the doors to help guarantee water and dust tightness • Easily reversible door, fixed with two or three invisible metal hinges allowing the door to open to 120° • Reinforcement on plain doors with welded perforated door profiles for equipment fixing from models NSYCRN54150 • Welded earth studs on door and body • Delivered with a reusable packaging and technical instructions


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Wall-Mounted Enclosures


Panel**SeT** CRN

Selection Table

Dimensions (mm)						Enclosures			Mounting plates		
											
Height (A)	Width (B)	Depth (C)	Doors	IP	Weight (kg) (1)	with plain door, with mounting plate	with plain door, without mounting plate	with glazed door, without mounting plate	Plain	Microperforated	Telequick
200	200	150	1	66	2.5	-	NSYCRN22150 (2)	-	NSYMM22	-	-
200	300	150	1	66	3.9	-	NSYCRN23150 (2)	-	NSYMM32	NSYMF32	-
250	200	150	1	66	3.2	NSYCRN252150P	NSYCRN252150	-	NSYMM2520	-	-
300	250	150	1	66	4.2	NSYCRN325150P	NSYCRN325150	NSYCRN325150T	NSYMM3025	-	NSYMR3025
300	250	200	1	66	4.9	NSYCRN325200P	NSYCRN325200	NSYCRN325200T	NSYMM3025	-	NSYMR3025
300	300	150	1	66	5.0	NSYCRN33150P	NSYCRN33150	NSYCRN33150T	NSYMM33	NSYMF33	NSYMR33
300	300	200	1	66	6.0	NSYCRN33200P	NSYCRN33200	NSYCRN33200T	NSYMM33	NSYMF33	NSYMR33
300	400	200	1	66	6.4	-	NSYCRN34200	NSYCRN34200T	NSYMM43	NSYMF43	NSYMR34
300	450	150	1	66	6.7	-	NSYCRN345150	-	NSYMM3045	-	-
400	300	150	1	66	6.0	NSYCRN43150P	NSYCRN43150	NSYCRN43150T	NSYMM43	NSYMF43	NSYMR43
400	300	200	1	66	6.8	NSYCRN43200P	NSYCRN43200	NSYCRN43200T	NSYMM43	NSYMF43	NSYMR43
400	400	200	1	66	8.0	NSYCRN44200P	NSYCRN44200	NSYCRN44200T	NSYMM44	NSYMF44	NSYMR44
400	600	250	1	66	10.0	NSYCRN46250P	NSYCRN46250	NSYCRN46250T	NSYMM64	NSYMF64	NSYMR46
400	600	300	1	66	11.2	-	NSYCRN46300	-	NSYMM64	NSYMF64	NSYMR46
500	400	150	1	66	8.7	NSYCRN54150P	NSYCRN54150	NSYCRN54150T	NSYMM54	NSYMF54	NSYMR54
500	400	200	1	66	9.8	NSYCRN54200P	NSYCRN54200	NSYCRN54200T	NSYMM54	NSYMF54	NSYMR54
500	400	250	1	66	11.0	NSYCRN54250P	NSYCRN54250	NSYCRN54250T	NSYMM54	NSYMF54	NSYMR54
500	500	250	1	66	12.8	NSYCRN55250P	NSYCRN55250	NSYCRN55250T	NSYMM55	NSYMF55	NSYMR55
600	400	150	1	66	9.3	NSYCRN64150P	NSYCRN64150	NSYCRN64150T	NSYMM64	NSYMF64	NSYMR64
600	400	200	1	66	10.8	NSYCRN64200P	NSYCRN64200	NSYCRN64200T	NSYMM64	NSYMF64	NSYMR64
600	400	250	1	66	12.3	NSYCRN64250P	NSYCRN64250	NSYCRN64250T	NSYMM64	NSYMF64	NSYMR64
600	500	150	1	66	11.3	NSYCRN65150P	NSYCRN65150	-	NSYMM65	NSYMF65	NSYMR65
600	500	200	1	66	14.3	NSYCRN65200P	NSYCRN65200	NSYCRN65200T	NSYMM65	NSYMF65	NSYMR65
600	500	250	1	66	16.2	NSYCRN65250P	NSYCRN65250	NSYCRN65250T	NSYMM65	NSYMF65	NSYMR65
600	600	200	1	66	16.3	NSYCRN66200P	NSYCRN66200	NSYCRN66200T	NSYMM66	NSYMF66	NSYMR66
600	600	250	1	66	18.2	NSYCRN66250P	NSYCRN66250	NSYCRN66250T	NSYMM66	NSYMF66	NSYMR66
600	600	300	1	66	19.8	NSYCRN66300P	NSYCRN66300	NSYCRN66300T	NSYMM66	NSYMF66	NSYMR66
600	800	300	1	66	26.0	-	NSYCRN68300	NSYCRN68300T	NSYMM86	NSYMF86	NSYMR68
700	500	200	1	66	17.3	NSYCRN75200P	NSYCRN75200	NSYCRN75200T	NSYMM75	NSYMF75	NSYMR75
700	500	250	1	66	19.3	NSYCRN75250P	NSYCRN75250	NSYCRN75250T	NSYMM75	NSYMF75	NSYMR75
800	600	200	1	66	21.8	NSYCRN86200P	NSYCRN86200	NSYCRN86200T	NSYMM86	NSYMF86	NSYMR86
800	600	250	1	66	24.8	NSYCRN86250P	NSYCRN86250	NSYCRN86250T	NSYMM86	NSYMF86	NSYMR86
800	600	300	1	66	26.3	NSYCRN86300P	NSYCRN86300	NSYCRN86300T	NSYMM86	NSYMF86	NSYMR86
800	600	400	1	66	30.0	-	NSYCRN86400	NSYCRN86400T	NSYMM86	NSYMF86	NSYMR86
800	800	200	1	66	29.5	NSYCRN88200P	NSYCRN88200	-	NSYMM88	NSYMF88	NSYMR88
800	800	300	1	66	32.5	NSYCRN88300P	NSYCRN88300	NSYCRN88300T	NSYMM88	NSYMF88	NSYMR88
800	1000	300	2	55	40.0	-	NSYCRN810300D	-	NSYMM108	NSYMF108	NSYMR810
800	1200	300	2	55	46.0	-	NSYCRN812300D	-	NSYMM128	NSYMF128	-
1000	600	250	1	66	28.4	NSYCRN106250P	NSYCRN106250	NSYCRN106250T	NSYMM106	NSYMF106	NSYMR106
1000	600	300	1	66	30.6	NSYCRN106300P	NSYCRN106300	NSYCRN106300T	NSYMM106	NSYMF106	NSYMR106
1000	600	400	1	66	36.0	-	NSYCRN106400	NSYCRN106400T	NSYMM106	NSYMF106	NSYMR106
1000	800	250	1	66	34.5	NSYCRN108250P	NSYCRN108250	NSYCRN108250T	NSYMM108	NSYMF108	NSYMR108
1000	800	300	1	66	37.4	NSYCRN108300P	NSYCRN108300	NSYCRN108300T	NSYMM108	NSYMF108	NSYMR108
1000	800	400	1	66	43.0	-	NSYCRN108400	NSYCRN108400T	NSYMM108	NSYMF108	NSYMR108
1000	1000	300	2 (3)	55	47.0	-	NSYCRN1010300D	NSYCRN1010300T	NSYMM1010	NSYMF1010	NSYMR1010 (4)
1000	1200	300	2	55	55.0	-	NSYCRN1012300D	-	NSYMM1210	NSYMF1210	NSYMR1012 (4)
1000	1200	400	2	55	60.0	-	NSYCRN1012400D	-	NSYMM1210	NSYMF1210	NSYMR1012 (4)
1200	600	300	1	66	37.0	-	NSYCRN126300	NSYCRN126300T	NSYMM126	NSYMF126	NSYMR126
1200	600	400	1	66	42.0	-	NSYCRN126400	NSYCRN126400T	NSYMM126	NSYMF126	NSYMR126
1200	800	300	1	66	45.0	-	NSYCRN128300	NSYCRN128300T	NSYMM128	NSYMF128	NSYMR128
1200	800	400	1	66	50.0	-	NSYCRN128400	NSYCRN128400T	NSYMM128	NSYMF128	NSYMR128
1200	1000	300	2	55	56.0	-	NSYCRN1210300D	-	NSYMM1210	NSYMF1210	NSYMR1210 (4)
1200	1000	400	2	55	61.0	-	NSYCRN1210400D	-	NSYMM1210	NSYMF1210	NSYMR1210 (4)
1200	1200	300	2	55	64.0	-	NSYCRN1212300D	-	NSYMM1212	-	-
1200	1200	400	2	55	90.0	-	NSYCRN1212400D	-	NSYMM1212	-	-
1400	1000	300	2	55	80.0	-	NSYCRN1410300D	-	NSYMM1410	-	NSYMR1410 (4)

(1) Enclosure without mounting plate.
(2) Two cable gland plates, one on the top, one on the bottom.
(3) Except glazed door in single-door.
(4) Ref. **NSYEMR** mandatory.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


			Cable entries					
						Dimensions (mm)		
	Bakelite	DIN rail chassis	Type of cable entry	Cable gland plate standard	Cable gland plate insulated	Height (A)	Width (B)	Depth (C)
	-	-	O	NSYTLCRNO	-	200	200	150
	NSYMB32	-	B	NSYTLCRNB	-	200	300	150
	-	-	O	NSYTLCRNO	-	250	200	150
	NSYMB3025	-	A	NSYTLCRNA	-	300	250	150
	NSYMB3025	-	A	NSYTLCRNA	-	300	250	200
	NSYMB33	NSYMD33	B	NSYTLCRNB	NSYTSACRNB	300	300	150
	NSYMB33	NSYMD33	B	NSYTLCRNB	NSYTSACRNB	300	300	200
	NSYMB43	-	C	NSYTLCRNC	NSYTSACRNC	300	400	200
	NSYMB43	-	B	NSYTLCRNB	NSYTSACRNB	300	450	150
	NSYMB43	NSYMD43	B	NSYTLCRNB	NSYTSACRNB	400	300	150
	NSYMB43	NSYMD43	B	NSYTLCRNB	NSYTSACRNB	400	300	200
	-	-	C	NSYTLCRNC	NSYTSACRNC	400	400	200
	NSYMB64	-	D	NSYTLCRND	NSYTSACRND	400	600	250
	NSYMB64	-	D	NSYTLCRND	NSYTSACRND	400	600	300
	NSYMB54	NSYMD54	B	NSYTLCRNB	NSYTSACRNB	500	400	150
	NSYMB54	NSYMD54	C	NSYTLCRNC	NSYTSACRNC	500	400	200
	NSYMB54	NSYMD54	C	NSYTLCRNC	NSYTSACRNC	500	400	250
	-	-	D	NSYTLCRND	NSYTSACRND	500	500	250
	NSYMB64	NSYMD64	B	NSYTLCRNB	NSYTSACRNB	600	400	150
	NSYMB64	NSYMD64	C	NSYTLCRNC	NSYTSACRNC	600	400	200
	NSYMB64	NSYMD64	C	NSYTLCRNC	NSYTSACRNC	600	400	250
	NSYMB65	-	B	NSYTLCRNB	NSYTSACRNB	600	500	150
	NSYMB65	-	D	NSYTLCRND	NSYTSACRND	600	500	200
	NSYMB65	-	D	NSYTLCRND	NSYTSACRND	600	500	250
	-	NSYMD66	D	NSYTLCRND	NSYTSACRND	600	600	200
	-	NSYMD66	D	NSYTLCRND	NSYTSACRND	600	600	250
	-	NSYMD66	D	NSYTLCRND	NSYTSACRND	600	600	300
	-	-	E	NSYTLCRNC (5)	NSYTSACRNC	600	800	300
	NSYMB75	NSYMD75	D	NSYTLCRND	NSYTSACRND	700	500	200
	NSYMB75	NSYMD75	D	NSYTLCRND	NSYTSACRND	700	500	250
	NSYMB86	NSYMD86	D	NSYTLCRND	NSYTSACRND	800	600	200
	NSYMB86	NSYMD86	D	NSYTLCRND	NSYTSACRND	800	600	250
	NSYMB86	NSYMD86	D	NSYTLCRND	NSYTSACRND	800	600	300
	NSYMB86	NSYMD86	D	NSYTLCRND	NSYTSACRND	800	600	400
	-	-	E	NSYTLCRNC (5)	NSYTSACRNC (6)	800	800	200
	-	-	E	NSYTLCRNC (5)	NSYTSACRNC (6)	800	800	300
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	800	1000	300
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	800	1200	300
	-	-	D	NSYTLCRND	NSYTSACRND	1000	600	250
	-	-	D	NSYTLCRND	NSYTSACRND	1000	600	300
	-	-	D	NSYTLCRND	NSYTSACRND	1000	600	400
	NSYMB108	NSYMD108	E	NSYTLCRNC (5)	NSYTSACRNC (6)	1000	800	250
	NSYMB108	NSYMD108	E	NSYTLCRNC (5)	NSYTSACRNC (6)	1000	800	300
	NSYMB108	NSYMD108	C	2 x NSYTLCRNC	2 x NSYTSACRNC	1000	800	400
	NSYMB1210	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1000	1000	300
	NSYMB1210	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1000	1200	300
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1000	1200	400
	-	-	D	NSYTLCRND	NSYTSACRND	1200	600	300
	-	-	D	NSYTLCRND	NSYTSACRND	1200	600	400
	-	NSYMD128	C	2 x NSYTLCRNC	2 x NSYTSACRNC	1200	800	300
	-	NSYMD128	C	2 x NSYTLCRNC	2 x NSYTSACRNC	1200	800	400
	NSYMB1210	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1200	1000	300
	NSYMB1210	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1200	1000	400
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1200	1200	300
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1200	1200	400
	-	-	D	2 x NSYTLCRND	2 x NSYTSACRND	1400	1000	300

(5) With two holes.
(6) For flange openings type E, two **NSYTSACRNC** are required.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** CRN

Selection Table

Dimensions (mm)				Electric distribution					
				 PB500152_33_nb	 PB500381_19_nb	 PB500382_16_nb	 NSYCTL600DLM	 NSYPMP600DLM	 DB300118_13_nb
Height	Width	Depth	Doors	DLA insulated Distribution chassis	DL metal distribution chassis	DLM metal distribution chassis	Plain cover plate for DLM	Mounting plate for DLM	Blanking plate
200	200	150	1	-	-	-	-	-	-
200	300	150	1	-	-	-	-	-	-
250	200	150	1	-	-	-	-	-	-
300	250	150	1	-	NSYDLCR18	-	-	-	-
300	250	200	1	-	NSYDLCR18	-	-	-	-
300	300	150	1	-	-	-	-	-	-
300	300	200	1	-	-	-	-	-	-
300	400	200	1	-	-	-	-	-	-
300	450	150	1	-	-	-	-	-	-
400	300	150	1	NSYDLA24G	NSYDLCR24	NSYDLM24	-	-	NSYATP72M
400	300	200	1	NSYDLA24G	NSYDLCR36	NSYDLM24	-	-	NSYATP72M
400	400	200	1	-	NSYDLCR24 (1)	-	-	-	-
400	600	250	1	-	NSYDLCR36 (1)	-	-	-	-
400	600	300	1	-	-	-	-	-	-
500	400	150	1	NSYDLA48G	-	NSYDLM48	-	-	NSYATP72M
500	400	200	1	NSYDLA48G	-	NSYDLM48	-	-	NSYATP72M
500	400	250	1	NSYDLA48G	NSYDLCR48	NSYDLM48	-	-	NSYATP72M
500	500	250	1	-	NSYDLCR48 (1)	-	-	-	-
600	400	150	1	NSYDLA48PG	-	NSYDLM48P	-	-	NSYATP72M
600	400	200	1	NSYDLA48PG	-	NSYDLM48P	-	-	NSYATP72M
600	400	250	1	NSYDLA48PG	NSYDLCR64	NSYDLM48P	-	-	NSYATP72M
600	500	150	1	-	NSYDLCR64	-	-	-	-
600	500	200	1	-	-	-	-	-	-
600	500	250	1	-	NSYDLCR88	-	-	-	-
600	600	200	1	-	NSYDLCR88	NSYDLM84P	NSYCTL600DLM	-	NSYATP72M
600	600	250	1	-	-	NSYDLM84P	NSYCTL600DLM	-	-
600	600	300	1	-	-	NSYDLM84P	NSYCTL600DLM	-	NSYATP72M
600	800	300	1	-	-	-	-	-	-
700	500	200	1	NSYDLA66G / NSYDLA88G	-	NSYDLM66 / NSYDLM88	NSYCTL500DLM	-	NSYATP72M
700	500	250	1	NSYDLA66G / NSYDLA88G	-	NSYDLM66 / NSYDLM88	NSYCTL500DLM	-	NSYATP72M
800	600	200	1	NSYDLA84G / NSYDLA112G	NSYDLCR110	NSYDLM84 / NSYDLM112	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
800	600	250	1	NSYDLA84G / NSYDLA112G	-	NSYDLM84 / NSYDLM112	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
800	600	300	1	NSYDLA84G / NSYDLA112G	NSYDLCR135	NSYDLM84 / NSYDLM112	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
800	600	400	1	NSYDLA84G / NSYDLA112G	-	NSYDLM84 / NSYDLM112	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
800	800	200	1	-	-	-	-	-	-
800	800	300	1	-	-	-	-	-	-
800	1000	300	2	-	-	-	-	-	-
800	1200	300	2	-	-	-	-	-	-
1000	600	250	1	-	-	NSYDLM168	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
1000	600	300	1	-	-	NSYDLM168	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
1000	600	400	1	-	-	NSYDLM168	NSYCTL600DLM	NSYPMP600DLM	NSYATP72M
1000	800	250	1	NSYDLA234G	-	NSYDLM240	NSYCTL800DLM	NSYPMP800DLM	NSYATP72M
1000	800	300	1	NSYDLA234G	-	NSYDLM240	NSYCTL800DLM	NSYPMP800DLM	NSYATP72M
1000	800	400	1	NSYDLA234G	-	NSYDLM240	NSYCTL800DLM	NSYPMP800DLM	NSYATP72M
1000	1000	300	2	-	-	-	-	-	-
1000	1200	300	2	-	-	-	-	-	-
1000	1200	400	2	-	-	-	-	-	-
1200	600	300	1	-	-	-	-	-	-
1200	600	400	1	-	-	-	-	-	-
1200	800	300	1	-	-	-	-	-	-
1200	800	400	1	-	-	-	-	-	-
1200	1000	300	2	-	-	-	-	-	-
1200	1000	400	2	-	-	-	-	-	-
1200	1200	300	2	-	-	-	-	-	-
1200	1200	400	2	-	-	-	-	-	-
1400	1000	300	2	-	-	-	-	-	-

(1) To install the plinth to a wall-mounted enclosure, order ref. **NSYAPFWM**.

- For other dimensions, see our application offer.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electronic and network		Plinths (100 mm)		Plinths (200 mm)		Installation system			Dimensions (mm)		
 PB500383_21_nb		 NSYSPF6100		 NSYSPF6200		 PB500328_12_nb	 PB500111_14_nb	 PB-502979_5_nb			
Fixed 19" rack	Swing 19" rack	Single plinths side plate (1)	Single plinths front plate (1)	Single plinths side plate (1)	Single plinths front plate (1)	Internal door	Step slides	Wall-fixing lugs	Height	Width	Depth
-	-	-	-	-	-	-	-	NSYPFCR	200	200	150
-	-	-	-	-	-	-	-	NSYPFCR	200	300	150
-	-	-	-	-	-	-	-	NSYPFCR	250	200	150
-	-	-	-	-	-	-	-	NSYPFCR	300	250	150
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	300	250	200
-	-	-	-	-	-	-	-	NSYPFCR	300	300	150
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	300	300	200
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	300	400	200
-	-	-	-	-	-	-	-	NSYPFCR	300	450	150
-	-	-	-	-	-	NSYPIN43	-	NSYPFCR	400	300	150
-	-	-	-	-	-	NSYPIN43	NSYSDCR200	NSYPFCR	400	300	200
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	400	400	200
NSYVDM8UF	-	-	-	-	-	-	NSYSDCR250	NSYPFCR	400	600	250
NSYVDM8UF	-	NSYSPS3100SD	NSYSPF6100	NSYSPS3200SD	NSYSPF6200	-	NSYSDCR300	NSYPFCR	400	600	300
-	-	-	-	-	-	NSYPIN54	-	NSYPFCR	500	400	150
-	-	-	-	-	-	NSYPIN54	NSYSDCR200	NSYPFCR	500	400	200
-	-	-	-	-	-	NSYPIN54	NSYSDCR250	NSYPFCR	500	400	250
-	-	-	-	-	-	-	NSYSDCR250	NSYPFCR	500	500	250
-	-	-	-	-	-	NSYPIN64	-	NSYPFCR	600	400	150
-	-	-	-	-	-	NSYPIN64	NSYSDCR200	NSYPFCR	600	400	200
-	-	-	-	-	-	NSYPIN64	NSYSDCR250	NSYPFCR	600	400	250
-	-	-	-	-	-	-	-	NSYPFCR	600	500	150
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	600	500	200
-	-	-	-	-	-	-	NSYSDCR250	NSYPFCR	600	500	250
NSYVDM12UF	NSYVDM11UP	-	-	-	-	-	NSYSDCR200	NSYPFCR	600	600	200
NSYVDM12UF	NSYVDM11UP	-	-	-	-	-	NSYSDCR250	NSYPFCR	600	600	250
NSYVDM12UF	NSYVDM11UP	NSYSPS3100SD	NSYSPF6100	NSYSPS3200SD	NSYSPF6200	-	NSYSDCR300	NSYPFCR	600	600	300
-	-	NSYSPS3100SD	NSYSPF8100	NSYSPS3200SD	NSYSPF8200	-	NSYSDCR300	NSYPFCR	600	800	300
-	-	-	-	-	-	NSYPIN75	NSYSDCR200	NSYPFCR	700	500	200
-	-	-	-	-	-	NSYPIN75	NSYSDCR250	NSYPFCR	700	500	250
NSYVDM17UF	-	-	-	-	-	NSYPIN86	NSYSDCR200	NSYPFCR	800	600	200
NSYVDM17UF	NSYVDM16UP	-	-	-	-	NSYPIN86	NSYSDCR250	NSYPFCR	800	600	250
NSYVDM17UF	NSYVDM16UP	NSYSPS3100SD	NSYSPF6100	NSYSPS3200SD	NSYSPF6200	NSYPIN86	NSYSDCR300	NSYPFCR	800	600	300
NSYVDM17UF	NSYVDM16UP	NSYSPS4100SD	NSYSPF6100	NSYSPS4200SD	NSYSPF6200	NSYPIN86	NSYSDCR400	NSYPFCR	800	600	400
-	-	-	-	-	-	-	NSYSDCR200	NSYPFCR	800	800	200
-	-	NSYSPS3100SD	NSYSPF8100	NSYSPS3200SD	NSYSPF8200	-	NSYSDCR300	NSYPFCR	800	800	300
-	-	NSYSPS3100SD	NSYSPF10100	NSYSPS3200SD	NSYSPF10200	-	NSYSDCR300	NSYPFCR	800	1000	300
-	-	NSYSPS3100SD	NSYSPF12100	NSYSPS3200SD	NSYSPF12200	-	NSYSDCR300	NSYPFCR	800	1200	300
NSYVDM21UF	NSYVDM20UP	-	-	-	-	NSYPIN106	NSYSDCR250	NSYPFCR	1000	600	250
NSYVDM21UF	NSYVDM20UP	NSYSPS3100SD	NSYSPF6100	NSYSPS3200SD	NSYSPF6200	NSYPIN106	NSYSDCR300	NSYPFCR	1000	600	300
NSYVDM21UF	NSYVDM20UP	NSYSPS4100SD	NSYSPF6100	NSYSPS4200SD	NSYSPF6200	NSYPIN106	NSYSDCR400	NSYPFCR	1000	600	400
-	NSYVDM20U8P	-	-	-	-	NSYPIN108	NSYSDCR250	NSYPFCR	1000	800	250
-	NSYVDM20U8P	NSYSPS3100SD	NSYSPF8100	NSYSPS3200SD	NSYSPF8200	NSYPIN108	NSYSDCR300	NSYPFCR	1000	800	300
-	NSYVDM20U8P	NSYSPS4100SD	NSYSPF8100	NSYSPS4200SD	NSYSPF8200	NSYPIN108	NSYSDCR400	NSYPFCR	1000	800	400
-	-	NSYSPS3100SD	NSYSPF10100	NSYSPS3200SD	NSYSPF10200	-	NSYSDCR300	NSYPFCR	1000	1000	300
-	-	NSYSPS3100SD	NSYSPF12100	NSYSPS3200SD	NSYSPF12200	-	NSYSDCR300	NSYPFCR	1000	1200	300
-	-	NSYSPS4100SD	NSYSPF12100	NSYSPS4200SD	NSYSPF12200	-	NSYSDCR400	NSYPFCR	1000	1200	400
-	-	NSYSPS3100SD	NSYSPF6100	NSYSPS3200SD	NSYSPF6200	NSYPIN126	NSYSDCR300	NSYPFCR	1200	600	300
-	-	NSYSPS4100SD	NSYSPF6100	NSYSPS4200SD	NSYSPF6200	NSYPIN126	NSYSDCR400	NSYPFCR	1200	600	400
-	NSYVDM25U8P	NSYSPS3100SD	NSYSPF8100	NSYSPS3200SD	NSYSPF8200	NSYPIN128	NSYSDCR300	NSYPFCR	1200	800	300
-	NSYVDM25U8P	NSYSPS4100SD	NSYSPF8100	NSYSPS4200SD	NSYSPF8200	NSYPIN128	NSYSDCR400	NSYPFCR	1200	800	400
-	-	NSYSPS3100SD	NSYSPF10100	NSYSPS3200SD	NSYSPF10200	-	NSYSDCR300	NSYPFCR	1200	1000	300
-	-	NSYSPS4100SD	NSYSPF10100	NSYSPS4200SD	NSYSPF10200	-	NSYSDCR400	NSYPFCR	1200	1000	400
-	-	NSYSPS3100SD	NSYSPF12100	NSYSPS3200SD	NSYSPF12200	-	NSYSDCR300	NSYPFCR	1200	1200	300
-	-	NSYSPS4100SD	NSYSPF12100	NSYSPS4200SD	NSYSPF12200	-	NSYSDCR400	NSYPFCR	1200	1200	400
-	-	NSYSPS3100SD	NSYSPF10100	NSYSPS3200SD	NSYSPF10200	-	NSYSDCR300	NSYPFCR	1400	1000	300

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Wall-Mounted Enclosures

Panel**SeT** CRN

Selection Table

Dimensions (mm)			Installation system		
					
Height	Width	Depth	Post-fixing device	Canopies	Support bracket for enclosure with anti-tilt kit and reinforcement1400 mm (2)
200	200	150	-	-	NSYCOCNS1400
200	300	150	-	-	NSYCOCNS1400
250	200	150	-	NSYTJ2015	NSYCOCNS1400
300	250	150	-	-	NSYCOCNS1400
300	250	200	-	-	NSYCOCNS1400
300	300	150	NSYSFPSC30	NSYTJ3015	NSYCOCNS1400
300	300	200	NSYSFPSC30	NSYTJ3020	NSYCOCNS1400
300	400	200	NSYSFPSC40	NSYTJ4020	NSYCOCNS1400
300	450	150	-	-	NSYCOCNS1400
400	300	150	NSYSFPSC30	NSYTJ3015	NSYCOCNS1400
400	300	200	NSYSFPSC30	NSYTJ3020	NSYCOCNS1400
400	400	200	NSYSFPSC40	NSYTJ4020	NSYCOCNS1400
400	600	250	NSYSFPSC60	NSYTJ6025	NSYCOCNS1400
400	600	300	NSYSFPSC60	NSYTJ6030	NSYCOCNS1400
500	400	150	NSYSFPSC40	NSYTJ4015	NSYCOCNS1400
500	400	200	NSYSFPSC40	NSYTJ4020	NSYCOCNS1400
500	400	250	NSYSFPSC40	NSYTJ4025	NSYCOCNS1400
500	500	250	NSYSFPSC50	NSYTJ5025	NSYCOCNS1400
600	400	150	NSYSFPSC40	NSYTJ4015	NSYCOCNS1400
600	400	200	NSYSFPSC40	NSYTJ4020	NSYCOCNS1400
600	400	250	NSYSFPSC40	NSYTJ4025	NSYCOCNS1400
600	500	150	NSYSFPSC50	-	NSYCOCNS1400
600	500	200	NSYSFPSC50	NSYTJ5020	NSYCOCNS1400
600	500	250	NSYSFPSC50	NSYTJ5025	NSYCOCNS1400
600	600	200	NSYSFPSC60	NSYTJ6020	NSYCOCNS1400
600	600	250	NSYSFPSC60	NSYTJ6025	NSYCOCNS1400
600	600	300	NSYSFPSC60	NSYTJ6030	NSYCOCNS1400
600	800	300	NSYSFPSC80	NSYTJ8030	NSYCOCNS1400
700	500	200	NSYSFPSC50	NSYTJ5020	NSYCOCNS1400
700	500	250	NSYSFPSC50	NSYTJ5025	NSYCOCNS1400
800	600	200	NSYSFPSC60	NSYTJ6020	NSYCOCNS1400
800	600	250	NSYSFPSC60	NSYTJ6025	NSYCOCNS1400
800	600	300	NSYSFPSC60	NSYTJ6030	NSYCOCNS1400
800	600	400	NSYSFPSC60	NSYTJ6040	-
800	800	200	NSYSFPSC80	-	NSYCOCNS1400
800	800	300	NSYSFPSC80	NSYTJ8030	NSYCOCNS1400
800	1000	300	-	NSYTJ10030	-
800	1200	300	-	NSYTJ12030	-
1000	600	250	-	NSYTJ6025	NSYCOCNS1400
1000	600	300	-	NSYTJ6030	NSYCOCNS1400
1000	600	400	-	NSYTJ6040	-
1000	800	250	-	NSYTJ8025	NSYCOCNS1400
1000	800	300	-	NSYTJ8030	NSYCOCNS1400
1000	800	400	-	NSYTJ8040	-
1000	1000	300	-	NSYTJ10030	-
1000	1200	300	-	NSYTJ12030	-
1000	1200	400	-	NSYTJ12040	-
1200	600	300	-	NSYTJ6030	-
1200	600	400	-	NSYTJ6040	-
1200	800	300	-	NSYTJ8030	-
1200	800	400	-	NSYTJ8040	-
1200	1000	300	-	NSYTJ10030	-
1200	1000	400	-	NSYTJ10040	-
1200	1200	300	-	NSYTJ12030	-
1200	1200	400	-	NSYTJ12040	-
1400	1000	300	-	NSYTJ10030	-


(1) 2 coupling plates and supporting poles are required.
(2) Available in version 1800 mm: Ref. **NSYCOCNS1800**.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT CRN

Accessories



Installation Accessories

Composition Accessories

1



Canopy

See details p. 458

2



Plinths

See details p. 469

3



Support brackets

See details p. 466

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Fixing and Lifting Accessories

4



Mounting lugs and covers for fixing brackets

See details p. 477

5



Eyebolts

See details p. 482

6



Post fixing device

See details p. 480

Cable Management Accessories

Cable Entry Accessories

7



Gland plates: standard and insulated

See details p. 498/499

Mounting Accessories

Equipment Assembly Accessories

8



Mounting plates: plain, microperforated, telequick, bakelite, polyester

See details p. 509

9



Mounting rail

See details p. 528

10



Step Slides

See details p. 521

11

Earthing

See details p. 540

Door Accessories


12



Internal door

See details p. 550

13



Inserts, keys, locks and handles

See details p. 563

14



Door switch and retainer

See details p. 569

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Dimensions

Fig. 1






Fig. 2



DB300105EN_176_nb

A: Enclosure height
B: Enclosure width
C: Enclosure depth

PanelSeT CRN Cable Entry Dimensions and Type




DB300106_52_nb

None of the glazed-door enclosures have door reinforcement profiles.

Our diagrams and technical instruction sheets can be downloaded from our websites.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Dimensions of the Door-Reinforcement Profiles, the T Doors Only Include Vertical Profiles

1-door enclosure		Reinforcement profile	
Height (A)	Width (B)	E	D
800	600	519	525
1000	600	519	725
	800	719	725
1200	600	464	1075
	800	664	1075

2-door enclosure		Reinforcement profile			
		Rt. Door		Lft. Door	
Height (A)	Width (B)	E	D	E	D
800	1000	372	675	419	675
	1200	472	675	519	675
1000	1000	372	875	419	875
	1200	472	875	519	875
1200	1000	372	1075	419	1075
	1200	472	1075	519	1075
1400	1000	372	1275	419	1275



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D

Introduction





The PanelSeT S3D range offers one of the widest selections of steel wall-mounted enclosures on the market. The enclosure body and door are fitted with welded earthing studs, helping ensure reliable grounding and compliance with safety standards.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Service Life
- Quality of the welding and the painting



Component Protection
- Water and dust tightness and impact resistance
- EMC and ATEX application offer



Increased Choice
- Large range of universal dimensions
- Application offer with special dimensions




Easy Maintenance
- Removable hinges
- 1-lock system for heights below 600 mm
- 3-point lock for heights from 600 mm



Electrical Safety
- Earthing studs welded to the body and door



Easy Equipping
- 4 or 6 10 mm shouldered welded studs
- Broad range of mounting plates
- Broad range of cable gland plates
- Cable guides welded to the door from the height of 400 mm



Easy Handling
- Reusable packaging made with recycled cardboard
- No sharp edges

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D

Characteristics

Characteristics	PanelSeT S3D
	 PB500199_48_nb
	Three steel enclosure configurations are available: • Enclosure with plain door. • Enclosure with plain door delivered with a galvanized plain mounting plate, not installed. • Enclosure with glazed door, 4 mm-thick Securit® glass.
Personnel protection	• Earth connection: equipped with M6 x 16 earth studs welded in the body and the door for equipotential connection. Earth braid to be ordered separately (see page 540). • The enclosures are equipped from the height of 600 mm with three locking points with linkage, with a single control point, helping prevent the enclosures from being left half-closed. Locks and inserts, page 558.
Material	Steel
Finish	Structured finish, epoxy polyester powder
Color	RAL 7035 gray
Ingress protection rating	• IP66 for the single-door enclosures • IP55 for the double-door enclosures according to IEC 60529
Mechanical protection rating	• IK10 for the plain-door enclosures • IK08 for the glazed-door enclosures according to IEC 62262
Standards	• Compliance with enclosure standards IEC 62208 • Compliant with the RoHS and REACH directives
Certifications (see page 594)	• UL (cULus), DNV. For Atex see page 362 • UL Types 4, 4X and 13 for the single-door enclosures • UL Types 12, 13 for the double-door enclosures • CAN C22.2 No14 on NEMA and UL classification on page 599 **Nuclear decontamination: RAL 7035 gray and AFNOR A550 tests available on demand.** **More information on painting properties on page 600**
Installation	**Indoor** • Given their strength, metal enclosures are particularly well suited to indoor areas where they may experience impacts • 4 or 6 studs for widths 1000 and 1200 (see page 57) M8 x 25 collared studs for installing mounting plates and step slides, leaving a space of 10 mm behind them.
Supply	**Body** • Single-piece body (cross-shaped structure). Gutter-shaped front profile with double fold. **Flat rear** • M6 x 16 earthing screws for equipotential connection between the door and the body of the enclosure • Cable gland plate to enable the maximum access surface, delivered with the enclosure. This plate is flush with the body of the enclosure (detail and other options on page 499) • Direct wall-mounted (4 x Ø 10 mm holes) or with the help of fixing lugs installed from the outside (to be ordered separately, see page 477) **Door** • Wall-mounted enclosure supplied with 3-mm double-bar lock as standard • Polyurethane door gasket • M6 x 16 earthing screws for equipotential connection between the door and the body of the enclosure • Easily removable and reversible, with 20 mm return with double thickness granting excellent rigidity, opening to 120°, equipped with 2 or 3 invisible hinges (from the height of 800 mm) • Door opening to 180° with optional hinges (page 555) • For heights from 600 mm, three locking points with linkage, with a single control point. Simple reversal of linkage. Maximum load: 50 kg/m² • A handle is delivered which provides 2 functions: - Operating key - Tool for loosening the stud protection caps. This handle can be solidly attached to the locking system by means of a captive element • Perforated rails on the door, with drill holes with a diameter of 4.2 mm in steps of 25 mm: - 2 vertical rails from the height of 400 mm - 2 vertical rails and 2 horizontal rails from the width of 800 mm
Vibration constraints	Specific construction of the PanelSeT S3D - single-piece body (crossshaped structure). The rear is flat without added parts - this allows it to comply with certain vibration constraints. The tests were conducted according to the “rules for ships” by “Det Norske Veritas”. Enclosures labelled “DNV” have undergone these tests and obtained classification “A”. Since the enclosure is tested empty, it is advisable to rerun the tests with the enclosure completely equipped in its final configuration.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Wall-Mounted Enclosures



Panel**SeT** S3D

Selection Table

Dimensions (mm) (1)						Enclosures			Mounting plates	
										
Height	Width	Depth	Doors	IP	Weight (kg) (2)	Plain without mounting plate	Plain with mounting plate	Glazed without mounting plate	Plain	Microperforated
300	200	150	1	66	3.02	NSYS3D3215	NSYS3D3215P	-	NSYMM32	NSYMF32
300	250	150	1	66	3.48	NSYS3D32515	NSYS3D32515P	NSYS3D32515T	NSYMM3025	-
300	300	150	1	66	3.90	NSYS3D3315	NSYS3D3315P	NSYS3D3315T	NSYMM33	NSYMF33
300	300	200	1	66	4.50	NSYS3D3320	NSYS3D3320P	NSYS3D3320T	NSYMM33	NSYMF33
300	400	150	1	66	4.82	NSYS3D3415	NSYS3D3415P	NSYS3D3415T	NSYMM43	NSYMF43
300	400	200	1	66	5.60	NSYS3D3420	NSYS3D3420P	NSYS3D3420T	NSYMM43	NSYMF43
400	300	150	1	66	4.90	NSYS3D4315	NSYS3D4315P	NSYS3D4315T	NSYMM43	NSYMF43
400	300	200	1	66	5.00	NSYS3D4320	NSYS3D4320P	NSYS3D4320T	NSYMM43	NSYMF43
400	400	200	1	66	6.50	NSYS3D4420	NSYS3D4420P	NSYS3D4420T	NSYMM44	NSYMF44
400	600	200	1	66	10.50	NSYS3D4620	NSYS3D4620P	NSYS3D4620T	NSYMM64	NSYMF64
400	600	250	1	66	12.00	NSYS3D4625	NSYS3D4625P	NSYS3D4625T	NSYMM64	NSYMF64
500	300	200	1	66	7.50	NSYS3D5320	NSYS3D5320P	NSYS3D5320T	NSYMM53	NSYMF53
500	400	200	1	66	9.30	NSYS3D5420	NSYS3D5420P	NSYS3D5420T	NSYMM54	NSYMF54
500	400	250	1	66	10.20	NSYS3D5425	NSYS3D5425P	NSYS3D5425T	NSYMM54	NSYMF54
500	500	200	1	66	11.18	NSYS3D5520	NSYS3D5520P	NSYS3D5520T	NSYMM55	NSYMF55
500	500	250	1	66	12.06	NSYS3D5525	NSYS3D5525P	NSYS3D5525T	NSYMM55	NSYMF55
600	400	200	1	66	11.00	NSYS3D6420	NSYS3D6420P	NSYS3D6420T	NSYMM64	NSYMF64
600	400	250	1	66	12.00	NSYS3D6425	NSYS3D6425P	NSYS3D6425T	NSYMM64	NSYMF64
600	500	250	1	66	16.20	NSYS3D6525	NSYS3D6525P	NSYS3D6525T	NSYMM65	NSYMF65
600	600	200	1	66	14.00	NSYS3D6620	NSYS3D6620P	NSYS3D6620T	NSYMM66	NSYMF66
600	600	250	1	66	15.00	NSYS3D6625	NSYS3D6625P	NSYS3D6625T	NSYMM66	NSYMF66
600	600	300	1	66	17.00	NSYS3D6630	NSYS3D6630P	NSYS3D6630T	NSYMM66	NSYMF66
600	600	400	1	66	19.00	NSYS3D6640	NSYS3D6640P	NSYS3D6640T	NSYMM66	NSYMF66
600	800	300	1	66	25.50	NSYS3D6830	NSYS3D6830P	NSYS3D6830T	NSYMM86	NSYMF86
700	500	250	1	66	15.00	NSYS3D7525	NSYS3D7525P	NSYS3D7525T	NSYMM75	NSYMF75
800	600	200	1	66	21.00	NSYS3D8620	NSYS3D8620P	NSYS3D8620T	NSYMM86	NSYMF86
800	600	250	1	66	23.00	NSYS3D8625	NSYS3D8625P	NSYS3D8625T	NSYMM86	NSYMF86
800	600	300	1	66	25.00	NSYS3D8630	NSYS3D8630P	NSYS3D8630T	NSYMM86	NSYMF86
800	600	400	1	66	29.00	NSYS3D8640	NSYS3D8640P	NSYS3D8640T	NSYMM86	NSYMF86
800	800	250	1	66	30.00	NSYS3D8825	NSYS3D8825P	NSYS3D8825T	NSYMM88	NSYMF88
800	800	300	1	66	32.00	NSYS3D8830	NSYS3D8830P	NSYS3D8830T	NSYMM88	NSYMF88
800	1000	300	1	66	38.00	NSYS3D81030	NSYS3D81030P	-	NSYMM108	NSYMF108
800	1000	300	2	55	43.50	NSYS3D81030D	NSYS3D81030DP	-	NSYMM108	NSYMF108
800	1200	300	2	55	46.00	NSYS3D81230D	NSYS3D81230DP	-	NSYMM128	NSYMF128
1000	600	250	1	66	28.00	NSYS3D10625	NSYS3D10625P	NSYS3D10625T	NSYMM106	NSYMF106
1000	600	300	1	66	30.60	NSYS3D10630	NSYS3D10630P	NSYS3D10630T	NSYMM106	NSYMF106
1000	600	400	1	66	33.00	NSYS3D10640	NSYS3D10640P	NSYS3D10640T	NSYMM106	NSYMF106
1000	800	250	1	66	35.00	NSYS3D10825	NSYS3D10825P	NSYS3D10825T	NSYMM108	NSYMF108
1000	800	300	1	66	38.00	NSYS3D10830	NSYS3D10830P	NSYS3D10830T	NSYMM108	NSYMF108
1000	800	400	1	66	42.00	NSYS3D10840	NSYS3D10840P	NSYS3D10840T	NSYMM108	NSYMF108
1000	1000	300	1	66	46.00	NSYS3D101030	NSYS3D101030P	NSYS3D101030T	NSYMM1010	NSYMF1010
1000	1000	300	2	55	46.00	NSYS3D101030D	NSYS3D101030DP	NSYS3D101030DT	NSYMM1010	NSYMF1010
1000	1200	300	2	55	53.00	NSYS3D101230D	NSYS3D101230DP	-	NSYMM1210	NSYMF1210
1000	1200	400	2	55	60.00	NSYS3D101240D	NSYS3D101240DP	-	NSYMM1210	NSYMF1210
1200	600	300	1	66	37.00	NSYS3D12630	NSYS3D12630P	NSYS3D12630T	NSYMM126	NSYMF126
1200	600	400	1	66	42.00	NSYS3D12640	NSYS3D12640P	NSYS3D12640T	NSYMM126	NSYMF126
1200	800	300	1	66	45.00	NSYS3D12830	NSYS3D12830P	NSYS3D12830T	NSYMM128	NSYMF128
1200	800	400	1	66	49.00	NSYS3D12840	NSYS3D12840P	NSYS3D12840T	NSYMM128	NSYMF128
1200	1000	300	1	66	53.00	NSYS3D121030	NSYS3D121030P	NSYS3D121030T	NSYMM1210	NSYMF1210
1200	1000	300	2	55	54.00	NSYS3D121030D	NSYS3D121030DP	NSYS3D121030DT	NSYMM1210	NSYMF1210
1200	1000	400	2	55	61.00	NSYS3D121040D	NSYS3D121040DP	-	NSYMM1210	NSYMF1210
1200	1200	300	2	55	64.00	NSYS3D121230D	NSYS3D121230DP	-	NSYMM1212	-
1200	1200	400	2	55	90.00	NSYS3D121240D	NSYS3D121240DP	-	NSYMM1212	-
1400	1000	300	2	55	80.00	NSYS3D141030D	NSYS3D141030DP	-	NSYMM1410	-

(1) For other dimensions, see our application offer, page 168.
(2) Enclosure without mounting plate.
(3) When width ≥ 1000 ref. **NSYEMR** is mandatory (see on page 57).

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

				Modular mounting plate			Cross-rails			
										
								Dimensions (mm) (1)		
	Telequick	Bakelite	Module	Modular chassis DLM Steel	Modular chassis DLA Insulated	DIN rail chassis	Type	Door cross-rails	Height	Width	Depth
	NSYMR32	NSYMB32	-	-	-	-	-	-	300	200	150
	NSYMR3025	NSYMB3025	-	-	-	-	-	-	300	250	150
	NSYMR33	-	-	-	-	NSYMD33	B	-	300	300	150
	NSYMR33	-	-	-	-	NSYMD33	B	-	300	300	200
	NSYMR34	NSYMB43	-	-	-	-	-	-	300	400	150
	NSYMR34	NSYMB43	-	-	-	-	-	-	300	400	200
	NSYMR43	NSYMB43	24	NSYDLM24	-	NSYMD43	B	-	400	300	150
	NSYMR43	NSYMB43	24	NSYDLM24	NSYDLA24G	NSYMD43	B	-	400	300	200
	NSYMR44	-	-	-	-	-	-	NSYTFPCRN4	400	400	200
	NSYMR46	NSYMB64	-	-	-	-	-	NSYTFPCRN6	400	600	200
	NSYMR46	NSYMB64	-	-	-	-	-	NSYTFPCRN6	400	600	250
	NSYMR53	-	-	-	-	-	-	-	500	300	200
	NSYMR54	NSYMB54	48	NSYDLM48	NSYDLA48G	NSYMD54	B	NSYTFPCRN4	500	400	200
	NSYMR54	NSYMB54	48	NSYDLM48	-	NSYMD54	B	NSYTFPCRN4	500	400	250
	NSYMR55	-	-	-	-	-	-	NSYTFPCRN5	500	500	200
	NSYMR55	-	-	-	-	-	-	NSYTFPCRN5	500	500	250
	NSYMR64	NSYMB64	48	NSYDLM48P	NSYDLA48PG	NSYMD64	B	NSYTFPCRN4	600	400	200
	NSYMR64	NSYMB64	48	NSYDLM48P	NSYDLA48PG	NSYMD64	B	NSYTFPCRN4	600	400	250
	NSYMR65	NSYMB65	-	-	-	-	-	NSYTFPCRN5	600	500	250
	NSYMR66	-	84	NSYDLM84P	-	NSYMD66	A	NSYTFPCRN6	600	600	200
	NSYMR66	-	84	NSYDLM84P	-	NSYMD66	A	NSYTFPCRN6	600	600	250
	NSYMR66	-	84	NSYDLM84P	-	NSYMD66	A	NSYTFPCRN6	600	600	300
	NSYMR66	-	84	NSYDLM84P	-	NSYMD66	A	NSYTFPCRN6	600	600	400
	NSYMR68	NSYMB86	-	-	-	NSYMD86	A	NSYTFPCRN8	600	800	300
	NSYMR75	NSYMB75	66	NSYDLM66	NSYDLA66G	NSYMD75	B	NSYTFPCRN5	700	500	250
	NSYMR86	NSYMB86	84 (3)	NSYDLM84	NSYDLA84G / NSYDLA112G	NSYMD86	A	NSYTFPCRN6	800	600	200
	NSYMR86	NSYMB86	112 (3)	NSYDLM112	NSYDLA84G / NSYDLA112G	NSYMD86	A	NSYTFPCRN6	800	600	250
	NSYMR86	NSYMB86	112 (3)	NSYDLM112	NSYDLA84G / NSYDLA112G	NSYMD86	A	NSYTFPCRN6	800	600	300
	NSYMR86	NSYMB86	112 (3)	NSYDLM112	NSYDLA84G / NSYDLA112G	NSYMD86	A	NSYTFPCRN6	800	600	400
	NSYMR88	-	-	-	-	-	-	NSYTFPCRN8	800	800	250
	NSYMR88	-	-	-	-	-	-	NSYTFPCRN8	800	800	300
	NSYMR810	NSYMB108	-	-	-	-	-	NSYTFPCRN10	800	1000	300
	NSYMR810	NSYMB108	-	-	-	-	-	-	800	1000	300
	2x NSYMR86	2x NSYMB86	-	-	-	2x NSYMD86	A	-	800	1200	300
	NSYMR106	-	168	NSYDLM168	-	-	-	NSYTFPCRN6	1000	600	250
	NSYMR106	-	168	NSYDLM168	-	-	-	NSYTFPCRN6	1000	600	300
	NSYMR106	-	168	NSYDLM168	-	-	-	NSYTFPCRN6	1000	600	400
	NSYMR108	NSYMB108	234	NSYDLM240	NSYDLA234G	NSYMD108	A	NSYTFPCRN8	1000	800	250
	NSYMR108	NSYMB108	234	NSYDLM240	NSYDLA234G	NSYMD108	A	NSYTFPCRN8	1000	800	300
	NSYMR108	NSYMB108	234	NSYDLM240	NSYDLA234G	NSYMD108	A	NSYTFPCRN8	1000	800	400
	NSYMR1012	-	-	-	-	-	-	NSYTFPCRN10	1000	1000	300
	NSYMR1012	-	-	-	-	-	-	-	1000	1000	300
	NSYMR1012	NSYMB1210	-	-	-	-	-	-	1000	1200	300
	NSYMR1012	NSYMB1210	-	-	-	-	-	-	1000	1200	400
	-	-	-	-	-	-	-	-	1200	600	300
	-	-	-	-	-	-	-	-	1200	600	400
	NSYMR128	-	-	-	-	NSYMD128	A	NSYTFPCRN8	1200	800	300
	NSYMR128	-	-	-	-	NSYMD128	A	NSYTFPCRN8	1200	800	400
	NSYMR1210	NSYMB1210	-	-	-	-	-	NSYTFPCRN10	1200	1000	300
	NSYMR1210	NSYMB1210	-	-	-	-	-	-	1200	1000	300
	NSYMR1210	NSYMB1210	-	-	-	-	-	-	1200	1000	400
	-	-	-	-	-	-	-	-	1200	1200	300
	-	-	-	-	-	-	-	-	1200	1200	400
	NSYMR1410	-	-	-	-	-	-	-	1400	1000	300

Wall fixing lugs: page 477
Steel: **NSYAEFPFSC**
Stainless-steel: **NSYAEFPFXSC**

Reinforcement for heavy loads: page 478
NSYAEFAHLBSC
Locking accessories: page 557


Door accessories: page 569
Clip-on nuts: page 523
Self-tapping screw: **NSYS13M5HS** / page 541

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Wall-Mounted Enclosures

Panel**SeT** S3D

Selection Table

			Electronics and networks, 19" racks				Cable entry accessories, Cable gland plates				
											
Dimensions (mm) (1)			Fixed	Number of units	Swing	Number of units	Entry type	Standard steel	Aluminum	Steel with cut-out for FL membrane (2)	FlexiCable (6)
Height	Width	Depth									
300	200	150	-	-	-	-	A	**NSYTLA**	**NSYTLAUHD**	-	-
300	250	150	-	-	-	-	A	**NSYTLA**	**NSYTLAUHD**	-	-
300	300	150	-	-	-	-	B	**NSYTLB**	**NSYTLBU**	-	-
300	300	200	-	-	-	-	C	**NSYTLC**	**NSYTLCUHD**	**NSYTLCFL**	**NSYTLCME**
300	400	150	-	-	-	-	B	**NSYTLB**	**NSYTLBU**	-	-
300	400	200	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
400	300	150	-	-	-	-	B	**NSYTLB**	**NSYTLBU**	-	-
400	300	200	-	-	-	-	C	**NSYTLC**	**NSYTLCUHD**	**NSYTLCFL**	**NSYTLCME**
400	400	200	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
400	600	200	**NSYVDM8UF**	8	-	-	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
400	600	250	**NSYVDM8UF**	8	-	-	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
500	300	200	-	-	-	-	C	**NSYTLC**	**NSYTLCUHD**	**NSYTLCFL**	**NSYTLCME**
500	400	200	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
500	400	250	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
500	500	200	-	-	-	-	E	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	**NSYTLEME**
500	500	250	-	-	-	-	E	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	**NSYTLEME**
600	400	200	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
600	400	250	-	-	-	-	D	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	**NSYTLDME**
600	500	250	-	-	-	-	E	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	**NSYTLEME**
600	600	200	**NSYVDM12UF**	12	**NSYVDM11UP**	11	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
600	600	250	**NSYVDM12UF**	12	**NSYVDM11UP**	11	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
600	600	300	**NSYVDM12UF**	12	**NSYVDM11UP**	11	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
600	600	400	**NSYVDM12UF**	12	**NSYVDM11UP**	11	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
600	800	300	-	-	-	-	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
700	500	250	-	-	-	-	E	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	**NSYTLEME**
800	600	200	**NSYVDM17UF**	17	**NSYVDM16UP**	16	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
800	600	250	**NSYVDM17UF**	17	**NSYVDM16UP**	16	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
800	600	300	**NSYVDM17UF**	17	**NSYVDM16UP**	16	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
800	600	400	**NSYVDM17UF**	17	**NSYVDM16UP**	16	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
800	800	250	-	-	-	-	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
800	800	300	-	-	-	-	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
800	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLDME**
800	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLDME**
800	1200	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLDME**
1000	600	250	**NSYVDM21UF**	21	**NSYVDM20UP**	20	F	**NSYTLF**	**NSYTLFU**	**NSYTLFFL**	**NSYTLFME**
1000	600	300	**NSYVDM21UF**	21	**NSYVDM20UP**	20	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
1000	600	400	**NSYVDM21UF**	21	**NSYVDM20UP**	20	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
1000	800	250	-	-	**NSYVDM20U8P**	20	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
1000	800	300	-	-	**NSYVDM20U8P**	20	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
1000	800	400	-	-	**NSYVDM20U8P**	20	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
1000	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1000	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1000	1200	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1000	1200	400	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1200	600	300	-	-	-	-	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
1200	600	400	-	-	-	-	G	**NSYTLG**	**NSYTLGU**	**NSYTLG2FL** (5)	**NSYTLGME**
1200	800	300	-	-	**NSYVDM25U8P**	25	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
1200	800	400	-	-	**NSYVDM25U8P**	25	D (4)	**NSYTLD**	**NSYTLDUHD**	**NSYTLDFL**	2x **NSYTLDME**
1200	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1200	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1200	1000	400	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1200	1200	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1200	1200	400	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**
1400	1000	300	-	-	-	-	E (4)	**NSYTLE**	**NSYTLEUHD**	**NSYTLEFL**	2x **NSYTLEME**

(1) For other dimensions, see our application offer, page 168.
(2) FL13 for entry type A and B FL21 for all other entries.
(3) To adjust the depth of the internal door, please order the step slides.
(4) 2 plates.
(5) Exists with 1 cut-out **NSYTLGFL**.
(6) Cable entry FlexiCable IP55.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

	Composition accessories					Plinths						
	 PB500328_12_nb	 PB500111_14_nb	 NSYTJ2015	 PB500156_34_nb	 NSYAEFPFS3DW40	 NSYSPF6100_nb		 NSYSPF6200_nb				
	Internal door (3)	Step slides	Canopy	Fixing on post	Full width wall fixing lugs	Single plinths front plate (9)	Single plinths side plate (9)	Single plinths front plate (7) (9)	Single plinths side plate (7) (9)	Dimensions (mm) (1)		
										Height	Width	Depth
	-	-	NSYTJ2015	-	-	-	-	-	-	300	200	150
	-	-	NSYTJ2515	-	-	-	-	-	-	300	250	150
	-	-	NSYTJ3015	NSYSFPSC30	-	-	-	-	-	300	300	150
	-	NSYSDCR200	NSYTJ3020	NSYSFPSC30	-	-	-	-	-	300	300	200
	-	-	NSYTJ4015	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	300	400	150
	-	NSYSDCR200	NSYTJ4020	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	300	400	200
	NSYPIN43	-	NSYTJ3015	NSYSFPSC30	-	-	-	-	-	400	300	150
	NSYPIN43	NSYSDCR200	NSYTJ3020	NSYSFPSC30	-	-	-	-	-	400	300	200
	-	NSYSDCR200	NSYTJ4020	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	400	400	200
	-	NSYSDCR200	NSYTJ6020	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	400	600	200
	-	NSYSDCR250	NSYTJ6025	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	400	600	250
	-	NSYSDCR200	NSYTJ3020	NSYSFPSC30	-	-	-	-	-	500	300	200
	NSYPIN54	NSYSDCR200	NSYTJ4020	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	500	400	200
	NSYPIN54	NSYSDCR250	NSYTJ4025	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	500	400	250
	-	NSYSDCR200	NSYTJ5020	NSYSFPSC50	-	-	-	-	-	500	500	200
	-	NSYSDCR250	NSYTJ5025	NSYSFPSC50	-	-	-	-	-	500	500	250
	NSYPIN64	NSYSDCR200	NSYTJ4020	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	600	400	200
	NSYPIN64	NSYSDCR250	NSYTJ4025	NSYSFPSC40	NSYAEFPFS3DW40	-	-	-	-	600	400	250
	-	NSYSDCR250	NSYTJ5025	NSYSFPSC50	-	-	-	-	-	600	500	250
	-	NSYSDCR200	NSYTJ6020	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	600	600	200
	-	NSYSDCR250	NSYTJ6025	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	600	600	250
	-	NSYSDCR300	NSYTJ6030	NSYSFPSC60	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS3100SD	NSYSPF6200	NSYSPS3200SD	600	600	300
	-	NSYSDCR400	NSYTJ6040	NSYSFPSC60	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS4100SD	NSYSPF6200	NSYSPS4200SD	600	600	400
	-	NSYSDCR300	NSYTJ8030	NSYSFPSC80	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS3100SD	NSYSPF8200	NSYSPS3200SD	600	800	300
	NSYPIN75	NSYSDCR250	NSYTJ5025	NSYSFPSC50	-	-	-	-	-	700	500	250
	NSYPIN86	NSYSDCR200	NSYTJ6020	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	800	600	200
	NSYPIN86	NSYSDCR250	NSYTJ6025	NSYSFPSC60	NSYAEFPFS3DW60	-	-	-	-	800	600	250
	NSYPIN86	NSYSDCR300	NSYTJ6030	NSYSFPSC60	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS3100SD	NSYSPF6200	NSYSPS3200SD	800	600	300
	NSYPIN86	NSYSDCR400	NSYTJ6040	NSYSFPSC60	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS4100SD	NSYSPF6200	NSYSPS4200SD	800	600	400
	-	NSYSDCR250	NSYTJ8025	NSYSFPSC80	NSYAEFPFS3DW80	-	-	-	-	800	800	250
	-	NSYSDCR300	NSYTJ8030	NSYSFPSC80	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS3100SD	NSYSPF8200	NSYSPS3200SD	800	800	300
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	800	1000	300
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	800	1000	300
	-	NSYSDCR300 (8)	NSYTJ12030	-	-	-	-	-	-	800	1200	300
	NSYPIN106	NSYSDCR250	NSYTJ6025	-	NSYAEFPFS3DW60	-	-	-	-	1000	600	250
	NSYPIN106	NSYSDCR300	NSYTJ6030	-	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS3100SD	NSYSPF6200	NSYSPS3200SD	1000	600	300
	NSYPIN106	NSYSDCR400	NSYTJ6040	-	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS4100SD	NSYSPF6200	NSYSPS4200SD	1000	600	400
	NSYPIN108	NSYSDCR250	NSYTJ8025	-	NSYAEFPFS3DW80	-	-	-	-	1000	800	250
	NSYPIN108	NSYSDCR300	NSYTJ8030	-	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS3100SD	NSYSPF8200	NSYSPS3200SD	1000	800	300
	NSYPIN108	NSYSDCR400	NSYTJ8040	-	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS4100SD	NSYSPF8200	NSYSPS4200SD	1000	800	400
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	1000	1000	300
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	1000	1000	300
	-	NSYSDCR300 (8)	NSYTJ12030	-	-	NSYSPF12100	NSYSPS3100SD	NSYSPF12200	NSYSPS3200SD	1000	1200	300
	-	NSYSDCR400 (8)	NSYTJ12040	-	-	NSYSPF12100	NSYSPS4100SD	NSYSPF12200	NSYSPS4200SD	1000	1200	400
	NSYPIN126	NSYSDCR300	NSYTJ6030	-	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS3100SD	NSYSPF6200	NSYSPS3200SD	1200	600	300
	NSYPIN126	NSYSDCR400	NSYTJ6040	-	NSYAEFPFS3DW60	NSYSPF6100	NSYSPS4100SD	NSYSPF6200	NSYSPS4200SD	1200	600	400
	NSYPIN128	NSYSDCR300	NSYTJ8030	-	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS3100SD	NSYSPF8200	NSYSPS3200SD	1200	800	300
	NSYPIN128	NSYSDCR400	NSYTJ8040	-	NSYAEFPFS3DW80	NSYSPF8100	NSYSPS4100SD	NSYSPF8200	NSYSPS4200SD	1200	800	400
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	1200	1000	300
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	1200	1000	300
	-	NSYSDCR400	NSYTJ10040	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS4100SD	NSYSPF10200	NSYSPS4200SD	1200	1000	400
	-	NSYSDCR300 (8)	NSYTJ12030	-	-	NSYSPF12100	NSYSPS3100SD	NSYSPF12200	NSYSPS3200SD	1200	1200	300
	-	NSYSDCR400 (8)	NSYTJ12040	-	-	NSYSPF12100	NSYSPS4100SD	NSYSPF12200	NSYSPS4200SD	1200	1200	400
	-	NSYSDCR300	NSYTJ10030	-	NSYAEFPFS3DW100	NSYSPF10100	NSYSPS3100SD	NSYSPF10200	NSYSPS3200SD	1400	1000	300

(7) Also available in ventilated version with cable gland for widths of 600 and 800, see page 468.

(8) For the double mounting plates.

(9) To install the plinth to a wall-mounted enclosure, order ref. **NSYAPFWM**.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D

Selection Table

Dimensions (mm)			Composition accessories		
			 PB500331_15_nb	 PB500332_9_nb	 PB501821_9_nb
Height	Width	Depth	Support pillar adaption plate	Support pillar	Support bracket for enclosure with anti-tilt kit and reinforcement 1400 mm (1)
300	200	150	-	-	**NSYCOCNS1400**
300	250	150	-	-	**NSYCOCNS1400**
300	300	150	-	**NSYCOCN80**	**NSYCOCNS1400**
300	300	200	-	**NSYCOCN80**	**NSYCOCNS1400**
300	400	150	-	**NSYCOCN80**	**NSYCOCNS1400**
300	400	200	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
400	300	150	-	**NSYCOCN80**	**NSYCOCNS1400**
400	300	200	-	**NSYCOCN80**	**NSYCOCNS1400**
400	400	200	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
400	600	200	-	-	**NSYCOCNS1400**
400	600	250	-	-	**NSYCOCNS1400**
500	300	200	-	**NSYCOCN80**	**NSYCOCNS1400**
500	400	200	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
500	400	250	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
500	500	200	-	-	**NSYCOCNS1400**
500	500	250	-	-	**NSYCOCNS1400**
600	400	200	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
600	400	250	**NSYAEFP42S3D**	**NSYCOCN80**	**NSYCOCNS1400**
600	500	250	-	-	**NSYCOCNS1400**
600	600	200	-	-	**NSYCOCNS1400**
600	600	250	-	-	**NSYCOCNS1400**
600	600	300	-	-	**NSYCOCNS1400**
600	600	400	-	-	**NSYCOCNS1400**
600	800	300	-	-	**NSYCOCNS1400**
700	500	250	-	-	**NSYCOCNS1400**
800	600	200	-	-	**NSYCOCNS1400**
800	600	250	-	-	**NSYCOCNS1400**
800	600	300	-	-	**NSYCOCNS1400**
800	600	400	-	-	**NSYCOCNS1400**
800	800	250	-	-	**NSYCOCNS1400**
800	800	300	-	-	**NSYCOCNS1400**
800	1000	300	-	-	**NSYCOCNS1400**
800	1000	300	-	-	**NSYCOCNS1400**
800	1200	300	-	-	**NSYCOCNS1400**
1000	600	250	-	-	**NSYCOCNS1400**
1000	600	300	-	-	**NSYCOCNS1400**
1000	600	400	-	-	**NSYCOCNS1400**
1000	800	250	-	-	**NSYCOCNS1400**
1000	800	300	-	-	**NSYCOCNS1400**


(1) Available in version 1800 mm: ref. **NSYCOCNS1800**.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Steel Wall-Mounted Enclosures
PanelSeT S3D

Accessories



Installation Accessories

Composition Accessories

1



Canopy

See details p. 458

2



Plinths

See details p. 469

3



Support brackets

See details p. 466

4



Support pillar and adaptation plate

See details p. 466

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Management Accessories

Fixing and Lifting Accessories

5



Eyebolts

See details p. 482

6



Mounting lugs and covers for fixing brackets

See details p. 477

7



Full width fixing lugs and post fixing device

See details p. 478 and 480

Cable Management Accessories

Cable Entry Accessories

8



Multi cable entries; membranes, circular, rectangle, quick

See details p. 493

9



Cable glands

See details p. 489

10



Flexicable entries

See details p. 493

11



Cable gland plates: standard, aluminum and cut-out

See details p. 498

Mounting Accessories

Equipment Assembly Accessories

12



Mounting plates: plain, microperforated, telequick, bakelite, polyester

See details p. 509

13



Mounting rail

See details p. 528

14



Step Slides

See details p. 521

15



Earthing

See details p. 540

Door Accessories

16



Internal door

See details p. 550

17



Door hinges

See details p. 555


18



Inserts, keys, locks and handles

See details p. 558

19



Door switch and retainer


See details p. 569

> For more information consult the Accessories chapter **page 456**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Dimensions

Single-Door Enclosure




Double-Door Enclosure



A: Enclosure height
B: Enclosure width
C: Enclosure depth

1. A-200 from the height of 800 mm.
2. 4 or 6 (widths 1000 - 1200 mm) M8 x 25 mm backstuds.
3. 2 M6 x 17.5 mm earthing studs
4. Stud center-to-center distance.
5. Center-to-center distance of the holes for direct fixing.



Detail (2) Detail (3)


Comment:
The DXF diagrams can be downloaded from our websites.

Enclosure (mm)		Cable gland plate						
Width	Depth	Dim. (mm)	Type	No.	J	K	L	References
200 - 250	150 - 250	140 x 80	A	1	57	115	55	**NSYTLA**
300 - 400	150	245 x 80	B	1	57	220	55	**NSYTLB**
300	200	245 x 130	C	1	80	220	105	**NSYTLC**
400	200 - 250	345 x 130	D	1	80	320	105	**NSYTLD**
500	200 - 250	445 x 130	E	1	80	420	105	**NSYTLE**
600	200 - 250	545 x 130	F	1	80	520	105	**NSYTLF**
600	300 - 400	495 x 220	G	1	126*	470	195	**NSYTLG**
800	250 - 300 - 400	345 x 130	D	2	95**	320	105	2 x **NSYTLD**
1000 - 1200	300 - 400	445 x 130	E	2	95	420	105	2 x **NSYTLE**

* Except enclosure 1000 x 600 x 400 mm, J = 140 mm.
** Except enclosure 600 x 800 x 300 mm, J = 80 mm.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Perforated Rails on Plain Door*



1 Perforations with 25 mm spacing
2 1 M6 x 17.5 mm earthing stud.

* The glazed doors are equipped with a vertical cable guide on the hinge side.

Enclosure** (mm)		Perforated rails on the door (mm)				Perforated rails on the double-door (mm)				Perforated rails on the internal door (mm)			
Height	Width	Vertical		Horizontal		Vertical		Horizontal		Vertical		Horizontal	
		F	D	E	C	F	D	E	C	F	D	E	C
400	300	320	237	-	-	-	-	-	-	-	-	-	-
400	400	320	337	-	-	-	-	-	-	-	-	-	-
400	600	320	537	-	-	-	-	-	-	-	-	-	-
500	300	370	237	-	-	-	-	-	-	-	-	-	-
500	400	370	337	-	-	-	-	-	-	-	-	-	-
500	500	370	437	-	-	-	-	-	-	-	-	-	-
600	400	370	337	-	-	-	-	-	-	-	-	-	-
600	500	370	437	-	-	-	-	-	-	-	-	-	-
600	600	370	537	-	-	-	-	-	-	-	-	-	-
600	800	370	737	-	-	-	-	-	-	-	-	-	-
700	500	470	437	-	-	-	-	-	-	-	-	-	-
800	600	570	537	-	-	-	-	-	-	-	-	-	-
800	800	570	737	620	749	-	-	-	-	-	-	-	-
800	1000	570	937	820	749	570	437	320	749	620	437	320	749
800	1200	-	-	-	-	570	537	420	749	620	537	420	749
1000	600	770	537	420	949	-	-	-	-	-	-	-	-
1000	800	770	737	620	949	-	-	-	-	-	-	-	-
1000	1000	770	937	820	949	770	437	320	949	820	437	320	949
1000	1200	-	-	-	-	770	537	420	949	820	537	420	949
1200	600	970	537	420	1149	-	-	-	-	-	-	-	-
1200	800	970	737	620	1149	-	-	-	-	-	-	-	-
1200	1000	970	937	820	1149	970	437	320	1149	1020	437	320	1149
1200	1200	-	-	-	-	970	537	420	1149	1020	537	420	1149
1400	1000	-	-	-	-	970	437	320	1349	1020	437	320	1349


** The doors of enclosures with dimensions of less than 800 x 600 mm do not have horizontal cable guides.

Download the configuration sheets and DXF diagrams from www.se.com
Send them back to your local Schneider Electric office.
Take advantage of a shorter delivery time!

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Mounting Rail

PB503346_51_nb



Quick-Fixing Cross-Rails

PB503372_33_nb




Ease of Installation

PB503347_30_nb




Door Switch Mounting Option

PB503370_38_nb




With Din Rail

PB503348_30_nb



With Light Cross-Rails and Cage Nut

PB503371_40_nb




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation of Telequick Mounting Plates

Spacers for raising the mounting plate in the enclosures equipped with 6 studs.





Reference **NSYEMR**

Acceptable Loads on the Mounting Plates, Bases and Doors




PanelSeT S3D wall-mounted enclosures

Acceptable loads (kg)					
On plain mounting plates	On base	On door *	On vertical lug	On horizontal lug	References
60	135	50	350	190	**NSYS3D3215** to **NSYS3D5320**
90	135	50	350	190	**NSYS3D5420** to **NSYS3D6425**
135	135	50	350	190	**NSYS3D6620** to **NSYS3D8630**
150	135	50	350	190	**NSYS3D10625** to **NSYS3D10830**
180	135	50	350	190	**NSYS3D101030D** to **NSYS3D141030D**

* On a sheet door with a thickness of 20/10^{e} mm: 60 kg of maximum acceptable load (please consult us).

Areas without Cut-Outs

Spacers for raising the mounting plate in the enclosures equipped with 6 studs.



- For 800, 1000 and 1200 mm widths, 2 cable gland plates: See previous page.
- Vertical cable guides from 400 mm height.
- Horizontal cable guides from 800 mm width.
- Download our DXF diagrams from our websites.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Steel Enclosures

Steel Floor-Standing Enclosures

Panel**SeT** SM: Compact Enclosures

New

PB504072_ioP-Default



Panel**SeT** SFN: Modular Enclosures

NSYSFN20860



NSYSFN20860_enclosure



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SM: Compact Enclosures

Introduction	**60**
Characteristics	**62**
Selection Table	**64**
Accessories	**66**
Dimensions	**68**

Panel**SeT** SFN: Modular Enclosures

Introduction	**70**
Characteristics	**72**
Selection Table	**74**
Accessories	**78**
Dimensions	**80**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SM: Compact Enclosures

Introduction



New

The PanelSeT SM is a range of enclosures ideal for industrial automation and control appliances, and for machinery.
It offers a large portfolio of dimensions and delivery options.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SM Compact Enclosures



New

Reduced carbon footprint: manufactured with a minimum of 50% of low carbon emission steel produced from renewable energy and recycled materials (1), leading to a 23% CO_2 reduction on the total enclosure lifecycle (2)

50%



Robust

- Body made as a single piece with welded rear panel
- Front part forming a rigid frame with welded corners






Easy to Install

- Height-adjustable door rails suitable for cable fixing
- Optional adapter profiles can be added to provide the same fixing points as the suitable enclosure PanelSeT SFN





Protection

- IP protection supported by the rigidity of the enclosure, the expanded-polyurethane sealing gasket, and the final welding
- Double-door enclosures with inner lock on the left door



New

Comfort

- Sturdy handle design for easy activation of the locking system, accommodating any insert shape and cylindrical combination key
- Easily interchangeable insert with one click

New

Accessible

- Quick door removal and installation to facilitate assemble

New

Efficient

- Quick system for the mounting plate allowing faster assembly

(1) More info on Arcelor Mittal website (XCarb® recycled and renewably produced).
(2) According to the comparison of PanelSeT SM (ENVPEP2501030) and Spacial SM (ENVPEP110923EN) using the same calculation methodology provided in the Product Category Rules of PEP Ecopassport association (PCRed4).

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SM: Compact Enclosures

Characteristics

Characteristics	Compact enclosures PanelSeT SM
	
	• Compact body with a front rigid frame with welded corners and rear panel supports installed in depth to adjust and fix the equipment with a pitch of 25 mm
Basic composition	• The double doors are overlapping, with system for fixing the left door • Door reversible, 120° opening • Welded rear panel • System with 4 locking points with handle and 5-mm double-bar insert • Cable gland plate with 1 entry • Mounting plate support brackets
Versions / Configurations	• Compact enclosure with plain door and mounting plate • Compact enclosure with plain door and without mounting plate • Compact enclosure with transparent Securit® glass door and without mounting plate
Protection of personnel	Earthing accessories needed to help ensure the grounding continuity, page 540
Material	Low carbon emission steel
Finish	Structured finish, epoxy polyester powder
Color	RAL 7035 gray
Ingress protection rating	IP55 according to IEC 60529
Mechanical protection rating	• IK10 for plain door • IK08 for transparent door according to IEC 62262
Standards	Compliance with enclosure standard IEC 62208 and RoHS and REACH directive
Certifications	• BV Marine • UL (cULus), Rating according UL50E: - single-door enclosures: Types 1, 2, 3R, 5, 12 and 13 - double-door enclosures: Types 1, 3R, 12 and 13
Installation	**Indoor** * Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to UV radiation) and §9.13 (resistance to corrosion) Canopy needed to avoid water stagnation on the upper part of the enclosure, page 458
Maximum load	500 kg
Options	• Plinths, heights 100 mm and 200 mm, page 469 • Lifting eyebolts, page 482 • Internal door, page 552 • Door accessories, page 553 • Other locking options, page 561 • Mounting plates and Telequick system, page 514

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Steel Floor-Standing Enclosures

Panel**SeT** SM: Compact Enclosures

Selection Table

Dimensions (mm)				Enclosures			Plinth (H 100 mm)	
								
Height	Width	Depth	Doors	Plain door, without mounting plate	Plain door, with mounting plate	Transparent door, without mounting plate	Front kit (corners + front panels)	Side panels, 2 units
1200	800	300	1	NSYSM12830	NSYSM12830P	-	NSYSPF8100	NSYSPS3100
1200	1000	300	2	NSYSM1210302D	NSYSM1210302DP	-	NSYSPF10100	NSYSPS3100
1200	1200	400	2	NSYSM1212402D	NSYSM1212402DP	-	NSYSPF12100	NSYSPS4100
1400	600	300	1	NSYSM14630	NSYSM14630P	-	NSYSPF6100	NSYSPS3100
1400	600	400	1	NSYSM14640	NSYSM14640P	-	NSYSPF6100	NSYSPS4100
1400	800	300	1	NSYSM14830	NSYSM14830P	-	NSYSPF8100	NSYSPS3100
1400	800	400	1	NSYSM14840	NSYSM14840P	NSYSM14840T	NSYSPF8100	NSYSPS4100
1400	1000	400	2	NSYSM1410402D	NSYSM1410402DP	-	NSYSPF10100	NSYSPS4100
1400	1200	400	2	NSYSM1412402D	NSYSM1412402DP	-	NSYSPF12100	NSYSPS4100
1600	600	300	1	NSYSM16630	NSYSM16630P	-	NSYSPF6100	NSYSPS3100
1600	600	400	1	NSYSM16640	NSYSM16640P	NSYSM16640T	NSYSPF6100	NSYSPS4100
1600	800	300	1	NSYSM16830	NSYSM16830P	-	NSYSPF8100	NSYSPS3100
1600	800	400	1	NSYSM16840	NSYSM16840P	NSYSM16840T	NSYSPF8100	NSYSPS4100
1600	1000	300	2	NSYSM1610302D	NSYSM1610302DP	-	NSYSPF10100	NSYSPS3100
1600	1000	400	2	NSYSM1610402D	NSYSM1610402DP	-	NSYSPF10100	NSYSPS4100
1600	1200	300	2	NSYSM1612302D	NSYSM1612302DP	-	NSYSPF12100	NSYSPS3100
1600	1200	400	2	NSYSM1612402D	NSYSM1612402DP	-	NSYSPF12100	NSYSPS4100
1800	600	300	1	NSYSM18630	NSYSM18630P	-	NSYSPF6100	NSYSPS3100
1800	600	400	1	NSYSM18640	NSYSM18640P	NSYSM18640T	NSYSPF6100	NSYSPS4100
1800	600	500	1	NSYSM18650	NSYSM18650P	-	NSYSPF6100	NSYSPS5100
1800	800	300	1	NSYSM18830	NSYSM18830P	NSYSM18830T	NSYSPF8100	NSYSPS3100
1800	800	400	1	NSYSM18840	NSYSM18840P	NSYSM18840T	NSYSPF8100	NSYSPS4100
1800	800	500	1	NSYSM18850	NSYSM18850P	NSYSM18850T	NSYSPF8100	NSYSPS5100
1800	800	600	1	NSYSM18860	NSYSM18860P	-	NSYSPF8100	NSYSPS6100
1800	1000	400	1	NSYSM181040	NSYSM181040P	-	NSYSPF10100	NSYSPS4100
1800	1000	400	2	NSYSM1810402D	NSYSM1810402DP	-	NSYSPF10100	NSYSPS4100
1800	1000	500	2	NSYSM1810502D	NSYSM1810502DP	-	NSYSPF10100	NSYSPS5100
1800	1200	400	2	NSYSM1812402D	NSYSM1812402DP	-	NSYSPF12100	NSYSPS4100
1800	1200	500	2	NSYSM1812502D	NSYSM1812502DP	-	NSYSPF12100	NSYSPS5100
1800	1600	400	2	NSYSM1816402D	NSYSM1816402DP	-	NSYSPF16100	NSYSPS4100
1800	1600	500	2	NSYSM1816502D	NSYSM1816502DP	-	NSYSPF16100	NSYSPS5100
2000	600	300	1	NSYSM20630	NSYSM20630P	-	NSYSPF6100	NSYSPS3100
2000	600	400	1	NSYSM20640	NSYSM20640P	NSYSM20640T	NSYSPF6100	NSYSPS4100
2000	600	500	1	NSYSM20650	NSYSM20650P	-	NSYSPF6100	NSYSPS5100
2000	800	300	1	NSYSM20830	NSYSM20830P	NSYSM20830T	NSYSPF8100	NSYSPS3100
2000	800	400	1	NSYSM20840	NSYSM20840P	NSYSM20840T	NSYSPF8100	NSYSPS4100
2000	800	500	1	NSYSM20850	NSYSM20850P	NSYSM20850T	NSYSPF8100	NSYSPS5100
2000	800	600	1	NSYSM20860	NSYSM20860P	NSYSM20860T	NSYSPF8100	NSYSPS6100
2000	1000	400	2	NSYSM2010402D	NSYSM2010402DP	-	NSYSPF10100	NSYSPS4100
2000	1000	500	2	NSYSM2010502D	NSYSM2010502DP	-	NSYSPF10100	NSYSPS5100
2000	1200	400	2	NSYSM2012402D	NSYSM2012402DP	-	NSYSPF12100	NSYSPS4100
2000	1200	500	2	NSYSM2012502D	NSYSM2012502DP	-	NSYSPF12100	NSYSPS5100
2000	1200	600	2	NSYSM2012602D	NSYSM2012602DP	-	NSYSPF12100	NSYSPS6100
2000	1600	400	2	NSYSM2016402D	NSYSM2016402DP	-	NSYSPF16100	NSYSPS4100
2000	1600	500	2	NSYSM2016502D	NSYSM2016502DP	-	NSYSPF16100	NSYSPS5100
2000	1600	600	2	NSYSM2016602D	NSYSM2016602DP	-	NSYSPF16100	NSYSPS6100


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

	Plinth (H 200 mm)		Internal door	Mounting plate	Vertical uprights		Dimensions (mm)		
	 PB500125-18  PB500126-13		 PB504102	 PB504101	 PB500482-10	 PB500483-13			
	Front kit (corners + front panels)	Side panels, 4 units	Plain door	Galvanized	Standard	Technical	Height	Width	Depth
	NSYSPF8200	NSYSPS3200	-	NSYMP128	-	NSYTVR12	1200	800	300
	NSYSPF10200	NSYSPS3200	-	NSYMP1210	-	NSYTVR12	1200	1000	300
	NSYSPF12200	NSYSPS4200	-	NSYMP1212	-	NSYTVR12	1200	1200	400
	NSYSPF6200	NSYSPS3200	-	NSYMP146	-	NSYTVR14	1400	600	300
	NSYSPF6200	NSYSPS4200	-	NSYMP146	-	NSYTVR14	1400	600	400
	NSYSPF8200	NSYSPS3200	-	NSYMP148	-	NSYTVR14	1400	800	300
	NSYSPF8200	NSYSPS4200	-	NSYMP148	-	NSYTVR14	1400	800	400
	NSYSPF10200	NSYSPS4200	-	NSYMP1410	-	NSYTVR14	1400	1000	400
	NSYSPF12200	NSYSPS4200	-	NSYMP1412	-	NSYTVR14	1400	1200	400
	NSYSPF6200	NSYSPS3200	NSYID166	NSYMP166	-	NSYTVR16	1600	600	300
	NSYSPF6200	NSYSPS4200	NSYID166	NSYMP166	-	NSYTVR16	1600	600	400
	NSYSPF8200	NSYSPS3200	NSYID168	NSYMP168	-	NSYTVR16	1600	800	300
	NSYSPF8200	NSYSPS4200	NSYID168	NSYMP168	-	NSYTVR16	1600	800	400
	NSYSPF10200	NSYSPS3200	-	NSYMP1610	-	NSYTVR16	1600	1000	300
	NSYSPF10200	NSYSPS4200	-	NSYMP1610	-	NSYTVR16	1600	1000	400
	NSYSPF12200	NSYSPS3200	-	NSYMP1612	-	NSYTVR16	1600	1200	300
	NSYSPF12200	NSYSPS4200	-	NSYMP1612	-	NSYTVR16	1600	1200	400
	NSYSPF6200	NSYSPS3200	NSYID186	NSYMP186	NSYVR18	NSYTVR18	1800	600	300
	NSYSPF6200	NSYSPS4200	NSYID186	NSYMP186	NSYVR18	NSYTVR18	1800	600	400
	NSYSPF6200	NSYSPS5200	NSYID186	NSYMP186	NSYVR18	NSYTVR18	1800	600	500
	NSYSPF8200	NSYSPS3200	NSYID188	NSYMP188	NSYVR18	NSYTVR18	1800	800	300
	NSYSPF8200	NSYSPS4200	NSYID188	NSYMP188	NSYVR18	NSYTVR18	1800	800	400
	NSYSPF8200	NSYSPS5200	NSYID188	NSYMP188	NSYVR18	NSYTVR18	1800	800	500
	NSYSPF8200	NSYSPS6200	NSYID188	NSYMP188	NSYVR18	NSYTVR18	1800	800	600
	NSYSPF10200	NSYSPS4200	NSYID1810	NSYMP1810	NSYVR18	NSYTVR18	1800	1000	400
	NSYSPF10200	NSYSPS4200	NSYID1810	NSYMP1810	NSYVR18	NSYTVR18	1800	1000	400
	NSYSPF10200	NSYSPS5200	NSYID1810	NSYMP1810	NSYVR18	NSYTVR18	1800	1000	500
	NSYSPF12200	NSYSPS4200	-	NSYMP1812	NSYVR18	NSYTVR18	1800	1200	400
	NSYSPF12200	NSYSPS5200	-	NSYMP1812	NSYVR18	NSYTVR18	1800	1200	500
	NSYSPF16200	NSYSPS4200	-	NSYMP1816	NSYVR18	NSYTVR18	1800	1600	400
	NSYSPF16200	NSYSPS5200	-	NSYMP1816	NSYVR18	NSYTVR18	1800	1600	500
	NSYSPF6200	NSYSPS3200	NSYID206	NSYMP206	NSYVR20	NSYTVR20	2000	600	300
	NSYSPF6200	NSYSPS4200	NSYID206	NSYMP206	NSYVR20	NSYTVR20	2000	600	400
	NSYSPF6200	NSYSPS5200	NSYID206	NSYMP206	NSYVR20	NSYTVR20	2000	600	500
	NSYSPF8200	NSYSPS3200	NSYID208	NSYMP208	NSYVR20	NSYTVR20	2000	800	300
	NSYSPF8200	NSYSPS4200	NSYID208	NSYMP208	NSYVR20	NSYTVR20	2000	800	400
	NSYSPF8200	NSYSPS5200	NSYID208	NSYMP208	NSYVR20	NSYTVR20	2000	800	500
	NSYSPF8200	NSYSPS6200	NSYID208	NSYMP208	NSYVR20	NSYTVR20	2000	800	600
	NSYSPF10200	NSYSPS4200	NSYID2010	NSYMP2010	NSYVR20	NSYTVR20	2000	1000	400
	NSYSPF10200	NSYSPS5200	NSYID2010	NSYMP2010	NSYVR20	NSYTVR20	2000	1000	500
	NSYSPF12200	NSYSPS4200	-	NSYMP2012	NSYVR20	NSYTVR20	2000	1200	400
	NSYSPF12200	NSYSPS5200	-	NSYMP2012	NSYVR20	NSYTVR20	2000	1200	500
	NSYSPF12200	NSYSPS6200	-	NSYMP2012	NSYVR20	NSYTVR20	2000	1200	600
	NSYSPF16200	NSYSPS4200	-	NSYMP2016	NSYVR20	NSYTVR20	2000	1600	400
	NSYSPF16200	NSYSPS5200	-	NSYMP2016	NSYVR20	NSYTVR20	2000	1600	500
	NSYSPF16200	NSYSPS6200	-	NSYMP2016	NSYVR20	NSYTVR20	2000	1600	600

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SM: Compact Enclosures

Accessories



Installation Accessories

Composition Accessories

1



Canopy

See details p. 458

2



Coupling kits and accessories

See details p. 464

3



Floor fixing plinths and accessories

See details p. 469

Fixing and Lifting Accessories

4



Lifting systems: eyebolts, brackets and bars

See details p. 482

5



Wall fixing support


See details p. 479

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Management Accessories

Cable Entry Accessories

6



Gland plates: plain, 1 entry, 2 entries

See details p. 500

7



Cables entry gaskets and sealing gaskets

See details p. 503

Mounting Accessories

Equipment Assembly Accessories

8



Mounting plate

See details p. 514

9



Support tray

See details p. 539

10



Vertical uprights

See details p. 530

11



Earthing

See details p. 540

Door Accessories

12



Internal door

See details p. 552

13



Intermediate crossbar

See details p. 553

14



Hinges

See details p. 555

15



Inserts, keys, locks and handles

See details p. 561


16



Door-centering caster

See details p. 569

17



Door switch

See details p. 570

18



Document pocket

See details p. 570


> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SM: Compact Enclosures


Dimensions

SM



Models with a Width of 1200 mm
without Top/Bottom Adjustment Rails

Internal Door



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures

Introduction



This steel floor-standing enclosure is made of low-carbon emission steel, capable of withstanding 1500 kg distributed across its volume. It is able to offer this capacity thanks to its unique framework design, based on the use of a highly rigid exclusive profile.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

This range can be configured according to your needs
4 different services available:

- Assemble to order
- Mounting of standard accessories
- Machining
- Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN Modular Floor-Standing Low-Carbon Steel Enclosures




PanelSeT SFN
The first low-carbon emission steel enclosure

Reduced carbon footprint: manufactured with a minimum of 50% of steel produced from renewable energy and recycled materials (1), leading to a 34% $C0_2$ reduction on the total enclosure lifecycle (2)



Robust
Patented frame and fixation corner system in a bolted structure. Uprights fixed by 8 screws, one at each corner of the enclosure.

Capable of withstanding a static load of up to 1500 kg throughout its volume.



Efficient
- Quick system for the mounting plate allowing faster assembly
- Most accessories to be installed using the same self-tapping Torx T30 screws



- Second door handle for easy and ergonomic open-close operation




- Quick door removal and installation to facilitate assembly



- Panels include self-centering piece and captive screws for easier assembly and dismantling



Modular
The design allows enclosures to be coupled in any direction and layout, adapting to all installation surfaces




Aesthetics
- Streamlined extended roof and panels giving a new smoother appearance with less fixation points




- Ergonomic and convenient main handle, which features a label that can be used for customizing a signature or identification tag



Flexible Mounting
Delivered assembled, with or without mounting plate, with plain or glazed door, as a kit or customized to adapt to all spaces and needs



Compatible
Fully couplable with the previous PanelSeT SF version and compatible with its accessories




Accessible
The symmetric design of the profile allows doors to be installed on any side of the enclosure, opening right or left and providing full accessibility to the enclosure

(1) More info on Arcelor Mittal website (XCarb® recycled and renewably produced).
(2) According to the comparison of PanelSeT SFN PEP (ENVPEP2301018) and Spacial SF PEP (ENVPEP110923) using the same calculation methodology provided in the Product Category Rules of PEP Ecopassport association (PCRed4).

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures

Characteristics


Characteristics	Suitable enclosures PanelSeT SFN - supplied assembled	Suitable enclosures PanelSeT SFN - supplied as a kit
	 SFN	 SFN kit
	• Structure made up of vertical uprights joined with top and bottom frames • Panels and doors built into the structure • Formed from a single section and perforated structure with a pitch of 25 mm	• Separate door, panels, frames and vertical uprights
Basic composition	• Front door with a reinforcement frame (horizontal rails height-adjustable)and bottom trim • The double doors are overlapping, with a central handle on the left door • Door reversible, 120° opening • Extended rear panel screwed on with captive screws • Removable extended roof • System with 4 locking points with handle and 5-mm double-bar insert • Mounting plate support brackets (for widths from 600 mm) and quick-fixation system • Mounting plate sliding rails (for widths from 600 mm)	• Front door with a reinforcement frame (horizontal rails height-adjustable) and bottom trim • The double doors are overlapping, with a central handle on the left door • Door reversible, 120° opening • Extended rear panel to be screwed on with captive screws • Removable extended roof delivered with top and bottom frame • System with 4 locking points with handle and 5-mm double-bar insert • Mounting plate support brackets delivered with top and bottom frame kit (for widths from 600 mm) and quick-fixation system • Mounting plate sliding rails delivered with top and bottom frame kit (for widths from 600 mm)
Versions / Configurations	• Modular enclosure with plain door and mounting plate • Modular enclosure with plain door and without mounting plate • Modular enclosure with transparent Securit® glass door and without mounting plate	• Uprights kit • Top and bottom frame kit • Rear panel kit • Door kit (plain or transparent)
Protection of personnel	Earthing accessories needed for grounding continuity	
Material	Low carbon emission steel	
Finish	Structured finish, epoxy polyester powder	
Color	RAL 7035 gray	
Ingress protection rating	IP55 according to IEC 60529 (with side panels and plain cable gland plate with gasket)	
Mechanical protection rating	• IK10 for plain door • IK08 for transparent door according to IEC 62262	
Standards	Compliance with enclosure standard IEC 62208 and RoHS and REACH directive	
Certifications	BV, DNV, UL (cULus) Rating according to UL50E: Types 1, 3R, 12	
Installation	**Indoor** * Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to UV radiation) and §9.13 (resistance to corrosion) Canopy needed to avoid water stagnation on the upper part of the enclosure, page 458	
Maximum static load	1500 kg	
Options	• Side panels options, page 461 • Enclosure suites options, page 464 • Plinths, heights 100 mm and 200 mm, page 469 • Cable gland plates, page 498 • Lifting systems, page 482 • Roof options, page 458 • Door accessories, page 553 • Other locking options, page 561 • Mounting plates and Telequick system, page 514	• Side panels options, page 461 • Enclosure suites options, page 464 • Plinths, heights 100 mm and 200 mm, page 469 • Cable gland plates, page 498 • Lifting systems, page 482 • Roof options, page 458 • Other locking options, page 561 • Mounting plates and Telequick system, page 514

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures





Selection Table

Dimensions (mm)				Enclosures			Side panels	Cable entry plates		
										
(A) Height	(B) Width	(C) Depth	Doors	Plain door, without mounting plate	Plain door, with mounting plate	Transparent door, without mounting plate	Plain	Plain	1 entry	2 entries
1200	600	400	1	NSYSFN12640	NSYSFN12640P	-	NSY2SPN124	NSYEC64	NSYEC641	-
1200	600	600	1	NSYSFN12660	NSYSFN12660P	-	NSY2SPN126	NSYEC66	NSYEC661	NSYEC662
1200	800	400	1	NSYSFN12840	NSYSFN12840P	-	NSY2SPN124	NSYEC84	NSYEC841	-
1200	800	600	1	NSYSFN12860	NSYSFN12860P	-	NSY2SPN126	NSYEC86	NSYEC861	NSYEC862
1400	600	400	1	NSYSFN14640	NSYSFN14640P	-	NSY2SPN144	NSYEC64	NSYEC641	-
1400	800	400	1	NSYSFN14840	NSYSFN14840P	-	NSY2SPN144	NSYEC84	NSYEC841	-
1600	600	600	1	NSYSFN16660	NSYSFN16660P	-	NSY2SPN166	NSYEC66	NSYEC661	NSYEC662
1600	600	800	1	NSYSFN16680	NSYSFN16680P	-	NSY2SPN168	NSYEC68	NSYEC681	NSYEC682
1600	800	600	1	NSYSFN16860	NSYSFN16860P	-	NSY2SPN166	NSYEC86	NSYEC861	NSYEC862
1600	800	800	1	NSYSFN16880	NSYSFN16880P	-	NSY2SPN168	NSYEC88	NSYEC881	NSYEC882
1800	400	400	1	NSYSFN18440	-	-	NSY2SPN184	NSYEC44	NSYEC441	-
1800	400	500	1	NSYSFN18450	-	-	NSY2SPN185	NSYEC45	NSYEC451	-
1800	400	600	1	NSYSFN18460	-	-	NSY2SPN186	NSYEC64	NSYEC461	NSYEC462
1800	600	400	1	NSYSFN18640	NSYSFN18640P	NSYSFN18640T	NSY2SPN184	NSYEC64	NSYEC641	-
1800	600	500	1	NSYSFN18650	NSYSFN18650P	NSYSFN18650T	NSY2SPN185	NSYEC65	NSYEC651	-
1800	600	600	1	NSYSFN18660	NSYSFN18660P	-	NSY2SPN186	NSYEC66	NSYEC661	NSYEC662
1800	600	800	1	-	-	NSYSFN18680T	NSY2SPN188	NSYEC68	NSYEC681	NSYEC682
1800	800	400	1	NSYSFN18840	NSYSFN18840P	NSYSFN18840T	NSY2SPN184	NSYEC84	NSYEC841	-
1800	800	500	1	NSYSFN18850	NSYSFN18850P	NSYSFN18850T	NSY2SPN185	NSYEC85	NSYEC851	-
1800	800	600	1	NSYSFN18860	NSYSFN18860P	NSYSFN18860T	NSY2SPN186	NSYEC86	NSYEC861	NSYEC862
1800	800	600	2	NSYSFN188602D	NSYSFN188602DP	-	NSY2SPN186	NSYEC86	NSYEC861	NSYEC862
1800	1000	400	1	NSYSFN181040	NSYSFN181040P	-	NSY2SPN184	NSYEC104	NSYEC1041	-
1800	1000	400	2	NSYSFN1810402D	NSYSFN1810402DP	-	NSY2SPN184	NSYEC104	NSYEC1041	-
1800	1000	500	1	NSYSFN181050	NSYSFN181050P	-	NSY2SPN185	NSYEC105	NSYEC1051	-
1800	1000	600	1	NSYSFN181060	NSYSFN181060P	-	NSY2SPN186	NSYEC106	NSYEC1061	NSYEC1062
1800	1000	600	2	NSYSFN1810602D	NSYSFN1810602DP	-	NSY2SPN186	NSYEC106	NSYEC1061	NSYEC1062
1800	1200	400	2	NSYSFN1812402D	NSYSFN1812402DP	-	NSY2SPN184	NSYEC124	NSYEC1241	-
1800	1200	500	2	NSYSFN1812502D	NSYSFN1812502DP	-	NSY2SPN185	NSYEC125	NSYEC1251	-
1800	1200	600	2	NSYSFN1812602D	NSYSFN1812602DP	-	NSY2SPN186	NSYEC126	NSYEC1261	NSYEC1262
1800	1600	400	2	NSYSFN1816402D	-	-	NSY2SPN184	NSYEC164	NSYEC1641	-
2000	300	500	1	NSYSFN20350	-	-	NSY2SPN205	NSYEC35	NSYEC351	-
2000	300	600	1	NSYSFN20360	-	-	NSY2SPN206	NSYEC36	NSYEC361	-
2000	300	800	1	NSYSFN20380	-	-	NSY2SPN208	-	NSYEC381	-
2000	400	400	1	NSYSFN20440	-	-	NSY2SPN204	NSYEC44	NSYEC441	-
2000	400	500	1	NSYSFN20450	-	-	NSY2SPN205	NSYEC45	NSYEC451	-
2000	400	600	1	NSYSFN20460	-	-	NSY2SPN206	NSYEC64	NSYEC461	NSYEC462
2000	400	800	1	NSYSFN20480	-	-	NSY2SPN208	NSYEC84	NSYEC481	NSYEC482
2000	600	400	1	NSYSFN20640	NSYSFN20640P	NSYSFN20640T	NSY2SPN204	NSYEC64	NSYEC641	-
2000	600	500	1	NSYSFN20650	NSYSFN20650P	NSYSFN20650T	NSY2SPN205	NSYEC65	NSYEC651	-
2000	600	600	1	NSYSFN20660	NSYSFN20660P	-	NSY2SPN206	NSYEC66	NSYEC661	NSYEC662
2000	600	800	1	NSYSFN20680	NSYSFN20680P	-	NSY2SPN208	NSYEC68	NSYEC681	NSYEC682
2000	800	400	1	NSYSFN20840	NSYSFN20840P	NSYSFN20840T	NSY2SPN204	NSYEC84	NSYEC841	-
2000	800	500	1	NSYSFN20850	NSYSFN20850P	NSYSFN20850T	NSY2SPN205	NSYEC85	NSYEC851	-
2000	800	600	1	NSYSFN20860	NSYSFN20860P	NSYSFN20860T	NSY2SPN206	NSYEC86	NSYEC861	NSYEC862
2000	800	600	2	NSYSFN208602D	NSYSFN208602DP	-	NSY2SPN206	NSYEC86	NSYEC861	NSYEC862
2000	800	800	1	NSYSFN20880	NSYSFN20880P	NSYSFN20880T	NSY2SPN208	NSYEC88	NSYEC881	NSYEC882
2000	1000	400	1	NSYSFN201040	NSYSFN201040P	NSYSFN201040T	NSY2SPN204	NSYEC104	NSYEC1041	-
2000	1000	400	2	NSYSFN2010402D	NSYSFN2010402DP	-	NSY2SPN204	NSYEC104	NSYEC1041	-
2000	1000	500	1	NSYSFN201050	NSYSFN201050P	NSYSFN201050T	NSY2SPN205	NSYEC105	NSYEC1051	-
2000	1000	500	2	NSYSFN2010502D	NSYSFN2010502DP	-	NSY2SPN205	NSYEC105	NSYEC1051	-
2000	1000	600	1	NSYSFN201060	NSYSFN201060P	NSYSFN201060T	NSY2SPN206	NSYEC106	NSYEC1061	NSYEC1062
2000	1000	600	2	NSYSFN2010602D	NSYSFN2010602DP	-	NSY2SPN206	NSYEC106	NSYEC1061	NSYEC1062
2000	1000	800	1	NSYSFN201080	NSYSFN201080P	-	NSY2SPN208	NSYEC108	NSYEC1081	NSYEC1082
2000	1200	400	2	NSYSFN2012402D	NSYSFN2012402DP	-	NSY2SPN204	NSYEC124	NSYEC1241	-
2000	1200	500	2	NSYSFN2012502D	NSYSFN2012502DP	-	NSY2SPN205	NSYEC125	NSYEC1251	-
2000	1200	600	2	NSYSFN2012602D	NSYSFN2012602DP	-	NSY2SPN206	NSYEC126	NSYEC1261	NSYEC1262
2000	1200	800	2	NSYSFN2012802D	NSYSFN2012802DP	-	NSY2SPN208	NSYEC128	NSYEC1281	NSYEC1282
2000	1600	400	2	NSYSFN2016402D	NSYSFN2016402DP	-	NSY2SPN204	NSYEC164	NSYEC1641	-
2000	1600	500	2	NSYSFN2016502D	NSYSFN2016502DP	-	NSY2SPN205	NSYEC165	NSYEC1651	-
2000	1600	600	2	NSYSFN2016602D	NSYSFN2016602DP	-	NSY2SPN206	NSYEC166	NSYEC1661	NSYEC1662
2200	400	600	1	NSYSFN22460	-	-	NSY2SPN226	NSYEC64	NSYEC461	-
2200	600	600	1	NSYSFN22660	NSYSFN22660P	-	NSY2SPN226	NSYEC66	NSYEC661	NSYEC662
2200	600	800	1	NSYSFN22680	NSYSFN22680P	-	NSY2SPN228	NSYEC68	NSYEC681	NSYEC682
2200	800	600	1	NSYSFN22860	NSYSFN22860P	-	NSY2SPN226	NSYEC86	NSYEC861	NSYEC862
2200	800	800	1	NSYSFN22880	NSYSFN22880P	NSYSFN22880T	NSY2SPN228	NSYEC88	NSYEC881	NSYEC882
2200	1000	600	1	NSYSFN221060	NSYSFN221060P	-	NSY2SPN226	NSYEC106	NSYEC1061	NSYEC1062
2200	1200	600	2	NSYSFN2212602D	NSYSFN2212602DP	-	NSY2SPN226	NSYEC126	NSYEC1261	NSYEC1262
2200	1200	800	2	NSYSFN2212802D	NSYSFN2212802DP	-	NSY2SPN228	NSYEC128	NSYEC1281	NSYEC1282

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures


Selection Table

Plinths (H 100 mm)		Plinths (H 200 mm)		Mounting plates		Vertical uprights		Dimensions (mm)		
										
Front kit (corners + front panels)	Side panels, 2 units	Front kit (corners + front panels)	Side panels, 4 units	Mounting plate	Intermediate mounting plate	Standard	Technical	(A) Height	(B) Width	(C) Depth
NSYSPF6100	NSYSPS4100	NSYSPF6200	NSYSPS4200	NSYMP126	NSYSIMP12	-	NSYTVR12	1200	600	400
NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYMP126	NSYSIMP12	-	NSYTVR12	1200	600	600
NSYSPF8100	NSYSPS4100	NSYSPF8200	NSYSPS4200	NSYMP128	NSYSIMP12	-	NSYTVR12	1200	800	400
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP128	NSYSIMP12	-	NSYTVR12	1200	800	600
NSYSPF6100	NSYSPS4100	NSYSPF6200	NSYSPS4200	NSYMP146	NSYSIMP14	-	NSYTVR14	1400	600	400
NSYSPF8100	NSYSPS4100	NSYSPF8200	NSYSPS4200	NSYMP148	NSYSIMP14	-	NSYTVR14	1400	800	400
NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYMP166	NSYSIMP16	-	NSYTVR16	1600	600	600
NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYMP166	NSYSIMP16	-	NSYTVR16	1600	600	800
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP168	NSYSIMP16	-	NSYTVR16	1600	800	600
NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYMP168	NSYSIMP16	-	NSYTVR16	1600	800	800
NSYSPF4100	NSYSPS4100	NSYSPF4200	NSYSPS4200	NSYMP184	NSYSIMP18	NSYVR18	NSYTVR18	1800	400	400
NSYSPF4100	NSYSPS5100	NSYSPF4200	NSYSPS5200	NSYMP184	NSYSIMP18	NSYVR18	NSYTVR18	1800	400	500
NSYSPF4100	NSYSPS6100	NSYSPF4200	NSYSPS6200	NSYMP184	NSYSIMP18	NSYVR18	NSYTVR18	1800	400	600
NSYSPF6100	NSYSPS4100	NSYSPF6200	NSYSPS4200	NSYMP186	NSYSIMP18	NSYVR18	NSYTVR18	1800	600	400
NSYSPF6100	NSYSPS5100	NSYSPF6200	NSYSPS5200	NSYMP186	NSYSIMP18	NSYVR18	NSYTVR18	1800	600	500
NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYMP186	NSYSIMP18	NSYVR18	NSYTVR18	1800	600	600
NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYMP186	NSYSIMP18	NSYVR18	NSYTVR18	1800	600	800
NSYSPF8100	NSYSPS4100	NSYSPF8200	NSYSPS4200	NSYMP188	NSYSIMP18	NSYVR18	NSYTVR18	1800	800	400
NSYSPF8100	NSYSPS5100	NSYSPF8200	NSYSPS5200	NSYMP188	NSYSIMP18	NSYVR18	NSYTVR18	1800	800	500
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP188	NSYSIMP18	NSYVR18	NSYTVR18	1800	800	600
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP188	NSYSIMP18	NSYVR18	NSYTVR18	1800	800	600
NSYSPF10100	NSYSPS4100	NSYSPF10200	NSYSPS4200	NSYMP1810	NSYSIMP18	NSYVR18	NSYTVR18	1800	1000	400
NSYSPF10100	NSYSPS4100	NSYSPF10200	NSYSPS4200	NSYMP1810	NSYSIMP18	NSYVR18	NSYTVR18	1800	1000	400
NSYSPF10100	NSYSPS5100	NSYSPF10200	NSYSPS5200	NSYMP1810	NSYSIMP18	NSYVR18	NSYTVR18	1800	1000	500
NSYSPF10100	NSYSPS6100	NSYSPF10200	NSYSPS6200	NSYMP1810	NSYSIMP18	NSYVR18	NSYTVR18	1800	1000	600
NSYSPF10100	NSYSPS6100	NSYSPF10200	NSYSPS6200	NSYMP1810	NSYSIMP18	NSYVR18	NSYTVR18	1800	1000	600
NSYSPF12100	NSYSPS4100	NSYSPF12200	NSYSPS4200	NSYMP1812	NSYSIMP18	NSYVR18	NSYTVR18	1800	1200	400
NSYSPF12100	NSYSPS5100	NSYSPF12200	NSYSPS5200	NSYMP1812	NSYSIMP18	NSYVR18	NSYTVR18	1800	1200	500
NSYSPF12100	NSYSPS6100	NSYSPF12200	NSYSPS6200	NSYMP1812	NSYSIMP18	NSYVR18	NSYTVR18	1800	1200	600
NSYSPF16100	NSYSPS4100	NSYSPF16200	NSYSPS4200	NSYMP1816	NSYSIMP18	NSYVR18	NSYTVR18	1800	1600	400
NSYSPF3100	NSYSPS5100	NSYSPF3200	NSYSPS5200	-	-	NSYVR20	NSYTVR20	2000	300	500
NSYSPF3100	NSYSPS6100	NSYSPF3200	NSYSPS6200	-	-	NSYVR20	NSYTVR20	2000	300	600
NSYSPF3100	NSYSPS8100	NSYSPF3200	NSYSPS8200	-	-	NSYVR20	NSYTVR20	2000	300	800
NSYSPF4100	NSYSPS4100	NSYSPF4200	NSYSPS4200	NSYMP204	NSYSIMP20	NSYVR20	NSYTVR20	2000	400	400
NSYSPF4100	NSYSPS5100	NSYSPF4200	NSYSPS5200	NSYMP204	NSYSIMP20	NSYVR20	NSYTVR20	2000	400	500
NSYSPF4100	NSYSPS6100	NSYSPF4200	NSYSPS6200	NSYMP204	NSYSIMP20	NSYVR20	NSYTVR20	2000	400	600
NSYSPF4100	NSYSPS8100	NSYSPF4200	NSYSPS8200	NSYMP204	NSYSIMP20	NSYVR20	NSYTVR20	2000	400	800
NSYSPF6100	NSYSPS4100	NSYSPF6200	NSYSPS4200	NSYMP206	NSYSIMP20	NSYVR20	NSYTVR20	2000	600	400
NSYSPF6100	NSYSPS5100	NSYSPF6200	NSYSPS5200	NSYMP206	NSYSIMP20	NSYVR20	NSYTVR20	2000	600	500
NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYMP206	NSYSIMP20	NSYVR20	NSYTVR20	2000	600	600
NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYMP206	NSYSIMP20	NSYVR20	NSYTVR20	2000	600	800
NSYSPF8100	NSYSPS4100	NSYSPF8200	NSYSPS4200	NSYMP208	NSYSIMP20	NSYVR20	NSYTVR20	2000	800	400
NSYSPF8100	NSYSPS5100	NSYSPF8200	NSYSPS5200	NSYMP208	NSYSIMP20	NSYVR20	NSYTVR20	2000	800	500
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP208	NSYSIMP20	NSYVR20	NSYTVR20	2000	800	600
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP208	NSYSIMP20	NSYVR20	NSYTVR20	2000	800	600
NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYMP208	NSYSIMP20	NSYVR20	NSYTVR20	2000	800	800
NSYSPF10100	NSYSPS4100	NSYSPF10200	NSYSPS4200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	400
NSYSPF10100	NSYSPS4100	NSYSPF10200	NSYSPS4200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	400
NSYSPF10100	NSYSPS5100	NSYSPF10200	NSYSPS5200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	500
NSYSPF10100	NSYSPS5100	NSYSPF10200	NSYSPS5200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	500
NSYSPF10100	NSYSPS6100	NSYSPF10200	NSYSPS6200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	600
NSYSPF10100	NSYSPS6100	NSYSPF10200	NSYSPS6200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	600
NSYSPF10100	NSYSPS8100	NSYSPF10200	NSYSPS8200	NSYMP2010	NSYSIMP20	NSYVR20	NSYTVR20	2000	1000	800
NSYSPF12100	NSYSPS4100	NSYSPF12200	NSYSPS4200	NSYMP2012	NSYSIMP20	NSYVR20	NSYTVR20	2000	1200	400
NSYSPF12100	NSYSPS5100	NSYSPF12200	NSYSPS5200	NSYMP2012	NSYSIMP20	NSYVR20	NSYTVR20	2000	1200	500
NSYSPF12100	NSYSPS6100	NSYSPF12200	NSYSPS6200	NSYMP2012	NSYSIMP20	NSYVR20	NSYTVR20	2000	1200	600
NSYSPF12100	NSYSPS8100	NSYSPF12200	NSYSPS8200	NSYMP2012	NSYSIMP20	NSYVR20	NSYTVR20	2000	1200	800
NSYSPF16100	NSYSPS4100	NSYSPF16200	NSYSPS4200	NSYMP2016	NSYSIMP20	NSYVR20	NSYTVR20	2000	1600	400
NSYSPF16100	NSYSPS5100	NSYSPF16200	NSYSPS5200	NSYMP2016	NSYSIMP20	NSYVR20	NSYTVR20	2000	1600	500
NSYSPF16100	NSYSPS6100	NSYSPF16200	NSYSPS6200	NSYMP2016	NSYSIMP20	NSYVR20	NSYTVR20	2000	1600	600
NSYSPF4100	NSYSPS6100	NSYSPF4200	NSYSPS6200	NSYMP224	NSYSIMP22	NSYVR22	NSYTVR22	2200	400	600
NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYMP226	NSYSIMP22	NSYVR22	NSYTVR22	2200	600	600
NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYMP226	NSYSIMP22	NSYVR22	NSYTVR22	2200	600	800
NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYMP228	NSYSIMP22	NSYVR22	NSYTVR22	2200	800	600
NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYMP228	NSYSIMP22	NSYVR22	NSYTVR22	2200	800	800
NSYSPF10100	NSYSPS6100	NSYSPF10200	NSYSPS6200	NSYMP2210	NSYSIMP22	NSYVR22	NSYTVR22	2200	1000	600
NSYSPF12100	NSYSPS6100	NSYSPF12200	NSYSPS6200	NSYMP2212	NSYSIMP22	NSYVR22	NSYTVR22	2200	1200	600
NSYSPF12100	NSYSPS8100	NSYSPF12200	NSYSPS8200	NSYMP2212	NSYSIMP22	NSYVR22	NSYTVR22	2200	1200	800

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN Kit: Modular Enclosures

Selection Table

				Vertical uprights	Bottom frame and top frame with roof	Panels		Doors		Mounting plate
				 NSYSFNV12	 NSYSFNC64	 NSYBPN126	 NSY2SPN124	 NSY2SFND128 (Hinges, locking bar catches and handle with 5-mm double-bar insert included)	 NSY2SPN126T (Securit® glass, hinges, locking bar catches and handle with 5-mm double-bar insert included)	 PB500477-7
Dimensions (mm)										
(A) Height	(B) Width	(C) Depth	Doors	Standard	Frames	Rear panel	Side panel	Plain	Transparent	Standard
1200	600	400	1	NSYSFNV12	NSYSFNC64	NSYBPN126	NSY2SPN124	NSYSFND126	NSYSFND126T	NSYMP126
1200	600	500	1	NSYSFNV12	NSYSFNC65	NSYBPN126	NSY2SPN125	NSYSFND126	NSYSFND126T	NSYMP126
1200	600	600	1	NSYSFNV12	NSYSFNC66	NSYBPN126	NSY2SPN126	NSYSFND126	NSYSFND126T	NSYMP126
1200	600	800	1	NSYSFNV12	NSYSFNC68	NSYBPN126	NSY2SPN128	NSYSFND126	NSYSFND126T	NSYMP126
1200	800	400	1	NSYSFNV12	NSYSFNC84	NSYBPN128	NSY2SPN124	NSYSFND128	NSYSFND128T	NSYMP128
1200	800	500	1	NSYSFNV12	NSYSFNC85	NSYBPN128	NSY2SPN125	NSYSFND128	NSYSFND128T	NSYMP128
1200	800	600	1	NSYSFNV12	NSYSFNC86	NSYBPN128	NSY2SPN126	NSYSFND128	NSYSFND128T	NSYMP128
1200	800	800	1	NSYSFNV12	NSYSFNC88	NSYBPN128	NSY2SPN128	NSYSFND128	NSYSFND128T	NSYMP128
1400	600	400	1	NSYSFNV14	NSYSFNC64	NSYBPN146	NSY2SPN144	NSYSFND146	NSYSFND146T	NSYMP146
1400	600	500	1	NSYSFNV14	NSYSFNC65	NSYBPN146	NSY2SPN145	NSYSFND146	NSYSFND146T	NSYMP146
1400	600	600	1	NSYSFNV14	NSYSFNC66	NSYBPN146	NSY2SPN146	NSYSFND146	NSYSFND146T	NSYMP146
1400	600	800	1	NSYSFNV14	NSYSFNC68	NSYBPN146	NSY2SPN148	NSYSFND146	NSYSFND146T	NSYMP146
1400	800	400	1	NSYSFNV14	NSYSFNC84	NSYBPN148	NSY2SPN144	NSYSFND148	NSYSFND148T	NSYMP148
1400	800	500	1	NSYSFNV14	NSYSFNC85	NSYBPN148	NSY2SPN145	NSYSFND148	NSYSFND148T	NSYMP148
1400	800	600	1	NSYSFNV14	NSYSFNC86	NSYBPN148	NSY2SPN146	NSYSFND148	NSYSFND148T	NSYMP148
1400	800	800	1	NSYSFNV14	NSYSFNC88	NSYBPN148	NSY2SPN148	NSYSFND148	NSYSFND148T	NSYMP148
1600	600	400	1	NSYSFNV16	NSYSFNC64	NSYBPN166	NSY2SPN164	NSYSFND166	NSYSFND166T	NSYMP166
1600	600	500	1	NSYSFNV16	NSYSFNC65	NSYBPN166	NSY2SPN165	NSYSFND166	NSYSFND166T	NSYMP166
1600	600	600	1	NSYSFNV16	NSYSFNC66	NSYBPN166	NSY2SPN166	NSYSFND166	NSYSFND166T	NSYMP166
1600	600	800	1	NSYSFNV16	NSYSFNC68	NSYBPN166	NSY2SPN168	NSYSFND166	NSYSFND166T	NSYMP166
1600	800	400	1	NSYSFNV16	NSYSFNC84	NSYBPN168	NSY2SPN164	NSYSFND168	NSYSFND168T	NSYMP168
1600	800	500	1	NSYSFNV16	NSYSFNC85	NSYBPN168	NSY2SPN165	NSYSFND168	NSYSFND168T	NSYMP168
1600	800	600	1	NSYSFNV16	NSYSFNC86	NSYBPN168	NSY2SPN166	NSYSFND168	NSYSFND168T	NSYMP168
1600	800	800	1	NSYSFNV16	NSYSFNC88	NSYBPN168	NSY2SPN168	NSYSFND168	NSYSFND168T	NSYMP168
1800	400	400	1	NSYSFNV18	NSYSFNC44	NSYBPN184	NSY2SPN184	NSYSFND184	-	NSYMP184
1800	400	500	1	NSYSFNV18	NSYSFNC45	NSYBPN184	NSY2SPN185	NSYSFND184	-	NSYMP184
1800	400	600	1	NSYSFNV18	NSYSFNC46	NSYBPN184	NSY2SPN186	NSYSFND184	-	NSYMP184
1800	400	800	1	NSYSFNV18	NSYSFNC48	NSYBPN184	NSY2SPN188	NSYSFND184	-	NSYMP184
1800	600	400	1	NSYSFNV18	NSYSFNC64	NSYBPN186	NSY2SPN184	NSYSFND186	NSYSFND186T	NSYMP186
1800	600	500	1	NSYSFNV18	NSYSFNC65	NSYBPN186	NSY2SPN185	NSYSFND186	NSYSFND186T	NSYMP186
1800	600	600	1	NSYSFNV18	NSYSFNC66	NSYBPN186	NSY2SPN186	NSYSFND186	NSYSFND186T	NSYMP186
1800	600	800	1	NSYSFNV18	NSYSFNC68	NSYBPN186	NSY2SPN188	NSYSFND186	NSYSFND186T	NSYMP186
1800	800	400	1	NSYSFNV18	NSYSFNC84	NSYBPN188	NSY2SPN184	NSYSFND188	NSYSFND188T	NSYMP188
1800	800	500	1	NSYSFNV18	NSYSFNC85	NSYBPN188	NSY2SPN185	NSYSFND188	NSYSFND188T	NSYMP188
1800	800	600	1	NSYSFNV18	NSYSFNC86	NSYBPN188	NSY2SPN186	NSYSFND188	NSYSFND188T	NSYMP188
1800	800	600	2	NSYSFNV18	NSYSFNC86	NSYBPN188	NSY2SPN186	NSYSFND1882D	-	NSYMP188
1800	800	800	1	NSYSFNV18	NSYSFNC88	NSYBPN188	NSY2SPN188	NSYSFND188	NSYSFND188T	NSYMP188
1800	800	800	2	NSYSFNV18	NSYSFNC88	NSYBPN188	NSY2SPN188	NSYSFND1882D	-	NSYMP188
1800	1000	400	1	NSYSFNV18	NSYSFNC104	NSYBPN1810	NSY2SPN184	NSYSFND1810	NSYSFND1810T	NSYMP1810
1800	1000	400	2	NSYSFNV18	NSYSFNC104	NSYBPN1810	NSY2SPN184	NSYSFND18102D	-	NSYMP1810
1800	1000	500	1	NSYSFNV18	NSYSFNC105	NSYBPN1810	NSY2SPN185	NSYSFND1810	NSYSFND1810T	NSYMP1810
1800	1000	600	1	NSYSFNV18	NSYSFNC106	NSYBPN1810	NSY2SPN186	NSYSFND1810	NSYSFND1810T	NSYMP1810
1800	1000	600	2	NSYSFNV18	NSYSFNC106	NSYBPN1810	NSY2SPN186	NSYSFND18102D	-	NSYMP1810
1800	1000	800	1	NSYSFNV18	NSYSFNC108	NSYBPN1810	NSY2SPN188	NSYSFND1810	NSYSFND1810T	NSYMP1810
1800	1000	800	2	NSYSFNV18	NSYSFNC108	NSYBPN1810	NSY2SPN188	NSYSFND18102D	-	NSYMP1810
1800	1200	400	2	NSYSFNV18	NSYSFNC124	NSYBPN1812	NSY2SPN184	NSYSFND18122D	NSYSFND18122DT	NSYMP1812
1800	1200	500	2	NSYSFNV18	NSYSFNC125	NSYBPN1812	NSY2SPN185	NSYSFND18122D	NSYSFND18122DT	NSYMP1812
1800	1200	600	2	NSYSFNV18	NSYSFNC126	NSYBPN1812	NSY2SPN186	NSYSFND18122D	NSYSFND18122DT	NSYMP1812
1800	1200	800	2	NSYSFNV18	NSYSFNC128	NSYBPN1812	NSY2SPN188	NSYSFND18122D	NSYSFND18122DT	NSYMP1812

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN Kit: Modular Enclosures


Selection Table

Dimensions (mm)				Vertical uprights	Bottom frame and top frame with roof	Panels		Doors		Mounting plate
				 NSYSFNV20	 NSYSFNC36	 NSYBPN2010  NSYBPN224		 NSYSFND2010 (Hinges, locking bar catches and handle with 5-mm double-bar insert included.)	 NSYSFND2010T (Securit® glass, hinges, locking bar catches and handle with 5-mm double-bar insert included.)	 PBS00477-7
(A) Height	(B) Width	(C) Depth	Doors	Standard	Frames	Rear panel	Side panel	Plain	Transparent	Standard
2000	300	500	1	NSYSFNV20	NSYSFNC35	NSYBPN203	NSY2SPN205	NSYSFND203	-	-
2000	300	600	1	NSYSFNV20	NSYSFNC36	NSYBPN203	NSY2SPN206	NSYSFND203	-	-
2000	300	800	1	NSYSFNV20	NSYSFNC38	NSYBPN203	NSY2SPN208	NSYSFND203	-	-
2000	400	400	1	NSYSFNV20	NSYSFNC44	NSYBPN204	NSY2SPN204	NSYSFND204	-	NSYMP204
2000	400	500	1	NSYSFNV20	NSYSFNC45	NSYBPN204	NSY2SPN205	NSYSFND204	-	NSYMP204
2000	400	600	1	NSYSFNV20	NSYSFNC46	NSYBPN204	NSY2SPN206	NSYSFND204	-	NSYMP204
2000	400	800	1	NSYSFNV20	NSYSFNC48	NSYBPN204	NSY2SPN208	NSYSFND204	-	NSYMP204
2000	600	400	1	NSYSFNV20	NSYSFNC64	NSYBPN206	NSY2SPN204	NSYSFND206	NSYSFND206T	NSYMP206
2000	600	500	1	NSYSFNV20	NSYSFNC65	NSYBPN206	NSY2SPN205	NSYSFND206	NSYSFND206T	NSYMP206
2000	600	600	1	NSYSFNV20	NSYSFNC66	NSYBPN206	NSY2SPN206	NSYSFND206	NSYSFND206T	NSYMP206
2000	600	800	1	NSYSFNV20	NSYSFNC68	NSYBPN206	NSY2SPN208	NSYSFND206	NSYSFND206T	NSYMP206
2000	600	1000	1	NSYSFNV20	NSYSFNC610	NSYBPN206	NSY2SPN2010	NSYSFND206	NSYSFND206T	NSYMP206
2000	800	400	1	NSYSFNV20	NSYSFNC84	NSYBPN208	NSY2SPN204	NSYSFND208	NSYSFND208T	NSYMP208
2000	800	500	1	NSYSFNV20	NSYSFNC85	NSYBPN208	NSY2SPN205	NSYSFND208	NSYSFND208T	NSYMP208
2000	800	600	1	NSYSFNV20	NSYSFNC86	NSYBPN208	NSY2SPN206	NSYSFND208	NSYSFND208T	NSYMP208
2000	800	600	2	NSYSFNV20	NSYSFNC86	NSYBPN208	NSY2SPN206	NSYSFND2082D	-	NSYMP208
2000	800	800	1	NSYSFNV20	NSYSFNC88	NSYBPN208	NSY2SPN208	NSYSFND208	NSYSFND208T	NSYMP208
2000	800	800	2	NSYSFNV20	NSYSFNC88	NSYBPN208	NSY2SPN208	NSYSFND2082D	-	NSYMP208
2000	800	1000	1	NSYSFNV20	NSYSFNC810	NSYBPN208	NSY2SPN2010	NSYSFND208	NSYSFND208T	NSYMP208
2000	800	1000	2	NSYSFNV20	NSYSFNC810	NSYBPN208	NSY2SPN2010	NSYSFND2082D	-	NSYMP208
2000	1000	400	1	NSYSFNV20	NSYSFNC104	NSYBPN2010	NSY2SPN204	NSYSFND2010	NSYSFND2010T	NSYMP2010
2000	1000	400	2	NSYSFNV20	NSYSFNC104	NSYBPN2010	NSY2SPN204	NSYSFND20102D	-	NSYMP2010
2000	1000	500	1	NSYSFNV20	NSYSFNC105	NSYBPN2010	NSY2SPN205	NSYSFND2010	NSYSFND2010T	NSYMP2010
2000	1000	500	2	NSYSFNV20	NSYSFNC105	NSYBPN2010	NSY2SPN205	NSYSFND20102D	-	NSYMP2010
2000	1000	600	1	NSYSFNV20	NSYSFNC106	NSYBPN2010	NSY2SPN206	NSYSFND2010	NSYSFND2010T	NSYMP2010
2000	1000	600	2	NSYSFNV20	NSYSFNC106	NSYBPN2010	NSY2SPN206	NSYSFND20102D	-	NSYMP2010
2000	1000	800	1	NSYSFNV20	NSYSFNC108	NSYBPN2010	NSY2SPN208	NSYSFND2010	NSYSFND2010T	NSYMP2010
2000	1000	800	2	NSYSFNV20	NSYSFNC108	NSYBPN2010	NSY2SPN208	NSYSFND20102D	-	NSYMP2010
2000	1200	400	2	NSYSFNV20	NSYSFNC124	NSYBPN2012	NSY2SPN204	NSYSFND20122D	NSYSFND20122DT	NSYMP2012
2000	1200	500	2	NSYSFNV20	NSYSFNC125	NSYBPN2012	NSY2SPN205	NSYSFND20122D	NSYSFND20122DT	NSYMP2012
2000	1200	600	2	NSYSFNV20	NSYSFNC126	NSYBPN2012	NSY2SPN206	NSYSFND20122D	NSYSFND20122DT	NSYMP2012
2000	1200	800	2	NSYSFNV20	NSYSFNC128	NSYBPN2012	NSY2SPN208	NSYSFND20122D	NSYSFND20122DT	NSYMP2012
2000	1600	400	2	NSYSFNV20	NSYSFNC164	NSYBPN2016	NSY2SPN204	NSYSFND20162D	-	NSYMP2016
2000	1600	500	2	NSYSFNV20	NSYSFNC165	NSYBPN2016	NSY2SPN205	NSYSFND20162D	-	NSYMP2016
2000	1600	600	2	NSYSFNV20	NSYSFNC166	NSYBPN2016	NSY2SPN206	NSYSFND20162D	-	NSYMP2016
2200	400	400	1	NSYSFNV22	NSYSFNC44	NSYBPN224	NSY2SPN224	NSYSFND224	-	NSYMP224
2200	400	500	1	NSYSFNV22	NSYSFNC45	NSYBPN224	NSY2SPN225	NSYSFND224	-	NSYMP224
2200	400	600	1	NSYSFNV22	NSYSFNC46	NSYBPN224	NSY2SPN226	NSYSFND224	-	NSYMP224
2200	400	800	1	NSYSFNV22	NSYSFNC48	NSYBPN224	NSY2SPN228	NSYSFND224	-	NSYMP224
2200	600	400	1	NSYSFNV22	NSYSFNC64	NSYBPN226	NSY2SPN224	NSYSFND226	NSYSFND226T	NSYMP226
2200	600	500	1	NSYSFNV22	NSYSFNC65	NSYBPN226	NSY2SPN225	NSYSFND226	NSYSFND226T	NSYMP226
2200	600	600	1	NSYSFNV22	NSYSFNC66	NSYBPN226	NSY2SPN226	NSYSFND226	NSYSFND226T	NSYMP226
2200	600	800	1	NSYSFNV22	NSYSFNC68	NSYBPN226	NSY2SPN228	NSYSFND226	NSYSFND226T	NSYMP226
2200	800	400	1	NSYSFNV22	NSYSFNC84	NSYBPN228	NSY2SPN224	NSYSFND228	NSYSFND228T	NSYMP228
2200	800	500	1	NSYSFNV22	NSYSFNC85	NSYBPN228	NSY2SPN225	NSYSFND228	NSYSFND228T	NSYMP228
2200	800	600	1	NSYSFNV22	NSYSFNC86	NSYBPN228	NSY2SPN226	NSYSFND228	NSYSFND228T	NSYMP228
2200	800	800	1	NSYSFNV22	NSYSFNC88	NSYBPN228	NSY2SPN228	NSYSFND228	NSYSFND228T	NSYMP228
2200	1000	400	1	NSYSFNV22	NSYSFNC104	NSYBPN2210	NSY2SPN224	NSYSFND2210	NSYSFND2210T	NSYMP2210
2200	1000	500	1	NSYSFNV22	NSYSFNC105	NSYBPN2210	NSY2SPN225	NSYSFND2210	NSYSFND2210T	NSYMP2210
2200	1000	600	1	NSYSFNV22	NSYSFNC106	NSYBPN2210	NSY2SPN226	NSYSFND2210	NSYSFND2210T	NSYMP2210
2200	1000	800	1	NSYSFNV22	NSYSFNC108	NSYBPN2210	NSY2SPN228	NSYSFND2210	NSYSFND2210T	NSYMP2210
2200	1200	400	2	NSYSFNV22	NSYSFNC124	NSYBPN2212	NSY2SPN224	NSYSFND22122D	NSYSFND22122DT	NSYMP2212
2200	1200	500	2	NSYSFNV22	NSYSFNC125	NSYBPN2212	NSY2SPN225	NSYSFND22122D	NSYSFND22122DT	NSYMP2212
2200	1200	600	2	NSYSFNV22	NSYSFNC126	NSYBPN2212	NSY2SPN226	NSYSFND22122D	NSYSFND22122DT	NSYMP2212
2200	1200	800	2	NSYSFNV22	NSYSFNC128	NSYBPN2212	NSY2SPN228	NSYSFND22122D	NSYSFND22122DT	NSYMP2212

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures

Accessories



Installation Accessories

Composition Accessories

1 Canopy

See details p. 458

2 Fixing panels: side and partition

See details p. 461

3 Coupling kits and accessories

See details p. 464

Fixing and Lifting Accessories

6 Wall fixing support

See details p. 479

4 Floor fixing plinths and accessories

See details p. 469

5 Airing elevators for roof

See details p. 476

7 Lifting systems: eyebolts, brackets and bars

See details p. 482

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Management Accessories

Cable Entry Accessories

8

Cables entry gaskets and sealing gaskets
See details p. 503

9

Gland plates: plain, 1 entry, 2 entries
See details p. 501

10

Entry plates and adapter for entry plates
See details p. 500

11

Membranes
See details p. 495

12

Flexicable
See details p. 493

Mounting Accessories

Equipment Assembly Accessories

13

Mounting plate
See details p. 514

14

Vertical uprights
See details p. 530

15

Support tray
See details p. 539

16

Earthing
See details p. 540

Door Accessories

17

Internal door
See details p. 552

18

Side door
See details p. 554

19

Partial door
See details p. 553

20

Hinges
See details p. 555

21


Inserts, keys, locks and handles
See details p. 561

22

Intermediate crossbar
See details p. 553

23

Door-centering caster
See details p. 569

24

Door switch
See details p. 570

25

Document pocket
See details p. 570


> For more information consult the Accessories chapter **page 456**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures


Dimensions

SFN | SFN kit






Internal door



Side Door



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Stainless-Steel Enclosures

Stainless-Steel Industrial Boxes

New



Stainless-Steel Wall-Mounted Enclosures



Stainless-Steel Floor-Standing Enclosures





Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Content

How to Select the Right Stainless-Steel Enclosures	**84**
Stainless-Steel Industrial Boxes	**86**
Stainless-Steel Wall-Mounted Enclosures	**96**
Stainless-Steel Floor-Standing Enclosures	**106**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

How to Select the Right Stainless-Steel Enclosures



Why Choose Stainless-Steel Enclosures?

Industries such as chemical processing, oil and gas, food and beverage, or marine environments require enclosures that withstand humidity, corrosive agents, and demanding hygiene requirements.
Stainless steel offers the mechanical strength, chemical resistance, and durability needed to protect electrical and automation equipment in harsh environments.

Selection of the Right Stainless-Steel Grades

The corrosion resistance of stainless steel is defined by the proportions of its main alloying elements: chromium, nickel, and molybdenum.
Higher alloy content increases resistance to aggressive environments, especially in the presence of chlorides.

Comparison of the Most Common Grades

Stainless-steel type		Chemical composition (%)			
AISI grade	N. Europe	Carbon	Chromium	Nickel	Molybdenum
304L	1.4307	< 0.03	17 - 19	8 - 10	0
316L	1.4404	< 0.03	17 - 19	10 - 13	2 - 2.25



AISI 304L Stainless-Steel

This is the most commonly used type in the food and beverage industry because of its greater resistance to corrosion and ease of cleaning.

- Improved prevention against corrosion, especially in the presence of organic acids.
- Greater resistance to the effects of nitrous gas in the presence of condensed water and in most aggressive environments.



AISI 316L Stainless-Steel

It is recommended in salty or chlorinated environments thanks to of its very high resistance to corrosion created by molybdenum.

- Improved resistance to corrosion.
- Particularly well adapted to environments with acidity, bromine and saline halides or very corrosive additives and solvents.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Selecting the Finish to Enhance Stainless-Steel Properties

Three Solutions for Protection Against Aggressive Substances

Surface condition plays an important role in the fight against bacteria. The lower the roughness, the fewer bacteria become incrusted. Reduced roughness means fewer bacteria, less adhesion, and a finish that's impeccable. The choice of finish determines the appearance of the enclosures that matches the environment of other machines and equipment.



Solution 1: Scotch-Brite® Brushing (by Default)

Method:

- Use of brushing/polishing process as defined by the ASTM (American Society for Testing and Material)

Result:

- Reduced surface roughness (Ra ≤ 0.8 µm)
- Improved characteristics against polluting elements

Typical Application:

- Standard applications
- Very commonly used in chemical as well as food and beverage industries



Solution 2: Micro-Beading (on Request)

Method:

- High-speed bombardment of the surface with tiny ceramic balls which largely repairs cracks caused by lamination process

Result:

- Even surface with a silky-smooth appearance (hardly no scratches and burrs)
- Reduced surface roughness (Ra ≈ 0.8 µm)
- Increased hardness
- Reduced material adhesion
- Facilitated disinfection

Typical Application:

- Pharmaceutical and food and beverage industries



Solution 3: Protective Painting (on Request)

Method:

- Application of a protective coat of paint to the enclosure

Result:

- Compared to previous finish, improved protection against corrosion (aggressive substances, external pollution) and projections of metal particles

Typical Application:

- Marine, seaside, off-shore

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Stainless-Steel Enclosures

Stainless-Steel Industrial Boxes

Panel**SeT** SBX

PB503675_66_nb

New



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SBX


Introduction	**88**
Characteristics	**90**
Selection Table	**91**
Accessories	**92**
Dimensions	**94**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SBX

New

Introduction



Stainless-Steel boxes ready to deliver the required protection in challenging environements where corrosion resistance and anti bacterial properties are required.

Now made of low carbon emission stainless-steel with 90% of recycled material content.

PanelSeT SBX can be configured to meet your specific requirements, supported by our customization services.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



New

Low Carbon Emission Stainless-Steel

- Made of low carbon emission Stainless-Steel with 90% of recycled content leading to a 39% C02 reduction on the total enclosure lifecycle(1)




Diverse Range for Selection

- 6 sizes
- 80 mm and 120 mm in depth



Sturdy Enclosure with High Ingress Protection

- Thickness of 1.2 mm
- Mechanical protection rating
- Ingress protection rating



Added-Value for Your Work

- Quality and aesthetics
- Consistent with the dimensions of steel boxes (PanelSeT SBM)
- Mounting with versatile external brackets
- Certification (on request): UL, Veritas and BVM



Intuitive Ergonomics

- Cover opening and accessory mounting with a simple screwdriver



Customized Cut-Outs Service

- Enclosure delivered with cut-outs so you can focus on your added-value work
- Cut-outs made with an industrial laser machine for a improved result, burr-free, with high accuracy and minimal machining tolerances
- Scotch-Brite®-brushed
- External surfaces with no scratches

For more information, see **CONFIGURE** page 9.

(1) According to the comparison of PanelSeT SBX with Low Carbon Emission material PEP (ENVPEP2603015_V1) and previous material SBX PEP (ENVPEP2109018_V2) using the same calculation methodology provided in the Product Category Rules of PEP Ecopassport association (PCRed4).

This range can be configured according to your needs
3 different services available:

Time Saving

Improved Aesthetics

High Quality Cut-Outs

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SBX

Characteristics

Characteristics	PanelSeT SBX Flat box
	
	• Single-piece body (rectangular structure). Front design incorporating folded gutters. Flat rear. • 2 drilled profiles for installing mounting plates and DIN rails, with mounting centers of 12.5 mm. • Equipped with 4 half-turn thread screws to maximize maximum watertightness. • Polyurethane gasket. • Earthing connection mandatory for all boxes: equipped with an M6 x 10 mm earthing stud welded on the cover, to be linked with the body for equipotential connection. Earthing braid to be ordered separately (Ø 6.4 mm terminal). • Made of low carbon emission Stainless-Steel with 90% of recycled content.
Material	AISI 304L stainless-steel, thickness of 1.2 mm.
Finish	Scotch-Brite® brushed.
Ingress protection rating	IP66 according to IEC 60529
Mechanical protection rating	IK10 according to IEC 62262
Compliance with standards	IEC 62208, RoHS and REACH directives.
Certifications	• UL (cULus), BV, BVM • Types 4, 4X and 13 according to UL50E
Installation	**Indoor installation** Direct wall-mounting (4 x Ø 10 mm holes with sealing plugs to maintain the IP rating) or with the help of fixing lugs installed from the outside (to be ordered separately, see the specific accessory pages). Distance between mounting holes enables the installation of the box in the same locations as many existing enclosures. **Outdoor installation** Compliant with IEC 62208 regarding type tests specified in §9.12 resistance to ultra-violet (UV) radiation and §9.13 resistance to corrosion. It is always advisable to place the box under shelter to avoid water stagnation on the upper part of the enclosure.
Maximum load capacity	On the body: 50 kg/m²
Other characteristics	**Oscillatory stress constraints** Specific construction of the PanelSeT SBX - Single-piece body. The rear is flat without added parts, which helps ensure compliance with certain vibration constraints. The tests were conducted according to the marine application by Bureau Veritas Marine.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Stainless-Steel Industrial Boxes

Panel**SeT** SBX


Selection Table

	Box	Mounting plate	DIN rail	Fixing lugs	Sealing kit
					
Dimensions (mm)					
Height	**Width**	**Depth**	**References**	**References**	**References**	**References**	**References**
150	150	80	**NSYSBX15158**	**NSYMM11SB**	**NSYAMRD15357SB**	**NSYAEFPFSBX**	**NSYPPSB**
150	300	80	**NSYSBX15308**	**NSYMM13SB**	**NSYAMRD30357SB**		
200	200	80	**NSYSBX20208**	**NSYMM22SB**	**NSYAMRD20357SB**		
200	300	80	**NSYSBX20308**	**NSYMM23SB**	**NSYAMRD30357SB**		
200	400	120	**NSYSBX204012**	**NSYMM24SB**	**NSYAMRD40357SB**		
300	300	120	**NSYSBX303012**	**NSYMM33SB**	**NSYAMRD30357SB**		

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SBX

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Fixing and Lifting Accessories

1



Mounting lugs

See details p. 477

Cable Management Accessories

Cable Entry Accessories

2



Cable glands

See details p. 489

Mounting Accessories

Equipment Assembly Accessories

3



Mounting plates

See details p. 508

4



Symmetrical DIN rails

See details p. 528

5



Self-tapping screws

See details p. 541

6



Earthing accessories

See details p. 540

Door Accessories

7



Sealing kit

See details p. 541


> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SBX

Dimensions

Section A-A




Section B-B



Dimensions (mm)			Sheet thickness (mm)	Box installation (mm)			Mounting (mm)	
Height	Width	Depth		Ah	Bh	Bw	C	D
150	150	80	1.2	20.5	109	109	125	12.5
150	300	80	1.2	20.5	109	259	275	12.5
200	200	80	1.2	20.5	159	159	175	12.5
200	300	80	1.2	20.5	159	259	275	12.5
200	400	120	1.2	20.5	159	359	375	12.5
300	300	120	1.2	20.5	259	259	275	12.5

Cut-Out Zone Limits



Dimensions (mm)			References	Dimensions of permissible cut-out zone (mm)																
Height	Width	Depth		Bh	Bw	Ghr	Ghl	Gw	Jh	Jw	Kh	Kw	Lhl	Lhr	Lw	Mh	Mw	N	P	Q	R
150	150	80	**NSYSBX15158**	109	109	70	49	70	110	110	150	150	40	34.5	130	80	60	34.5	130	60	40
150	300	80	**NSYSBX15308**	109	259	70	49	220	110	260	150	300	40	34.5	280	80	210	34.5	130	60	40
200	200	80	**NSYSBX20208**	159	159	120	99	120	160	160	200	200	40	34.5	180	80	110	34.5	180	110	40
200	300	80	**NSYSBX20308**	159	259	120	99	220	160	260	200	300	40	34.5	280	80	210	34.5	180	110	40
200	400	120	**NSYSBX204012**	159	359	120	99	320	160	360	200	400	80	74.5	380	120	310	74.5	180	110	80
300	300	120	**NSYSBX303012**	259	259	220	199	220	260	260	300	300	80	74.5	280	120	210	74.5	280	210	80

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Stainless-Steel Enclosures

Stainless-Steel Wall-Mounted Enclosures

Panel**SeT** S3X

PB500075_40_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3X

Introduction	**98**
Characteristics	**100**
Selection Table	**101**
Accessories	**102**
Dimensions	**104**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3X

Introduction



These enclosures are specifically designed for demanding environments such as the chemical, oil and gas, and food and beverage industries, where strict hygiene and high corrosion resistance are essential.

They are engineered to provide the reliable protection required for the industry's most challenging applications

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Stainless-Steel Wall-Mounted Enclosures
PanelSeT S3X
Introduction



Material Type and Custom Finish Choices
- Two types of stainless-steel: 304L and 316L
- Scotch-Brite® brushed finish offered as standard
- Painted or micro-beaded finish (on request)



Large Range of Accessories
- Stainless-steel accessories: canopy, wall fixing lugs
- Standard accessories: mounting plate, internal door, modular chassis and step slides
- Large selection of locks made of 100% stainless-steel



Enhanced Sealing
- Protection rating
- Sealing polyurethane gasket
- Gutter-shaped front profile
- Three locking points in the double-door version



High Robustness and Durability
High resistance to external mechanical impacts:
- Door reinforcement frame or profile
- Stainless-steel hinges



Time Savings and Easy Assembly
- 304L or 316L stainless-steel wall fixing lugs
- Vertical reinforcement perforated profiles, which make it easier to equip the door
- Reversible door opening to 120°
- Easy installation directly on the machine thanks to the 4 rear drilled holes

This range can be configured according to your needs
4 different services available:


Assemble to order


Mounting of standard accessories


Machining


Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3X

Characteristics


Characteristics	NSYS3X●●●●	NSYS3X●●●●T	NSYS3X●●●●H
			
Comment: For dimensions see page 104			
	304L stainless-steel Enclosure with plain door	304L stainless-steel Enclosure with glazed door, Securit® glass, 4 mm thick	316L stainless-steel Enclosure with plain door
Material	AISI 304L		AISI 316L
Finish	Scotch-Brite® brushed		
Thickness	10/10e - 15/10e mm		
Ingress protection rating	• Single-door: IP66 • Double-door: IP55 according to IEC 60529		
Mechanical protection rating	IK10 according to IEC 62262	IK08 according to IEC 62262	IK10 according to IEC 62262
Standards and certifications	Rating according to UL50E: • Single-door: Types 4,4X and 13 • Double-door: Types 1 and 12. See technical guide on page 594		
Installation	Suitable for outdoor installation, but consideration of environmental aggressiveness is advised. Stainless steel 316L, offering superior corrosion resistance, is recommended for outdoor use, especially in harsh or saline environments. The enclosure can also be installed indoor. Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to ultra-violet (UV) radiation) and §9.13 (resistance to corrosion). It is always advisable to install a canopy to reduce water stagnation on the upper part of the enclosure.		
Other characteristics	• Single-piece body (cross-shaped structure) with gutter-shaped front profile • 4 or 6 rear studs for mounting plate fixation • 2 cut-out vertical profiles on the door (from a height of 600 mm), with drill holes with a diameter of 4.25 mm and a pitch of 25 mm for accessory installation • Door reinforcement frame (from a height of 1000 mm), cross-section of 20 mm x 15 mm, with drilled holes with a diameter of 5 mm and a pitch of 25 mm • Standard lock with 3-mm double-bar lock (chrome-plated zamak) • 2 locking points for heights of more than 500 mm or three points for two-door enclosures • Stainless-steel hinges screwed to the body of the enclosure. They make it easier to remove and invert the door. Opening angle: 120° • Maximum load: - on Mounting plate: 250 kg/m² - on door: 50 kg/m² • Polyurethane gasket • M6 x 16 mm screws on the door and on the body, allowing equipotential connection between the earth connections (on request) • 4 holes for fixing to the wall directly or with the help of mounting lugs (sold separately), sealed by sealing plugs		

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Stainless-Steel Wall-Mounted Enclosures

Panel**SeT** S3X

Selection Table

External dimensions (mm)					304L stainless-steel		316L stainless-steel
							
Height	Width	Depth	No. of locks	No. of doors	References		
300	200	150	1	1	**NSYS3X3215**	-	**NSYS3X3215H**
300	250	150	1	1	**NSYS3X302515**	-	**NSYS3X302515H**
300	300	150	1	1	**NSYS3X3315**	-	**NSYS3X3315H**
400	300	150	1	1	**NSYS3X4315**	-	**NSYS3X4315H**
400	300	200	1	1	**NSYS3X4320**	**NSYS3X4320T**	**NSYS3X4320H**
400	400	200	1	1	**NSYS3X4420**	-	**NSYS3X4420H**
400	600	200	1	1	**NSYS3X4620**	-	**NSYS3X4620H**
500	400	200	2	1	**NSYS3X5420**	**NSYS3X5420T**	**NSYS3X5420H**
600	400	200	2	1	**NSYS3X6420**	**NSYS3X6420T**	**NSYS3X6420H**
600	600	250	2	1	**NSYS3X6625**	-	**NSYS3X6625H**
600	1000	300	(1)	2	**NSYS3X601030**	-	-
600	1200	300	(1)	2	**NSYS3X601230**	-	-
700	500	250	2	1	**NSYS3X7525**	**NSYS3X7525T**	**NSYS3X7525H**
800	600	250	2	1	**NSYS3X8625**	**NSYS3X8625T**	**NSYS3X8625H**
800	800	300	2	1	**NSYS3X8830**	-	**NSYS3X8830H**
800	1000	300	(1)	2	**NSYS3X801030**	-	-
800	1200	300	(1)	2	**NSYS3X801230**	-	-
1000	800	300	2	1	**NSYS3X10830**	**NSYS3X10830T**	**NSYS3X10830H**
1000	1000	300	(1)	2	**NSYS3X101030**	-	**NSYS3X101030H**
1200	800	300	2	1	**NSYS3X12830**	-	**NSYS3X12830H**
1200	1000	300	(1)	2	**NSYS3X121030**	-	**NSYS3X121030H**


(1) Three-point locking system.

External dimensions				Mounting Plates			Chassis	Step Slides
								
Height (mm)	Width (mm)	Depth (mm)	Number of modules	Plain	Microperforated	Telequick	Modular Chassis	Step slides
300	200	150	-	**NSYMM32**	**NSYMF32**	**NSYMR32**	-	-
300	250	150	-	**NSYMM3025**	-	**NSYMR3025**	-	-
300	300	150	-	**NSYMM33**	**NSYMF33**	**NSYMR33**	-	-
400	300	150	24	**NSYMM43**	**NSYMF43**	**NSYMR43**	**NSYDLM24**	-
400	300	200	24	**NSYMM43**	**NSYMF43**	**NSYMR43**	**NSYDLM24**	**NSYSDCR200**
400	400	200	-	**NSYMM44**	**NSYMF44**	**NSYMR44**	-	**NSYSDCR200**
400	600	200	-	**NSYMM64**	**NSYMF64**	**NSYMR46**	-	**NSYSDCR200**
500	400	200	48	**NSYMM54**	**NSYMF54**	**NSYMR54**	**NSYDLM48**	**NSYSDCR200**
600	400	200	48	**NSYMM64**	**NSYMF64**	**NSYMR64**	**NSYDLM48P**	**NSYSDCR200**
600	600	250	84	**NSYMM66**	**NSYMF66**	**NSYMR66**	**NSYDLM84P**	**NSYSDCR250**
600	1000	300*	-	**NSYMM106**	**NSYMF106**	**NSYMR106**	-	**NSYSDCR300**
600	1200	300*	-	**NSYMM126**	**NSYMF126**	-	-	**NSYSDCR300**
700	500	250	66	**NSYMM75**	**NSYMF75**	**NSYMR75**	**NSYDLM66**	**NSYSDCR250**
700	500	250	88	-	-	-	**NSYDLM88**	-
800	600	250	84	**NSYMM86**	**NSYMF86**	**NSYMR86**	**NSYDLM84**	**NSYSDCR250**
800	600	250	112	-	-	-	**NSYDLM112**	-
800	800	300	-	**NSYMM88**	**NSYMF88**	**NSYMR88**	-	**NSYSDCR300**
800	1000	300(1)	-	**NSYMM108**	**NSYMF108**	**NSYMR108**	-	**NSYSDCR300**
800	1200	300(1)	-	**NSYMM128**	**NSYMF128**	**NSYMR128**	-	**NSYSDCR300**
1000	800	300	234	**NSYMM108**	**NSYMF108**	**NSYMR108**	**NSYDLM240**	**NSYSDCR300**
1000	1000	300	-	**NSYMM1010**	**NSYMF1010**	**NSYMR1010**	-	**NSYSDCR300**
1200	800	300	-	**NSYMM128**	**NSYMF128**	**NSYMR128**	-	**NSYSDCR300**
1200	1000	300	-	**NSYMM1210**	**NSYMF1210**	**NSYMR1210**	-	**NSYSDCR300**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3X

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1 Canopy



See details p. 459

2 Plinths



See details p. 470

3 Support bracket



See details p. 466

Fixing and Lifting Accessories

4 Mounting lugs



See details p. 477

5 Eyebolts




See details p. 482

Mounting Accessories

Equipment Assembly Accessories

6 Mounting plates plain, microperforated and Telequick



See details p. 509

7 Mounting plate screw



See details p. 541

8 Step sides



See details p. 521

9 Earthing accessories



See details p. 540

Equipment Assembly Accessories

10 Modular chassis



See details p. 542

Equipment Assembly Accessories

11 Internal door



See details p. 550

12 Inserts, keys, locks and handles



See details p. 556

13 Door switch and retainer



See details p. 569

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3X

Dimensions

Fig. 1





Fig. 2



External dimensions (mm)			Fig.
A	B	C	
300	200	150	1
300	250	150	1
300	300	150	1
400	300	150	1
400	300	200	1
400	400	200	1
400	600	200	1
500	400	200	2 (without door reinforcement)
600	400	200	2
600	600	250	2
700	500	250	2
800	600	250	2
800	800	300	2

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Fig. 3





Fig. 4



** For glazed door.

External dimensions (mm)			Fig.
A	B	C	
1000	800	300	3
1000	1000	300	4
1200	800	300	3
1200	1000	300	4

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Stainless-Steel Enclosures

Stainless-Steel Floor-Standing Enclosures

Panel**SeT** SMX: Monobloc Enclosures

PB500138



Panel**SeT** SFX: Modular Enclosures

PB502731_22_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SMX: Monobloc Enclosures

Introduction	**108**
Characteristics	**110**
Selection Table	**111**
Accessories	**112**
Dimensions	**116**

Panel**SeT** SFX: Modular Enclosures

Introduction	**108**
Characteristics	**110**
Selection Table	**111**
Accessories	**114**
Dimensions	**117**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SMX and SFX

Introduction




Designed for industries with stringent hygiene and corrosion-resistance requirements, such as chemical, oil and gas, and food and beverage sectors, the floor-standing stainless-steel ranges offer reliable protection in harsh conditions.
The SMX monobloc enclosure delivers a rigid, fully integrated structure ideal for compact installations, while the modular SFX system enables the creation of large, scalable assemblies.
Each solution can be tailored to your exact specifications with our extensive customization capabilities.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Material Type and Custom Finish Choices
- AISI 304L as standard in PanelSeT SMX and SFX
- AISI 316L as standard in PanelSeT SMX and on request in PanelSeT SFX
- Finish: Scotch-Brite® brushed (standard), micro-beaded (on request), painted (on request)



Time Savings and Easy Assembly
- Complete range of accessories for installation, cable management, etc
- 304L or 316L stainless-steel plinth: easy cable entry (PanelSeT SFX and SMX)
- Reversible door opening to 120°
- Adjustment rails perforated with a pitch of 25 mm
- Perforated reinforcement frame allowing accessories to be mounted on the door



Enhanced Sealing
- Protection rating against dust and water, depending model
- 3-point locking system
- Canopy (accessory): helps protect the door sealing, helps guarantee correct water drainage, no stagnation on the top
- Single-piece cable gland plate with polyurethane gasket



Compatible with the Other Ranges
- Compatible with mounting plates and certain accessories of PanelSeT SFN and SM, providing seamless interchangeability and enhanced versatility



Hygienic Properties
- The high quality of the standard finish enables easy maintenance while limiting contamination
- The hygienic feet made from 316L stainless-steel, adjustable between 140 mm and 200 mm in height, make it easier to clean under the enclosures



High Robustness and Durability
- High resistance to external mechanical impacts
- 3 hinges made entirely from stainless-steel
- Door reinforcement frame



Resistance to Corrosion
- Highly resistant to corrosion. 304L and 316L stainless-steels provide a good solution for applications in demanding environments

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SMX and SFX

Characteristics

Characteristics	PanelSeT SMX	PanelSeT SFX
	 PB500138	 PB502731_22_nb
	• Stainless-steel floor-standing enclosure, folded and welded • Single and double front door, with reinforcement frame	• Enclosure made up of a structure, consisting of top and bottom, rear panel and vertical profiles • Single and double front door, with reinforcement frame
Material	304L stainless-steel, 316L stainless-steel	304L stainless-steel, 316L version (on request)
Finish	Scotch-Brite® brushed finish Micro-beaded and painted finishes (on request)	
Thickness	• Enclosure: 20/10e mm • Cable gland plate: 15/10e mm	Consult us
Ingress protection rating	IP66 (single-door enclosure) according to IEC 60529	
Mechanical protection rating	• IK10 according to IEC 62262 • IP55 (double door enclosure) according to IEC 60529	
Standards and certifications	• cULus only for Single door SMX and SFX enclosures Rating 1, 2, 3, 3R, 4, 4x, 5, 12 and 13 • For double door on SMX:1, 12 and 13 and for SFX double doors rated 1 • See technical guides page 594	
Installation	Suitable for indoor and outdoor installation, but consideration of environmental aggressiveness is advised. Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to ultra-violet (UV) radiation) and §9.13 (resistance to corrosion). It is always advisable to install a canopy to reduce water stagnation on the upper part of the enclosure.	
Other characteristics	Plain front door. Opening to left or right to 120° with reinforcement frame installed: • 3 stainless-steel hinges • 3-point locking system with handle made from painted zamak, 5-mm double-bar • SMX max. Load: Mounting plate: 220 kg/m² -Door: 50 kg/m² - Max Total Load: 460.35 kg/m² • SFX max. Load: mounting plate 220 kg/m² - Door: 50 kg/m² - Side panels: 80 kg/m² - Roof: 100 kg/m²	
Supply	• Welded compact body • Single-piece cable gland plate with sealing gasket • Welded mounting plate support brackets	• Welded rear panel • 4 mounting plate-supporting brackets • Single-piece cable gland plate with sealing gasket

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Stainless-Steel Floor Standing Enclosures
PanelSeT SMX and SFX
Selection Table


				SMX		SFX
				 PB500138	 NSYSMX18840H	 PB502731_22_nb
External dimensions (mm)						
Height	Width	Depth	Number of front doors	304 L	316L	304L
1400	1000	300	2	**NSYSMX141030**	-	-
1600	800	400	1	**NSYSMX16840**	-	-
1800	600	400	1	**NSYSMX18640**	-	**NSYSFX18640**
1800	800	400	1	**NSYSMX18840**	**NSYSMX18840H**	**NSYSFX18840**
1800	1200	400	2	**NSYSMX181240**	-	**NSYSFX181240**
1800	1600	400	2	**NSYSMX181640**	**NSYSMX181640H**	-
2000	600	500	1	-	-	**NSYSFX20650**
2000	800	400	1	-	-	**NSYSFX20840**
2000	800	500	1	**NSYSMX20850**	-	-
2000	800	600	1	-	-	**NSYSFX20860**
2000	1000	400	2	**NSYSMX201040**	**NSYSMX201040H**	-
2000	1000	600	2	-	-	**NSYSFX201060**
2000	1200	500	2	**NSYSMX201250**	**NSYSMX201250H**	-
2000	1200	600	2	-	-	**NSYSFX201260**
2000	1600	600	2	**NSYSMX201660**	**NSYSMX201660H**	-

Comment:
For dimensions see page 116

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SMX: Monobloc Enclosures

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Canopy

See details p. 459

2



Plinths

See details p. 470

Fixing and Lifting Accessories

3



Wall fixing lugs

See details p. 477

4



Eyebolts

See details p. 482

5



Hygienic feet

See details p. 481

Mounting Accessories

Equipment Assembly Accessories

6



Plain mounting plates

See details p. 514

7



Vertical uprights

See details p. 530

8




Earthing accessories

See details p. 540

Door Accessories

9



Locking options


See details p. 563

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFX: Modular Enclosures

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Canopy

See details p. 459

2



Side panels

See details p. 461

3



Plinths

See details p. 470

Fixing and Lifting Accessories

4



Lifting brackets

See details p. 482

5



Eyebolts

See details p. 482

6



Hygienic feet

See details p. 481

Mounting Accessories

Equipment Assembly Accessories

7



Plain mounting plates

See details p. 514

8



Vertical uprights

See details p. 530

9




Earthing accessories

See details p. 540

Door Accessories

10



Locking options


See details p. 563


> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SMX: Monobloc Enclosures


Dimensions






Enclosure width of 1000 and 1200 mm


Floor-standing enclosure (mm)			Number of front doors	Number of cable gland plates	Dimensions (mm)	
Height (A)	Width (B)	Depth (C)			E	F
1400	1000	300	1	1	720	270
1600	800	400	1	1	520	270
1800	600	400	1	1	520	270
1800	800	400	1	1	520	270
1800	1200	400	2	1	920	270
1800	1600	400	2	2	1320	270
2000	800	500	1	1	520	370
2000	1000	400	2	1	720	270
2000	1200	500	2	1	920	370
2000	1600	600	2	2	1320	470




Enclosure width of 1600 mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.








Enclosure width 1000 mm

External dimensions (mm)			Number of front doors	Number of cable gland plates
Height (A)	Width (B)	Depth (C)		
1800	600	400	1	1
1800	800	400	1	1
1800	1200	400	2	2
2000	600	500	1	1
2000	800	400	1	1
2000	800	600	1	1
2000	1000	600	2	1
2000	1200	600	2	2




Enclosure width 1200 mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Insulated Enclosures

Insulated Boxes



Insulated Wall-Mounted Enclosures



Insulated Floor-Standing Enclosures





Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Content

Insulated Boxes	**120**
Insulated Wall-Mounted Enclosures	**144**
Insulated Floor-Standing Enclosures	**156**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Insulated Enclosures


Insulated Boxes

Panel**SeT** TBS-TBP: Industrial Boxes

NSYTBS19168



NSYTBS19168T



Panel**SeT** PLS: Modular Boxes

PBS502791_61_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes

Introduction	122
Characteristics	124
Selection Table	126
Accessories	128
Dimensions	130

Panel**SeT** PLS: Modular Boxes

Introduction	134
Characteristics	136
Selection Table	138
Accessories	140
Dimensions	142

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes

Introduction



The PanelSeT TBS and TBP boxes offer superior protection against dust and water, enhanced electrical insulation, as well as high resistance to impacts, UV rays, and extreme temperatures. Additionally, these boxes are well-known for their ease of installation.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT TBS-TBP: Industrial Boxes

Introduction

Only for TBS



New

Recycled Material

- Usage of a 45% post-industrial recycled ABS plastic

TBS-TBP



Easy to Install

- 3 methods of fixing the box to its support



Easy to Use

- Only one tool is required: A flat-bladed screwdriver



Smart

- Fixing studs on the cover

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes

Characteristics

Characteristics	Universal boxes rated IP66
Class II	 
	Boxes can be coupled (exactly the same dimensions) with kit ref. **13934**. Locks from box size of 116 x 116 x 62 mm: • Cover locking by 4 plastic captive screws with coarse thread outside the sealed area, • Plumbable lock. Locks from box size of 138 x 93 x 72 mm: • The standard screws (flat-bladed screwdriver) can be replaced with other standardised screws. The 4 reinforced edges of the cover improve its robustness and support during customization operations. Adaptable hinges on all the 20 and 40 mm covers.
Material	ABS boxes: • Transparent cover made of polycarbonate • Glow wire resistance: 650 °C according to IEC 60695-2-11 • Operating temperature: -25 °C...+60 °C • Installation temperature: -15 °C...+40 °C Polycarbonate boxes: • Glow wire resistance: 960 °C • Operating temperature: -25 °C...+80 °C • Installation temperature: -15 °C...+60 °C
Color	• Body: RAL 7035 gray • Cover: RAL 7035 gray or transparent
Ingress protection rating	IP66 according to IEC 60529
Mechanical protection rating	ABS: IK07 according to IEC 62262 Polycarbonate: IK08 according to IEC 62262
Standards	IEC 62208
Certifications	• IEC 62208 certified by TÜV • UL (cULus): Polycarbonate boxes • Product Environmental Profile • Class II according to IEC 61140 Polycarbonate boxes: • Rating according UL50E: Types 4, 4X • Self-extinguishing
Installation	Fixing the box: • Outside the sealed sensitive volume by the 4 chimneys in the corners from box size of 138 x 93 x 72 mm • Through the rear of the box by 2 or 4 elongated holes to be perforated • With fixing lugs from box size of 116 x 116 x 62 mm (ref. **NSYAEFTB**) **Outdoor installation, only for polycarbonate boxes:** Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance UV radiation) and §9.13 (resistance to corrosion). Equipment installation: • Studs for fixing the equipment in the body and the cover of the box by means of a Ø 4 mm self-tapping screw (ref. **NSYAMFSTB**, screw Ø 4 x 10 mm with Pozidriv and slotted head) • Option of installing rails, plates or other types of supports (card, etc.) • Spacers and stand-offs to be installed on the studs for adjusting the height of the equipment

NOTICE

ENCLOSURE PROTECTION

For outdoor use, in case the boxes are not installed under a shelter to protect them against bad weather conditions, a canopy must be installed on the top of the boxes. This will help avoid water stagnation between body and lid.

To prevent condensation, install plastic airing louvres accessories. To prevent internal pressure, install a sealed pressure balance valve.

Failure to follow these instructions can result in equipment damage.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes

Characteristics

Characteristics	ABS boxes with push-buttons rated IP54	ABS boxes prepared for push-buttons
Class II	 PB500250_15_nb	 PB500252_22_nb
	Boxes can be coupled (exactly the same dimensions) with kit ref. **13934**. Locks from box size of 116 x 116 x 62 mm: • Cover locking by 4 plastic captive screws with coarse thread outside the sealed area, • Plumbable lock. Locks from box size of 138 x 93 x 72 mm: • The standard screws (flat-bladed screwdriver) can be replaced with other standardised screws. The 4 reinforced edges of the cover improve its robustness and support during customization operations. Adaptable hinges on all the 20 and 40 mm covers.	
Material	ABS boxes: • Glow wire resistance: 650 °C according to IEC 60695-2-11 • Operating temperature: -25 °C...+60 °C • Installation temperature: -15 C...+40 °C	
Color	• Body: RAL 7035 gray • Cover: RAL 7035 gray or transparent	
Ingress protection rating	IP54 according to IEC 60529	-
Mechanical protection rating	ABS: IK07 according to IEC 62262	
Standards	IEC 62208	
Certifications	• IEC 62208 certified by TÜV • Product Environmental Profile • Class II according to IEC 61140	
Installation	Fixing the box: • Outside the sealed sensitive volume by the 4 chimneys in the corners from box size of 138 x 93 x 72 mm • Through the rear of the box by 2 or 4 elongated holes to be perforated • With fixing lugs from box size of 116 x 116 x 62 mm (ref. **NSYAEFTB**) Equipment installation: • Studs for fixing the equipment in the body and the cover of the box by means of a Ø 4 mm self-tapping screw (ref. **NSYAMFSTB**, screw Ø 4 x 10 mm with Pozidriv and slotted head) • Option of installing rails, plates or other types of supports (card, etc.) • Spacers and stand-offs to be installed on the studs for adjusting the height of the equipment	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT TBS-TBP: Industrial Boxes

Selection Table

Universal boxes with ABS IP66 IK07											PC-UL IP66 IK08	
												
Overall external dimensions (mm)			Overall internal dimensions (mm)									
Height	Width	Depth	Height	Width	Depth	Body	Cover	Minor pack.	Cover screw	Opaque cover	Transparent cover	Opaque cover	Transparent cover
74	74	54	65	65	47	37	10	5	Metal	**NSYTBS775**	-	**NSYTBP775**	-
89	89	54	80	80	47	37	10	5	Metal	**NSYTBS885**	-	**NSYTBP885**	-
116	74	62	105	65	55	45	10	5	Metal	**NSYTBS1176**	-	**NSYTBP1176**	-
116	74	94	105	65	85	45	40	3	Metal	**NSYTBS1179H**	-	-	-
116	116	62	105	105	55	45	10	5	Plastic	**NSYTBS11116**	-	**NSYTBP11116**	-
116	116	133	105	105	125	45	80	2	Plastic	**NSYTBS111113H**	-	-	-
138	93	72	125	80	65	45	20	2	Plastic	**NSYTBS1397**	**NSYTBS1397T**	**NSYTBP1397**	**NSYTBP1397T**
164	121	87	150	105	80	60	20	2	Plastic	**NSYTBS16128**	**NSYTBS16128T**	**NSYTBP16128**	**NSYTBP16128T**
192	121	87	175	105	80	60	20	2	Plastic	**NSYTBS19128**	**NSYTBS19128T**	**NSYTBP19128**	**NSYTBP19128T**
192	121	105	175	105	100	60	40	2	Plastic	**NSYTBS191210H**	**NSYTBS191210HT**	**NSYTBP191210H**	**NSYTBP191210HT**
192	164	87	175	150	80	60	20	1	Plastic	**NSYTBS19168**	**NSYTBS19168T**	**NSYTBP19168**	**NSYTBP19168T**
192	164	105	175	150	100	60	40	1	Plastic	**NSYTBS191610H**	**NSYTBS191610HT**	**NSYTBP191610H**	**NSYTBP191610HT**
241	194	87	225	175	80	60	20	1	Plastic	**NSYTBS24198**	**NSYTBS24198T**	**NSYTBP24198**	**NSYTBP24198T**
241	194	107	225	175	100	80	20	1	Plastic	**NSYTBS241910**	**NSYTBS241910T**	**NSYTBP241910**	**NSYTBP241910T**
241	194	107	225	175	100	60	40	1	Plastic	**NSYTBS241910H**	**NSYTBS241910HT**	**NSYTBP241910H**	**NSYTBP241910HT**
241	194	127	225	175	120	80	40	1	Plastic	**NSYTBS241912H**	**NSYTBS241912HT**	**NSYTBP241912H**	**NSYTBP241912HT**
291	241	88	275	225	80	60	20	1	Plastic	**NSYTBS29248**	**NSYTBS29248T**	**NSYTBP29248**	**NSYTBP29248T**
291	241	128	275	225	120	100	20	1	Plastic	**NSYTBS292412**	**NSYTBS292412T**	**NSYTBP292412**	**NSYTBP292412T**
291	241	128	275	225	120	60	60	1	Plastic	**NSYTBS292412H**	**NSYTBS292412HT**	**NSYTBP292412H**	**NSYTBP292412HT**
291	241	168	275	225	160	100	60	1	Plastic	**NSYTBS292416H**	**NSYTBS292416HT**	**NSYTBP292416H**	**NSYTBP292416HT**
341	291	128	325	275	120	100	20	1	Plastic	**NSYTBS342912**	**NSYTBS342912T**	**NSYTBP342912**	**NSYTBP342912T**
341	291	168	325	275	160	100	60	1	Plastic	**NSYTBS342916H**	**NSYTBS342916HT**	**NSYTBP342916H**	**NSYTBP342916HT**

Mounting Plates for Adjustment to Mounting Surface

Installation:

- Fixing by means of Ø 4 mm self-tapping screws, Pozidrive and slotted head, ref. **NSYAMFSTB**

Supply:
Plates supplied without screws

Mounting plates	
	
Material: Galvanized steel	**Material:** Insulated polyester plate reinforced with fiberglass, halogen-free: Glow wire resistance 750 °C according to IEC 60695-2-11.

Box		Mounting plate dimensions				
Height (mm)	Width (mm)	A (mm)	B (mm)	Minor pack.	Thickness: 15/10e mm	Thickness: 25/10e mm
192	164	168.5	140	1	**NSYAMPM1916TB**	**NSYAMPA1916TB**
241	194	215	168.5	1	**NSYAMPM2419TB**	**NSYAMPA2419TB**
291	241	265	215	1	**NSYAMPM2924TB**	**NSYAMPA2924TB**
341	291	315	265	1	**NSYAMPM3429TB**	**NSYAMPA3429TB**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT TBS-TBP: Industrial Boxes

Selection Table

Button Description
- Emergency-off function with a red, Ø 40 mm, turn-to-unlock palm button.
- Start/stop function with 2 push-buttons.
- Up/down/stop function with 3 push buttons.

Technical Features of the Switches:
- NC switch with positive opening maneuver according to IEC 60947-5-1 appendix K,
- Mechanical durability of the emergency switch: 0.1 million cycles,
- Mechanical durability of the NC and NO switches: 5 million cycles,
- Protection against short circuits: 10 A.

- Ref. **XALEK1702** houses an emergency switching off palm button with mechanical locking according to standards IEC 60364-5-53 and 60947-5-5.


Comment:
For dimensions see page 130






Overall external dimensions			Overall internal dimensions								Boxes equipped with IP54 ABS buttons	ABS button boxes, to be equipped
Height (mm)	Width (mm)	Depth (mm)	Height (mm)	Width (mm)	Depth (mm)	Body (mm)	Cover (mm)	Minor pack.	No. of holes	Function	References	References
74	74	83	-	-	-	-	-	1	-	Emergency switching off	**XALEK170**	-
116	74	62	105	65	55	45	10, Gray	5	2	-	-	**XALE2**
116	74	62	105	65	55	45	10, Gray	5	3	-	-	**XALE3**
116	74	75	-	-	-	-	-	1	-	Up/down/stop	**XALE3255**	-


Function	Push-button type	Type NO
Emergency switching off	Locking, red	1
Start/stop		
Start	Flush, green	1
Stop	Projecting, red	-
Up/down/stop		
Up	Flush, black	-
Down	Flush, white	-
Stop	Projecting, red	-



Function	Push-button type	Type NC
Emergency switching off	Locking, red	1
Start/stop		
Start	Flush, green	-
Stop	Projecting, red	1
Up/down/stop		
Up	Flush, black	-
Down	Flush, white	-
Stop	Projecting, red	1




Function	Push-button type	Type C/O
Emergency switching off	Locking, red	-
Start/stop		
Start	Flush, green	-
Stop	Projecting, red	-
Up/down/stop		
Up	Flush, black	1
Down	Flush, white	1
Stop	Projecting, red	-



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT TBS-TBP: Industrial Boxes

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Coupling kit

See details p. 464

2



Sealed pressure balance valves

See details p. 476

Fixing Accessories

3



Set of fixing lugs

See details p. 477

Cable Management Accessories

Cable Entry Accessories

4



Cable entries: membranes, cone shaped, quick cable entries

See details p. 488

5



Cable glands

See details p. 490

Mounting Accessories

Equipment Assembly Accessories

6



Mounting plates: plain and insulated

See details p. 508

7



Symmetric DIN rails and screws for rails

See details p. 529

Door Accessories

8



Hinges

See details p. 555

9



Cover accessories

See details p. 564

> For more information consult the Accessories chapter **page 456**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes


Dimensions

Box of 74 x 74 x 54 mm (external dimensions) **NSYTB●●●775**


Interior



Side




Rear




Box of 89 x 89 x 54 mm (external dimensions) **NSYTB●●●885**


Interior



Side




Rear





Box of 116 x 74 x 62 or 94 mm (external dimensions) **NSYTB●●●1176** or **NSYTB●●●1179**

Interior




Side






Rear





Box of 116 x 116 x 62 or 133 mm (external dimensions) **NSYTB●●●11116** or **NSYTB●●●111113**

Interior




Side






Rear




Cover




Box of 138 x 93 x 72 mm (external dimensions) **NSYTB●●●1397**


Interior




Side



Rear



Cover




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes


Dimensions

Box of 164 x 121 x 87 mm (external dimensions) **NSYTB●●●16128**


Interior




Side



Rear




Cover




Box of 192 x 121 x 87 or 105 mm (external dimensions) **NSYTB●●●19128** or **NSYTB●●●191210**

Interior




Side

Height 80 mm
(60 + 20 mm)




Side


Height 100 mm
(60 + 40 mm)




Rear




Cover




Box of 192 x 164 x 87 or 105 mm (external dimensions) **NSYTB●●●19168** or **NSYTB●●●191610**





Height 80 mm
(60 + 20 mm)



Height 100 mm
(60 + 40 mm)








Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Panel**SeT** TBS-TBP: Industrial Boxes

Dimensions

Box of 241 x 194 x 87, 107 or 127 mm (external dimensions)
NSYTB●●●24198, **NSYTB●●●241910** or **NSYTB●●●241912**



Box of 291 x 241 x 88, 128 or 168 mm (external dimensions)
NSYTB●●●29248, **NSYTB●●●292412** or **NSYTB●●●292416**




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** TBS-TBP: Industrial Boxes

Dimensions

Box of 341 x 291 x 128 or 168 mm (external dimensions)
NSYTB●●●342912 or **NSYTB●●●342916**



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLS: Modular Boxes

Introduction



The PanelSeT PLS range includes Class II insulated polyester and polycarbonate industrial boxes, which can be interconnected on all sides, allowing for a wide variety of modular assemblies.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.


Note:
Prolonged exposure to UV radiation, wind and rain can cause aesthetics changes in the external surface of the enclosure without affecting the technical properties according to IEC 62208. For long-term aesthetics requirements, it is recommended to use painted enclosures available through our customization offer.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Enhanced Protection

- IP66
- Gasket between body and cover
- IK09
- Insulation Class II



Easy Access

Bosses with inserts, at the rear of the body, for fixing plates or various supports



Modular Offer

The dimensions of the sides, multiples of 9 cm, allow the creation of assemblies

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLS: Modular Boxes

Characteristics

Characteristics	NSYPLS5454AG	NSYPLS1827G	NSYPLSC5472AG	NSYPLSC1827G	NSYPLSP1827G
According to Reach and RoHs and Halogen-free					
Class II	Complete box				
	• Insulated boxes that can be coupled by all their side surfaces, allowing the creation of the greatest variety of modular assemblies. • The product references show the two lateral dimensions in cm. • 14 sizes of insulated boxes; The sides are multiples of 9 cm. • Body made from polyester reinforced with fiberglass, molded by hot compression, 9 sizes. • 3 types of cover available according to the sizes: Standard cover, made from transparent polycarbonate with neoprene gasket, 45 mm high, or 95 mm high (final index A), Opaque polycarbonate cover (index C), with neoprene gasket, 45 mm high, or 95 mm high (final index A), Polyester reinforced with fiberglass cover (index P) with PUR gasket, 45 mm high. • Complete box includes body, cover, locking screws and sealing device. • The bodies (prefix F) and the covers (prefix T) are supplied separately as standard references. The separate covers are supplied without locking screws or sealing accessories. • The PLS enclosures with transparent cover are also offered in sets; The reference refers to the complete set. • Excellent resistance to corrosion; withstands most chemical substances. • Full insulation to create Class II assemblies. • Standard lock with slot screws outside the volume of the boxes. Delivered with sealing system. • External wall-mounted by 4 lugs, to be ordered separately. • Service temperature: -40 to +80 °C. • Bosses with M6 inserts for fixing the mounting plate. • Halogen-free and compliant with the RoHS directive.				
Color	RAL 7035 gray (opaque bodies and opaque covers)				
Ingress protection rating	IP66				
Mechanical protection rating	IK09				
Certifications	• Certification according to standard IEC 62208 to help ensure compliance with IP, IK, resistance to heat and fire (self-extinguishing), insulation to 5000 V, and load of the mounting plate, 100 kg/m^2 • Certified UL (cULus). Rating according UL50E Type 1, 2, 3, 3R, 4, 4X, 12 and 13				
Installation	Outdoor installation: Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to UV radiation) and §9.13 (resistance to corrosion). It is always advisable to install a canopy to avoid water stagnation on the top of the enclosure and to help protect against UV radiation.				

NSYPLS, **NSYPLSP** and **NSYPLSC** followed by suffixes.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLS: Modular Boxes

Characteristics

Characteristics	NSYDLS12
	
Class II	Modular distribution chassis
	Built-in DLS modular chassis, made up of an insulated protection panel, RAL 7011 color, 35-mm DIN rails and a 2 x 16 + 5 x 6 mm² neutral/earth connection strip.
Ingress protection rating	IP43
Mechanical protection rating	IK09
Installation	Indoor

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLS: Modular Boxes


Selection Table

Complete box



Dimensions (mm)			Transparent cover	Polycarbonate cover	Polyester cover
Height	Width	Depth			
180	270	180	**NSYPLS1827G**	**NSYPLSC1827G**	**NSYPLSP1827G**
270	270	180	**NSYPLS2727G**	**NSYPLSC2727G**	**NSYPLSP2727G**
270	270	230	**NSYPLS2727AG**	**NSYPLSC2727AG**	-
270	360	180	**NSYPLS2736G**	**NSYPLSC2736G**	**NSYPLSP2736G**
270	360	230	**NSYPLS2736AG**	**NSYPLSC2736AG**	-
270	540	180	**NSYPLS2754G**	**NSYPLSC2754G**	**NSYPLSP2754G**
270	540	230	**NSYPLS2754AG**	**NSYPLSC2754AG**	-
360	270	180	-	-	-
360	270	180	-	-	-
360	360	180	**NSYPLS3636G**	**NSYPLSC3636G**	**NSYPLSP3636G**
360	540	180	**NSYPLS3654G**	**NSYPLSC3654G**	**NSYPLSP3654G**
360	540	230	**NSYPLS3654AG**	**NSYPLSC3654AG**	-
360	720	230	**NSYPLS3672AG**	**NSYPLSC3672AG**	-
540	270	180	-	-	-
540	540	180	**NSYPLS5454G**	**NSYPLSC5454G**	**NSYPLSP5454G**
540	540	230	**NSYPLS5454AG**	**NSYPLSC5454AG**	-
540	720	230	**NSYPLS5472AG**	**NSYPLSC5472AG**	-

Rear | **Low covers: 45 mm**




Dimensions (mm)			Rear 135 mm	Transparent	Polycarbonate	Polyester
Height	Width	Depth				
180	270	180	**NSYFPLS1827G**	**NSYTPLS1827**	**NSYTPLSC1827G**	-
270	270	180	**NSYFPLS2727G**	**NSYTPLS2727**	**NSYTPLSC2727G**	**NSYTPLSP2727G**
270	270	230	**NSYFPLS2727G**	-	-	-
270	360	180	**NSYFPLS2736G**	**NSYTPLS2736**	**NSYTPLSC2736G**	-
270	360	230	**NSYFPLS2736G**	-	-	-
270	540	180	**NSYFPLS2754G**	**NSYTPLS2754**	**NSYTPLSC2754G**	**NSYTPLSP2754G**
270	540	230	**NSYFPLS2754G**	-	-	-
360	360	180	**NSYFPLS3636G**	**NSYTPLS3636**	**NSYTPLSC3636G**	-
360	540	180	**NSYFPLS3654G**	**NSYTPLS3654**	**NSYTPLSC3654G**	**NSYTPLSP3654G**
360	540	230	**NSYFPLS3654G**	-	-	-
360	720	230	**NSYFPLS3672G**	-	-	-
540	540	180	**NSYFPLS5454G**	**NSYTPLS5454**	**NSYTPLSC5454G**	-
540	540	230	**NSYFPLS5454G**	-	-	-
540	720	230	**NSYFPLS5472G**	-	-	-

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLS: Modular Boxes

Selection Table

	Insulated modular boxes with modular distribution chassis			Modular distribution chassis			
				 NSYDLS12			
	Number of 18 mm modules	Number of rows	Approximate weight (kg)	References	Dimensions (mm)		
					Height	Width	Depth
	12	1	1.7	**NSYDLS12**	180	270	180
	24	2	2.5	**NSYDLS24**	270	270	180
	-	-	-	-	270	270	230
	-	-	-	-	270	360	180
	-	-	-	-	270	360	230
	-	-	-	-	270	540	180
	-	-	-	-	270	540	230
	24	2	2.7	**NSYDLS242**	360	270	180
	36	3	2.8	**NSYDLS36**	360	270	180
	-	-	-	-	360	360	180
	-	-	-	-	360	540	180
	-	-	-	-	360	540	230
	-	-	-	-	360	720	230
	-	4	3.8	**NSYDLS48**	540	270	180
	48	-	-	-	540	540	180
	-	-	-	-	540	540	230
	-	-	-	-	540	720	230

	High covers: 95 mm		Metal mounting plates		Insulated mounting plates			
	 NSYTPLS2736A	 NSYTPLSC2727AG	 PB500072_11_2_nb	 PB500102_15_2_nb	 NSYPMA1827G			
	Transparent	Opaque	Plain	Telequick	Polyester	Dimensions (mm)		
						Height	Width	Depth
	-	-	**NSYPMM1827**	**NSYPMR1827**	**NSYPMA1827G**	180	270	180
	-	-	**NSYPMM2727**	**NSYPMR2727**	**NSYPMA2727G**	270	270	180
	NSYTPLS2727A	**NSYTPLSC2727AG**	**NSYPMM2727**	**NSYPMR2727**	**NSYPMA2727G**	270	270	230
	-	-	**NSYPMM2736**	**NSYPMR2736**	**NSYPMA2736G**	270	360	180
	NSYTPLS2736A	**NSYTPLSC2736AG**	**NSYPMM2736**	**NSYPMR2736**	**NSYPMA2736G**	270	360	230
	-	-	**NSYPMM2754**	**NSYPMR2754**	**NSYPMA2754G**	270	540	180
	NSYTPLS2754A	**NSYTPLSC2754AG**	**NSYPMM2754**	**NSYPMR2754**	**NSYPMA2754G**	270	540	230
	-	-	**NSYPMM3636**	-	**NSYPMA3636G**	360	360	180
	-	-	**NSYPMM3654**	**NSYPMR3654**	**NSYPMA3654G**	360	540	180
	NSYTPLS3654A	**NSYTPLSC3654AG**	**NSYPMM3654**	**NSYPMR3654**	**NSYPMA3654G**	360	540	230
	NSYTPLS3672A	**NSYTPLSC3672AG**	**NSYPMM3672**	-	**NSYPMA3672G**	360	720	230
	-	-	**NSYPMM5454**	-	**NSYPMA5454G**	540	540	180
	NSYTPLS5454A	**NSYTPLSC5454AG**	**NSYPMM5454**	-	**NSYPMA5454G**	540	540	230
	NSYTPLS5472A	**NSYTPLSC5472AG**	**NSYPMM5472**	-	**NSYPMA5472G**	540	720	230

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLS: Modular Boxes

Accessories




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Side plates

See details p. 462

2



Coupling frames

See details p. 463

3



Box coupling unit piece

See details p. 465

Fixing and Lifting Accessories

4



Wall fixing lugs

See details p. 477

5



Plastic carrying handle

See details p. 482

Mounting Accessories

Door Accessories

6



Internal hinges

See details p. 555

7



External hinges

See details p. 555

8



Closing locks

See details p. 560

9



Locking screws

See details p. 564

> For more information consult the Accessories chapter **page 456**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLS: Modular Boxes


Dimensions


The Surfaces Are Numbered to Enable Identification of the Surfaces to Be Drilled in the Customized Offer

NSYPLS●●●1827G




NSYPLS●●●3654●G






A - B: Internal view of the corners of the polyester covers with bosses for inserts ref. **NSYTEX5** for M5 screws.


NSYPLS●●●2727●G




NSYPLS●●●5454●G




NSYPLS●●●2736●G




NSYPLS●●●3672●G




NSYPLS●●●3636G



NSYPLS●●●5472●G



NSYPLS●●●2754●G




* Thickness of 30/10e mm for the polyester cover.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

3

Examples of Assembly

All the boxes can be joined by their lateral surfaces using the coupling frames **NSYUM●●●** or **NSYUCC●●●**, and the joining and fixing pieces **NSYPS2C27** and **NSYPS4C27**.





Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Insulated Enclosures

Insulated Wall-Mounted Enclosures

Panel**SeT** PLM

PB504038



NSYPLM54TG_image



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLM

Introduction	**146**
Characteristics	**148**
Selection Table	**150**
Accessories	**152**
Dimensions	**154**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLM

Introduction



The fiberglass reinforced polyester wall-mounted enclosure is suitable for both indoor and outdoor installations, especially in harsh environments. It can withstand extreme temperatures and offers high electrical insulation. Additionally, it is highly resistant to fire, vandalism, and corrosion.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Note:
Prolonged exposure to UV radiation, wind and rain can cause aesthetics changes in the external surface of the enclosure without affecting the technical properties according to IEC 62208. For long-term aesthetics requirements, it is recommended to use painted enclosures available through our customization offer.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



New

Recycled Material Content

- Made of polyester with 37% of post-industrial recycled material content
- Use of recycled packaging



Easy Installation

- Door easily reversible by turning it over
- Opening to 120° or 180°
- Easy machining with no corrosion
- Lightness
- Polyamide hinge pin, easily removable and captive



Smart Interior

- Notches for easy fixing of DIN rails
- Grid pattern on the rear of the door for marking the machining operations



Service Life

- High resistance to corrosion in harsh environments, maintaining mechanical properties and insulation



Landscape Option

- Horizontal enclosures for photovoltaic and multiple applications
- Easily and quickly removable door system (without removing hinges and pins)
- For more details see page 149

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Wall-Mounted Enclosures

Panel**SeT** PLM

Characteristics

Characteristics	ABS/PC wall-mounted enclosures	Polyester wall-mounted enclosures		
According to Reach and RoHs and Halogen-free Class II				
	• Monobloc wall-mounted enclosure. • Version with transparent polycarbonate door. • Door opening: 180°. • Supplied with a lock with double-bar insert as standard • For harsh environments without UV exposure	• Monobloc wall-mounted enclosure. • Version with transparent tempered-glass door. • Door opening angle: 120°. • Grid pattern with a pitch of 50 mm on the back of the door. • Supplied with one lock with a double-bar insert as standard.	• Monobloc wall-mounted enclosure. • Version with transparent tempered-glass door. • Locking device outside the sealed area for long-term tightness according to IP66. • Locking system: enclosure height ≤ 847 mm: 2 locks with double-bar insert ref. **NSYCDBPLM** or 1 handle with key lock and 3-point locking system, • Enclosure height 1056 mm: 1 lock with double-bar insert and 4-point locking system ref. **NSYVPLM108**. • Door opening angle: 180°. • Bosses for accessory-fixing inserts: M6 inside the enclosure, M5 in the door for enclosure heights of 430 and 530 mm, M6 in the door for enclosure heights ≥ 647 mm. • Grid pattern with a pitch of 25 mm on the back of the door.	
Material	ABS/PC	Polyester reinforced with fiberglass, molded by hot compression		
Temperature range - Gasket	-40 °C to +80 °C			
Color	RAL 7035 gray			
Ingress protection rating	IP66 according to IEC 60529			
Mechanical protection rating	• IK10 plain door • IK08 glazed door			
Certifications (see page 594)	• IEC 62208 • Bureau Veritas Marine	• IEC 62208 • Marine • UL (cULus). Rating according to UL50E: 1, 2, 3, 3R, 4, 4X, 5, 12 and 13. • Certifications exclude range NSYPLM...VG or TVG		• IEC 62208 • Marine
Installation	• Direct fixing of symmetrical rails ref. **NSYCS200PLM** with plastic nuts ref. **NSYTCSPLM**, to be installed in the notches on the rear of the body, with a pitch of 25 mm • Fixing of installation plates on the studs at the rear of the enclosure	• Fixing of rear accessories on 4 M8 x 18 studs	• Fixing of rear accessories on 4 M8 studs, included in the standard supply • Direct fixing of symmetrical rails ref. **NSYCS●●●PLM**, with plastic nuts, ref. NSYTCSPLM, to be installed in the notches on the rear of the body, with a pitch of 25 mm	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLM Landscape


Horizontal wall-mounted enclosures designed for photovoltaic and multiple outdoor applications installed in harsh environments

General Characteristics

- Wall-mounted enclosures made of fiberglass reinforced polyester molded by hot compression.
- Monobloc body with polyurethane gasket.
- Wider sizes with more space available in the bottom of the enclosure to install additional cable entries.
- Impact resistance IK10, IEC 62262.
- Protection degree IP 66, IEC 60529.
- Class II insulation.
- Certifications: IEC 62208 and UL 508A - NEMA type: 1, 2, 3, 3R, 3S, 4, 4X, 5, 12 and 13.
- Reach and RoHs compliance.
- Color: RAL 7035.


Removable Door System

- Removable door system that allows:
  - Enhanced access to the internal part of the enclosure.
  - Easy and quick assembly/disassembly of the door (without dismounting the hinges and removing the pin).



Self-Adhesive and Fixable Canopy

- Self-adhesive canopy made of PVC available as an accessory - black RAL 9005 Color.
- For outdoor use, the canopy must be installed to protect the door gasket against water stagnation.



Wall Fixing Lugs

- Set of 4 wall fixing lugs (plastic or stainless-steel) available as an accessory.
- Quick and easy assembly through the inserts, without drilling the enclosure. IP66 guaranteed.



For more information, on the **related accessories** check **page 478**.

Landscape Enclosures - RAL 7035



NSYPLM68G

Characteristics	Height (mm)	Width (mm)	Depth (mm)	Number of locks	References
Landscape enclosures. RAL 7035	536	747	300	2	**NSYPLM57G**
Landscape enclosures. RAL 7035	636	847	300	2	**NSYPLM68G**
Landscape enclosures. RAL 7035	852	1056	350	1	**NSYPLM810G**

Canopy



NSYCSA68

Characteristics	Dimensions (mm)	References
Self-adhesive and fixable canopy for landscape enclosure	536 x 747 x 300	**NSYCSA57**
Self-adhesive and fixable canopy for landscape enclosure	636 x 847 x 300	**NSYCSA68**
Self-adhesive and fixable canopy for landscape enclosure	852 x 1056 x 350	**NSYCSA810**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Wall-Mounted Enclosures

Panel**SeT** PLM

Selection Table

External dimensions (mm)			References of wall-mounted enclosures with door							
Height	Width	Depth	Plain (3)	Transparent (4)	Plain (3)	Transparent (4)	Plain (3)	Transparent (4)	Plain (1)	Transparent (1) (4)
308	255	160	-	-	**NSYPLM3025G**	**NSYPLM3025TG**	-	-	-	-
310	215	160	**NSYPLM32G**	**NSYPLM32TG**	-	-	-	-	-	-
430	330	200	-	-	-	-	**NSYPLM43G**	**NSYPLM43TG**	**NSYPLM43VG**	**NSYPLM43TVG**
530	430	200	-	-	-	-	**NSYPLM54G**	**NSYPLM54TG**	**NSYPLM54VG**	**NSYPLM54TVG**
647	436	250	-	-	-	-	**NSYPLM64G**	**NSYPLM64TG**	**NSYPLM64VG**	**NSYPLM64TVG**
747	536	300	-	-	-	-	**NSYPLM75G**	**NSYPLM75TG**	**NSYPLM75VG**	**NSYPLM75TVG**
847	636	300	-	-	-	-	**NSYPLM86G**	**NSYPLM86TG**	**NSYPLM86VG**	**NSYPLM86TVG**
1056	852	350	-	-	-	-	**NSYPLM108G** (2)	**NSYPLM108TG** (2)	-	-

(1) Wall-mounted enclosure with handle and lock with 3-point locking system and key 1242 E delivered as standard.
(2) Wall-mounted enclosure with standard 5-mm double-bar lock and lock with 4-point locking system.
(3) These enclosures are also available equipped with metal or insulated mounted plates.
(4) Must be protected against UV radiation.

Comment:
NSYPLMRS108GA is also certified by UL (cULus).

Comment:
For dimensions see page 154

			ABS/PC wall-mounted enclosures with door		Polyester wall-mounted enclosures with door	
						
External dimensions (mm)						
Height	Width	Depth	Plain (3)	Transparent (4)	Plain (3)	Transparent (4)
310	215	160	**NSYPLM32G**	**NSYPLM32TG**	-	-
308	255	160	-	-	**NSYPLM3025G**	**NSYPLM3025TG**

Comment:
For dimensions see page 155

			Polyester wall-mounted enclosures with door			
			 	 		
External dimensions (mm)						
Height	Width	Depth	Plain (3)	Transparent (4)	Plain (1)	Transparent (1)(4)
430	330	200	**NSYPLM43G**	**NSYPLM43TG**	**NSYPLM43VG**	**NSYPLM43TVG**
530	430	200	**NSYPLM54G**	**NSYPLM54TG**	**NSYPLM54VG**	**NSYPLM54TVG**
647	436	250	**NSYPLM64G**	**NSYPLM64TG**	**NSYPLM64VG**	**NSYPLM64TVG**
747	536	300	**NSYPLM75G**	**NSYPLM75TG**	**NSYPLM75VG**	**NSYPLM75TVG**
847	636	300	**NSYPLM86G**	**NSYPLM86TG**	**NSYPLM86VG**	**NSYPLM86TVG**
1056	852	350	**NSYPLM108G** (2)	**NSYPLM108TG** (2)	-	-

(1) Wall-mounted enclosure with handle and lock with 3-point locking system and key 1242 E delivered as standard.
(2) Wall-mounted enclosure with standard 5-mm double-bar lock and lock with 4-point locking system.
(3) These enclosures are also available equipped with metal or insulated mounted plates.
(4) Must be protected against UV radiation.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Wall-Mounted Enclosures


PanelSeT PLM

Selection Table

Comment:
For dimensions see page 155

External dimensions (mm)			ABS/PC wall-mounted enclosures with door		Polyester wall-mounted enclosures with door	
						
Height	Width	Depth	Plain	Bakelite	Plain	Bakelite
310	215	160	**NSYPLM32PG**	**NSYPLM32BG**	-	-
308	255	160	-	-	**NSYPLM3025PG**	**NSYPLM3025BG**


Comment:
For dimensions see page 155

External dimensions (mm)			Wall-mounted enclosures with plain door and mounting plate (not mounted)	
				
Height	Width	Depth	Plain	Bakelite
430	330	200	**NSYPLM43PG**	**NSYPLM43BG**
530	430	200	**NSYPLM54PG**	**NSYPLM54BG**
647	436	250	**NSYPLM64PG**	**NSYPLM64BG**
747	536	300	**NSYPLM75PG**	**NSYPLM75BG**
847	636	300	**NSYPLM86PG**	**NSYPLM86BG**
1056	852	350	-	**NSYPLM108BG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLM

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1 
Plinths and feet for buried installation
See details p. 472

2 
Floor mounted pillar
See details p. 466

3 
Support bracket
See details p. 466

4 
Airing louvres
See details p. 476

5 
Water drain plug
See details p. 476

6 
Blanking plates
See details p. 476

Fixing and Lifting Accessories

7 
Wall fixing lugs
See details p. 478

8 
Post fixing device
See details p. 480

Mounting Accessories

Equipment Assembly Accessories

9 
Mounting plate
See details p. 509

10 
Rails and plastic nuts for rails
See details p. 529

11 
Step slides
See details p. 522

12 
Fixing inserts
See details p. 541

Electric distribution Accessories

13 
Modular chassis and panels for chassis
See details p. 544

Door Accessories

14 
Internal doors
See details p. 551

15 
Inserts, keys, locks, padlocks and handles
See details p. 560


> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Panel**SeT** PLM

Dimensions

ABS/PC Wall-Mounted Enclosures




Polyester Wall-Mounted Enclosures 308 x 255 mm



Note: This model is available with only one lock!

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Other Polyester Wall-Mounted Enclosures



External fixing with lugs (mm)				
Vertical		Horizontal		
X	Y	X'	Y'	References
490	225	355	360	**NSYPLM43G**
590	325	455	460	**NSYPLM54G**
690	330	555	465	**NSYPLM64G**
790	430	655	565	**NSYPLM75G**
890	530	755	665	**NSYPLM86G**
1090	750	955	885	**NSYPLM108G**

Glazed door opening (mm)		
U	V	References
273	194	**NSYPLM43TG**
273	151	**NSYPLM43TVG**
373	294	**NSYPLM54TG**
373	251	**NSYPLM54TVG**
463	294	**NSYPLM64TG**
463	252	**NSYPLM64TVG**
563	394	**NSYPLM75TG**
563	352	**NSYPLM75TVG**
663	494	**NSYPLM86TG**
663	452	**NSYPLM86TVG**
854	661	**NSYPLM108TG**

Dimensions (mm)										Bottom screw and door bosses (mm)		Internal fixing (mm)			
A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	References
430	330	200	380	260	181	247	150	179	168	325	225	375	150	13	**NSYPLM43G**
530	430	200	480	360	181	347	150	279	168	425	325	475	250	13	**NSYPLM54G**
647	436	250	580	360	228	388	192	279	212	525	325	575	250	13	**NSYPLM64G**
747	536	300	680	460	278	487	241	379	261	625	425	675	350	15	**NSYPLM75G**
847	636	300	780	560	278	587	241	479	261	725	525	775	450	15	**NSYPLM86G**
1056	852	350	980	760	327	775	280	680	300	925	725	975	650	15	**NSYPLM108G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Insulated Enclosures

Insulated Floor-Standing Enclosures

Panel**SeT** PLA Version




Panel**SeT** PLAT Version



Panel**SeT** PLAZ Version



Panel**SeT** PLAZT Version



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLA

Introduction	**158**
Characteristics	**160**
Selection Table	**162**
Accessories	**164**
Dimensions	**166**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLA

Introduction



The PanelSeT PLA is a range of fiberglass-reinforced polyester floor-standing enclosures, ideal for outdoor installations, harsh environments, and public areas. It features class II electrical insulation and offers exceptional resistance to fire, vandalism, and corrosion.

It is available in a variety of versions to meet different needs:
- PLA version: Completely sealed enclosure
- PLAT version: Enclosure with a ventilated canopy
- PLAZ version: Enclosure with an open bottom
- PLAZT version: Enclosure with an open bottom and a ventilated canopy.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Note:
Prolonged exposure to UV radiation, wind and rain can cause aesthetics changes in the external surface of the enclosure without affecting the technical properties according to IEC 62208. For long-term aesthetics requirements, it is recommended to use painted enclosures available through our customization offer.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PLAT version



Airing
- Open top with canopy allowing passive airing

PLAZ version



Open Bottom
- Open bottom to be mounted directly on the floor or on a plinth

PLAZT version



Easy Installation
- Door opening to 180°
- Ventilated canopy and open bottom



Easy Mounting
- Various bosses for M8 inserts



Smart Interior
- Plain mounting plate installed on step slides and compulsory adapter plates in all the enclosures with open bottom part



Resistant
- Anti-lever security system



Wide offer
- More than 200 options available as standard

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLA, PLAT

Characteristics

Characteristics	PLA version	PLAT version
Class II		
	Sealed enclosure Enclosure obtained by assembling: • 1 sealed top part, • 1 sealed bottom part, • 2 side parts, • 1 or 2 rear panels (depending on width), • 1 or 2 doors (depending on width). • Locking system with handle with a 5-mm double-bar insert block, included in the standard supply. Other blocks with inserts or barrels and keys optionally available. • Door opening to 120°.	Enclosure with ventilated canopy Enclosure obtained by assembling: • 1 open top part with canopy, • 1 sealed bottom part, • 2 side parts, • 1 or 2 rear panels (depending on width), • 1 or 2 doors (depending on width). • Locking system with handle with a 5-mm double-bar insert block, included in the standard supply. Other blocks with inserts or barrels and keys optionally available. • Door opening to 120°.
Material	Polyester reinforced with fiberglass	
Finish	• Molded by hot compression: the pieces have an excellent finish on both sides and can include numerous bosses for accommodating inserts and mounting or cable management accessories	
Color	• RAL 7035 gray	
Ingress protection rating	IP65 according to IEC 60529	• IP44 according to IEC 60529 • IP54 with 1 or 2 internal grilles, ref. **NSYCAG125LPF**, to be ordered separately.
Mechanical protection rating	IK10 (20 joules) plain door - IEC62262 and IK08 glazed door	
Insulation	• Class II according to IEC 60950-1 if the mounting process follows the included mounting instructions sheet	
Certifications	• UL (cULus). • Single door: NEMA types 1, 2, 3, 3X, 3R, 3RX, 3S, 3SX, 5, 12 and 13 • Double door: NEMA types 1, 2, 3R, 3RX, 5, 12 and 13 • Bureau Veritas Marine • IEC 62208	• IEC 62208
Installation	• Indoor use, for outdoor use canopy • Direct fixing to the floor or by means of a plinth with a height of 60 mm, as an option, see page 473 • Option of fixing on a semi-embedded plinth, see page 473 • Optional wall fixing lugs • The versions with glassed door must be protected against the direct sunlight to avoid overheating.	• Outdoor or indoor installation
Options	• Anti-posting door upon request	

Note:
For more information on harsh environments see our PHD offer in the Specific Applications chapter on page 168.

NOTICE

ENCLOSURE PROTECTION

■ Outdoor use requires the installation of a canopy.

■ Glazed door enclosures must be protected against the direct sunlight to avoid overheating.

Failure to follow these instructions can result in equipment damage.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Floor-Standing Enclosures
PanelSeT PLAZ, PLAZT
Characteristics

Characteristics	PLAZ version	PLAZT version
Class II		
	Enclosure with open bottom Enclosure obtained by assembling: • 1 sealed top part, • 1 plinth-type open bottom part, • 2 side parts, • 1 or 2 rear panels (depending on width), • 1 or 2 doors (depending on width). • Locking system with handle with a 5-mm double-bar insert block, included in the standard supply. Other blocks with inserts or barrels and keys optionally available. • Door opening to 120°.	Enclosure with open bottom and ventilated canopy Enclosure obtained by assembling: • 1 open top part with canopy, • 1 plinth-type open bottom part, • 2 side parts, • 1 or 2 rear panels (depending on width), • 1 or 2 doors (depending on width). • Locking system with handle with a 5-mm double-bar insert block. Other blocks with inserts or barrels and keys optionally available. • Door opening to 180°. • Anti-lever system to reduce the risk of forcing the door open.
Material	Polyester reinforced with fiberglass	
Finish	• Molded by hot compression: the pieces have an excellent finish on both sides and can include numerous bosses for accommodating inserts and mounting or cable management accessories	
Color	• RAL 7035 gray	
Ingress protection rating	• IP54 according to IEC 60529	• IP44 according to IEC 60529 • IP54 with 1 or 2 internal grilles, ref. **NSYCAG125LPF**, to be ordered separately
Mechanical protection rating	IK10 (20 joules) plain door - IEC62262 and IK08 glazed door	
Insulation	• Class II according to IEC 60950-1 if the mounting process follows the included mounting instructions sheet	
Certifications	• IEC 62208	
Installation	• Indoor use, for outdoor use canopy • The open bottom part forms a 60 mm plinth which is fixed to the floor directly or by means of an optional fixing frame, see page 473, or else it is installed on a semi-embedded plinth, see page 473 • The versions with glassed door must be protected against the direct sunlight to avoid overheating.	• Outdoor or indoor installation
Options	• Anti-posting door upon request	

Note:
For more information on harsh environments see our PHD offer in the Specific Applications chapter on page 168.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Floor-Standing Enclosures

Panel**SeT** PLA, PLAZ

Selection Table

Completely sealed enclosures, IP65						Enclosures with open bottom part, IP54
						
Dimensions (mm)						
Height	Width	Depth	N° of doors	Plain	Glazed**	Plain
500	500	320	1	**NSYPLA553G**	**NSYPLA553TG**	**NSYPLAZ553G**
500	500	420	1	**NSYPLA554G**	**NSYPLA554TG**	**NSYPLAZ554G**
500	750	320	1	**NSYPLA573G**	**NSYPLA573TG**	**NSYPLAZ573G**
500	750	420	1	**NSYPLA574G**	**NSYPLA574TG**	**NSYPLAZ574G**
500	1000	320	2	**NSYPLA5103G**	-	-
500	1000	420	2	**NSYPLA5104G**	-	-
500	1250	320	2	**NSYPLA5123G**	-	-
500	1250	420	2	**NSYPLA5124G**	-	-
750	500	320	1	**NSYPLA753G**	**NSYPLA753TG**	**NSYPLAZ753G**
750	500	420	1	**NSYPLA754G**	**NSYPLA754TG**	**NSYPLAZ754G**
750	750	320	1	**NSYPLA773G**	**NSYPLA773TG**	**NSYPLAZ773G**
750	750	420	1	**NSYPLA774G**	**NSYPLA774TG**	**NSYPLAZ774G**
750	750	620	1	**NSYPLA776G**	**NSYPLA776TG**	**NSYPLAZ776G**
750	1000	320	2	**NSYPLA7103G**	**NSYPLA7103TG**	**NSYPLAZ7103G**
750	1000	420	2	**NSYPLA7104G**	**NSYPLA7104TG**	**NSYPLAZ7104G**
750	1250	320	2	**NSYPLA7123G**	**NSYPLA7123TG**	**NSYPLAZ7123G**
750	1250	420	2	**NSYPLA7124G**	**NSYPLA7124TG**	**NSYPLAZ7124G**
1000	500	320	1	**NSYPLA1053G**	**NSYPLA1053TG**	**NSYPLAZ1053G**
1000	500	420	1	**NSYPLA1054G**	**NSYPLA1054TG**	**NSYPLAZ1054G**
1000	750	320	1	**NSYPLA1073G**	**NSYPLA1073TG**	**NSYPLAZ1073G**
1000	750	420	1	**NSYPLA1074G**	**NSYPLA1074TG**	**NSYPLAZ1074G**
1000	1000	320	2	**NSYPLA10103G**	**NSYPLA10103TG**	**NSYPLAZ10103G**
1000	1000	420	2	**NSYPLA10104G**	**NSYPLA10104TG**	**NSYPLAZ10104G**
1000	1250	320	2	**NSYPLA10123G**	**NSYPLA10123TG**	**NSYPLAZ10123G**
1000	1250	420	2	**NSYPLA10124G**	**NSYPLA10124TG**	**NSYPLAZ10124G**
1250	500	320	1	**NSYPLA1253G**	**NSYPLA1253TG**	**NSYPLAZ1253G**
1250	500	420	1	**NSYPLA1254G**	**NSYPLA1254TG**	**NSYPLAZ1254G**
1250	750	320	1	**NSYPLA1273G**	**NSYPLA1273TG**	**NSYPLAZ1273G**
1250	750	420	1	**NSYPLA1274G**	**NSYPLA1274TG**	**NSYPLAZ1274G**
1250	750	620	1	**NSYPLA1276G**	**NSYPLA1276TG**	**NSYPLAZ1276G**
1250	1000	320	2	**NSYPLA12103G**	**NSYPLA12103TG**	**NSYPLAZ12103G**
1250	1000	420	2	**NSYPLA12104G**	**NSYPLA12104TG**	**NSYPLAZ12104G**
1250	1250	320	2	**NSYPLA12123G**	**NSYPLA12123TG**	**NSYPLAZ12123G**
1250	1250	420	2	**NSYPLA12124G**	**NSYPLA12124TG**	**NSYPLAZ12124G**
1250	1250	620	2	**NSYPLA12126G**	**NSYPLA12126TG**	**NSYPLAZ12126G**
1500	500	320	1	**NSYPLA1553G**	**NSYPLA1553TG**	**NSYPLAZ1553G**
1500	500	420	1	**NSYPLA1554G**	**NSYPLA1554TG**	**NSYPLAZ1554G**
1500	750	320	1	**NSYPLA1573G**	**NSYPLA1573TG**	**NSYPLAZ1573G**
1500	750	420	1	**NSYPLA1574G**	**NSYPLA1574TG**	**NSYPLAZ1574G**
1500	750	620	1	**NSYPLA1576G**	**NSYPLA1576TG**	**NSYPLAZ1576G**
1500	1000	320	2	**NSYPLA15103G**	**NSYPLA15103TG**	**NSYPLAZ15103G**
1500	1000	420	2	**NSYPLA15104G**	**NSYPLA15104TG**	**NSYPLAZ15104G**
1500	1250	320	2	**NSYPLA15123G**	**NSYPLA15123TG**	**NSYPLAZ15123G**
1500	1250	420	2	**NSYPLA15124G**	**NSYPLA15124TG**	**NSYPLAZ15124G**
1500	1250	620	2	**NSYPLA15126G**	**NSYPLA15126TG**	**NSYPLAZ15126G**
2000	750	420	2*	**NSYPLA2074G**	**NSYPLA2074TG**	**NSYPLAZ2074G**

*Two doors in vertical.

**Recommended to protect against the direct UV radiation.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Floor-Standing Enclosures
Panel**SeT** PLAT, PLAZT
Selection Table


				Enclosures with ventilated canopy, IP44	Enclosures with open bottom part and ventilated canopy, IP44
				 PB503702_nb	 PB503703_nb
Dimensions (mm)					
Height	Width	Depth	N° of doors	Plain	Plain
500	500	320	1	**NSYPLAT553G**	**NSYPLAZT553G**
500	500	420	1	**NSYPLAT554G**	**NSYPLAZT554G**
500	750	320	1	**NSYPLAT573G**	**NSYPLAZT573G**
500	750	420	1	**NSYPLAT574G**	**NSYPLAZT574G**
500	1000	320	2	-	-
500	1000	420	2	-	-
500	1250	320	2	-	-
500	1250	420	2	-	-
750	500	320	1	**NSYPLAT753G**	**NSYPLAZT753G**
750	500	420	1	**NSYPLAT754G**	**NSYPLAZT754G**
750	750	320	1	**NSYPLAT773G**	**NSYPLAZT773G**
750	750	420	1	**NSYPLAT774G**	**NSYPLAZT774G**
750	750	620	1	**NSYPLAT776G**	**NSYPLAZT776G**
750	1000	320	2	**NSYPLAT7103G**	**NSYPLAZT7103G**
750	1000	420	2	**NSYPLAT7104G**	**NSYPLAZT7104G**
750	1250	320	2	**NSYPLAT7123G**	**NSYPLAZT7123G**
750	1250	420	2	**NSYPLAT7124G**	**NSYPLAZT7124G**
1000	500	320	1	**NSYPLAT1053G**	**NSYPLAZT1053G**
1000	500	420	1	**NSYPLAT1054G**	**NSYPLAZT1054G**
1000	750	320	1	**NSYPLAT1073G**	**NSYPLAZT1073G**
1000	750	420	1	**NSYPLAT1074G**	**NSYPLAZT1074G**
1000	1000	320	2	**NSYPLAT10103G**	**NSYPLAZT10103G**
1000	1000	420	2	**NSYPLAT10104G**	**NSYPLAZT10104G**
1000	1250	320	2	**NSYPLAT10123G**	**NSYPLAZT10123G**
1000	1250	420	2	**NSYPLAT10124G**	**NSYPLAZT10124G**
1250	500	320	1	**NSYPLAT1253G**	**NSYPLAZT1253G**
1250	500	420	1	**NSYPLAT1254G**	**NSYPLAZT1254G**
1250	750	320	1	**NSYPLAT1273G**	**NSYPLAZT1273G**
1250	750	420	1	**NSYPLAT1274G**	**NSYPLAZT1274G**
1250	750	620	1	**NSYPLAT1276G**	**NSYPLAZT1276G**
1250	1000	320	2	**NSYPLAT12103G**	**NSYPLAZT12103G**
1250	1000	420	2	**NSYPLAT12104G**	**NSYPLAZT12104G**
1250	1250	320	2	**NSYPLAT12123G**	**NSYPLAZT12123G**
1250	1250	420	2	**NSYPLAT12124G**	**NSYPLAZT12124G**
1250	1250	620	2	**NSYPLAT12126G**	**NSYPLAZT12126G**
1500	500	320	1	**NSYPLAT1553G**	**NSYPLAZT1553G**
1500	500	420	1	**NSYPLAT1554G**	**NSYPLAZT1554G**
1500	750	320	1	**NSYPLAT1573G**	**NSYPLAZT1573G**
1500	750	420	1	**NSYPLAT1574G**	**NSYPLAZT1574G**
1500	750	620	1	**NSYPLAT1576G**	**NSYPLAZT1576G**
1500	1000	320	2	**NSYPLAT15103G**	**NSYPLAZT15103G**
1500	1000	420	2	**NSYPLAT15104G**	**NSYPLAZT15104G**
1500	1250	320	2	**NSYPLAT15123G**	**NSYPLAZT15123G**
1500	1250	420	2	**NSYPLAT15124G**	**NSYPLAZT15124G**
1500	1250	620	2	**NSYPLAT15126G**	**NSYPLAZT15126G**
2000	750	420	2*	**NSYPLAT2074G**	**NSYPLAZT2074G**

*Two doors in vertical.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PLA

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1 Canopy



See details p. 460

2 Coupling kit



See details p. 464

3 Plinth and plinth accessories



See details p. 473


4 Feet for buried Installation



See details p. 475

Fixing and Lifting Accessories

5 Wall fixing lug



See details p. 478

Cable Management Accessories

Cable Entry Accessories

6 PLAZ PLATZ Cable entry plate



See details p. 503

Mounting Accessories

Equipment assembly Accessories

7 Mounting plate



See details p. 513

8 Step slides, plates and additional supports



See details p. 522

9 Intermediate support in two floor enclosures



See details p. 536

10 Inserts



See details p. 541

Electric distribution Accessories

11 Chassis



See details p. 544


Door Accessories

12 Internal door



See details p. 551

13 Inserts, keys, locks and handles



See details p. 562

14 Door switch



See details p. 569

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Insulated Floor-Standing Enclosures


Panel**SeT** PLA, PLAT, PHD


Dimensions

Sealed Enclosure or Enclosure with Ventilated Canopy

For enclosures without canopy, please just disregard the related 38 mm.









1. 4 bosses with M8 inserts and studs for direct fixing of mounting plates.
2. Bosses designed to accommodate M8 inserts, ref. **NSYTEX8**. They are placed:
   – On the back of the enclosure, from the height of 1000 mm. They allow the fixing of partial mounting plates and assorted equipment.
   – On the top and bottom parts of the enclosure. They are used for fixing the step slides, an internal door, 19” chassis, etc.
3. Dimensions for fixing on the floor or on a plinth.
4. Entry dimensions, door open.
5. Dimension of 28 mm for enclosures with heights of more than 1000 mm (height after the installation of the plain mounting plates with reinforcement foldings).
6. With a width of 1250 mm in standard supply, 500 mm door on the left and 750 mm door on the right.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Enclosures with Open Bottom - Plinth Type with or without Ventilated Canopy

For enclosures without canopy, please disregard the corresponding 38 mm.







1. 4 bosses with M8 inserts and studs for direct fixing of mounting plates.
2. Bosses designed to accommodate M8 inserts, ref. **NSYTEX8**. They are placed:
   – On the back of the enclosure, from the height of 1000 mm. They allow the fixing of partial mounting plates and assorted equipment.
   – On the top and bottom parts of the enclosure. They are used for fixing the step slides, an internal door, 19” chassis, etc.
3. Dimensions for fixing on the floor or on a plinth.
4. Entry dimensions, door open.
5. Dimension of 28 mm for enclosures with heights of more than 1000 mm (height after the installation of the plain mounting plates with reinforcement foldings).
6. With a width of 1250 mm in standard supply, 500 mm door on the left and 750 mm door on the right.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications Enclosures

Low-Voltage Switchboard Systems

Image 08



Image 09



Nuclear Environments



Network and Server



Human Machine Interface



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Content

Low-Voltage Switchboard Systems	170
Human Machine Interface	256
Network and Server	286
Severe Outdoor	320
Seismic and Nuclear Ready Environments	334
Explosive Atmospheres	362
Electro Magnetic Compatibility	374
Variable-Speed Drive Flush-Mounting Kit	382
Enclosure Interlock	386

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Low-Voltage Switchboard Systems

Prisma**SeT** HD: Functional System

Image 08



Panel**SeT** SFN-SM: Steel Floor-Standing Enclosures



Panel**SeT** PLA: Polyester Floor-Standing Enclosures



Panel**SeT** S3DM-S3DB: Steel Wall-Mounted Enclosures



Panel**SeT** SFN MCC: Compartmentalized Enclosures

Image 09



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Choosing the right Low-Voltage System	172
Internal Separation Forms and their usage	174
Schneider Electric Device Ecosystem	176

Prisma**SeT** HD - High-Power Functional System

Introduction	182
Busbar Selection	186
Partitioning	194
Cubicle Selection	197
Accessories	198
Dimensions	199

Panel**SeT** SFN/SM: Steel Enclosures for Power Control Center (PCC)

Introduction	202
Accessories for Modular Floor-Standing Enclosures	204
Accessories for Low Voltage Switchboards	210
IEC 61439-2 Certification	224

Panel**SeT** PLA: Polyester Enclosures for EV Charging Stations

IEC 61439-2 Certification	224

Panel**SeT** S3DM/S3DB: Wall-Mounting Enclosures for Sub-Distribution

Introduction	226
Characteristics	228
Dimensions	228

Panel**SeT** SFN MCC: Compartmentalized Enclosures for Motor Control Centers (MCCs)

Introduction	230
Characteristics	232
Selection Tables of Functional Units	236
Selection Tables of Busbar	244
Selection Tables for Enclosure Partitioning	249
Accessories	254

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Choosing the right Low-Voltage System

This chapter brings together Universal Enclosure's core low-voltage systems for power distribution and motor control. These ranges form a coherent portfolio engineered to help ensure consistent performance and reliability across electrical systems.
Each system plays a specific role within low-voltage distribution and control schemes, while sharing common values of performance, safety, modularity, and compliance with international standards such IEC61439-1 and 2.

Panel**SeT** SFN



Modular enclosures for low-voltage distribution with a wide selection of IEC 61439-2 certified dimensions ranging up to 4000A.

Prisma**SeT** HD



Type Tested System combining the robustness of Panel**SeT** SFN enclosure and the flexibility of Prisma**SeT** functional units up to 4000A (up to 6300A with Prisma**SeT** 6300).

Panel**SeT** SFN MCC



Compartmentalized enclosure for Motor Control Centers (MCC) up to 250kW and 4000A.

Panel**SeT** S3DB/S3DM



Sub-distribution panels for Electrical Distribution up to 63A.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Choosing the right Low-Voltage System






Enclosure	PanelSeT SFN/SM (ED)	PrismaSeT HD	PanelSeT SFN MCC	S3DB/S3DM
Primary use	Electrical Distribution	High-power electrical distribution	Motor control	Sub-distribution
Power range	Up to 4000 A	Up to 6300 A	Up to 4000 A	Up to 63A
Architecture type	Open, free layout. Universal system with cross rails and mounting plates	Type tested system with flexible functional units	Fix and Compartmentalized MCC	Modular system on Din-rail
Partitioning	Form 1	Up to form 4b	Up to form 4b (mandatory form 2b)	No forms
Safety level	High (IEC 61439-1 and 2 compliant)	Very high (functional units validated under IEC 61439-1 and 2)	Very high (IEC 61439-1 and 2 compliant and compartment isolation)	High (IP66 and IK10)
Modularity	Very flexible (mechanical freedom)	Structured modularity	Compartment/cell modularity	Modular assembly
Device integration	Compatible	Fully engineered and certified	Motor-starter certified specific	Compatible with standard devices
Digital readiness	Possible	Native (Panel Server, HeatTag)	Possible	Possible
When to choose it	Control Panel and Simple ED (no partitioning) or MCC (no compartmentalized)	Large Electrical Distribution Panels	Compartmentalized MCC	Standard sub-distribution

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Internal Separation Forms and their usage


Partitioning forms according to IEC 61439-2
Decisions concerning the form of separation, and the degree of protection are subject to a joint agreement between manufacturer and Customer.

Safety being one of its foremost goals, Schneider Electric offers options and features that go well beyond the recommendations of the standard.

The protection of life and property is a standard feature due to:
- Front plates that require a tool to be removed
- Keylock on doors providing Access to live parts
- The systematic installation of terminal shields on ComPacT NSX circuit breakers and ComPacT INS and INV switch-disconnectors
- Covering of the upstream and downstream terminals on the incoming device to support compliance with protection requirements and enhance operator safety when the incoming device is off (open).


What is more, our certified solutions offers different levels of partitioning to create separations inside the enclosures, thereby creating Form 2b, 3b, 4a and 4b electrical switchboards. Electrical switchboards must meet the IP2X degree of protection to comply with standard IEC 61439-2.

> Form 1




In most installations, enclosures does not require partitioning. In this case, the switchboard is a Form 1

> Form 2b



The partitioning separates busbars from:
- Terminals for external conductors
- The functional units and the terminals


> Form 3b



The partitioning separates:
- Busbars from terminals for external conductors
- Functional units from each other and from the busbars

Terminals aren't separated from each other


> Form 4a



The partitioning separates:
- Busbars from terminals for external conductors
- Functional units from each other and from the busbars

Terminals for external conductors in the same compartment as the associated functional unit

> Form 4b



The partitioning separates:
- Busbars from terminals for external conductors
- Functional units from each other and from the busbars
- Terminals for external conductors between them

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Internal Separation Forms and their usage







IEC Form	Explanation	PrismaSeT HD	PanelSeT SFN/SM	PanelSeT SFN MCC
Form 1	No internal separation. All busbars, terminals, and functional units share the same space.	✓ Supported (basic configuration)	✓ Supported (basic configuration)	✗ Not possible - MCC always requires form 2b as minimum
Form 2b	Busbars separated from functional units and from terminals for external conductors. Terminals are not separated from each other.	✓ Supported using Busbar partitionings (page 194)	✗ Not possible	✓ Mandatory using Busbar partitionings (page 249) and Intermediate crossbar (page 250)
Form 3b	Functional units separated from: • busbars • each other Terminals are in the same compartment (not individually separated) and separated from their functional unit.	✓ Supported using Busbar partitionings (page 194) and form 3b accessories (page 195)	✗ Not possible	✓ Supported using Busbar partitionings (page 249) and form 3b horizontal separation (page 250)
Form 4a	Functional units separated from busbars and from each other. Terminals are separated from other functional units but remain inside the same functional unit compartment.	✓ Supported using Busbar partitionings (page 194), form 3b (page 195) and form 4a accessories (page 196)	✗ Not possible	✓ Supported using Busbar partitionings (page 249) and form 3b horizontal separation (page 250) and installing the terminals inside of the functional unit
Form 4b	Highest standard level. Functional units separated from busbars and each other. Terminals for external conductors are in individual, separate, enclosed spaces.	✓ Supported using Busbar partitionings (page 194), form 3b (page 195) and form 4b accessories (page 196)	✗ Not possible	✓ Supported using Busbar partitionings (page 249), form 3b horizontal separation (page 250) and terminal boxes (page 251)

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Non-Connected Switchboard

PB124027



MasterPacT™ MTZ main switchboard

At the switchboard head, the drawout MasterPacT MTZ circuit breaker helps to protect the building's entire electrical distribution system.

PB124093



ComPacT NSXm 160 A

The smallest circuit breaker in the ComPacT range, rated up to 160 A.

PB124120



Final switchboard

The Acti9 range circuit breakers helps to protect the terminal loads.


PB124028



ComPacT NSX630 A circuit breaker


The ComPacT NSX circuit breaker, rated up to 630 A, helps to protect the final distribution feeders.

PB124030



Terminal connection blocks

The Linergy terminal blocks and busbars are designed to provide the rapid connection performances expected from a high-quality installation.




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Non-Connected Switchboard



Tesys Deca and GV

The TeSys Deca Advanced is a compact, rugged 3-pole AC-3 contactor up to 115 A, featuring a wide-band electronic coil, front-access wiring, high environmental resistance, and global certifications.

The TeSys GV is a smart, high-capacity 3-pole motor circuit breaker up to 115 A, offering advanced, adjustable motor protection with global certifications.



LC1D115AKUE

PB114917

Altiva Process ATV600

The Altivar Process ATV600 is a versatile variable speed drive for 3-phase motors (380–480 V) that delivers energy savings, advanced connectivity, and flexible performance for fluid management and industrial process applications.



ATV630D11N4Z

Altistart ATS480 Softstarter

The Altivar Soft Starter ATS480 is a compact, certified soft starter for asynchronous motors (208–690 V) offering advanced torque control, efficient braking, digital connectivity, and easy integration with EcoStruxure and ATS48 systems.



ATS480D47Y

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Connected Switchboard

PB124031



Enerlin'X EIFE embedded Ethernet Interface module

The EIFE Ethernet interface is available for MTZ drawout circuit breakers, and provides a direct connection to the Ethernet network.

LV947286W_Image

PB124032



MicroLogic

MicroLogic X and Micrologic Active are types of control units used in MasterPacT MTZ circuit breakers.
They integrate functions such as metering, protection and communication. MicroLogic offers features such as overload protection, short-circuit protection, as well as ground fault and earth-leakage protection (depending on the model). Energy management is possible via various communication protocols such as Modbus RS485, Modbus TCP /IP and wireless communication such as IEEE 802.15.4, Bluetooth and NFC.
All these communication protocols are optional.

PB111801-32_r



Enerlin'X FDM128 local interface

The FDM128 has a wide but shallow screen.
The anti-reflection graphic screen is backlit for easy reading, even in a dark environment or at unusual viewing angles. Please refer to the Enerlin'X catalog.

PB124033



Modicon Ethernet switch

Ethernet switch, 5 copper ports. Communication port protocols: Ethernet TCP/IP.
Ethernet port: 10BASE-T/100BASE-TX-5.
Max. number of connected switches: unlimited.

PB124034



24 V DC power supply

A 24 V DC power supply is required for a networked installation, whatever the MicroLogic types installed in the switchboard.

The requisite specifications are:
- output voltage 24 V DC +/-5%, SELV
- ripple: +/-1%
- overvoltage category: OVC IV - as specified by standard IEC 60947-1.

PB124035



MicroLogic 5/6 E for NSX100 to 630 A

MicroLogic 5/6 E (Energy) releases can be fitted on all ComPacT NSX100 to 630 with performance B/F/H/N/S/L/R/ HB1/HB2. They come with a display. They include the basic LSI protection (MicroLogic 5), which can be supplemented by Ground fault protection (MicroLogic 6). They also come with measurement, alarm functions and are communication ready.

PB124036



Enerlin'X I/O module

The I/O (Input/Output) module for LV circuit breakers is part of the ULP system. It offers predefined or configurable functions and applications and helps ensure that requirements can be met precisely. Two I/O modules can be connected to the same ULP network.


PB124071



Acti9 Active

Acti9 Active is a family of all-in-one protection devices with wireless connectivity. When connected to a gateway, it enables remote monitoring, diagnostics, pre-alarming, and alarming.

DB301361




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Connected Switchboard



PowerLogic HeatTag

HeatTag analyzes suspended gases and particles inside the switchboard to detect invisible yet hazardous transformations of cable insulators.



PB124037

Wireless Indication Auxiliary for ComPacT NSX and NSXm

The Wireless Indication Auxiliary provides remote indications of the circuit breaker status.



PB124040

PowerLogic PowerTag Energy

PowerTag Energy sensors measure electrical quantities and send these wirelessly to a gateway such as Panel Server.

A PowerTag Energy M250/M630

PowerTag Energy M250/M630 are modules for ComPacT NSX, INS/INV and for TeSys GV5/GV6/GV7. For ComPacT NSX, these modules are fitted directly downstream of the circuit breaker or the Vigi extension.



PB124039

B PowerTag Energy F160

PowerTag Energy F160 is a version used on ComPacT NSXm, ComPacT INS up to 160 A, Acti9 NG125, Acti9 C120, TeSys GV4, and all other devices rated 63 to 160 A.



PB124041

C PowerTag Energy M63

PowerTag Energy M63 are designed to fit directly on the Acti9 or Multi9 range devices with 18mm pitch up to 63 A.



PB124042

EcoStruxure I/O Smart Link

The I/O Smart Link is used for monitoring and controlling Acti9 range devices via a Modbus serial connection.



PB107753_80

EcoStruxure Panel Server

The Panel Server gateway is designed to connect and digitize the electrical distribution installation and to perform energy management and monitoring, from the enclosure incomer down to the load level. It is mandatory when using wireless devices.



PB124043

Enerlin'X IFM Modbus Interface module

For ComPacT NS/NSX and MasterPacT: makes a circuit breaker fitted with a ULP port accessible via a Modbus serial network. Data that may be transmitted includes the circuit breaker settings, alarms, voltage, current, power factor, energy, and power.



IFMV2_Image

Modbus SL Hub

For ComPacT NSX: makes a circuit breaker equipped with a BSCM Modbus SL/ULP directly accessible via a Modbus serial network through a Modbus SL cord. Uses the same dataset as an IFM. Up to 3 circuit breakers with BSCM Modbus SL/ULP can be connected to one Modbus SL Hub.



LV434224_Image

Enerlin'X IFE Ethernet Interface module

For ComPacT NS/NSX and MasterPacT: provides an IP address and makes a circuit breaker fitted with a ULP port (could be via IFM) accessible via an Ethernet network. Data that may be transmitted includes the circuit breaker settings, alarms, voltage, current, power factor, energy, and power.



DB416830

Modbus
Ethernet network
ULP Universal Logic Plug system

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Linergy

PB111244-50
PB111252-70



Linergy DS

Designed for installation on DIN rails or mounting plates and compatible with various switchboards. It simplified power distribution with easy cabling, good accessibility, and clear phase separation for improved safety and organization.


Lingery_BW



Linergy BW


A pre-assembled system designed for quick and reliable installation, with integrated supports, end caps, and protective covers. Its modular design, threaded connections, and wide range of pre-wired connectors simplify integration and help ensure efficient power distribution.

montage_linergy LGY-E
PD390408



Linergy LGY/LGE

This system provides a complete and coherent solution for electrical current routing, combining optimized busbars, pre-wired connectors, and tailored distribution blocks. It helps ensure efficient power distribution while simplifying installation and improving overall system organization.




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Overview of Low-Voltage System Types

Schneider Electric Device Ecosystem

Linergy



Linergy BZ

This mounting plate system for busbars simplifies the installation of motor feeder components used in electrical installations. Power distribution is performed by a busbar. The mounting plates are fitted directly on this busbar, by snap-on mounting, thus implementing electrical distribution.



PB502367

Linergy HK

The assembly of automated control and distribution panels requires the use of products that are not only reliable, but also simple and quick to mount and wire up. These pre-assembled busbar systems meet all these criteria.



PB502364

Linergy FT

Simplifies the creation of protection and control assemblies by enabling grouped power supply, component mounting, and interconnection. These solutions simplify installation, optimize panel space, and significantly reduce wiring time.



Produits_FTs

Linergy TR

The Linergy terminal blocks and busbars are designed to provide the rapid connection performances expected from a high-quality installation.



PB124030

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System


Introduction



The PrismaSeT HD system can be used for all types of low-voltage distribution switchboards up to 4000 A for harsh environments (up to 6300A with PrismaSeT 6300).

It is a modular system designed for building and industrial electrical distribution. Its architecture supports flexible assembly standardized functional units, and clear organization of devices and busbars.

The system integrates with Schneider Electric equipment and can be expanded or adapted depending on installation needs. Connected options up to 4000 A also allow remote supervision for monitoring electrical conditions and system performance.




For more information about PrismaSeT 6300 and for solutions up to 6300 A see the catalog PrismaSeT 6300
UEMKCAT008EN

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PrismaSeT HD: Functional System

Introduction




1. Modular Structure

- Composed of pre-assembled metal frameworks.
- Frameworks can be arranged side-by-side or back-to-back.
- Enables flexible and scalable switchboard design.



2. Efficient Distribution

- Horizontal busbars installed on top or bottom.
- Vertical busbars placed in lateral or rear compartments.
- Helps ensure reliable distribution of electricity throughout the enclosure.



3. Functional Units

- Modular units dedicated to specific switchboard functions.
- Include mounting plates, front protective plates, and connection devices.
- Designed and tested with device characteristics for high reliability.



4. Safer Operation

- Devices installed behind protective front plates for safer operation.
- Optional internal partitions/barriers aligned with Forms 2–4.
- Terminal shields required for ComPacT NSX and INS/INV devices.



5. Connected Supervision


- Remote monitoring available up to 4000 A.
- Supports fire prevention through early detection.
- Improves power availability and continuity of service.
- Enhances energy monitoring and management efficiency.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System

Characteristics

Components in the PrismaSeT HD system enables the compliance of switchboards with standards IEC 61439-1 + 2.



Electrical switchboards built using the PrismaSeT functional system and Schneider Electric recommendations fully comply with international standard IEC 61439-2.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System

Characteristics

Mechanical Characteristics up to 4000 A

- Steel sheet metal.
- Structured finish, epoxy polyester powder.
- Two options:
  - White color RAL 9003 outside and inside
  - Gray color RAL 7035 outside and white color inside (for the PrismaSeT references)
- Can be dismantled.
- Can be combined side-by-side and back-to-back.
- Degree of protection: IP55 according to IEC 60529.
- Degree of protection against mechanical impacts: IK10 (IK08 for the glazed-door) according to IEC 62262.

Framework dimensions

Two widths:

- W 300: Cable management or vertical busbar compartment
- W 700: Device compartment

Three depths:

- D500 up to 1600 A with incoming MasterPacT NT and MTZ1 only
- D600 up to 1600 A with incoming MasterPacT NT and MTZ1 only. Option to connect with cables from rear
- D800 up to 4000 A with incoming MasterPacT NT and MTZ1 or NW and MTZ2. Option to connect to cables from rear or to connect to rear vertical busbars
- Height: 2000 mm
- Enclosures for indoor installation.

Electrical Characteristics









- Rated insulation level of main busbars: 1000 V.
- Rated operational current Ie: 4000 A.
- Rated peak withstand current Ipk: 220 kA.
- Rated short-time withstand current I_{cw}: 100 kA rms/1 second.
- Frequency: 50/60 Hz.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System








Busbar Selection

Linergy LGYE - Horizontal Profiles up to 4000 A

Installation in PrismaSeT HD		Up to 1600 A					Up to 4000 A			
Linergy profile, 2000 mm length										
		630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
Permissible current for an ambient temperature of 35 °C around the switchboard	IP ⩽ 31	630 A	800 A	1000 A	1250 A	1650 A	2000 A	2440 A	3200 A	3620 A
	IP > 31	530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Number of profiles per phase		1								
Total number of vertical modules (50 mm)		3					3		4	
References		**LVS04560**	**LVS04561**	**LVS04562**	**LVS04563**	**LVS04564**	**LVS04565**	**LVS04566**	**LVS04567**	**LVS04568**
Busbar supports										
		 Fixed Support **LVS04664**					 Free Support **NSYBSA**			
		2 fixed supports for PrismaSeT HD 700 wide frame are compulsory. 1 fixed support for 300/400 wide frame are compulsory. If more supports are needed, add free supports.								
In enclosure: W700 busbar supports with 75 mm distance between bars	Number of supports depending on I_{cw} (kA rms/1 s) ≤ 15	2								
	≤ 25	2								
	≤ 30	2								
	≤ 40	-		2						
	≤ 50	-			2					
	≤ 60	-			2+1		2			
	≤ 65	-				2+1				
	≤ 75	-				2+1				
	≤ 85	-				2+1				
	≤ 100	-					2+2			
References Fixed support		**LVS04664**					**LVS04664 + LVS04671** (order 1 per support)		**LVS04664 + LVS04646** (sold in lots of 12 spacers)	
References Free support		**NSYBSA**					**NSYBSA + LVS04671** (order 1 per support)		**NSYBSA + LVS04646** (sold in lots of 12 spacers)	
In duct: W300 busbar supports with 75 mm distance between bars	Number of supports depending on I_{cw} (kA rms/1 s) ≤ 15	1								
	≤ 25	1								
	≤ 30	1								
	≤ 40	1								
	≤ 50	1								
	≤ 60	1								
	≤ 65	1 + 1								
	≤ 75	1 + 1								
	≤ 85	1 + 1								
	≤ 100	-					1 + 1			
References Fixed support		**LVS04664**					**LVS04664 + LVS04671** (order 1 per support)		**LVS04664 + LVS04646** (sold in lots of 12 spacers)	
References Free support		**NSYBSA**					**NSYBSA + LVS04671** (order 1 per support)		**NSYBSA + LVS04646** (sold in lots of 12 spacers)	
Joints		Up to 1600 A					Up to 4000 A			
		630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
										
		LVS04620		**LVS04623**			**LVS04624**			
References (3P)		**3x LVS04620**					3x **LVS04621**		3x **LVS04623**	
References (4P)		4x **LVS04620** + **LVS04624**					4x **LVS04621** + **LVS04624**		4x **LVS04623** + **LVS04624**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Linergy BS - Horizontal Flat Busbars up to 4000 A

Installation in PrismaSeT HD			Up to 1600 A				Up to 4000 A					
Copper bar, 2000 mm length												
Permissible current for an ambient temp. of 35 °C around the switchboard		IP ⩽ 31	800 A	1000 A	1400 A	1800 A	1800 A	2050 A	2300 A	2820 A	3300 A	3760 A
		IP > 31	750 A	900 A	1250 A	1600 A	1600 A	1850 A	2000 A	2500 A	2900 A	3340 A
Busbar cross-section (mm)			60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10	120 x 10
Number of busbars per phase			1	1	2	2	1	2	2	2	2	2
Total number of vertical modules (50 mm)			3									4
References			**LVS04536**	**LVS04538**	**LVS04536**	**LVS04538**	**LVS04548**	**LVS04545**	**LVS04546**	**LVS04548**	**LVS04550**	**LVS04552**
Busbar supports							 Fixed Support **LVS04664**			 Free Support **NSYBSA**		
			2 fixed supports for PrismaSeT HD 700 wide frame are compulsory. 1 fixed support for 300/400 wide frame are compulsory. If more supports are needed, add free supports.									
In enclosure: W700 with 75 mm distance between bars	Number of supports depending on I_{cw} (kA rms/1 s)	≤ 15	2									
		≤ 25	2+1	2								
		≤ 30	2+1	2								
		≤ 40	2+1				2					
		≤ 50	-	2+1					2			
		≤ 60	-				2+1					
		≤ 65	-				2+1					
		≤ 75	-				2+2	2+1				
		≤ 85	-				-		2+1			
References Fixed support			**LVS04664**				**LVS04664**			**LVS04664 + LVS04671**		
References Free support			**NSYBSA**				**NSYBSA**			**NSYBSA + LVS04671**		
In duct: W300 with 75 mm distance between bars	Number depending on I_{cw} (kA rms/1 s)	≤ 30	1									
		≤ 50	1+1				1					
		≤ 85	-				2					
References (depending on depth) Fixed support			**NSYBHS500** (D500) or **NSYBHS600** (D600) or **NSYBHS800** (D800)				**NSYBHS500** (D500) or **NSYBHS600** (D600) or **NSYBHS800** (D800)			**NSYBHS500** (D500) or **NSYBHS600** (D600) or **NSYBHS800** (D800) + **LVS04671**		
References (depending on depth) Free support			**NSYBSA**				**NSYBSA**			**NSYBSA** + **LVS04671**		
Joints			**Up to 1600 A**				**Up to 4000 A**					
			1 vertical bar per phase		2 vertical bars per phase		1 vert. bar per phase	2 vertical bars per phase				
Busbar cross-section (mm)			60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10	120 x 10
Sliding joints with self-breaking lock nut			 **LVS04640**			 **LVS04641**						
References			**LVS04640**	**LVS04641**	**LVS04640**	**LVS04641**	**LVS04641**	**LVS04640**	**LVS04640**	**LVS04641**	**LVS04641**	**LVS04643**

⚠⚠ DANGER

RISK OF ELECTRIC SHOCK AND ARC FLASH

- Reference **LVS04624** is compulsory when installing jointed Linergy LGYE 4P busbars and must be fitted where the frames meet.
- When installed at the bottom of an enclosure, the busbar must be partitioned.






Failure to follow these instructions will result in death or serious injury.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PrismaSeT HD: Functional System


Busbar Selection

Linergy LGY - Lateral Profiles up to 1600 A

In PrismaSeT HD duct		W300				
						
		630 A	**800 A**	**1000 A**	**1250 A**	**1600 A**
Permissible current for an ambient temp. of 35 °C around the switchboard	IP ⩽ 31	680 A	840 A	1040 A	1290 A	1650 A
	IP > 31	590 A	760 A	950 A	1170 A	1480 A
Number of profiles per phase		1				
References		**LVS04502**	**LVS04503**	**LVS04504**	**LVS04505**	**LVS04506**

Busbar supports








Fixed Support **LVS04651**

Number depending on I_{cw} (kA rms/1 s)	⩽ 25	3				
	⩽ 30	-	3			
	⩽ 40	-		3		
	⩽ 50	-			4	
	⩽ 60	-			5	
	⩽ 65	-				5
	⩽ 75	-				7
Only for enclosures with a depth ≥ 500 mm	⩽ 85	-				8
References		**LVS04651** (set of 2 upright adapters **NSYSFPAED** for installation in PrismaSeT HD enclosure)				


Connections to the Linergy BS horizontal busbar



Note:
Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase.

References according to horizontal busbar size	**5 mm thick**	**LVS04634**	**LVS04635**	
	10 mm thick	**Width ⩽ 80 mm**	**LVS04636**	
	10 mm thick	**Width > 80 mm**	**LVS04636 + LVS04642** **LVS04638 + LVS04642**	

Connections to the Linergy LGYE horizontal busbar



Note:
Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase.

References (vertical connection)	**LVS04602**
References (vertical shifted connection)	**LVS04603**

NOTICE

FITTING OF END STOP


An end stop must be fitted on the bottom support: **LVS01109** (sold in lots of 12).

Failure to follow these instructions can result in equipment damage.


(1) Dedicated connection **LVS04603** for Linergy LGYE busbar in 150 mm duct with horizontal jointing.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Linergy LGYE - Lateral Profiles up to 4000 A

In PrismaSeT HD duct		W300								
Linergy profile, 2000 mm length										
		630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
Permissible current for an ambient temperature of 35 °C around the switchboard	IP ⩽ 31	630 A	800 A	1000 A	1250 A	1650 A	2000 A	2440 A	3200 A	3620 A
	IP > 31	530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Length to cut for side-mounted		1675 mm							1625 mm	
Number of profiles per phase		1								
Height available (mm)		150					150		200	
References		**LVS04560**	**LVS04561**	**LVS04562**	**LVS04563**	**LVS04564**	**LVS04565**	**LVS04566**	**LVS04509**	**LVS04510**


Busbar supports




Number depending on I_{cw} (kA rms/1 s)									
	⩽ 30	3							
	⩽ 40	-	3+2 *				3		
	⩽ 50	-		3+2 *			3		
	⩽ 60	-			3+2 *			3	
	⩽ 65	-				3+2 *			
	⩽ 75	-				3+4 **		3+2 *	
	⩽ 85	-				3+4 **			
	⩽ 100	-					3+6 ***		



Fixed Support **NSYBVS500**



Free Support **NSYBSA**



Bottom Support **NSYAS500**


3 fixed supports are compulsory to hold the busbar in position.
If more than 3 supports are needed, use free supports (in addition).

References* 75 mm distance between bars	W300, D500	**NSYBVS500** (fixed) + **NSYBSA** (free) + **NSYAS500** (bottom) (1)
	W300, D600	**NSYBVS600** (fixed) + **NSYBSA** (free) + **NSYAS600** (bottom) (1)
	W300, D800	**NSYBVS800** (fixed) + **NSYBSA** (free) + **NSYAS800** (bottom) (1)
References* 115 mm distance between bars	W300, D800	**NSYBVS800L** (fixed) + **LVS04678** (free) + **NSYAS800L** (bottom) (1)


* References of supports depending on distance between bars and duct depth

(1) If using a 100 x 10 bars, add a pack of screws ref. **LVS04671** for each fixed support and free support.

Wedging busbars in position



Wedge Fitted on Bottom Support **LVS04658**




Wedge Fitted on Bottom Support **LVS04659**

The bottom support is used to place profiles in the correct position.
It is not considered to be a busbar support.


References Wedge	**LVS04658**	**LVS04659**

Connections to the Linergy LGYE horizontal busbar

2000/2500 A



3200/4000 A



Supplied with mounting hardware.
Reference include 1 connection only. Order 1 connection per phase.


References (short connection)	**LVS04604**	**LVS04607**
References (long connection)	**LVS04605**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PrismaSeT HD: Functional System

Busbar Selection

Linergy BS - Lateral Flat Busbars up to 3200 A

In PrismaSeT HD duct		W300										
Pre-slotted copper, 1675 mm length												
Permissible current for an ambient temp. of 35 °C around the switchboard	IP ≤ 31	800 A	1000 A	1400 A	1800 A	1200 A	1400 A	1800 A	2050 A	2300 A	2820 A	3200 A
	IP > 31	750 A	900 A	1250 A	1600 A	1080 A	1250 A	1600 A	1850 A	2000 A	2500 A	2820 A
Busbar cross-section (mm)		60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10
Number of profiles per phase		1		2		1			2			
References		LVS04516	LVS04518	LVS04516	LVS04518	LVS04525	LVS04526	LVS04528	LVS04525	LVS04526	LVS04528	LVS04550(1)

Busbar supports



Number of supports depending on I_{cw} (kA rms/1 s)												
	≤ 15	3 *										
	≤ 25	3+2 *				3 *						
	≤ 30	3+2 *										3 *
	≤ 40	3+4		3+2 *								
	≤ 50		3+4			3+2 *						
	≤ 60					3+4						3+2 *
	≤ 65					3+4						3+2 *
	≤ 75						3+6		3+4			
	≤ 85									3+4		


3 fixed supports are compulsory to hold the busbar in position.
If more than 3 supports are needed, use free supports (in addition).
The bottom wedge support is used to place the busbar in the correct position.
It does not count as a busbar support.


References* 75 mm distance betw. bars	**W300, D500**	**NSYBVS500** (fixed) + **NSYBSA** (free) + **NSYAS500** (bottom) (2)
	W300, D600	**NSYBVS600** (fixed) + **NSYBSA** (free) + **NSYAS600** (bottom) (2)
	W300, D800	**NSYBVS800** (fixed) + **NSYBSA** (free) + **NSYAS800** (bottom) (2)
References* 115 mm distance betw. bars	**W300, D800**	**NSYBVS800L** (fixed) + **LVS04678** (free) + **NSYAS800L** (bottom) (2)

* References. of supports depending on distance between bars and duct depth

(1) Copper bar without holes.
(2) If using a 100 x 10 bars, add a pack of screws ref. **LVS04671** for each fixed support and free support.


Connections to the Linergy BS horizontal busbar






For a busbar with 75 mm distance between bars, the bars are completely covered.
Staggered assembly points between one bar and the next, to maintain the necessary clearance distances.(3)

References **LVS04636**, **LVS04637**, **LVS04638** are supplied individually:
1 connection per phase.
Reference **LVS04642** consists of 2 M8 x 140 screws which can replace the original M8 x 120 screws.




	1 bar per phase		2 bars per phase		1 bar per phase			2 bars per phase			
	60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10
References depending on horizontal busbar size											
≤ 80 mm	**LVS04645**				**LVS04636**		**LVS04637**	**LVS04637**			**LVS04645**
> 80 mm	**LVS04645**				**LVS04636 + LVS04642**		**LVS04637 + LVS04642**	**LVS04637 + LVS04642** **LVS04638 + LVS04642**			**LVS04645**

(1) Drill Hole Dimensions for 5 mm Thick Horizontal Busbars














Drill Hole Dimensions for 10 mm Thick Horizontal Busbars



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Linergy LGYE - Rear Profiles up to 1600 A

At the rear of a PrismaSeT HD enclosure		W700				
		 DD381233_LIN_7_nb	 DD381234_LIN_7_nb	 DD381235_LIN_7_nb	 DD381236_LIN_7_nb	 DD381237_LIN_7_nb
		630 A	**800 A**	**1000 A**	**1250 A**	**1600 A**
Permissible current for an ambient temp. of 35 °C around the switchboard	IP ⩽ 31	680 A	840 A	1040 A	1290 A	1650 A
	IP > 31	590 A	760 A	950 A	1170 A	1480 A
Number of profiles per phase		1				
References		**LVS04502**	**LVS04503**	**LVS04504**	**LVS04505**	**LVS04506**
Busbar supports		 DD381242_LIN_nb Fixed Support **LVS04652**				
 DD385374_EN_nb (387.5 mm max., 350 mm max., 350 mm max., 350 mm max., 350 mm max.)	Number depending on I_{cw} (kA rms/1 s) ⩽ 25	3				
	⩽ 30		4			
	⩽ 40			5		
	⩽ 50				7	
		 DD381243_LIN_nb				
References		**LVS04652**				
Connections to the Linergy BS horizontal flat busbar		 DD385372_nb **LVS04635** Connection to 5 mm Thick Horizontal Busbar		 DD385373_nb **LVS04636** Connection to 10 mm Thick Horizontal Busbar		
		Fixings supplied, order 1 connection per phase. Some parts of the connection require flexible insulated busbars.				
References according to horizontal busbar size	**5 mm thick**	**LVS04635**				
	10 mm thick **Width ⩽ 80 mm**	**LVS04636**				
	10 mm thick **Width > 80 mm**	**LVS04636 + LVS04642**				
Connections to the Linergy LGYE horizontal flat busbar		 DD385375_nb **LVS04602** Connection to the Linergy LGYE Horizontal Flat Busbar				
		Fixings supplied, order 1 connection per phase. Some parts of the connection require flexible insulated busbars.				
References		**LVS04602**				

NOTICE

FITTING OF END STOP

An end stop must be fitted on the bottom support **LVS01109** (sold in lots of 12).









Failure to follow these instructions can result in equipment damage.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System

Busbar Selection

Linergy BS - Rear Flat Busbars up to 1600 A

At the rear of a PrismaSeT HD enclosure		W700					
Pre-slotted copper, 1670 mm length		800 A	1000 A	1400 A	1000 A	1200 A	1600 A
Permissible current for an ambient temperature of 35 °C around the switchboard	IP ⩽ 31	800 A	1000 A	1400 A	-	-	-
	IP > 31	750 A	900 A	1250 A	1080 A	1250 A	1600 A
Busbar cross-section (mm)		60 x 5	80 x 5	60 x 5	50 x 10	60 x 10	80 x 10
Number of busbars per phase		1		2	1		
References		LVS04516	LVS04518	LVS04516	LVS04525	LVS04526	LVS04528
Busbar supports		 Fixed Busbar Support **LVS04653**		 Busbar Free Support **NSYBSA**		 Mounting Chocks **LVS04669**	
		3 fixed supports ref. **LVS04653** are compulsory to keep the busbar vertical. If more than 3 supports are needed, use free support ref. **NSYBSA** (in addition). Metal shim ref. **LVS04669** (sold in lots of 100), 5 mm thick, is screwed onto the busbar. It rests on a fixed support and is used to wedge the busbar in position.					
		 Wedging: 1 busbar/phase					
		 Wedging: 2 busbars/phase					
Number depending on I_{cw} (kA rms/1 s)	⩽ 15	3			3		
	⩽ 25	3+2			3		
	⩽ 30	3+2			3+2		
	⩽ 40	3+4		3+2	3+2		
	⩽ 50		3+4		3+2		
	⩽ 60				3+4		
	⩽ 65				3+4		
	⩽ 75					3+6	
	⩽ 85						
References		LVS04653 (fixed) + **NSYBSA** (free) + **LVS04669** (spacer)					
Connections to the Linergy BS horizontal flat busbar		 **LVS04635** Connection to Horizontal Busbar 5 mm Thick			 **LVS04636** Connection to Horizontal Busbar 10 mm Thick		
		For part of the connection, flexible insulated busbars are needed. References **LVS04635**, **LVS04636** are supplied individually = 1 connection per phase. Reference **LVS04642** consists of 2 M8 x 140 screws which can replace the original M8 x 120 screws.					
References according to horizontal busbar size	5 mm thick		LVS04635				
	10 mm thick	Width ⩽ 80 mm	LVS04636 (1)				
	10 mm thick	Width > 80 mm	LVS04636 + LVS04642 (1)				


(1) To be made.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Linergy LGYE - Accessories

Linergy Screw


- Sold in lots of 20: 20 screws + 20 nuts + 20 contact washers, grade 8.8. The screws slide into the profile and are then locked in the desired position.



Characteristics		AD	References
Steel plain washers	M8 sold in lots of 20	20 mm	**LVS04772**
	M8 sold in lots of 20	24 mm	**LVS04773**
	M8 sold in lots of 20	28 mm	**LVS04774**
Brass plain washers	M8 sold in lots of 20 for connection of ≤ 25 mm² lugs to Linergy	20 mm	LVS04775
Identification	12 clip-on supports + N, L1, L2, L3, PE, PEN labels		**LVS04794**
	Linergy LGYE busbar screw plate kit after sales service		**LVS01130**

M8 Screws

- Set of 20 screws + 20 nuts + 40 contact washers.


LVS04782

Characteristics	References
Linergy BS, 20 screws grade 8.8, M8 x 20	**LVS04782**
Linergy BS, 20 screws grade 8.8, M8 x 25	**LVS04783**
Linergy BS, 20 screws grade 8.8, M8 x 30	**LVS04784**
Linergy BS, 20 screws grade 8.8, M8 x 35	**LVS04785**
Linergy BS, 20 screws grade 8.8, M8 x 40	**LVS04786**
Linergy BS, 20 screws grade 8.8, M8 x 45	**LVS04787**
Linergy BS, 20 screws grade 8.8, M8 x 50	**LVS04788**

Torque Nuts


- Can be used to obtain the correct tightening torque (28 Nm) recommended by the manufacturer, without using a torque wrench. Torque nuts may be used for all electrical connections.


LVS04759

Characteristics	References
20 M8 torque nuts	**LVS04759**


Voltage Tap-Offs

- For small lugs (on low-current cables or measurement tap-offs), insert a conducting washer (ref. **LVS04775**) between the busbar and the lug.


LVS04229

Characteristics	References
20 M10 voltage tap-offs for two 6.35 mm tab connectors	**LVS04229**

Connections on Linergy LGYE and LGY


LVS04766


LVS04768


LVS04769

Characteristics	InA	bar	Utilisation	References
Use the 25 mm Linergy screw	0 A to 630 A	Cable Insulated flexible bar	Recommended	**LVS04766**
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	0 A to 630 A	Cable Insulated flexible bar	Possible	**LVS04767**
Use the 25 mm Linergy screw	800 A to 1250 A	5 mm thick bar	Recommended	**LVS04766**
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	800 A to 1250 A	5 mm thick bar	Possible	**LVS04767**
Use the flat plate screw with 2 studs	800 A to 1250 A	5 mm thick bar	Possible	**LVS04768**
Use the flat plate screw with 2 studs	1600 A to 2500 A	5 or 10 mm thick bar	Recommended	**LVS04768**
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	1600 A to 2500 A	5 or 10 mm thick bar	Possible	**LVS04767**
Use the flat plate screw with 3 studs	3200 A to 4000 A	10 mm thick bar	Recommended	**LVS04769**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PrismaSeT HD: Functional System

Partitioning


Form 2b Partitioning

Separation of busbars from the functional units:

- Protection against contact with live parts upstream of the outgoing circuits
- Protection against penetration by foreign solid bodies.





Lateral Partitioning; Form 2 Restoration for Side-Barrier Cut-Out


LVS06545

Characteristics	References
Lateral partitioning • Vertical barrier made of insulated slats. • Can be installed on both sides of Linergy and flat busbars. • The space between the slats is sufficient for prefabricated connections (one copper bar, 5 or 10 mm thick, or insulated flexible bars) or for cables up to 35 mm², while maintaining the IP2X degree of protection in compliance with standard IEC 60695.2.1 concerning fire resistance.	**LVS06545**
Form 2 restoration for side-barrier cut-out • This kit enables the passage of the connection between a device > 1600 A (MTZ2, INS) and lateral vertical busbars. • It is made up of an insulated plate (six modules H 300 mm) that can be cut as required, supplied with supports and the necessary hardware.	**LVS04924**

Partitioning Extension



LVS06541




- The partitioning extension is required for PrismaSeT system switchboards with a depth of 600 or 800 mm.

Characteristics	References
D600	**LVS06541**
D800	**LVS06543**


Front and Rear Barrier


LVS06540




Characteristics	References
• Front protection is provided by the combination of door W300 and this barrier. • Metal barrier, composed of 2 parts H850, pre-cut at both ends. • Rear protection: a barrier is required at the rear of the busbar compartment in enclosures that are 800, 1000 or 1300 mm deep.	**LVS06540**

Inter-Enclosure Partitioning


LVS06555


- Metal partition, used to separate two adjacent enclosures.
- It is made up of two panels, each 850 mm high.
- The top and bottom ends have knock-outs for horizontal busbars.
- Supplied with the necessary supports and hardware, the partition is mounted on the framework and does not hinder installation of the functional mounting plates.



Characteristics	References
D500	**LVS06555**
D600	**LVS06555** + **LVS06541**
D800	**LVS06555** + **LVS06543**

Partitioning of Horizontal Busbars


LVS06560


LVS06570

- Set of two barriers (front and rear), plus a slotted rear panel for efficient natural convection in the switchboard.
- The set can be used to partition horizontal busbars installed at the top or bottom of the enclosure.
- The space required for the busbars is not increased.

Characteristics	References
3M-busbar, W300, D500	**LVS06560**
3M-busbar, W300, D600	**LVS06561**
3M-busbar, W300, D800	**LVS06563**
4M-busbar, W300, D500 or D600 or D800	**LVS06568**
3M-busbar, W700, D500 or D600 or D800	**LVS06570**
4M-busbar, W700, D500 or D600 or D800	**LVS06567**

⚠⚠ DANGER

RISK OF ELECTRIC SHOCK AND ARC FLASH

If the busbars are at the bottom of the enclosure, gland plates are mandatory.

Failure to follow these instructions will result in death or serious injury.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Form 3b Partitioning

Separation of busbars from the functional units and separation of all functional units from one another.
Separation of the terminals for external conductors from the functional units, but not from each other.


- Protection against contact with live parts
- Reduction in the risk of faults between the functional units (propagation of electrical arcs, etc.).

Front Connection


LVS04901

A horizontal metal partition can be used to physically separat functional units from one another.

Characteristics	References
Horizontal metal partition, W650 mm	**LVS04901**


DD384420_nb


LVS04943


It is fixed at the rear by a support (two uprights) secured to the framework (500 mm deep) or to the intermediate uprights (800 mm deep frameworks).

Characteristics	References
Rear support for partitions, W650 mm	**LVS04943**


LVS03583

A set of brackets can be used to install partial Form 3 partitioning in the enclosure.
It does not take up any useful space in the switchboard.


Characteristics	References
6 universal angle brackets	**LVS03583**



DD384422_nb

Rear Connection

Vertical partitions (two catalogue number per functional unit)

Characteristics	References
3 to 4 modules	**LVS04955**
5 to 6 modules	**LVS04956**


LVS04955


DD384421_nb

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System


Partitioning

Form 4 Partitioning

Separation of busbars from the functional units and separation of all functional units from one another, including the terminals for external conductors which are an integral part of the functional unit.


- Protection against contacts with live parts and reduction in the risk of faults between the functional units (propagation of electrical arcs, etc.).
- Form 4a: Terminal for external conductors in the same compartment as the associated.
- Form 4b: Terminals for external conductors not in the same compartment as the associated functional unit, but in individual, separate, enclosed spaces or compartments.

Form 4a Partition for Front Connection



LVS04946

Backplate (one catalogue number per enclosure) made up to two metal half panels mounted on the rear supports for Form 3 partitions. This backplate is not indispensable for 500 mm deep frameworks.

Characteristics	References
Form 4a backplate (one catalogue number per enclosure)	**LVS04946**




Form 4a Gland Plate



LVS04951

Gland plate that can be easily cut-out (one for each functional unit) and is mounted on the framework.

Characteristics	References
3 or 4 modules	**LVS04951**
5 or 6 modules	**LVS04952**




Form 4b Partition



LVS06600

Cover with metal gland plates that can be easily cut-out on the side and bottom. It is available in two heights:

Characteristics	References
3 to 5 modules	**LVS06600**
4 to 6 modules	**LVS06601**




Connection Transfer Assembly, 3 to 5 Modules, 250 A


LVS06606

Transfer assembly without connections to simplify cable installation.

Characteristics	References
3P	**LVS06606**
4P	**LVS06604**

Connection Transfer Assembly, 4 to 6 Modules, 630 A


LVS06605




Transfer assembly without connections to simplify cable installation.

Characteristics	References
3P	**LVS06607**
4P	**LVS06605**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Common Characteristics

- Roof characteristics:
  - equipped with a factory-mounted polyurethane (PUR) gasket
  - supplied with mounting hardware
  - with markings for clear identification of cable-running zones
- The cable compartment can be mounted on the right or left.
- Can be combined side-by-side or back-to-back.
- Receive the IP55 cover panels.

Mounting			W700			W300		
			 DD385545_nb			 DD385546_nb		
Depth			**D500**	**D600**	**D800**	**D500***	**D600**	**D800**
Enclosures for front connection H2000	Plain-door enclosure	White RAL 9003	**NSYSFPN20750ED**	-	**NSYSFPN20780ED**	**NSYSFN20350ED**	-	**NSYSFN20380ED**
		Gray RAL 7035	**NSYSFPN20750G**	**NSYSFPN20760G**	**NSYSFPN20780G**	**NSYSFN20350**	**NSYSFN20360**	**NSYSFN20380**
	Transparent-door enclosure	White RAL 9003	**NSYSFPN20750TED**	-	**NSYSFPN20780TED**	-	-	-
		Gray RAL 7035	**NSYSFPN20750TG**	**NSYSFPN20760TG**	**NSYSFPN20780TG**	-	-	-
Additional enclosure for rear connection H2000  DD436037	Vertical uprights	White RAL 9003	**NSYSFNV20ED**	-	-	**NSYSFNV20ED**	-	-
		Gray RAL 7035	**NSYSFNV20**	-	-	**NSYSFNV20**	-	-
	Bottom and top frame wit roof	White RAL 9003	**NSYSFNC75ED**	-	-	**NSYSFNC35ED**	-	-
		Gray RAL 7035	**NSYSFNC75**	-	-	**NSYSFNC35**	-	-
Adapter uprights for busbar installation in vertical on Linergy LGY  06502_nb			-	-	-	**NSYSFPAED**	**NSYSFPAED** + **NSYSUCR40200**	**NSYSFPAED** + **NSYSUCR40200**
Side panel (Set of 2)**  DD384425_nb		White RAL 9003	**NSY2SPN205ED**	-	**NSY2SPN208ED**	**NSY2SPN205ED**	-	**NSY2SPN208ED**
		Gray RAL 7035	**NSY2SPN205**	**NSY2SPN206**	**NSY2SPN208**	**NSY2SPN205**	**NSY2SPN206**	**NSY2SPN208**
Hinged front plate support frame***  DD381324_nb			**LVS08566**	**LVS08566**	**LVS08566**	-	-	-

* For cables and to install Linergy LGY, LGYE, BS Busbars.
** An earthing braid must be installed between the lateral panels and the frame.
*** Reversible for left or right-hand opening.

Accessories

Width			W700			W300		
Depth			**D500**	**D600**	**D800**	**D500**	**D600**	**D800**
 DD384428_nb	Plinth H100*	Front and rear cross-pieces	**NSYSPF7100**	**NSYSPF7100**	**NSYSPF7100**	**NSYSPF3100**	**NSYSPF3100**	**NSYSPF3100**
		Lateral cross-pieces	**NSYSPS5100**	**NSYSPS6100**	**NSYSPS8100**	**NSYSPS5100**	**NSYSPS6100**	**NSYSPS8100**
	Plinth H200*	Front and rear cross-pieces	**NSYSPF7200**	**NSYSPF7200**	**NSYSPF7200**	**NSYSPF3200**	**NSYSPF3200**	**NSYSPF3200**
		Lateral cross-pieces	**NSYSPS5200**	**NSYSPS6200**	**NSYSPS8200**	**NSYSPS5200**	**NSYSPS6200**	**NSYSPS8200**
 DD384427_nb	Single-entry gland-plates		**NSYEC751**	**NSYEC761**	**NSYEC781**	**NSYEC351**	**NSYEC361**	**NSYEC381**

* The plinth is made up of two catalog numbers: Front and rear cross-pieces + lateral cross-pieces.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PrismaSeT HD: Functional System

Accessories

Coupling Kit

- Side-by-side combination
- Back-to-back combination: D500+D500, D800+D500
- Back-to-back combination shipped individually and combined during on-site installation

PB500531_29



NSYSFBK19

Characteristics	References
PrismaSet SFN coupling kit for PrismaSeT HD or SFN enclosures equipped with swinging 19" rack, IP55	**NSYSFBK19**

4 Lifting Rings

- Use a set of lifting rings for each framework for one framework (W700 mm) containing devices




NSYSFEB

Characteristics	References
PanelSeT SFN M12 lifting eyebolt, galvanized cast steel	**NSYSFEB**

4 Lifting Brackets

- When two enclosures with devices have been combined, use a lifting beam.

PB503870



NSYSFELB

Characteristics	References
Set of 4 PanelSeT SFN lifting bracket, zinc-coated steel	**NSYSFELB**

Set of 20 Screws + M6 Nuts



LVS06461

Characteristics	References
20 screws and M6 nuts	**LVS06461**

Earthing Cable, 6 mm²

The cable is equipped with a 4 mm diameter lug at one end and a 6 mm diameter lug on the other.
The earthing cable is used to earth:

- A door or wicket door with devices
- A front-plate support frame equipped with switchgear in an enclosure.



LVS08911

Characteristics	References
Earthing cable 6 mm²	**LVS08911**

Earthing Braid

- An earthing braid is installed between the roof and the frame.
- For NSYEL166D8: Length 160 mm, Section 6 mm², Terminal 8.3 mm.
- For NSYEL3525D8: Length 350 mm, Section 25 mm², Terminal 8.3 mm.




NSYEL166D8

Characteristics	References
Earth leads section 6 mm², length 160 mm	**NSYEL166D8**
Earth leads section 25 mm², length 350 mm	**NSYEL3525D8**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Ground Fastening


Front Connection
(Example: device enclosure W700 mm + compartment W300 mm)



Rear Connection D1000
(Example: device enclosure + compartment D500 + D500 mm)



Rear Connection D1300
(Example: device enclosure + compartment D800 + D500 mm)



- compulsory fixing point
- optional fixing point

8.8-class screws: Screw M10 TH
+ washers (external Ø 25 mm, thickness 3 mm)
+ CS contact washers Ø 10 mm.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT HD: Functional System


Dimensions

Enclosures


Profile



Cover Panels, Plain or Transparent Door, Lateral Panel




Standard Plinth




Gland Plates

W300




W700




Functional System in PrismaSeT HD Switchboards, Enclosure Mounting

D500, D600, D800




Busbars Mounting, Lateral Vertical Busbars


1600 A



2000



2500 A up to 4000 A



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN-SM: Steel Floor-Standing Enclosures

Introduction



Explore our extensive range of accessories and solutions designed to elevate your Electrical Distribution panel with our PanelSeT families.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Introduction



Lower Impact Approach

- CO_2 footprint reduction using low-carbon emission steel in PanelSeT SFN enclosures
- Recycled cardboard packaging



Flexibility

- Unlock greater flexibility with top busbar chamber providing more space in your SFN cubicle for the devices
- Comprehensive range of cover plates designed to enhance your ED enclosure experience with the FS modular chassis



Reability

- Compliant with IEC 61439-1 and 2 standard, technical guide provided with assembly recommendations to comply with the standard
- Integrated with Linergy systems, offering a versatile compatibility for your needs
- Use of high quality components to meet the requirements of heavy industry in terms of service life



Easy Mounting

- Designed for simplified assembly, for fast, efficient installation and seamless integration of modular equipment, and for integration of non-modular equipment using PanelSeT SFN accessories
- Easily combined side-by-side or back-to-back

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Modular Floor-Standing Enclosures



The accessories are installed on a chassis mounted at the front of the enclosure, such as:

- cover plates for enclosures with widths of 600 and 800 mm, solid or cut-out, screw-mounted or hinged. They enable 24 or 36 modules per row, depending on the width of the enclosure
- material support rails, fixed or with adjustable depth
- mounting plate supports for coupling non-modular equipment
- supports for fixing cable-distribution cable ducts
- the sum of the heights of all the covers that complete a chassis must be the height of the cabinet minus 200 mm

Sets of accessories made up of material-supporting frames with chassis and cover plates are offered for the construction of double or busbar modular chassis.
All accessories of the individual chassis system can also be combined in the same way with a double chassis or with a chassis with busbar area.

4


Modular Chassis

Single-Chassis Coupling Set

- Chassis made up of vertical uprights and horizontal crossbars:
- PanelSeT SFN: They are screwed to the front frame of the enclosure.
- PanelSeT SM: They are screwed to the front frame of the enclosure by means of vertical adaptation profiles, see page 527.
- Easy access to the inside for component installation.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Note:
Installation example: See page 205.

Supply:
2 vertical uprights, 2 horizontal crossbars and fixing elements



NSYCSH166


Characteristics	Maximum number of 18 mm modules	Height (mm)	Width (mm)	References
Single-chassis coupling set	216	1600	600	**NSYCSH166**
Single-chassis coupling set	324	1600	800	**NSYCSH168**
Single-chassis coupling set	240	1800	600	**NSYCSH186**
Single-chassis coupling set	360	1800	800	**NSYCSH188**
Single-chassis coupling set	288	2000	600	**NSYCSH206**
Single-chassis coupling set	432	2000	800	**NSYCSH208**

Double-Chassis Coupling Set

- Mounting on enclosures with widths of 1200 and 1600 mm.
- PanelSeT SFN: The double-door enclosure adaptation kit is required for enclosure widths of 1200 and 1600 mm, see page 521.
- PanelSeT SM: They are screwed to the front frame of the enclosure by means of the vertical adaptation profiles, see page 531.
  For enclosures with a width of 1200 mm the top/bottom adjustment rails are necessary.
- Set made up of two modular chassis with an intermediate central upright.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Note:
Installation example: See page 205.

Supply:
2 single-chassis coupling sets, 1 intermediate central upright and fixing elements




NSYDCSH2012

Characteristics	Maximum number of 18 mm modules	Set made up of columns with a width (mm)	Height (mm)	Width (mm)	References
Double-chassis coupling set	576	600 + 600	2000	600	**NSYDCSH2012**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Installation Examples

Combination of Cut-Out Screw-Mounted Cover Plates and Single-Chassis Coupling Set




Dimensions (mm)		Number of 18 mm modules	1 single-chassis coupling set	5 screwed-on cut-out cover plates	2 adjustment cover plates
H (A)	W (B)		References	References	References
1800	600	240	1 x **NSYCSH186**	5 x **NSYMUC306**	1 x **NSYADC16**

Single-Chassis Coupling Set



Combination of Cut-Out Screw-Mounted Cover Plates and Double-Chassis Coupling Set



Dimensions (mm)			Number of 18 mm modules	1 double-chassis coupling set	12 screwed-on cut-out 300 mm cover plates	Double-door enclosure adaptation kit
H (A)	W (B)	D (C)		References	References	References
2000	1200	500	576	1 x **NSYDCSH2012**	12 x **NSYMUC306**	**NSYSMP2D5**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Modular Floor-Standing Enclosures

Cover Plates

Screwed-On Plain Cover Plate

- Metal cover plates for protecting control devices.
- The cut-outs in non-modular control devices are at user's request.
- Suitable by modules of 150 or 200 mm.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Versions:
- Screwed-on plain cover plate,
- Hinged plain cover plate.
- 120° opening with flat hinge.

Supply:
1 plain cover plate and fixing elements


NSYMPC206

Characteristics	Height (mm) (A)	Width (mm) (B)	References
Screwed-on plain cover plate	150	600	**NSYMPC156**
Screwed-on plain cover plate	150	800	**NSYMPC158**
Screwed-on plain cover plate	200	600	**NSYMPC206**
Screwed-on plain cover plate	200	800	**NSYMPC208**
Screwed-on plain cover plate	300	600	**NSYMPC306**
Screwed-on plain cover plate	300	800	**NSYMPC308**
Screwed-on plain cover plate	400	600	**NSYMPC406**
Screwed-on plain cover plate	400	800	**NSYMPC408**
Screwed-on plain cover plate	450	600	**NSYMPC456**
Screwed-on plain cover plate	450	800	**NSYMPC458**
Screwed-on plain cover plate	600	600	**NSYMPC606**
Screwed-on plain cover plate	600	800	**NSYMPC608**

Hinged Plain Cover Plate

- Metal cover plates for protecting control devices.
- The cut-outs in non-modular control devices are at user's request.
- Suitable by modules of 150 or 200 mm.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray


Versions:
- Screwed-on plain cover plate,
- Hinged plain cover plate.
- 120° opening with flat hinge.

Supply:
1 plain cover plate and fixing elements


NSYMPCH206

Characteristics	Height (mm) (A)	Width (mm) (B)	References
Hinged plain cover plate	150	600	**NSYMPCH156**
Hinged plain cover plate	150	800	**NSYMPCH158**
Hinged plain cover plate	200	600	**NSYMPCH206**
Hinged plain cover plate	200	800	**NSYMPCH208**
Hinged plain cover plate	300	600	**NSYMPCH306**
Hinged plain cover plate	300	800	**NSYMPCH308**
Hinged plain cover plate	400	600	**NSYMPCH406**
Hinged plain cover plate	400	800	**NSYMPCH408**
Hinged plain cover plate	450	600	**NSYMPCH456**
Hinged plain cover plate	450	800	**NSYMPCH458**
Hinged plain cover plate	600	600	**NSYMPCH606**
Hinged plain cover plate	600	800	**NSYMPCH608**

Plain Cover Plates



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cover Plates

Screwed-On Cut-Out Cover Plate

- Cut-out metal cover plates for modular switchgear (1 module = 18 mm).
- Suitable by modules of 150 or 200 mm.
- Cover plates for 600 mm width enclosures: 24 modules per row,
- Cover plates for 800 mm width enclosures: 36 modules per row.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- To close the unoccupied DIN rail spaces, use the blanking plate **NSYATPUND**

Versions:
- Screwed-on cut-out cover plate,
- Hinged cut-out cover plate. 120° opening with flat hinge.

Supply:
1 cut-out cover plate and fixing elements



NSYMUC206

Characteristics	Maximum number of 18 mm modules	Number of cut-outs	Dimensions (mm)		References
			Height (A)	Width (B)	
Screwed-on cut-out cover plate	24	1	150	600	**NSYMUC156**
Screwed-on cut-out cover plate	36	1	150	800	**NSYMUC158**
Screwed-on cut-out cover plate	24	1	200	600	**NSYMUC206**
Screwed-on cut-out cover plate	36	1	200	800	**NSYMUC208**
Screwed-on cut-out cover plate	48	2	300	600	**NSYMUC306**
Screwed-on cut-out cover plate	72	2	300	800	**NSYMUC308**
Screwed-on cut-out cover plate	48	2	400	600	**NSYMUC406**
Screwed-on cut-out cover plate	72	2	400	800	**NSYMUC408**

Hinged Cut-Out Cover Plate

- Cut-out metal cover plates for modular switchgear (1 module = 18 mm).
- Suitable by modules of 150 or 200 mm.
- Cover plates for 600 mm width enclosures: 24 modules per row,
- Cover plates for 800 mm width enclosures: 36 modules per row.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- To close the unoccupied DIN rail spaces, use the blanking plate **NSYATPUND**

Versions:
- Screwed-on cut-out cover plate,
- Hinged cut-out cover plate. 120° opening with flat hinge.


Supply:
1 cut-out cover plate and fixing elements




NSYMUCH206

Characteristics	Maximum number of 18 mm modules	Number of cut-outs	Dimensions (mm)					References
			Height (A)	Width (B)	D	E	F	
Hinged cut-out cover plate	24	1	150	600	432	51.75	150	**NSYMUCH156**
Hinged cut-out cover plate	36	1	150	800	642	51.75	150	**NSYMUCH158**
Hinged cut-out cover plate	24	1	200	600	432	76.75	200	**NSYMUCH206**
Hinged cut-out cover plate	36	1	200	800	642	76.75	200	**NSYMUCH208**
Hinged cut-out cover plate	48	2	300	600	432	51.75	150	**NSYMUCH306**
Hinged cut-out cover plate	72	2	300	800	642	51.75	150	**NSYMUCH308**
Hinged cut-out cover plate	48	2	400	600	432	76.75	200	**NSYMUCH406**
Hinged cut-out cover plate	72	2	400	800	642	76.75	200	**NSYMUCH408**


Cut-Out Cover Plates




A = 150 and 200 mm



A = 300 and 400 mm



Screwed-On Cover Plate



Hinged Cover Plate

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Modular Floor-Standing Enclosures

Cover Plates

Adjustment Cover Plates

- Metal adjustment cover plates designed to complete the front of the modular chassis according to the combinations made by modules of 150 or 200 mm.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
2 adjustment cover plates and fixing elements


NSYADC16

Characteristics	Height (mm)	Width (mm)	References
Adjustment cover plates	50	600	**NSYADC16**
Adjustment cover plates	50	800	**NSYADC18**

Set of Fixed Rail with Supports


- Set made up of a galvanized symmetric DIN rail, 35 x 15 mm, and fixed mounting supports, for the installation of modular devices or not.
- Material: Zinc-coated steel
- Fixing: Mounting by screws directly on the uprights of the chassis-coupling set


Maximum number of 18 mm modules:
- Enclosure width 600 mm: 24 modules,
- Enclosure width 800 mm: 36 modules.

Supply:
1 DIN rail, 2 fixed supports and fixing elements


NSYMFSC60

Characteristics	Width (mm)	References
Set of fixed rail with supports	**600**	**NSYMFSC60**
Set of fixed rail with supports	**800**	**NSYMFSC80**





Set of Depth-Adjustable Rail with Supports

- Set made up of a galvanized symmetric DIN rail, 35 x 15 mm, and depth adjustable mounting supports, for the installation of modular devices or not.
- Material: Zinc-coated steel (mounting support)


Fixing: Mounting by screws directly on the uprights of the modular chassis-coupling set


Maximum number of 18 mm modules:
- Enclosure width 600 mm: 24 modules,
- Enclosure width 800 mm: 36 modules.

Supply:
1 DIN rail, 2 adjustable supports and fixing elements


NSYMFSC60D

Characteristics	Width (mm)	References
Set of depth-adjustable rail with supports	600	**NSYMFSC60D**
Set of depth-adjustable rail with supports	800	**NSYMFSC80D**





Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cover Plates

Cable Duct Fixing Supports


- Supports for fixing cable-distribution gutters in the modular chassis.
- Allows the fixing of gutters in horizontal and vertical position on the same plane to facilitate cable distribution.
- Material: Zinc-coated steel

Fixing: Installation by screws directly on the rail supplied with the fixed or adjustable rail

Supply:
6 supports (3 on the right and 3 on the left) and fixing elements

Characteristics	References
Cable duct fixing supports	**NSYMCDFIX**


NSYMCDFIX



Reinforced Plate Supports


- Supports for fixing the partial mounting plate for small non-modular equipment or material-supporting cross-rails for heavy equipment. See partial mounting plate, page 518.
- Material: Zinc-coated steel

Fixing: Direct fixing by screws to the vertical uprights of the modular chassis-coupling set and at the rear directly to the structure (PanelSeT SFN) and on universal or quick-fixing cross-rails (see page 525) installed vertically in the back of the enclosure (PanelSeT SM)

Supply:
2 supports and fixing elements

Characteristics	Number of cut-outs (Ø 5.2 mm)	Depth (mm)	References
Reinforced plate supports	16	600	**NSYMPS60**
Reinforced plate supports	24	800	**NSYMPS80**


NSYMPS60



Blanking Plate

- Blanking plate for full or partial covering of the circuit-breaker windows; it can easily be cut to the required size.
- Material: PVC (polyvinyl chloride)

Characteristics	Number of modules	Color	Length (mm)	References
Blanking plate	4	RAL 7035 gray	72	**NSYATP72M**
Blanking plate	24	RAL 7035 gray	432	**NSYATP24DTM**
Blanking plate	61	RAL 7035 gray	1100	**NSYATPUND**

NSYATP72M

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

MasterPacT Support

Introduction
Installation of a MasterPacT in a SFN switchboard requires:
- Lateral cross-rails (**NSYSQCR●●**, **NSYSUCR●●**) (See table below)
- 1 specific transversal MasterPacT support (**NSYFXMN●●**) fixed to the lateral cross-rails
- Bar supports to reduce bar movements due to constraints

MasterPacT Supports
Dedicated offer to shelter a MasterPacT circuit breaker and facilitate its positioning in the switchboard
- Less distortion
- Reduced installation time


PB503917

MasterPacT Supports W600

- Cut-outs already defined (availlable in the Schneider CAD library)
- Material: Galvanized steel
- Mounting instructions (screwdriver: T30, Tightening torque: 4.5 Nm/39.82 lb-in)

Supply:
1 support delivered with fixing elements (self tapping screws and cage nuts: M6)


NSYFXMNT60F

Characteristics	MasterPacT combination	References
MasterPacT MTZ1 and NT	Fixed	**NSYFXMNT60F**
MasterPacT MTZ1 and NT	Withdrawable	**NSYFXMNWT60FW**
MasterPacT MTZ2 and NW*	Fixed	**NSYFXMNWT60FW**
MasterPacT MTZ2 and NW*	Withdrawable	**NSYFXMNWT60FW**

* Only compatible for 3P. In case of 4P move to W800.

MasterPacT Supports W800

- Cut-outs already defined (availlable in the Schneider CAD library)
- Material: Galvanized steel
- Mounting instructions (screwdriver: T30, Tightening torque: 4.5 Nm/39.82 lb-in)

Supply:
1 support delivered with fixing elements (self tapping screws and cage nuts: M6)



NSYFXMNT80F

Characteristics	MasterPacT combination	References
MasterPacT MTZ1 and NT	Fixed	**NSYFXMNT80F**
MasterPacT MTZ1 and NT	Withdrawable	**NSYFXMNT80W**
MasterPacT MTZ2 and NW	Fixed	**NSYFXMNW80F**
MasterPacT MTZ2 and NW	Withdrawable	**NSYFXMNW80W**

Associated Cross-Rails

- Material: Zinc-coated steel

Supply:
2 cross-rails and fixing elements (see cross-rail section page 525 for more information)



NSYSUCR65●●

Characteristics	References
in MasterPacT combination: MTZ1 and NT	**NSYSUCR65●●**
in MasterPacT combination: MTZ2 and NW	**NSYSUCR90●●**

Associated Cross-Rails

- Material: Zinc-coated steel

Supply:
2 cross-rails and fixing elements (see cross-rail section page 525 for more information)


NSYSQCR65●●

Characteristics	References
in MasterPacT combination: MTZ1 and NT	**NSYSQCR65●●**
in MasterPacT combination: MTZ2 and NW	**NSYSQCR90●●**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

MasterPacT Support - Bar Supports

Supports for MasterPacT MTZ1 and NT

- Fixing by screw with hexagonal head.
- Material: Metal support: Zinc-coated steel, Isolating supports: thermosetting painting

Supply:
2 insulated bar supports,
1 metal horizontal support and fixing element


NSYBHNT600

Characteristics	Width (mm)	References
Fixed support	600	**NSYBHNT600**
Fixed support	800	**NSYBHNT800**

Supports for MasterPacT MTZ1 and NT

- Fixing by screw with hexagonal head.
- Material: Isolating supports: Thermosetting painting

Supply:
2 insulated bar supports and fixing elements


NSYBSA70

Characteristics	References
Free support	**NSYBSA70**

Supports for MasterPacT MTZ2 and NW

- Fixing by screw with hexagonal head.
- Material: Metal support: Zinc-coated steel, Isolating supports: thermosetting painting

Supply:
2 insulated bar supports,
1 metal horizontal support and fixing element


NSYBHNW600

Characteristics	Width (mm)	References
Fixed support	600	**NSYBHNW600**
Fixed support	800	**NSYBHNW800**

Supports for MasterPacT MTZ2 and NW

- Fixing by screw with hexagonal head.
- Material: Isolating supports: Thermosetting painting

Supply:
2 insulated bar supports and fixing elements


LVS04678

Characteristics	References
Free support	**LVS04678**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

Top Busbar Chamber


Top Busbar Chamber

- Chamber which shelters and supports the sets of horizontal bars.
- Enables new switchgear by tapping and isolates the sets of bars from the rest of the equipment.
- It is only installed at the top of the enclosure.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP55 according to IEC 60529

Supply:
One structure of the busbar chamber as a kit
Two front panels
Reinforced coupling kit
One sealing gasket


NSYTBCN366


Characteristics	Height (mm)	Width (mm) (B)	Depth (mm) (C)	References
Top busbar chamber	300	400	500	**NSYTBCN345**
Top busbar chamber	300	400	600	**NSYTBCN346**
Top busbar chamber	300	400	800	**NSYTBCN348**
Top busbar chamber	300	600	500	**NSYTBCN365**
Top busbar chamber	300	600	600	**NSYTBCN366**
Top busbar chamber	300	600	800	**NSYTBCN368**
Top busbar chamber	300	800	500	**NSYTBCN385**
Top busbar chamber	300	800	600	**NSYTBCN386**
Top busbar chamber	300	800	800	**NSYTBCN388**
Top busbar chamber	300	1000	500	**NSYTBCN3105**
Top busbar chamber	300	1000	600	**NSYTBCN3106**
Top busbar chamber	300	1000	800	**NSYTBCN3108**
Top busbar chamber	300	1200	500	**NSYTBCN3125**
Top busbar chamber	300	1200	600	**NSYTBCN3126**
Top busbar chamber	300	1200	800	**NSYTBCN3128**



Side Panels for the Top Busbar Chamber

- Set of two side panels for coupling with the busbar chamber.
- Captive screws.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
Two side panels and fixing elements


NSYSPBCN35

Characteristics	Depth (mm)	References
Side panels for the top busbar chamber	500	**NSYSPBCN35**
Side panels for the top busbar chamber	600	**NSYSPBCN36**
Side panels for the top busbar chamber	800	**NSYSPBCN38**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

Busbar Cubicle

Busbar Cubicle

- Shelters and supports the sets of vertical bars.
- Enables new switchgear by tapping and isolates the sets of bars from the rest of the equipment.
- It can be installed on either of the two sides of the enclosure.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP55 according to IEC 60529
- UL-certified (cULus): Rating according UL50E: Type 1,12 AND 3R

Supply:
One structure of the busbar cubicle
One roof
One rear panel
One door with handle (5 mm DB lock)



NSYSFN18440


Characteristics	Height (mm)	Width (mm)	Depth (mm)	References
Busbar cubicle	1800	400	400	**NSYSFN18440**
Busbar cubicle	1800	400	500	**NSYSFN18450**
Busbar cubicle	1800	400	600	**NSYSFN18460**
Busbar cubicle	2000	300	500	**NSYSFN20350**
Busbar cubicle	2000	300	600	**NSYSFN20360**
Busbar cubicle	2000	300	800	**NSYSFN20380**
Busbar cubicle	2000	400	400	**NSYSFN20440**
Busbar cubicle	2000	400	500	**NSYSFN20450**
Busbar cubicle	2000	400	600	**NSYSFN20460**
Busbar cubicle	2000	400	800	**NSYSFN20480**
Busbar cubicle	2200	400	600	**NSYSFN22460**

4

Side Panels for the Busbar Cubicle

- Set of 2 side panels fixed to the outside.
- Captive screws.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
Two side panels with external fixing and fixing elements



NSY2SPN184

Characteristics	Height (mm)	Depth (mm)	References
Side panels	1800	400	**NSY2SPN184**
Side panels	1800	500	**NSY2SPN185**
Side panels	1800	600	**NSY2SPN186**
Side panels	2000	400	**NSY2SPN204**
Side panels	2000	500	**NSY2SPN205**
Side panels	2000	600	**NSY2SPN206**
Side panels	2000	800	**NSY2SPN208**
Side panels	2200	600	**NSY2SPN226**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

Vertical Bar Support


Vertical Bar Support


- Support prepared for fixing bars in vertical position, mounted directly on the structure of the enclosure. Adjustable height with a pitch of 25 mm.
- For a nominal rating In ≥ 3000 A and ≤ 4000 A, you add one spacer ref. **LVS04646**.

Supply:
2 insulated bar supports,
1 metal vertical support and fixing elements


NSYBVS400

Characteristics	Width / Depth (B) (mm)	References
Vertical bar support	400	**NSYBVS400**
Vertical bar support	500	**NSYBVS500**
Vertical bar support	600	**NSYBVS600**
Vertical bar support	800	**NSYBVS800**
Vertical bar support for 115 mm pitch	800	**NSYBVS800L**




PB500073_39_nb


Setting Support


- Bottom support for bars in vertical position.
- It is fixed to the bottom frame of the enclosure.
- It is required for supporting the bars.
- It is not considered a bar support when calculating the number of supports

Supply:
1 insulated bar support,
1 metal vertical support and fixing elements


NSYAS500

Characteristics	Width / Depth (B) (mm)	References
Setting support	500	**NSYAS500**
Setting support	600	**NSYAS600**
Setting support	800	**NSYAS800**
Setting support for 115 mm pitch	800	**NSYAS800L**




PB500930_32_nb

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Horizontal Bar Support

Horizontal Bar Support


- Support prepared for fixing bars in horizontal position.
- Direct mounting to the structure of the enclosure, on the vertical uprights, at any height, adjustable with a pitch of 25 mm.
- For a nominal rating I_n ≥ 3000 A and ≤ 4000 A, you add one spacer ref. **LVS04646**.


Supply:
2 insulated bar supports,
1 metal horizontal support and fixing elements



NSYBHS500

Characteristics	Width / Depth (B) (mm)	References
Horizontal bar support	500	**NSYBHS500**
Horizontal bar support	600	**NSYBHS600**
Horizontal bar support	800	**NSYBHS800**
Horizontal bar support for 115 mm pitch		**NSYBHS800L**





PB500932_34_nb

Bar Support Arm

- Used to maintain the distance between bars, whether vertical or horizontal.
- No need to attach to the enclosure.
- It is used on bars in both vertical and horizontal position.
- For a nominal rating I_n ≥ 3000 A and ≤ 4000 A, you add one spacer ref. **LVS04646**.

Supply:
2 insulated bar supports and fixing elements



NSYBSA

Characteristics	Width / Depth (B) (mm)	References
Bar support arm	500 / 600 / 800	**NSYBSA**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

Vertical Bar Support

Sigma Safety Terminals

- Safety terminals made from self-extinguishing Polyamide-6, with matt black base, MS-58 brass terminal (DIN 17660), tempered, zinc-plated and dichromated steel ring, and cover made from orange-colored self-extinguishing polypropylene.
- Anti-shearing: The connection is made by means of a tightening mechanism which distributes the pressure across the entire contact surface, limiting friction and occasional stress that can damage the conductors.
- The ring that surrounds the brass body helps prevent the pressure exerted by the actual conductors from opening the terminal and loosening the connection.
- All SIGMA "S" terminals are supplied with a terminal-covering cap, that helps prevent accidental contact with live parts. All the gauges can be coupled together, forming strips of any length. Operating voltage: 500 V.



Note:
Each terminal accepts up to 2 conductors with the specified section.
20 units
(except for ref. **NSYS95100**: 10 units)


NSYS16

Characteristics	Section (mm²)	A	B	C	D	E	References
Sigma safety terminals	1 x 4	30	20	13	21	4	**NSYS04**
Sigma safety terminals	1 x 6	33	25	16	24	7	**NSYS06**
Sigma safety terminals	1 x 10	38	28	16	28	6	**NSYS10**
Sigma safety terminals	1 x 16	42	32	19	32	9	**NSYS16**
Sigma safety terminals	1 x 35	46	38	23	34	11	**NSYS2535**
Sigma safety terminals	1 x 50	52	45	27	40	15	**NSYS50**
Sigma safety terminals	1 x 70	55	50	30	40	15	**NSYS70**
Sigma safety terminals	1 x 100	58	54	33	40	20	**NSYS95100**

Earthing Strips

- For the junction of neutral and earth cables.
- Models **NSYRBL●●** (Fig. 3) for installation in boxes with insulated rear or by means of insulators, not supplied.

Supply:
10 earthing strips

Fig. 3











NSYRBL21656M

Characteristics	Number of terminals x section	Fig	References
Earthing strips	2 x 16 mm² + 5 x 6 mm²	3	**NSYRBL21656M**
Earthing strips	2 x 16 mm² + 8 x 6 mm²	3	**NSYRBL21686M**
Earthing strips	2 x 16 mm² + 14 x 6 mm²	3	**NSYRBL216146M**
Earthing strips	2 x 16 mm² + 29 x 6 mm²	3	**NSYRBL216296M**




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Power Busbars

Linergy LGYE - Horizontal Profiles up to 4000 A

Installation in PanelSeT SFN		Up to 1600 A					Up to 4000 A			
Linergy profiles, 2000 mm length										
		630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
Permissible current for an ambient temperature of 35 °C around the switchboard	IP > 31	530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Number of profiles per phase		1								
Height available (mm)		150					150		200	
References		LVS04560	LVS04561	LVS04562	LVS04563	LVS04564	LVS04565	LVS04566	LVS04567	LVS04568
Busbar supports		 Fixed Support **NSYBHS●●**			 Free Support **NSYBSA**					
Number of supports depending on Icw (kA rms/1 s)	⩽ 15	2 x **NSYBHS●●** *								
	⩽ 25	2 x **NSYBHS●●** *								
	⩽ 30	2 x **NSYBHS●●** *								
	⩽ 40	-		2 x **NSYBHS●●** *						
	⩽ 50	-			2 x **NSYBHS●●** *					
	⩽ 60	-			2+1 **		2 x **NSYBHS●●** *			
	⩽ 65	-				2+1 **				
	⩽ 75	-				2+1 **				
	⩽ 85	-				2+1 **				
	⩽ 100	-					2+4 ***			
References Fixed support		**NSYBHS●●**							**NSYBHS●●** + **LVS04646**	
References Free support		**NSYBSA**							**NSYBSA** + **LVS04646**	

* If spacing between supports > 800 mm add 1 **NSYBSA** free support.
** If spacing between supports > 300 mm add 1 **NSYBSA** free support.
*** If spacing between supports > 135 mm add 1 **NSYBSA** free support.

Joints	Up to 1600 A					Up to 4000 A			
	630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
References (3P)	3x **LVS04620**					3x **LVS04621**		3x **LVS04623**	
References (4P)	4x **LVS04620**					4x **LVS04621**		4x **LVS04623**	
	 **LVS04620**					 **LVS04621**		 **LVS04623**	

⚠⚠ DANGER

RISK OF ARC FLASH

- 2 fixed supports for PrismaSeT HD Active 700 wide frame are compulsory.
- 1 fixed support for 300/400 wide frame are compulsory.

If more supports are needed, add free supports.

Failure to follow these instructions will result in death or serious injury.

NOTICE

INSULATED SHIELD INSTALLATION

If insulation clearance < 20 mm add an insulated shield between the busbar and the metal part of the cabinet.

Failure to follow these instructions can result in equipment damage.



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures




Accessories for Low Voltage Switchboards

Power Busbars

Linergy BS - Horizontal Busbars up to 4000 A

Installation in PanelSeT SFN		Up to 1600 A				Up to 4000 A					
Copper without holes, 2000 mm length											
Permissible current for an ambient temp. of 35 °C around the switchboard	IP > 31	750 A	900 A	1250 A	1600 A	1600 A	1800 A	2000 A	2500 A	2900 A	3340 A
Size of bars (mm)		60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10	120 x 10
Number of bars per phase		1	1	2	2	1	2	2	2	2	2
Height available (mm)		150									200
References		**LVS04536**	**LVS04538**	**LVS04536**	**LVS04538**	**LVS04548**	**LVS04545**	**LVS04546**	**LVS04548**	**LVS04550**	**LVS04552**
Busbar supports		 Fixed Support **NSYBHS●●**				 Free Support **NSYBSA**					
Number of supports depending on Icw (kA rms/1 s)	⩽ 15	2 x **NSYBHS●●** *									
	⩽ 25	2+1 **	2 x **NSYBHS●●** *								
	⩽ 30	2+1 **		2 x **NSYBHS●●** *							
	⩽ 40	2+1 **				2 x **NSYBHS●●** *					
	⩽ 50	-	2+1 **					2 x **NSYBHS●●** *			
	⩽ 60	-				2+1 **					
	⩽ 65	-				2+1 **					
	⩽ 75	-				2+4 ***	2+1 **				
	⩽ 85	-				-		2+1 **			
References Fixed support		**NSYBHS●●**									**NSYBHS●●** + **LVS04646**
References Free support		**NSYBSA**									**NSYBSA** + **LVS04646**

* If spacing between supports > 800 mm add 1 **NSYBSA** free support.
** If spacing between supports > 300 mm add 1 **NSYBSA** free support.
*** If spacing between supports > 135 mm add 1 **NSYBSA** free support.

Joints Installation dans PanelSeT SFN	Up to 1600 A				Up to 4000 A					
	1 vertical bar per phase		2 vertical bars per phase		1 vert. bar per phase	2 vertical bars per phase				
Size of bars (mm)	60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10	120 x 10
References	**LVS04640**	**LVS04641**	**LVS04640**	**LVS04641**	**LVS04641**	**LVS04640**	**LVS04640**	**LVS04641**	**LVS04641**	**LVS04643**
Sliding joints with torque nut	 **LVS04640**			 **LVS04641**						

⚠⚠ DANGER

RISK OF ARC FLASH

- 2 fixed supports for PrismaSeT HD Active 700 wide frame are compulsory.
- 1 fixed support for 300/400 wide frame are compulsory.









If more supports are needed, add free supports.

Failure to follow these instructions will result in death or serious injury.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Power Busbars

Linergy LGY - Lateral Profiles up to 1600 A

Installation in PanelSeT SFN		L 300				
		 DD381233_LIN_7_nb 630 A	 DD381234_LIN_7_nb 800 A	 DD381235_LIN_7_nb 1000 A	 DD381236_LIN_7_nb 1250 A	 DD381237_LIN_7_nb 1600 A
Permissible current for an ambient temp. of 35 °C around the switchboard	IP ⩽ 31	590 A	760 A	950 A	1170 A	1480 A
Number of profiles per phase		1				
References		**LVS04502**	**LVS04503**	**LVS04504**	**LVS04505**	**LVS04506**
Busbar supports		 DD380741_LIN_nb  DD380742_LIN_12_nb Fixed Support **LVS04651**				
 DD385383_nb 387.5 mm max. 700 mm max. 700 mm max.						
Number depending on I_{cw} (kA rms/1 s)	⩽ 25	3				
	⩽ 30	-	3			
	⩽ 40	-		3		
	⩽ 50	-			4	
	⩽ 60	-			5	
	⩽ 65	-				5
	⩽ 75	-				7
Only for enclosures with a depth ≥ 500 mm	⩽ 85	-				8
References		**LVS04651** + upright adapters **NSYSFPAED** + **NSYSUCR40●●**				
Connections to the Linergy BS horizontal busbar		 DD385409_nb **Note:** Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase.				
References according to horizontal busbar size	**5 mm thick**	**LVS04634**			**LVS04635**	
	10 mm thick **Width ⩽ 80 mm**	**LVS04636**				
	10 mm thick **Width > 80 mm**	**LVS04636** + **LVS04642** **LVS04638** + **LVS04642**				
Connections to the Linergy LGYE horizontal busbar		 DD385387_nb **Note:** Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase. ⩽ 1600 A				
References (vertical connection)		**LVS04602**				
References (vertical shifted connection)		**LVS04603**				

NOTICE

FITTING OF END STOP

An end stop must be fitted on the bottom support: **LVS01109** (sold in lots of 12).

Failure to follow these instructions can result in equipment damage.







Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN-SM: Steel Floor-Standing Enclosures

Accessories for Low Voltage Switchboards

Power Busbars


Linergy LGYE - Lateral Profiles up to 4000 A

Installation in PanelSeT SFN		L 300								
Linergy profile, 2000 mm length										
		630 A	**800 A**	**1000 A**	**1250 A**	**1600 A**	**2000 A**	**2500 A**	**3200 A**	**4000 A**
Permissible current for an ambient temperature of 35 °C around the switchboard	IP > 31	530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Number of profiles per phase		1								
Height available (mm)		150					150		200	
References		**LVS04560**	**LVS04561**	**LVS04562**	**LVS04563**	**LVS04564**	**LVS04565**	**LVS04566**	**LVS04567**	**LVS04568**
Busbar supports										
		Fixed Support **NSYBVS●●**			Free Support **NSYBSA**		Bottom Support **NSYAS●●**			
		3 fixed supports are compulsory to hold the busbar in position. If more than 3 supports are needed, use free supports (in addition).								
										
Number depending on I_{cw} (kA rms/1 s)	⩽ 30	3								
	⩽ 40	-		3+2 *			3			
	⩽ 50	-			3+2 *		3			
	⩽ 60	-			3+2 *				3	
	⩽ 65	-				3+2 *				
	⩽ 75	-				3+4 **			3+2 *	
	⩽ 85	-				3+4 **				
	⩽ 100	-						3+6 ***		
References Fixed support		**NSYBVS●●**							**NSYBVS●●** + **LVS04646**	
References Bottom support		**NSYAS●●**							**NSYAS●●** + **LVS04646**	
References Free support		**NSYBSA**							**NSYBSA** + **LVS04646**	
		* If spacing between supports > 400 mm add 1 **NSYBSA** free support. ** If spacing between supports > 250 mm add 1 **NSYBSA** free support. *** If spacing between supports > 130 mm add 1 **NSYBSA** free support.								
Wedging busbars in position										
		Wedge Fitted on Bottom Support					Wedge Fitted on Bottom Support			
		The bottom support **NSYAS●●** + **LVS0465●** is used to place profiles in the correct position. It is not considered to be a busbar support.								
References		**LVS04658** (set of 12 wedges)					**LVS04659** (set of 12 wedges)			
Connections to the Linergy LGYE horizontal busbar		2000/2500 A							3200/4000 A	
										
		Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase.								
References (short connection)		**LVS04604**							**LVS04607**	
References (long connection)		**LVS04605**								

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Power Busbars

Linergy BS - Lateral Flat Busbars up to 3200 A

Installation in PanelSeT SFN		Up to 1600 A				Up to 3200 A						
Pre-slotted copper, 1675 mm length												
Permissible current for an ambient temp. of 35 °C around the switchboard	IP > 31	750 A	900 A	1250 A	1600 A	1080 A	1250 A	1600 A	1850 A	2000 A	2500 A	2820 A
Busbar cross-section (mm)		60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10
Number of profiles per phase		1		2		1			2			
References		LVS04516	LVS04518	LVS04516	LVS04518	LVS04525	LVS04526	LVS04528	LVS04525	LVS04526	LVS04528	LVS04550

Busbar supports



Fixed Support **NSYBVS●●**




Free Support **NSYBSA**



Bottom Support **NSYAS●●**

3 fixed supports are compulsory to hold the busbar in position.
If more than 3 supports are needed, use free supports (in addition).
The bottom wedge support is used to place the busbar in the correct position.
It does not count as a busbar support.





Number of supports depending on I_{cw} (kA rms/1 s)												
	≤ 15	3 *										
	≤ 25	3+2 *			3 *							
	≤ 30	3+2 *									3 *	
	≤ 40	3+4		3+2 *								
	≤ 50		3+4			3+2 *						
	≤ 60					3+4					3+2 *	
	≤ 65					3+4					3+2 *	
	≤ 75						3+6		3+4			
	≤ 85									3+4		

References Fixed support	NSYBVS●●
References Bottom support	NSYAS●●
References Free support	NSYBSA


* If spacing between supports > 350 mm add 1 **NSYBSA** free support.

Connections to the Linergy BS horizontal busbar






Staggered assembly points between one bar and the next, to maintain the necessary clearance distances.(3)




References **LVS04636**, **LVS04637**, **LVS04638** are supplied individually: 1 connection per phase.
Reference **LVS04642** consists of 2 M8 x 140 screws which can replace the original M8 x 120 screws.

		1 bar per phase		2 bars per phase		1 bar per phase			2 bars per phase			
		60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10	100 x 10
References depending on horizontal busbar size	Width ≤ 80 mm	LVS04645				LVS04636		LVS04637				LVS04645
	Width > 80 mm	LVS04645				LVS04636 + LVS04642		LVS04637 + LVS04642				LVS04645

(1) Drill Hole Dimensions for 5 mm Thick Horizontal Busbars



Drill Hole Dimensions for 10 mm Thick Horizontal Busbars



⚠⚠ DANGER

RISK OF ELECTRIC SHOCK, ARC FLASH AND HUMAN SAFETY

For a busbar with 75 mm distance between bars, the bars must be completely covered.

Failure to follow these instructions will result in death or serious injury.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN-SM: Steel Floor-Standing Enclosures


Accessories for Low Voltage Switchboards

PE Conductor

Linergy TB










Characteristics		PE conductor						
		Vertical PE conductor with Linergy LGY profile (W = 1670 mm)			Vertical PE conductor with Linergy BS busbar (W = 1675 mm)		Horizontal PE conductor with Linergy BS busbar	
Rated short-time current	(Isc)	≤ 65	> 65... ≤ 80	= 100	≤ 40	> 40	≤ 40	> 40
Permissible current	(A)	630	800	1250	-	-	-	-
Bar size	(mm)	-	-	-	25 x 5	50 x 5	25 x 5	50 x 5
Characteristics		-	-	-	Drilled flat bar Ø10.6 mm (one 10.6 mm hole every 25 mm along the entire length)	Drilled flat bar Ø10.6 mm (two 10.6 mm hole every 25 mm along the entire length)	-	-
References		LVS04502	LVS04503	LVS04505	LVS04512	LVS04515	LVS04512	LVS04512

Connection Between PE Conductors



LVS04672



LVS04766



Characteristics	Composition	References
Connection plates for horizontal/vertical PE bars	2 copper angle brackets	**LVS04672**
Linergy connection hardware	20 M8 screws (W = 25 mm) + 20 nuts + 20 contact washers for connection to cable lugs or flexible bars	**LVS04766**

PEN Conductor


LVS04656



Characteristics	References
Linergy TB PEN installation kit with LGY vertical profile	**LVS04656**
1600-A connection 10-mm horizontal busbar with Linergy LGY profile	**LVS04636**
Linergy LGYE vertical connection 1600 A	**LVS04602**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Insulated Flexible Bars

Connection Between Device and Busbars

- The flexible bars are determined taking into account the connected device, whatever the internal temperature of the switchboard.
- The bar sizes indicated below take into account the derating curves of devices.
- Width: 1800 mm
- Rated insulation voltage (Ui): 1000 V
- Maximum withstand temperature for the insulated material: 125 °C



04742

Characteristics	Size (mm)	References
NSX100	20 x 2	**LVS04742**
NSX160/250	20 x 3	**LVS04743**
NSX400	32 x 5	**LVS04751**
NSX630	32 x 8	**LVS04753**
FM 200 A Linergy	20 x 3	**LVS04743**
FC 3P Linergy	32 x 8	**LVS04753**
FC 4P Linergy	32 x 8	**LVS04753**
Fupact 250	24 x 5	**LVS04746**
Fupact 400	32 x 5	**LVS04751**
Fupact 630	32 x 8	**LVS04753**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PLA, SFN and SM: Floor Standing Enclosures

IEC 61439-2 Certification

PanelSeT SFN Assemblies with IEC 61439-2 Certification

Introduction

Because low-voltage switchboards must comply with the IEC 61439-2 standard, we have tested the most unfavorable and the most representative configurations (§ 10.10.2 of IEC 61439-1 ed2 2011) ranging up to 4000 A. We cover the entire product range, based on the PanelSeT SFN universal assembly system, enabling you to comply with the requirements of the standard.

To meet continuity of service and electrical safety requirements, we provide certificates based on assemblies tested by an independent third-party organization in accordance with IEC 61439-2. These certificates are based on commonly used configurations and provide verified, reliable, and practical information to support the design and completion of your switchboard.

These tests cover the entire PanelSeT SFN range of dimensions and supplement our range of tested PrismaSeT HD enclosures based on the functional unit system of PrismaSeT, and PanelSeT SFN MCC for fixed MCC applications.

PanelSeT PLA Assembly with IEC 61439-1 and 2 Certification

A specific architecture of PanelSeT PLA suitable for applications as EV charging station has been certified with IEC 61439-1 and 2 for 630 A and 1600 A.
The solution was certified as a full assembly including a PanelSeT PLA polyester floor-standing enclosure with DLP chassis, thermal management and Schneider Electric devices.
Choosing a polyester enclosure offers multiple advantages for outdoor and public areas, such as Class II insulation, fire resistance and corrosion resistance.



Compatibility table

Quantity	Dimensions			Intensity (A)	
	Height (mm)	Width (mm)	Depth (mm)	≤ 630 A	≤ 1600 A
1	1250	1250	420	●	
3	2000	750	420	●	●

The tests were carried out with one configuration, it is necessary to build a similar solution to obtain the same electrodynamic constraints and heat dissipation for the certification to be valid.

630 A

Mandatory references:

- PanelSeT PLA: Dimensions 1500 x 1250 x 420mm
- 2x Fans : **NSYCVF550M230FB**
  with IP55 filters: **NSYCAF190**
- 2x Outlet grille (one in each side): **NSYCAG291LPF**
- Heavy duty ventilated canopy: **NSYPCVR124HD**
- In case of completely sealed PLA: **NSYTJPLA124G**
- Modular chassis: **NSYDLP264G**
- Internal door: **NSYPAPLA155G**

1600 A

Mandatory references:

- 3x PanelSeT PLA: Dimensions 2000 x 750 x 420mm
- 3x Fans : **NSYCVF550M230FB**
  with IP55 filters: **NSYCAF190**
- 2x Outlet grille (one in each side): **NSYCAG291LPF**
- 2x Coupling PLA kit: **NSYMUPLA204G**
- 3x Heavy duty ventilated canopy: **NSYPCVR74HD**
- 3x In case of completely sealed PLA: **NSYTJPLA74G**
- Modular chassis: **NSYDLP165G**
- 3x plinth: **NSYZA274G**

The test for the certification have been performed with one configuration. Please contact your SE teams for more information on this configuration.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IEC 61439-2 Certified Assemblies

Compatibility table

Dimensions			Intensity (A)				
Height (mm)	Width (mm)	Depth (mm)	≤ 800 A	≤ 1250 A	≤ 1600 A	≤ 2500 A	≤ 4000 A
1200	600	400	●				
	600	600	●				
	800	400	●				
	800	600	●				
1400	600	400	●	●			
	800	400	●	●			
1600	600	600	●	●			
	600	800	●	●			
	800	600	●	●			
	800	800	●	●			
1800	600	400	●	●	●		
	600	500	●	●	●		
	600	600	●	●	●	●	
	600	800	●	●	●	●	
	800	400	●	●	●		
	800	500	●	●	●		
	800	600	●	●	●	●	
	1000	400	●	●	●		
	1000	500	●	●	●		
	1000	600	●	●	●	●	
	1200	400	●	●	●		
	1200	500	●	●	●		
	1200	600	●	●	●	●	
2000	600	400	●	●	●		
	600	500	●	●	●		
	600	600	●	●	●	●	
	600	800	●	●	●	●	●
	800	400	●	●	●		
	800	500	●	●	●		
	800	600	●	●	●	●	
	800	800	●	●	●	●	●
	1000	400	●	●	●		
	1000	500	●	●	●		
	1000	600	●	●	●	●	
	1000	800	●	●	●	●	●
	1200	400	●	●	●		
	1200	500	●	●	●		
	1200	600	●	●	●	●	
	1200	800	●	●	●	●	●
	1600	400	●	●	●		
	1600	500	●	●	●		
	1600	600	●	●	●	●	
2200	600	600	●	●	●	●	
	600	800	●	●	●	●	●
	800	600	●	●	●	●	
	800	800	●	●	●	●	●
	1000	600	●	●	●	●	
	1200	600	●	●	●	●	
	1200	800	●	●	●	●	●

●: Certified dimensions for indicated intensity



How to assemble a PanelSeT SFN switchboard
(Implementation of the standard IEC 61439) Technical guide
Ref: UEMKTG002EN

IEC 61439-2 certification (IECEE CB scheme issued by DEKRA) is valid only once installation has been carried out, according to the recommendations indicated in the technical guide, "how to assemble a PanelSeT SFN switchboard", with the Schneider Electric devices featured in this guide.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DM-S3DB: Steel Wall-Mounted Enclosures

Introduction



Vertical Position

Horizontal Position

S3DM:
Enclosure for Modular Switchgear installation with cable gland plates at the top and bottom. It can be equipped with:
- Modular chassis (NSYDLM•••) with cut-out front plates for 24 to 234 modules according to the dimensions and references.
- 6 mm² earth connection placed between the body and the door.

S3DB:
Ready to be equipped with terminal blocks, a ladder mounting plate and a symmetrical DIN rail (to be ordered separately).
The body does not have cable gland openings.
The PanelSeT S3DB enclosure is the ideal coupling enclosure with FL21 cut-outs.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DM-S3DB: Steel Wall-Mounted Enclosures

Introduction

S3DM:



Easily Removable and Reversible Door


- With 20 mm return with double thickness granting excellent rigidity, opening to 120°, equipped with 2 or 3 invisible hinges
- Three locking points for heights of more than 600 mm
- Perforated rails on the hinge side of the door, with drill holes with a diameter of 4.2 mm in steps of 25 mm



Dedicated Accessories

- The DLM modular chassis consists of metal cut-out front panels which can clip on with any screws
- Rigid structure made from galvanized steel. The depth of the chassis can be adjusted from 40 to 85 mm between the rail and the front panel, allowing the installation of all types of devices
- For enclosures with a depth of 150 mm, the chassis can be installed at the front or on the backstuds at the rear. It is possible to adjust its depth using the adjustable supports (NSYSDCR●● type)
- It can also be equipped with a plain mounting plate, see page 509

S3DB:



Enhanced Safety

Welded studs on door and body
(earth cables to be ordered separately)



Smart

Example of installation with the ladder mounting plate

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DM: Steel Wall-Mounted Enclosures

Characteristics

Supply:
Wall-mounted enclosure supplied with 3-mm double-bar lock as standard


PanelSeT S3DM




- Single-piece body, folded and welded.
- Front rail with double sheet thickness, gutter-shaped.
- 4 M8 x 25 mm shouldered backstuds for installing chassis and step slides, leaving a space of 10 mm behind them.
- Cable gland plate (245 x 80) at the top and bottom of the enclosure, enabling the maximum access surface (also available in plain door).
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP66 according to IEC 60529
- Mechanical protection rating: IK08 according to IEC 62262

Height (mm)	Width (mm) (B)	Depth (mm) (C)	References
400	300	150	**NSYS3DM4315T**
500	400	150	**NSYS3DM5415T**
600	400	150	**NSYS3DM6415T**
600	600	150	**NSYS3DM6615T**
700	500	150	**NSYS3DM7515T**
800	600	150	**NSYS3DM8615T**
1000	600	150	**NSYS3DM10615T**
1000	800	150	**NSYS3DM10815T**


Dimensions



B: Enclosure width
C: Enclosure depth



Front panel cut-out (see table below)



Detail A

1 Front face of the modular chassis / front face of the door
2 Cable gland plates at the top and bottom of the enclosure.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DB: Steel Wall-Mounted Enclosures

Characteristics


PanelSeT S3DB



Body	Single-piece body, folded and welded. Front rail with double sheet thickness, guttershaped. • Depth 150 mm: The terminal enclosure can be installed vertically (width becoming height, and vice versa) • Wall-mounted directly or by means of fixing lugs (to be ordered separately). • 4 M8 x 25 shouldered backstuds. • Body without cable gland openings.
Door	• Easily removable and reversible door, with 20 mm return with double sheet thickness granting excellent rigidity; equipped with 2 hinges opening to 180°. • Door opening to more than 180° for maximum accessibility (the door comes to rest on the body of the enclosure in top position). • Maximum acceptable load on the door: 20 kg/m². • Wall-mounted enclosure supplied with 3-mm double-bar lock as standard. • M6 x 16 earthing screw for equipotential connection between the door and the body of the enclosure.
Dedicated accessories	The terminal enclosure, with a depth of 150 mm, can be equipped: • With 2 rails to be installed on the 4 M8 x 25 shouldered backstuds. • With a symmetrical rail to be installed on the rails. • With a 6 mm² earth braid to be placed between the body and the door. • It can also be equipped with a plain mounting plate, see page 509.
Finish	• Structured finish, epoxy polyester powder
Color	• RAL 7035 gray
Protection and Standards	• IP66 according to IEC 60529 • Mechanical protection rating: IK10 according to IEC 62262

Height (mm)	Width (mm)	Depth (mm)	References
250	300	150	**NSYS3DB25315**
250	400	150	**NSYS3DB25415**
250	500	150	**NSYS3DB25515**
300	400	150	**NSYS3DB3415**
300	500	150	**NSYS3DB3515**
300	600	150	**NSYS3DB3615**
400	800	150	**NSYS3DB4815**
600	400	150	**NSYS3DB6415**

Dimensions



A: Enclosure height
B: Enclosure width
C: Enclosure depth

1. With ladder mounting plate installed.
2. M6 x 17.5 mm earthing stud.
3. Stud center-to-center distance.
4. Center-to-center distance of the holes for direct fixing.
5. Drop-leaf door.

The dimensions provided include the ladder mounting plate which is the most commonly used accessory with this enclosure.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Introduction



The PanelSeT SFN system of enclosures with fixed compartments for Motor Control Centers (MCCs) is based on the standard PanelSeT SFN range. It offers the same functions and advantages, including:

- Multiple configuration options (side-by-side or back-to-back)
- Built-in partial doors and panels providing the required degree of protection
- Time savings during all assembly phases
- High enclosure robustness

PanelSeT SFN enclosures can host MCC compartments in industrial environments (IP54) thanks to a complete set of dedicated accessories and solutions, such as:

- Lynergy distribution systems
- Motor starter solutions
- Partial doors and front fixing panels
- Partitioning accessories for various forms

These solutions are tested with device characteristics to help ensure a high level of operational reliability. PanelSeT SFN supports the installation of motor starters up to 250 kW and can be configured to meet specific project requirements, with support from Schneider Electric customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Introduction




Lower Impact Approach

- CO_2 footprint reduction using low-carbon emissions steel
- Recycled cardboard packaging



Flexibility

- Compatible with PanelSeT SFN and PrismaSeT HD to combine power distribution, automation and motor control in the same switchboard
- Unrivaled number of possible combinations thanks to kits model and PanelSeT customization services



Enhanced Reliability

- Compliant with IEC 61439-1 and 2 standards: enabling to host motor starters up to 250 kW
- Certified with Linergy busbars up to form 4b partitioning
- Use of high quality components and appropriate design to meet the requirements of heavy industry in terms of service life



Easy Mounting

- Designed for streamlined mounting, enabling quick and efficient installation of the motor protection functional units
- Easily combined side-by-side or back-to-back

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Characteristics

Characteristics	PanelSeT SFN - Compartmentalized Enclosures for MCC
	Image 07 
	• PanelSeT SFN MCC system based on PanelSeT SFN range. • Same functions: multiple configurations (side-by-side/back-to-back), partial doors/panels for required protection • Same benefits: faster assembly, robust enclosures.
General data	• Applications: MCC • Standards: IEC 61439-2 • Installation: Indoor
Mechanical data	• Cable inlet: Top / Bottom • Access: Front / Rear Side • IP 54 and IK10 • Form: 4b type 7 • Withdrability: FFF • Dimensions: H 2000 / W 600 and 800 / D 600 and 800 • Color: RAL 7035 gray
Electrical Data	• Insulation voltage (Ui): 1000 V • Rated voltage (Ue): 415 V • Coordination: Type 2 • Frequency: 50/60 Hz • Auxiliary circuit voltage: 230 V • Degree of pollution: 3 • Rated current: 4000 A (with Copper and Linergy) • Short circuit (Icw - 1s): 100 kA
Modularity and Versatility	• 36 vertical modules (50 mm each) for functional units installation in 4 sizes of enclosures with 2 additional chambers for distribution busbars or cabling management • Compatible with PrismaSeT HD
Distribution	Vertical busbars positioned in a lateral compartment and horizontal busbars are used to distribute electricity inside the switchboard.
Fuctional Units	• Include: motor control/protection devices, mounting plate, gland boxes (rear or side) for Form 4b, and on-site connection components • Modular, stackable, supplied with all mounting and connection elements • Designed/tested per device characteristics for reliability and personnel safety • Reversible partial doors (120° opening) • Locking: 1–4 locking points, standard 5-mm double-bar insert, others optional
Environmental Resistance	• IP54 for dusty/damp areas • Seismic resistance • Available ClimaSys Options

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Characteristics







Mounting Plates for Fixed MCC Switchboards

The plain mounting plates can be used to install all the devices making up an MCC motor starter on a single support.

Easy installation


Motor feeders can be prepared on a bench making the cut-outs needed. The quick-fixing system allows holding the mounting plate during device installation and wiring. The mounting plate can be fixed on the side partitions in adjustable depth with a pitch of 50 mm.

Switchboard upgradeability

- Functional units with partitioning of Form 3b and 4b.
- Access from sides and rear.
- Separation panels with pre-cuts for cable glands ref. **LVS01215**.

Functional unit selection

- 3 to 24 module (150 to 1200 mm) mounting plates are installed in 600 and 800 mm wide enclosures.
- Capacity of PanelSeT SFN enclosures equipped for Motor Control Centers: 36 modules (50 mm each).
- Cables are routed in dedicated 300 or 400 mm wide lateral compartments.



Plain Mounting Plates

Dimension of the compartment				
Number of modules	Height (mm)	Width (mm)	Mounting plate	Fixing kit
3M	150	600	**NSYMP3M6**	**NSYMPFIX**
3M	150	800	**NSYMP3M8**	
4M	200	600	**NSYMP4M6**	
4M	200	800	**NSYMP4M8**	
5M	250	600	**NSYMP5M6**	
5M	250	800	**NSYMP5M8**	
6M	300	600	**NSYMP6M6**	
6M	300	800	**NSYMP6M8**	
8M	400	600	**NSYMP8M6**	
8M	400	800	**NSYMP8M8**	
9M	450	600	**NSYMP9M6**	
9M	450	800	**NSYMP9M8**	
12M	600	600	**NSYMP12M6**	
12M	600	800	**NSYMP12M8**	
16M	800	600	**NSYMP16M6**	
16M	800	800	**NSYMP16M8**	
18M	900	600	**NSYMP18M6**	
18M	900	800	**NSYMP18M8**	
20M	1000	600	**NSYMP20M6**	
20M	1000	800	**NSYMP20M8**	
24M	1200	600	**NSYMP24M6**	
24M	1200	800	**NSYMP24M8**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Characteristics

Motor Starter Solutions

2-Component Motor Starter

Thermomagnetic circuit-breaker + contactor

Advantages

- Very economic solutions.
- Suitable for all types of diagrams.
- Manual reset following a thermal fault.
- Type 2 coordination.

Applications

- Manufacturing and continuous and semi-continuous processes.

GV2P10_Image



LC1D09M7_Image



3-Component Motor Starter

Advantages

- Wide choice of solutions.
- Suitable for all types of diagrams.
- Manual or automatic reset following a thermal fault.
- 2 starting classes (10 and 20).
- Type 2 coordination.
- Separation of thermal and magnetic faults.

Magnetic circuit-breaker + contactor + thermal protection

- For manufacturing and continuous and semi-continuous processes.

Switch-disconnector fuse + contactor + thermal protection

- For all types of machines.
- For manufacturing and continuous and semi-continuous processes.

GV2P10_Image



LC1D09M7_Image



LRD086_Image



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Motor Starter Solutions

Variable Speed Drive

Advantages

- Improved Process Control and Energy Efficiency.
- Precise speed and torque control allows the motor to exactly match process demand (fans, pumps, conveyors).
- Energy savings, especially in variable-torque loads (affinity laws), often 20–50% compared with DOL starters.
- Smooth acceleration/deceleration helps eliminate mechanical shocks and process instability.







Soft Starter

Advantages

- Reduced Mechanical Stress and Longer Equipment Life
- Controlled voltage ramp-up reduces starting torque peaks.
- Helps prevent:
  - Shock loads on shafts, couplings, belts
  - Water hammer in pumps
  - Conveyor belt slippage
- Smooth stopping (with soft stop function) helps protect pipework and process equipment.
- Lower maintenance cost and fewer mechanical failures








Optimizing the choice of the devices associated to ATV and ATS

Line contactor

The line contactor (A) allows power to be connected to the starter, that can also be performed by ATS soft starter or the ATV variable speed drive. This line contactor is therefore optional: it has to be installed only on explicit customer request.

By-pass contactor for ATS soft starters

The by-pass contactor (B) allows to by-pass the starter at the end of the starting, while keeping the electronic protections.
As a consequence, a less expensive starter can be used.



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Functional Units

2-Component Motor Starter

Direct on Line and Reversing, GV2, GV3, GV4 and GV5


Selection of Recommended Combinations

GV2							
Iq (kA)		Motor characteristics		Motor starter solution		Number of modules on mounting plate (1M = 50 mm)	
Without limiter	With GV1L3	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor (1)	DOL	Reversing
85	-	0.18	0.6	GV2P04	LC1D09	3M	3M
85	-	0.25	0.9	GV2P05	LC1D09	3M	3M
85	-	0.37	1.1	GV2P06	LC1D09	3M	3M
85	-	0.55	1.5	GV2P06	LC1D09	3M	3M
85	-	0.75	1.8	GV2P07	LC1D09	3M	3M
85	-	1.1	2.6	GV2P08	LC1D09	3M	3M
85	-	1.5	3.4	GV2P08	LC1D09	3M	3M
85	-	2.2	4.8	GV2P10	LC1D09	3M	3M
85	-	3	6.5	GV2P14	LC1D09	3M	3M
85	-	4	8.2	GV2P14	LC1D18	3M	3M
50	85	5.5	11	GV2P16	LC1D25	3M	3M
50	85	7.5	14	GV2P20	LC1D25	3M	3M
50	85	10	19	GV2P21	LC1D32	3M	3M
50	85	11	21	GV2P22	LC1D32	3M	3M
50	85	15	28	GV2P32	LC1D32	3M	3M
50	-	18.5	34	GV3P40	LC1D40A	3M	4M
50	-	22	40	GV3P50	LC1D50A	3M	4M
50	-	30	55	GV3P65	LC1D65	3M	4M
100	-	37	-	GV4P80	LC1D80	-	-
100	-	55	88	GV4P115	LC1D115	4M	9M
70	-	55	88	GV5P150	LC1G115	6M	9M
70	-	75	120	GV5P150	LC1G150	9M	12M
70	-	90	145	GV5P220	LC1G150	9M	12M
70	-	110	177	GV5P220	LC1G185	9M	12M

(1) 2xLC1-D for reversing

Plain Mounting Plates

Dimension of compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
3M	150	600	**NSYMP3M6**	**NSYMPFIX**
3M	150	800	**NSYMP3M8**	
4M	200	600	**NSYMP4M6**	
4M	200	800	**NSYMP4M8**	
6M	300	600	**NSYMP6M6**	
6M	300	800	**NSYMP6M8**	
9M	450	600	**NSYMP9M6**	
9M	450	800	**NSYMP9M8**	
12M	600	600	**NSYMP12M6**	
12M	600	800	**NSYMP12M8**	



Example of 55kW Functional unit.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

3-Component Motor Starter

Star-Delta, GV2, GV3, GV4 and GV5

Ue	IP	Ambient temperature
415 V	≤ IP54	35 °C

Selection of Recommended Combinations

Iq (kA)		Motor characteristics		Motor starter solution		Number of modules on mounting plate (1M = 50 mm)
Without limiter	With GV1L3	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor	Star-delta
85	-	0,37	1,1	GV2P06	3xLC1D09	4M
85	-	0,55	1,5	GV2P06	3xLC1D09	4M
85	-	0,75	1,8	GV2P07	3xLC1D09	4M
85	-	1,1	2,6	GV2P08	3xLC1D09	4M
85	-	1,5	3,4	GV2P08	3xLC1D09	4M
85	-	2,2	4,8	GV2P10	3xLC1D18	4M
85	-	3	6,5	GV2P14	3xLC1D18	4M
85	-	4	8,2	GV2P14	3xLC1D18	4M
50	85	5,5	11	GV2P16	3xLC1D25	4M
50	85	7,5	14	GV2P20	3xLC1D25	4M
50	85	10	19	GV2P21	3xLC1D32	5M
50	85	11	21	GV2P22	3xLC1D32	4M
35	85	15	28	GV2P32	3xLC1D32	4M
50	-	18,5	34	GV3P40	3xLC1D50A	5M
50	-	22	40	GV3P50	3xLC1D50A	5M
50	-	30	55	GV3P65	3xLC1D65A	5M
-	-	45	-	GV4P115	3xLC1D115	12M
-	-	55	-	GV4P115	3xLC1D115	12M
-	-	75	-	GV5P115	3xLC1D115	16M
-	-	90	160	GV5P220	2xLC1G115 + LC1D65	16M
-	-	110	195	GV5P220	2xLC1G150 + LC1D80	16M

Selection of the Mounting Plate

Dimension of the compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
4M	200	600	**NSYMP4M6**	**NSYMPFIX**
4M	200	800	**NSYMP4M8**	
5M	250	600	**NSYMP5M6**	
5M	250	800	**NSYMP5M8**	
12M	600	600	**NSYMP12M6**	
12M	600	800	**NSYMP12M8**	
16M	800	600	**NSYMP16M6**	
16M	800	800	**NSYMP16M8**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Functional Units

3-Component Motor Starter

Direct on Line and Reversing GV2 and GV3

Ue	IP	Ambient temperature
415 V	≤ IP54	35 °C

Selection of Recommended Combinations

GV2								
Iq (kA)		Motor characteristics		Motor starter solution			Number of modules on mounting plate (1M = 50 mm)	
Without limiter	With LA9LB920	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor (1)	Thermal relay	DOL	Reversing
85	-	0.18	0.6	GV2-L04	LC1D09	LRD04	3M	3M
85	-	0.25	0.9	GV2-L05	LC1D09	LRD05	3M	3M
85	-	0.37	1.1	GV2-L06	LC1D09	LRD06	3M	3M
85	-	0.55	1.5	GV2-L06	LC1D09	LRD06	3M	3M
85	-	0.75	1.8	GV2-L07	LC1D09	LRD07	3M	3M
85	-	1.1	2.6	GV2-L08	LC1D09	LRD08	3M	3M
85	-	1.5	3.4	GV2-L08	LC1D09	LRD08	3M	3M
85	-	2.2	4.8	GV2-L10	LC1D09	LRD10	3M	3M
85	-	3	6.5	GV2-L14	LC1D09	LRD12	3M	3M
85	-	4	8.2	GV2-L14	LC1D18	LRD14	3M	3M
50	85	5.5	11	GV2-L16	LC1D25	LRD16	3M	3M
50	85	7.5	14	GV2-L20	LC1D25	LRD21	3M	3M
50	85	10	19	GV2-L21	LC1D32	LRD22	3M	3M
50	85	11	21	GV2-L22	LC1D32	LRD22	3M	3M
50	85	13	24	GV2-L32	LC1D32	LRD32	3M	3M
50	-	18.5	34	GV3-L40	LC1D40	LRD340	3M	4M
50	-	22	40	GV3-L50	LC1D50	LRD350	3M	4M
50	-	26	49	GV3-L65	LC1D65	LRD365	3M	4M

(1) 2xLC1-D for reversing

Selection of the Mounting Plate

Dimension of the compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
3M	150	600	**NSYMP3M6**	**NSYMPFIX**
3M	150	800	**NSYMP3M8**	
4M	200	600	**NSYMP4M6**	
4M	200	800	**NSYMP4M8**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

3-Component Motor Starter

Star-Delta, GV2 and GV3

Ue	IP	Ambient temperature
415 V	≤ IP54	35 °C

Selection of Recommended Combinations

Iq (kA)		Motor characteristics		Motor starter solution			Number of modules on mounting plate (1M = 50 mm)
Without limiter	With LA9LB920	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor	Thermal relay	Star-delta
85	-	0,37	1,1	GV2-L06	3xLC1D09	LRD06	4M
85	-	0,55	1,5	GV2-L06	3xLC1D09	LRD06	4M
85	-	0,75	1,8	GV2-L07	3xLC1D09	LRD07	4M
85	-	1,1	2,6	GV2-L08	3xLC1D09	LRD08	4M
85	-	1,5	3,4	GV2-L08	3xLC1D09	LRD08	4M
85	-	2,2	4,8	GV2-L10	3xLC1D18	LRD10	4M
85	-	3	6,5	GV2-L14	3xLC1D18	LRD12	4M
85	-	4	8,2	GV2-L14	3xLC1D18	LRD14	4M
50	85	5,5	11	GV2-L16	3xLC1D25	LRD16	4M
50	85	7,5	14	GV2-L20	3xLC1D25	LRD21	4M
50	85	10	19	GV2-L21	3xLC1D32	LRD22	4M
50	85	11	21	GV2-L22	3xLC1D32	LRD22	4M
35	85	15	24	GV2-L32	3xLC1D32	LRD32	4M
50	-	18,5	34	GV3-L40	3xLC1D50A	LRD340	5M
50	-	22	40	GV3-L50	3xLC1D50A	LRD350	5M
50	-	30	49	GV3-L65	3xLC1D65A	LRD365	5M

Selection of the Mounting Plate

Dimension of the compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
4M	200	600	**NSYMP4M6**	**NSYMPFIX**
4M	200	800	**NSYMP4M8**	
5M	250	600	**NSYMP5M6**	
5M	250	800	**NSYMP5M8**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Functional Units

3-Component Motor Starter

Direct on Line and Reversing, NSX


Ue	IP	Ambient temperature
415 V	≤ IP54	35 °C

Selection of Recommended Combinations

Iq (kA)	Motor characteristics		Motor starter solution			Number of modules on mounting plate (1M = 50 mm)	
	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor	Thermal relay	DOL	Reversing
NSX...F = 36 kA NSX...N = 50 kA NSX...H = 70 kA NSX...S = 85 kA NSX400L = 150 kA NSX630L = 150 kA	18.5	34	NSX100 MA	LC1D80	LRD3355	3M	6M
	22	40	NSX100 MA	LC1D80	LRD3357	3M	6M
	30	55	NSX100 MA	LC1D80	LRD3359	3M	6M
	37	64	NSX100 MA	LC1D80	LRD3363	3M	6M
	45	80	NSX100 MA	LC1G115	LR9G115	6M	9M
	55	97	NSX160 MA	LC1G115	LR9G225	6M	9M
	75	132	NSX250 MA	LC1G150	LR9G225	9M	12M
	90	160	NSX250 MA	LC1G185	LR9G225	9M	12M
	110	195	NSX400 1.3-M	LC1G265	LR9G500	12M	16M
	132	230	NSX400 1.3-M	LC1G265	LR9G500	12M	16M
	160	280	NSX630 1.3-M	LC1G330	LR9G500	12M	16M
	200	350	NSX630 1.3-M	LC1G400	LR9G500	12M	16M
	220	380	NSX630 1.3-M	LC1G500	LR9G500	12M	16M
	250	430	NSX630 1.3-M	LC1G500	LR9G500	12M	16M

Selection of the Mounting Plate

Dimension of the compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
3M	150	600	**NSYMP3M6**	**NSYMPFIX**
3M	150	800	**NSYMP3M8**	
6M	300	600	**NSYMP6M6**	
6M	300	800	**NSYMP6M8**	
9M	450	600	**NSYMP9M6**	
9M	450	800	**NSYMP9M8**	
12M	600	600	**NSYMP12M6**	
12M	600	800	**NSYMP12M8**	
16M	800	600	**NSYMP16M6**	
16M	800	800	**NSYMP16M8**	



Example of 200 kW Functional unit.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

3-Component Motor Starter

Star-Delta, NSX

Ue	IP	Ambient temperature
415 V	≤ IP54	35 °C

Selection of Recommended Combinations

Iq (kA)	Motor characteristics		Motor starter solution			Number of modules on mounting plate (1M = 50 mm)
	P_{max} (kW)	I_{max} (A)	Circuit breaker	Contactor	Thermal relay	Star-delta
NSX...F = 36 kA NSX...N = 50 kA NSX...H = 70 kA NSX...S = 85 kA NSX400L = 150 kA NSX630L = 150 kA	18.5	34	NSX100 MA	3xLC1D80	LRD3355	9M
	22	40	NSX100 MA	3xLC1D80	LRD3357	9M
	30	55	NSX100 MA	3xLC1D80	LRD3359	9M
	37	64	NSX100 MA	3xLC1D80	LRD3363	9M
	45	80	NSX100 MA	3xLC1D115	LR9D5367	12M
	55	100	NSX160 MA	3xLC1D150	LR9D5369	12M
	90	160	NSX250 MA	2xLC1G115 + LC1D65	LR9G115	16M
	110	195	NSX250 MA	2xLC1G150 + LC1D80	LR9G225	16M
	132	230	NSX400 1.3-M	2xLC1G150 + LC1D80	LR9G225	20M
	160	280	NSX400 1.3-M	2xLC1G185 + LC1G115	LR9G225	20M
	200	350	NSX630 1.3-M	2xLC1G225 + LC1G150	LR9G225	24M
	220	380	NSX630 1.3-M	2xLC1G265 + LC1G150	LR9G500	24M
	250	430	NSX630 1.3-M	2xLC1G265 + LC1G150	LR9G500	24M

Selection of the Mounting Plate

Dimension of the compartment			Mounting plate	Fixing kit
Number of modules	Height (mm)	Width (mm)	References	References
9M	450	600	**NSYMP9M6**	**NSYMPFIX**
9M	450	800	**NSYMP9M8**	
12M	600	600	**NSYMP12M6**	
12M	600	800	**NSYMP12M8**	
16M	800	600	**NSYMP16M6**	
16M	800	800	**NSYMP16M8**	
20M	1000	600	**NSYMP20M6**	
20M	1000	800	**NSYMP20M8**	
24M	1200	600	**NSYMP24M6**	
24M	1200	800	**NSYMP24M8**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Fixed variable speed drive - ATV630/ATV930 - 0,75 to 45 kW

Functional Unit Description

ATV630 fixed functional units are mounting in a W600 mm cubicle.

They can be equipped with:
- Current transformers,
- Auxiliary transformer.

Each functional unit is equipped with fans to avoid an excessive internal temperature.

Ue	IP	Ambient temperature
415 V	≤ 54	35 °C


Selection of Recommended Combinations

Motor Power (kW)	Breaker	Contactor	ATV	Thermal Management (fan)	Thermal Management (outgrilles)	Dimension Functional Unit
0.75	GV2L07	LC1D09	ATV630U07N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
1.5	GV2L08	LC1D09	ATV630U15N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
2.2	GV2L10	LC1D09	ATV630U22N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
3	GV2L14	LC1D09	ATV630U30N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
4	GV2L14	LC1D09	ATV630U40N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
5.5	GV2L16	LC1D18	ATV630U55N4Z	2 x **NSYCVF38M230PF**	2 x **NSYCAG92LPF**	9M
7.5	GV2L20	LC1D18	ATV630U75N4Z	**NSYCVF165M230PF**	**NSYCAG223LPF**	12M
11	GV2L22	LC1D25	ATV630D11N4Z	**NSYCVF165M230PF**	**NSYCAG223LPF**	12M
15	GV3L32	LC1D25	ATV630D15N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	16M
18.5	GV3L40	LC1D40	ATV630D18N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	16M
22	GV4LE	LC1D65	ATV630D22N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	16M
30	GV4LE	LC1D65	ATV630D30N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	18M
37	GV4LE	LC1D65	ATV630D37N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	18M
45	GV4LE	LC1D80	ATV630D45N4Z	**NSYCVF300M230PF**	**NSYCAG223LPF**	18M

Selection of the Mounting Plate

Dimension of the compartment				Mounting plate	Fixing kit	Internal separation
Number of modules	Height (mm)	Width (mm)	Depth (mm)	References	References	References
9M	450	600	800	**NSYMP9M6**	**NSYMPFIX**	**NSYHATVSK**
12M	600	600	800	**NSYMP12M6**	**NSYMPFIX**	**NSYVSP18M**
16M	800	600	800	**NSYMP16M6**	**NSYMPFIX**	**NSYVSP18M**
18M	900	600	800	**NSYMP18M6**	**NSYMPFIX**	**NSYVSP18M**

PB504132



Example of 11 kW Functional unit.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Fixed soft starter - ATS480 - 5,5 to 55 kW

Functional Unit Description

The fixed soft starter functional units are mounted in a cubicle W600 mm.

Functional units are designed to accept the auxiliary transformer.

Note: usage of trip indicator lamp is mandatory.

Ue	IP	Ambient temperature
415 V	≤ 54	35 °C


Selection of Recommended Combinations

Motor Power (kW)	Breaker	Contactor	ATS	Thermal Management (fan)	Thermal Management (outgrilles)	Dimension Functional Unit
5.5 up to 7.5	GV2L20	LC1D18P7	ATS480D17Y	**NSYCVF85FM230PF**	**NSYCAG125LPF**	12M
11	GV2L22	LC1D25P7	ATS480D22Y	**NSYCVF85FM230PF**	**NSYCAG125LPF**	12M
15	GV2L32	LC1D32P7	ATS480D32Y	**NSYCVF85FM230PF**	**NSYCAG125LPF**	12M
18.5	GV3L40	LC1D38AP7	ATS480D38Y	**NSYCVF85FM230PF**	**NSYCAG125LPF**	12M
22	GV4LE	LC1D50AP7	ATS480D47Y	**NSYCVF85FM230PF**	**NSYCAG125LPF**	12M
30	GV4LE	LC1D65AP7	ATS480D62Y	**NSYCVF165M230PF**	**NSYCAG223LPF**	18M
37	GV4LE	LC1D80P7	ATS480D75Y	**NSYCVF165M230PF**	**NSYCAG223LPF**	18M
45	GV4LE	LC1D115P7	ATS480D88Y	**NSYCVF165M230PF**	**NSYCAG223LPF**	18M
55	GV4LE	LC1D115P7	ATS480C11Y	**NSYCVF165M230PF**	**NSYCAG223LPF**	18M

Selection of the Mounting Plate

Dimension of the compartment				Mounting plate	Fixing kit	Internal separation
Number of modules	Height (mm)	Width (mm)	Depth (mm)	References	References	References
12M	600	600	800	**NSYMPR12M6**	**NSYMPFIX**	**NSYRS12M**
18M	900	600	800	**NSYMP18M6**	**NSYMPFIX**	-

PB504133



Example of 22 kW Functional unit.







Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Busbar

Electrical Distribution

Linergy LGYE - Lateral Profiles up to 4000 A

Installation in PanelSeT SFN		L 300								
Linergy profile, 2000 mm length										
		630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
Permissible current for an ambient temperature of 35 °C around the switchboard	IP > 31	530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Number of profiles per phase		1								
Height available (mm)		150					150		200	
References		LVS04560	LVS04561	LVS04562	LVS04563	LVS04564	LVS04565	LVS04566	LVS04567	LVS04568
Busbar supports										
		Fixed Support **NSYBVS●●**			Free Support **NSYBSA**		Bottom Support **NSYAS●●**			
		3 fixed supports are compulsory to hold the busbar in position. If more than 3 supports are needed, use free supports (in addition).								
 Number depending on I_{cw} (kA rms/1 s)	⩽ 30	3								
	⩽ 40	-		3+2 *			3			
	⩽ 50	-			3+2 *		3			
	⩽ 60	-			3+2 *				3	
	⩽ 65	-				3+2 *				
	⩽ 75	-				3+4 **			3+2 *	
	⩽ 85	-				3+4 **				
	⩽ 100	-						3+6 ***		
References Fixed support		NSYBVS●●							NSYBVS800 + LVS04646	
References Bottom support		NSYAS●●							NSYAS●● + LVS04646	
References Free support		NSYBSA							NSYBSA + LVS04646	
		* If spacing between supports > 400 mm add 1 **NSYBSA** free support. ** If spacing between supports > 250 mm add 1 **NSYBSA** free support. *** If spacing between supports > 130 mm add 1 **NSYBSA** free support.								
Wedging busbars in position										
		Wedge Fitted on Bottom Support					Wedge Fitted on Bottom Support			
		The bottom support **NSYAS●●** + **LVS0465●** is used to place profiles in the correct position. It is not considered to be a busbar support.								
References		**LVS04658** (set of 12 wedges)					**LVS04659** (set of 12 wedges)			
Connections to the Linergy LGYE horizontal busbar		2000/2500 A							3200/4000 A	
										
		Supplied with mounting hardware. Reference include 1 connection only. Order 1 connection per phase.								
References (short connection)		LVS04604							LVS04607	
References (long connection)		LVS04605								







Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Busbar

Linergy LGYE - Horizontal Profiles up to 4000 A

Note:
For accessories, see page 248.

Installation in PanelSeT SFN compartmentalized			Up to 1600 A					Up to 4000 A			
Linergy profile, 2000 mm length											
			630 A	**800 A**	**1000 A**	**1250 A**	**1600 A**	**2000 A**	**2500 A**	**3200 A**	**4000 A**
Permissible current for an ambient temp. of 35 °C around the switchboard			530 A	680 A	850 A	1050 A	1480 A	1650 A	2100 A	2800 A	3350 A
Number of profiles per phase			1								
Total number of vertical modules (50 mm)			3					3		4	
References			**LVS04560**	**LVS04561**	**LVS04562**	**LVS04563**	**LVS04564**	**LVS04565**	**LVS04566**	**LVS04567**	**LVS04568**
Busbar supports											
			Fixed support		Free support						
			2 fixed supports for PanelSeT SFN wide enclosure are compulsory according compartment depth (400 or 500 mm). 1 fixed support for PanelSeT SFN 300/400 wide chamber are compulsory. Fixed directly on framework. If more supports are needed, add free supports.								
In a PanelSeT SFN W600/800 Busbar supports 75 mm distance between bars	**Number of supports depending on I_{cw} (kA rms/1 s)**	≤ 15	2								
		≤ 25	2								
		≤ 30	2								
		≤ 40	-		2						
		≤ 50	-			2					
		≤ 60	-			2+1		2			
		≤ 65	-				2+1				
		≤ 75	-				2+1				
		≤ 85	-				2+1				
		≤ 100						2+4 *			
References Fixed support		D400	**NSYMBHS4**							-	
References Fixed support		D500	**NSYMBHS5**							**NSYMBHS54** + **LVS04646**	
References Free support			**NSYBSA**							**NSYBSA** + **LVS04646**	
In busbar chamber SFN: W300/400 Busbar supports 75 mm distance between bars	**Number of supports depending on I_{cw} (kA rms/1 s)**	≤ 15	1								
		≤ 25	1								
		≤ 30	1								
		≤ 40	-		1						
		≤ 50	-			1					
		≤ 60	-			1					
		≤ 65	-				1 + 1				
		≤ 75	-				1 + 1				
		≤ 85	-				1 + 1				
		≤ 100						1 + 1			
References Fixed support		D600	**NSYBHS600**					**NSYBHS600**		-	
References Fixed support		D800	**NSYBHS800**					**NSYBHS800**		**NSYBHS800** + **LVS04646**	
References Free support			**NSYBSA**					**NSYBSA**		**NSYBSA** + **LVS04646**	
Joints			Up to 1600 A					Up to 4000 A			
			630 A	800 A	1000 A	1250 A	1600 A	2000 A	2500 A	3200 A	4000 A
											
			LVS04620					**LVS04621**		**LVS04623**	
References (3P)			3x **LVS04620**					3x **LVS04621**		3x **LVS04623**	
References (4P)			4x **LVS04620**					4x **LVS04621**		4x **LVS04623**	



* If spacing between supports > 135 mm add 1 **NSYBSA** free support.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Busbar

Linergy BS - Lateral Flat Busbars up to 2500 A

In PanelSeT SFN busbar chamber		W300 D500/600/800, up to 1600 A				W300 D500/600/800, up to 2500 A					
Pre-slotted copper, 1675 mm length  											
Permissible current for an ambient temp. of 35 °C around the switchboard	IP > 31	750 A	900 A	1250 A	1600 A	1080 A	1250 A	1600 A	1850 A	2000 A	2500 A
Busbar cross-section (mm)		60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10
Number of busbars per phase		1		2		1			2		
References		**LVS04516**	**LVS04518**	**LVS04516**	**LVS04518**	**LVS04525**	**LVS04526**	**LVS04528**	**LVS04525**	**LVS04526**	**LVS04528**

Busbar supports




3 fixed supports are compulsory to hold the busbar in position.
If more than 3 supports are needed, use free supports (in addition).
The bottom wedge support is used to place the busbar in the correct position.
It does not count as a busbar support.


Number of supports depending on I_{cw} (kA rms/1 s)											
	≤ 15	3				3					
	≤ 25	3+2			3	3					
	≤ 30	3+2				3+2					3
	≤ 40	3+4		3+2		3+2					
	≤ 50		3+4			3+2					
	≤ 60					3+4					3+2
	≤ 65					3+4					3+2
	≤ 75						3+6		3+4		
	≤ 85									3+4	


References* PanelSeT SFN busbar chamber 75 mm distance between bars		
	W300, D600	**NSYBVS600** (fixed) + **NSYBSA** (free) + **NSYAS600** (end stop support)
	W300, D800	**NSYBVS800** (fixed) + **NSYBSA** (free) + **NSYAS800** (end stop support)

* References of supports depending on distance between bars and busbar chamber depth

Connections to the Linergy BS horizontal busbar








References **LVS04636**, **LVS04637** are supplied individually: 1 connection per phase.
Reference **LVS04642** consists of 2 M8 x 140 screws which can replace the original M8 x 120 screws.


	1 vertical bar per phase		2 vertical bars per phase		1 vertical bar per phase			2 vertical bars per phase		
	60 x 5	80 x 5	60 x 5	80 x 5	50 x 10	60 x 10	80 x 10	50 x 10	60 x 10	80 x 10
References* ≤ 80 mm	**LVS04645**				**LVS04636**		**LVS04637**	**LVS04637**		

* References of the connection piece depending on horizontal busbar size

(1) Drill hole dimensions for 5 mm thick horizontal busbars.



Drill hole dimensions for 10 mm thick horizontal busbars.



⚠ DANGER

RISK OF ELECTRICAL SHOCK AND ARC FLASH

For a busbar with 75 mm distance between bars, the bars must be completely covered.

Staggered assembly points between one bar and the next, to maintain the necessary clearance distances (1).

Failure to follow these instructions will result in death or serious injury.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Busbar

Linergy BS - Horizontal Flat Busbars up to 2500 A

Installation in PanelSeT SFN compartmentalized			Up to 1600 A				Up to 2500 A			
Copper bar, 2000 mm length			DB301128_nb							
Permissible current for an ambient temp. of 35 °C around the switchboard			750 A	900 A	1250 A	1600 A	1600 A	1850 A	2000 A	2500 A
Busbar cross-section (mm)			60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10
Number of busbars per phase			1	1	2	2	1	2	2	2
Total number of vertical modules (50 mm)			3							
References			**LVS04536**	**LVS04538**	**LVS04536**	**LVS04538**	**LVS04548**	**LVS04545**	**LVS04546**	**LVS04548**
Busbar supports			DB300926_nb Fixed support; DD381225_LIN_15_1_nb Free support							
			2 fixed supports for PanelSeT SFN wide enclosure are compulsory according compartment depth (400 or 500 mm). 1 fixed support for PanelSeT SFN 300/400 wide chamber is compulsory. Fixed directly on framework. If more supports are needed, add free supports.							
In a PanelSeT SFN W600/800 with 75 mm distance between bars	**Number of supports depending on I_{cw} (kA rms/1 s)**	≤ 15	2							
		≤ 25	2+1	2						
		≤ 30	2+1		2					
		≤ 40	2+1				2			
		≤ 50	-	2+1					2	
		≤ 60	-				2+1			
		≤ 65	-				2+1			
		≤ 75	-				2+2	2+1		
		≤ 85	-				-		2+1	
References Fixed support			**NSYMBHS4** (D400) or **NSYMBHS5** (D500)							
References Free support			**NSYBSA**							
In busbar chamber SFN: W300/400 with 75 mm distance between bars	**Number depending on I_{cw} (kA rms/1 s)**	≤ 30	1							
		≤ 50	1+1				1			
		≤ 85	-				2			
References* Fixed support			**NSYBHS600** (D600) or **NSYBHS800** (D800)				**NSYBHS600** (D600) or **NSYBHS800** (D800)			
References* Free support			**NSYBSA**				**NSYBSA**			
			* References depending on depth							

Joints, Installation in PanelSeT SFN	Up to 1600 A				Up to 2500 A			
	1 vertical bar per phase		2 vertical bars per phase		1 vert. bar per phase	2 vertical bars per phase		
Busbar cross-section (mm)	60 x 5	80 x 5	60 x 5	80 x 5	80 x 10	50 x 10	60 x 10	80 x 10
Sliding joints with self-breaking lock nut	DD385385b_nb **LVS04640**		DD385398b_nb **LVS04641**					
References	**LVS04640**	**LVS04641**	**LVS04640**	**LVS04641**	**LVS04641**	**LVS04640**	**LVS04640**	**LVS04641**

⚠⚠ DANGER

RISK OF ELECTRICAL SHOCK OR ARC FLASH

When installed at the bottom of an enclosure, the busbar must be partitioned.

Failure to follow these instructions will result in death or serious injury.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables of Busbar

Linergy LGYE - Accessories

Linergy Screw


- Sold in lots of 20: 20 screws + 20 nuts + 20 contact washers, grade 8.8. The screws slide into the profile and are then locked in the desired position.



Characteristics		AD	References
Steel plain washers	M8 sold in lots of 20	20 mm	LVS04772
	M8 sold in lots of 20	24 mm	LVS04773
	M8 sold in lots of 20	28 mm	LVS04774
Brass plain washers	M8 sold in lots of 20 for connection of ≤ 25 mm² lugs to Linergy	20 mm	LVS04775
Identification	12 clip-on supports + N, L1, L2, L3, PE, PEN labels		LVS04794
	Linergy LGYE busbar screw plate kit after sales service		LVS01130

M8 Screws

- Set of 20 screws + 20 nuts + 40 contact washers.


LVS04782

Characteristics	References
Linergy BS, 20 screws grade 8.8, M8 x 20	LVS04782
Linergy BS, 20 screws grade 8.8, M8 x 25	LVS04783
Linergy BS, 20 screws grade 8.8, M8 x 30	LVS04784
Linergy BS, 20 screws grade 8.8, M8 x 35	LVS04785
Linergy BS, 20 screws grade 8.8, M8 x 40	LVS04786
Linergy BS, 20 screws grade 8.8, M8 x 45	LVS04787
Linergy BS, 20 screws grade 8.8, M8 x 50	LVS04788


Torque Nuts

- Can be used to obtain the correct tightening torque (28 Nm) recommended by the manufacturer without without using a torque wrench. Torque nuts may be used for all electrical connections.


LVS04759

Characteristics	References
20 M8 torque nuts	LVS04759


Voltage Tap-Offs


LVS04229

- For small lugs (on low-current cables or measurement tap-offs), insert a conducting washer (ref. **LVS04775**) between the busbar and the lug.

Characteristics	References
20 M10 voltage tap-offs for two 6.35 mm tab connectors	LVS04229

Connections on Linergy LGYE and LGY


LVS04766


LVS04768






LVS04769






Characteristics	InA	bar	Use	References
Use the 25 mm Linergy screw	0 A to 630 A	Cable Insulated flexible bar	Recommended	LVS04766
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	0 A to 630 A	Cable Insulated flexible bar	Possible	LVS04767
Use the 25 mm Linergy screw	800 A to 1250 A	5 mm thick bar	Recommended	LVS04766
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	800 A to 1250 A	5 mm thick bar	Possible	LVS04767
Use the flat plate screw with 2 studs	800 A to 1250 A	5 mm thick bar	Possible	LVS04768
Use the flat plate screw with 2 studs	1600 A to 2500 A	5 or 10 mm thick bar	Recommended	LVS04768
Use the 39 mm Linergy screw is only compatible with Linergy LGY.	1600 A to 2500 A	5 or 10 mm thick bar	Possible	LVS04767
Use the flat plate screw with 3 studs	3200 A to 4000 A	10 mm thick bar	Recommended	LVS04769

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Partitioning Form 2

Separation of busbars from the functional units:
- Protection against contact with live parts upstream of the outgoing circuits,
- Protection against penetration by foreign solid bodies.

	Lateral partitioning	Rear partitioning
		
Diagrams		
		
Characteristics	• Set of 2 vertical metal separation for better insulation of the sides of the compartment (IP2x). • Top and bottom ends have knock-outs for installation of horizontal busbars and pre-cuts of 40 x 70 mm for cable glands using grommets ref. **LVS01215** when Form 4b is required. • Partition extension required for D800 mm. • Direct fixing on structure of enclosure.	• Vertical metal separation for better insulation of the back of the compartment (IP2x). • Pre-cuts of 40 x 70 mm for cable glands using grommets ref. **LVS01215** when Form 4b is required on back installation. • Direct fixing on structure of enclosure.
References	D600: **NSYMSC206** D800: **NSYMSC206** + **NSYMSC202** + **NSYSUCR40200**	W600: **NSYMBC206** W800: **NSYMBC208**

	Front and Rear busbar barrier	Horizontal busbar barriers			
					
Diagrams					
					
		W600	**W800**	**W300**	**W400**
Characteristics	• Front protection is realized by the combination of the door W300 and this barrier. Metal barrier, composed of 2 parts H850, pre-cut at both ends • Rear protection is realized by the combination of the back panel of the enclosure.	• Horizontal protection by the combination of slotted front barrier and horizontal partition for efficient natural convection in the switchboard. • The set can be used to partition horizontal busbar at the top or bottom of the enclosure. • The space required for the busbars is not increased.		• Set of 2 slotted barriers (front and rear), plus horizontal panel to be used when busbars cross the cable chamber.	
References	W300: **LVS06540** W400: **NSYVPFN2B4**	D600 (1): **NSYHPF2B3M64** D800 (1): **NSYHPF2B3M65** **NSYHPF2B4M65***	D600 (1): **NSYHPF2B3M84** D800 (1): **NSYHPF2B3M85**	D600: **LVS06561** D800: **LVS06563** **LVS06568***	D600: **NSYHPF2B3M4** D800: **NSYHPF2B3M4**

* When Horizontal Busbar is > 2500 A

(1) For an enclosure with a depth of 600 mm the compartment depth is 400 mm. For an enclosure with a depth of 800 mm the compartment depth is 500 mm

⚠⚠ DANGER

RISK OF ELECTRICAL SHOCK OR ARC FLASH

When the busbars are at the bottom of the enclosure, gland plates are mandatory.

Failure to follow these instructions will result in death or serious injury.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables for Enclosure Partitioning

External claddings






Intermediate Crossbar	
Characteristics	• It is mounted between partial doors, for better sealing. • It is included inside of Horizontal busbar barriers and form 3 partitioning • To be used in the absence of the partition tray. • Direct fixing to the structure. • Available in 2 widths (mm).
Supply	• 2 crossbars with fixing elements
References	W600: **NSYMICN6** W800: **NSYMICN8**

Partitioning Form 3

Separation of busbars from the functional units and separation of all functional units from one another.
Separation of the terminals for external conductors from the functional units, but not from each other.
- Enhanced protection against contact with live parts
- Reduction in the risk of faults between the functional units (propagation of electrical arcs, etc.).

Form 3 partitioning



Note:
Supplied with 2 horizontal partitioning.

Horizontal partitioning	W600	W800
Characteristics	• A horizontal metal partition to separate functional units from one another and insulate the compartments (IP2x). • It is fixed to the front uprights of the enclosure and the side partitions. • Quick-fixing system with intermediate crossbar to improve the degree of protection of the partial doors. • Order by multiples of 2 (2, 4, 6…).	
References	D600 (1): **NSYMTRN64** D800 (1): **NSYMTRN65**	D600 (1): **NSYMTRN84** D800 (1): **NSYMTRN85**

(1) For an enclosure with a depth of 600 mm the compartment depth is 400 mm. For an enclosure with a depth of 800 mm the compartment depth is 500 mm.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Partitioning Form 4

Separation of busbars from the functional units and separation of all functional units from one another, including the terminals for external conductors which are an integral part of the functional unit:

- Protection against contacts with live parts and reduction in the risk of faults between the functional units (propagation of electrical arcs, etc.).
- Form 4a: Terminal for external conductors in the same compartment as the associated.
- Form 4b: Terminals for external conductors not in the same compartment as the associated functional unit, but in individual, separate, enclosed spaces or compartments.

Form 4b boxes



Characteristics	• Metal plain box composed by 2 parts that can be easily installed for side or rear connection to separate the terminals for external conductors of the functional unit. • Quick-fixing system on the side or on the back partition. • Available in 6 heights:					
References	3M: **NSYBF4B3M**	4M: **NSYBF4B4M**	5M: **NSYBF4B5M**	6M: **NSYBF4B6M**	8M: **NSYBF4B8M**	9M: **NSYBF4B9M**

Rail Support Bracket

SM | SFN | SD | SFX

Telequick

- Bracket for fixing rails at an angle of 45°.
- Material: Zinc-coated steel
- PanelSeT SFN: Mounted on the structure and/or mounting plates
- PanelSeT SM: Mounted on the bottom mounting rail and/ or mounting plates



Characteristics	References
Rail support bracket	**NSYFB45**

Grommets

Grommets



	Grommets
Characteristics	5 square grommets 70 x 40
References	**LVS01215**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables for Enclosure Partitioning


Selection of PanelSeT SFN MCC Enclosures

Common Characteristics

- PanelSeT SFN framework with compartment system that can be combined side-by-side with busbar and cable chambers.
- Receive the cover panels and partial doors IP54.
- Material: Steel.
- Finish: Painted with epoxy polyester resin.
- Color: RAL 7035 gray.
- Available as kit.

	Kit supply
	  

Compartmentalised enclosure	W600	W800
Characteristics	• Structure: Top and bottom frame and vertical uprights with a height of 2000 mm. • Useful height of 1800 mm/36M for partial doors installation if top and bottom fix panels are installed for modularity (needed for installation of partial doors). • Equipped with removable roof and external fixing rear panel. • 4 dimensions available.	
References	-	-
Vertical uprights, height 2000 mm	**NSYSFNV20**	**NSYSFNV20**
Top and Bottom frame with roof	D600: **NSYSFNC66** D800: **NSYSFNC68**	D600: **NSYSFNC86** D800: **NSYSFNC88**
Rear panel	**NSYBPN206**	**NSYBPN208**
Fixed panels for modularity, height 100 mm/2M (intermediate crossbars included)	See table below	See table below

	Front Fix panel for modularity		Frontal partial doors		Frontal transparent partial doors		Side panels	
								
External claddings	**W600**	**W800**	**W600**	**W800**	**W600**	**W800**	**D600**	**D800**
Characteristics	• Top and bottom fix panel to obtain modularity required to install partial doors. • Supplied with a bottom trim. • If there is no horizontal partitioning on top or bottom, the intermediate crossbar has to be ordered separately, ref. NSYMICN6 (W600 mm) or NSYMICN8 (W800 mm). • Available in 3 heights (M) Heights according modularity (1M = 50 mm). • 6M is for Horizontal Busbars > 2500 A.		• Plain partial door with lock with 5-mm double-bar insert. • They are fixed to the uprights of the framework by means of hinges. • Drilling template for uprights ref. NSYMDT (Only 1 drilling template by order is needed). • Opening to right or left. • 1, 2 or 4 locking points depending on height. • Replaceable locking insert (see page 563). • Available in following heights (M) Heights according modularity (1M = 50 mm).		• Glazed (Securit glass) partial door with lock 5-mm double-bar insert. • They are fixed to the uprights of the framework by means of hinges. • Opening to right or left. • 1 or 2 locking points according different heights. • Available in following heights (mm). • Ingress protection rating: IP54 according to IEC 60529		• Set of 2 side panels fixed to the outside of the enclosure. • Captive screws pre-mounted on • The panels. • Available in 2 depths (mm).	
References	**2M: NSYMFP2M6** **5M: NSYMFP5M6** **6M: NSYMFP6M6**	**2M: NSYMFP2M8** **5M: NSYMFP5M8**	**3M: NSYMPD3M6** **4M: NSYMPD4M6** **5M: NSYMPD5M6** **6M: NSYMPD6M6** **8M: NSYMPD8M6** **9M: NSYMPD9M6** **12M: NSYMPD12M6** **16M: NSYMPD16M6** **18M: NSYMPD18M6** **20M: NSYMPD20M6** **24M: NSYMPD24M6**	**3M: NSYMPD3M8** **4M: NSYMPD4M8** **5M: NSYMPD5M8** **6M: NSYMPD6M8** **8M: NSYMPD8M8** **9M: NSYMPD9M8** **12M: NSYMPD12M8** **16M: NSYMPD16M8** **18M: NSYMPD18M8** **20M: NSYMPD20M8** **24M: NSYMPD24M8**	**8M: NSYMPD46T** **12M: NSYMPD66T** **16M: NSYMPD86T** **20M: NSYMPD106T**	**8M: NSYMPD48T** **12M: NSYMPD68T** **16M: NSYMPD88T** **20M: NSYMPD108T**	**NSY2SPN206**	**NSY2SPN208**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Selection Tables for Enclosure Partitioning

Selection of PanelSeT Enclosures

Selection of PanelSeT Enclosures for Motor Control Centers


	Assembled supply		Kit supply	
				
Busbar and cabling chambers	**W300**	**W400**	**W300**	**W400**
Characteristics	• Structure: Top and bottom frame and vertical uprights with a height of 2000 mm. • Equipped with removable roof, external fixing rear panel and front plain door with 4-point locking system with handle and DB 5 mm insert. • 4 dimensions available.			
References	D600: **NSYSFN20360** D800: **NSYSFN20380**	D600: **NSYSFN20460** D800: **NSYSFN20480**	-	-
Vertical uprights, height 2000 mm	-	-	**NSYSFNV20**	**NSYSFNV20**
Top and Bottom frame with roof	-	-	D600: **NSYSFNC36** D800: **NSYSFNC38**	D600: **NSYSFNC46** D800: **NSYSFNC48**
Rear panel	-	-	**NSYBPN203**	**NSYBPN204**
Front plain door	-	-	**NSYSFND203**	**NSYSFND204**

	Enclosure vertical separation
	
Vertical Intermediate Crossbar	
Characteristics	• It is mounted on an enclosure to separate it in 2. Example: W800 (600+200) or W1000 (800+200). • In W200 compartment is for Busbar installation or cable management. • Compatible with partial doors, full doors and PanelSeT SFN distribution chassis and partitioning accessories up to form 4b (PanelSeT SFN MCC). • Available in 3 heights (mm). • When partitioning form 2b panels are installed, it is need it to order 1 Universal cross rail NSYSUCR40••.
Supply	• 1 crossbar with fixing elements • 1 external fixing panel W200
References	H1800: **NSYVMICN18** H2000: **NSYVMICN20** H2200: **NSYVMICN22**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Compartmentalized Enclosures for MCC

Accessories

Mounting Accessories

1



Rear panel

See details p. 252

2



Top and bottom frame with roof

See details p. 252

3



Vertical upright

See details p. 253

MCC Accessories

4



Front fix panel for modularity

See details p. 252

5



Front partial doors

See details p. 252

6



Partial mounting plates and fixing kit

See details p. 233

7



Form 2b partitioning: lateral, rear

See details p. 249

8



Form 3b partitioning: horizontal, intermediate crossbar

See details p. 250

9



Vertical MIC

See details p. 250

PanelSeT SFN Accessories


10



Side panels

See details p. 461

11



Cable gland plate: plain, 1 entry, 2 entries

See details p. 501

12



Plinth: front, side

See details p. 469

> For more information consult the Accessories chapter **page 250** and **456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Human Machine Interface

Panel**SeT** SFN PC: Suitable Control PC Rack

PB503963



Panel**SeT** SD: Control Desk







Panel**SeT** S3CM: Control Enclosure with Suspension Rack



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN PC: Suitable Control PC Rack

Introduction	258
Characteristics	260
Dimensions	261
Accessories	262

Panel**SeT** SD: Control Desk

Introduction	264
Characteristics	266
Accessories	268
Dimensions	274

Panel**SeT** S3CM: Control Enclosure with Suspension Rack

Introduction	276
Selection Table	279
Accessories	281
Dimensions	284

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN PC: Suitable Control PC Rack

Introduction





The PanelSeT SFN PC Rack is designed to shelter and control computer equipment in industrial environments. It proposes various functions and working heights for optimal comfort.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN PC: Suitable Control PC Rack

Introduction



Convenience

- Anti-glare glazed door designed for viewing screens up to 17"
- Cable entry made easier by a two-piece cable-gland plate




Ergonomics

- Access to the various functions and working heights
- Partial doors delimit the access to each function with a 3-mm double-bar lock
- Display and CPU support
- Keyboard and mouse support



Protection

- Locking system in the rear door
- locks in the front partial doors



Robust

Unique bolted structure with high load-bearing capacity

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN PC: Suitable Control PC Rack

Characteristics

Suitable Control PC Rack



- Partial door for PC display, with Securit® anti-glare glass.
- Plain partial door for CPU (enclosures with height of 1800 mm).
- Hinged plain door for keyboard.
- Plain partial door for optional installation of A4 printer support.
- Partial front doors opening to the right.
- Plain rear door, reversible opening direction (right or left).
- Roof and side panels fixed from the outside.
- Cable-gland plate with 1 entry.
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP40 according to IEC 60529
- Mechanical protection rating: IK08 according to IEC 62262
- Certifications: UL (cULus). Rated 1, 12 according to UL50E













Dimensions (mm)			Number of compartments	Uprights	Frames + roof	Door	Panels	Tray	Cable gland plate 1-entry
H	W	D							
1600	600	600	3	**NSYSFNV16**	**NSYSFNC66**	**NSYSFND166**	**NSY2SPN166**	**NSYFXT6060**	**NSYEC661**
1600	600	800	3	**NSYSFNV16**	**NSYSFNC68**	**NSYSFND166**	**NSY2SPN168**	**NSYFXT8060**(1)	**NSYEC681**
1800	600	600	4	**NSYSFNV18**	**NSYSFNC66**	**NSYSFND186**	**NSY2SPN186**	**NSYFXT6060**	**NSYEC661**
1800	600	800	4	**NSYSFNV18**	**NSYSFNC68**	**NSYSFND186**	**NSY2SPN188**	**NSYFXT8060**(1)	**NSYEC681**

(1) The tray needs to be installed turned 90 degrees. This positioning differs from the standard orientation, as it places the cables at the side instead of the back.

Front partial doors














Dimensions (mm)			Number of compartments	Top and bottom covers	Display (top glazed H600)	CPU (plain H200)	Keyboard (door + housing)	Bottom plain	Intermediate crossbar
H	W	D							
1600	600	600	3	**NSYMFP2M6**	**NSYSFNPCPD600T**	-	**NSYSFNPCMK600**	**NSYSFNPCPD600**	2x **NSYMICN6**
1600	600	800	3	**NSYMFP2M6**	**NSYSFNPCPD600T**	-	**NSYSFNPCMK600**	**NSYSFNPCPD600**	2x **NSYMICN6**
1800	600	600	4	**NSYMFP2M6**	**NSYSFNPCPD600T**	**NSYMPD4M6**	**NSYSFNPCMK600**	**NSYSFNPCPD600**	3x **NSYMICN6**
1800	600	800	4	**NSYMFP2M6**	**NSYSFNPCPD600T**	**NSYMPD4M6**	**NSYSFNPCMK600**	**NSYSFNPCPD600**	3x **NSYMICN6**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN PC: Suitable Control PC Rack

Dimensions

DB300242EN_60_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN PC: Suitable Control PC Rack

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1




Plinths

See details p. 469

Mounting Accessoires

Equipment Assembly Accessories

2



Universal cross rail

See details p. 525


3



Telescopic rails

See details p. 538

4



Fixed tray

See details p. 538

5



Handle for tray

See details p. 538

> For more information consult the Accessories section **page 270**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Introduction



The range of PanelSeT SD control desks provides all features required of a workstation intended for industrial and infrastructure applications.
PanelSeT SD products offer two distinct solutions:
- The SD compact control desk,
- The SD control desk with console.

The range has protection ratings of IP55 and IK10 for enhanced protection of the installed devices.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Accessibility
- Front accessibility, designed for straightforward solutions
- Rear accessibility, enables the installation of two adjoining plates
- The control desk with console offers full accessibility



Ease of Mounting
- The option of connecting the modular control desk to the modular consoles offers multiple combinations
- The opening direction of the door can be changed quickly thanks to the included hinges



Ease of Use
- The console opens easily and Smoothly thanks to the installed pneumatic opening lid stays
- Cable entry is optimized because all the models of the range include a cable gland plate with two adjustable parts



Compatibility
The PanelSeT SD control desk is compatible with several of the accessories of the PanelSeT SFN and SM ranges

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Characteristics

Compact Control Desk



Options:
It can also be equipped with a mounting plate, see page 272

Characteristics

- This range is available in 4 widths with fixed rear panel.
- Full accessibility is provided from the front (no central upright).
- Easy removable and reversible door opening to 120°.
- Locking by 3 mm doublebar lock (other inserts or cylinders also available, to be ordered separately, see page 272).
- Desk lid equipped with a pneumatic opening stay.
- Opens to 75°. Perforated reinforcement rails with a pitch of 25 mm.
- Control desk equipped with adjustment rails with a pitch of 25 mm and brackets allowing adjustment of the mounting plate depth.
- Cable gland plate with 2 adjustable parts, with polyurethane gasket.
- M8 x 18 mm earthing screw for equipotential connection between the door and the body.
- Material: Welded folded steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Thickness: 15/10e mm
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Number of doors	Width (mm)	Height (mm)	Depth (mm)	References
1	600	1000	469	**NSYSD6**
1	800	1000	469	**NSYSD8**
2	1000	1000	469	**NSYSD10**
2	1200	1000	469	**NSYSD12**

Compact Control Desk with Rear Panel



Options:
Modular consoles to be installed on top of compact control desk.
See details and combinations page 271. It can also be equipped with a mounting plate, see page 272.

Characteristics

- Removable rear panel. It enables the installation of two mounting plates back-to-back, allowing the installation of a large number of devices, while enabling full accessibility from the front and the rear.
- At the top, these control desks are equipped with cable entry cut-outs, that allows the installation of one or more modular consoles.
- Easy removable and reversible door, opening to 120°.
- Locking by 3 mm doublebar lock (other inserts or cylinders also available, to be ordered separately, see page 272).
- Desk lid equipped with a pneumatic opening stay.
- Opens to 75°. Perforated reinforcement rails with a pitch of 25 mm.
- Top cable entry cut-outs covered by a entire blanking cover.
- Control desk equipped with adjustment rails with a pitch of 25 mm and brackets allowing adjustment of the mounting plate depth.
- Cable gland plate with 2 adjustable parts, with polyurethane gasket.
- M8 x 18 mm earthing screw for equipotential connection between the door and the body.
- Material: Welded folded steel
- Finish: Structured finish, epoxy polyester powder paint
- Color: RAL 7035 gray
- Thickness: 15/10e mm
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Number of doors	Width (mm)	Height (mm)	Depth (mm)	References
1	600	1000	600	**NSYSD6R**
1	800	1000	600	**NSYSD8R**
2	1000	1000	600	**NSYSD10R**
2	1200	1000	600	**NSYSD12R**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Characteristics

Options:
- Plinth see page 270.
- Mounting plate, see page 272.
- Locking system: Other inserts or cylinders, see page 272.

Control Desk with Console

NSYSDF88




Characteristics	• Full accessibility is provided from the front and rear. • Easy removable and reversible front door, opening to 120°. • Locking by two-point locks with 3-mm double-bar insert. • Desk lid equipped with a pneumatic opening stay. Opens to 75°. • Perforated reinforcement rails with a pitch of 25 mm for quick installation of cables and cable ducts. • Locking by two-point locks with 3-mm double-bar insert. • Hinged console cover equipped with a pneumatic opening stay. • Opens to 75°. • Locking by two-point locks with 3-mm double-bar insert. • Easy removable and reversible rear door, opening to 120°. • Locking by three-point lock with flat escutcheon, 5-mm double-bar insert. • One entry cable gland plate, with polyurethane gasket. • Control desk equipped with adjustment rails with a pitch of 25 mm and brackets allowing adjustment of the mounting plate depth. • M8 x 18 mm earthing screw for equipotential connection between the door and the body. • Material: Welded folded steel • Finish: Structured finish, epoxy polyester powder • Color: RAL 7035 gray • Thickness: 15/10e mm • Ingress protection rating: IP55 according to IEC 60529 • Mechanical protection rating: IK10 according to IEC 62262

Nb of front doors	Nb of rear doors	Nb cable gland plates	Width (mm)	Height (mm)	Depth (mm)	References
1	1	1	800	1400	845	**NSYSDF88**
1	1	1	800	1400	1045	**NSYSDF810**
2	2	1	1000	1400	845	**NSYSDF108**
2	2	1	1000	1400	1045	**NSYSDF1010**
2	2	1	1200	1400	845	**NSYSDF128**
2	2	1	1200	1400	1045	**NSYSDF1210**
2	2	2	1600	1400	845	**NSYSDF168**
2	2	2	1600	1400	1045	**NSYSDF1610**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Plinths

See details p. 270

2



Fixing brackets

See details p. 272

Mounting Accessoires

Equipment Assembly Accessories

3



Mounting plates

See details p. 272

4



Adjustment rails

See details p. 272

5



Technical uprights

See details p. 530

6



Modular consoles

See details p. 271

Door Accessories

7



Opening stay

See details p. 271

8



Key locks and shape inserts

See details p. 272


> For more information consult the Accessories section **page 270**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Accessories

For more information, see page 467.

	Front and rear plinth	Plinth side panels
		

Characteristics	NSYSPF6100	NSYSPS4100SD
	The front and rear of the plinth consists of 4 corners with 2 or 4 panels.	They are fixed to the corner of the plinth by 2 fixing screws.
Material	Folded sheet steel, corner with a thickness of 25/10e mm	Folded sheet steel
Finish	Painted with epoxy polyester resin	Painted with epoxy polyester resin
Color	RAL 7022 gray	RAL 7022 gray
Ingress protection rating	IP30	IP30
Mechanical protection rating	IK10	IK10
Supply	• Height 100 mm: 4 corners, 2 panels (front and rear), 4 corner covers and fixing elements • Height 200 mm: 4 corners, 4 panels (2 front and 2 rear), 4 corner covers and fixing elements • The use of 304L stainless-steel plinths on an SD control desk requires an earthing cable (description page 540) to be ordered separately.	• Height 100 mm: 2 side panels, 4 corner covers and fixing elements • Height 200 mm: 4 side panels (height of 100 mm, 2 for each side), 4 corner covers and fixing elements • The use of 304L stainless-steel plinths on an SD control desk requires an earthing cable (description page 540) to be ordered separately.

Control desk references	Plinths references			
Compact control desks with fixed rear panel	100 mm	200 mm	100 mm	200 mm
References	References	References	References	References
 NSYSD6	NSYSPF6100	NSYSPF6200	NSYSPS4100SD	NSYSPS4200SD
NSYSD8	NSYSPF8100	NSYSPF8200	NSYSPS4100SD	NSYSPS4200SD
NSYSD10	NSYSPF10100	NSYSPF10200	NSYSPS4100SD	NSYSPS4200SD
NSYSD12	NSYSPF12100	NSYSPF12200	NSYSPS4100SD	NSYSPS4200SD
Compact control desks with removable rear panel Sheet steel	**100 mm**	**200 mm**	**100 mm**	**200 mm**
 NSYSD6R	NSYSPF6100	NSYSPF6200	NSYSPS5100SD	NSYSPS5200SD
NSYSD8R	NSYSPF8100	NSYSPF8200	NSYSPS5100SD	NSYSPS5200SD
NSYSD10R	NSYSPF10100	NSYSPF10200	NSYSPS5100SD	NSYSPS5200SD
NSYSD12R	NSYSPF12100	NSYSPF12200	NSYSPS5100SD	NSYSPS5200SD
Control desk with console	**100 mm**	**200 mm**	**100 mm**	**200 mm**
 NSYSDF88	NSYSPF8100	NSYSPF8200	NSYSPS4100SD	NSYSPS4200SD
NSYSDF108	NSYSPF10100	NSYSPF10200	NSYSPS4100SD	NSYSPS4200SD
NSYSDF128	NSYSPF12100	NSYSPF12200	NSYSPS4100SD	NSYSPS4200SD
NSYSDF168	NSYSPF16100	NSYSPF16200	NSYSPS4100SD	NSYSPS4200SD
NSYSDF810	NSYSPF8100	NSYSPF8200	NSYSPS6100SD	NSYSPS6200SD
NSYSDF1010	NSYSPF10100	NSYSPF10200	NSYSPS6100SD	NSYSPS6200SD
NSYSDF1210	NSYSPF12100	NSYSPF12200	NSYSPS6100SD	NSYSPS6200SD
NSYSDF1610	NSYSPF16100	NSYSPF16200	NSYSPS6100SD	NSYSPS6200SD

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Modular Consoles

- Hinged modular console cover equipped with a pneumatic opening stay.
- Opens to 75°. Locking of the hinged modular console cover by two 3-mm double-bar locks (other inserts or barrels also available, to be ordered separately, see page 563).
- Screw fixed rear panel equipped with step slides in the version with a depth of 300 mm.
- Material: Welded folded steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Thickness: 15/10e mm
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Options:
The link between the control desk and the modular console requires, in certain cases, the addition of one or several blanking covers (to be ordered separately).
Optional galvanized mounting plate.


NSYSDC42

Characteristics	Number of cable entry cut-outs	Width (mm)	Height (mm)	Depth (mm)	References
Modular consoles	2	400	483	200	**NSYSDC42**
Modular consoles	2	400	483	300	**NSYSDC43**
Modular consoles	3	600	483	200	**NSYSDC62**
Modular consoles	3	600	483	300	**NSYSDC63**

Blanking Cover

- To conceal the free space of the control desk when the width of the console or consoles is less than the width of the control desk.
- In any case, it is necessary to first remove the top plate delivered with the control desk.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Thickness: 15/10e mm
- Fixing: Fixing by screws


NSYRP2

Characteristics	Width (mm)	Height (mm)	References
Blanking cover	200	40	**NSYRP2**

Door for SD

Pneumatic opening stay

- Holds the desk lid in open position at an angle of 75°.


PB501213_42_nb

Nominal load per stay (N)	Max. load on lid (kg)	Compatibility	Control desk references			Standard supply stay
			With fixed rear panel References	With removable rear panel Sheet steel References	With console References	References
244	13	SD	**NSYSD6**	**NSYSD6R**	**NSYSDF88**	-
244	13	SD	**NSYSD8**	**NSYSD8R**	**NSYSDF810**	-
300	11	SD	-	-	**NSYSDF168**	**NSYPLS30**
300	11	SD	-	-	**NSYSDF1610**	**NSYPLS30**
300	15	SD	**NSYSD12**	**NSYSD12R**	**NSYSDF128**	**NSYPLS30**
300	15	SD	-	-	**NSYSDF1210**	**NSYPLS30**
300	17	SD	**NSYSD10**	**NSYSD10R**	**NSYSDF108**	**NSYPLS30**
300	17	SD	-	-	**NSYSDF1010**	**NSYPLS30**

Pneumatic Opening Stay

- Holds the desk lid in open position at an angle of 75°.

Supply:
Delivered with fixings


NSYPLS30

Characteristics	Nominal load per stay (N)	Max. load on lid (kg)	References
Pneumatic opening stay	300	17	**NSYPLS30**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SD: Control Desk

Accessories


Escutcheon with Key Lock



NSYML405SD

- Insert breakage torque: 15 daN.
- Material: Polyamide PA 6 material charged with 30% fiberglass
- Color: RAL 7011 gray
- Mechanical protection rating according to IEC 62262: IK10

Characteristics	References
405E key	**NSYML405SD**


Plain Mounting Plate for Compact Control Desks




NSYPMP8560


Characteristics	Width (mm)	Surface (dm²)	References
Mounting plate plain	600	42	**NSYPMP8560**
Mounting plate plain	800	59	**NSYPMP8580**
Mounting plate plain	1000	76	**NSYPMP85100**
Mounting plate plain	1200	93	**NSYPMP85120**

Plain Mounting Plate for Control Desk




NSYPMP4580

Characteristics	Width (mm)	Surface (dm²)	References
Mounting plate plain	800	31	**NSYPMP4580**
Mounting plate plain	1000	40	**NSYPMP45100**
Mounting plate plain	1200	77	**NSYPMP45120**
Mounting plate plain	1600	67	**NSYPMP45160**




NSYPMP8580

Characteristics	Width (mm)	Surface (dm²)	References
Mounting plate plain	800	49	**NSYPMP8580**
Mounting plate plain	1000	63	**NSYPMP85100**
Mounting plate plain	1200	77	**NSYPMP85120**
Mounting plate plain	1600	105	**NSYPMP85160**

Fixing Brackets


NSYMPBSD

- Set of 4 fixing brackets.
- Depth adjustment on 25 mm pitch.
- Included as standard with desk (all versions).
- To be ordered separately when required for installation of two back-to-back mounting plates in control desks with rear access.
- Material: Galvanized steel
- Thickness: 40/10^{e} mm
- Maximum load: 250 kg

Characteristics	References
Fixing brackets	**NSYMPBSD**


Adjustment Rails and Fixing Brackets




NSYMPB6SD



- Set of 4 rails and 4 fixing brackets.
- To install a plain mounting plate or a Telequick mounting plate, either at the top or across the height of the monobloc control desk with console.
- For positioning 2 plates (back-to-back), order fixing brackets ref. **NSYMPBSD**.



Characteristics	For control desks with console Depth (mm)	References
Adjustment rails and fixing brackets	600	**NSYMPB6SD**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Combination examples of modular consoles installation		Compact control desk	Modular console	Blanking cover
600		PanelSeT SD	PanelSeT SD	PanelSeT SD
		**NSYSD6R**	**NSYSDC42 / NSYSDC43**	**NSYRP2**
		**NSYSD6R**	**NSYSDC62 / NSYSDC63**	-

800		PanelSeT SD	PanelSeT SD	PanelSeT SD
		**NSYSD8R**	**NSYSDC42 / NSYSDC43**	2 x **NSYRP2**
		**NSYSD8R**	2 x **NSYSDC42** / 2 x **NSYSDC43**	-
		**NSYSD8R**	**NSYSDC62 / NSYSDC63**	**NSYRP2**

1000		PanelSeT SD	PanelSeT SD	PanelSeT SD
		**NSYSD10R**	**NSYSDC42 / NSYSDC43**	3 x **NSYRP2**
		**NSYSD10R**	**NSYSDC62 / NSYSDC63**	2 x **NSYRP2**
		**NSYSD10R**	**NSYSDC62 / NSYSDC63**	2 x **NSYRP2**
		**NSYSD10R**	**NSYSDC42 + NSYSDC62 / NSYSDC43 + NSYSDC63**	-

1200		PanelSeT SD	PanelSeT SD	PanelSeT SD
		**NSYSD12R**	**NSYSDC42 / NSYSDC43**	4 x **NSYRP2**
		**NSYSD12R**	**NSYSDC62 / NSYSDC63**	3 x **NSYRP2**
		**NSYSD12R**	**NSYSDC62 / NSYSDC63**	3 x **NSYRP2**
		**NSYSD12R**	2 x **NSYSDC62** / 2 x **NSYSDC63**	-
		**NSYSD12R**	**NSYSDC42 + NSYSDC62 / NSYSDC43 + NSYSDC63**	**NSYRP2**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SD: Control Desk

Dimensions

ComPacT Control Desk

1 door

2 doors




Cable gland plate clearance dimensions (mm)	
Width	**Maximum opening.**
B-280	56

Common side view.
(1) Usable clearance.

ComPacT Control Desks with Rear Panel

1 door

2 doors



Cable gland plate clearance dimensions (mm)	
Width	**Maximum opening.**
B-280	56

Adjustment of the depth of the mounting plate (mm)		
Depth	**Min.**	**Max.**
a	42	392
b	129	479


Common side view.
(1) Usable clearance.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Control Desk with Console

1 door

2 doors



Cable gland plate clearance dimensions (mm)	
Width	**Maximum opening.**
B-280	56


Notes	
1	1 entry cable gland plate
2	Maximum opening of the hinged desk lid: 75°
3	Maximum opening of the hinged console cover: 75°
4	Optional mounting plate installation, see page 272

Common side view.
(1) Usable clearance.

Modular Console

Depth 200 mm

Depth 300 mm




(1) Usable clearance.
(2) Same dimensions for the rear panel.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Introduction







The PanelSeT S3CM offer for human-machine interface combines robustness with aesthetics and ergonomics. It consist of:

- A control enclosure,
- A keyboard-box,
- A suspension system of arms and joints, for fixed or rotating solutions, and support accessories.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Introduction



Robustness

- Extruded steel tubes with thickness 40/10e mm
- Top wall reinforced by a plate with a thickness of 30/10e mm



Ease of Use

Easy access to the equipment by a rear door, opening to 120°
Direct installation of accessories on the enclosure frame rail:


- vertical document support
- keyboard support
- laptop computer support

A box keyboard is installed directly on the enclosure



Aesthetics

- Extruded aluminum rail frame
- Frame: RAL 7040 Window gray
- Enclosure: RAL 7035 Light gray
- Customization to your image or the aesthetics of your machine: Consult us



Flexibility

Adaptable system with diverse options of tubes and connectors



Ergonomics

Frame designed to facilitate the handling and usage of the enclosure by the operator

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack


Introduction

Every model is suitable for tubes with a cross-section of 50 mm.
For cross-section of 80 mm consult us.


Steps to Choose the Suspension System (Medium or Heavy Loads)

1 - Define the total load of the system*: a + b + enclosure + installed equipment (Y-axis).
2 - Define the length of arm L (X-axis).
3 - Find the configuration:


Suspension System without Intermediate Joint.




Size 80 is on demand



Suspension System with Intermediate Joint.




Size 80 is on demand



* The load (a + b + enclosure + installed equipment) needs to be less than the maximum load.

Example



Size 80 is on demand

1 - Total load (kg) = 80 kg.
2 - Length (L) = 1200 mm.
3 - Suspension system without intermediate joint.

Recommended system
> Medium loads Ø 50.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Selection Table

Enclosure dimensions (mm)				Tube section U 50 mm
	H (mm)	W (mm)	D (mm)	References
 PB500421_24_nb	300	300	200	**NSYS3CM303020**
	300	400	200	**NSYS3CM304020**
	400	400	200	**NSYS3CM404020**
	400	600	250	**NSYS3CM406025***
	500	500	250	**NSYS3CM505025**
	600	600	200	**NSYS3CM606020***
	600	800	300	-
	800	600	300	-

Tube		Tube section U 50 mm
	Length (m)	References
 PB500422_33_nb	0.5	**NSYCMT5005**
	1	**NSYCMT5010**
	1.5	**NSYCMT5015**
	2	**NSYCMT5020**

Fixing on support (steel material)		Tube section U 50 mm
		References
 NSYCMUMR50	1 Fixed base	**NSYCMUMR50**
 PB500424_25_nb	2 Wall fixing with joint	**NSYCMUMA50**
 PB500425_30_nb	3 Rotating straight fitting	**NSYCMUMC50**

Inter-tube fitting (aluminum material)		Tube section U 50 mm
		References
 PB500426_28_nb	4 Horizontal inter-tube joint	**NSYCMUIA50**
 PB500427_24_nb	5 Fixed bracket	**NSYCMUTC50**

Fixing on enclosure (aluminum material)		Tube section U 50 mm
		References
 PB500428_18_nb	6 Rotating fixing on enclosure	**NSYCMUCR50**
 PB500429_28_nb	7 Rotating fixing in bracket on enclosure	**NSYCMUCC50**


* Enclosure equipped with a cable gland plate.

4

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack


Selection Table



Fixing on support
2 See page 282

Inter-tube fitting
5 See page 283


Fixing on enclosure
6 See page 283



Fixing on support
1 See page 282

Inter-tube fitting


Fixing on enclosure
6 See page 283



Fixing on support
1 See page 282

Inter-tube fitting
4 See page 282


Fixing on enclosure
7 See page 283



Fixing on support
1 See page 282

Inter-tube fitting

Fixing on enclosure
6 See page 283



Fixing on support
3 See page 282

Inter-tube fitting
5 See page 283

Fixing on enclosure
6 See page 283

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Accessories

PanelSeT S3CM

The control enclosures consist of:
A steel body equipped with:
- Reinforcement plate: The top wall is reinforced by a plate (3 mm) and pierced with a hole Ø 54 or 87 mm (according to the reference) to allow hanging installation of the enclosure,
- 4 welded studs on the 2 inner vertical walls, for fixing the rails,
- 2 rails (with drill holes) for installing equipment,
- A rear door, opening to 120° and closing with double-bar lock.

(1) Enclosure equipped with a cable gland plate

An aluminum front face (2.5 mm thick):
- This surface is protected on both sides by a plastic film, allowing the installation of the dialogue elements,
- A trim frame made from 4 extruded-aluminum rails.
- Structured finish, epoxy polyester powder, RAL 7040 gray color (other colors on demand).
- The design of these rails takes into account the accessory mounting functions (lamp, document support, keyboard support, laptop support, etc.), the ergonomics for handling the enclosure and its overall aesthetics.
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Ingress protection rating: IP54 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262
- UL (cULus) certification with rating 1, 2, 3R, 12 and 13 according to UL50E

For more details see page 284



NSYS3CM303020

Characteristics	Enclosure load (kg)	Tube section (mm)	Height (mm)	Width (mm)	Depth (mm)	References
HMI encl. PanelSeT S3CM	8.6	50	300	300	200	**NSYS3CM303020**
HMI encl. PanelSeT S3CM	9.5	50	300	400	200	**NSYS3CM304020**
HMI encl. PanelSeT S3CM	11.4	50	400	400	200	**NSYS3CM404020**
HMI encl. PanelSeT S3CM (1)	17.9	50	400	600	250	**NSYS3CM406025**
HMI encl. PanelSeT S3CM	20.2	50	500	500	250	**NSYS3CM505025**
HMI encl. PanelSeT S3CM (1)	26.5	50	600	600	200	**NSYS3CM606020**

Human-Machine Interface - Specific Accessories

Box Keyboard for Control Enclosure

- The box is installed on the control enclosures with a width of 600 mm. It then has an angle of 120° with its front face. All the accessories required for installation are delivered with 2 brackets and 1 trim rail, 1 hose for cable entry.

The box consists of:
- A steel body, structured finish, epoxy polyester powder, RAL 7035 gray color, with a screwed cover, an aluminum front face (2.5 mm thick) for installing a keyboard,
- A trim frame made from 2 extruded-aluminum rails for ergonomic handling of the box and the aesthetics of the unit. The frame and the front face are delivered assembled. Structured finish, epoxy polyester powder painting, RAL 7040 gray color.
- Ingress protection rating: IP54
- Mechanical protection rating: IK10
- Weight: 8 kg

For more details see page 284



NSYCMT2560110

Characteristics	Height (mm)	Width (mm)	References
Box-keyboard for control enclosure	250	600	**NSYCMT2560110**

Support

- Installation on the left or right rail of the frame of the control enclosure.
- Material: Sheet steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Thickness: 15/10e mm

For more details see page 284



NSYCMBPT

Characteristics	References
Support for Keyboard	**NSYCMBPT**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Accessories

Tube

The tubes are available in:
- 2 sizes: Square of 50 and 80 mm,
- 4 lengths: 0.5, 1, 1.5 and 2 m
- Material: Extruded steel
- Finish: structured finish, powder
- Color: RAL 7035 gray
- Thickness: 40/10e mm


NSYCMT5005

Characteristics	Square (mm)	Length (m)	Weight (kg/m)	References
Tube	50	0.5	6.5	**NSYCMT5005**
Tube	50	1	6.5	**NSYCMT5010**
Tube	50	1.5	6.5	**NSYCMT5015**
Tube	50	2	6.5	**NSYCMT5020**

Fixed Base

- Support foot for direct horizontal or vertical connection.
- Material: Molded steel
- Color: RAL 7040 gray

For more details see page 285


NSYCMUMR50

Characteristics	Square (mm)	Weight (kg)	References
Fixed base	50	3.25	**NSYCMUMR50**

Wall Fixing with Joint

- Device allowing rotation through 170° of a horizontal tube, with a square section of 50 or 80 mm, and its fixing on a vertical surface.
- Protection by bellows, RAL 7035 gray color.
- Option of passing cables through the inside of the joint.
- Material: Molded steel
- Color: RAL 7040 gray

For more details see page 285



NSYCMUMA50

Characteristics	Square (mm)	Weight (kg)	References
Wall fixing with joint	50	4.35	**NSYCMUMA50**

Rotating Straight Fitting

- Device allowing the fixing and rotation through 295° of tubes, with a square section of 50 or 80 mm, in horizontal position.
- Without blocking the chosen position.
- Fixing by 4 screws, not included.
- Material: Molded steel
- Color: RAL 7040 gray

For more details see page 285



NSYCMUMC50

Characteristics	Square (mm)	Weight (kg)	References
Rotating straight fitting	50	5.4	**NSYCMUMC50**

Horizontal Inter-Tube Joint

- Device allowing the linking and rotation through 170° of 2 horizontal tubes, with a square section of 50 or 80 mm.
- Protection by bellows, RAL 7035 gray color.
- Option of passing cables through the inside of the joint.
- Material: Molded steel
- Color: RAL 7040 gray

For more details see page 285



NSYCMUIA50

Characteristics	Square (mm)	Weight (kg)	References
Horizontal inter-tube joint	50	4.25	**NSYCMUIA50**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack

Accessories

Fixed Bracket

- Our system of tubes and joints, fixed or rotating, enables all the solutions to respond to the installation needs of the control enclosures for human-machine dialogue.
- Device allowing the combination and fixing of a horizontal tube with a vertical tube.
- Material: Aluminum
- Color: RAL 7040 gray



NSYCMUTC50

For more details see page 285

Characteristics	Square (mm)	Weight (kg)	References
Fixed bracket	50	1.35	**NSYCMUTC50**

Rotating Fixing on Enclosure

- Device allowing the fixing and rotation through 300° of tubes, with a square section of 50 or 80 mm, in vertical position.
- System for blocking in the chosen position.
- Fixing through the support surface by 4 screws.
- Material: Aluminum
- Color: RAL 7040 gray



NSYCMUCR50

For more details see page 285

Characteristics	Square (mm)	Weight (kg)	References
Rotating fixing on enclosure	50	1.25	**NSYCMUCR50**

Rotating Fixing in Bracket on Enclosure

- Devices allowing the fixing and rotation through 300° of tubes, with a square section of 50 or 80 mm, in horizontal position.
- System for blocking in the chosen position.
- Fixing through the support surface by 4 screws.
- Material: Aluminum
- Color: RAL 7040 gray



NSYCMUCC50

For more details see page 285

Characteristics	Square (mm)	Weight (kg)	References
Rotating fixing in bracket on enclosure	50	2	**NSYCMUCC50**

Adapter for Signaling Beacon

- It is installed on fixed brackets ref. **NSYCMUTC50**.
- Material: Aluminum.
- Finish: Structured finish, powder.
- Color: RAL 7040 gray



NSYCMACS50


Characteristics	Square (mm)	Weight (kg)	References
Adapter for signaling beacon	50	0.025	**NSYCMACS50**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT S3CM: Control Enclosure with Suspension Rack

Dimensions

HMI Enclosure PanelSeT S3CM








A: Height.
B: Width.
C: Depth.

W600 enclosure + box keyboard installation



1 Cable gland plate.

Figure 1
Enclosure depth from 200 to 250





Figure 2
Enclosure depth 300



Enclosure dimensions (mm)								Cable gland plate	Ø Top hole (mm)	Fig.	Enclosure References
Height (mm)	Width (mm)	Depth (mm)	D	F	G	H	J				
300	300	200	162	262	262	100	45	-	54	1	**NSYS3CM303020**
300	400	200	162	362	262	100	45	-	54	1	**NSYS3CM304020**
400	400	200	262	362	362	100	45	-	54	1	**NSYS3CM404020**
400	600	250	262	562	362	125	75	●	54	1	**NSYS3CM406025***
500	500	250	362	462	462	125	75	-	54	1	**NSYS3CM505025**
600	600	200	462	562	562	100	45	●	54	1	**NSYS3CM606020***
600	800	300	462	762	562	150	100	-	87	2	**NSYS3CM608030**

* Enclosure equipped with a cable gland plate.



Perforated Rails Installed on Lateral Studs.



Detail of the Reinforcement Plate.





Rear Door with Double-Bar Lock.



Fixing of the Trim Frame by Screws.

Box Keyboard for Control Enclosure






Detail from the Installation of the Box Keyboard on the Control Enclosure.

Support

Keyboard




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3CM: Control Enclosure with Suspension Rack


Dimensions

Suspension System


	Fixed base	Wall fixing with joint		Rotating straight fitting	Horizontal inter-tube joint
Weight (kg)	3.25	4.35	9.45	5.4	4.25
Dimensions (mm) ⍁ A	**50 mm²**	**50 mm²**	**80 mm²**	**50 mm²**	**50 mm²**
B	42	92	115	50	42
C	105	118	160	68	236
D	11	42	72	42	67
E	125	85	130	30	148
F	152	11	11	96	-
G	-	148	190	96	-
H	72	80	115	134	-
I	97	130	175	140	-
J	-	55	90	120	-
K	-	68	103	9	-
L	110	105	150	55	-
S	15	-	-	-	-
References	**NSYCMUMR50**	**NSYCMUMA50**	**NSYCMUMA80**	**NSYCMUMC50**	**NSYCMUIA50**



	Fixed bracket	Rotating fixing on enclosure	Rotating fixing in bracket on enclosure
Weight (kg)	1.35	1.25	2
Dimensions (mm) ⍁ A	**50 mm²**	**50 mm²**	**50 mm²**
B	46	42	46
C	60	115	60
D	60	96	147
E	46	52.3	96
F	42	58	42
G	144	-	154
H	-	-	42
I	-	-	58
M	-	M6	M6
References	**NSYCMUTC50**	**NSYCMUCR50**	**NSYCMUCC50**



Adapter for Signalling Beacon



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Network and Server

Panel**SeT** SFN IT: Floor-Standing Enclosures for IT

PB503964



Panel**SeT** S3D: Wall-Mounted Enclosures for IT

NSYS3D4620



Actassi OPB: Open Box

PB501435-layout694



Actassi KDB: Knock Down Box

PB501418-layout8463



P133087-layout4746



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D: Wall-Mounted Enclosures for IT

Introduction	288
Characteristics	290
Accessories	291

Panel**SeT** SFN IT: Floor-Standing Enclosures for IT

Introduction	288
Selection Table	292
Accessories	294
Dimensions	311

Actassi OPB: Open Box

Introduction	312
Characteristics	314
Accessories	317

Actassi KDB: Knock Down Box

Introduction	312
Characteristics	318

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3D-SFN IT

Introduction



Industrial businesses need adaptable IT solutions that evolve with their needs. A dynamic industrial environment requires versatile, future-proof systems that drive operational efficiency and innovation.

Our approach centers on flexible modular systems that are meticulously designed to be tailored to the specific requirements of each customer. Offering customizable configurations, seamless scalability, and integration possibilities, our solutions effortlessly adapt to evolving technological and operational demands.

Moreover, this range can be configured to meet your specific requirements, supported by our customization services.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.




Robust
- Housing for IT infrastructure
- Sturdy with IP55 ingress protection
- Durable




Flexible
- Modular system based on SFN enclosure in kit and rack accessories
- Configurable to adapt it to specific requirements



Lower Impact Approach
- CO_2 footprint reduction using low-carbon steel
- Recycled cardboard packaging



Efficient
- Simplified design for an optimized mounting
- User friendly mounting and intuitive design
- Streamline operations and enhance productivity



Cooling
- Effective thermal management to maintain optimal operating temperatures, to preserve longevity and performance of the IT equipment
- Wide range of cooling options



Customizable
- Personalization to specific requirements including several services
- Easy design thanks to the Custom Enclosure Configurator software tool

This range can be configured according to your needs
4 different services available:


Assemble to order


Mounting of standard accessories


Machining


Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D: Wall-Mounted Enclosures for IT

Characteristics

Panel**SeT** S3D Empty Enclosure

- Single-piece body (cross-shaped structure). Gutter-shaped front profile with double fold. Flat rear.
- Cable gland plate with marking for easy drilling and to help guarantee the maximum access surface; delivered with the enclosure. This plate is flush with the body of the enclosure.
- Glazed door, 4 mm-thick Securit® glass, easily removable and reversible, with 20 mm return with double thickness granting excellent rigidity, opening to 120°, equipped with 2 or 3 invisible hinges (From the height of 800 mm).
- Material: Steel.
- Finish: structured finish, epoxy polyester powder.
- Color: RAL 7035 gray.
- Ingress protection rating: IP66 for the single-door enclosures according to IEC 60529.
- Mechanical protection rating: IK10 for the plain-door enclosures according to IEC 62262, IK08 for the glazed-door enclosures.
- Maximum load: 50 kg/m².
- Fixing: direct wall-mounted or with the help of fixing lugs installed from the outside (to be ordered separately, see page 478).
- Other characteristics: for heights from 600 mm, three locking points with linkage, with a single control point. Simple reversal.

Delivery includes a handle with two functions:



- Operating key.
- Tool for loosening the stud protection caps.

This handle can be solidly attached to the locking system by means of a captive element.
Perforated rails on the door, with drill holes with a diameter of 4.2 mm in steps of 25 mm:

- 2 vertical rails from the height of 400 mm and from the width of 800 mm.

Note:
Door opening to 180°
with optional hinges (page 555)

Supply:
Wall-mounted enclosure supplied with 3-mm double-bar lock as standard

Glazed Door	Plain Door	Fixed Rack	Swing Rack
			

Dimensions (mm)			References			
Height	Width	Depth				
400	600	200	**NSYS3D4620T**	**NSYS3D4620**	**NSYVDM8UF**	-
400	600	250	**NSYS3D4625T**	**NSYS3D4625**	**NSYVDM8UF**	-
600	600	200	**NSYS3D6620T**	**NSYS3D6620**	**NSYVDM12UF**	**NSYVDM11UP**
600	600	250	**NSYS3D6625T**	**NSYS3D6625**	**NSYVDM12UF**	**NSYVDM11UP**
600	600	300	**NSYS3D6630T**	**NSYS3D6630**	**NSYVDM12UF**	**NSYVDM11UP**
600	600	400	**NSYS3D6640T**	**NSYS3D6640**	**NSYVDM12UF**	**NSYVDM11UP**
800	600	200	**NSYS3D8620T**	**NSYS3D8620**	**NSYVDM17UF**	**NSYVDM16UP**
800	600	250	**NSYS3D8625T**	**NSYS3D8625**	**NSYVDM17UF**	**NSYVDM16UP**
800	600	300	**NSYS3D8630T**	**NSYS3D8630**	**NSYVDM17UF**	**NSYVDM16UP**
800	600	400	**NSYS3D8640T**	**NSYS3D8640**	**NSYVDM17UF**	**NSYVDM16UP**
1000	600	250	**NSYS3D10625T**	**NSYS3D10625**	**NSYVDM21UF**	**NSYVDM20UP**
1000	600	300	**NSYS3D10630T**	**NSYS3D10630**	**NSYVDM21UF**	**NSYVDM20UP**
1000	600	400	**NSYS3D10640T**	**NSYS3D10640**	**NSYVDM21UF**	**NSYVDM20UP**
1000	800	250	**NSYS3D10825T**	**NSYS3D10825**	-	**NSYVDM20U8P**
1000	800	300	**NSYS3D10830T**	**NSYS3D10830**	-	**NSYVDM20U8P**
1000	800	400	**NSYS3D10840T**	**NSYS3D10840**	-	**NSYVDM20U8P**
1200	800	300	**NSYS3D12830T**	**NSYS3D12830**	-	**NSYVDM25U8P**
1200	800	400	**NSYS3D12840T**	**NSYS3D12840**	-	**NSYVDM25U8P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT S3D: Wall-Mounted Enclosures for IT

Accessories

PanelSeT S3D Fixed Rack (racks to be ordered separately)

- 19" fixed chassis composed by 2 19" uprights with fixing hardware.
- Thickness: 20/10e mm.
- Material: Galvanized steel
- Maximum load: 3 kg per unit

Note:
Adjustable in depth by fixing on the step slides in accessories (see page 521).




NSYVDM8UF

Characteristics	Number of U	Height (mm)	Width (mm)	References
Fixed rack	8	400	600	**NSYVDM8UF**
Fixed rack	12	600	600	**NSYVDM12UF**
Fixed rack	17	800	600	**NSYVDM17UF**
Fixed rack	21	1000	600	**NSYVDM21UF**

PanelSeT S3D Swing Rack (racks to be ordered separately)

- 19" swing chassis opening to 120° with locking system by 3-mm double-bar insert.
- Material: Steel
- Finish: Epoxy polyester powder
- Color: RAL 7035 gray
- Maximum load: 3 kg per unit



NSYVDM11UP

Characteristics	Number of U	Height (mm)	Width (mm)	References
Swing rack	11	600	600	**NSYVDM11UP**
Swing rack	16	800	600	**NSYVDM16UP**
Swing rack	20	1000	600	**NSYVDM20UP**
Swing rack	25	1200	800	**NSYVDM25U8P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.




PanelSeT SFN IT: Floor-Standing Enclosures for IT

Selection Table

All the parts you need to build your Industrial IT enclosure in 4 simple steps:

Choose:

1 Dimensions ····· 2 Front and back ·····

			Structure		Side panels	Doors			Back panel	Cable entry plates
			 NSYSFNV12	 NSYSFNC64	 NSYEC35	 NSYSFND128	 NSYSFND128T	 NSYPCVDN126	 NSYBPN126	 NSY2SPN124
Dimensions (mm)										
Height	**Width**	**Depth**	**Uprights**	**Frames+roof**	**Side panels**	**Plain**	**Transparent**	**Ventilated**	**Back panel**	**plain**
1200	600	600	**NSYSFNV12**	**NSYSFNC66**	**NSY2SPN126**	**NSYSFND126**	**NSYSFND126T**	**NSYPCVDN126**	**NSYBPN126**	**NSYEC66**
	600	800	**NSYSFNV12**	**NSYSFNC68**	**NSY2SPN128**	**NSYSFND126**	**NSYSFND126T**	**NSYPCVDN126**	**NSYBPN126**	**NSYEC68**
	800	600	**NSYSFNV12**	**NSYSFNC86**	**NSY2SPN126**	**NSYSFND128**	**NSYSFND128T**	**NSYPCVDN128**	**NSYBPN128**	**NSYEC86**
	800	800	**NSYSFNV12**	**NSYSFNC88**	**NSY2SPN128**	**NSYSFND128**	**NSYSFND128T**	**NSYPCVDN128**	**NSYBPN128**	**NSYEC88**
1400	600	600	**NSYSFNV14**	**NSYSFNC66**	**NSY2SPN146**	**NSYSFND146**	**NSYSFND146T**	-	**NSYBPN146**	**NSYEC66**
	600	800	**NSYSFNV14**	**NSYSFNC68**	**NSY2SPN148**	**NSYSFND146**	**NSYSFND146T**	-	**NSYBPN146**	**NSYEC68**
	800	600	**NSYSFNV14**	**NSYSFNC86**	**NSY2SPN146**	**NSYSFND148**	**NSYSFND148T**	-	**NSYBPN148**	**NSYEC86**
	800	800	**NSYSFNV14**	**NSYSFNC88**	**NSY2SPN148**	**NSYSFND148**	**NSYSFND148T**	-	**NSYBPN148**	**NSYEC88**
1600	600	600	**NSYSFNV16**	**NSYSFNC66**	**NSY2SPN166**	**NSYSFND166**	**NSYSFND166T**	-	**NSYBPN166**	**NSYEC66**
	600	800	**NSYSFNV16**	**NSYSFNC68**	**NSY2SPN168**	**NSYSFND166**	**NSYSFND166T**	-	**NSYBPN166**	**NSYEC68**
	800	600	**NSYSFNV16**	**NSYSFNC86**	**NSY2SPN166**	**NSYSFND168**	**NSYSFND168T**	-	**NSYBPN168**	**NSYEC86**
	800	800	**NSYSFNV16**	**NSYSFNC88**	**NSY2SPN168**	**NSYSFND168**	**NSYSFND168T**	-	**NSYBPN168**	**NSYEC88**
1800	600	600	**NSYSFNV18**	**NSYSFNC66**	**NSY2SPN186**	**NSYSFND186**	**NSYSFND186T**	-	**NSYBPN186**	**NSYEC66**
	600	800	**NSYSFNV18**	**NSYSFNC68**	**NSY2SPN188**	**NSYSFND186**	**NSYSFND186T**	-	**NSYBPN186**	**NSYEC68**
	800	600	**NSYSFNV18**	**NSYSFNC86**	**NSY2SPN186**	**NSYSFND188**	**NSYSFND188T**	**NSYPCVDN188**	**NSYBPN188**	**NSYEC86**
	800	800	**NSYSFNV18**	**NSYSFNC88**	**NSY2SPN188**	**NSYSFND188**	**NSYSFND188T**	**NSYPCVDN188**	**NSYBPN188**	**NSYEC88**
2000	600	600	**NSYSFNV20**	**NSYSFNC66**	**NSY2SPN206**	**NSYSFND206**	**NSYSFND206T**	**NSYPCVDN206**	**NSYBPN206**	**NSYEC66**
	600	800	**NSYSFNV20**	**NSYSFNC68**	**NSY2SPN208**	**NSYSFND206**	**NSYSFND206T**	**NSYPCVDN206**	**NSYBPN206**	**NSYEC68**
	600	1000	**NSYSFNV20**	**NSYSFNC610**	**NSY2SPN2010**	**NSYSFND206**	**NSYSFND206T**	**NSYPCVDN206**	**NSYBPN206**	**NSYEC610**
	800	600	**NSYSFNV20**	**NSYSFNC86**	**NSY2SPN206**	**NSYSFND208**	**NSYSFND208T**	**NSYPCVDN208**	**NSYBPN208**	**NSYEC86**
	800	800	**NSYSFNV20**	**NSYSFNC88**	**NSY2SPN208**	**NSYSFND208**	**NSYSFND208T**	**NSYPCVDN208**	**NSYBPN208**	**NSYEC88**
	800	1000	**NSYSFNV20**	**NSYSFNC810**	**NSY2SPN2010**	**NSYSFND208**	**NSYSFND208T**	**NSYPCVDN208**	**NSYBPN208**	**NSYEC810**
2200	600	600	**NSYSFNV22**	**NSYSFNC66**	**NSY2SPN226**	**NSYSFND226**	**NSYSFND226T**	**NSYPCVDN226**	**NSYBPN226**	**NSYEC66**
	600	800	**NSYSFNV22**	**NSYSFNC68**	**NSY2SPN228**	**NSYSFND226**	**NSYSFND226T**	**NSYPCVDN226**	**NSYBPN226**	**NSYEC68**
	600	1000	**NSYSFNV22**	**NSYSFNC610**	**NSY2SPN2210**	**NSYSFND226**	**NSYSFND226T**	**NSYPCVDN226**	**NSYBPN226**	**NSYEC610**
	800	600	**NSYSFNV22**	**NSYSFNC86**	**NSY2SPN226**	**NSYSFND228**	**NSYSFND228T**	**NSYPCVDN228**	**NSYBPN228**	**NSYEC86**
	800	800	**NSYSFNV22**	**NSYSFNC88**	**NSY2SPN228**	**NSYSFND228**	**NSYSFND228T**	**NSYPCVDN228**	**NSYBPN228**	**NSYEC88**
	800	1000	**NSYSFNV22**	**NSYSFNC810**	**NSY2SPN2210**	**NSYSFND228**	**NSYSFND228T**	**NSYPCVDN228**	**NSYBPN228**	**NSYEC810**
Details			see page 252		see page 461	see page 554		see page 296	see page 76	see page 501

SELECT IT!
Use our Product Selector to order the necessary parts:
https://www.se.com/ww/en/product-range/5778




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Selection Table

3 Generic accessories

4 Rack system

Cable entry plates		Plinths (H 100 mm)		Plinths (H 200 mm)		19" fixed rack			19" swing rack	
 NSYEC351 NSYEC662		 NSYSPF6100 NSYSPS6100		 NSYSPF6200 NSYSPS6200		 NSYRCK24 NSYRCK36 NSYRC12			 NSYRSW636 NSYRSW36	
1-entry	2-entry	Front/rear	Sides	Front/rear	Sides	Rack	Support	Side covers	Centered	Off-center
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK24	-	-	-	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK24	-	-	-	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK24(1)	NSYRCKS6	NSYRC12	-	-
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK24(1)	NSYRCKS8	NSYRC12	-	-
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK29	-	-	-	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK29	-	-	-	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK29(1)	NSYRCKS6	NSYRC14	-	NSYRSW27
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK29(1)	NSYRCKS8	NSYRC14	-	NSYRSW27
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK33	-	-	-	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK33	-	-	-	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK33(1)	NSYRCKS6	NSYRC16	-	NSYRSW31
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK33(1)	NSYRCKS8	NSYRC16	-	NSYRSW31
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK38	-	-	NSYRSW636	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK38	-	-	NSYRSW636	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK38(1)	NSYRCKS6	NSYRC18	NSYRSWC36	NSYRSW36
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK38(1)	NSYRCKS8	NSYRC18	NSYRSWC36	NSYRSW36
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK42	-	-	NSYRSW640	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK42	-	-	NSYRSW640	-
NSYEC6101	NSYEC6102	NSYSPS6100	NSYSPF10100	NSYSPS6200	NSYSPF10200	NSYRCK42	-	-	NSYRSW640	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK42(1)	NSYRCKS6	NSYRC20	NSYRSWC40	NSYRSW40
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK42(1)	NSYRCKS8	NSYRC20	NSYRSWC40	NSYRSW40
NSYEC8101	NSYEC8102	NSYSPS8100	NSYSPF10100	NSYSPS8200	NSYSPF10200	NSYRCK42(1)	NSYRCKS10	NSYRC20	NSYRSWC40	NSYRSW40
NSYEC661	NSYEC662	NSYSPF6100	NSYSPS6100	NSYSPF6200	NSYSPS6200	NSYRCK47	-	-	NSYRSW645	-
NSYEC681	NSYEC682	NSYSPF6100	NSYSPS8100	NSYSPF6200	NSYSPS8200	NSYRCK47	-	-	NSYRSW645	-
NSYEC6101	NSYEC6102	NSYSPS6100	NSYSPF10100	NSYSPS6200	NSYSPF10200	NSYRCK47	-	-	NSYRSW645	-
NSYEC861	NSYEC862	NSYSPF8100	NSYSPS6100	NSYSPF8200	NSYSPS6200	NSYRCK47(1)	NSYRCKS6	NSYRC22	NSYRSWC45	NSYRSW45
NSYEC881	NSYEC882	NSYSPF8100	NSYSPS8100	NSYSPF8200	NSYSPS8200	NSYRCK47(1)	NSYRCKS8	NSYRC22	NSYRSWC45	NSYRSW45
NSYEC8101	NSYEC8102	NSYSPS8100	NSYSPF10100	NSYSPS8200	NSYSPF10200	NSYRCK47(1)	NSYRCKS10	NSYRC22	NSYRSWC45	NSYRSW45
see page 502		see page 469				see page 298	see page 299	see page 299	see page 301	see page 301

(1) Support brackets for coupling the fixed rack to enclosures of width 800 mm (NSYRCK•, see **page 298**), possible to reinforce the rigidity by central fixing kit (**NSYRCK19KIT**, see **page 299**).


CONFIGURE IT!
Try our Custom Enclosure Configurator for fully assembled and personalized solution:
https://custom-enclosures.se.com

Request it mounted with our customization services (on demand)

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories



Installation Accessories

Composition Accessories

1 Plinths

See details p. 469

2 1 U / 3 U Support

See details p. 303

3 Partial single slides

See details p. 303

4 Front panels

See details p. 309

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Fixing Accessories

5



Fixings

See details p. 304

Cable Management Accessories

Cable Entry Accessories

6



Cable gland plate: Plain, 1 entry, 2 entries

See details p. 501

7



Actassi gland plates and related accessories

See details p. 296

8



Fixing of cable ducts

See details p. 303

9



Guides

See details p. 309

Cable Management Accessories

Electrical Distribution Accessories

10



Trays

See details p. 305

11



Earthing strip

See details p. 305

12



Slides and related accessories

See details p. 307

13



DIN rail

See details p. 309

Electrical Distribution Accessories

14



Rear cable guide support

See details p. 303

15



19'' fixed rakcs and related accessories

See details p. 298

16



Swing racks and related accessories

See details p. 301

Door Accessories

17



Doors: plain, transparent and ventilated

See details p. 296

18



Hinges

See details p. 302

19



Switch

See details p. 304

20



Mechanical and pneumatic retainer

See details p. 304

> For more information consult the Accessories chapter **page 296** and **456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Single Ventilated Door for 19" Racks

- Door designed to achieve natural airing of the enclosure.
- Installation on enclosures with a width of 600 and 800 mm, equipped with centered fixed or swing racks. Opening of 120°.
- Standard locking system with handle and 5-mm double-bar insert.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
1 ventilated door for racks


NSYPCVDN126

Characteristics	Height (mm)	Width (mm)	References
Single ventilated door	1200	600	**NSYPCVDN126**
Single ventilated door	1200	800	**NSYPCVDN128**
Single ventilated door	1800	800	**NSYPCVDN188**
Single ventilated door	2000	600	**NSYPCVDN206**
Single ventilated door	2000	800	**NSYPCVDN208**
Single ventilated door	2200	600	**NSYPCVDN226**
Single ventilated door	2200	800	**NSYPCVDN228**

4

Roof Plate Elevators for Aeration

- Columns with a height of 20 mm.
- Fixing: Between the roofplate and the roof.

Supply:
100 units. Reference by unit.
Order by multiples of 100 (100, 200, 300…).


NSYEX206

Characteristics	References
Roof plate elevators for aeration	**NSYEX206**

Actassi Plain Cable Gland Plate

- Material: Galvanized steel
- Fixing: Fixing on the outside of the roof and bottom support plate
  Can be combined with other types of cable gland plates

Supply:
1 plain cable gland plate and fixing elements


NSYEC440

Characteristics	References
Actassi plain cable gland plate	**NSYEC440**

Actassi Cable Gland Plate with Brush

- Material: Galvanized steel
- Fixing: Fixing on the outside of the roof and bottom support plate
  Can be combined with other types of cable gland plates

Supply:
1 cable gland plate with brush and fixing elements


NSYECP440

Characteristics	References
Actassi cable gland plate with brush	**NSYECP440**

Actassi Self-Ventilated Cable Gland Plate

- Material: Galvanized steel
- Fixing: Fixing on the outside of the roof and bottom support plate
  Can be combined with other types of cable gland plates

Supply:
1 self-ventilated cable gland plate and fixing elements


NSYECAV440

Characteristics	References
Actassi self-ventilated cable gland plate	**NSYECAV440**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Actassi Airing Plate with or without Fans, Symbol Diameter Before 120 mm

Supply:
1 cable gland plate with or without fans, 2-m power cord (version with fans) and fixing elements
Versions with 2 or 3 fans: Each of them has an output capacity of 170 m³/h, 220 V-50/60 Hz, installed and wired to a terminal strip. A 2-m power cord is supplied connected




- Fixing: Fixing on the outside of the roof and bottom support plate
  Can be combined with other types of cable gland plates
- Other characteristics: Sound level: 34 dB (A)



NSYECVT3V440

Characteristics	Description	References
Actassi airing plate with or without fans, symbol diameter before 120 mm	With 3 fans	**NSYECVT3V440**
Actassi airing plate with or without fans, symbol diameter before 120 mm	With 2 fans	**NSYECVT2V440**





Top frame - 3 blanking plates

Width	Depth	Example 1	Example 2	Example 3	Example 4
600 mm **800 mm**	**600 mm** **800 mm** **1000 mm**				
Cut-out = 400 x 450 mm		400 mm	400 mm	400 mm	400 mm

DB300703

3 x 150 mm

Top frame - 2 Blanking plates

Width	Depth	Example 1	Example 2	Example 3	Example 4
600 mm **800 mm**	**600 mm**				
Cut-out = 400 x 300 mm		400 mm	400 mm	400 mm	400 mm

DB300704_nb

2 x 150 mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Partial 19" Fixed Rack


NSYRCKP12

- Rack designed for coupling in enclosures with a width of 600 mm.
- Adjustable depth with a pitch of 25 mm.
- Material: Zinc-coated steel
- Maximum load: 2 kg/U


Installation:

PanelSeT SFN:

- Installation at the top front of the enclosure, no cross-rails needed (1)
- Depth adjustment of the partial rack: two cross-rails need to be installed, see page 526
- For installation at any other height, four cross-rails are required (2)

PanelSeT SM:

- At the front of the enclosure (1): Install two front vertical adaptation profiles, see page 531
- For depth adjustment (2): Install two front vertical adaptation profiles, see page 531 and two rear vertical 40 mm (1 row) cross-rails and four cross-rails, see page 526



(1) (2)

Supply:
2 uprights and fixing elements

Characteristics	Number of units	Height (mm)	References
Partial 19" fixed rack	4	200	**NSYRCKP4**
Partial 19" fixed rack	8	400	**NSYRCKP8**
Partial 19" fixed rack	12	600	**NSYRCKP12**
Partial 19" fixed rack	17	800	**NSYRCKP17**
Partial 19" fixed rack	21	1000	**NSYRCKP21**
Partial 19" fixed rack	26	1200	**NSYRCKP26**

19" Fixed Rack


NSYRCK38

- Rack designed for installation in enclosures with a width of 600 mm.
- Adjustable depth with a pitch of 25 mm.
- Material: Zinc-coated steel
- Maximum load: 400 kg for 4 uprights
- Maximum load: 200 kg for 2 uprights


Installation:

PanelSeT SFN:

- Direct fixing on the structure of the enclosures:
- For installation on enclosures with a width of 800 mm, use the 19" fixed-rack support brackets,
- To reinforce the rigidity of the uprights in enclosures with a width of 800 mm, it is advisable to use the central fixing kit, for enclosure heights above 1800 mm, ref. **NSYRCK19KIT**.

PanelSeT SM:

- Fixing on the top/bottom adjustment rails.



Supply:
2 uprights and fixing elements

Characteristics	Number of units	Height (mm)	References
19" fixed rack	24	1200	**NSYRCK24**
19" fixed rack	29	1400	**NSYRCK29**
19" fixed rack	33	1600	**NSYRCK33**
19" fixed rack	38	1800	**NSYRCK38**
19" fixed rack	42	2000	**NSYRCK42**
19" fixed rack	47	2200	**NSYRCK47**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT


Accessories

Support Brackets for 19" Fixed Rack with a Width of 800 mm



NSYRCKS8

- Support brackets for coupling the fixed rack to enclosures with a width of more than 600 mm.
- They allow the depth of the fixed rack to be adjusted with a pitch of 25 mm.
- The fixed sizes are delivered in pairs.
- Material: Zinc-coated steel
- Maximum load: 400 kg



Supply:
4 support brackets and fixing elements


Characteristics	Depth (mm)	References
Support brackets for 19" fixed rack	600	**NSYRCKS6**
Support brackets for 19" fixed rack	800	**NSYRCKS8**
Support brackets for 19" fixed rack	1000	**NSYRCKS10**

Side Plates of the Centered Fixed Rack for a Width of 800 mm



NSYRC20

- Side plates for coupling to the fixed rack in enclosures with a width of 800 mm.
- Direct installation on the rack by screws.
- The fixed sizes are delivered in pairs.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray



Supply:
2 side plates and fixing elements


Characteristics	Height (mm)	References
Side plates of the centered fixed rack	1200	**NSYRC12**
Side plates of the centered fixed rack	1800	**NSYRC18**
Side plates of the centered fixed rack	2000	**NSYRC20**
Side plates of the centered fixed rack	2200	**NSYRC22**

Central Fixing Kit



NSYRCK19KIT

- To reinforce the rigidity of the 19" fixed racks in enclosures with a width of 800 mm.
- Fixing to the enclosure by cross-rails or light cross-rails installed depthwise. See page 526.
- Material: Zinc-coated steel



Supply:
2 supports and fixing elements

Characteristics	References
Central fixing kit	**NSYRCK19KIT**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Partial 19" Swing Rack for 600 and 800 mm Enclosures

- Rack for coupling to enclosures with widths of 600 and 800 mm.
- In enclosures with a width of 800 mm, the rack can be installed centered or off-center.
- Maximum opening: 120°.
- Reversible opening direction: Left/right.
- Locking system, top and bottom, with 5-mm double-bar key.
- The 6 and 9 units racks only with bottom lock.
- Maximum equipment installation depth: 180 mm, in enclosures with a width of 600 mm.
- Material: Zinc-coated steel


Installation:

PanelSeT SFN:

- To install at the front at any height of the enclosure: directly to the framework by rack fixing elements
- For depth adjustment: Install two (for top height) or four (for any height) 65 mm (2 rows) cross-rails, see page 526

PanelSeT SM:

- To install at the front at any height of the enclosure: install two front vertical adaptation profiles, see page 531
- For depth adjustment: Install two front vertical adaptation profiles, see page 531 and two rear vertical 40 mm cross-rails and four 65 mm (2 rows) cross-rails, see page 526
- Maximum load: 2 kg/U



For more details see page 311

(1) Optional installation in enclosures with height of 1200 mm.

Supply:
1 partial 19" swing rack


NSYRSWP15


Characteristics	Number of units (H)	Height (mm)	References
Partial 19" swing rack	6	355	**NSYRSWP6**
Partial 19" swing rack	9	468	**NSYRSWP9**
Partial 19" swing rack	12	601	**NSYRSWP12**
Partial 19" swing rack	15	735	**NSYRSWP15**
Partial 19" swing rack	18	868	**NSYRSWP18**
Partial 19" swing rack (1)	21	1002	**NSYRSWP21**

Partial 19" Swing Rack Support for 600 and 800 mm Enclosures

- Supports for coupling the partial swing rack to enclosures with widths of 600 and 800 mm.
- Height or depth adjustment, with a pitch of 25 mm, by two 65 mm (2 rows) universal cross-rails and a 19" multiple bracket, ref. **NSYMBR19**.
- PanelSeT SFN: Direct fixing to the structure.
- PanelSeT SM: Fixing to the enclosure by means of the vertical adaptation profile, see page 531.
- Material: Zinc-coated steel

Installation:

- Installation of the rack in centered or off-center position, for enclosures with a width of 800 mm



Supply:
2 supports and fixing elements



NSYRSWSP6

Characteristics	Width (mm)	References
Partial 19" swing rack support	600	**NSYRSWSP6**
Partial 19" swing rack support	800	**NSYRSWSP8**

19" Multiple Bracket



NSYMBR19

- Bracket for fixing 65 mm universal cross-rails (2 rows), depthwise, to position the partial 19" swing rack in any direction, up and down and/or depthwise.
- Material: Zinc-coated steel.

Supply:
4 brackets and fixing elements

Characteristics	Width (mm)	References
19" multiple bracket	600	**NSYMBR19**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

19" Swing Rack for 600 mm Enclosures


NSYRSW640

- To be coupled to enclosures with widths of 600 mm.
- Can be moved depthwise with a pitch of 25 mm.
- Reversible opening direction: Left/right.
- Locking system, top and bottom, with 5-mm double-bar key.
- Maximum opening: 130°.
- Maximum equipment installation depth: 180 mm.
- Not compatible with 120° mechanical retainer **NSYRCDR12**

Fixing to the enclosure structure:

PanelSeT SFN:


- Fixing to the enclosure structure.

PanelSeT SM:

- Fixing to the enclosure on top/bottom adjustment rails.

Components:

- Zinc-coated steel central structure.
- Mounting cross-rail on structure made from steel painted with epoxy polyester resin, textured RAL 7035 gray. Fixed to the central structure by screws.


PB504112

Note:
Swing racks are not compatible with double-door.

For more details see page 311

Supply:
1 19" swing rack with no panels

Characteristics	Number of units (H)	Height (mm)	References
19" swing rack	36	1800	**NSYRSW636**
19" swing rack	40	2000	**NSYRSW640**
19" swing rack	45	2200	**NSYRSW645**

19" Swing Rack for 800 mm Enclosures, Off-Center


NSYRSW40

- To be coupled to enclosures with widths of 800 mm.
- Can be moved depthwise with a pitch of 25 mm.
- Reversible opening direction: Left/right.
- Locking system, top and bottom, with 5-mm double-bar key.
- Maximum opening: 130° (option of opening to 180° using 180° hinges).
- Material: Zinc-coated steel and steel painted
- Maximum load: 3.75 kg/unit with a max of 150 kg

Installation:

- PanelSeT SFN-SM
- Other mounting options: Consult us

Maximum equipment installation depth:


- Off-center 19" swing rack: 470 mm
- Centered 19" swing rack: 390 mm

Fixing to the enclosure structure:

- PanelSeT SFN: Fixing to the entire height of the enclosure structure.
- PanelSeT SM: Fixing to the enclosure on top/bottom adjustment rails.

Components:

- Zinc-coated steel central structure.
- Mounting cross-rail on structure made from steel painted with epoxypolyester resin, textured RAL 7035 gray.
- Fixed to the central structure by screws.
- Side plate made from steel painted with epoxy polyester resin, textured RAL 7035 gray. Fixed to the central structure by screws.


PB504113

Note:
Swing racks are not compatible with double-door.

For more details see page 311

Spare handle:
Order ref. **NSYTEDB5ML** (handle) + **NSYTMME** (blind barrel).

Supply:
Centered and off-center 19" swing rack: hinged rack, 800 mm swing rack supports, side plates with locking system double-bar and fixing elements

Characteristics	Number of units (H)	Height (mm)	References
19" swing rack, off-center	27	1400	**NSYRSW27**
19" swing rack, off-center	31	1600	**NSYRSW31**
19" swing rack, off-center	36	1800	**NSYRSW36**
19" swing rack, off-center	40	2000	**NSYRSW40**
19" swing rack, off-center	45	2200	**NSYRSW45**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

19" Swing Rack for 800 mm Enclosures, Centered


NSYRSWC40


- To be coupled to enclosures with widths of 800 mm.
- Can be moved depthwise with a pitch of 25 mm.
- Reversible opening direction: Left/right.
- Locking system, top and bottom, with 5-mm double-bar key.
- Maximum opening: 130° (option of opening to 180° using 180° hinges).
- Material: Zinc-coated steel and steel painted
- Maximum load: 3.75 kg/unit with a max of 150 kg

Installation:
- PanelSeT SFN-SM
- Other mounting options: Consult us

Maximum equipment installation depth:
- Off-center 19" swing rack: 470 mm
- Centered 19" swing rack: 390 mm

Fixing to the enclosure structure:
- PanelSeT SFN: Fixing to the entire height of the enclosure structure.
- PanelSeT SM: Fixing to the enclosure on top/bottom adjustment rails.

Components:
- Zinc-coated steel central structure.
- Mounting cross-rail on structure made from steel painted with epoxypolyester resin, textured RAL 7035 gray.
- Fixed to the central structure by screws.
- Side plate made from steel painted with epoxy polyester resin, textured RAL 7035 gray. Fixed to the central structure by screws.


PB504114

Note:
Swing racks are not compatible with double-door.

For more details see page 311

Supply:
Centered and off-center 19" swing rack: hinged rack, 800 mm swing rack supports, side plates with locking system double-bar and fixing elements


Characteristics	Number of units (H)	Height (mm)	References
19" swing rack, centered	36	1800	**NSYRSWC36**
19" swing rack, centered	40	2000	**NSYRSWC40**
19" swing rack, centered	45	2200	**NSYRSWC45**

180° Hinge


NSYRSWH180

- Hinge for installation on centered and off-center 19" swing racks.
- Allows the swing rack to be opened to 180°.
- Fixing by M8 screws directly to the swing rack.
- Material: Zamak 5

Maximum equipment installation depth:
Off-center 19" swing rack: 425 mm,
Centered 19" swing rack: 345 mm.


PB504115

Supply:
2 hinges and fixing elements


Characteristics	References
180° hinge	**NSYRSWH180**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

1 U / 3 U Support





NSYRC1U


- Support prepared for installing equipment 1 U or 3 U high.
- Designed with quick-locking for easy installation.
- **PanelSeT SFN:** Direct fixing to the structure.
- **PanelSeT SM:** Fixing to the enclosure by means of the vertical adapter section, see page 531.
- Material Zinc-coated steel

For more details see page 311

Supply:
4 1 U/3 U supports (2 units right and 2 units left) and fixing elements

Characteristics	References
1 U / 3 U support	**NSYRC1U**

19" Partial Single Slides






NSYGB140

- Rails for installation on fixed or swing racks.
- Direct fixing on the structure of the enclosure, by quick-locking.
- Material: Zinc-coated steel
- Thickness: 12/10e mm
- Maximum load: 15 kg

Supply:
2 rails and fixing elements

Characteristics	References
19" partial single slides	**NSYGB140**

Fixing of Cable Ducts on 19" Racks






NSYRCDFIX

- Allows vertical fixing of cable ducts for cable guide.
- Service depth: 150 mm.
- Fixed by quick-locking to the 19" rack profile.
- Material: Zinc-coated steel

Supply:
3 units and fixing elements

Characteristics	References
Fixing of cable ducts on 19" racks	**NSYRCDFIX**

Rear Cable-Guide Support





NSYRCSUP25

- Supports used for installation on the rear of the swing racks.
- Suitable for fixing cable-guide accessories.
- Allow vertical fixing of cable ducts: Adjustable depth with a pitch of 44.45 mm.
- Material: Zinc-coated steel

Supply:
2 cable-guide supports, crossbar and fixing elements

Characteristics	Service depth (mm)	References
Rear cable-guide support	150	**NSYRCSUP15**
Rear cable-guide support	250	**NSYRCSUP25**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

120° Mechanical Retainer

- Retainer for installation on the swing racks.
- Maximum opening: 120°.
- Not compatible with the 19'' swing racks for 600 mm enclosures (NSYRSW6*)

Fixing:
Direct fixing to the rack support and the 19" rack

Supply:
1 mechanical door stop and fixing elements


NSYRCDR12

Characteristics	References
120° mechanical retainer	**NSYRCDR12**

180° Pneumatic Retainer

- Retainer for installation on the swing racks installed with 180° hinges, in enclosures with a depth of 600, 800 or 1000 mm.
- Maximum opening: 180°.

Fixing:
PanelSeT SFN:
Fixing to the base of the structure and to the rack.
PanelSeT SM:
Direct fixing to the rack support and to the 19" rack.

Supply:
1 pneumatic door stop and fixing elements


NSYRCDR18

Characteristics	References
180° pneumatic retainer	**NSYRCDR18**

Flat Escutcheon for Swing 19" Rack


NSYRCLOCK

- Flat escutcheon with 5-mm double-bar insert lock, for installation on swing 19" racks

Supply:
1 flat escutcheon, 5-mm double-bar insert and fixing elements

Characteristics	References
Flat escutcheon for swing 19" rack	**NSYRCLOCK**

Switch for Swing 19" Rack


NSYRCINT

- Switch for direct fixing on the bottom or top support of the swing rack.
- M20 connection.
- NO + NC contact, 10 A/500 V.

Supply:
1 19" rack switch and fixing elements

Characteristics	References
Switch for swing 19" rack	**NSYRCINT**

Fixings for 19" Rack


PB500189_28_nb

- They allow 19" accessories to be mounted.
- Caged nut compatible with 8.5 x 8.5 mm and 9.5 x 9.5 mm holes.


NSYGFR95M63

Characteristics	Set of	References
M6 screws + washers + nuts	30	**NSYGFR95M63**
M6 x 16 screws and washers	50	**NSYGFR166P**
M6 caged nuts	100	**NSYCN9M625**
M6 screws + washers + nuts	50	**NSYGFR95M65**
M5 screws + washers + nuts	50	**NSYGFR95M55**

For any information, refer to Thermal Management chapter, see page 391.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Stand-Off Plinth for Raised Floor


NSYAEBP2F68

- Folded and welded sheet-steel frame, RAL 9005 black, epoxy-polyester, textured, powder paint
- Delivered with feet adjustable from 0 to 60 mm with holes for fixing to the floor
- Can support Actassi VDA, Actassi VDS, Spacial SM and PanelSeT SFN enclosures
- Standard adjustment for heights from 200 mm to a maximum of 300 mm in steps of 25 mm
- Acceptable static load: 1000 kg
- To adjust heights from 335 to 435 mm, use feet reference **NSYAEBP2F4F**.

Characteristics	Width (mm)	Depth (mm)	References
Stand-off plinth for raised floor	600	800	**NSYAEBP2F68**
Stand-off plinth for raised floor	600	1000	**NSYAEBP2F610**
Stand-off plinth for raised floor	800	800	**NSYAEBP2F88**
Stand-off plinth for raised floor	800	1000	**NSYAEBP2F810**

Sheet-Edge Protection Strip


NSYTPV

- 10-m roll of rubber protection strip.

Characteristics	References
Sheet-edge protection strip	**NSYTPV**

Floor-Panel Support Bracket


NSYAEBP2FS6

- Set of 2 brackets made from folded sheet steel painted RAL 9005 black
- They are installed across the width and/or depth on the stand-off plinth to support the panels of the raised floor
- Height adjustment ± 30 mm.

Characteristics	Width (mm)	Depth (mm)	References
Floor-panel support bracket	600	600	**NSYAEBP2FS6**
Floor-panel support bracket	800	800	**NSYAEBP2FS8**
Floor-panel support bracket	1000	1000	**NSYAEBP2FS10**

Earthing Strip (Y)

- Two models available:
  - insulated: 10 x 5 mm brass bar with 40 connection points by screws for lugs (screws not installed)
  - non-insulated: stainless-steel bar, connection by Faston lug 6.5 or by copper bar with caged terminal ref. **NSYAEEC1UN**
- Fixing to the 19" rack or to the framework
- Length: 480 mm
- Delivered with fixings
- Strip reference **NSYAEEC1UN** is equipped with caged terminal blocks.


NSYAEECS

Characteristics	Insulated	References
Earthing strip (Y)	Yes	**NSYAEECS**

Fixed Perforated and Plain 19" Trays, 1U

- Fixing by attachment without tools between the front and rear 19" uprights
- Sheet steel, RAL 7035 or RAL 7016 gray paint
- Acceptable load: 100 kg

Note:
(1) –100 ...+50 mm, adjustable in steps of 25 mm.


NSYBBF1U40P


NSYBBF1U40

Characteristics	Rack depth (mm)	Fixing center-to-center distance (mm)	Color	References
Perforated 19" tray	600-800-1000	258 (1)	RAL 7035	**NSYBBF1U40P**
Perforated 19" tray	800-1000	458 (1)	RAL 7035	**NSYBBF1U60P**
Perforated 19" tray	1000	658 (1)	RAL 7035	**NSYBBF1U80P**
Plain 19" tray	600-800-1000	258 (1)	RAL 7035	**NSYBBF1U40**
Plain 19" tray	800-1000	458 (1)	RAL 7035	**NSYBBF1U60**
Plain 19" tray	1000	658 (1)	RAL 7035	**NSYBBF1U80**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Telescopic Perforated and Plain 19" Trays, 1U

- Fixing by attachment without tools between the front and rear 19" uprights
- Fixing on the telescopic slides supplied
- Sheet steel, RAL 7035 or RAL 7016 gray paint
- Acceptable load: 45 kg

Note:
(1) Slides delivered with the tray.
(2) -100 ...+50 mm, adjustable in steps of 50 mm.


NSYBBT1U40P

Characteristics	Mounting on slides (1)	Rack depth (mm)	Fixing center-to-center distance (mm)	Color	References
Perforated 19" tray	NSYGT40	600-800-1000	258 (2)	RAL 7035	**NSYBBT1U40P**
Perforated 19" tray	NSYGT60	800-1000	458 (2)	RAL 7035	**NSYBBT1U60P**
Perforated 19" tray	NSYGT80	1000	658 (2)	RAL 7035	**NSYBBT1U80P**
Plain 19" tray	NSYGT40	600-800-1000	258 (2)	RAL 7035	**NSYBBT1U40**
Plain 19" tray	NSYGT60	800-1000	458 (2)	RAL 7035	**NSYBBT1U60**
Plain 19" tray	NSYGT80	1000	658 (2)	RAL 7035	**NSYBBT1U80**

1U and 2U Fixed 19" Tray

- Fixing to the front or rear uprights of the 19" rack
- Heel of 5 mm
- Sheet steel, RAL 7035 or RAL 7016 gray paint


NSYBF1U25P

Characteristics	Number of U	Depth (mm)	Load (kg)	Color	References
Fixed 19" tray	1U	250	15	RAL 7035	**NSYBF1U25P**
Fixed 19" tray	2U	250	20	RAL 7035	**NSYBF2U25P**
Fixed 19" tray	2U	380	20	RAL 7035	**NSYBF2U40P**

2U Telescopic 19" Tray

- Fixing to the front uprights of the 19" rack
- Sheet steel, RAL 7035 or RAL 7016 gray paint
- Acceptable load: 5 kg
- Heel of 5 mm.

Supply:
Delivered with the telescopic slides assembled


NSYBT2U25P


Characteristics	Number of U	Depth (mm)	Load (kg)	Color	References
Telescopic 19" tray	2U	250	5	RAL 7035	**NSYBT2U25P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Fixed 19" Slides



- Set of 2 slides for the 19" hardware
- Material: treated steel
- Acceptable load: 60 kg
- Heel 0 mm: fixing by attachment between the front and rear 19" uprights
- Heel ± 5 mm: fixing by screws between the front and rear 19" uprights; supplied with the slides.


NSYGF356

Characteristics	Rack depth (mm)	Distance between the front and rear uprights	Fixing center-to-center distance (mm)	Heel height (mm)	References
Fixed 19" slides	600-800-1000	350	258	0	**NSYGF356**
Fixed 19" slides	800-1000	450	358	0	**NSYGF456**
Fixed 19" slides	800-1000	550	458	0	**NSYGF556**
Fixed 19" slides	1000	650	558	0	**NSYGF656**
Fixed 19" slides	1000	750	658	0	**NSYGF756**
Fixed 19" slides	600-800-1000	350	258	± 5	**NSYGF356H5**

Full Telescopic 19" Slides


NSYGT60

- Set of 2 slides for the 19" hardware
- Material: treated steel
- Acceptable load: 60 kg
- Heel 0 mm: fixing by attachment between the front and rear 19" uprights
- Heel ± 5 mm: fixing by screws between the front and rear 19" uprights; supplied with the slides.

Characteristics	Rack depth (mm)	Fixing center-to-center distance (mm)	References
Full telescopic 19" slides	800-1000	458, -100 ...+50 mm, adjustable in steps of 50 mm	**NSYGT60**
Full telescopic 19" slides	1000	658,-100...+50mm, adjustable in steps of 50 mm	**NSYGT80**

4

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

UTE - 16 A/230 V~ with Pin-Earthed Outlets


NSYAPU19F9


NSYAPU19F8S


NSYAPU19F6CB


NSYAPUF10S


NSYAPUF12CB

- Sockets set at 35° with child protection
- Aluminum profile silver - heigh 1U
- Material: fiberglass polyamide plastic that helps ensuring fire resistance up to 850 °C
- Equipped with power cord (3G 1.5 mm2) type H05 VVF, equipped with a molded right-angle plug with earthing contact system
- According to NF C 61314, IEC 60884 and NBNC61112-1 standards
- Could be used in: France, Belgium, Poland, Monaco, Slovakia, Czech Republic.

Note:
(1) A: rail of sockets without protection
(2) B: rail of sockets with recessed green LED switch
(3) C: rail of sockets with bi-polar magnetothermal circuit-breaker C16 type C60N 16 A curve C
(4) D: suppression filter for interferences up to 30 MHz, guaranteed frequency 400 Hz, attenuation 20 dB per decade.
(5) E: rail of sockets with interference filter and surge suppressor, 6.5 kA short-circuit protection. Protection level Up 1.5 kV, test voltage Uoc 5 kV Uc 255 V, 50 Hz. Operation indicator light, interfaces 30 MHz. Frequency nominal 400 Hz, attenuation 20 dB per decade.
(6) F: rail of sockets with differential protection 30 mA, 2 poles 25 A type NC

Characteristics	Width (mm)	Depth (mm)	Type	References
19" Adapted				
9 sockets outlets	19"	44	A (1)	**NSYAPU19F9**
8 sockets outlets with recessed green led switch	19"	44	B (2)	**NSYAPU19F8S**
6 sockets outlets with Overvoltage protection 16 A	19"	76	C (3)	**NSYAPU19F6CB**
Vertical – 0U				
10 sockets outlets with recessed green led switch (D. 968 mm)	968	44	B (2)	**NSYAPUF10S**
12 sockets outlets with Overvoltage protection 16 A (D. 1232 mm)	1232	76	C (3)	**NSYAPUF12CB**

VDE - 16 A/230 V~ with Pin-Earthed Outlets


NSYAPU19S9


NSYAPU19S8S

- Sockets set at 35° with child protection
- Aluminum profile silver - heigh 1U
- Material: fiberglass polyamide plastic that helps ensuring fire resistance up to 850 °C
- Equipped with power cord (3G 1.5 mm2) type H05 VVF, equipped with a molded right-angle plug with earthing contact system
- According to DIN49 440, VDE0620-1, IEC 60884 and UNE20315 standards
- Could be used in: Germany, Austria, Netherlands, Italy (partial), Spain, Portugal, Sweden, Norway, Finland, Slovenia, Romania, Hungary, Afghanistan, Andorra, Vatican City, San Marino, Estonia, South Korea, Indonesia, Iceland, Chile, Bulgaria.

Note:
(1) A: rail of sockets without protection
(2) B: rail of sockets with recessed green LED switch
(3) C: rail of sockets with bi-polar magnetothermal circuit-breaker C16 type C60N 16 A curve C
(4) D: suppression filter for interferences up to 30 MHz, guaranteed frequency 400 Hz, attenuation 20 dB per decade.
(5) E: rail of sockets with Interference filter and surge suppressor, 6.5 kA short-circuit protection. Protection level Up 1.5 kV, test voltage Uoc 5 kV Uc 255 V, 50 Hz. Operation indicator light, interfaces 30 MHz. Frequency nominal 400 Hz, attenuation 20 dB per decade.
(6) F: rail of sockets with differential protection 30 mA, 2 poles 25 A type NC

Characteristics	Width (mm)	Depth (mm)	Type	References
19" Adapted				
9 sockets outlets	19"	44	A (1)	**NSYAPU19S9**
8 sockets outlets with recessed green led switch	19"	44	B (2)	**NSYAPU19S8S**

Fixing Brackets


NSYAPUBV


NSYAPUB

- For vertical assembly of distribution rails
- Set of 2 brackets, adaptable to all rails, delivered with fixings
- Material: treated steel, thickness 10/10 mm
- Fixing to the ends of the rail: reference
- Fixing with an orientation of 90°: reference **NSYAPUB**.

Characteristics	Fixing	References
Fixing brackets	End of the rail	**NSYAPUBV**
Fixing brackets	Orientation of 90°	**NSYAPUB**

19" Front Plate for Modular Circuit-Breakers


NSYCRTM3UD

- Front plates for mounting 22 modules
- Fixing to the 19" rack
- Front panel made from sheet steel, 15/10 mm thick, RAL 7035 or RAL 7016 gray paint
- Front panel made from 3 mm anodised aluminum.

Supply:
Delivered with steel DIN rail

Characteristics	Number of U	Color	References
19" front plate for modular circuit-breakers	3U	RAL 7035	**NSYCRTM3UD**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

19" DIN Rail


NSYR19DN

- DIN rail for fixing on the front surface of the 19" uprights

Supply:
Delivery by unit.

Characteristics	References
19" DIN rail	**NSYR19DN**

Guides (X)


NSYGCA410

Mounting on:
- The 19" uprights (laterally)
- All the cable-support cross-rails
- At the rear of the 19" shelves
- Material: plastic, RAL 7035 light gray
- Guides and supports: set of 10.

Characteristics	Dimensions (mm)	References
Guides (X)	40 x 100	**NSYGCA410**

1U 19" Front Panel with Cable-Gland Openings

- Fixing on the 19" uprights
- Cable openings protected by a gasket
- Sheet steel, RAL 7035 or RAL 7016 gray paint.


NSYCRTM1U2

Characteristics	References
1U 19" front panel with cable-gland openings, RAL 7035	**NSYCRTM1U2**

1U 19" Front Panels with Metal Guides

- Channels the cables over the front panel of the rack
- Fixing to the 19" rack
- Sheet steel, RAL 7035 or RAL 7016 gray paint.


NSYCRTM1U40B

Characteristics	Number of guides Vert.	Number of guides Horiz.	References
1U 19" front panels with metal guides, RAL 7035	4	0	**NSYCRTM1U40B**

1U 19" Front Panels with Cable-Gland and Brush Gasket

- Fixing on the 19" uprights
- Sheet steel, RAL 7035 or RAL 7016 paint
- 150 mm cable support.


NSYCRTM1U1P

Characteristics	References
With cable support at the rear, RAL 7035	**NSYCRTM1U1P**

1U 19" Front Panel with Insulated Guides

- Channels the cables over the front panel of the rack
- Fixing on the 19" uprights
- Steel front panel, RAL 7035 light gray paint
- Equipped with 5 guides in horizontal, vertical and 45° positions.


NSYCRTM1U5GCA

Characteristics	References
1U 19" front panel with insulated guides	**NSYCRTM1U5GCA**

2U Depth-Adjustable 19" Support

- Fixing on the 19" uprights
- Depth-adjustable from 50 to 200 mm; it allows the installation of non-19" devices or the fixing of cables, ducting, etc.
- Sheet steel, RAL 7035 light gray paint


NSYCRTM2US

Supply:
Delivered with assembly fixings.

Characteristics	References
2U depth-adjustable 19" support	**NSYCRTM2US**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN IT: Floor-Standing Enclosures for IT

Accessories

Plain 19" Front Panel

- Fixing to the 19" rack
- Front panel made from sheet steel, 15/10 mm thick, RAL 7035 or RAL 7016 gray paint
- Front panel made from 3 or 4 mm anodised aluminum
- Fixing by screws reference **NSYGFR95M65**.


NSYCRTM1U

Characteristics	Number of U	RAL 7035 steel References	Aluminum 3 mm References
Plain 19" front panel	1U	**NSYCRTM1U**	**NSYCRTA1U**
Plain 19" front panel	2U	**NSYCRTM2U**	-
Plain 19" front panel	3U	**NSYCRTM3U**	-
Plain 19" front panel	4U	**NSYCRTM4U**	-
Plain 19" front panel	5U	**NSYCRTM5U**	-
Plain 19" front panel	6U	**NSYCRTM6U**	-
Plain 19" front panel	9U	**NSYCRTM9U**	-
Plain 19" front panel	10U	**NSYCRTM10U**	-
Plain 19" front panel	12U	**NSYCRTM12U**	-

Plain 19" Front Panel

- Direct fixing to the 19" rack
- Sheet steel, 15/10 mm thick, RAL 7035 light gray paint
- Allow the entry of air for natural airing of the installations
- Option of installing reference **NSYCRTMR3U** with 3 fans reference: **NSYCVF65M230PF** as accessories
- Fixing by screws reference **NSYGFR95M65**.

PB501481


NSYCRTMR1U

Characteristics	Number of U	Color	References
Plain 19" front panel	1U	RAL 7035	**NSYCRTMR1U**
Plain 19" front panel	3U	RAL 7035	**NSYCRTMR3U**

Adhesive Strip for Marking the U

- Set of 10 self-adhesive strips
- Attached on the front panel of the 19" upright
- Allows the units to be numbered
- Length: 42U.


NSYENU

Characteristics	References
Adhesive strip for marking the U	**NSYENU**

Set of 4 Feet for Stand-Off Plinths

- Folded and welded sheet-steel feet, textured, RAL 9005 black epoxy-polyester powder paint
- They are installed on the stand-off plinths for raised floor, reusing the levelling feet delivered with the plinth
- Acceptable static load: 1000 kg on 4 feet.


NSYAEBP2F4F

Characteristics	References
Set of 4 feet for stand-off plinths	**NSYAEBP2F4F**

Nuts for 19" Uprights


NSYGFR12M65

- Set of 50 M6 caged nuts
- Bag of M6 caged nuts for 12 mm square holes (holes on the rear of the 19" uprights).


Characteristics	Set of	References
Nuts for 19" uprights	50	**NSYGFR12M65**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN IT: Floor-Standing Enclosures for IT

Dimensions


PanelSeT SFN 19" Electronic Enclosure



Partial 19" Swing Rack for 600 and 800 mm Enclosures




Partial 19" Swing Rack for Enclosures with a Width of 600 mm




Partial 19" Swing Rack, Off-Centered, Centered, for Enclosures with a Width of 800 mm


19" Swing Rack for 600 mm Enclosures



19" Swing Racks for 800 mm Enclosures




1 U / 3 U Support



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Actassi OPB and KDB

Introduction



Introducing Actassi OPB and KDB wall-mounted enclosures, designed for seamless integration of network connectivity and optimum protection of data and telecom networks.

KDB and OPB enclosures are an integral part of the Actassi system, and can be fully equipped with patch panels, cables, switches and DVRs.



The Actassi system
Network Connectivity
Actassi is an end-to-end network infrastructure solution for building and data center that serves data and PoE power, and that optimizes the network infrastructure operating costs as part of the Schneider Electric's Collaborative Smart Building IoT Platform.

Ref of the 2024 catalogue :
Ref : LSB02659EN

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Actassi OPB: Open Box



Easy to Install
The Actassi OPB enclosure can be wall-mounted by a single person using the fixing points intended for the passage of holding screw heads into the wall




Ergonomics
The side panels swing through 120° and can be easily removed without tools. Rear access is easy. Door easily removable without tools



Easy to Cable
The cable entries, top or bottom, are pre-cut and open into the rear of the Actassi OPB enclosure. The enclosure fits around those cables that are already in place (rear blanking plate optional)



Adaptable
The 19" uprights are designed to be depth-adjustable with a step of 25 mm. Their fixing with screws helps guaranteeing the rigidity of the Actassi OPB enclosure




Easy to Install and to Reverse
Its drilling template on the packaging and its 4 wall-mounted points enable quick and efficient installation while helping guarantee reversibility by simply turning the enclosure around




Ergonomics
The side panels are locked from the inside by two 1/4-turn nuts, accessible only when the door is open

Actassi KDB: Knock Down Box



Easy to Stock and Ship
The flat-pack architecture of KDB enclosure helps saving 60% of space in the stock. It is also very easy to ship and carry




Easy to Assemble
The symmetric construction of the top, bottom and side panels gives easy and helps assembling



Easy to Use
Tool-less door with spring hinges facilitates the access to the patch panels



Easy Cable Management (Option)
Use the 19” brush panel to easily manage the entry of cables supress into the top and bottom



Smart Airing (Option)
Helps protecting the installed components like switches and PABX. Use the 19” smart fan plates equipped with a thermostat adjustable from 0 °C to 55 °C



Easy to Adapt
If you need more space at the front of the enclosure, you can easily move the 19” uprights each 25 mm



OPB: assembled at delivery, ready to use.
KDB: quick and easy to mount.



OPB: parts can be removed without tools.
KDB: easy to assemble.
1 tool needed.



OPB: body allows mounting of components up to 50 kg.
KDB: body allows mounting of components up to 40 kg.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Actassi OPB: Open Box


Characteristics

Open for Easy Installation and Maintenance
Introduction and Selection Guides

- Wall-mounted enclosure made from folded and welded sheet steel, powder paint, leather-grain finish, RAL 7035 light gray epoxy-polyester
- Enclosure made up of a body, 2 hinged and removable side panels, a 19" swing rack and a Securit® glass transparent door with key no. 333
- Protection rating: IP20 according to IEC 60529
- Impact Protection: IK08 according to IEC 62262
- Available enclosures:
  - 5 heights: 6, 9, 12, 15, 18U
  - 3 depths: 400, 500 and 600 mm
- Swing rack: acceptable load of 25 kg (Include 25% of margin load rating according to IEC 62208)
- Certifications: in compliance with directive RoHs, with 19" standard IEC 60297-3-100 and EIA-310-E.



Installed enclosures










Number of U	Dimensions (mm)			Enclosure references Swing rack	Blanking plate	Cable-gland plate with brush gasket	Blanking plate with 2 fans, cannot be used directly with UK PDU
	Height	Width	Depth				
6	380	600	400	-	**NSYOPB6UTPN**		
6	380	600	500	-	**NSYOPB6UTPN**		
9	515	600	400	-	**NSYOPB9UTPN**		
9	515	600	500	**NSYOPB9U5P**	**NSYOPB9UTPN**		
12	650	600	500	**NSYOPB12U5P**	**NSYOPB12UTPN**	**NSYECP300**	**NSYECVT300**
12	650	600	600	**NSYOPB12U6P**	**NSYOPB12UTPN**		
15	780	600	500	-	**NSYOPB15UTPN**		
15	780	600	600	-	**NSYOPB15UTPN**		
18	915	600	500	**NSYOPB18U5P**	**NSYOPB18UTPN**		

Total accessibility with the swing rack and the swingable and removable side panels and door.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Ergonomic and Adaptable
Introduction and Selection Guides

- Wall-mounted enclosure made from folded and welded sheet steel, powder paint, leather-grain finish, RAL 7035 light gray epoxy-polyester
- Enclosure made up of a body, 2 hinged and removable side panels, 19" fixed uprights and a Securit® glass transparent door or plain sheet steel door with key no. 333
- Protection rating: IP20 according to IEC 60529
- Impact Protection: IK08 according to IEC 62262 (for glazed door)
- Impact Protection: IK10 according to IEC 62262 (for plain door)
- Available enclosures:
  - 6 heights: 6, 9, 12, 15, 18, 21U
  - 3 depths: 400, 500 and 600 mm
- Fixed 19" rack. Acceptable load: 3 kg/U; max. 50 kg per enclosure (Include 25% of margin load rating according to IEC 62208)
- Certifications: in compliance with directive RoHs, with 19" standard IEC 60297-3-100 and EIA-310-E.



Installed enclosures









Number of U	Dimensions (mm)			Enclosure references Fixed rack	Blanking plate	Cable-gland plate with brush gasket	Blanking plate with 2 fans, cannot be used directly with UK PDU
	Height	Width	Depth				
6	380	600	400	**NSYOPB6U4F**	**NSYOPB6UTPN**	**NSYECP300**	**NSYECVT300**
6	380	600	500	**NSYOPB6U5F**	**NSYOPB6UTPN**		
9	515	600	400	**NSYOPB9U4F**	**NSYOPB9UTPN**		
9	515	600	500	**NSYOPB9U5F**	**NSYOPB9UTPN**		
9	515	600	600	**NSYOPB9U6F**	**NSYOPB9UTPN**		
12	650	600	400	**NSYOPB12U4F**	**NSYOPB12UTPN**		
12	650	600	500	**NSYOPB12U5F**	**NSYOPB12UTPN**		
12	650	600	600	**NSYOPB12U6F**	**NSYOPB12UTPN**		
15	780	600	400	**NSYOPB15U4F**	**NSYOPB15UTPN**		
15	780	600	500	**NSYOPB15U5F**	**NSYOPB15UTPN**		
15	780	600	600	**NSYOPB15U6F**	**NSYOPB15UTPN**		
18	915	600	400	**NSYOPB18U4F**	**NSYOPB18UTPN**		
18	915	600	500	**NSYOPB18U5F**	**NSYOPB18UTPN**		
21	1050	600	500	**NSYOPB21U5F**	**NSYOPB21UTPN**		
21	1050	600	600	**NSYOPB21U6F**	**NSYOPB21UTPN**		

Enclosure with plain door







Number of U	Dimensions (mm)			Enclosure reference	Blanking plate	Blanking plate with 2 fans, cannot be used directly with UK PDU
	Height	Width	Depth			
9	515	600	400	**NSYOPB9U4FR**	**NSYOPB9UTPN**	**NSYECVT300**
12	650	600	400	**NSYOPB12U4FR**	**NSYOPB12UTPN**	
15	780	600	500	**NSYOPB15U5FR**	**NSYOPB15UTPN**	
18	915	600	500	**NSYOPB18U5FR**	**NSYOPB18UTPN**	

2U extra space "for free", 1U in the top and 1U in the bottom. Can be used for example for power rails.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Actassi OPB: Open Box

Characteristics

19" Wall-Mounted Open Box with Swing Rack

- Wall-mounted enclosure made from folded and welded sheet steel, powder paint, leather-grain finish, RAL 7035 light gray epoxy-polyester
- Enclosure made up of a body, 2 hinged and removable side panels, a 19" swing rack and a Securit® glass transparent door with key no. 333
- Protection rating: IP20 according IEC 60529
- Impact Protection: IK08 according to IEC 62262

Available enclosures:
- 5 heights: 6, 9, 12, 15, 18U
- 3 depths: 400, 500 and 600 mm

- Swing rack: acceptable load of 25 kg (Include 25% of margin load rating according to IEC 62208)
- Certifications: in compliance with directive RoHs, with 19" standard IEC 60297-3-100 and EIA-310-E.

Cable-gland plate with brush gasket, ref. **NSYECP300**, see page 317
Blanking plate with 2 fans, cannot be used directly with UK PDU, ref. **NSYECVT300**, see page 317


NSYOPB9U5P

Characteristics	Number of U	Height (mm)	Width (mm)	Depth (mm)	References
19" Wall-Mounted Open Box with swing rack, glazed door	9	515	600	500	**NSYOPB9U5P**
19" Wall-Mounted Open Box with swing rack, glazed door	12	650	600	500	**NSYOPB12U5P**
19" Wall-Mounted Open Box with swing rack, glazed door	12	650	600	600	**NSYOPB12U6P**
19" Wall-Mounted Open Box with swing rack, glazed door	18	915	600	500	**NSYOPB18U5P**

19" Wall-Mounted Open Box with Fixed Rack

- Wall-mounted enclosure made from folded and welded sheet steel, powder paint, leather-grain finish, RAL 7035 light gray epoxy-polyester
- Enclosure made up of a body, 2 hinged and removable side panels, 19" fixed uprights and a Securit® glass transparent door or plain sheet steel door with key no. 333
- Protection rating: IP20 according IEC 60529
- Impact Protection: IK08 according to IEC 62262 (for glazed door)
- Impact Protection: IK10 according to IEC 62262 (for plain door)

Available enclosures:
- 6 heights: 6, 9, 12, 15, 18, 21U
- 3 depths: 400, 500 and 600 mm

- Fixed 19" rack. Acceptable load: 3 kg/U; max. 50 kg per enclosure (Include 25% of margin load rating according to IEC 62208)
- Certifications: in compliance with directive RoHs, with the 19" standard IEC 60297-3-100 and EIA-310-E.

Cable-gland plate with brush gasket, ref. **NSYECP300**, see page 317
Blanking plate with 2 fans, cannot be used directly with UK PDU, ref. **NSYECVT300**, see page 317


NSYOPB6U4F

Characteristics	Number of U	Height (mm)	Width (mm)	Depth (mm)	References
19" Wall-Mounted Open Box with fixed rack, glazed door	6	380	600	400	**NSYOPB6U4F**
19" Wall-Mounted Open Box with fixed rack, glazed door	6	380	600	500	**NSYOPB6U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	9	515	600	400	**NSYOPB9U4F**
19" Wall-Mounted Open Box with fixed rack, glazed door	9	515	600	500	**NSYOPB9U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	9	515	600	600	**NSYOPB9U6F**
19" Wall-Mounted Open Box with fixed rack, glazed door	12	650	600	400	**NSYOPB12U4F**
19" Wall-Mounted Open Box with fixed rack, glazed door	12	650	600	500	**NSYOPB12U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	12	650	600	600	**NSYOPB12U6F**
19" Wall-Mounted Open Box with fixed rack, glazed door	15	780	600	400	**NSYOPB15U4F**
19" Wall-Mounted Open Box with fixed rack, glazed door	15	780	600	500	**NSYOPB15U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	15	780	600	600	**NSYOPB15U6F**
19" Wall-Mounted Open Box with fixed rack, glazed door	18	915	600	400	**NSYOPB18U4F**
19" Wall-Mounted Open Box with fixed rack, glazed door	18	915	600	500	**NSYOPB18U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	21	1050	600	500	**NSYOPB21U5F**
19" Wall-Mounted Open Box with fixed rack, glazed door	21	1050	600	600	**NSYOPB21U6F**

Enclosure with Plain Door

Blanking plate with 2 fans, cannot be used directly with UK PDU, ref. **NSYECVT300**, see page 317


NSYOPB9U4FR

Characteristics	Number of U	Height (mm)	Width (mm)	Depth (mm)	References
19" Wall-Mounted Open Box with fixed rack, plain door	9	515	600	400	**NSYOPB9U4FR**
19" Wall-Mounted Open Box with fixed rack, plain door	12	650	600	400	**NSYOPB12U4FR**
19" Wall-Mounted Open Box with fixed rack, plain door	15	780	600	500	**NSYOPB15U5FR**
19" Wall-Mounted Open Box with fixed rack, plain door	18	915	600	500	**NSYOPB18U5FR**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Rear Blanking Plate

- Blanking plate made from sheet steel, powder paint, leather-grain finish, RAL 7035 light gray epoxy-polyester

Supply:
Delivered with the fixings required for installation


NSYOPB6UTPN

Characteristics	Number of U	References
Rear blanking plate	6	**NSYOPB6UTPN**
Rear blanking plate	9	**NSYOPB9UTPN**
Rear blanking plate	12	**NSYOPB12UTPN**
Rear blanking plate	15	**NSYOPB15UTPN**
Rear blanking plate	18	**NSYOPB18UTPN**
Rear blanking plate	21	**NSYOPB21UTPN**

Blanking Plate with Brush Gasket

- Fixing to the top or bottom openings of the enclosures
- Material: zinc-coated steel sheet

Supply:
Delivered with the fixings required for installation.


NSYECP300

Characteristics	Dimensions (mm)	References
Blanking plate with brush gasket	35 x 300	**NSYECP300**

Total Brush Gasket

- It is fixed to the top and bottom cable entries.


NSYECPT300

Characteristics	Dimensions (mm)	References
Total brush gasket	100 x 300	**NSYECPT300**

Top or Bottom Blanking Plate with 2 Fans

- 2 fans installed and wired to on the terminal block, including a protection grille.
- A power supply cable of 2 m in length is supplied connected
- Free flow of 35 m³/h each
- Fixing to the top or bottom openings of the enclosures
- Material: zinc-coated sheet steel
- Delivered with the fixings required for installation
- Sound level: 35 dB (A)
- Cannot be used directly with UK PDU.

Supply:
Delivered with the fixings required for installation.


NSYECVT300

Characteristics	References
Top or bottom blanking plate with 2 fans	**NSYECVT300**

Brush Gasket for the Cable Entries through the Plinth

- It is fixed to the knock-out areas for the cable entries
- Delivery as a unit.


NSYJPSVD

Characteristics	Entry width (mm)	References
Brush gasket for the cable entries through the plinth	75 x 400	**NSYJPSVD**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Actassi KDB: Knock Down Box

Characteristics

19" Wall Knock-Down Box Simple and Space-Saving

P133084_layout_698_nb



60%

The Flat-Pack Helps Saving up to 60% of Space in the Stock.

Introduction and Selection Guidess

- Flat-pack wall-mounted enclosure dismounted in 1 package
- Symmetric enclosure made from welded sheet steel, powder-painted, leather-grain finish, RAL 7035 light gray epoxy-polyester
- Enclosure made up of a body, one pair of 19" fixed uprights and a Securit® glass transparent door with key no. 333
- Top and bottom 19” knock-down plates for entry cables and fans – 0U
- Protection rating: IP20 according to IEC 60529
- Impact Protection: IK08 according to IEC 62262
- Acceptable load: 3 kg/U; max. 40 kg per enclosure
- (Include 25% of margin load rating according to IEC 62208)
- Certifications: in compliance with directive RoHs, with 19" standard IEC 60297-3-100 and EIA-310-E
- Brush entry cables NSYCRTM1U1PS (in option)

Flat-pack enclosures

P133087_layout_686_nb



P131660_layout_712_nb



Number of U	Dimensions (mm)			Enclosure reference	Brush entry cables
	Height	Width	Depth		
6	352	600	400	**NSYKDB6U4F**	**NSYCRTM1U1PS**
9	485	600	400	**NSYKDB9U4F**	
12	618	600	400	**NSYKDB12U6F**	
15	752	600	400	**NSYKDB15U6F**	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Severe Outdoor

Panel**SeT** PHD: Polyester

NSYPHDZT774



Panel**SeT** S3HD - SFN HD: Outdoor Coated Steel

NSYSFNHD20860



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** PHD: Polyester

Introduction	**322**
Characteristics	**325**
Accessories	**328**
Certifications	**332**

Panel**SeT** S3HD - SFN HD: Outdoor Coated Steel

Introduction	**322**
Characteristics	**326**
Accessories	**330**
Certifications	**332**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PHD - S3HD - SFN HD

Introduction



PanelSeT PHD enclosures are suitable for outdoor public areas thanks to their multiple features:
- mechanical strength (IEC 61439-5.2023),
- anti-posting surface thanks to the special ribbed door surface,
- insulated (ready for Class II according to IEC 61439-1: 2011).

Our enclosures are reinforced and designed to withstand harsh outdoor conditions. PanelSeT SFN HD and S3HD made of coated steel are suited for installation in private areas due to their exceptional resistance to corrosion (up to C4H level according to ISO 12944:2018) and UV protection.

PanelSeT PHD, a Class II polyester cabinet, is designed for installation in public spaces, offering high resistance to pressure and impact, along with an anti-posting coating.


NOTICE

POSSIBLE AESTHETICS CHANGES OF ENCLOSURE SURFACE

For long exposure applications, use painted enclosures available through the customized offer, to protect from UV radiation, wind and rain.

Failure to follow these instructions can result in equipment damage.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Fully Equipped

Standard, pre-installed equipment includes:
- A canopy to avoid water stagnation
- An aluminum cable gland plate to easily drill holes and avoid corrosion
- A document pocket to hold your documents in a practical place



Anti-Vandalism Feature

- PHD and SFN HD: handle with keylock and additional padlock hole (padlock not included) as a standard accessory to help protect the equipment




High Resistance

- PHD: Heavy-duty polyester reinforced with a double layer of fiberglass



Upper Airing

- The newly engineered roof airing accessory
- Helps prevent condensation (one of the causes of corrosion)




Heavy-Duty Accessories

- Dedicated accessories to resist harsh outdoor environments



Simplified Installation

- Easy lifting even when loaded with up to 1000 kg of equipment
- HD lifting accessories also available





Thermal Management Solutions

- 3 airing architectures help protecting the equipment installed inside from overheating and humidity

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PHD - S3HD - SFN HD

Characteristics

Characteristics	Wall-mounted enclosure	Floor-standing enclosure	Wall-mounted enclosure	Floor-standing enclosure
According to Reach and RoHs and Halogen-free				
	Polyester outdoor Heavy-Duty enclosures		Steel outdoor Heavy-Duty enclosures	
	Outdoor Heavy-Duty (HD) enclosures made of polyester insulated material. Offer multiple features suitable for outdoor public spaces: • High pressure and shock resistance • Posting-deterrent for floor standing • Enhanced insulation.		Outdoor Heavy-Duty (HD) enclosures made of coated steel. Offer multiple features suitable for private areas with harsh environments: • High resistance to corrosion (up to C4H level according ISO 12944:2018) • High resistance to UV.	
Material	HD Polyester reinforced with fiberglass to meet standard EN 439-5		HD steel with anti-corrosive painting	
Finish	-		Structured finish, 100% polyester powder	
Color	RAL 7035 gray		RAL 7035 gray	
Conditions of use	Outdoor and/or harsh environments		Outdoor and/or harsh environments	
Temperature range	-40...80 °C		-40...80 °C	
Ingress protection rating	IP65 according to IEC 60529	IP55 according to IEC 60529	IP66 according to IEC 60529	IP55 according to IEC 60529
Mechanical protection rating	IK10 according to IEC 62262		IK10 according to IEC 62262	
Standards	See table page 332		See table page 332	
Certifications	See table page 332		See table page 332	
Fixing	On wall by means of optional wall fixing accessory	Option for installation on floor	• On wall by means of optional stainless-steel wall fixing lugs • On post by means of optional HD post fixing device	• Directly on floor by means of plinth (see page 471)
Maximum load according to IEC 62208	500 kg (depends on the size of the enclosure)		200 kg (depends on the size of the enclosure)	1312 kg (1168 kg lifting) (depends on the size of the enclosure)
Other characteristics	• Fire resistance according to EN 1794-2 • Lifting possible from top with eyebolt accessory • New dedicated airing solutions to be integrated in roof, lateral or plinth. 3 airing architectures proposed (see page 406 and 407)		New dedicated airing solutions to be integrated in roof, side or plinth	
Options	Plain door	Plain or ribbed door	-	
Supply	• Curved canopy • Handle with keylock (1242E type) and padlock • Door retainer • Plastic document pocket (A4 size)	• Curved canopy • Integrated plinth • Handle with keylock (1242E type) and padlock • Aluminum cable gland plate • Door retainer • Plastic document pocket (A4 size)	• Curved canopy • 3-mm double-bar lock • Plastic document pocket (A4 size) • Door retainer • Aluminum cable gland plate	• Canopy • Rear panel • Handle with keylock (1242E type) and padlock • Aluminum cable gland plate

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Severe Outdoor
PanelSeT PHD: Polyester
Characteristics

Polyester Outdoor Heavy-Duty Enclosures

- Outdoor Heavy-Duty (HD) enclosures made of polyester insulated material. Offer multiple features suitable for public spaces: high resistance to pressure and shocks, posting deterrence, and high insulation.
- Material: HD Polyester reinforced with fiberglass to meet standard EN 439-5
- Color: RAL 7035 gray
- Conditions of use: Outdoor and/or harsh environments
- Temperature range: -40...80 °C
- Mechanical protection rating: IK10 according to IEC 62262
- Standards: See table page 332
- Certifications: See table page 332
- Maximum load according to IEC 62208: 500 kg
- Other characteristics: Fire resistance according to EN 1794-2, Lifting possible from top with eyebolt accessory, new dedicated airing solutions to be integrated in roof, lateral or plinth.
  3 airing architectures proposed (see page 406 and 407)
- Options: Plain door or ribbed door for polyester floor standing enclosure

Wall-Mounted Enclosure


NSYPHDT753P

- Ingress protection rating: IP65 according to IEC 60529
- Fixing: On wall by means of optional wall fixing accessory

Supply:
Curved canopy
Handle with keylock (1242E type) and padlock
Door retainer
Plastic document pocket (A4 size)

Characteristics	Door type	Number of doors	Dimensions (H x W x D)	References
Wall-mounted enclosure	Plain	1	538 x 500 x 320	**NSYPHDT553P**
Wall-mounted enclosure	Plain	1	788 x 500 x 320	**NSYPHDT753P**

Floor-Standing Enclosure

- Ingress protection rating: IP55 according to IEC 60529
- Fixing: 2 options for installation on floor:
- With floor fixing kit **NSYMF2PLAZ4** or **NSYMF2PLAZ6** for integrated plinth (50 mm)
- With additional ZZ plinths available as accessory (200 mm) (see page 473)

Supply:
Curved canopy
Integrated plinth
Handle with keylock (1242E type) and padlock
Aluminum cable gland plate
Door retainer
Plastic document pocket (A4 size)


NSYPHDZT774


NSYPHDZT774P

Characteristics	Door type	Number of doors	Dimensions (H x W x D)	References
Floor-standing enclosure	Anti-posting	1	843 x 750 x 420	**NSYPHDZT774**
Floor-standing enclosure	Anti-posting	1	843 x 750 x 620	**NSYPHDZT776**
Floor-standing enclosure	Anti-posting	1	1093 x 500 x 420	**NSYPHDZT1054**
Floor-standing enclosure	Anti-posting	1	1093 x 750 x 420	**NSYPHDZT1074**
Floor-standing enclosure	Anti-posting	1	1343 x 500 x 420	**NSYPHDZT1254**
Floor-standing enclosure	Anti-posting	1	1343 x 750 x 420	**NSYPHDZT1274**
Floor-standing enclosure	Anti-posting	1	1343 x 750 x 620	**NSYPHDZT1276**
Floor-standing enclosure	Anti-posting	2	1343 x 1250 x 420	**NSYPHDZT12124**
Floor-standing enclosure	Anti-posting	2	1343 x 1250 x 620	**NSYPHDZT12126**
Floor-standing enclosure	Anti-posting	1	1593 x 750 x 420	**NSYPHDZT1574**
Floor-standing enclosure	Anti-posting	1	1593 x 750 x 620	**NSYPHDZT1576**
Floor-standing enclosure	Anti-posting	2	1593 x 1250 x 420	**NSYPHDZT15124**
Floor-standing enclosure	Anti-posting	2	1593 x 1250 x 620	**NSYPHDZT15126**
Floor-standing enclosure	Anti-posting	2 Vertical	2093 x 750 x 420	**NSYPHDZT2074**
Floor-standing enclosure	Plain	1	843 x 750 x 420	**NSYPHDZT774P**
Floor-standing enclosure	Plain	1	843 x 750 x 620	**NSYPHDZT776P**
Floor-standing enclosure	Plain	1	1093 x 500 x 420	**NSYPHDZT1054P**
Floor-standing enclosure	Plain	1	1093 x 750 x 420	**NSYPHDZT1074P**
Floor-standing enclosure	Plain	1	1343 x 500 x 420	**NSYPHDZT1254P**
Floor-standing enclosure	Plain	1	1343 x 750 x 420	**NSYPHDZT1274P**
Floor-standing enclosure	Plain	1	1343 x 750 x 620	**NSYPHDZT1276P**
Floor-standing enclosure	Plain	2	1343 x 1250 x 420	**NSYPHDZT12124P**
Floor-standing enclosure	Plain	2	1343 x 1250 x 620	**NSYPHDZT12126P**
Floor-standing enclosure	Plain	1	1593 x 750 x 420	**NSYPHDZT1574P**
Floor-standing enclosure	Plain	1	1593 x 750 x 620	**NSYPHDZT1576P**
Floor-standing enclosure	Plain	2	1593 x 1250 x 420	**NSYPHDZT15124P**
Floor-standing enclosure	Plain	2	1593 x 1250 x 620	**NSYPHDZT15126P**
Floor-standing enclosure	Plain	2 Vertical	2093 x 750 x 420	**NSYPHDZT2074P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3HD - SFN HD: Outdoor Coated Steel

Characteristics

Steel Outdoor HD Enclosures

- Outdoor Heavy-Duty (HD) enclosures made of coated steel.
- Offer multiple features suitable for private areas with harsh environments: high resistance to corrosion (up to C4H level according ISO 12944) and to UV
- Material: HD steel with anti-corrosive painting
- Finish: Structured finish, 100% polyester powder
- Color: RAL 7035 gray
- Conditions of use: Outdoor and/or harsh environments
- Temperature range: -40...80 °C
- Mechanical protection rating: IK10 according to IEC 62262
- Standards: IEC 61439-5, IEC 62208, IEC 60297-3-100, ISO 12.944 (C4H)
- Certifications: See table page 332
- Other characteristics: New dedicated airing solutions to be integrated in roof, side or plinth

Supply:
Canopy
Aluminum cable gland plate

Wall-Mounted Enclosure

- Ingress protection rating: IP66 according to IEC 60529
- Fixing: On wall by means of optional stainless-steel wall fixing lugs, on post by means of optional HD post fixing device
- Maximum load according to IEC 62208: 200 kg
- cUL according to 508A CSA C.22.2 N° 14 .
- Environmental rating according UL50E 4, 4x and 13

Supply:
3-mm double-bar lock


NSYS3HD3215

Characteristics	Dimensions (H x W x D)	References
Wall-mounted enclosure	343 x 200 x 180	**NSYS3HD3215**
Wall-mounted enclosure	448 x 300 x 230	**NSYS3HD4320**
Wall-mounted enclosure	548 x 400 x 230	**NSYS3HD5420**
Wall-mounted enclosure	653 x 400 x 280	**NSYS3HD6425**
Wall-mounted enclosure	658 x 600 x 330	**NSYS3HD6630**
Wall-mounted enclosure	753 x 500 x 280	**NSYS3HD7525**
Wall-mounted enclosure	858 x 600 x 330	**NSYS3HD8630**
Wall-mounted enclosure	862 x 800 x 430	**NSYS3HD8840**
Wall-mounted enclosure	1062 x 600 x 430	**NSYS3HD10640**
Wall-mounted enclosure	1062 x 800 x 430	**NSYS3HD10840**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3HD - SFN HD: Outdoor Coated Steel

Characteristics

Floor-Standing Enclosure

- Ingress protection rating: IP55 according to IEC 60529
- Fixing: Directly on floor by means of optional plinth
- Maximum load according to IEC 62208: 1312 kg (1168 kg lifting) (depends on the size of the enclosure)
- Coupling SFN HD is possible using standard coupling kit
- If ordered assembled from our service there are length limitations (consult us)
- cUL according to UL508a
- Environmental ratings according to UL50E,12 and 3R

Supply:
Rear panel
Handle with keylock (1242E type)



NSYSFNHD20860

Characteristics	Dimensions (H x W x D)	References
Floor-standing enclosure SFN	1800 x 600 x 400	**NSYSFNHD18640**
Floor-standing enclosure SFN	1800 x 800 x 400	**NSYSFNHD18840**
Floor-standing enclosure SFN	1800 x 800 x 600	**NSYSFNHD18860**
Floor-standing enclosure SFN	1800 x 800 x 800	**NSYSFNHD18880**
Floor-standing enclosure SFN	2000 x 600 x 600	**NSYSFNHD20660**
Floor-standing enclosure SFN	2000 x 800 x 400	**NSYSFNHD20840**
Floor-standing enclosure SFN	2000 x 800 x 600	**NSYSFNHD20860**

Side Panel Internal Fixing



NSY2SPINHD184

Characteristics	Dimensions (mm)	References
SFN HD 2 side panels int. fix.	1800 x 400	**NSY2SPINHD184**
SFN HD 2 side panels int. fix.	1800 x 600	**NSY2SPINHD186**
SFN HD 2 side panels int. fix.	1800 x 800	**NSY2SPINHD188**
SFN HD 2 side panels int. fix.	2000 x 400	**NSY2SPINHD204**
SFN HD 2 side panels int. fix.	2000 x 600	**NSY2SPINHD206**

Upper Ventilated Module



NSYSFNCVR64HD

Characteristics	Dimensions (mm)	References
SFN HD upper ventilated module	600 x 400	**NSYSFNCVR64HD**
SFN HD upper ventilated module	600 x 600	**NSYSFNCVR66HD**
SFN HD upper ventilated module	800 x 400	**NSYSFNCVR84HD**
SFN HD upper ventilated module	800 x 600	**NSYSFNCVR86HD**
SFN HD upper ventilated module	800 x 800	**NSYSFNCVR88HD**

Coupling




- Coupling SFN HD is possible using standard coupling kit. Each enclosure with its own canopy.
- If ordered assembled from our factory, there are length limitations due to transport (consult us).

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PHD: Polyester

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Fixing Accessories

Fixing and Lifting Accessories

1 
Eyebolts
See details p. 482

2 
Wall fixing accessory
See details p. 478

Cable Management Accessories

Cable Entry Accessories

3 
Cables entries
See details p. 494

Mounting Accessories

Equipment Assembly Accessories

4 
Plain mounting plates
See details p. 515

Airing System

5 
Roof airing module
See details p. 460

6 
Fanbox
See details p. 408

7 
Filter
See details p. 408

8 
Roof filter for fanbox
See details p. 408

9 
IP55 HD metal grid
See details p. 408


10 
Anti-vandalism kit for HD metal grid
See details p. 408

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN HD: Outdoor Coated Steel

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Installation Accessories

Composition Accessories

1 

Side panels

See details p. 327

2 

Ventilated plinths

See details p. 471

3 

Eyebolts

See details p. 482

4 

Wall fixing accessory

See details p. 477

Mounting Accessories

Equipment Assembly Accessories

5 

Plain mounting plates

See details p. 514

Door Accessories

6 

Heavy-duty padlockable double lock

See details p. 558

Airing System

7 

Roof airing module

See details p. 327

8 

Fanbox

See details p. 408

9 

Filter

See details p. 408

10 

Roof filter for fanbox

See details p. 408

11 

IP55 HD metal grid

See details p. 408

12 

Anti-vandalism kit for HD metal grid

See details p. 408

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT PHD - S3HD - SFN HD

Certifications

Test description	Standard	Standard title	Certification	Declaration
POLYESTER PanelSeT PHD				
IP55, IK10, lifting: 500 kg max. (IP65 for wall-mounted)	IEC 62208: 2011	Empty enclosures for low-voltage switchgear and controlgear assemblies - General requirements	●	-
Class II Insulation	IEC 61439-1: 2011	Low-voltage switchgear and controlgear assemblies Part 1: General rules	-	✓
Mechanical strength	IEC 61439-5:2023	Low-voltage switchgear and controlgear assemblies Part 5: Assemblies for power distribution in public networks	●	-
Corrosion resistance C4H. It affects the painted accessories (ventilated roof, anti-burglary kit). All other metal parts have special treatment to pass the same test.	ISO 12944-6:2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: laboratory performance testing methods	-	✓
Space for electronics	IEC 60297-3-100: 2009	Mechanical structures for electronic equipment Dimensions of mechanical structures of the 482.6 mm (19 in) series - Part 3-100: Basic dimensions of front panels, subracks, chassis, racks and cabinets	-	✓
Dimensional	EIA-310-E	Cabinets, Racks, Panels, and associated equipment	-	✓
Fire resistance	EN 1794-2:2011	Vandalism: Fire resistance	-	✓
Posting	Internal test	Door anti-posting internal test	-	✓
Single-door: types 1, 2, 3, 3R, 4, 4X, 5, 12 and 13 Double-door: types 1, 2, 3, 3R, 5, 12 and 13	UL 508 A CSA c.22.2 No 14	Standard for Industrial Control Panels. Standard for Industrial Control Equipment.	●	-
PanelSeT SFN HD (floor-standing enclosures)				
IP55, IK10, lifting: 1312 kg (1168 kg lifting for the larger size)	IEC 62208: 2011	Empty enclosures for low-voltage switchgear and controlgear assemblies - General requirements	●	-
Mechanical strength	IEC 61439-5:2023	Low-voltage switchgear and controlgear assemblies Part 5: Assemblies for power distribution in public networks	●	-
Corrosion resistance C4H	ISO 12944-6:2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: laboratory performance testing methods	●	-
Space for electronics	IEC 60297-3-100: 2009	Mechanical structures for electronic equipment Dimensions of mechanical structures of the 482.6 mm (19 in) series - Part 3-100: Basic dimensions of front panels, subracks, chassis, racks and cabinets	-	✓
Dimensional	EIA-310-E	Cabinets, Racks, Panels, and associated equipment	-	✓
Single-door: Types 1, 3R, 12	UL 508 A CSA C.22 No 14-18 UL50E	Standard for Industrial Control Panels. Standard for Industrial Control Equipment.	●	-
PanelSeT S3HD (wall-mounted enclosures)				
IP66, IK10, lifting: 200 kg max.	IEC 62208: 2011	Empty enclosures for low-voltage switchgear and controlgear assemblies - General requirements	●	-
Mechanical strength	IEC 61439-5:2023	Low-voltage switchgear and controlgear assemblies Part 5: Assemblies for power distribution in public networks	●	-
Corrosion resistance C4H	ISO 12944-6:2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: Laboratory performance testing methods	●	-
Space for electronics	IEC 60297-3-100: 2009	Mechanical structures for electronic equipment Dimensions of mechanical structures of the 482.6 mm (19 in) series - Part 3-100: Basic dimensions of front panels, subracks, chassis, racks and cabinets	-	✓
Dimensional	EIA-310-E	Cabinets, Racks, Panels, and associated equipment	-	✓
Single-door: Types 1, 2, 3, 3R, 4, 4X. 5, 12 and 13	UL 508 A: 2007 CSA c.22.2 No 14	Standard for Industrial Control Panels. Standard for Industrial Control Equipment.	●	-

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Certifications

Test description	Standard	Standard title	Certification	Declaration
HD ACCESSORIES HD THERMAL Management, Fanbox				
NSYCVF Series are intended for mounting on the flat surface of a Type 12 or 12K enclosure	UL 508A CAN/CSA-C22.2 No. 14, CAN/CSA C22.2 No. 94-M91 CAN/CSA C22.2 No. 73	Industrial Control Panels Industrial Control Equipment Special Purpose Enclosures Electrically Equipped Machine Tools	●	-
IP55 HD Metal grille (NSYCAG223LFHD)				
IP55 (in conditions of use)	IEC 60529: 2013	Degrees of protection provided by enclosures (IP Code)	-	✓
Corrosion resistance C4H	ISO 12.944: 2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: Laboratory performance testing methods	●	-
Anti-vandalism kit for HD metal grille (NSYCAAPVHD)				
Resistance Class 2	ENV 1627:2011	Burglar resistance - Requirements and classification	●	-
Upper airing module (PHD / SFN HD / S3HD)				
IP55 (in conditions of use)	IEC 60529: 2013	Degrees of protection provided by enclosures (IP Code)		✓
Corrosion resistance at level C4H	ISO 12.944: 2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: Laboratory performance testing methods	●	-
HD POLYESTER ENCLOSURES				
Corrosion resistance at level C4H	ISO 12.944: 2018	Paints and varnishes-corrosion protection of steel structures by protective paint systems Part 6: Laboratory performance testing methods	●	-
ZZ plinths (NSYZZ•••)				
ZZ Plinth: IP44 (in conditions of use)	IEC 60.529:2013	Degrees of protection provided by enclosures (IP Code)	-	✓
Eyebolts (NSYPLHD)				
Maximum load 500 kg	IEC 62208: 2011	Empty enclosures for low-voltage switchgear and controlgear assemblies - General requirements	-	✓
HD STEEL ENCLOSURES **Stainless-steel plinths (NSYSPFVX••• / NSYSPLVX••• / NSYSPSX••• / NSYSPSX•••)**				
Ventilated plinth: IP20 (in conditions of use) Standard plinth: IP30 (in conditions of use)	IEC 60.529:2013	Degrees of protection provided by enclosures (IP Code)	-	✓

For Information on Airing Architecture, check ClimaSys chapter, see page 406.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Seismic and Nuclear Ready Environments

Panel**SeT** S3D 6G: Wall-Mounted Enclosures

PB502933_56_nb



PB502934_58_nb



Panel**SeT** SFN 6G: Floor-Standing Enclosures

NSYSFN6G20860



Panel**SeT** SFN 3G: Floor-Standing Enclosures

NSYSFN20860



Panel**SeT** SFN 6G Nuclear Ready: Floor-Standing Enclosures

NSYSFN20860NUC



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D 6G Seismic: Wall-Mounted Enclosures

Introduction	336
Characteristics	338
Accessories	339
Dimensions	340

Panel**SeT** SFN 6G Seismic: Floor-Standing Enclosures

General Information	342
Introduction	344
Characteristics	346
Accessories	348
Dimensions	352

Panel**SeT** SFN 3G Seismic: Floor-Standing Enclosures

General Information	342
Characteristics	354
Dimensions	355
PrismaSeT HD	358

Panel**SeT** SFN 6G Nuclear Ready: Floor-Standing Enclosure

Introduction	360
Characteristics	361
Application	360

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D 6G: Wall-Mounted Enclosures

Introduction



The Panel**SeT** S3D 6G wall-mounted enclosure, designed for seismic applications, this robust and reliable solution help ensuring the safety and protection of electrical components in demanding environments.
Its steel construction with a 2 mm thickness for both the body and the door, this enclosure features a solid door with reinforced full frame, helping to secure installation. The earth continuity between the body and the door, along with a 3-point locking system using key 405E, provides added security.
Coated with epoxy-polyester powder color gray (RAL 7035), help providing durability and aesthetic appeal.
Compliant with standards such as IEC 62208 and featuring IP65 protection and IK10 impact resistance, this enclosure is designed to perform reliably in challenging conditions.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D 6G: Wall-Mounted Enclosures

Introduction



Strength

Panel thickness:

- Casing + door: 20/10 mm
- Entry flange: 15/10 mm




Security Locking System

- 405E locking system with captive key
- Door not reversible, opening in opposite direction available on demand



Optional on Request

- Continuity of masses between interior and exterior by 2 studs welded opposite each other



Reinforced Mounting Plate

- Mounting plate reinforcement
- Increased number of attachment points



Wall-Mounted

- Reinforced bracket for wall-mounted



Decontaminable Smooth Paint PID 100 Series

- Complies with CCTR 91.C.031.08 Double layer of paint (minimum thickness: 60 µ)
- PIA/PIB/PID and PIC REP 100
- Powder system according to FNP 1125

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3D 6G: Wall-Mounted Enclosures

Characteristics

Panel**SeT** S3D 6G Solutions for Seismic Risks

Seismic constraint

The seismic behavior of the wall-mounted enclosure PanelSeT S3D has been qualified according to MRI spectra “big material” specified in the standard IEC 60068-2-6 and IEC 60068-2-57, resulting in a 3G level.
Tested enclosure configuration:

- Plain door,
- Plain mounting plate with a load of 150 kg/m² uniformly distributed on the mounting plate,
- The wall fixing must be appropriate for the type of material (in the test, the metal wall fixing of the test platform was done using four M8 class 8.8 screws with a tightening torque of 23 Nm).
- Seismic applications up to UBC zone 4.
- Material: Steel
- Color: RAL 7035
- Ingress protection rating: IP65 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262
- Maximum load: 80 kg/m² on plain mounting plate, uprights
- Standards:
  - Enclosure standard: IEC 62208
  - Seismic standards: IEC 60068-2-57, IEC 60068-3-3 and CRT 91 C 112 01 - EDF
  - Recommended for UBC zone 4 (this is a widely used Building code despite not being in force)
- Certifications: 6G certification as per CRT 91-C-112-00 (EDF)

Supply:

Body

- Monobloc casing (cross structure). Gutter-shaped front profile. Flat back
- M6 x 16 earthing screws and earth strap for equipotential connection between the enclosure door and casing
- Entry flange

Door

- Plain door with handle equipped with 405 key
  - H < 600: 1 fastening point
  - H ≥ 600: 3 fastening points
- Non-reversible door (for reversibility, please contact us)
- M6 x 16 earthing screws and earth strap for equipotential connection between the enclosure door and casing
- 120° door opening

Mounting plate

- Mounting plate galvanized before mounting
- Maximum load: 80 kg/m²
- Two wall-mounted brackets



NSYS3D6G32515P

Characteristics	Height (mm)	Width (mm)	Depth (mm)	References
PanelSeT S3D 6G seismic plain door with mount. plate	300	250	150	**NSYS3D6G32515P**
PanelSeT S3D 6G seismic plain door with mount. plate	400	300	200	**NSYS3D6G4320P**
PanelSeT S3D 6G seismic plain door with mount. plate	700	500	250	**NSYS3D6G7525P**
PanelSeT S3D 6G seismic plain door with mount. plate	800	600	300	**NSYS3D6G8630P**
PanelSeT S3D 6G seismic plain door with mount. plate	1200	800	400	**NSYS3D6G12840P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Table of Compatibility of Accessories in 6G Seismic S3D Enclosures

Accessories		Compatibility	Comments	Trade references impacted
 ISPA011_010_43_nb	Door switch	Limited	Conditions: Drilling by customization department to be provided for	NSYINLCRN
 PB500083_29_nb	Diagram holder	Yes	-	NSYDPA●●
 PB500338_24_nb	Lifting rings	Limited	Conditions: Drilling by customization department to be provided for	NSYAELYTCRG8

Comment: None of the accessories is certified 6G.

Locks for Enclosure

- < H 600
- With captive key.
- Material: Zamak lock and metal cam
- For door with hinges on the right side, not reversible, opening in opposite direction available on demand

Supply:
1- or 3-point lock with 1 lock button and 1 cremone screw


NSYAEDL1242K31

Characteristics	Key lock	References
Lock for enclosure	1242E	**NSYAEDL1242K31**
Lock for enclosure	405E	**NSYAEDL405K31**
Lock for enclosure	455E	**NSYAEDL455K31**

Locks for Enclosure

- > H 600
- With captive key.
- Material: Polyamide handle, metal connecting rods and cam
- For door with hinges on the right side, not reversible, opening in opposite direction available on demand

Supply:
3-point lock with 1 lock button and 1 cremone screw


NSYAEDL1242K33

Characteristics	Key lock	References
Lock for enclosure	1242E	**NSYAEDL1242K33**
Lock for enclosure	405E	**NSYAEDL405K33**
Lock for enclosure	455E	**NSYAEDL455K33**

Padlocking Lug

- Securing of enclosure access.
- Material: White galvanized steel


NSYAEDLPADS3DK3

Characteristics	References
Padlocking lug	**NSYAEDLPADS3DK3**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3D 6G: Wall-Mounted Enclosures

Dimensions


Special Dimensions

Height	Width					
	250	300	400	500	600	800
1200	-	-	-	-	200/250/300/400	200/250/300/400
1000	-	-	-	-	200/250/300/400	200/250/300/400
800	-	-	200/250/300	200/250/300	200/250/400	200/250/300
700	-	-	200/250/300	200/300	200/250/300/400	-
500	200	150/200/250	200/250/300	200/250/300	-	-
400	150/200	150/250	-	-	-	-
300	150/200	150/200/250	-	-	-	-


Cut-Outs

Customization Areas

Door




Entry Flange



Depth	A
150	65
200	82
250	98
300	115
400	148

Casing



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT S3D 6G: Wall-Mounted Enclosures

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 6G and 3G

General Information

Earthquakes are highly specialized phenomena that demand expert-level understanding. The following two pages will provide an overview of seismic topics



Seismic risk is worldwide. Maps that describe the maximum ground accelerations with a low probability to be exceeded in a specific time interval, are available to illustrate it. Ground accelerations are therefore basic data that can be used to compare risks by localizations.
Each project must check at the localization installation of their building if specific design requirements for seismic withstand must be implemented. All countries close to faults should be specially checked.

Earthquakes are events that can cause a lot of structural damage so building have to be designed to withstand those constraints.
Inside those building are our electrical equipment which are considered as nonstructural devices. According to the level of criticity of those equipment those nonstructural devices must be able to withstand mechanically and sometimes functionally the seismic waves transmitted by the ground to the building to its anchoring points.


In specific building such as data centers, power plants, nuclear plant… it is often mandatory that electrical enclosures will be able to function after earthquake without causing damage to people and without needing to be replaced.

The seismic level an electrical enclosure has to withstand is not directly the ground acceleration as the building will affect the seismic waves transmitted to the equipment. The point within the earth where an earthquake rupture starts is the focus or hypocenter. From this point the seismic waves is transmitted.

To define the seismic resistance of equipment, it is necessary to take into account the geological characteristics of the ground and the behavior of the building and compare these with the equipment's seismic performances.

Each country/region has their own standards that are different enough to the extent that it is not straightforward to compare them. Those standard mainly focus more on building than electrical installation. Moreover, the location and the building where the electrical enclosures are installed can also impact the seismic level the enclosures has to withstand.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Geology Equivalence between scales characterizing the earthquake		
MSK	**Richter**	**IEC 60068-3-3 (ground acc.)**
<VIII	< 5.5	2 m/s²
VIII to IX	≥ 5.5 and ≤ 7	3 m/s²
>IX	> 7	5 m/s²

Definitions

- **MSK scale:** is a measure of the size of the earthquake based on the effects it produces on people, objects, buildings, nature and terrain.
  For example, considering damage to buildings:
  - Grade VII: Some buildings with metal or concrete structures suffer light damage.
  - Grade X: Many buildings with metal or concrete structures suffer destruction and some collapse.
- **Richter scale:** It represents the seismic energy released in each earthquake and is based on the seismographic record. It is a scale that grows in a potential or semi-logarithmic manner, so that each point increase can mean an increase in energy ten or more times greater.
  - Between 3.5 and 5.4, it is an earthquake that is often felt, but only causes minor damage.
  - Between 7.0 and 7.9, it is a major earthquake that causes serious damage.

The same earthquake will have a different value according to the MSK scale depending on the place it affects due to the different seismic resistance of its constructions, but it will have the same value according to the Richter scale.

- **Ground acceleration:** Acceleration resulting from an earthquake.
  Note: In practice, ground acceleration can be broken down into horizontal and vertical components.
- **Floor acceleration:** Acceleration measured on a particular floor in a building (at the location of an equipment item).
  Note: In practice, floor acceleration can be broken down into horizontal and vertical components.
- **Equipment acceleration:** Acceleration resulting at the anchoring points of an equipment.
- **Building codes level:** set of regulations and requirement that lead structural design and calculation methods for building.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN 6G: Floor-Standing Enclosures

Introduction



SFN tested for Nuclear application:
- Enclosure designed for installation in areas subject to critical seismic conditions
- Recommended for UBC zone 4 (this is a widely used building code despite not being in force)
- PanelSeT SFN 6G has been tested with a plain mounting plate, and PanelSeT SFN 6G IT with 19-inch fixed uprights

PanelSeT SFN 6G and PanelSeT SFN 6G IT have been tested to the standards:
- IEC 60068-2-57
- IEC 60068-3-3
- CRT 91 C 112 01 - EDF

Seismic Test Levels:
- 6G CRT EDF (tested Zero Period Acceleration at twice the value required CRT 91 C 112 01 - EDF _ Nuclear application
- Air Crash Test (5g Zero Period Acceleration), according to CRT 91 C 112 01 - EDF method, 4 seconds and triaxial test

Description:
- Integrated 100 mm plinth
- Material: Steel
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262
- UL50E types 1, 12
- Maximum load: 130 kg in Panel**SeT** SFN 6G (depends on the size), 140 kg in Panel**SeT** SFN 6G IT (depends on the size)

Note: nuclear application sequence is 5 times 50% final seismic levels and once full seismic level.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT SFN 6G: Floor-Standing Enclosures

Introduction




Panels with reinforced fixations

- 12 fastening points by M6 screws per panel



Reinforced Plinths

- 100 mm height
- Floor fixing: minimum 6 fastening points by M12 screws
- Fixing from inside and outside the enclosure



Coupling kit tested

- Coupling kit to allow coupling of SFN, choices of sizes in table 1




Security locking system

- Seismic locking system
- Special connecting rods and handle to help prevent any accidental door opening under severe vibration conditions



Reinforcement corners

- To strengthen the enclosure and respond to seismic risks
- To strengthen fastening of the side panels and rear panel
- To fasten the door connecting rods



19 inches kit

- Set to install 19 inches uprights
- Available for width 600 and 800
- Available Height see table 3

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN 6G: Floor-Standing Enclosures

Characteristics



NSYSFN6G20860

Supply:
Catalog sizes available : Ht 2000 W 800 D600
(other sizes available on demand see sizes table 1)
- Color: RAL 7035
- Plinth Color: RAL 7022

Composed of:
- Framework
  - 4 uprights
  - 1 lower frame
  - 1 upperframe with roof
- 1 rear panel
- 8 multi-purpose reinforcement corners
- 8 cross-rails fastened to the framework contributing to the seismic resistance (3 left, 3 right, 2 rear)
- Monobloc Plinth 4 mm thick 100 mm high
- Door
  - Plain door with handle with 405 key lock (other lock available)
  - 3 fastening points with connecting rods
  - Door hinges on right, door not reversible (opposite direction available on request)
- 3 parts gland plate

Kit
- Mounting plate reinforcement kit or 19 inches reinforcement kit (Mounting plate nor 19 inches uprigths not included)

Coupling
- Option to couple SFN 6G enclosures with the coupling kits reference: **NSYSFBKR** and **NSYSFBK19**

Aesthetic
- Trim cap for 6G panel fixing screws (accessory and not part of the enclosure)

Panel**SeT** SFN 6G for device installation on mounting plate (recommended sizes for nuclear application)

Description	Dimensions (mm)	References	Mounting plate	Reinforcement kit for mounting plate	Heavy cross rail
SFN 6G	2000 x 800 x 600	**NSYSFN6G20860**	**NSYMP208**	**NSYSFPB6G**	**NSYHLCR60**
SFN 6G	2000 x 600 x 800	Available on demand			
SFN 6G	2000 x 800 x 800	Available on demand			

Panel**SeT** SFN 6G IT and server application (19 in)

Description	Dimensions (mm)	References	Vertical upright	Reinforcement kit for 19 inches
SFN 6G IT width 800	2000 x 800 x 600	**NSYSFN6G20860**	**NSYRCK42** (x2)	**NSYRCK19KITN6G**
SFN 6G IT width 800	2000 x 800 x 800	Available on demand	**NSYRCK42** (x2)	**NSYRCK19KIT6G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN 6G: Floor-Standing Enclosures

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 6G: Floor-Standing Enclosures

Accessories



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Installation Accessories

Composition Accessories

1



Side panels

See details p. 350


2



Trim cap for panels

See details p. 350

3



Reinforced fixing kit for mounting plate

See details p. 350

Mounting Accessoires

Equipment Assembly Accessories


4



Mounting plates

See details p. 350


5



Rails for heavy load

See details p. 350

6



19” fixes uprights

See details p. 351

Equipment Assembly Accessories

7



Optional locks

See details p. 351

> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** SFN 6G: Floor-Standing Enclosures

Accessories

Panel**SeT** SFN 6G for Seismic Risks

Side Panels


NSY6G2SP206

- Material: Steel
- Installation: 12 fastening points

Supply:
2 side panels and fasteners

Characteristics	Height (mm)	Depth (mm)	References
Side panel	2000	600	**NSY6G2SPN206**

Mounting Plate



NSYMP206

- Material: Galvanized steel
- Installation: Mounting plate to be installed with **NSYSFPB6G** fastening kit + **NSYHLCR●●** cross-rails

Supply:
1 mounting plate and sliding shoes

Characteristics	Height of the enclosure (mm)	Width of the enclosure (mm)	Height (mm)	Depth (mm)	References
Mounting plate	2000	800	1897	696	**NSYMP208**

Rails for Heavy Load



NSYHLCR40

- Material: Zinc-coated steel

Supply:
2 cross-rails and fixing elements

Characteristics	Depth (mm)	References
Rails for heavy load	600	**NSYHLCR60**

Reinforced Fixing Kit for Mounting Plate


NSYSFPB6G

- Material: Steel

Supply:
6 anti-vibration supports
4 mounting brackets
4 supports
2 connectors and fixing elements

Characteristics	References
Reinforced fixing kit for mounting plate	**NSYSFPB6G**

Trim Cap for SF 6G Panels


NSYCSP6G

- Material: Plastic


Supply:
50 units

Characteristics	References
Trim cap for SF 6G panels	**NSYCSP6G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 19 inches width 800

19" Fixed Uprights



NSYRCK42


- Uprigth designed to be assembled on enclosures 800 width (width 600 on demand).
- Material: Zinc-coated steel
- Fixing: To fasten the 19" uprights
- It is necessary to use the fixing kit **NSYRCK19KITN6G**

Note:
For a 19" seismic configuration,
4 uprights must be used

Supply:
2 uprights and fasteners,

Characteristics	References
19" fixed uprights	**NSYRCK42**

Uprights Fixing Kit



NSYRCK19KIT6G

- Material: Steel

Supply:
4 cross-rails
8 fastening brackets
12 reinforcements
Fixing elements

Characteristics	References
6G upright´s fixing kit for width 800 and depth 600	**NSYRCK19KITN6G**
6G upright´s fixing kit for width 800 and depth 800 (enclosure on demand)	**NSYRCK19KIT6G**

Optional Locks for Enclosure



NSYAEDL1242K33

- With captive key.
- Material: Polyamide handle, metal connecting rods and cam
- For door with hinges on the right, for opening opposite available on demand

Supply:
3-point lock with
1 lock button and
1 cremone screw

Characteristics	References
Optional lock for enclosure, 1242E	**NSYAEDL1242K33**
Optional lock for enclosure, 405E	**NSYAEDL405K33**
Optional lock for enclosure, 455E	**NSYAEDL455K33**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 6G: Floor-Standing Enclosures

Dimensions

SFN possible sizes for Nuclear application

Indication of sizes with maximum weight installed:
- Fixation to the floor with conical washer and large flat washer
- Load evenly distributed on the plate with center of gravuty at the middle height of the cabinet

Dimensions (mm)		Width						
Height	Depth	300	400	500	600	700	800	1000
1200	400							
	500							
	600				75	75	75	
	800				75	75	75	
	1000							
1400	400							
	500							
	600				90	90	90	
	800				90	90	90	
	1000							
1600	400							
	500							
	600				100	100	100	
	800				100	100	100	
	1000							
1800	400							
	500							
	600				115	115	115	
	800				115	115	115	
	1000							
2000	400							
	500							
	600				130	130	130	
	800				130	130	130	
	1000							
2200	400							
	500							
	600				130	130	130	
	800				130	130	130	
	1000							


Size on demand for single enclosure

Size on demand for coupling
Minimum foot print of coupled enclosures: 600 x 600

Not covered

SFN IT: Table of size validated for 6G performance with installed weight of 140 kg as picture underneath.

Dimensions (mm)		Width	
Height	Depth	600	800
1200	600	100	120
	800	100	120
1800	600	140	140
	800	140	140
2000	600	140	140
	800	140	140
	1000		




Distribution of maximum weights for the case of 140 kg.
For the rest of the cases:
- 120 kg: 60 kg on racks + 60 kg on the base
- 120 kg: 40 kg on racks + 60 kg on the base

- Fixing to the floor with conical washer and large flat washer.
- 60 kg on the base and the rest of the racks screwed into the 4 profiles.
- Total weight of racks with center of gravity at half height.
- Minimum 4 racks with maximum weight per rack of 20 kg.
  If less, trays screwed to the 4 profiles must be put in place, until the minimum of 4.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical information

Floors fixing dimensions



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 3G: Floor-Standing Enclosures

Characteristics

SFN for Low to Medium Seismic Level

Tests performed on SFN offer



The offer PanelSeT SFN have been tested to the Standard :
- IEC 60068-2-57
- IEC 60068-3-3

Tested seismic level for equipment :
- 2G level with (0.65 g Zero Period Acceleration)
- 2.5G level with (0.85 g Zero Period Acceleration)
- 3G Schneider Electric level with (1.2 g Zero Period Acceleration)

We have 4 categories of PanelSeT offers with 3G performances:
- SFN 3G
- SFN 3G reinforced
- SFN IT 3G
- PrismaSeT HD 3G

SFN 3G for device installation on mounting plate



To build a SFN in conformity to seismic performances it is necessary to use the following elements.

Composition:
- SFN standard enclosures, size to choose within the table 1 or 2
- Plinth ht 100 mm
- 4 screws M12 x 30 mm for fixation between structure and plinth in addition to the standard fixations

Table 1: SFN one door
Table 2: SFN 2 doors

To increase the weight installed, use the 3G reinforcement kit and 2 heavy cross rails NSYHLCR•••.
(••• according to depth of the enclosure)

Description	Reference
Reinforcement kit for 3G performance for SFN with mounting plate	**NSYSFNRB3G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 3G: Floor-Standing Enclosures

Dimensions

Schneider goes beyond the basic mechanical strength of the enclosure and helps protect the devices installed inside it.

During an earthquake that can apply a 3G acceleration to the enclosure, the acceleration on the mounting plate and therefore on the devices mounted on it can greatly exceeds the 3G value, so Schneider uses two strategies to limit this amplification of the acceleration:

- Reduce the permissible load on the mounting plate
- Consider a higher permissible load by installing the reinforcement kit which, by securing the mounting plate at additional points, limits the amplification of the acceleration passed

This is especially important in components with electronics, moving parts… or in applications where functionality must be ensured at all times such as hospitals, nuclear…
Taking this into account, the following tables indicates the sizes with the maximum weight to be installed for the two previous cases.

Table 1: SFN one door
Indication of sizes with maximum weight installed.

- Fixation to the floor with conical washer and large flat washer.
- Load evenly distributed on the plate with center of gravity at the middle height of the cabinet.

Dimensions (mm)		Width						
Height	Depth	300	400	500	600	700	800	1000
600	400							
	500							
	600				•	•	•	•
	800				•	•	•	•
	1000				•	•	•	•
800	400							
	500							
	600				•	•	•	•
	800				•	•	•	•
	1000				•	•	•	•
1000	400							
	500							
	600				•	•	•	•
	800				•	•	•	•
	1000				•	•	•	•
1200	400							
	500							
	600				75 (60)	90 (60)	105 (80)	135 (80)
	800				75 (60)	90 (60)	105 (80)	135 (80)
	1000				60 (50)	80 (60)	100 (70)	100 (70)
1400	400							
	500							
	600				90 (60)	105 (60)	125 (90)	140 (90)
	800				90 (60)	105 (60)	125 (90)	140 (90)
	1000				80 (60)	80 (60)	100 (70)	100 (70)
1600	400							
	500							
	600				100 (60)	120 (60)	140 (100)	140 (100)
	800				100 (60)	120 (60)	140 (100)	140 (100)
	1000				80 (60)	80 (60)	100 (70)	100 (70)
1800	400							
	500							
	600		•		115 (60)	120 (60)	140 (100)	140 (100)
	800		•		115 (60)	120 (60)	140 (100)	140 (100)
	1000				80 (60)	80 (60)	100 (70)	100 (70)
2000	400							
	500							
	600	•	•		120 (60)	120 (60)	140 (100)	140 (100)
	800	•	•	•	120 (60)	120 (60)	140 (100)	140 (100)
	1000				80 (60)	80 (60)	100 (70)	100 (70)
2200	400							
	500							
	600		•		120	120	120	75
	800		•		120	120	120	75
	1000				80	80	80	60

xxx	Value in kg for SFN with reinforcement kit
(xxx)	Value in kg for SFN without kit
	Size available in catalogue premounted or kit (consult us for weight)
•	Specific size on demand
•	Size standard with coupling foot print must be 600 by 600 or greater Allowed load corresponding to the resulting foot print
	Size available on demand with coupling foot print must be 600 by 600 or greater Allowed load corresponding to the resulting foot print
	Not covered

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 3G: Floor-Standing Enclosures

Dimensions

SFN with double-door sizes tested

Table 2: SFN 2 doors
Indication of sizes with maximum weight installed.

- Fixation to the floor with conical washer and large flat washer.
- Load evenly distributed on the plate with center of gravity at the middle height of the cabinet.

Dimensions (mm)		Width			
Height	Depth	800	1000	1200	1600
1800	400		130 (100)	130 (100)	
	500		130 (100)	130 (100)	
	600	140 (100)	140 (100)	85 (65)	60
	800	140 (100)	140 (100)	85 (65)	
	1000	100 (70)	100 (70)	70 (50)	
2000	400		130 (100)	130 (100)	
	500		130 (100)	130 (100)	
	600	140 (100)	140 (100)	85 (65)	60
	800	140 (100)	140 (100)	85 (65)	
	1000	100 (70)	100 (70)	70 (50)	

xxx Value in kg for SFN with reinforcement kit
(xxx) Value in kg for SFN without kit
3G
2.5 G
Not covered

4

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 3G: Floor-Standing Enclosures

Dimensions




Fixation to the floor

- Fixing to the floor with conical washer and large flat washer.

Loads repartition

- 60 kg on the base and the rest of the racks screwed into the 4 profiles.
- Total weight of racks with center of gravity at half height.
- Minimum 4 racks with maximum weight per rack of 20 kg. If less, trays screwed to the 4 profiles must be put in place, until the minimum of 4.



Distribution of maximum weights for the case of 140 kg.
For the rest of the cases:

- 120 kg: 60 kg on racks + 60 kg on the base
- 110 kg: 50 kg on racks + 60 kg on the base
- 100 kg: 40 kg on racks + 60 kg on the base

To build a SFN 19 in conformity to seismic performances, use the following elements:

Composition

To compose a SFN 19 inche with 3G performance you need to order :

- SFN standard enclosures, size to choose within the table 3
- Kit seismic 3G. 19 inches width 600 or 800 mm
- 4 uprights
- Plinth ht 100 mm
- 4 cross rail according to depth of the chosen enclosure

Composition of the kit seismic 3G for SFN 19 inches

- Four plinth corners´s reinforcement bracket.
- Additional Mounting Brackets top and bottom for 19 inches uprights
- Lateral fixing bracket for 19 inches upright W800
- 2 heavy cross rails installed at the bottom and at the top, in the direction of the width of the cabinet
- Fixing hardware

Description	References
19 inches reinforcement kit for 3G performance for SFN width 600	**NSYSFNRB6003G**
19 inches reinforcement kit for 3G performance for SFN width 800	**NSYSFNRB8003G**

Table 3: SFN 19 inches

Dimensions (mm)		Width	
Height	Depth	600	800
1200	600	100 kg	120 kg
	800	120 kg	120 kg
1800	600	110 kg	140 kg
	800	140 kg	140 kg
2000	600	110 kg	140 kg
	800	140 kg	140 kg
	1000	110 kg	110 kg

3G : one door on the front
2.5G: one door on the front and one on back
Maximum weight of installed devices in kg

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 3G: Floor-Standing Enclosures

PrismaSeT HD

PrismaSeT has been tested to a 3G seismic level according to the following seismic standards: IEC 60068-2-57 and IEC 60068-3-3.




Main function
- LV Switchboard from 630 A to 4000 A dedicated to ED for harsh environments

Added value
- Modular and Functional Type Tested System
- Devices installation and connection with PrismaSeT prefabricated components in SFN structure

Other added value
- IEC61439-1 and 2 certified
- Compatible with PanelSeT SFN and PanelSeT SFN MCC

4

SFN Prisma**SeT** configuration tested with loads



One configuration of PrisamSeT HD tested with weight installed to simulate Circuit breaker and vertical busbar.

Configuration tested:
- Enclosure PrismaSeT:
  height 2000 width 700 depth 500
  - coupled with enclosure height 2000 width 300 depth 500
  - mounted on a 100 mm plinth.
- Plinth with reinforcement bracket.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 6G: Floor-Standing Enclosure

Introduction




The nuclear segment is highly specialized and regulated.
All materials installed follow very strict specifications and standards.
Depending on the installation zone K1, K2, or K3 and the function involved, equipment may be classified from highly critical to non-critical.
The Universal Enclosure Offer can be installed in K3 zone.
If the enclosure is used in one of the following three safety-related functions:

- Control of nuclear fission,
- Control of reactor cooling
- Confinement of radioactive material

It is then considered as “Classified” and all projects must follow a biding process to validate that the enclosure has all the characteristics required in the specification.
For any project in Nuclear application, please contact your Sales representatives.
An enclosure should never be supplied for a nuclear application without first understanding its intended function.

PanelSeT SFN enclosures for Nuclear applications are designed, manufactured, tested to support K3 qualification of the complete switchboard assembly (fully wired and equipped with devices).



Application

Additional feature for Nuclear application

- Material traceability (raw material to finish product)
- Seismic 6G
- DFF (Nuclear manufacturing report)
- Manufacturing control points (AIP)
- Torque tightening marking
- Weld control and welding log book QMOS DMOS Application of ISO 19443 (interrogative approach, CFS...)
- Nuclear-trained personnel + Technical Control) of AIP activities
- Paint PIA PIC PID on demand

Paint PIA, PIC and PID:
Coating system compliant with EDF CCTR for our PanelSeT SFN and PanelSeT SFN 6G Enclosures.
To meet the requirements of the Specification for coating work CCTR 91.C.031 ind.8, we use our powder coating system with a double-layer process.
Our coating is registered in the National Paint File (FNP) under number 1125 in series PIA 100, PID 100, PIC 100.



Our Enclosures for Nuclear are Manufactured in Sarre Union factory (France)

Sarel Plant is certified ISO 19443

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN 6G: Floor-Standing Enclosure

Characteristics

SFN for Nuclear application is based on SFN 6G with additional documented and filed manufacturing and quality constrains (according to RCCE 2019)

SFN for Nuclear application

PB504103




The enclosure used as a base is SFN with 6G certified according to the standards:
- IEC 60068-2-57
- IEC 60068-3-3
- CRT 91 C 112 01 – EDF

Tested seismic level:
- 6G CRT EDF (tested Zero Period Acceleration at twice the value required CRT 91 C 112 01 EDF Nuclear application
- Air Crash Test (5g Zero Period Acceleration), according to CRT 91 C 112 01 - EDF method, 4 seconds and triaxial test
- PanelSeT SFN 6G have been tested with a plain mounting plate and PanelSeT SFN 6G IT with 19 inches fix upright.

Characteristics	Dimensions	References
SFN 2000 x 800 x 600 Single door for Nuclear applications	H 2000 W 800 D 600	**NSYSFN20860NUC**
SFN 2000 x 800 x 600 Double doors for Nuclear applications.	H 2000 W 800 D 600	**NSYSFN208602DNU**

PB504104



Description:
- Integrated plinth 100mm
- Material: Steel
- Ingress protection rating: IP55 according to IEC 60529 / IP54 for double door
- Mechanical protection rating: IK10 according to IEC 62262
- UL50E types 1, 12
- Maximum load: 130 kg in PanelSeT SFN 6G (depends on the size),
  140 kg in PanelSeT SFN 6G IT (depends on the size)
  See table page SFN 6G.

Catalog sizes available: H 2000 W 800 D600:
(other sizes available on demand see sizes table SFN 6G)
- Color: RAL 5012 other colors on demand
- Plinth Color: RAL 5012
- Paint type PIA PIC PID on demand.



NSYSFN208602DNU

Composition:
- Framework
  - 4 uprights
  - 1 lower frame
  - 1 upperframe with roof
- 1 rear panel
- 8 multi-purpose reinforcement corners
- 8 cross-rails fastened to the framework contributing to the seismic resistance (3 left, 3 right, 2 rear)
- Monobloc Plinth 4 mm thick 100 mm high
- Single Door or double door
  - Plain door with handle with a 405 key lock (other lock available)
  - 3 fastening points with connecting rods
  - Single door with hinges on right, door not reversible (opposite direction available on request)
- 3 parts gland plate

Coupling:
- Option to couple SFN 6G enclosures with the coupling kits reference: **NSYSFBKR** and **NSYSFBK19**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Explosive Atmospheres

Panel**SeT** S3DEX

PB501817_54_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DEX

Introduction	364
Characteristics	369
Accessories	370
Dimensions	372

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DEX

Introduction



Industrial Environments, Equipment Rooms

The PanelSeT S3DEX steel enclosure is certified by the LCIE with no. LCIE 02ATEX0037U (component certification).

- Ten sizes: From 300 x 200 x 150 mm to 1000 x 800 x 300 mm.
- Degree of protection:
  - IP66 according to IEC 60529
  - IP64 according to EN60079-0; EN60079-7; EN60079-31.
- Rated service temperature range (°C).
- Resistance to external mechanical impacts: IK10.
- Structured finish, epoxy polyester powder paint, RAL 7035 gray.

Note:

In accordance with the ATEX directive

- The enclosures bear the marking shown on page 603.
- The enclosures offer a degree of protection of IP66 according to IEC 60529 and IP64 according to EN60079-0; EN60079-7; EN60079-31, reaching the highest dust protection according to ATEX standards.
- The certification of our production sites and inspection procedures helps guarantee the observance and regularity of the quality level.

Protection of all applications in ATEX II2 or II3 areas

- Thanks to ATEX-certified steel.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Enhanced Safety
- Blind nut for external earth connection




- Earthing studs welded to the door and inside the body




Robustness
- The chassis is mounted on four 10 mm shouldered backstuds



- The 4 fixing holes are blocked by 4 crimped blind nuts



Labelling
- Example of specific ATEX marking (description: page 603)



Easy Handling
- Reusable packaging
- No sharp edges

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Introduction

ATEX Enclosures from Schneider Electric

Steel enclosures

- All the wall-mounted enclosures presented in this brochure comply with standards for protection against the potential risk of explosion in atmospheres containing gas (G) or dust (D).
- The Schneider Electric offer, designed to be used in group II, is classified as category 2.

Protection of equipment against explosion			ATEX	
Group *	Category	Level	Probability	Zone
I	M1	Very high	Permanent	0 / 20
I	M2	High	Occasional	1 / 21
II	1	Very high	Permanent	0 / 20
II	2	High	Occasional	1 / 21
II	3	Normal	Accidental	2 / 22

* I = equipment designed to be used in the mining and quarrying industries
II = equipment designed to be used in surface industries

- Products of category 2 can be used as category 3.


Our products are certified:

- For gas environments: Increased safety "e" (Ex e) but not flameproof safety "d" (Ex d);
- For dust environments: Protection by enclosure "t" or "tb".
- The wall-mounted enclosures offer a degree of protection of IP66 according to IEC 60529 and IP64 according to EN60079-0; EN60079-7; EN60079-31, exceeding the recommendations of the ATEX directive.
- Certification of our production sites and inspection procedures helps guarantee observance and consistency of the quality level.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Potentially Explosive Atmospheres (ATEX)

DB301035EN_nb



Explosion Hexagon


Definition

Product directive 2014/34/UE:
defines the manufacturers' obligations.


Personal protection directive 99/92/CE:
defines the users' obligations.

Degree of protection:
In hazardous areas, equipment is required to offer a minimum degree of protection of IP54, but it can be tested or certified for a higher degree of protection.

PB500060_47_nb



PB500061_26_nb



Process Leading to an Explosion in an Explosive Atmosphere

For an explosion to occur, six conditions must be met simultaneously (see explosion hexagon opposite). The process is as follows:

- Mixing combustible substances (gases, dusts) with air whose oxygen acts as combustion agent;
- Dosing of combustible products and combustion agents in precise proportions; thereby obtaining a potentially explosive atmosphere;
- Confining the explosive atmosphere thus obtained in a place conducive to explosion;
- Exposing it to an ignition source having sufficient energy to cause an explosion.

ATEX Regulations

Two EU directives and an international standard regulate potentially explosive atmospheres:

- The objective of the two EU directives (the so-called ATEX directives) is to enhance protection from explosions by making various technical and organizational measures compulsory:
  - The 2014/34/EU directive (a revision of the 94/9/EC directive) came into application on 20 April 2016. It describes the requirements that must be met by protection devices and systems, and the conformity assessment procedures.
  - The 99/92/EC directive, a labour relations supplement to the preceding one, presents the minimum requirements to be met to improve the protection of workers liable to be exposed to ATEX-related risks.
- An IEC international standard harmonized with the European standard EN:
  - IEC 60079: electrical equipment for potentially explosive gaseous atmospheres.

Classification

Locations liable to be in the presence of an explosive atmosphere have been classified according to 2 criteria:

- The probability assessed on a scale comprising 3 levels;
- The nature of the combustible product.

The following 6 ATEX zones are obtained:

Probability of an explosive atmosphere	Gas / vapor or mist	Dust
Place in which an explosive atmosphere is present **constantly**, or for long periods or frequently	Zone 0	Zone 20
Place in which an explosive atmosphere is likely to occur **occasionally** in normal operation	Zone 1	Zone 21
Place in which an explosive atmosphere is not likely to occur in normal operation or, if it does occur, will persist for a **short period** only	Zone 2	Zone 22

Equipment installed in an explosive-atmosphere zone must be protected against the risk of explosion. Three levels of protection have been defined, corresponding to the three probabilities of existence of an explosive atmosphere. They are broken down into 5 categories depending on the type of industry.

Protection of equipment against explosions			ATEX	
Group *	Category	Level	Probability	Zone
I	M1	Very high	Permanent	0 / 20
I	M2	High	Occasional	1 / 21
II	1	Very high	Permanent	0 / 20
II	2	High	Occasional	1 / 21
II	3	Normal	Accidental	2 / 22

* I = equipment designed to be used in the mining and quarrying industries
II = equipment designed to be used in surface industries

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Protection of Electrical Equipment

The standards define various methods of protection for electrical equipment according to the application in explosive atmospheres containing gas or dust.


Electrical equipment		ATEX	Methods of protection	
CENELEC	IEC		Symbol	Title
EN 50015	IEC 60079-6	G, D	o	Immersion in oil
EN 50016	IEC 60079-2	G, D	p	Enclosures with internal overpressure
EN 50017	IEC 60079-5	G, D	q	Filling with powder product
EN 60079-1	IEC 60079-1	G, D	d	Explosion-proof enclosures
EN 60079-7	IEC 60079-7	G, D	e	Increased safety "e"
EN 50020	IEC 60079-11	G, D	i	Intrinsic safety
EN 60079-15	IEC 60079-15	G, D	n	Product design
EN 60079-31	IEC 60079-31	G, D	tD	Protection by enclosure "t"

G = gas / vapor or mist
D = dust

ATEX Certification of Electrical Switchboards

- Since 1 July 2003, the European Union has made it compulsory to use certified equipment (electrical or non-electrical) when it is to be installed in areas where the atmosphere is potentially explosive.
- The certification must be established by an approved organization in accordance with the 2014/34/EU directive.
- The organization certifies that the product complies with the health and safety requirements defined in the European directive and the international standards.
- The certificate indicates, via the marking, the product's category and accordingly the zone and the atmosphere in which it may be used.
- Enclosures are certified as components. They will be assembled with other ATEX components (electrical, pneumatic, hydraulic, etc.), to form a final solution which must itself be ATEX-certified and covered by a declaration of conformity.

PB500062_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DEX

Protection for users

- Earthing: The PanelSeT S3DEX steel enclosures are provided with M6 x 16 earth studs welded to the casing and door for equipotential connection. Earth strap to be ordered separately.
- Closing: Enclosures higher than 600 mm are provided with three locking points with connecting rods, with a single control point helping prevent the enclosures from being left half-open.

Casing

- Monobloc casing (cross-structure). Gutter-shaped front profile.
- 4 bottom shoulder studs M8 x 25 for mounting the chassis and notched bars to provide a space of 10 mm at the rear.

Door

- Standard fastening by 3-mm double-bar lock
- Polyurethane door seal
- Double-thickness 20 mm return conferring excellent rigidity;
- 2 concealed hinges (3 above H = 800 mm) to facilitate dismounting and reversibility of the door. Opening angle: 120°
- Maximum load: 50 kg/m².
- Perforated sections on the door, with holes of diameter 4.2 mm every 25 mm for mounting accessories:
- 2 vertical sections from H = 400 mm;
- 2 vertical sections and 2 horizontal sections from L = 800 mm.

Specific ATEX features

- 4 fastening holes closed by 4 crimped blind nuts.
- One crimped M8 blind nut for an external frame earth link (strap not provided)
- Rated service temperature range (°C)
- Marking: See page 603.
- Material: Steel
- Finish: Structured finish, epoxi-polyester powder painting
- Color: RAL 7035 gray
- Ingress protection rating:
  - IP66 (enclosures with single-door) according to IEC 60529
  - IP64 according to EN60079-0; EN60079-7; EN60079-31
- Mechanical protection rating: IK10 (enclosures with plain door) according to IEC 62262
- Fixing: Wall fixing lugs:
  Passivated zinc-coated steel: Reference **NSYAEFPFSC**
  304L stainless-steel: Reference **NSYAEFPFXSC**


NSYS3DEX3215

Characteristics	Height (mm)	Width (mm)	Depth (mm)	References
PanelSeT S3DEX	300	200	150	**NSYS3DEX3215**
PanelSeT S3DEX	300	300	200	**NSYS3DEX3320**
PanelSeT S3DEX	400	300	200	**NSYS3DEX4320**
PanelSeT S3DEX	400	400	200	**NSYS3DEX4420**
PanelSeT S3DEX	500	400	200	**NSYS3DEX5420**
PanelSeT S3DEX	600	400	250	**NSYS3DEX6425**
PanelSeT S3DEX	600	600	250	**NSYS3DEX6625**
PanelSeT S3DEX	700	500	250	**NSYS3DEX7525**
PanelSeT S3DEX	800	600	300	**NSYS3DEX8630**
PanelSeT S3DEX	1000	800	300	**NSYS3DEX10830**

NOTICE

RISK OF STATIC CHARGE

The accessories of the PanelSeT standard wall-mounted enclosures can be installed in the PanelSeT S3DEX wall-mounted enclosures. However, plastic accessories should not be used due to the risk of a static charge.

Failure to follow these instructions can result in equipment damage.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DEX

Accessories







Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Mounting Accessories

Equipment Assembly Accessories


1



Plain mounting plate

See details p. 509

2



Microperforated mounting plate

See details p. 511

3



Telequick mounting plate

See details p. 510

Electrical Distribution Accessories

4



Mixed symmetrical chassis

See details p. 547


> For more information consult the Accessories chapter **page 456**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


PanelSeT S3DEX

Dimensions


Single-Door Enclosure



Detail 1 Detail 2




Detail 4
4 Crimped Blind Nuts for Direct Fixing of the Fixing Lugs






1 4 M8 x 25 mm backstuds.
2 2 M6 x 17.5 mm earthing studs.
3 Stud center-to-center distance.
4 Crimped blind nut center-to-center distance.
5 Blind nut for external earth.


A: Height
B: Width
C: Depth



Detail 5
1 Crimped Blind Nut for the External Earth



Perforated Rails on the Door



Enclosure (8)		Perforated rails on the door (mm)			
Height (A) (mm)	Width (B) (mm)	Vertical F	Vertical D	Horizontal E	Horizontal C
400	300	320	237	-	-
400	400	320	337	-	-
600	400	370	337	-	-
600	600	370	537	-	-
700	500	470	437	-	-
800	600	570	537	-	-
1000	800	770	737	620	949

6 Perforations with a pitch of 25 mm.
7 1 M6 x 17.5 mm earthing stud.
8 The doors of enclosures with dimensions less than 800 x 600 mm do not have horizontal cable guides.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Applications

Electro Magnetic Compatibility

Panel**SeT** S3HF

PB500205_46_nb



Panel**SeT** SFN HF

PB503996



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** S3HF - SFN HF

Introduction	**376**
Characteristics	**378**
Accessories	**379**
Dimensions	**380**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3HF - SFN HF

Introduction



Floor-standing PanelSeT SFN HF and wall-mounting S3HF are designed for sensitive applications requiring Electro-Magnetic Compatibility protection, enabling to operate without being disturbed, and without disturbing neighboring equipment or radio services by Electromagnetic Interference (E.M.I.).

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



PanelSeT S3HF Wall-Mounted Enclosure

From 400 x 300 x 200 mm to 1000 x 800 x 300 mm (W x D x H)

- Metal monobloc enclosures constructed from special zinc-magnesium steel sheet
- Body constructed from single folded and welded sheet
- The enclosure surface, helps ensure good reflection of radiated electromagnetic interference
- Ingress protection rating: IP55
- Mechanical protection rating: IK10
- Structured finish, exclusively epoxy polyester paint on the outside
- RAL 7035 gray



PanelSeT SFN HF Suitable Enclosure

From 1800 x 600 x 600 mm to 2200 x 800 x 800 mm (W x D x H)

- Metal, extendable enclosure constructed from a closed triangular profile, door and panel from special zinc-magnesium steel sheet
- The enclosure surface helps ensure good reflection of radiated electromagnetic interference
- Ingress protection rating: Consult us
- Mechanical protection rating: IK10
- Structured finish, exclusively epoxy polyester paint on the outside
- RAL 7035 gray

This range can be configured according to your needs
4 different services available:

Assemble to order

Mounting of standard accessories

Machining

Painting

For more information, see **CONFIGURE** page 9.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3HF - SFN HF

Characteristics

PanelSeT S3HF

- Single-piece metal enclosures made from special sheets of zing-magnesium 90.
- The presence on the surface of the sheet metal helps ensure good reflection of electromagnetic waves.

Body

- Single-piece body, folded and welded,
- Entirely sealed body with no cable entry and no opening,
- Equipped with four shouldered backstuds allowing direct fixing of the mounting plate,
- Low resistivity for good earth continuity
- Direct fixing or using wall fixing lugs, ref. **NSYPFCR** (to be ordered separately).

Door

- The special body-door gasket (IP + EMC) provides, in addition to water and dust tightness, electric continuity between the door and the body of the enclosure,
- The metal lock with earth continuity helps improve the general shielding,
- An earthing braid added to the enclosure between the body and the door helps guarantee a good earth connection and, consequently, good electromagnetic compatibility,
- 3-mm double-bar lock as standard delivery (if a 405 key is needed it is possible to mount ref. **NSYCLL405CRN**).
- Other sizes: Consult us.
- Finish: Structured finish, epoxy polyester powder (inside not painted)
- Color: RAL 7035 gray
- Ingress protection rating: IP55 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262
- Certifications and declarations: UL, CE declaration
- Fixing: Fixing lugs, ref. **NSYPFCR** to be ordered separately (1 set of 4 lugs)

For more details see page 380

Supply:
Enclosure delivered with galvanized mounting plate.



NSYS3HF4320P

Characteristics	Fig.	Weight (kg)	Width (mm)	Height (mm)	Depth (mm)	References
PanelSeT S3HF	1	7.5	300	400	200	**NSYS3HF4320P**
PanelSeT S3HF	2	13.0	400	600	200	**NSYS3HF6420P**
PanelSeT S3HF	2	20.5	600	600	250	**NSYS3HF6625P**
PanelSeT S3HF	2	32.8	600	800	300	**NSYS3HF8630P**
PanelSeT S3HF	2	53.2	800	1000	300	**NSYS3HF10830P**

PanelSeT SFN HF

Structure

- Galvanized steel structure,
- Top and bottom frame, vertical upright,
- The doors and panels are made of special zinc-magnesium steel sheet.

Claddings

- Enclosure with screwed panels (on side and rear) and front plain door (with reinforcement frame) made from zinc-magnesium steel,
- Bolted side panels included,
- Special gasket (IP + EMC) between framework, door panels, gland plate support and gland plate.
- Finish: Epoxy polyester paint on the outside (inside not painted)
- Color: RAL 7035 gray
- Ingress protection rating: Consult us
- Mechanical protection rating: IK10 according to IEC 62262
- Certifications: RoHS and REACH compliant
- Dimensions manufacturing from 1800 x 600 x 600 mm to 2200 x 800 x 800 mm (W x D x H) are available on demand

One standard reference available

Note:
For more details see page 380

Supply:

- 1 single plain door with door-reinforcement frame (double-door on request, please consult us).
- Left or right opening to 120° (hinges 180° on demand).
- Delivered with standard locking system handle and 5-mm double-bar insert.
- 1 rear panel screwed from the outside.
- 2 side panels mounted with screws.
- 1 removable roof.
- 1 part cable gland plate with special gasket (IP + EMC).



NSYSFNHF20860

Characteristics	Reference
PanelSeT SFN HF	**NSYSFNHF20860**

More sizes on demand, contact us.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

All mounting accessories are compatible with the SFN and SM standard range.
- Mounting plate (see page 514).
- Rails (see page 490).
- 19" frame (fixed and swing-out) (see page 298).

Earth Braids


- They help guarantee the earth connection for high frequencies, avoiding the disturbing electric currents that are produced.
- Material: Tinned copper.

Supply:
10 earth braids (nuts and washers not included)


NSYEB156D6

Characteristics	Section (mm²)	Terminal Ø (mm)	Length (mm)	Width (mm)	References
Earth braids	6	6.5	150	12	**NSYEB156D6**
Earth braids	10	6.5	150	17	**NSYEB1510D6**
Earth braids	16	8.5	155	17	**NSYEB1516D8**
Earth braids	25	8.5	200	27	**NSYEB2025D8**
Earth braids	50	8.5	200	33	**NSYEB2050D8**


EMC Coupling Kit


NSYSFHFBK206

- Used to join enclosures side-by-side or back-to-back. Special gasket for EMC solution.
- Attenuation level is decreased by 5 db when enclosures are joined (please consult us).
- Ingress protection rating: IP55 according to IEC 60529.

Characteristics	Height (mm)	Depth (mm)	References
EMC coupling kit	2000	600	**NSYSFHFBK206**

EMC Protection



PB500311_51_nb

Standard PanelSeT S3D enclosures are tested against electromagnetic interference. Since the enclosure is tested empty, it is advisable to rerun the tests with the enclosure completely equipped in its final configuration.

Earth braids to be ordered separately, see page 540.

Another solution and information on electromagnetic compatibility: PanelSeT S3HF enclosure, page 376.

Attenuation Curve of the PanelSeT S3D Compared with the PanelSeT S3HF



Frequency: 3 - 13.2 Hz
Amplitude: 1 mm/sec below 22 Hz
Frequency: 3 - 100 Hz
Acceleration: 0.7 g above 30 Hz

Vertical Polarization
PV Trend
Horizontal Polarization
PH Trend
Average of Trends

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3HF - SFN HF

Dimensions

PanelSeT S3HF

Fig. 1






Fig. 2



A: Height.
B: Width.
C: Depth.

* Model 1200 x 800.

PanelSeT SFN HF



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electro Magnetic Compatibility
PanelSeT S3HF - SFN HF
Characteristics

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Variable-Speed Drive Flush-Mounting Kit
PanelSeT S3D, SFN and SM

Introduction

The variable-speed drives flush-mounting kits have been designed to isolate the power part, which is an important source of heat. They are mounted in the PanelSeT range of steel enclosures (floor-standing and wall-mounted enclosures) and have been approved for Altivar Process variable-speed drives of the ATV630 and ATV930 ranges (power range: 0.75 to 45 kW at 200/240 V, 0.75 to 90 kW at 380/480 V).

The kits are available in five sizes and offer two methods of mounting variable-speed drives:
- slide-rail mounting for sizes 1, 2 and 3
- bracket mounting for sizes 4 and 5.

The kits can be installed:
- at the back of the enclosure.

This installation provides full thermal insulation.

- inside the enclosure on a mounting plate.

This installation may require additional thermal control.







Tightness
- IP55 according to IEC 60529 with polyurethane seal provided.

Configured offer

Services
Option of cut-outs (enclosure and frame) by Schneider Electric: No risk of corrosion and cuts (cut-out made before painting).



Ease of Installation
- Set of slide-rails allowing the variable-speed drive to be mounted quickly and efficiently.



Strength
- The rigidity of the kit allows it to be installed on PanelSeT S3D, SFN and SM enclosures.


Earth Continuity
- Earth continuity is ensured by tightening the M6 nuts combined with pin washers.



Maintenance of the Variable-Speed Drive Fan (Kit Sizes 4 and 5)
- Easy front panel maintenance for fan servicing.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Variable-Speed Drive Flush-Mounting Kit
PanelSeT S3D, SFN and SM
Characteristics

Characteristics	Mounting kits	
	 PB502935_25_nb **Sizes 1, 2 and 3**	 PB502936_32_nb **Sizes 4 and 5**
Note: For dimensions see page 384	Variable-speed drive installation kits allowing the hot part to be isolated.	
Material	Steel	
Finish	Structured finish, epoxy polyester powder	
Color	RAL 7035 gray	
Ingress protection rating	IP55 according to IEC 60529	
Certifications	UL (cULus). Rated 1, 3R and 12 according to UL50E	
Supply	Sizes 1, 2 and 3: • Painted steel plate with cut-out fitted with two slide-rails + adhesive seal + 7 to 9 M6 studs for kit mounting • Protection seal profile supplied for frame cut-out • Enclosure drilling template	Sizes 4 and 5: • Painted steel plates with cut-out fitted with painted mounting brackets + screws and nuts for fixing the brackets and the kit • Protection seal supplied for frame cut-out


Dimensions (mm)				Compatibilities						
					Variable-speed drives					Kits
					ATV340 380/480 V	ATV630 200/240 V	380/480 V	ATV930 200/240 V	380/480 V	
H	L	P	Sizes	Enclosures	References	References	References	References	References	References
360	235	22	1	S3D, SFN, SM	-	**ATV630U07M3**	**ATV630U07N4**	**ATV930U07M3**	**ATV930U07N4**	**NSYPTDS1**
360	235	22	1	S3D, SFN, SM	-	**ATV630U15M3**	**ATV630U15N4**	**ATV930U15M3**	**ATV930U15N4**	**NSYPTDS1**
360	235	22	1	S3D, SFN, SM	-	**ATV630U22M3**	**ATV630U22N4**	**ATV930U22M3**	**ATV930U22N4**	**NSYPTDS1**
360	235	22	1	S3D, SFN, SM	-	**ATV630U30M3**	**ATV630U30N4**	**ATV930U30M3**	**ATV930U30N4**	**NSYPTDS1**
360	235	22	1	S3D, SFN, SM	-	**ATV630U40M3**	**ATV630U40N4**	**ATV930U40M3**	**ATV930U40N4**	**NSYPTDS1**
360	235	22	1	S3D, SFN, SM	-	-	**ATV630U55N4**	-	**ATV930U55N4**	**NSYPTDS1**
420	265	22	2	S3D, SFN, SM	-	**ATV630U55M3**	**ATV630U75N4**	**ATV930U55M3**	**ATV930U75N4**	**NSYPTDS2**
420	265	22	2	S3D, SFN, SM	-		**ATV630D11N4**	-	**ATV930D11N4**	**NSYPTDS2**
555	295	22	3	S3D, SFN, SM	-	**ATV630U75M3**	**ATV630D15N4**	**ATV930U75M3**	**ATV930D15N4**	**NSYPTDS3**
555	295	22	3	S3D, SFN, SM	-	**ATV630D11M3**	**ATV630D18N4**	**ATV930D11M3**	**ATV930D18N4**	**NSYPTDS3**
555	295	22	3	S3D, SFN, SM	-	-	**ATV630D22N4**	-	**ATV930D22N4**	**NSYPTDS3**
800	385	151.5	4	SFN, SM	**ATV340D30N4E**	**ATV630D15M3**	**ATV630D30N4**	**ATV930D15M3**	**ATV930D30N4**	**NSYPTDS4**
800	385	151.5	4	SFN, SM	**ATV340D37N4E**	**ATV630D18M3**	**ATV630D37N4**	**ATV930D18M3**	**ATV930D37N4**	**NSYPTDS4**
800	385	151.5	4	SFN, SM	-	**ATV630D22M3**	**ATV630D45N4**	**ATV930D22M3**	**ATV930D45N4**	**NSYPTDS4**
975	427	205.5	5	SFN, SM	**ATV340D45N4E**	**ATV630D30M3**	**ATV630D55N4**	**ATV930D30M3**	**ATV930D55N4**	**NSYPTDS5**
975	427	205.5	5	SFN, SM	**ATV340D55N4E**	**ATV630D37M3**	**ATV630D75N4**	**ATV930D37M3**	**ATV930D75N4**	**NSYPTDS5**
975	427	205.5	5	SFN, SM	**ATV340D75N4E**	**ATV630D45M3**	**ATV630D90N4**	**ATV930D45M3**	**ATV930D90N4**	**NSYPTDS5**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Variable-Speed Drive Flush-Mounting Kit
PanelSeT S3D, SFN and SM

Dimensions


NSYPTDS1




NSYPTDS2




NSYPTDS3



NSYPTDS4



NSYPTDS5



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Variable-Speed Drive Flush-Mounting Kit
PanelSeT S3D, SFN and SM

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures


Introduction

Function

New

PanelSeT SFN Interlocking solution provides a mechanical interlock of coupled cells.
This system works as follows:

- The main double door is prepared to receive a switch
- This switch has to be linked with the incomer device of the switchboard (i.e.: circuit breaker)
- When the switch is “ON”, all the doors cannot be opened
- The main door can only be opened when the switch is in the “OFF” position
- The interlock solution is compatible with plain door type only
- Once the main door is opened, it enables access to unlock the doors of the other enclosures of the switchboard
- The main double door cannot be closed if one (or more) of the other doors is opened
- The interlocking system can couple up to 8 enclosures
- The solution can be installed on the previous Spacial SF offer.



Technical information

Mechanical protection rating:
- IK10 for plain door
- IK08 for transparent door according to IEC 62262

Standards:
- Compliance with enclosure standard IEC 62208 and RoHS and REACH directive

Certifications
- UL (cULus) Rating according to UL50E: Types 1, 12


Installation:
- **Indoor:** * Compliant with IEC 62208 regarding type tests specified in §9.12 (resistance to UV radiation) and §9.13 (resistance to corrosion). Canopy needed to avoid water stagnation on the upper part of the enclosure, page 458

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Coupled enclosures can be in any configuration as shown below.



Left position




Middle position




Right position

The main double door (200 mm wide) will always be on the right and the wider door will always be on the left (600, 800 or 1000 mm wide).



The doors of the locked enclosures can open on the right- or left-hand side.





Interlocking up to 9 coupled enclosures.




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Modular Enclosures

Characteristics

Lock for main enclosure

- Designed to be installed on specific double door with cut-outs (reference below).
- Compatible with Square D 9422 A1 et A2.
- Unlock the door of the main enclosure when the switch is in the “OFF” position to allow access.
- Material: Steel.
- Finish: Zinc-coated.


NSYSLCKP

Characteristics	References
Main door lock	**NSYSLCKP**

Interlock link for double door

- Use when the main enclosure has a coupled enclosure on its right.
- Designed to be installed in the main enclosure for widths of 800, 1000, and 1200 mm; a height of 2000/2200 mm; and any depth.
- Material: Zinc-coated steel mechanism, black plastic activation handle.


NSYSLINK800

Characteristics	References
Interlock link for double door SFN W800	**NSYSLINK800**
Interlock link for double door SFN W1000	**NSYSLINK1000**
Interlock link for double door SFN W1200	**NSYSLINK1200**

Interlock actuator


NSYSODS

- Designed to be installed on PanelSeT SFN for widths of 800, 1000, 1200 mm.
- Enables the enclosures coupled to the main one to be manually unlocked by moving a rod horizontally.
- Material: Zinc-coated steel mechanism, black plastic activation handle.

Characteristics	References
Interlock actuator	**NSYSODS**

Double doors for main enclosure


NSYSFND20802DI

- Designed to install the lock for the main enclosure and the switch.
- Installation directly on the structure of the enclosure, opening 120°.
- Lock with handle and 5-mm double-bar insert, with 4 locking points.
- Reinforced frame, cut-out with a pitch of 25 mm.
- The door with the cut-out for the switch is 200 mm wide and is always positioned on the right.
- Material: Steel.
- Finish: Structured finish, epoxy polyester powder.
- Color: RAL 7035 gray.
- Maximum acceptable weight to be installed on the door: 50 kg.

Characteristics	References
Double door SFN Flange discon. 2000x 800	**NSYSFND20802DI**
Double door SFN Flange discon. 2200x800	**NSYSFND22802DI**
Double door SFN Flange discon. 2000x1000	**NSYSFND20102DI**
Double door SFN Flange discon. 2200x1000	**NSYSFND22102DI**
Double door SFN Flange discon. 2000x1200	**NSYSFND20122DI**
Double door SFN Flange discon. 2200x1200	**NSYSFND22122DI**

Interlock for locked enclosures

- Designed to be installed on PanelSeT SFN for widths of 600, 800, and 1000 mm; heights of 2000 and 2200 mm; and any depth.
- Single door only.
- Mechanical lock for enclosure coupled to the main one.
- Material: Zinc-coated steel.



NSYSLCKS6

Characteristics	References
Interlock for secondary doors width 600	**NSYSLCKS6**
Interlock for secondary doors width 800	**NSYSLCKS8**
Interlock for secondary doors width 1000	**NSYSLCKS10**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Example of configuration:

A One enclosure Height 2000 x Width 600 x Depth 600 locked enclosure
B One enclosure Height 2000 x Width 800 x Depth 600 main enclosure with switch
C One enclosure Height 2000 x Width 600 x Depth 600 locked enclosure:
- Plinth height 100 mm for each enclosure
- 2 coupling kits



	Required products			A	B	C	
	References	Characteristics	Common	H 2000 / W 600 / D600	H 2000 / W 800 / D600	H 2000 / W 600 / D600	Qty
	Interlocking						
1	NSYSLCKS6	Interlock for secondary doors width 600		1		1	2
2	NSYSLCKP	Main door lock			1		1
3	NSYSODS	Interlock actuator			1		1
4	NSYSLINK800	Interlock link for double door SFN W800			1		1
	Enclosure						
5	NSYSFNV20	Vertical upright		1	1	1	3
6	NSYSFNC86	Bottom and top frame			1		1
7	NSYBPN208	Back panel W800			1		1
8	NSY2SPN206	Side panel D600	2				2
9	NSYSFNC66	Bottom and top frame		1		1	2
10	NSYBPN206	Back panel W600		1		1	2
11	NSYSFBKF	Coupling kit	2				2
12	NSYSFND206	Plain door SFN/SM 2000x600		1		1	2
	Double door						
13	NSYSFND20802DI	Double door SFN Flange discon. 2000 x 800			1		1
	Switch						
14	9422*	Switch disconnector			1		1
	Plinth enclosure						
15	NSYSPF6100	Front and rear plinth 100 x 600		1		1	2
16	NSYSPS6100	2 plinth side panels 100 x 600		1		1	2
17	NSYSPF8100	Front and rear plinth 100 x 800			1		1
16	NSYSPS6100	2 plinth side panels 100 x 600			1		1

* A1, A2, A3, A4, A9, and A10 handles.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys Thermal Management System

Thermal Management Solutions

PB503912



5

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Thermal Management Solutions

Introduction	**392**
Thermal Functions	**394**
Airing	**396**
ClimaSys CA: Natural Airing	396
ClimaSys CV: Forced Airing	396
Heating	**416**
ClimaSys CRS: Ultra Thin Heaters	416
ClimaSys CR: Resistance Heaters	420
Controlling	**424**
ClimaSys CC: Thermal Controllers	424
Cooling	**428**
ClimaSys CE: Exchangers	428
ClimaSys CU: Cooling Units	438
ProClima Software	**454**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys

Introduction



All companies face growing challenges that significantly impact their strategic direction, profitability, and environmental goals. These challenges require careful consideration to navigate successfully.



Extreme Ambient Conditions

Extreme weather events such as heat waves, storms, and floods are becoming more frequent and severe. The increased frequency and intensity of these weather phenomena can disrupt operations, damage equipment, lead to costly repairs, downtime, and the loss of resilience in facilities and infrastructure.



Increasing Costs of Energy and Materials

The rising costs of energy and materials are forcing companies to rationalize and optimize their operations. Energy prices and the cost of raw materials can fluctuate dramatically due to various factors such as geopolitical tensions, supply chain disruptions, or market volatility. These rising costs directly impact profitability, making it essential for companies to find ways to reduce consumption and improve efficiency.



Data Management

As processes and projects become more complex, the volume of data that needs to be managed increases. Effective data management is essential for making informed decisions, optimizing operations, and maintaining competitive advantage.



Industrial Processes Reliability

Ensuring the reliability of industrial processes and continuity of service is vital to maintain production and facilitate safety.
The reliability of industrial processes is influenced by factors such as equipment maintenance, process control, and workforce training. Failures in any of these areas can result in costly interruptions and safety hazards.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

In the context of the challenges faced by industrial companies, effective thermal management is crucial for several reasons.

Dependability of Manufacturing Processes

Maintaining optimal temperature and humidity levels helps prevent overheating and equipment failures. This reliability is essential for reducing downtime and avoiding production losses, which can have significant financial consequences for businesses.

Reducing Downtime and Production Losses

Unplanned downtime due to thermal issues can disrupt production schedules and lead to significant financial losses. Effective thermal management helps ensure that equipment operates within safe temperature ranges, minimizing the risk of unexpected breakdowns, and maintaining continuous production.

Financial Impact

Thermal management directly impacts the financial health of a company. By minimizing equipment failures and reducing downtime, it helps avoid costly repairs and lost production time. This contributes to overall cost savings and improved profitability.

Thermal Functions

Thermal Functions refer to the physical principles used to regulate temperature and humidity levels in an electrical panel. These functions are categorized into four main families: airing, cooling, heating, and controlling functions. Each function is associated with a specific thermal management solution.
















Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Thermal Functions

	Homogenize	Airing		Cooling
		 DB300447_18_nb	 DB300448_60_nb	 DB300449_60_nb
Solution	**Air circulation**	**Natural airing**	**Forced-airing**	**Air-to-air exchanger**
Description	Circulation fan inside the enclosure.	Air circulation achieved by installing grids (side or roof-mounted) with or without filter, or by elevating the roof.	A fan (with or without filter) feeds fresh external air into the enclosure. This creates a slight overpressure, forcing the warm air out of the enclosure through an outlet grid. The air flow balances the temperature, and the overpressure helps prevent dust ingress. Side or roof-mounted. Can be combined with a thermostat	Cooling system comprising an aluminum heat exchanger and separate internal and external air circuits and two centrifugal fans circulating the air, and a thermostat for temperature control. Side or roof-mounted.
Use	To help prevent hot spots.	Low power to be dissipated. Dusty environment.	High heat dissipation performance, suitable for dusty and non-hazardous environments. Helps prevent hot spots	Medium heat dissipation performance, suitable for corrosive environments (food processing) and relatively cold environments (approx. 25 °C).
Temperature conditions Ta = ambient temperature (outside the enclosure) Td = desired temperature inside the enclosure.	None	Td > Ta + 5 °C	Td > Ta + 5 °C 3 °C < Ta ≤ 35 °C	Td > Ta + 10 °C
Need for sealing between the external ambient environment and the inside of the enclosure	Yes	No	No	Yes
Advantages	• Uniform temperature inside the enclosure.	• Very economical solution. • No maintenance. • Easy, fast installation.	• Economical solution. • Easy maintenance. • Easy, fast installation. • Uniform temperature inside the enclosure. • Level of protection: IP54 (IP55 with cover).	• Easy maintenance (no filter). • Far lower maintenance frequency than for fans. • IP55 between the enclosure and the air-to-air exchanger.
Limitations		• Low power dissipated. • Reduction of IP rating. • Risk of ingress of particles and dust if no filter.	• Internal temperature always higher than external temperature. • Maintenance required: filter change.	• Internal temperature always higher than external temperature.
Illustration	 PB501067_37_nb	 PB501020_28_nb Outlet grids	 PB501021_53_nb Fans	 PB502618_9_1_nb PB502596_11_nb Air-to-air exchangers

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

	Cooling		Heating
			
	Air-to-water exchanger	**Cooling unit**	**Resistor heaters**
	Cooling system using an exchanger coil supplied with cold water, separated from the internal air circuit, a centrifugal fan for air circulation, and a thermostat to regulate the temperature inside the enclosure. Side-mounting.	Operates like a heat pump: A condenser dissipates the calorific energy absorbed by an evaporator to the ambient air, thereby cooling and drying the air in the enclosure. Mounted on Side (surface, half flush, flush) or Roof. Connected cooling units provides data related to alarming, operations, and setting, locally and remotely, in any process SCADA, supervision, including EcostruXure SE Software and Application and services.	The heating resistors help prevent the formation of condensation and ensure an ideal temperature inside the enclosure.
	Dissipation of large quantities of heat. Suitable for difficult environments (cement plants, production lines, etc.) or humid environments (sewage plants, bottling lines, etc.). Calorific energy is not discharged to the environment.	Filter recommendation: Office environment (no dust, no grease): filter free, Industrial environment (dust, grease, not explosive): G3 fiber filter is recommended, Outdoor (not explosive) : aluminum filter is recommended, Indoor CU are delivered without any filter by default. Outdoor CU are delivered with Aluminum filter by default.	To heat the inside of the enclosure and help prevent condensation.
	Ta > Td	Ta > Td and Ta ≤ 55 °C	Ta < Td
	Yes	Yes	-
	• Internal temperature independent of external temperature • Protection system against any leaks • Calorific energy dissipated externally. • Level of protection: IP55.	• Internal temperature independent of external temperature. • Even temperature inside the enclosure. • Level of protection: IP54 for roof, IP55 for side-mounted models. • Drainage system for condensed water from evaporator heat exchanger.	• Small size (1.6 mm thick for the ultra-thin version). • Low surface temperature (< 70 °C for insulated version, 75 °C for aluminum version). • Even temperature inside the enclosure with the version equipped with a fan.
	• Cold-water circuit with stabilized temperature and flow rate required. • Installation of special piping.	• Water condensation evaporation unit integrated in side-mounted models from 1 to 4 kW. • Maintenance required: filter change.	
			
	Air-to-water exchangers	Cooling units	Heating resistors

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CA and CV

Introduction



The ClimaSys CA and CV airing and ventilation ranges are designed to help safeguard components from overheating. These products help ensure operational reliability and extend the lifespan of equipment by managing the internal temperature of the enclosures.

While both ranges focus on airflow, they cater to different thermal demands.

ClimaSys CA

Uses Convection and passive grilles for low-heat environments.

ClimaSys CV

Uses powered fan to move larger volumes of air in high-heat or high-density scenarios.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CA: Natural Airing



Versatile Components
The range includes a variety of hardware to facilitate airflow, such as
- Outlet Grilles
- Metal Louvres
- Roof extensions

Compatibility
Designed as the primary solution of thermal management, it is fully compatible with all Schneider PanelSeT ranges

ClimaSys CV: Forced Airing



Easy Installation
Quick installation
- Reliable fixing with the assisted fixing device and the system of multi-thickness fixing-clips

Easy to invert
- To operate as extractors, all the motors can be inverted by simply removing four screws



Quality of Components
Selection of motors
- Improved flow rate and longer service life
- Large range of input voltages available on all motors delivered as standard, with 50/60-Hz alternating current or direct current



Easy Maintenance
Quick filter replacement
- Quick, easy and reliable replacement of the filter installed in the fan, even during operation



Optimized Flow Rate: Average Increase of 50%
- Maximum use of surface
- Minimal pressure loss



High Protection ratings
- UL-certified Products
- Rated Type 12 according to UL50E
- IP54 as Standard



Filter-Retaining System
Locks the synthetic filter firmly in place to maintain IP54 protection rating, even under challenging industrial conditions



Fixing Guide
Aligns the fan to the enclosure wall, compensates for machining errors and helps ensure the mounting clips engage securely



Multi-Fit
Fixing clips enable tool-free installation for a thicknesses ranging from 0.8 to 4.5mm while using a inclined profile to shield the filter from vertical water spray



Water Evacuation
This system maintains IP54 (or IP55 with a cover) by automatically evacuating water absorbed by the filter, even during high-pressure spraying



Sealing Gasket
The Polyurethane gasket is precision-molded and heat-set to help guarantee a long-lasting seal for the enclosure


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CA and CV


Grilles

Metal Louvre Plate, Rectangular

Louvre dimensions



Cut-out dimensions




- Material: Steel.
- Color: RAL 7035 gray.
- Structured finish, epoxy polyester panting.
- Ingress protection rating (according to IEC 60529): IP20.
- Installation: On the sides of the enclosure. Fixing by screws.

Supply:
One metal louvre and fixing elements.


NSYCAG110X46M

Characteristics	(mm)									References
	A	B	C	D	E	F	G	H	R	
Metal louvre plate, rectangular	144	62	36	110	-	-	46	94	10	**NSYCAG110X46M**
Metal louvre plate, rectangular	208	90	72	94	190	-	62	180	18	**NSYCAG180X62M**
Metal louvre plate, rectangular	244	90	72	130	226	-	62	216	18	**NSYCAG216X62M**
Metal louvre plate, rectangular	345	118	100	231	327	115.5	90.5	317	30	**NSYCAG317X91M**
Metal louvre plate, rectangular	345	148	130	231	327	115.5	120	317	30	**NSYCAG317X120M**
Metal louvre plate, rectangular	445	148	130	267	427	148.5	120	417	30	**NSYCAG417X120M**

Metal Louvre Plate, Square



- Ingress protection rating (according to IEC 60529): IP23.
- Color: RAL 7035 gray.

Supply:
One metal louvre.


NSYCAG104X95LM

Characteristics	Dimensions (mm)	A	B	C	Slot width	Number of slots	References
Metal louvre plate, square	120 x 120	95	90	104.8	90	5	**NSYCAG104X95LM**
Metal louvre plate, square	160 x 160	110	130	140	100	5	**NSYCAG130X110LM**
Metal louvre plate, square	220 x 220	190	170	200	180	5	**NSYCAG170X190LM**

Anti-Insect Filters for Metal Louvre Plate, Square


- Material: Stainless-steel 304L Ø 0.32 mm wire mesh, 1.07 mm, thickness 0.6 mm.
- Color: RAL 7035 gray
- Ingress protection rating (according to IEC 60529): IP33.
- Installation: Between the enclosure and the metal louvre.

Supply:
One anti-insect filter.


NSYCAF104X95X

Characteristics	External dimensions (mm)	Weight	References
Anti-insect filters for metal louvre plate, square	98 x 115	0.8 kg/m²	**NSYCAF104X95X**
Anti-insect filters for metal louvre plate, square	133 x 158	0.8 kg/m²	**NSYCAF130X110X**
Anti-insect filters for metal louvre plate, square	197 x 215	0.8 kg/m²	**NSYCAF170X190X**

Roof Elevators



- Allow the roof to be raised, providing natural airing.
- Material: Zinc-coated steel.
- They are screwed onto the structure of SF enclosures at the roof fixing points.

Supply:
4 elevators.



NSYRE26

Characteristics	Top elevation (mm)	References
Roof elevators	26	**NSYRE26**
Roof elevators	60	**NSYRE60**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Hood for Natural Airing

- Natural airing device for coupling to the top of metal floor-standing enclosures. Solution for combination with the airing slots.
- Material: Steel.
- Finish: Structured finish, epoxy polyester painting, RAL 7035 gray for NSYCAC228RMF and RAL9003 for NSYCAC228RMB.
- Ingress protection rating (according to IEC 60529): IP54.
- Installation: Fixing to the top by means of caged nuts and special screws.



Supply:
1 hood for natural airing and fixing elements.


NSYCAC228RMF

Characteristics	Weight	References
Hood for natural airing	4.6 (kg)	**NSYCAC228RMF**
Hood for natural airing	4.6 (kg)	**NSYCAC228RMB**
Spare filter	-	**NSYCAF228R**

Plastic Airing Louvres


NSYCAG45LP


NSYCAG33LP

Four models available according to IP rating, in vertical position.

Supply:
References by unit. Order by multiples of 2 units (2, 4, 6, etc)

Characteristics	Ingress protection rating	Cut-out Ø (mm)	References
Plastic airing louvres	IP22	45.5	**NSYCAG45LP**
Plastic airing louvres	IP30/44	35	**NSYCAG35LP**
Plastic airing louvres	IP45	38	**NSYCAG38LP**
Plastic airing louvres	IP44	33	**NSYCAG33LP**
Plastic airing louvres	IP45	19	**NSYCAG19LP**

Sealed pressure balance valve

- Controls the pressure to avoid condensation following internal temperature increase.
- Material: PA6-V2, acrylic co-polymer membrane, water- and oil-repelling.
- Ingress protection rating: IP68.
- Permeability: Air flow under Δ P = 0.7 bar.


NSYCAG12LPH2

Characteristics	Cut-out Ø (mm)	Permeability	Pressure difference	Minor pack.	References
Sealed pressure balance valve	M12	16 litres/h	ΔP < 1 bar	10	**NSYCAG12LPH1**
Sealed pressure balance valve	M12	120 litres/h	ΔP < 0.1 bar	10	**NSYCAG12LPH2**

Airing Systems, IP54 Outlet Grilles

- Delivered with G2 M1 synthetic standard filter according to ISO 16890 and with an anti-insect filter.
- Material: Injected thermoplastic polycarbonate.
- Color: RAL 7035 gray.
- Ingress protection rating (according to IEC 60529): IP54.
- UL recognized (cURus), rated Type 12 according to UL50E.


NSYCAG92LPF

Characteristics	Height (mm)	Width (mm)	Depth (mm)	Cut-out (mm)	References
IP54 outlet grilles	137	117	13	92 x 92	**NSYCAG92LPF** (1)
IP54 outlet grilles	170	150	15	125 x 125	**NSYCAG125LPF** (1)
IP54 outlet grilles	268	248	18	223 x 223	**NSYCAG223LPF** (1)
IP54 outlet grilles	336	316	18	291 x 291	**NSYCAG291LPF** (1)

(1) CSA compliant.

EMC IP54 Outlet Grille

- Grille equipped with:
  - a steel frame covering the plastic elements (self-extinguishing ABS according to standard UL 94 V-0),
  - a metal grille attached to the frame,
  - a beryllium gasket to help ensure conductivity between the perimeter of the fan unit and the enclosure.
- Color: RAL 7035 gray.
- Ingress protection rating (according to IEC 60529): IP54.


NSY17997

Characteristics	Dimensions (mm)		References
	External	Cut-out	
EMC IP54 outlet grille	145 x 145 x 70	126 x 126	**NSY17996**
EMC IP54 outlet grille	252 x 252 x 97	224 x 224	**NSY17997**
EMC IP54 outlet grille	320 x 320 x 150	292 x 292	**NSY17998**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Forced Airing

Ventilation

- Characteristics: The fans comprise an axial motor, a protective housing on the front and rear surfaces and a filter designed to retain dust particles. This filter can be replaced during operation without risk of contact with the rotating element.
- Material of external grids: Injected thermoplastic (ASA PC). self-extinguishing according to UL 94 V-0
- Color external grids: RAL 7035 gray as standard
- Conditions of use: The external temperature must not exceed 30 °C and must be more than 5 °C lower than the temperature wanted in the enclosure. The filters that equip the fans must be cleaned and replaced regularly. The ambient air must be relatively clean and overfrequent filter replacement should be avoided. Bear in mind the pressure losses caused by the outlet element (grille with filter, airing louvre or simple opening) when determining the fan flow rate
- Storage Temperature: -40…+ 70 °C
- Ingress protection rating (according to IEC 60529): IP54
- If the enclosure contains electronics, material sensitive to dust deposits or if it is needed to use several fans and grills in the same enclosure, we highly recommend using ProClima and a solution with better filtering using a G3 filter or a higher IP (cooling option as example). In any case, do not hesitate to contact our sales teams to collaborate on your project.
- Mechanical protection rating (according to IEC 62262): IK08
- UL recognized (cURus). Rated Type 12 according to UL50E.
- Installation: The cut-out template supplied with the device avoids the need for marking and helps protect the surface of the enclosure during handling
- All fan references are also delivered with one anti-insect filter
- Options: The device can be equipped with a filter that provides even more efficient protection for your sensitive facilities against dust particles

Free flow rate with standard filter (m^3/h)	Flow rate with outlet grille(s) (m^3/h)		Voltage range (nominal voltage)	Absorbed power (max. intensity)	Noise level	External dim. H x L x W (cut-out)	Weight (kg)	Operating temperature	Max. static pressure	Pre-fuse
	1	2								
38 (50 Hz) 39 (60 Hz)	25 (50 Hz) 26 (60 Hz)	33 (50 Hz)	150 V...250 V (230 V)	4.5/4.8 W (0.16/0.17 A)	40/41 dB (A)	137 x 117 x 49 (92 x 92)	0.220	-10...+ 70 °C	29 Pa	Pre-fuse T 2A
38 (50 Hz) 39 (60 Hz)	27 (50 Hz) 28 (60 Hz)	35 (50 Hz)	75 V...125 V (115 V)	3.3/3.5 W (0.16/0.16 A)	40/41 dB (A)	137 x 117 x 49 (92 x 92)	0.220	-10...+ 70 °C	29 Pa	Pre-fuse T 2A
58	39	47	10 V...27.6 V (24 V DC)	3.6 W (0.18 A)	40/41 dB (A)	137 x 117 x 49 (92 x 92)	0.230	-10...+ 70 °C	29 Pa	Pre-fuse T 2A
44	34	41	36 V...56 V (48 V DC)	3.6 W (70 mA)	40/41 dB (A)	137 x 117 x 49 (92 x 92)	0.230	-10...+ 70 °C	29 Pa	Pre-fuse T 2A
85 (50 Hz) 98 (60 Hz)	63 (50 Hz) 72 (60 Hz)	71 (50 Hz)	175 V...253 V (230 V)	17/15 W (0.121/0.097 A)	46/49 dB (A)	170 x 150 x 62 (125)	0.780	-20…+60 °C	50 Pa	Pre-fuse T 2A
79 (50 Hz) 92 (60 Hz)	65 (50 Hz) 74 (60 Hz)	73 (50 Hz)	75 V...126 V (115 V)	16/15 W (0.207/0.179 A)	46/49 dB (A)	170 x 150 x 62 (125)	0.780	-20…+60 °C	50 Pa	Pre-fuse T 2A
80	57	77	10 V...27.6 V (24 V DC)	7.6 W (0.30 A)	46/49 dB (A)	170 x 150 x 62 (125)	0.480	-10...+ 70 °C	50 Pa	Pre-fuse T 2A
79	59	68	25 V...55.2 V (48 V DC)	8 W (0.173 A)	46/49 dB (A)	170 x 150 x 62 (125)	0.480	-10...+ 70 °C	50 Pa	Pre-fuse T 2A
165 (50 Hz) 193 (60 Hz)	153 (50 Hz) 171 (60 Hz)	161 (50 Hz) 175 (60 Hz)	175 V...253 V (230 V)	16.3/14.3 W (0.12/0.94 A)	50/51 dB (A)	268 x 248 x 104 (223 x 223)	1.140	-20…+60 °C	50 Pa	Pre-fuse T 2A
164 (50 Hz) 193 (60 Hz)	153 (50 Hz) 171 (60 Hz)	161 (50 Hz) 179 (60 Hz)	75 V...126 V (115 V)	15.5/14.4 W (0.20/0.18 A)	50/51 dB (A)	268 x 248 x 104 (223 x 223)	1.140	-20…+60 °C	50 Pa	Pre-fuse T 4A
188	171	179	10 V...27.6 V (24 V DC)	8 W (0.3 A)	50/51 dB (A)	268 x 248 x 104 (223 x 223)	0.810	-10...+ 70 °C	50 Pa	Pre-fuse T 2A
193	171	179	25 V...55.2 V (48 V DC)	8.7 W (0.18 A)	50/51 dB (A)	268 x 248 x 104 (223 x 223)	0.810	-10...+ 70 °C	50 Pa	Pre-fuse T 2A
302 (50 Hz) 350 (60 Hz)	260 (50 Hz) 307 (60 Hz)	268 (50 Hz)	145 V...253 V (230 V)	36/37 W (0.17/0.16 A)	53/57 dB (A)	268 x 248 x 116 (223 x 223)	1.3	-10...+ 70 °C	158 Pa	Pre-fuse T 2A
302 (50 Hz) 350 (60 Hz)	263 (50 Hz) 307 (60 Hz)	271 (50 Hz)	75 V...126 V (115 V)	36/36 W (0.35/0.32 A)	53/57 dB (A)	268 x 248 x 116 (223 x 223)	1.3	-10…+70 °C	158 Pa	Pre-fuse T 4A
262	221	229	12 V...30 V (24 V DC)	13 W (0.53 A)	53/57 dB (A)	268 x 248 x 103.4 (223 x 223)	1.1	-10...+ 70 °C	158 Pa	Pre-fuse T 2A
247	210	218	25 V...60 V (48 V DC)	11 W (0.24 A)	53/57 dB (A)	268 x 248 x 103.4 (223 x 223)	1.1	-10…+70 °C	158 Pa	Pre-fuse T 2A
562 (50 Hz) 586 (60 Hz)	473 (50 Hz) 477 (60 Hz)	481 (50 Hz)	207 V...244 V (230 V)	64/80 W (0.29/0.35 A)	59/59 dB (A)	336 x 316 x 161 (291 x 291)	3.2	-15…+60 °C	140 Pa	Pre-fuse T 4A
582 (50 Hz) 586 (60 Hz)	485 (50 Hz) 477 (60 Hz)	494 (50 Hz)	103 V...122 V (115 V)	65/83 W (0.60/0.72 A)	59/59 dB (A)	336 x 316 x 161 (291 x 291)	3.2	-15…+60 °C	140 Pa	Pre-fuse T 6A
838 (50 Hz) 803 (60 Hz)	718 (50 Hz) 568 (60 Hz)	728 (50 Hz)	207 V...244 V (230 V)	150/195 W (0.65/0.85 A)	76/75 dB (A)	336 x 316 x 162 (291 x 291)	4.1	-15…+60 °C	170 Pa	Pre-fuse T 4A
983 (50 Hz) 944 (60 Hz)	843 (50 Hz) 642 (60 Hz)	854 (50 Hz)	103 V...122 V (115 V)	145/182 W (1.279/1.6 A)	78/77 dB (A)	336 x 316 x 162 (291 x 291)	4.1	-15…+60 °C	170 Pa	Pre-fuse T 6A
931 (50 Hz) 803 (60 Hz)	798 (50 Hz) 568 (60 Hz)	809 (50 Hz)	400 V (0, +10%)	126/126 W (0.21/0.26 A)	77/75 dB (A)	336 x 316 x 162 (291 x 291)	4.1	-15…+60 °C	170 Pa	Motor circuit-breaker

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.











by cable ★ Forced-airing fan 38 m³/h	by faston (1) Forced-airing fan 85 m³/h	by faston (1) Forced-airing fan 165 m³/h	by faston (1) Forced-airing fan 300 m³/h	by terminal block Forced-airing fan 560-850 m³/h
NSYCVF38M230PF ★	-	-	-	-
NSYCVF38M115PF ★	-	-	-	-
NSYCVF38M24DPF	-	-	-	-
NSYCVF38M48DPF	-	-	-	-
-	**NSYCVF85M230PF** (2)	-	-	-
-	**NSYCVF85M115PF** (2)	-	-	-
NSYCVF85M24DPF (2)	-	-	-	-
-	**NSYCVF85M48DPF** (2)	-	-	-
-	-	**NSYCVF165M230PF** (2)	-	-
-	-	**NSYCVF165M115PF** (2)	-	-
NSYCVF165M24DPF (2)	-	-	-	-
-	-	**NSYCVF165M48DPF** (2)	-	-
-	-	-	**NSYCVF300M230PF** (2)	-
-	-	-	**NSYCVF300M115PF** (2)	-
NSYCVF300M24DPF (2)	-	-	-	-
-	-	-	**NSYCVF300M48DPF** (2)	-
-	-	-	-	**NSYCVF560M230PF** (2)
-	-	-	-	**NSYCVF560M115PF** (2)
-	-	-	-	**NSYCVF850M230PF**
-	-	-	-	**NSYCVF850M115PF**
-	-	-	-	**NSYCVF850M400PF** (2)

(1) Fan models with connection are delivered with the connection cord included (2 metres).
(2) CSA compliant.

Note: The fan **NSYCVF38M230PF** and **NSYCVF38M115PF** MUST NOT be connected to a power conversion module, an inverter or UPS!

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


ClimaSys CV: Forced Airing


Ventilation


Fans


NSYCVF65M115PF

- Two models according to the input voltage: 230 and 115 V, 50-60 Hz.
- Ingress protection rating: IP20 according to IEC 60529.
- Options: IP20 outlet grille (ABS, black) and filter (black polyurethane foam).
- UL (cURus). Rated 12 according to UL50E.
- With 1 outlet kit (grille and filter), 1 rear grille, 1 fan motor NSYCVF156M•••, 4 fixing screws.








Characteristics	Free air flow (m³/h)	Air flow with fan and outlet grilles and filters (m³/h)	Voltage (V)	References
Fan	170	Fan: 65	115	**NSYCVF65M115PF**
Fan	170	Fan: 65	230	**NSYCVF65M230PF**


EMC IP54 Fan


- To effectively help protect the equipment against electromagnetic interference, the EMC fan is equipped with:
  - a steel frame covering the plastic elements (self-extinguishing ABS according to standard UL94 V0),
  - a metal grille attached to the frame,
  - a beryllium gasket to help ensure conductivity between the perimeter of the fan unit and the enclosure.
- Color: RAL 7035 gray.
- Ingress protection rating (according to IEC 60529): IP54.


NSY17990

Characteristics	Flow rate (m³/h)	Voltage (V)	Dimensions (mm)		References
			External	Cut-out	
EMC IP54 fan	61	230	145 x 145 x 70	126 x 126	**NSY17990**
EMC IP54 fan	156	230	252 x 252 x 97	224 x 224	**NSY17991**
EMC IP54 fan	480	230	320 x 320 x 150	292 x 292	**NSY17992**







Fan Accessories



NSYCAG108LP

Characteristics	Dimensions External (mm)	References
Outlet grille	124 x 124 x 11	**NSYCAG108LP**
Filter	124 x 124	**NSYCAF108**

Airing Kit


NSYCVF54M230MM2

- Ingress protection rating: IP33 according to IEC 60529.
- Mechanical protection rating: IK10 according to IEC 62262.
- Overall flow rate: 54 m³/h.



Supply:
- One 120 x 120 x 38 mm fan, 230 V - 50/60 Hz, free flow rate 170 m³/h,
- Two 120 x 120 mm metal grilles, RAL 7035 gray,
- Two 115 x 98 mm anti-insect filters, stainless-steel 304L cable Ø 0.32 mm braided,
- 1.07 mm meshes,
- 1 power cord,
- The fixings required for installation.

Characteristics	Flow rate (m³/h)	Voltage (V)	References
Airing kit	54	230	**NSYCVF54M230MM2**

Top Hood with Fan and Cover


NSYCVF570M115MF

- Ingress protection rating: IP54 according to IEC 60529.
- Color: RAL 7035 gray.
- Installation: Installation and removal from the outside.
- Electric power: 85 W.
- Noise level: 64 dB (A).


Comment:
Flow rate measured without counter-pressure.

Supply:
Delivered with fixings and connection terminal block.

Characteristics	Weight (kg)	Flow rate (m³/h)	Voltage (V)	References
Top hood with fan and cover	5.8	570	115	**NSYCVF570M115MF**
Top hood with fan and cover	5.8	575	230	**NSYCVF575M230MF**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Fan Motor





NSYCVF156M230 NSYCVF156M115

- Turbine-type fan motor for airing/extraction.

Characteristics	Flow rate (m³/h)	Voltage (V/Hz)	Absorbed power (W)	Noise level (dB (A))	External dimensions (mm)	References
Fan motor	156	230/50-60	17/15	42	120 x 120 x 38	**NSYCVF156M230**
Fan motor	156	115/50-60	17/15	42	120 x 120 x 38	**NSYCVF156M115**
Fan motor	35	230/50-60	16/14	32	80 x 80 x 25	**NSYCVF35M230**
Fan motor	35	115/50-60	16/14	32	80 x 80 x 25	**NSYCVF35M115**

Outlet Grille




NSYCAG114LPF

- Outlet filter kit for enclosure airing.
- For coupling to fans use **NSYCVF156M●●●** and **NSYCVF35M●●●**.

Characteristics	External dimensions (mm)	References
Outlet grille	120 x 120 x 38	**NSYCAG114LPF**
Outlet grille	80 x 80 x 25	**NSYCAG78LPF**

Rear Protective Grille



NSYCVA114M

- Protective grille for enclosure fan motor.
- For coupling to fans use **NSYCVF156M●●●** and **NSYCVF35M●●●**.

Characteristics	External dimensions (mm)	References
Rear protective grille	120 x 120 x 38	**NSYCVA114M**

5

Fan Connection Cable



NSYCVAC200

- For coupling to the connection terminal of the fan motors.

Characteristics	References
Fan connection cable, length = 2 m	**NSYCVAC200**

Air Circulation for Internal Forced Convection
Circulation Fan



PB501067_53_nb

User protection according to DIN 31001.
Dimensions:
- Fan: 119 x 119 x 38 mm.
- Collar: Length: 140 mm; Fixing center-to-center distance: 130 mm.
- Motor mounted on ball bearing.


Comment:
(1) Free flow.

Characteristics	Flow rate (m³/h) (1)	Voltage (V)	Weight. (kg)	P (W)	dB (A)	References
Circulation fan	170	115	0.82	17	41	**NSYCVF170M115**
Circulation fan	170	230	0.82	17	41	**NSYCVF170M230**

Anti-Vandalism Kit



NSYCAAPV



- Helps prevent the grid from being opened from the outside.
- The unlocking thumbwheel is accessed from the inside of the enclosure.
- Color: RAL 7011.

Supply:
2 items per kit

Characteristics	References
Anti-vandalism kit	**NSYCAAPV**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Forced Airing

Accessories

Filters

Supply:
- G2 M1 synthetic standard filters, Filters for greasy environments G2 M1, G3 M1 synthetic fine filters: 5 units
- Stainless-steel anti-insect filters: 1 unit

- For fans and grilles.
- Filters according to ISO 16890.



NSYCAF223T

Characteristics	Height (mm)	Width (mm)	Cut-out (mm)	References
G2 M1 synthetic standard filters	137	117	92 x 92	**NSYCAF92**
G2 M1 synthetic standard filters	170	150	125 x 125	**NSYCAF125**
G2 M1 synthetic standard filters	268	248	223 x 223	**NSYCAF223**
G2 M1 synthetic standard filters	336	316	291 x 291	**NSYCAF291**
Filters for greasy environments G2 M1	170	150	125 x 125	**NSYCAF125O**
Filters for greasy environments G2 M1	268	248	223 x 223	**NSYCAF223O**
Filters for greasy environments G2 M1	336	316	291 x 291	**NSYCAF291O**
G3 M1 synthetic fine filters	170	150	125 x 125	**NSYCAF125T**
G3 M1 synthetic fine filters	268	248	223 x 223	**NSYCAF223T**
G3 M1 synthetic fine filters	336	316	291 x 291	**NSYCAF291T**
Stainless-steel anti-insect filters	137	117	92 x 92	**NSYCAF92M**
Stainless-steel anti-insect filters	170	150	125 x 125	**NSYCAF125M**
Stainless-steel anti-insect filters	268	248	223 x 223	**NSYCAF223M**
Stainless-steel anti-insect filters	336	316	291 x 291	**NSYCAF291M**

Covers IP55

(1) Values given for a fan powered at 230 V. For other voltages, the values are similar

- This solution helps protect the fan or grille from any direct spray.
- The cover is the preferred solution to help ensure the following:
  - an efficient air flow for cooling,
  - IP55 rating.
- Material: 2 materials available:
  - steel painted with epoxy polyester powder (RAL 7035 gray) for indoor applications,
  - stainless-steel 304L for food and beverage applications for indoor applications. For outdoor applications please contact Schneider sales team or use the reference **NSYCAG223LFHD**.
- Ingress protection rating (according to IEC 60529): IP55.
- Mechanical protection rating (according to IEC 62262): IK10.
- Certifications: UL Recognized (cURus). Rated 12 and 3R according to UL 50E.
- Installation: Double insulation maintained if installed in an insulated enclosure. The cover is placed over the fan or the grille with a filter located at the bottom of the cover to help prevent the entry of particles. Easy access to the filter: Only two screws needed. When mounting: Remove the external part of the fan or the grille as well as the filter.



Supply:
It is necessary to order 1 fan + 1 grille + 2 covers to have a complete system


NSYCAP125LZF

Characteristics	Flow rate (m³/h) with cover (1)		Dimensions (mm)		References
	Free	With 1 outlet grille	External	Cut-out	
Steel painted RAL 7035 gray	74	53	240 x 180 x 60	125 x 125	**NSYCAP125LZF** (1)
Steel painted RAL 7035 gray	110	82	350 x 305 x 80	223 x 223	**NSYCAP223LZF** (1)
Steel painted RAL 7035 gray	165	123	350 x 305 x 80	223 x 223	**NSYCAP223LZF** (1)
Steel painted RAL 7035 gray	316	265	430 x 373 x 105	291 x 291	**NSYCAP291LZF** (1)
Steel painted RAL 7035 gray	502	430	430 x 373 x 105	291 x 291	**NSYCAP291LZF** (1)
Stainless-steel 304L	74	53	240 x 180 x 60	125 x 125	**NSYCAP125LXF** (1)
Stainless-steel 304L	110	82	350 x 305 x 80	223 x 223	**NSYCAP223LXF** (1)
Stainless-steel 304L	165	123	350 x 305 x 80	223 x 223	**NSYCAP223LXF** (1)
Stainless-steel 304L	316	265	430 x 373 x 105	291 x 291	**NSYCAP291LXF** (1)
Stainless-steel 304L	502	430	430 x 373 x 105	291 x 291	**NSYCAP291LXF** (1)

(1) CSA compliant.

Spare Filter for Cover


Supply:
5 items per kit


NSYCAF125L55

Characteristics	Flow rate (m³/h) with cover (1)		Cover references	References
	Free	With 1 outlet grille		
Spare filter for cover	74	53	**NSYCAP125LZF**	**NSYCAF125L55**
Spare filter for cover	110	82	**NSYCAP223LZF**	**NSYCAF223L55**
Spare filter for cover	165	123	**NSYCAP223LZF**	**NSYCAF223L55**
Spare filter for cover	316	265	**NSYCAP291LZF**	**NSYCAF291L55**
Spare filter for cover	502	430	**NSYCAP291LZF**	**NSYCAF291L55**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

EMC IP55 Cover




- This solution provides protection against electromagnetic interference and helps ensure IP55 ingress protection.
- The EMC cover is installed on the fans or standard IP54 outlet grilles.
- The cover is made of painted steel for outdoor use and completely covers the fan or outlet grille.
- Conductivity is obtained by means of:
  - a conductive painting (2 Ω),
  - a conductive copper braid.
- Color: RAL 7035 gray.
- Ingress protection rating (according to IEC 60529): IP55.
- Mechanical protection rating (according to IEC 62262): IK10.

(1) Values given for a fan powered at 230 V. For other voltages, the values are similar



NSYCAP125LE

Characteristics	Flow rate (m³/h) with cover (1)		Dimensions (mm)		References
	Free	With 1 outlet grille	External	Cut-out	
Sheet steel painted for outdoor applications, RAL 7035 gray	74	53	240 x 180 x 60	125 x 125	**NSYCAP125LE**
Sheet steel painted for outdoor applications, RAL 7035 gray	110	82	350 x 305 x 80	223 x 223	**NSYCAP223LE**
Sheet steel painted for outdoor applications, RAL 7035 gray	165	123	350 x 305 x 80	223 x 223	**NSYCAP223LE**
Sheet steel painted for outdoor applications, RAL 7035 gray	316	265	430 x 373 x 105	291 x 291	**NSYCAP291LE**
Sheet steel painted for outdoor applications, RAL 7035 gray	502	430	430 x 373 x 105	291 x 291	**NSYCAP291LE**



Dimensions (mm)							Number of fixing points	Cover references		
A	B	C	D	E	F	G		IP55		EMC
180	240	49	49	49	157	182	4	**NSYCAP125LZF**	**NSYCAP125LXF**	**NSYCAP125LE**
305	350	61	61	61	283	280	8	**NSYCAP223LZF**	**NSYCAP223LXF**	**NSYCAP223LE**
373	430	73	73	73	351	348	8	**NSYCAP291LZF**	**NSYCAP291LXF**	**NSYCAP291LE**

Spare Filter for Cover

(1) Values given for a fan powered at 230 V. For other voltages, the values are similar.

Supply:
5 items per kit.





NSYCAF125L55

Characteristics	Flow rate (m³/h) with cover (1)		Cover references	References
	Free	With 1 outlet grille		
Spare filter for cover	74	53	**NSYCAP125LE**	**NSYCAF125L55**
Spare filter for cover	110	82	**NSYCAP223LE**	**NSYCAF223L55**
Spare filter for cover	165	123	**NSYCAP223LE**	**NSYCAF223L55**
Spare filter for cover	316	265	**NSYCAP291LE**	**NSYCAF291L55**
Spare filter for cover	502	430	**NSYCAP291LE**	**NSYCAF291L55**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Airing System for Heavy Duty

Specific Solutions

	S-Line	T-Line
	 1 IP55 metal grille 2 Fanbox	 2 Fanbox 3 Roof airing module
Architecture benefits	• Most common and competitive architecture • Maximum heat dissipation to extract 800 W-1000 W • ΔT° of 5 °C • Easy access to mount-dismount fanbox • Air flow in horizontal axis	• High thermal extraction capacity up to 1500 W • Noise level with 1 fan: 55 dB (A) when installed inside the upper airing module • ΔT° of 5 °C • Air flow in vertical axis

	IP55 metal grille		Fanbox		IP55 metal grille		Fanbox (1 filter NSYCAF190 for each Fanbox)	Roof airing module	
	Door	Side	Door	Side	Door	Side			
Polyester outdoor HD enclosure									
References	**Quantity to be installed**				**Quantity to be installed**				**References**
NSYPHDT553P	-	-	-	-	-	-	-	-	-
NSYPHDT753P	1 to 2	-	1 to 2	-	1 to 2	-	-	-	-
NSYPHDZT774	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT774P	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT776	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT776P	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT1054	-	1	-	1	-	1	1	1	**NSYPCVR54HD** (1)
NSYPHDZT1054P	1 to 2	1	1 to 2	1	1 to 2	1	1	1	**NSYPCVR54HD** (1)
NSYPHDZT1074	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT1074P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT12124	-	1 to 3	-	1 to 3	-	1 to 3	1 to 3	1	**NSYPCVR124HD** (1)
NSYPHDZT12124P	1 to 4	1 to 3	1 to 4	1 to 3	1 to 4	1 to 3	1 to 3	1	**NSYPCVR124HD** (1)
NSYPHDZT12126	-	1 to 3	-	1 to 3	-	1 to 3	1 to 3	1	**NSYPCVR126HD** (1)
NSYPHDZT12126P	1 to 4	1 to 3	1 to 4	1 to 3	1 to 4	1 to 3	1 to 3	1	**NSYPCVR126HD** (1)
NSYPHDZT1254	-	1	-	1	-	1	1	1	**NSYPCVR54HD** (1)
NSYPHDZT1254P	1 to 3	1	1 to 3	1	1 to 3	1	1	1	**NSYPCVR54HD** (1)
NSYPHDZT1274	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT1274P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT1276	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT1276P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT15124	-	1 to 3	-	1 to 3	-	1 to 3	1 to 3	1	**NSYPCVR124HD** (1)
NSYPHDZT15124P	1 to 4	1 to 3	1 to 4	1 to 3	1 to 4	1 to 3	1 to 3	1	**NSYPCVR124HD** (1)
NSYPHDZT15126	-	1 to 3	-	1 to 3	-	1 to 3	1 to 3	1	**NSYPCVR126HD** (1)
NSYPHDZT15126P	1 to 4	1 to 3	1 to 4	1 to 3	1 to 4	1 to 3	1 to 3	1	**NSYPCVR126HD** (1)
NSYPHDZT1574	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT1574P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT1576	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT1576P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR76HD** (1)
NSYPHDZT2074	-	1 to 2	-	1 to 2	-	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
NSYPHDZT2074P	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	**NSYPCVR74HD** (1)
Steel outdoor HD enclosure									
NSYS3HD8630	1 to 2	-	1 to 2	-	1 to 2	-	-	-	-
NSYS3HD8840	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1	-
NSYS3HD10640	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1 to 2	1	1	-
NSYS3HD10840	1 to 4	1 to 2	1 to 4	1 to 2	1 to 4	1 to 2	1 to 2	1	-
NSYSFNHD18640	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR64HD**
NSYSFNHD18840	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR84HD**
NSYSFNHD18860	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR86HD**
NSYSFNHD18880	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR88HD**
NSYSFNHD20660	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR66HD**
NSYSFNHD20840	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR84HD**
NSYSFNHD20860	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 4	1 to 2	-	**NSYSFNCVR86HD**


(1) CSA compliant.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Airing System for Heavy Duty

Specific Solutions

I-Line



2 Fanbox
3 Roof airing module
4 Ventilated plinths
5 IP54 grille

This table helps to configure thermal architectures, but it is highly recommended to use the ProClima Software to help ensure the right thermal solution according to the selected architecture.

- Integrated architecture particularly suitable for public areas
- High thermal extraction of calorific energy up to 1500 W
- Noise level with 1 fan: 55 dB (A) when installed inside the upper airing module
- High flow rate and extraction performance
- Air flow in vertical axis

IP54 outlet grille (NSYCAG223LPF + G3 filter NSYCAF223T)		Ventilated plinths		Fanbox (1 filter NSYCAF190 for each Fanbox)		Roof airing module
Quantity to be installed		References		Quantity to be installed		References
-	-	-	-	-	-	-
-	-	-	-	-	-	-
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1	-	-	-	1	1	**NSYPCVR54HD** (1)
1	-	-	-	1	1	**NSYPCVR54HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR124HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR124HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR126HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR126HD** (1)
1	-	-	-	1	1	**NSYPCVR54HD** (1)
1	-	-	-	1	1	**NSYPCVR54HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR124HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR124HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR126HD** (1)
1 to 3	-	-	-	1 to 3	1	**NSYPCVR126HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR76HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1 to 2	-	-	-	1 to 2	1	**NSYPCVR74HD** (1)
1	1	**NSYSPFVX6200**	**NSYSPSX3200**	-	-	-
1 to 2	1	**NSYSPFVX8200**	-	1 to 2	1	-
1	1	**NSYSPFVX6200**	-	1	1	-
1	1	**NSYSPFVX8200**	-	1 to 2	1	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Airing System for Heavy Duty

Specific Solutions

Fanbox


NSYCVF550M24FB



- Free flow rate: 550 m3/h (50/60 Hz).
- UL Recognized (cURus). Rated Type 12.
- Minimal depth inside the enclosure (90 mm).
- Allows multiple cooling architectures (**see page 406 and 407**).
- Material: polyamide.
- Color: RAL 7016 dark gray.


Supply:
1 (grille not included)

Characteristics	Voltage	References
Fanbox	24 V DC	**NSYCVF550M24FB** (1)
Fanbox	115 V AC	**NSYCVF550M115FB** (1)
Fanbox	230 V AC	**NSYCVF550M230FB** (1)

(1) CSA compliant.

IP55 HD Metal Grille


NSYCAG223LFHD



- Slim grille (35 mm external depth).
- UL Recognized (cURus). Rated Type 12 according UL 50e.
- Includes a G3 M1.
- Material: Steel with anti-corrosive painting + plastic PA6 / GF25 for fixing frame.
- Finish: Structured finish, 100% polyester powder.
- Color: RAL 7035 gray.
- Ingress protection rating: IP55 according to IEC 60529.
- Mechanical protection rating: IK10 according to IEC 62262.

Supply:
1 grille delivered with G3 M1 type synthetic filter (215 x 215 mm) and fixings

Characteristics	References
IP55 HD Metal Grille	**NSYCAG223LFHD** (1)

(1) CSA compliant.

Roof Filter for Fanbox (Extraction Mode)

NSYCAF190

- Roof G2 round synthetic filter designed to cover the fanbox. Covers completely the fanbox to help protect it from dust and humidity. Mandatory for fanbox installation in the roof airing module for IP55 configurations.
- Material: 100% polyester fibers.
- Color: White.

Supply:
1

Characteristics	References
IP55 HD Metal Grille	**NSYCAG223LFHD**

Filter


NSYCAF223T

- Replacement G3 M1-type synthetic filter for HD metal grille.
- Dimensions: 215 x 215 mm.
- Material: 100% polyester fibers.
- Color: White.

Supply:
5

Characteristics	Height (mm)	Width (mm)	Depth (mm)	Cut-out (mm)	References
G3 M1 synthetic fine filters	268	248	18	223 x 223	**NSYCAF223T**

Anti-Vandalism Kit for HD Metal Grille


• NSYCAAPVHD

Comment:
Not compatible with **NSYSPLA150**

- Fixings that help to prevent to open the grille from the outside with standard tools (EN 1627-1630:2011 Class 2).
- Quick installation without tools.
- Material: Steel with anticorrosive painting + plastic for fixing screws.

Supply:
4 grip knob
4 clip nuts

Characteristics	References
Anti-vandalism kit for HD metal grille	**NSYCAAPVHD**

Note: Accessories mounted outside of the enclosure.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Smart Ventilation System

Specific Solutions

Concept of the ClimaSys Smart Ventilation System (CSVS)

PB503602_43_nb



> Use Corrective and Predictive Maintenance of the Airing System to:
- Improve CAPEX and OPEX of the installation.
- Improve maintenance and operation of the installation.
- Improve peace of mind.

Reduce maintenance cost for new and existing installations.

> Functions of the CSVS Systems:

Detect general poor health of the enclosure by monitoring:
- Input/output temperature.

Detect fan issues by monitoring:
- Air flow temperature.
- Current level, consumed energy.
- Blade speed measurement.
- Used and remaining (approximate) lifespan.

Detect grid filter issues:
- Air flow temperature.
- Dust level (0% clean – 100% dirty).
- Number of replacements.
- Remaining time to next replacement.

5

The Technical Solution

2 sensors connected to a controller relaying Information and alarms

PB503557_30_nb



Dust sensor (patented)

Composed of an optical sensor which detects the filter dirt level + temperature sensor

PB503552_30_nb



Fan Sensor

Composed of:
RPM sensor to control fan rotation and transported air temperature Toroidal sensor to measure fan consumption

Filterstat™ Controller ClimaSys CC DG

PB503542_30_nb



Information displayed on Filterstat's controller display

- **Detect general poor health of enclosure by monitoring:**
  - Input/output temperature.
- **Detect fan issues by monitoring:**
  - Air flow temperature
  - Current level, consumed energy
  - Blade speed measurement
  - Used and remaining (approximate) lifespan.
- **Detect grid filter issues:**
  - Air flow temperature
  - Dust level (0% clean – 100% dirty)
  - Number of replacements
  - Remaining time before next replacement.

The alarms
The system offers different types of alarms for notification when something is not right:
- **Dust filter alarm:** Filter capacity below user-defined level. 0%-60% (LED green), 60%-80% (LED orange), > 80% (LED flashing red)
- **No power supply to fan:** Fan is running (there is an rpm reading but the current sensor shows a 0 mA reading).
- **Fan rpm slow:** Fan speed is below a user-predefined level.
- **Fan flaps blocked:** Consumption in a fan is detected but the rpm speed is zero.
- **Over-temperature alarm on airflow:** Fan exceeds a user-defined threshold.
- **Over-temperature or under-temperature alarm:** On inlet or outlet air from grids.
- **Fan lifespan over:** The fan lifetime has almost expired and it should be replaced (front LEDs light up purple).
- **Δt deviation:** Δt deviation is greater that a user-predefined threshold.
- **Remote sensor not connected/broken:** A device in the network is disconnected.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Smart Ventilation System

Specific Solutions

1 Select Your Smart Fan

PB503599_19_nb



PB503516_13_nb



PB503562_14_nb



See details page 412

2 Select Your Smart Grid

PB503516_13_nb



PB503569_15_nb



See details page 414

ClimaSys Smart Grid Offer

Complete Smart Grid that includes:

- A dust Sensor.
- A smart Filter G2, G3 smart filter to be order separately (**See** page 405).

3 Select Your Controller and Potential Thermal Hubs to Digitalize More Than 1 Enclosure

NSYCCOFSTB0250V



NSYCCOFSEM8U2



Filterstat Controllers (4 Ports) and Thermal Hubs (8 Ports)

NSYCCOFR55



Modular frame IP55

See details page 414

4 Select Your Communication Cables

NSYCCA50MFST



Filterstat Communication Cable


Black unshielded cable with 2 connectors on each end.
Material: PVC.

See details page 414

Note: Control devices (thermostat, hygrostat, hygrotherm) must be ordered separately.

Thermal Network Architecture

PB503530_104_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Smart Ventilation System

Specific Solutions

- Characteristics: The Smart fans are equipped with an axial motor, a protective housing on the front, rear surfaces, and a Smart filter with Dust sensor and a Fan sensor with infrared technology. The external smokey-colored grid displays the status of the airing functions through the LED colors of the Dust sensor. This Smart filter can be replaced for maintenance during operation without risk of contact with the rotating element.
- Material of external grids: Injected thermoplastic (ASA PC). self-extinguishing according to UL 94 V-0.
- Color of external grids: Smokey black RAL 9005
- Conditions of use: The external temperature must not exceed 30 °C and must be more than 5 °C lower than the temperature required in the enclosure. The Smart filters that equip the Smart fans must be replaced when the alarm is triggered by the Filterstat controller (see more details page 410)
  Storage Temperature: -40…+ 70 °C
- Ingress protection rating (according to IEC 60529): IP54
- If the enclosure contains electronics, material sensitive to dust deposits or if it is needed to use several fans and grills in the same enclosure, we highly recommend using ProClima and a solution with better filtering using a G3 filter or a higher IP (cooling option as example). In any case, do not hesitate to contact our sales teams to collaborate on your project.
- Mechanical protection rating (according to IEC 62262): IK08
- Installation: The cut-out template supplied with the device avoids the need for marking and helps protect the surface of the enclosure during handling.
- Options: For maintenance replacement of Smart filters please see spare parts references, page 405

Free flow rate with standard filter (m^3/h)	Flow rate with outlet grille(s) (m^3/h)		Voltage range (nominal voltage)	Absorbed power (max. intensity)	Noise level	External dimensions (cut-out)	Weight	Operating temperature	Max. static pressure
	1	2							
34 (50 Hz) 35 (60 Hz)	21 (50 Hz) 22 (60 Hz)	29 (50 Hz)	150 V...250 V (230 V)	4.5/4.8 W (0.16/0.17 A)	40/41 dB (A)	137 x 117 x 49 (92 x 92)	0.220 kg	-10...+ 70 °C	29 Pa
74 (50 Hz) 87 (60 Hz)	52 (50 Hz) 61 (60 Hz)	60 (50 Hz)	175 V...253 V (230 V)	17/15 W (0.121/0.097 A)	46/49 dB (A)	170 x 150 x 62 (125)	0.780 kg	-20…+60 °C	50 Pa
142 (50 Hz) 170 (60 Hz)	130 (50 Hz) 151 (60 Hz)	138 (50 Hz) 152 (60 Hz)	175 V...253 V (230 V)	16.3/14.3 W (0.12/0.94 A)	50/51 dB (A)	268 x 248 x 104 (223 x 223)	1.140 kg	-20…+60 °C	50 Pa
259 (50 Hz) 307 (60 Hz)	209 (50 Hz) 251 (60 Hz)	218 (50 Hz)	145 V...253 V (230 V)	36/37 W (0.17/0.16 A)	55/56 dB (A)	268 x 248 x 116 (223 x 223)	1.3 kg	-10...+ 70 °C	158 Pa
502 (50 Hz) 526 (60 Hz)	412 (50 Hz) 448 (60 Hz)	420 (50 Hz)	207 V...244 V (230 V)	64/80W (0.29/0.35 A)	59/59 dB (A)	336 x 316 x 161 (291 x 291)	3.2 kg	-15…+60 °C	140 Pa
638 (50 Hz) 603 (60 Hz)	500 (50 Hz) 462 (60 Hz)	528 (50 Hz)	207 V...244 V (230 V)	150/195 W (0.65/0.85 A)	76/75 dB (A)	336 x 316 x 162 (291 x 291)	4.1 kg	-15…+60 °C	170 Pa
731 (50 Hz) 603 (60 Hz)	598 (50 Hz) 368 (60 Hz)	609 (50 Hz)	396 V...466 V (400 V)	126/126 W (0.226/0.232 A)	77/75 dB (A)	336 x 316 x 162 (291 x 291)	4.1 kg	-15…+60 °C	170 Pa

How to Identify Whether Your ClimaSys CV Fan Has Been Upgraded to Install the CSVS Solution

Your installation				Installation of CSVS solution	
Greenfield					
	**NSYCV•••DG**	Schneider Electric	>	It's possible to install the CSVS solution	
Brownfield					
	**NSYCV•••LPF**	Schneider Electric	>	It's possible to install the CSVS solution	

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Smart Ventilation System

Specific Solutions





	by cable ✶ Forced-airing fan 38 m³/h	by faston (1) Forced-airing fan 85 m³/h	by faston (1) Forced-airing fan 165 m³/h	by faston (1) Forced-airing fan 300 m³/h	by terminal block Forced-airing fan 560-850 m³/h
	NSYCVF38M230DG	-	-	-	-
	-	**NSYCVF85M230DG**	-	-	-
	-	-	**NSYCVF165M230DG**	-	-
	-	-	-	**NSYCVF300M230DG**	-
	-	-	-	-	**NSYCVF560M230DG**
	-	-	-	-	**NSYCVF850M230DG**
	-	-	-	-	**NSYCVF850M400DG**

(1) Fan models with connection are delivered with the connection cord included (2 meters).

Note: The fan **NSYCVF38M230DG** MUST NOT be connected to a power conversion module, an inverter or UPS!

High-Visibility LED Indicators



Dust filter alarm 0%-60%



Dust filter alarm 60%-80%



Dust filter alarm >80%



Fan lifespan exhausted



PING function Identification of the sensor on the panel (flashing blue color)

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CV: Smart Ventilation System

Specific Solutions

Filterstat Controllers (4 Ports) and Thermal Hubs (8 Ports)


NSYCCOFST30V

- Trim frame IP55 for installing the Filterstat Controller and thermal hub on enclosure doors, side panels etc.

Characteristics	Voltage	References
Filterstat Controllers	30 V AC/DC	**NSYCCOFST30V**
Filterstat Controllers	90-250 V AC	**NSYCCOFST90250V**


NSYCCOFSEM8U2

Characteristics	Voltage	References
Thermal Hub	90-250 V AC	**NSYCCOFSEM8U2**

Modular frame IP55


NSYCCOFR55

Characteristics	References
Modular frame	**NSYCCOFR55**

Filterstat Communication Cable


NSYCCA500MFST

- Black unshielded cable with 2 connectors on each side.
- Material: PVC.

Characteristics	References
Filterstat communication cable	**NSYCCA500MFST**

Smart Grid Systems
Complete Smart Grids


NSYCAG92DG

- A Dust Sensor.
- A SmartFilter G2.
- Material: Injected thermoplastic (PC), self-extinguishing according to UL 94 V-0.
- Color: Smokey black RAL 9005.
- Ingress protection rating (according to IEC 60529): IP54.

Characteristics	Height (mm)	Width (mm)	Depth (mm)	Cut-out (mm)	References
Complete Smart Grid	137	117	13	92 x 92	**NSYCAG92DG**
Complete Smart Grid	170	150	15	125 x 125	**NSYCAG125DG**
Complete Smart Grid	268	248	18	223 x 223	**NSYCAG223DG**
Complete Smart Grid	336	316	18	291 x 291	**NSYCAG291DG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Smart Filters



NSYCAF92DG

- Set of 5 Smart filters for replacement on Smart Fans and Smart Grids. For fans and grilles.
- Material: Polyester.
- Filters according to ISO 16890.
- Color: White with green lettering.

Characteristics	Height (mm)	Width (mm)	Cut-out (mm)	References
External Smart Grid, G2 M1 filters	137	117	92 x 92	**NSYCAF92DG**
External Smart Grid, G2 M1 filters	170	150	125 x 125	**NSYCAF125DG**
External Smart Grid, G2 M1 filters	268	248	223 x 223	**NSYCAF223DG**
External Smart Grid, G2 M1 filters	336	316	291 x 291	**NSYCAF291DG**

Dust Sensor



NSYCCAFSDUST

- Individual Dust Sensor ready to be implemented on any existing ClimaSys CV fan or ClimaSys CA grids in the Brownfield installation or used as spare part.

Characteristics	References
Dust Sensor	**NSYCCAFSDUST**

Fan Sensor



NSYCCARPM


- Individual Fan Sensor ready to be implemented on any existing fan in the Brownfield installation or used as spare part.

Characteristics	References
Fan Sensor	**NSYCCARPM**

Anti-Vandalism Kit



NSYCAAPV



- Helps prevent the grid from being opened from the outside.
- The unlocking thumbwheel is accessed from the inside of the enclosure.
- Color: RAL 7011.

Supply:
Minor packaging 2


Characteristics	References
Anti-vandalism kit	**NSYCAAPV**


5

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CRS: Ultra Thin Heaters


Introduction





Ultra-thin resistance heaters have been designed to resolve condensation problems in the most complex installations.
Is your enclosure short of space?
Does your mounting plate make it impossible to install a conventional heater?
Do you not want to take out the equipment?
Discover the benefits of this offer and its numerous mounting solutions.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.



Small Size (Thickness = 1.6 mm)

- The space saving available for the equipment compared with a conventional resistor can be up to 30%



Heat and Safety

- The heat is distributed over the whole surface and does not exceed 70 °C. This temperature helps reduce the risk of contact with hot surfaces on devices installed next to the heater



Multiple Options for Fixing

- Innovative quick-fixing system using Velcro pads (no need for a tool!) or with basic fixing accessories (screw + spacer). These systems make it easy to move the heater if necessary



Numerous Positions for Installation

- These heaters are so slim and flexible they can be installed in a variety of positions:
  - Vertically on side panels
  - On the mounting plate



Energy Efficiency

- Ultra-thin resistance heaters have a low starting current



No Electromagnetic Emissions


- These resistors can be installed near electronic equipment to help ensure an optimal temperature

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.






ClimaSys CRS: Ultra Thin Heaters

Characteristics and Selection Guide

Other Characteristics - Electrical Circuit Diagram



Electrical Circuit Diagram

					
5 mounting solutions:	On a Telequick mounting plate	On plain or micro-perforated mounting plate with fixing hardware	On DIN rail	On plain mounting plate with self-adhesive Velcro pads	On wall with self-adhesive Velcro pads
	A Telequick mounting plate, ref. **NSYMR●●●●** B Telequick nuts, ref. **AF1EA●**, supplied with the mounting kit	A Mounting plate, ref. **NSYMM●●●●** B Fixing hardware included in the mounting kit	A Mounting plate, ref. **NSYMM●●●●** B Symmetrical DIN rail, ref. **NSYSDR●●●●** C Clip-on nuts, ref. **AF1CG●**, supplied with the mounting kit	A Mounting plate, ref. **NSYMM●●●●** B Self-adhesive Velcro pad and plastic fixings supplied with the mounting kit	A Self-adhesive Velcro pads and plastic fixings supplied in the mounting kit

Characteristics

	Flexible, ultra-thin resistance heaters to be installed inside the enclosure
Material	Silicon reinforced with fiberglass
Color	Red (heaters), black (cables)
Certification	**UL**
Supply	• 6 self-adhesive Velcro pads • 6 plastic fixings • 4 Telequick nuts • 4 clip-on nuts • Fixing hardware

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CRS: Ultra Thin Heaters

Characteristics and Selection Guide

Ultra-Thin Resistance Heaters



NSYCRS10W240V

Flexible, ultra-thin resistance heaters to be installed inside the enclosure
- Material: Silicon reinforced with fiberglass
- Color: Red (heaters), black (cables)
- Certification: UL (cURus)

Comment:
Ultra-thin resistance heaters can be manufactured with other dimensions and power ratings than those indicated above. Please contact us.

Characteristics	Power (W)	Voltage (V)	Inrush current (A)	Height (mm)	Width (mm)	Depth (mm)	References
Ultra-thin resistance heaters	10	240	0.04	110	140	1.6	**NSYCRS10W240V**
Ultra-thin resistance heaters	25	240	0.10	110	230	1.6	**NSYCRS25W240V**
Ultra-thin resistance heaters	50	240	0.21	200	320	1.6	**NSYCRS50W240V**
Ultra-thin resistance heaters	100	240	0.42	260	440	1.6	**NSYCRS100W240V**
Ultra-thin resistance heaters	200	240	0.83	380	650	1.6	**NSYCRS200W240V**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CR: Resistance Heaters

Introduction



Resistance heaters help prevent the formation of condensation and help guarantee the correct temperature for the correct operation of the electronic components in the enclosure.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CR: Resistance Heaters

Introduction

Insulated PTC Heaters



Large Range of Power Levels

- 2 versions: By natural convection or by fan
- AC or DC power supply
- 7 power levels from 10 W to 550 W



Easy Installation and Connection

- Reduced dimensions
- Quick electric connection by terminal board
- No maintenance required
- Direct clipping onto a 35-mm DIN rail



Safety

- The protection helps prevent direct contact with the aluminum radiator
- Electric protection device with terminal block cover
- Equipped with a PTC-type heater
- Surface temperature lower than 70 °C

High Thermal Efficiency

- The configuration of the aluminum profile produces a “chimney” effect: high natural convection
- Low power consumption thanks to self-control of the PTC-type heater



Models with Fan

- The heaters equipped with a fan helps to ensure circulation of the air and a uniform temperature inside the enclosure
- High-flow, silent fan



Certifications


- CE marking
- Range compliant with UL and VDE, UL (*only the marked references)

Aluminum PTC Heaters



Models with Fan

- Models of 250 to 400 W with fan



Quick-Fixing

- The resistance heaters are fixed by means of fixing clips to a 35-mm DIN rail



Resistance Heaters Equipped with a PTC-Type Sensor

The resistance heaters for electrical and electronic enclosures are equipped with PTC-type heating devices (Positive Temperature Coefficient). Thanks to these heaters:

- The surface temperature stabilises at 75 °C when the ambient temperature is -5 °C
- Power consumption is reduced

Improved Convection

- The design of the profile of the resistance heaters produces a “chimney” effect, leading to increased natural convection and maintaining an even temperature inside the enclosure



Connection Cables

- The 10 and 20-W heaters are equipped with a 2 x 0.75 x 300 mm power cord



Connection Terminal Boards

- Heaters with a power of more than 20 W are equipped with a connection terminal board

Large range of power levels


- 8 power levels from 10 W to 400 W

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CR: PTC Isolated Heaters

Characteristics

Insulated PTC Resistance Heaters



- Compact resistance heater helps preventing the formation of condensation or frost.
- Designed to help ensure natural convection and high thermal efficiency.
- Material: Extruded aluminum body
- Conditions of use: The heaters must be installed with a thermal controller (see selection table on page 426 and 427) to control the temperature or the humidity inside the enclosure
- The enclosure must be sealed to help prevent the entry of air from the outside
- An electrical protection device must be installed on the supply side of the unit
- Operating position: Vertical
- Operating temperature: -40…+70 °C; -10…+158 °F
- Surface temperature: <70 °C, except for the top protection grille
- Ingress protection rating: IP20
- Certifications: UL (cURus) only the reference marked with (*), Class II (double insulated)
- Mounting: By clip on a 35-mm DIN rail



NSYCR10WU2C




NSYCR50WU2C

Characteristics	Heating power at 0 °C (W)	Voltage (V)	Electric connection	References
Insulated PTC resistance heater	10	12-24 V DC	2 screw terminals, 2.5 mm²	**NSYCR10WU1C**
Insulated PTC resistance heater	10	120-240V AC	2 screw terminals, 2.5 mm²	**NSYCR10WU2C ***
Insulated PTC resistance heater	20	12-24 V DC	2 screw terminals, 2.5 mm²	**NSYCR20WU1C**
Insulated PTC resistance heater	20	120-240V AC	2 screw terminals, 2.5 mm²	**NSYCR20WU2C ***
Insulated PTC resistance heater	55	12-24 V DC	4 screw terminals, 2.5 mm²	**NSYCR50WU1C**
Insulated PTC resistance heater	55	120-240V AC	4 screw terminals, 2.5 mm²	**NSYCR50WU2C ***
Insulated PTC resistance heater	55	270-420V AC	4 screw terminals, 2.5 mm²	**NSYCR50WU3C**
Insulated PTC resistance heater	100	12-24 V DC	4 screw terminals, 2.5 mm²	**NSYCR100WU1C**
Insulated PTC resistance heater	100	120-240V AC	4 screw terminals, 2.5 mm²	**NSYCR100WU2C ***
Insulated PTC resistance heater	100	270-420V AC	4 screw terminals, 2.5 mm²	**NSYCR100WU3C**
Insulated PTC resistance heater	147	12-24 V DC	4 screw terminals, 2.5 mm²	**NSYCR150WU1C**
Insulated PTC resistance heater	147	120-240V AC	4 screw terminals, 2.5 mm²	**NSYCR150WU2C ***

Insulated Ventilated PTC Heaters

- Compact resistance heater helps preventing the formation of condensation or frost.
- Designed to help ensure good natural convection and high thermal efficiency.
- Material: Extruded aluminum body
- Conditions of use: The heaters must be installed with a thermal controller (see selection table on page 426 and 427) to control the temperature or the humidity inside the enclosure
- The enclosure must be sealed to help prevent the entry of air from the outside
- An electrical protection device must be installed on the supply side of the unit
- Operating position: Vertical
- Operating temperature: -40…+70 °C; -10…+158 °F
- Surface temperature: Max. 50 °C in the enclosure, 100 °C on the top protection grille, (for an ambient temperature of 20 °C / 68 °F)
- Ingress protection rating: IP20
- Certifications: VDE and UL, Cover: UL 94 V-0 plastic, Class II (double insulated)
- Mounting: By clip on a 35-mm DIN rail





NSYCR170W230VVC

Characteristics	Heating power at 0 °C (W)	Voltage (V)	Electric connection	References
Insulated ventilated PTC heater	177	230 AC / 50-60 HZ	2 poles, 2.5 mm²	**NSYCR170W230VVC**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CR: Aluminum Heaters

Characteristics

Aluminum PTC Heaters

- Extruded aluminum body.
- Surface temperature limited to 75 °C when the ambient temperature is -5 °C.
- Heaters equipped with a power cable with a length of 500 mm with silicon insulation, or with a connection terminal block.

Conditions of use:

- The heaters must be installed with a thermal controller to control the temperature or the humidity inside the enclosure
- The enclosure must be sealed to help prevent the entry of air from the outside
- An electrical protection device must be installed on the supply side of the unit
- Certifications:
  - UL only the reference marked with (*), Class II (double insulated)
  - cURus: only the references marked with (**)



NSYCR10WU1



NSYCR250W115VV

Characteristics	Power (W)	Voltage (V)	References
Aluminum PTC heater	10	12-24 DC	**NSYCR10WU1**
Aluminum PTC heater	10	110-250 AC	**NSYCR10WU2 ***
Aluminum PTC heater	20	12-24 DC	**NSYCR20WU1**
Aluminum PTC heater	20	110-250 AC	**NSYCR20WU2 ***
Aluminum PTC heater	20	270-420 AC	**NSYCR20WU3**
Aluminum PTC heater	55	12-24 DC	**NSYCR55WU1**
Aluminum PTC heater	55	110-250 AC	**NSYCR55WU2 ***
Aluminum PTC heater	55	270-420 AC	**NSYCR55WU3**
Aluminum PTC heater	90	12-24 DC	**NSYCR100WU1**
Aluminum PTC heater	90	110-250 AC	**NSYCR100WU2 ***
Aluminum PTC heater	90	270-420 AC	**NSYCR100WU3**
Aluminum PTC heater	150	12-24 DC	**NSYCR150WU1**
Aluminum PTC heater	150	110-250 AC	**NSYCR150WU2 ***
Aluminum PTC heater	150	270-420 AC	**NSYCR150WU3**
Aluminum PTC heater with fan	250	230 AC	**NSYCR250W230VV ****
Aluminum PTC heater with fan	400	230 AC	**NSYCR400W230VV ****
Aluminum resistive heater with fan	200	230 AC	**NSYCRS200W230V**


Thermofan



NSYCRP1W120VTVC

Combination of a resistance heater and an axial fan to help ensure uniform heating of the enclosure

- Fixing by clip on a DIN rail
- Thermostat adjustable from 0…+60 °C
- Visual operation indicator
- Certifications: UL (cURus).



Characteristics	Power (W)	Voltage (V)	References
Thermofan	350/550	120 AC	**NSYCRP1W120VTVC**
Thermofan	350/550	230 AC	**NSYCRP1W230VTVC**

5

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CC: Thermal Controllers

Introduction



The ClimaSys range of thermal controllers is made up of mechanical and electronic thermostats and electronic hygrostats and hygrometers.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Thermal control



Mechanical and Electronic Thermostats
- Large range of temperature control
- Small dimensions
- Easily accessible terminals




LED Display
- Display visible even in the dark




Operational Temperature Range
- For mechanical thermostats: 0 °C ... +60 °C
- For electronic thermostats: -40 °C ... +80 °C


The New Quick-Fixing Systems



- On 35-mm DIN rail



- On PanelSeT upright



- On cross-rail



- On mounting plate

Certifications and Declarations

- UL
- CE

5

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CC: Thermal Controllers

Characteristics

Mechanical Thermostats


Thermostat with NC Contact:
To control the stopping of a resistance heater when the temperature exceeds the displayed value.
Thermostat with NO Contact:
To control the starting of a fan when the temperature exceeds the displayed maximum value.
To control the temperature inside the enclosure by only starting the fan when necessary, thus increasing the service life of the fan and reducing the clogging of the filter.

- Ingress protection rating according to IEC 60529: IP20
- Sensor element: Bimetal
- Contact resistance: < 10 mΩ
- Service life: > 100,000 cycles
- Mounting: By clip on 35-mm DIN rail, PanelSeT SFN profile, on VDI cross-rail or on mounting plate
- Enclosure: UL 94 V-0 plastic, light gray
- Mounting position: Indifferent
- Operating temperature: -20...+80 °C (-4...+176 °F)
- Hysteresis: 7± 4°K

Thermostat with NC Contact


NSYCCOTHC

- Button color: Red
- Contact: NC, forced rupture
- Switching capacity with alternative current:
  - 240 V AC; 10 A (resistive load)
  - 120 V AC; 15 A (resistive load)
  - 240 V AC/120 V AC 2 A (inductive load cos = 0.6)
- Max interrupting capacity with direct current: NC
- Connection: Two 2.5-mm² terminals
- Weight: 40 g
- Temperature setting range: 0...+60 °C




Characteristics	Display	Max. command intensity	Dimensions (H x W x D)	References
Thermostat with NC contact	°C	10 A 250 V	60 x 33 x 43 mm	**NSYCCOTHC**
Thermostat with NC contact	°F	10 A 250 V	60 x 33 x 43 mm	**NSYCCOTHCF**

Thermostat with NO Contact


NSYCCOTHO

- Button color: Blue
- Contact: NO, forced rupture
- Switching capacity with alternative current:
  - 240 V AC; 10 A (resistive load)
  - 120 V AC; 15 A (resistive load)
  - 240 V AC/120 V AC 2 A (inductive load cos = 0.6)
- Max interrupting capacity with direct current: NO
- Connection: Two 2.5-mm² terminals
- Weight: 40 g
- Temperature setting range: 0...+60 °C




Characteristics	Display	Max. command intensity	Dimensions (H x W x D)	References
Thermostat with NO contact	°C	10 A 250 V	60 x 33 x 43 mm	**NSYCCOTHO**
Thermostat with NO contact	°F	10 A 250 V	60 x 33 x 43 mm	**NSYCCOTHOF**

Thermostat with NO/NC Contact


PB501172_25_nb
NSYCCOTHI

- Button color: Black
- Contact: Inverse,forced rupture
- Switching capacity with alternative current:
  - 240 V AC; 10 A (resistive load)
- Max interrupting capacity with direct current:
  - 240 V AC 4 A (inductive load cos = 0.6)
  - 120 V AC; 15 A (resistive load)
  - 240 V AC 4 A (inductive load cos = 0.6)
- Connection: Four 2.5-mm² terminals
- Weight: 100 g
- Temperature setting range: +5...+60 °C




Characteristics	Display	Max. command intensity	Dimensions (H x W x D)	References
Thermostat with NO/NC contact	°C	(NO) 5 A (NC) 10 A	67 x 50 x 44 mm	**NSYCCOTHI**

Double Thermostat


NSYCCOTHD

- Button color: Red and blue
- Contact: NO / NC, forced rupture
- Switching capacity with alternative current:
  - 240 V AC; 10 A (resistive load)
  - 120 V AC; 15 A (resistive load)
  - 240 V AC/120 V AC 2 A (inductive load cos = 0.6)
- Max interrupting capacity with direct current: NA
- Connection: Six 2.5-mm² terminals
- Weight: 40 g
- Temperature setting range: 0...+60 °C



Characteristics	Display	Max. command intensity	Dimensions (H x W x D)	References
Double Thermostat	°C	(NO) 5 A (NC) 10 A	60 x 33 x 43 mm	**NSYCCOTHD**
Double Thermostat	°F	(NO) 5 A (NC) 10 A	60 x 33 x 43 mm	**NSYCCOTHDF**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CC: Thermal Controllers

Characteristics


Electronic Thermostats

- Ingress protection rating according to IEC 60529: IP20
- Certification: UL / UR
- Contact resistance: Free with zero potential
- Mounting: 4 methods: By DIN rail, PanelSeT SFN profile, on VDI cross-rail or on mounting platel
- Dimensions: 85 x 56 x 44 mm
- Enclosure: UL 94 V-0 plastic, light gray
- Operating temperature: -40 °C…+70 °C
- Hysteresis: 7 K
- Max. command intensity: Motor: 4 / 13.1 A, FLA / LRA, 250 Vac Resistive load: 4 A, 250 Vdc

Electronic Thermostats with LED Display



NSYCCOTH30VID




- Electronic temperature controller
- Internal sensor element: Temperature sensor
- Connection:2 x 2.5 mm² (input voltage) + 2 relays (2 x 2.5 mm² + 2 x 2.5 mm²)
- Hysteresis:Programmed 2 K
- Temperature setting range: -40 °C…+80 °C

Characteristics	Display	Voltage (type of current)	References
Electronic thermostats, with LED display	°C or °F	9-30 V (AC/DC)	**NSYCCOTH30VID**
Electronic thermostats, with LED display	°C or °F	90-140 V (AC)	**NSYCCOTH120VID**
Electronic thermostats, with LED display	°C or °F	200-240 V (AC)	**NSYCCOTH230VID**

Electronic Hygrotherm



NSYCCOHYT30VID




- Electronic temperature and humidity controller
- Internal sensor element: Temperature sensor and humidity sensor
- Connection: 2 x 2.5 mm² (input voltage) + 2 relays (2 x 2.5 mm² + 2 x 2.5 mm²)
- Hysteresis: Programmed 2 K and 3%
- Temperature setting range: -40 °C…+80 °C
- Humidity setting range: 20%…80%

Characteristics	Display	Voltage (type of current)	References
Electronic hygrotherm	°C or °F or % RH	9-30 V (AC/DC)	**NSYCCOHYT30VID**
Electronic hygrotherm	°C or °F or % RH	90-140 V (AC)	**NSYCCOHYT120VID**
Electronic hygrotherm	°C or °F or % RH	200-240 V (AC)	**NSYCCOHYT230VID**

Electronic Hygrostat



NSYCCOHY230VID



- Electronic humidity controller
- Internal sensor element: Humidity sensor
- Connection: 2 x 2.5 mm² (input voltage) + 1 relay (2 x 2.5 mm²)
- Hysteresis: 3%
- Humidity setting range: 20%…80%

Characteristics	Display	Voltage (type of current)	References
Electronic hygrostat	% RH	200-240 V (AC)	**NSYCCOHY230VID**

External Temperature Sensor (Double Insulation)



NSYCCASTE

Sensor operation or reading range: -40 °C…+150 °C.
Thermostat installation tips: The thermostat should be installed at the top of the enclosure (the hottest place). See the various operating modes of each thermostat to choose the one that meets your needs. Hygrostat installation tips: The hygrostat should be installed at the bottom of the enclosure. 60% RH is the optimal value in the enclosure.

- Ingress protection rating: IP67
- Fixing: On DIN rail, on PanelSeT SFN profile, on VDI cross-rail, on mounting plate

Characteristics	Length of cable supplied	References
External temperature sensor	3 m	**NSYCCASTE**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers

Introduction



Choose air-to-air exchangers to take advantage of cooler ambient temperatures, such as in food and beverage plants, to evacuate large amounts of heat while retaining the independence of the internal and external air circuits.


Choose air-to-water exchangers for especially difficult environments where there is no external air circuit available but a stable cold-water circuit can be supplied.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers

Introduction

Air-to-Air Exchangers: Designed for Energy Efficiency



Higher Efficiency through Improved Design

- With an updated external grill design, and by positioning cooling closer to critical equipment, such as speed drives, ClimaSys now provides better flow, better cooling, and higher energy efficiency

Faster Installation

- A number of design improvements reduce installation time. Mounting requires single cut-outs and a minimum of screws. Wiring is accomplished with smart interconnects

Simplicity Saves You Time

- Our free ProClima thermal calculation software makes specification simple and fast. A new thermal solutions module integrates calculation for cooling and control devices, helping you maximize the energy efficiency of your systems


Protection

- All side-mounted models are IP55 internally according to EN 60529

Certifications and Declarations

- CE
- EAC

Air-to-Water Exchangers: For Highly Polluted Environments



Many Mounting Options Give You the Right Fit

- Air-to-water exchangers offer roof and side-mounted options

Extended Ratings to Meet Any Challenge

- Provide options for up to 6 kW of cooling power, among the world's highest power ratings for air-to-water exchangers

Certifications and Declarations

- CE
- EAC



Protection

- All side-mounted models are IP55-protected internally and externally according EN 60529. Top-mounted models are IP54

5

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers

Characteristics

Air-to-Air Exchangers, Side-Mounted Models



Characteristics	Side-mounted models			
				
	• The air-to-air exchanger can be used in heavily polluted environments provided that the ambient temperature is at least 10 °C lower than the internal temperature wanted. • Main components: Thermostat adjustment system, exchanger cassette, fans for internal and external circuits of the enclosure.			
Material	Painted zinc-coated steel			
Color	RAL 7035 gray			
Ingress protection rating (according to IEC 60529)	IP55			
Certifications and declarations	CE, EAC			
Installation	Indoor. For outdoor applications or other surface finishes please consult us.			
Cooling characteristics				
Specific power	22 W/K	36 W/K	50 W/K	80 W/K
Air flow of the internal circuit (enclosure)	280 m³/h	570 m³/h	600 m³/h	1050 m³/h
Air flow of the external circuit (ambient)	280 m³/h	570 m³/h	600 m³/h	1050 m³/h
Thermostat type	-	Mechanical	Mechanical	Mechanical
Temperature setting range	-	+5 … +60 °C	+5 … +60 °C	+5 … +60 °C
Temperature range of external circuit (ambient)	-5 … +55 °C	-5 … +55 °C	-5 … +55 °C	-5 … +55 °C
Type of fluid	Air	Air	Air	Air
Electric characteristics				
Input voltage	1 x 230 V / 50-60 Hz	1 x 230 V / 50-60 Hz	1 x 230 V / 50-60 Hz	1 x 230 V / 50-60 Hz
Rated current	0.5 A	0.7 A	0.7 A	1.1 A
Power consumption	72 W	160 W	160 W	240 W
Thermal protection recommended (fuse)	T1 A	T1 A	T1 A	T2 A
Physical characteristics				
External dimensions (H x W x D)	413 x 189 x 149 mm	771 x 316 x 103 mm	771 x 316 x 103 mm	1260 x 317 x 148 mm
Protection degree IP internal /external (according to IEC 60529)	IP55 / IP22	IP55 / IP22	IP55 / IP22	IP55 / IP22
Noise level	59 dB (A)	62 dB (A)	62 dB (A)	64 dB (A)
Weight of unit	7 kg	10 kg	10 kg	17 kg
References				
	NSYCEA22E	**NSYCEA36**	**NSYCEA50**	**NSYCEA80**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers

Characteristics

Air-to-Water Exchangers, Side-Mounted Models

Characteristics	Side-mounted models				
					
	• Main components: Thermostat adjustment system, Exchange cassette, fans for internal circuits of the enclosure, protection device against possible leaks. • Eyebolts included in all models.				
Material	RAL 7035 gray painted zinc-coated steel or stainless-steel				
Ingress protection rating (according to IEC 60529)	IP55				
Certifications and declarations	• CE declaration • EAC				
Installation	Indoor. For outdoor applications or other surface finishes please consult us.				
Cooling characteristics					
Cooling power W10A35	1000 W	1750 W	2500 W	3500 W	4500 W
Hydraulic circuit maximum pressure	5 bar	5 bar	5 bar	5 bar	5 bar
Internal airflow	330 m³/h	570 m³/h	860 m³/h	1050 m³/h	1450 m³/h
Thermostat type	Mechanical	Mechanical	Mechanical	Mechanical	Mechanical
Temperature setting range	+20 … +46 °C	+20 … +46 °C	+20 … +46 °C	+20 … +46 °C	+20 … +46 °C
Temperature range of external circuit (ambient)	+1 … +70 °C	+1 … +70 °C	+1 … +70 °C	+1 … +70 °C	+1 … +70 °C
Type of fluid	Filtered water or glicolised water	Filtered water or glicolised water	Filtered water or glicolised water	Filtered water or glicolised water	Filtered water or glicolised water
Water flow	150 l/h	150 l/h	500 l/h	500 l/h	500 l/h
Pressure drop	0.1 bar	0.1 bar	0.3 bar	0.2 bar	0.2 bar
Hydraulic connection	3/8" G	1/2" G	1/2" G	1/2" G	1/2" G
Electric characteristics					
Input voltage	1 x 230 V / 50-60 Hz*	1 x 230 V / 50-60 Hz*	1 x 230 V / 50-60 Hz*	1 x 230 V / 50-60 Hz*	1 x 230 V / 50-60 Hz*
Rated Intensity	0.17 A	0.36 A	0.33 A	0.55 A	0.71 A
Power consumption absorved W10A35	29 W	75 W	80 W	130 W	160 W
Thermal protection recommended (fuse)	T2 A	T2 A	T2 A	T2 A	T2 A
Physical characteristics					
External dimensions (H x W x D)	450 x 310 x 115 mm	901 x 398 x 137 mm	901 x 398 x 137 mm	1148 x 398 x 163 mm	1148 x 398 x 163 mm
Protection degree IP internal /external (according to IEC 60529)	IP55 / IP55	IP55 / IP55	IP55 / IP55	IP55 / IP55	IP55 / IP55
Noise level	55 dB (A)	58 dB (A)	58 dB (A)	64 dB (A)	69 dB (A)
Weight of unit	12 kg	18 kg	19 kg	29 kg	30 kg
References					
Steel	**NSYCEW1K**	**NSYCEW1K8**	**NSYCEW2K5**	**NSYCEW3K5**	**NSYCEW4K5**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers

Characteristics

Side-Mounting Model

Top Mounting Model

Characteristics	Side-mounted models		Top mounting model
			
	• Main components: Thermostat adjustment system, Exchange cassette, fans for internal circuits of the enclosure, protection device against possible leaks. • Eyebolts included in all models.		
Material	RAL 7035 gray painted zinc-coated steel or stainless-steel		
Ingress protection rating (according to IEC 60529)	IP55		IP54
Certifications and declarations	• CE declaration • EAC		
Installation	Indoor. For outdoor applications or other surface finishes please consult us.		
Cooling characteristics			
Cooling power W10A35	6000 W	6000 W	2500 W
Hydraulic circuit maximum pressure	5 bar	8 bar	5 bar
Internal airflow	1450 m³/h	1450 m³/h	750 m³/h
Thermostat type	Mechanical	Mechanical	Mechanical
Temperature setting range	+20 … +46 °C	+20 … +46 °C	+20 … +46 °C
Temperature range of external circuit (ambient)	+1 … +70 °C	+1 … +70 °C	+1 … +70 °C
Type of fluid	Filtered water or glicolised water	Filtered water or glicolised water	Filtered water or glicolised water
Water flow	800 l/h	800 l/h	500 l/h
Pressure drop	0.5 bar	0.5 bar	0.3 bar
Hydraulic connection	1/2" G	1/2" G	1/2" G
Electric characteristics			
Input voltage	1 x 230 V / 50-60 Hz*	2 x 400-440 V / 50-60 Hz	1 x 230 V / 50-60 Hz
Rated Intensity	0.71 A	0.4 A	0.30 A
Power consumption absorved W10A35	160 W	170 W	65 W
Thermal protection recommended (fuse)	T2 A	T1 A	T2 A
Physical characteristics			
External dimensions (H x W x D)	1500 x 450 x 163 mm	1500 x 450 x 163 mm	270 x 400 x 542 mm
Protection degree IP internal /external (according to IEC 60529)	IP55 / IP55	IP55 / IP55	IP54 / IP55
Noise level	69 dB (A)	69 dB (A)	58 dB (A)
Weight of unit	40 kg	42 kg	19 kg
References			
Steel	**NSYCEW6K**	**NSYCEW6K2P4**	**NSYCEW2K5R**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers


Dimensions

Air-to-Air Exchangers, Side-Mounted Models


NSYCEA22E



NSYCEA36 / NSYCEA50




NSYCEA80




Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Air-to-Water Exchangers, Side-Mounted Models


Performance Curves




NSYCEW●●1K●●




Performance Curves





NSYCEW●●1K8●● – NSYCEW●●2K5●●



P = Cooling power
Ta= Inlet water temperature
Ti= Target internal temperature of the enclosure


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CE: Exchangers


Dimensions


Air-to-Water Exchangers, Side-Mounted Models

Performance Curves




NSYCEW●●3K5●● – NSYCEW●●4K5●●






Performance Curves



NSYCEW●●6K●●





P = Cooling power
Ta= Inlet water temperature
Ti= Target internal temperature of the enclosure

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Air-to-Water Exchangers, Side-Mounted Models

Performance Curves







NSYCEW●●3K5●● – NSYCEW●●4K5●●



Performance Curves



NSYCEW●●6K●●



P = Cooling power
Ta= Inlet water temperature
Ti= Target internal temperature of the enclosure

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Cooling Units

Introduction



This range of Cooling units is the ideal solution for electrical cabinets with :
- High power dissipation generated inside (ex.: VSD - Variable Speed Drive),
- High ambient temperature or humidity (ex.: Steel industry, Specific geographical location),
- Environmental dust or pollution (to avoid air flow from ambient to internal atmosphere).

The unit's integrated alarm and communication system keeps you informed about the operating status of your cooling systems and any temperature conditions.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Cooling Units

Introduction

Reliability for Greater Peace of Mind



Connectivity

- Remote visibility for alarms, operating status, and setting data
- Native feature with no specific option / configuration to be defined



Hardware Features

- IP55 for all side cooling units
- Ambient temperature up to 55 °C
- Optimized condensation water management with no clogging pipe solution
- Top of the art components from the automotive industry: Rotary compressors, micro-channel condenser heat exchanger



Robust Design in Every Situation

- Indoor and outdoor
- Side and roof
- Steel / Stainless Steel



Certifications and Declarations

- Cooling capacity compliant with EN14511 (L35L35 and L35L50)
- Dual compliance with IEC and UL
- C-UL Listed
- Cybersecurity certified according with IEC62443
- Rated types 12 and 3R



Redundant Modes for Critical Applications

- 3 redundant mode options: serial, back-up, sequential
- Native feature

Efficiency for Easier Product Selection and Quicker Mounting




Product Selection

- Easy, optimized product selection with ProClima combined with SEE Electrical



Mounting and Cabling

- Small sizes Cooling Unit
- Mounting bracket and lifting eyebolts
- 4 independent connectors (Power supply, Signal and Alarm, Modbus, Synchronization)



Offer Portfolio

- All cooling unit functions in 40 references
- Possible customization if required
- 3 mounting options for the Side Indoor Cooling Units: Surface, Half-flush, Flush



Simplicity

- Roof screw fixing from inside (by default) or from outside if required
- Schneider EcoStruxure integration in edge software and cloud advisors

Lower Impact Approach



Qualification

- Compliant with RoHS and REACH regulation
- Product Environmental Profile available





Key Performances

- Suitable combination of Energy Efficiency Ratio and size/weight, compared to the market
- Up to 80% recycled cardboard, no single-use plastic packaging
- Lighter Instruction Sheet with digital link to user manual

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Side Cooling Units






Characteristics

Characteristics	Side-mounted models				
	 NSYCU350DG_image	 NSYCU600DG_image	 NSYCU800DG_image	 NSYCU8002P4DG_image	 NSYCU1KDG_image
	• Alarm, operation and setting info available remotely and locally • Simple, open and easy, native connectivity with Modbus RTU communication • Electronic thermostat with touch screen display • Alarm signal for door contact included in all References • Internal IP55 • Passive water condensate evaporator for all Side Cooling Units strictly above 800 W • Unique combination of optimized Energy Efficiency Ratio and reduced sizes and weight • Easy product selection with ProClima associated with SEE Electrical • Filter recommendation: - Office environment (no dust, no grease) : filter free, - Industrial environment (dust, grease, not explosive) : G3 fiber filter is recommended, Indoor CU are delivered without any filter by default.				
Material	Galvanized steel painted in gray RAL 7035 or stainless-steel				
Certifications and declarations	CE (all references, 50 Hz only) and C-UL listed (all references, 60Hz only). Rated types 12				
Installation	Indoor				
Cooling characteristics					
Cooling power L35-L35 according to EN 14511	350 W	620 W	810 W	810 W	960 W
Cooling power L35-L50 according to EN 14511	240 W	470 W	560 W	560 W	710 W
Air flow of the internal circuit. Rated value	117 m³/h	106 m³/h	330 m³/h	330 m³/h	330 m³/h
Air flow of the external circuit. Rated value	166 m³/h	177 m³/h	450 m³/h	450 m³/h	450 m³/h
Thermostat type	Electronic	Electronic	Electronic	Electronic	Electronic
Temperature range of circuit	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
Maximum outside temperature	+55 °C	+55 °C	+55 °C	+55 °C	+55 °C
Temperature range of external circuit	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C
Type of cooling gas	R513a	R513a	R513a	R513a	R513a
Cooling gas weight	0.127 kg	0.115 kg	0.137 kg	0.137 kg	0.200 kg
Maximum pressure of cooling circuit	28 bar	28 bar	28 bar	28 bar	28 bar
External filter	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448
Electric characteristics					
Input voltage	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~
Starting / rated current	3.8 A / 1.3 A	6 A / 1.8 A	6 A / 2.2 A	4 A / 1.3 A	6 A / 2.3 A
Power consumption L35-L35 according to EN 14511	270 W	470 W	461 W	461 W	480 W
Power consumption L35-L50 according to EN 14511	300 W	410 W	509 W	509 W	540 W
Energy efficiency ratio L35-L35 according to EN 14511	1.3	1.7	1.8	1.8	2
Thermal protection recommended (circuit breaker)	M9F22116	M9F22116	M9F22116	M9F22216	M9F22116
Thermal protection recommended (fuse)	T15 A	T15 A	T15 A	2 x 15 A	T15 A
Physical characteristics					
External dimensions (H x W x D)	460 x 290 x 190 mm	460 x 290 x 190 mm	780 x 345 x 215 mm	780 x 345 x 215 mm	780 x 345 x 215 mm
Protection degree IP internal/external according to IEC	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24
Max. Noise Pressure level according to UNE-EN ISO 11202-2010 V2+A1:2021	62 dB (A)	62 dB (A)	76 dB (A)	76 dB (A)	76 dB (A)
Weight of Unit	11.7 kg	11.7 kg	22.4 kg	27.4 kg	22.4 kg
References					
Steel	**NSYCU350DG**	**NSYCU600DG**	**NSYCU800DG**	**NSYCU8002P4DG**	**NSYCU1KDG**
Stainless-steel	**NSYCUX350DG**	**NSYCUX600DG**	-	-	**NSYCUX1KDG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Side Cooling Units


Characteristics

						
	NSYCU1K2P4DG_Image	NSYCU1K2DG_Image	NSYCU1K22P4DG_Image	NSYCU1K6DG_Image	NSYCU1K62P4DG_Image	NSYCU2KDG_Image
	960 W	1240 W	1240 W	1620 W	1630 W	1980 W
	710 W	970 W	970 W	1340 W	1350 W	1620 W
	330 m³/h	1000 m³/h	1000 m³/h	1000 m³/h	1000 m³/h	1000 m³/h
	450 m³/h	1000 m³/h	1000 m³/h	1000 m³/h	1000 m³/h	1200 m³/h
	Electronic	Electronic	Electronic	Electronic	Electronic	Electronic
	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
	+55 °C	+55 °C	+55 °C	+55 °C	+55 °C	+55 °C
	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C
	R513a	R513a	R513a	R513a	R513a	R513a
	0.200 kg	0.283 kg	0.283 kg	0.333 kg	0.366 kg	0.410 kg
	28 bar	28 bar	28 bar	28 bar	28 bar	28 bar
	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448
	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~
	4 A / 2 A	16 A / 3.0 A	8 A / 1.8 A	16 A / 3.1 A	8 A / 3.3 A	22 A / 4.4 A
	480 W	651 W	651 W	670 W	716 W	995 W
	550 W	745 W	745 W	770 W	770 W	1140 W
	2.1	1.9	1.9	2.4	2.3	2.0
	M9F22216	M9F22116	M9F22216	M9F22116	M9F22216	M9F22116
	2 x 15 A	T15 A	2 x 15 A	T15 A	2 x 15 A	T15 A
	780 x 345 x 215 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm
	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24
	76 dB (A)	76 dB (A)	76 dB (A)	76 dB (A)	75 dB (A)	76 dB (A)
	27.4 kg	39 kg	44.5 kg	39 kg	44.5 kg	40.4 kg
	NSYCU1K2P4DG	**NSYCU1K2DG**	**NSYCU1K22P4DG**	**NSYCU1K6DG**	**NSYCU1K62P4DG**	**NSYCU2KDG**
	NSYCUX1K2P4DG	-	-	**NSYCUX1K6DG**	-	-

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Side Cooling Units

Characteristics

Characteristics	Side-mounted models	
	 NSYCU2K3P4DG_Image	 NSYCU3K2DG_Image
	• Alarm, operation and setting info available remotely and locally • Simple, open and easy, native connectivity with Modbus RTU communication • Electronic thermostat with touch screen display • Alarm signal for door contact included in all References • Internal IP55 • Passive water condensate evaporator for all Side Cooling Units strictly above 800 W • Unique combination of optimized Energy Efficiency Ratio and reduced sizes and weight • Easy product selection with ProClima associated with SEE Electrical • Filter recommendation: - Office environment (no dust, no grease) : filter free, - Industrial environment (dust, grease, not explosive) : G3 fiber filter is recommended, Indoor CU are delivered without any filter by default.	
Material	Galvanized steel painted in gray RAL 7035 or stainless-steel	
Certifications and declarations	CE (all references, 50 Hz only) and C-UL listed (all references, 60Hz only). Rated types 12	
Installation	Indoor	
Cooling characteristics		
Cooling power L35-L35 according to EN 14511	1940 W	3180 W
Cooling power L35-L50 according to EN 14511	1580 W	2370 W
Air flow of the internal circuit	890 m³/h	1200 m³/h
Air flow of the external circuit	1200 m³/h	1400 m³/h
Thermostat type	Electronic	Electronic
Temperature range of circuit	+20… +50 °C	+20… +50 °C
Maximum outside temperature	55 °C	55 °C
Temperature range of external circuit	+5… +55 °C	+5… +55 °C
Type of cooling gas	R513a	R513a
Cooling gas weight	0.445 kg	0.482 kg
Maximum pressure of cooling circuit	28 bar	32 bar
External filter	Optional, **see** page 448	Optional, **see** page 448
Electric characteristics		
Input voltage	EN IEC: 380–415V 50 Hz 3~ UL: 400V / 460V ± 6% 60 Hz 3~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~
Starting / rated current	13 A / 1.8 A	30 A / 5.6 A
Power consumption L35-L35 according to EN 14511	980 W	1236 W
Power consumption L35-L50 according to EN 14511	1130 W	1410 W
Energy efficiency ratio L35-L35 according to EN 14511	2	2.6
Thermal protection recommended (circuit breaker)	M9F22316	M9F22116
Thermal protection recommended (fuse)	3 x 15 A	T15 A
Physical characteristics		
External dimensions (H x W x D)	1000 x 405 x 225 mm	1300 x 490 x 250 mm
Protection degree IP internal/external according to IEC	IP55 / IP24	IP55 / IP24
Max. Noise Pressure level according to UNE-EN ISO 11202-2010 V2+A1:2021	76 dB (A)	77 dB (A)
Weight of Unit	40.4 kg	59.6 kg
References		
Steel	**NSYCU2K3P4DG**	**NSYCU3K2DG**
Stainless-steel	**NSYCUX2K3P4DG**	-

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Side Cooling Units

Characteristics





3150 W	3910 W
2510 W	3120 W
1200 m³/h	1200 m³/h
1400 m³/h	1400 m³/h
Electronic	Electronic
+20… +50 °C	+20… +50 °C
55 °C	55 °C
+5… +55 °C	+5… +55 °C
R513a	R513a
0.512 kg	0.679 kg
32 bar	32 bar
Optional, **see** page 448	Optional, **see** page 448
EN IEC: 380–415V 50 Hz 3~ UL: 400V / 460V ± 6% 60 Hz 3~	EN IEC: 380–415V 50 Hz 3~ UL: 400V / 460V ± 6% 60 Hz 3~
20 A / 2.8 A	15 A / 3.6 A
1205 W	1810 W
1410 W	2220 W
2.6	2.2
M9F22316	M9F22316
3 x 15 A	3 x 15 A
1300 x 490 x 250 mm	1300 x 490 x 250 mm
IP55 / IP24	IP55 / IP24
77 dB (A)	77 dB (A)
59.0 kg	62.2 kg
NSYCU3K23P4DG	**NSYCU4K3P4DG**
-	-

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Roof Cooling Units

Characteristics

Characteristics	Roof-mounted models				
					
	• Alarm, operation and setting info available remotely and locally • Simple, open and easy, native connectivity with Modbus RTU communication • Electronic thermostat with touch screen display • Alarm signal for door contact included in all References • Passive water condensate evaporator for all Side Cooling Units strictly above 800 W • Unique combination of optimized Energy Efficiency Ratio and reduced sizes and weight • Easy product selection with ProClima associated with SEE Electrical • Filter recommendation: - Office environment (no dust, no grease) : filter free, - Industrial environment (dust, grease, not explosive) : G3 fiber filter is recommended, Indoor CU are delivered without any filter by default.				
Material	Galvanized steel painted in gray RAL 7035 or stainless-steel				
Certifications and declarations	CE (all references, 50 Hz only) and C-UL listed (all references, 60Hz only). Rated types 12				
Installation	Indoor				
Cooling characteristics					
Cooling power L35-L35 according to EN 14511	620 W	810 W	810 W	1280 W	1280 W
Cooling power L35-L50 according to EN 14511	470 W	550 W	550 W	810 W	810 W
Air flow of the internal circuit	180 m^3/h	850 m^3/h	850 m^3/h	850 m^3/h	850 m^3/h
Air flow of the external circuit	408 m^3/h	850 m^3/h	850 m^3/h	850 m^3/h	850 m^3/h
Thermostat type	Electronic	Electronic	Electronic	Electronic	Electronic
Temperature range of circuit	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
Maximum outside temperature	55 °C	55 °C	55 °C	55 °C	55 °C
Temperature range of external circuit	5… +55 °C	5… +55 °C	5… +55 °C	5… +55 °C	+5… +55 °C
Type of cooling gas	R513a	R513a	R513a	R513a	R513a
Cooling gas weight	0.143 kg	0.133 kg	0.133 kg	0.183 kg	0.183 kg
Maximum pressure of cooling circuit	28 bar	28 bar	28 bar	28 bar	28 bar
External filter	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448
Electric characteristics					
Input voltage	EN IEC: 220–240V 50 Hz 1~ UL: 230V ± 6% 60 Hz 1~	EN IEC: 220–240V 50 Hz 1~ UL: 230V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 460V ± 6% 60 Hz 2~	EN IEC: 220–240V 50 Hz 1~ UL: 230V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 460V ± 6% 60 Hz 2~
Starting / rated current	6 A / 1.7 A	6 A / 2.6 A	4 A / 1.5 A	16 A / 3.3 A	8 A / 1.9 A
Power consumption L35-L35 according to EN 14511	343 W	560 W	560 W	699 W	699 W
Power consumption L35-L50 according to EN 14511	410 W	660 W	660 W	793 W	793 W
Energy efficiency ratio L35-L35 according to EN 14511	1.8	1.5	1.5	1.8	1.8
Thermal protection recommended (circuit breaker)	M9F22116	M9F22116	M9F22216	M9F22116	M9F22216
Thermal protection recommended (fuse)	T15 A	T15 A	2 x 15 A	T15 A	2 x 15 A
Physical characteristics					
External dimensions (H x W x D)	368 x 400 x 325 mm	412 x 595 x 395 mm	412 x 595 x 395 mm	412 x 595 x 395 mm	412 x 595 x 395 mm
Protection degree IP internal/external according to IEC	IP54 / IP24	IP54 / IP24	IP54 / IP24	IP54 / IP24	IP54 / IP24
Max. Noise Pressure level according to UNE-EN ISO 11202-2010 V2+A1:2021	61 dB (A)	74 dB (A)	74 dB (A)	74 dB (A)	74 dB (A)
Weight of Unit	16.8 kg	27.5 kg	32 kg	34.5 kg	39 kg
References					
Steel	**NSYCU600RDG**	**NSYCU800RDG**	**NSYCU8002P4RDG**	**NSYCU1K2RDG**	**NSYCU1K22P4RDG**

Evaporation device for condensation water (external installation)

- Device allowing the evaporation of water condensate from the internal heat exchanger (evaporator).
- Accessory compatible for all Indoor Cooling Unit (Side and Roof).

Heat sink

NSYCUACC009DG

Characteristics	Value
Mechanical data	
Height x Width x Depth	103 x 164 x 148 mm (4.1 x 6.5 x 5.8 in)
Weight	1.2 kg (2.2 lb)
Implementation	External mounting of the Cooling Unit
Electrical data	
Voltage / Frequency	1 x 230 V / 50-60 Hz
Starting current	2 A
Power consumption	
During operation (max. heater fully immersed)	230 W
Standby (dry)	25 W
Performance	
Evaporation rate	0.25l/h


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Roof Cooling Units


Characteristics

						
	1480 W	1480 W	1960 W	2080 W	3170 W	3890 W
	1140 W	1140 W	1630 W	1710 W	2470 W	3170 W
	850 m³/h	850 m³/h	850 m³/h	850 m³/h	1200 m³/h	1200 m³/h
	850 m³/h	850 m³/h	1200 m³/h	1200 m³/h	1400 m³/h	1400 m³/h
	Electronic	Electronic	Electronic	Electronic	Electronic	Electronic
	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
	55 °C	55 °C	55 °C	55 °C	55 °C	55 °C
	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C	+5… +55 °C
	R513a	R513a	R513a	R513a	R513a	R513a
	0.285 kg	0.285 kg	0.355 kg	0.420 kg	0.490 kg	0.545 kg
	28 bar	28 bar	28 bar	28 bar	28 bar	28 bar
	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448	Optional, **see** page 448
	EN IEC: 220–240V 50 Hz 1~ UL: 230V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 460V ± 6% 60 Hz 2~	EN IEC: 220–240V 50 Hz 1~ UL: 230V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 3~ UL: 460V ± 6% 60 Hz 3~	EN IEC: 380–415V 50 Hz 3~ UL: 460V ± 6% 60 Hz 3~	EN IEC: 380–415V 50 Hz 3~ UL: 460V ± 6% 60 Hz 3~
	16 A / 3.6 A	8 A / 2.1 A	22 A / 4.2 A	13 A / 1.8 A	28 A / 2.9 A	28 A / 3.3 A
	781 W	781 W	950 W	940 W	1173 W	1599 W
	885 W	885 W	1080 W	1100 W	1397 W	1917 W
	2.1	2.1	2.1	2.4	2.7	2.4
	M9F22116	M9F22216	M9F22116	M9F22316	M9F22316	M9F22316
	T15 A	2 x 15 A	T15 A	3 x 15 A	3 x 15 A	3 x 15 A
	412 x 595 x 395 mm	412 x 595 x 395 mm	435 x 595 x 475 mm	435 x 595 x 475 mm	456 x 795 x 575 mm	456 x 795 x 575 mm
	IP54 / IP24	IP54 / IP24	IP54 / IP24	IP54 / IP24	IP54 / IP24	IP54 / IP24
	74 dB (A)	74 dB (A)	75 dB (A)	73 dB (A)	77 dB (A)	77 dB (A)
	34.5 kg	34.5 kg	38.1 kg	40.1 kg	54.2 kg	57.2 kg
	NSYCU1K5RDG	**NSYCU1K52P4RDG**	**NSYCU2KRDG**	**NSYCU2K3P4RDG**	**NSYCU3K3P4RDG**	**NSYCU4K3P4RDG**


Side-Mounted 01




Side-Mounted 02



Roof-Mounted








Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Outdoor Cooling Units


Characteristics


Characteristics	Side-mounted models			
	 NSYCUHD350DG_Image	 NSYCUHD600DG_Image	 NSYCUHD800DG_Image	 NSYCUHD1KDG_Image
	• Alarm, operation and setting info available remotely and locally • Simple, open and easy, native connectivity with Modbus RTU communication • Electronic thermostat with touch screen display mounter in the enclosure side • Alarm signal for door contact included in all References • Internal IP55 • Unique combination of optimized Energy Efficiency Ratio and reduced sizes and weight • Easy product selection with ProClima associated with SEE Electrical • Anti-corrosion protection (class C3H) • External screws are safety Torx head • Aluminum filter re placement access is closed with a lid • Minimum ambient temperature range reaches -20 °C adding a heater to the compressor body • Filter recommendation: - Office environment (no dust, no grease): filter free, - Industrial environment (dust, grease, not explosive): G3 fiber filter is recommended, - Outdoor (not explosive) : aluminum filter is recommended, Indoor CU are delivered without any filter by default Outdoor CU are delivered with Aluminum filter by default.			
Material	Galvanized steel painted in gray RAL 7035			
Certifications and declarations	CE (all references, 50 Hz only) and C-UL listed (all references, 60Hz only). Rated types 3R			
Installation	Indoor or outdoor			
Cooling characteristics				
Cooling power L35-L35 according to EN 14511	340 W	630 W	800 W	990 W
Cooling power L35-L50 according to EN 14511	220 W	460 W	540 W	710 W
Air flow of the internal circuit	106 m^3/h	106 m^3/h	330 m^3/h	330 m^3/h
Air flow of the external circuit	170 m^3/h	177 m^3/h	530 m^3/h	530 m^3/h
Thermostat type	Electronic	Electronic	Electronic	Electronic
Temperature range of circuit	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
Maximum outside temperature	55 °C	55 °C	55 °C	55 °C
Temperature range of external circuit	-20 °C… +55 °C	-20 °C… +55 °C	-20 °C… +55 °C	-20 °C… +55 °C
Type of cooling gas	R513a	R513a	R513a	R513a
Cooling gas weight	0.127 kg	0.115 kg	0.130 kg	0.200 kg
Maximum pressure of cooling circuit	28 bar	28 bar	28 bar	28 bar
External filter	Aluminum filter included	Aluminum filter included	Aluminum filter included	Aluminum filter included
Electric characteristics				
Input voltage	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~
Starting / rated current	3.8 A / 1.2 A	6 A / 1.8 A	6 A / 2.2 A	6 A / 2.3 A
Power consumption L35-L35 according to EN 14511	240 W	370 W	466 W	502 W
Power consumption L35-L50 according to EN 14511	270 W	420 W	513 W	561 W
Energy efficiency ratio L35-L35 according to EN 14511	1.4	1.7	1.7	2
Thermal protection recommended (circuit breaker)	M9F22116	M9F22116	M9F22116	M9F22116
Thermal protection recommended (fuse)	T15 A	T15 A	T15 A	T15 A
Physical characteristics				
External dimensions (H x W x D)	460 x 290 x 190 mm	460 x 290 x 190 mm	780 x 345 x 215 mm	780 x 345 x 215 mm
Protection degree IP internal/external according to IEC	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24
Max. Noise Pressure level according to UNE-EN ISO 11202-2010 V2+A1:2021	62 dB (A)	62 dB (A)	76 dB (A)	76 dB (A)
Weight of Unit	11.7 kg	11.7 kg	22.4 kg	22.4 kg
References				
Steel	**NSYCUHD350DG**	**NSYCUHD600DG**	**NSYCUHD800DG**	**NSYCUHD1KDG**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


ClimaSys CU: Outdoor Cooling Units

Characteristics









	990 W	1630 W	1630 W	1990 W
	710 W	1350 W	1350 W	1550 W
	330 m^3/h	1000 m^3/h	1000 m^3/h	890 m^3/h
	530 m^3/h	1000 m^3/h	1000 m^3/h	1200 m^3/h
	Electronic	Electronic	Electronic	Electronic
	+20… +50 °C	+20… +50 °C	+20… +50 °C	+20… +50 °C
	55 °C	55 °C	55 °C	55 °C
	-20 °C… +55 °C	-20 °C… +55 °C	-20 °C… +55 °C	-20 °C… +55 °C
	R513a	R513a	R513a	R513a
	0.200 kg	0.366 kg	0.366 kg	0.418 kg
	28 bar	28 bar	28 bar	28 bar
	Aluminum filter included	Aluminum filter included	Aluminum filter included	Aluminum filter included
	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 220–240 V 50 Hz 1~ UL: 230 V ± 6% 60 Hz 1~	EN IEC: 380–415V 50 Hz 2~ UL: 400V / 460V ± 6% 60 Hz 2~	EN IEC: 380–415V 50 Hz 3~ UL: 400V / 460V ± 6% 60 Hz 3~
	4 A / 1.4 A	16 A / 3.3 A	8 A / 3.3 A	13 A / 2.5 A
	502 W	716 W	716 W	950 W
	561 W	770 W	770 W	1130 W
	2	2.3	2.3	1.9
	M9F22216	M9F22116	M9F22216	M9F22316
	T15 A	T15 A	T15 A	T15 A
	780 x 345 x 215 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm	1000 x 405 x 225 mm
	IP55 / IP24	IP55 / IP24	IP55 / IP24	IP55 / IP24
	76 dB (A)	75 dB (A)	75 dB (A)	75 dB (A)
	27.4 kg	39 kg	44.5 kg	40.4 kg
	NSYCUHD1K2P4DG	**NSYCUHD1K6DG**	**NSYCUHD1K62P4DG**	**NSYCUHD2K3P4DG**



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Cooling Units

Accessories

Characteristics	Material		Filter	
				
	Steel	Stainless-steel	Fiber filter	Aluminum filter
			Filter not recommended for outdoor models	Filter recommended for outdoor models
Color			-	-
Supply			5 units	1 unit
Cooling units	**References**			
Side Indoor CU	**NSYCU350DG**	**NSYCUX350DG**	**NSYCUACC001DG**	**NSYCUACC005DG**
	NSYCU600DG	**NSYCUX600DG**	**NSYCUACC001DG**	**NSYCUACC005DG**
	NSYCU800DG	-	**NSYCUACC002DG**	**NSYCUACC006DG**
	NSYCU8002P4DG	-	**NSYCUACC002DG**	**NSYCUACC006DG**
	NSYCU1KDG	**NSYCUX1KDG**	**NSYCUACC002DG**	**NSYCUACC006DG**
	NSYCU1K2P4DG	**NSYCUX1K2P4DG**	**NSYCUACC002DG**	**NSYCUACC006DG**
	NSYCU1K2DG	-	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU1K22P4DG	-	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU1K6DG	**NSYCUX1K6DG**	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU1K62P4DG	-	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU2KDG	-	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU2K3P4DG	**NSYCUX2K3P4DG**	**NSYCUACC003DG**	**NSYCUACC007DG**
	NSYCU3K2DG	-	**NSYCUACC004DG**	**NSYCUACC008DG**
	NSYCU3K23P4DG	-	**NSYCUACC004DG**	**NSYCUACC008DG**
	NSYCU4K3P4DG	-	**NSYCUACC004DG**	**NSYCUACC008DG**
Roof indoor CU	**NSYCU600RDG**	-	**NSYCUACC010DG**	**NSYCUACC014DG**
	NSYCU800RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU8002P4RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU1K2RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU1K22P4RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU1K5RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU1K52P4RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU2KRDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU2K3P4RDG	-	**NSYCUACC011DG**	**NSYCUACC015DG**
	NSYCU3K3P4RDG	-	**NSYCUACC013DG**	**NSYCUACC017DG**
	NSYCU4K3P4RDG	-	**NSYCUACC013DG**	**NSYCUACC017DG**
Side outdoor CU	**NSYCUHD350DG**	-	-	**NSYCUACC005DG**
	NSYCUH600DG	-	-	**NSYCUACC005DG**
	NSYCUHD800DG	-	-	**NSYCUACC006DG**
	NSYCUHD1KDG	-	-	**NSYCUACC006DG**
	NSYCUHD1K2P4DG	-	-	**NSYCUACC006DG**
	NSYCUHD1K6DG	-	-	**NSYCUACC007DG**
	NSYCUHD1K62P4DG	-	-	**NSYCUACC007DG**
	NSYCUHD2K3P4DG	-	-	**NSYCUACC007DG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

	External condensate evaporator	Half-flush kit		Retrofit kit	
					
		Steel	Stainless-steel	Steel	Stainless-steel
	For water condensate evaporation	-	-	Kit to mount a new Cooling Unit in place of an existing Schneider Electric Cooling Unit from the previous range	Kit to mount a new Cooling Unit in place of an existing Schneider Electric Cooling Unit from the previous range
	-	RAL 7035 gray	-	RAL 7035 gray	-
	1 unit	1 unit	1 unit	1 unit	1 unit
	NSYCUACC009DG	**NSYCUACC034DG**	**NSYCUACC038DG**	-	-
	NSYCUACC009DG	**NSYCUACC034DG**	**NSYCUACC038DG**	**NSYCUACC032DG**	**NSYCUACC022DG**
	NSYCUACC009DG	**NSYCUACC035DG**	-	-	-
	NSYCUACC009DG	**NSYCUACC035DG**	-	-	-
	NSYCUACC009DG	**NSYCUACC035DG**	**NSYCUACC039DG**	-	-
	NSYCUACC009DG	**NSYCUACC035DG**	**NSYCUACC039DG**	-	-
	NSYCUACC009DG	**NSYCUACC036DG**	-	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC036DG**	-	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC036DG**	**NSYCUACC040DG**	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	**NSYCUACC029DG** - Flush **NSYCUACC030DG** - Half-flush **NSYCUACC031DG** - Surface
	NSYCUACC009DG	**NSYCUACC036DG**	-	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC036DG**	-	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC036DG**	**NSYCUACC040DG**	**NSYCUACC023DG** - Flush **NSYCUACC024DG** - Half-flush **NSYCUACC025DG** - Surface	**NSYCUACC029DG** - Flush **NSYCUACC030DG** - Half-flush **NSYCUACC031DG** - Surface
	NSYCUACC009DG	**NSYCUACC037DG**	-	**NSYCUACC026DG** - Flush **NSYCUACC027DG** - Half-flush **NSYCUACC028DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC037DG**	-	**NSYCUACC026DG** - Flush **NSYCUACC027DG** - Half-flush **NSYCUACC028DG** - Surface	-
	NSYCUACC009DG	**NSYCUACC037DG**	-	-	-
	NSYCUACC009DG	-	-	**NSYCUACC033DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC018DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC018DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC019DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC019DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC019DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC019DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC020DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC020DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC021DG**	-
	NSYCUACC009DG	-	-	**NSYCUACC021DG**	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-
	-	-	-	-	-

5


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Cooling Units

Dimensions

Side-Mounted Models: Dimensions and Cut-Outs


NSYCU-350-650DG



The Half-flush drawings are available on se.com

NSYCU350DG / NSYCUX350DG / NSYCU600DG / NSYCUX600DG


NSYCU-800-1KDG



The Half-flush drawings are available on se.com

NSYCU800DG / NSYCU8002P4DG / NSYCU1KDG / NSYCUX1KDG / NSYCU1K2P4DG / NSYCUX1K2P4DG

NSYCU-1K2-1K6-2KDG




The Half-flush drawings are available on se.com

NSYCU1K2DG / NSYCU1K22P4DG / NSYCU1K6DG / NSYCUX1K6DG / NSYCU1K62P4DG / NSYCU2KDG / NSYCU2K3P4DG / NSYCUX2K3P4DG

Indoor Side Cooling Unit Mounting Types Could Be either Surface, Half-Flush or Flush, and Out-Door Side Cooling Unit Mounting Type Is Only Surface.
Units of Measurement Are mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Side-Mounted Models: Dimensions and Cut-Outs



The Half-flush drawings are available on se.com

NSYCU3K2DG / NSYCU3K23P4DG / NSYCU4K3P4DG


Indoor Side Cooling Unit Mounting Types Could Be either Surface, Half-Flush or Flush, and Out-Door Side Cooling Unit Mounting Type Is Only Surface.
Units of Measurement Are mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


ClimaSys CU: Cooling Units

Dimensions


Outdoor Side-Mounted Models: Dimensions and Cut-Outs



NSYCUHD350DG / NSYCUHD600DG



NSYCUHD800DG / NSYCUHD1KDG / NSYCUHD1K2P4DG




NSYCUHD1K6DG / NSYCUHD1K62P4DG / NSYCUHD2K3P4DG


Indoor Side Cooling Unit Mounting Types Could Be either Surface, Half-Flush or Flush, and Out-Door Side Cooling Unit Mounting Type Is Only Surface.
Units of Measurement Are mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Roof-Mounted Models: Dimensions and Cut-Outs




NSYCU600RDG



NSYCU800RDG / NSYCU8002P4RDG / NSYCU1K2RDG / NSYCU1K22P4RDG / NSYCU1K5RDG / NSYCU1K52P4RDG



NSYCU2KRDG / NSYCU2K3P4RDG



NSYCU3K3P4RDG / NSYCU4K3P4RDG

Units of Measurement Are mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ProClima Software

Introduction

ProClima is an intuitive online tool that guides the selection of the suitable ClimaSys thermal management solution for control and electrical panels, based on key environmental and installation parameters.
Compare and select from multiple optimized solutions to enable reliable performance, prevent overheating and condensation, and optimize your thermal design from the earliest stage.

Benefits of ProClima

Flexible access and reporting

- Available on PC, tablet, and mobile
- Intuitive interface in multiple languages
- Generate thermal performance reports

Field Data and Diagnostics


- Import real operating data
- Detect overheating and condensation risks
- Perform accurate thermal diagnostics based on actual conditions

Comprehensive Technical Resources


- Direct access to technical documentation and enclosure catalogs
- Additional support through tutorials, videos, and application guides

Get started with ProClima

https://proclima.se.com



ProClima Software User Guide



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Key Features

Optimized Solution Selection

- Automatic heat balance calculation
- Based on key environmental and installations parameters (temperature, humidity, heat dissipation, sun radiation, pressure and altitude effects…) and installation conditions
- Accurate and reliable sizing

Multiple Solutions and Optimization

- Generate a range of alternative solutions for the same project
- Compare different technologies (fan, cooling unit, heat exchanger, heater)
- Optimize design to avoid over- or under-sizing

Solution Comparison and Cost Insight

- Compare solutions side by side (performance, size, characteristics)
- Evaluate different design options easily
- Built-in support for cost comparison between solution

Real Data Integration

- Import thermal data from dataloggers for accurate analysis
- Use real operating conditions for precise diagnostics
- Integrate weather data for outdoor projects

Reporting, BOM and Quotation

- Generate detailed thermal reports in multiple formats
- Export Bill of Materials (BOM)
- Prepare quotation requests for sending

Seamless Digital Integration

- Compatible with SEE Electrical 3D Panel+ by ETAP
- Export configurations for 3D panel design
- Help ensure continuity from design to assembly

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Accessories

Enclosure Installation Accessories

NSY2SPN124



NSYAEFPFSB



NSYPLHD



Cable Management Accessories

PB500023_35_nb



PB500218_32_nb



PB500218_32_nb



6

Equipment Mounting Accessories

PB500072_11_1



PB500222_45_nb



PB500188_35_nb



PB500223_25_nb



PB500084_43_nb



PB500217_29_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Contents

Enclosure Installation Accessories	**458**
Composition Accessories	458
Fixing Accessories	477
Lifting Accessories	482
Cable Management Accessories	**483**
Cable Entries	483
Cable Holding	504
Equipment Mounting Accessories	**508**
Equipment Assembly Accessories	508
Electrical Distribution and IT	542
Door Accessories	550
Maintenance Accessories	571

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Composition Accessories

Roof Canopy

Roof Canopy

CRN S3D


NSYTJ2015



- Direct fixing to the body of the enclosure by 4 M6 screws.
- Material: galvanized steel
- Finish: Epoxy-polyester paint
- Color: RAL 7035 gray

Supply:
Delivered with the fixings required for installation


Characteristics	Compatibility	Width (mm)	Depth (mm)	F (mm)	G (mm)	H (mm)	References
Roof canopy	CRN, S3D	200	150	36	75	23	**NSYTJ2015**
Roof canopy	CRN, S3D	300	150	36	75	23	**NSYTJ3015**
Roof canopy	CRN, S3D	400	150	36	75	23	**NSYTJ4015**
Roof canopy	CRN, S3D	500	200	36	130	23	**NSYTJ5020**
Roof canopy	CRN, S3D	600	200	36	130	23	**NSYTJ6020**
Roof canopy	CRN, S3D	300	200	36	130	23	**NSYTJ3020**
Roof canopy	CRN, S3D	400	200	36	130	23	**NSYTJ4020**
Roof canopy	CRN, S3D	400	250	42	150	48	**NSYTJ4025**
Roof canopy	CRN, S3D	500	250	42	150	48	**NSYTJ5025**
Roof canopy	CRN, S3D	600	250	42	150	48	**NSYTJ6025**
Roof canopy	CRN, S3D	800	250	42	150	48	**NSYTJ8025**
Roof canopy	CRN, S3D	600	300	42	200	48	**NSYTJ6030**
Roof canopy	CRN, S3D	800	300	42	200	48	**NSYTJ8030**
Roof canopy	CRN, S3D	1000	300	42	200	48	**NSYTJ10030**
Roof canopy	CRN, S3D	1200	300	42	200	48	**NSYTJ12030**
Roof canopy	CRN, S3D	600	400	42	300	48	**NSYTJ6040**
Roof canopy	CRN, S3D	800	400	42	300	48	**NSYTJ8040**
Roof canopy	CRN, S3D	1000	400	42	300	48	**NSYTJ10040**
Roof canopy	CRN, S3D	1200	400	42	300	48	**NSYTJ12040**

Roof Canopy

SM SFN


NSYSC630

- Provides excellent protection against splashes from rainwater.
- Canopy cannot be used together with lifting fixtures.
- PanelSeT SFN: when modular enclosures coupled, a single canopy with the total lenght must be used (example: one 1600-mm canopy with two coupled 800-mm enclosures).
  Canopies cannot be coupled together.
- Material: Galvanized steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray




Fixing:
PanelSeT SFN: Fixing by holes to be made in the roof of the enclosure
PanelSeT SM: Fixing by holes already made in the roof

Supply:
One canopy, drilling template and fixing elements

Characteristics	Compatibility	(B) Width (mm)	(C) Depth (mm)	References
Roof canopy	SM, SFN	600	300	**NSYSC630**
Roof canopy	SM, SFN	600	400	**NSYSC640**
Roof canopy	SM, SFN	600	600	**NSYSC660**
Roof canopy	SM, SFN	800	300	**NSYSC830**
Roof canopy	SM, SFN	800	400	**NSYSC840**
Roof canopy	SM, SFN	800	500	**NSYSC850**
Roof canopy	SM, SFN	800	600	**NSYSC860**
Roof canopy	SM, SFN	1000	300	**NSYSC1030**
Roof canopy	SM, SFN	1000	400	**NSYSC1040**
Roof canopy	SM, SFN	1000	500	**NSYSC1050**
Roof canopy	SM, SFN	1000	600	**NSYSC1060**
Roof canopy	SM, SFN	1200	300	**NSYSC1230**
Roof canopy	SM, SFN	1200	400	**NSYSC1240**
Roof canopy	SM, SFN	1200	500	**NSYSC1250**
Roof canopy	SM, SFN	1200	600	**NSYSC1260**
Roof canopy (used when coupling 2 enclosures together)	SM, SFN	1600	400	**NSYSC1640**
Roof canopy (used when coupling 2 enclosures together)	SM, SFN	1600	500	**NSYSC1650**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Roof Canopy



S3X

- Material: 304L stainless-steel sheet
- Finish: Scotch-Brite® brushed
- Thickness: 15/10e mm
- Installation: Direct fixing to the body of the enclosure.
- Canopy cannot be used together with lifting fixtures.

Supply:
Delivered with the fixings required for installation


NSYTX2015

				Dimensions (mm)					
Characteristics	**Compatibility**	**Width (mm)**	**Depth (mm)**	**A**	**B**	**C**	**D**	**E**	**References**
Roof canopy	S3X	200	150	205	183	51	120	-	**NSYTX2015**
Roof canopy	S3X	250	150	205	183	51	120	-	**NSYTX2515**
Roof canopy	S3X	300	150	305	183	51	220	-	**NSYTX3015**
Roof canopy	S3X	300	200	305	233	51	220	70	**NSYTX3020**
Roof canopy	S3X	400	200	405	233	70	320	70	**NSYTX4020**
Roof canopy	S3X	600	200	605	233	70	520	70	**NSYTX6020**
Roof canopy	S3X	600	250	605	283	70	520	120	**NSYTX6025**
Roof canopy	S3X	1000	300	1005	333	70	920	170	**NSYTX10030**
Roof canopy	S3X	500	250	505	283	70	420	120	**NSYTX5025**
Roof canopy	S3X	800	300	805	333	70	720	170	**NSYTX8030**

SMX

- Helps guarantee very high protection of the enclosure when used outdoors.
- Material: 304L stainless-steel sheet
  Other types of stainless-steel, contact us
- Finish: Scotch-Brite® brushed
- Other finishes, contact us
- Thickness 15/10e
- Installation: It is fixed in the same holes as the eyebolt.
- Canopy cannot be used together with lifting fixtures.

Supply:
Delivered with fixings. Other dimensions and canopy for sets, contact us


NSYSCMX10030

Characteristics	**Compatibility**	**Width (mm)**	**Depth (mm)**	References
Roof canopy	SMX	800	400	**NSYSCMX8040**
Roof canopy	SMX	800	500	**NSYSCMX8050**
Roof canopy	SMX	1000	300	**NSYSCMX10030**
Roof canopy	SMX	1000	400	**NSYSCMX10040**
Roof canopy	SMX	1200	400	**NSYSCMX12040**
Roof canopy	SMX	1600	600	**NSYSCMX16060**

SFX

Supply:
Delivered with fixings. Other dimensions and canopy for sets, contact us


NSYSCX6040

Characteristics	**Compatibility**	**Width (mm)**	**Depth (mm)**	References
Roof canopy	SFX	600	400	**NSYSCX6040**
Roof canopy	SFX	800	400	**NSYSCX8040**
Roof canopy	SFX	800	600	**NSYSCX8060**
Roof canopy	SFX	1000	600	**NSYSCX10060**
Roof canopy	SFX	1200	400	**NSYSCX12040**
Roof canopy	SFX	1200	600	**NSYSCX12060**
Roof canopy (used when coupling 2 SFX together)	SFX	1200	500	**NSYSCX12050**
Roof canopy (used when coupling 2 SFX together)	SFX	1600	400	**NSYSCX16040**
Roof canopy (used when coupling 2 SFX together)	SFX	1600	600	**NSYSCX16060**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Composition Accessories

Roof Canopy

Roof Canopy

PLA

- Can be installed in all enclosure models.
- High resistance to impacts, temperature and bad weather.
- Increases the height (A) of the enclosure by 38 mm without modifying its width or depth.
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray
- Installation: Essential for outdoor use



Supply:
Delivered with the fixings required for installation

NSYTJPLA53G

Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Roof canopy	PLA	500	320	**NSYTJPLA53G**
Roof canopy	PLA	500	420	**NSYTJPLA54G**
Roof canopy	PLA	750	320	**NSYTJPLA73G**
Roof canopy	PLA	750	420	**NSYTJPLA74G**
Roof canopy	PLA	750	620	**NSYTJPLA76G**
Roof canopy	PLA	1000	320	**NSYTJPLA103G**
Roof canopy	PLA	1000	420	**NSYTJPLA104G**
Roof canopy	PLA	1250	320	**NSYTJPLA123G**
Roof canopy	PLA	1250	420	**NSYTJPLA124G**
Roof canopy	PLA	1250	620	**NSYTJPLA126G**

Roof Airing Module

PHD

- Airing module to enable airing from the top of the enclosure (H = 95 mm).
- Material: Steel with anti-corrosive painting (C4H according ISO 12.944: 2018)
- Finish: Structured finish, 100% polyester powder
- Color: RAL 7035 gray



Supply:
1


NSYPCVR54HD

Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Roof airing module	PHD	750	420	**NSYPCVR74HD**
Roof airing module	PHD	1250	420	**NSYPCVR124HD**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Set of 2 Side Panels

SFN MCC

- Set of 2 side panels fixed from the outside of the enclosure.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
2 side panels, with sealing gasket and captive screws



NSY2SPN124

Characteristics	Compatibility	Height (mm)	Depth (mm)	References
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1200	400	**NSY2SPN124**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1200	500	**NSY2SPN125**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1200	600	**NSY2SPN126**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1200	800	**NSY2SPN128**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1400	400	**NSY2SPN144**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1400	500	**NSY2SPN145**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1400	600	**NSY2SPN146**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1400	800	**NSY2SPN148**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1600	400	**NSY2SPN164**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1600	500	**NSY2SPN165**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1600	600	**NSY2SPN166**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1600	800	**NSY2SPN168**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1800	400	**NSY2SPN184**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1800	500	**NSY2SPN185**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1800	600	**NSY2SPN186**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	1800	800	**NSY2SPN188**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2000	400	**NSY2SPN204**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2000	500	**NSY2SPN205**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2000	600	**NSY2SPN206**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2000	800	**NSY2SPN208**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2200	400	**NSY2SPN224**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2200	500	**NSY2SPN225**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2200	600	**NSY2SPN226**
Set of 2 side panels fixed from the outside of the enclosure	SFN, MCC	2200	800	**NSY2SPN228**

SFX

- Side panels including a polyurethane sealing gasket.
- Their special design helps guarantee the protection of the door gasket.
- 304L stainless-steel sheet


NSY2SPX184

Characteristics	Compatibility	Height of the enclosure (mm)	Depth of the enclosure (mm)	References
Set of 2 side panels	SFX	1800	400	**NSY2SPX184**
Set of 2 side panels	SFX	2000	400	**NSY2SPX204**
Set of 2 side panels	SFX	2000	500	**NSY2SPX205**
Set of 2 side panels	SFX	2000	600	**NSY2SPX206**

Accessories for Panels

SFN

- Trim cap for external fixing panels, both sides and rear
- Material: Polyamide 6
- Color: RAL 7035 gray

Supply:
50 units


NSYCSP

Characteristics	Compatibility	References
Trim cap for external fixing panels	SFN	**NSYCSP**

Partition Panel

SFN

- Partition panel for direct fixing to the structure, helps guarantee a water/dustproof protection of IP10 between enclosure suites.
- Material: Galvanized steel

Supply:
1 partition panel, sealing gasket and fixing elements


NSYPPS184

Characteristics	Compatibility	Height (mm)	Depth (mm)	References
Partition panel	SFN	1800	400	**NSYPPS184**
Partition panel	SFN	1800	500	**NSYPPS185**
Partition panel	SFN	1800	600	**NSYPPS186**
Partition panel	SFN	2000	400	**NSYPPS204**
Partition panel	SFN	2000	500	**NSYPPS205**
Partition panel	SFN	2000	600	**NSYPPS206**
Partition panel	SFN	2000	800	**NSYPPS208**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Panels

Side Plates

PLS


NSYTL27270G

- Ingress protection rating: IP65


Characteristics	Compatibility	For surfaces (mm)	Width (mm)	References
Side plate	PLS	270	200	**NSYTL27270G**
Side plate	PLS	360	290	**NSYTL27360G**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Coupling of Panel**SeT** Steel Enclosures

- Available in 2 versions:
  Coupling version without cable entry.
  Version with coupling frame allowing the entry of cables.
- Separation of 17 mm between 2 coupled enclosures, allowing full opening of the doors.
- Allows lateral coupling of 2 enclosures.
- These frames allow the door to open to 120°.
- Material: Fiberglass-reinforced polyester, self-extinguishing
- Ingress protection rating: IP66 according to IEC 60529



Coupling Spacers for Steel

CRN S3D

Supply:
Set of 4 spacers and their fixings. Mounting by screws, included


NSYAEUBUSC

Characteristics	Compatibility	References
Set of 4 coupling spacers	CRN, S3D	**NSYAEUBUSC**

Coupling Frames for Steel

CRN S3D


NSYAEUBU41SC

Characteristics	Compatibility	References
Coupling frame, 435 x 185 mm	S3D, CRN	**NSYAEUBU41SC**
Coupling frame, 635 x 185 mm	S3D, CRN	**NSYAEUBU61SC**

Coupling Frame for Polyester

PLS

Comment:
Use the dimensional drawings of the boxes to identify which coupling frame you need. Consider the sides and surfaces you will join. Not UL-certified.

- Ingress protection rating: Frame with full opening: IP65 between enclosures


NSYUM27180

Characteristics	Compatibility	For surfaces (mm)	Opening (mm)	References
Full-opening frame	PLS	180	110	**NSYUM27180**
Full-opening frame	PLS	270	200	**NSYUM27270**
Full-opening frame	PLS	360	290	**NSYUM27360**

Partial Opening Frame for Polyester

PLS

Supply:
References by unit. Order by multiples of 10 units (10, 20, 30, etc.)

- Ingress protection rating: Frame with full opening: IP44 between enclosures


NSYUCC270

Characteristics	Compatibility	For surfaces (mm)	Opening (mm)	References
Partial-opening frame	PLS	270	200	**NSYUCC270**
Partial-opening frame	PLS	360	290	**NSYUCC360**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Coupling

Standard Coupling Kit

SFN



NSYSFBK

- Used for joining enclosures side-to-side or depthwide.
- Fixing from the inside of the enclosure.
- Material: Flat connectors and brackets: Zinc-coated steel Sealing gasket: EPDM
- Ingress protection rating: IP55 according to IEC 60529 (**NSYSFBK**)

Supply:
4 brackets, 2 flat connectors, sealing gasket, fixing elements and 16 caps

Characteristics	Compatibility	References
Standard coupling kit	SFN	**NSYSFBK**

SM


NSYSMBK

- Used for joining enclosures side-to-side.
- Enclosures fixed from the inside.
- Material: 3 x 10 mm sealing gasket: EPDM
- Ingress protection rating: IP55 according to IEC 60529


Supply:
1 sealing gasket and fixing elements

Characteristics	Compatibility	References
Enclosure coupling kit	SM	**NSYSMBK**

Coupling Kit

TBS TBP


13934




The coupling kit allows you to join several boxes with dimensions from 138 x 93 mm.
- Material: Polystyrene, glow wire resistance: 650 °C according to IEC 60695-2-11
- Ingress protection rating: IP66 according to IEC 60529
- Installation: The kit is installed by drilling a hole with Ø 32 mm in the boxes to be coupled

Supply:
The kit consists of 2 linking parts, nuts and seals

Characteristics	Compatibility	Drilling Ø	Minor pack.	Reference
Coupling kit	TBS, TBP	32 mm	1	**13934**

Swing 19" Rack or PrismaSet HD Coupling Kit

SFX MCC


NSYSFBK19


- Used for joining enclosures equipped with swing 19" rack, side-to-side or depthwise.
- Fixing from the inside of the enclosures.
- Material: Flat connectors: Zinc-coated steel (**NSYSFBK19**); Sealing gasket: EPDM (**NSYSFXJG**)
- Ingress protection rating: IP55 according to IEC 60529
- For SFX NSYSFBK19 and NSYSFXJG are mandatory

Supply:
8 flat connectors, sealing gasket, fixing elements and 16 caps

Characteristics	Compatibility	References
Swing 19" rack coupling kit	SFX, MCC	**NSYSFBK19**
Coupling gasket for SFX	SFX	**NSYSFXJG**

Horizontal Coupling Kits, 15 mm, Joining Two Enclosures Mounted on ZA Plinths

PLA PLAT PHDT


NSYMUPLA53G

- For coupling two enclosures side by side.
- Coupling frame kit: Made up of a coupling kit and the fixings required for installation.
- Trim kit: Made up of two frames for aesthetic fitting of the two coupled enclosures.
- Coupling kit widths: 15 mm, joining two enclosures mounted on ZA plinths.
- Ingress protection rating: IP55 at the coupling point.


Note:
Not valid for coupling two enclosures using ZZ or ZH type plinth.


Characteristics	Compatibility	Depth (mm)	Height (mm)	References
Coupling frame kit 15 mm	PLA, PLAT, PHDT	320	500	**NSYMUPLA53G**
Coupling frame kit 15 mm	PLA, PLAT, PHDT	320	750	**NSYMUPLA73G**
Coupling frame kit 15 mm	PLA, PLAT	320	1000	**NSYMUPLA103G**
Coupling frame kit 15 mm	PLA, PLAT	320	1250	**NSYMUPLA123G**
Coupling frame kit 15 mm	PLA, PLAT	320	1500	**NSYMUPLA153G**
Coupling frame kit 15 mm	PLA, PLAT	420	500	**NSYMUPLA54G**
Coupling frame kit 15 mm	PLA, PLAT	420	750	**NSYMUPLA74G**
Coupling frame kit 15 mm	PLA, PLAT	420	1000	**NSYMUPLA104G**
Coupling frame kit 15 mm	PLA, PLAT	420	1250	**NSYMUPLA124G**
Coupling frame kit 15 mm	PLA, PLAT	420	1500	**NSYMUPLA154G**
Coupling frame kit 15 mm	PLA, PLAT	420	2000	**NSYMUPLA204G**
Trim kit for enclosure without canopy	PLA, PLAT	320	-	**NSYSUPLA3G**
Trim kit for enclosure with canopy	PLA, PLAT	320	-	**NSYSUPLA3TG**
Trim kit for enclosure without canopy	PLA, PLAT	420	-	**NSYSUPLA4G**
Trim kit for enclosure with canopy	PLA, PLAT	420	-	**NSYSUPLA4TG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Horizontal coupling kits, 35 mm, joining two enclosures mounted on ZZ or ZH plinths

PLAZ PLAZT PHDZT





NSYMUPLA103W


- For coupling two enclosures side by side.
- Coupling frame kit: Made up of a coupling kit and the fixings required for installation.
- Coupling kit widths: 35 mm, joining two enclosures mounted on ZZ or ZH plinths
- Ingress protection rating: IP55 at the coupling point

Note:
Not valid for coupling two enclosures using ZA plinths.

Characteristics	Compatibility	Depth (mm)	Height (mm)	References
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	320	1000	**NSYMUPLA103W**
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	320	1250	**NSYMUPLA123W**
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	320	1500	**NSYMUPLA153W**
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	420	1000	**NSYMUPLA104W**
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	420	1250	**NSYMUPLA124W**
Coupling frame kit 35 mm	PLAZ, PLAZT, PHDZT	420	1500	**NSYMUPLA154W**

Vertical Coupling Kit

PLA



DB300634_27_nb

NSYUVPLA

- For coupling two enclosures on top of one another.
- Set of 3.5 m of adhesive seal and the fixings required for mounting.
- Ingress protection rating: IP55 at the coupling point.

Characteristics	Compatibility	References
Vertical coupling kit	PLA	**NSYUVPLA**

Reinforced Coupling

SFN



NSYSFBKR


- It is used together with the coupling kit to reinforce the connection between 2 enclosures when they carry heavy loads.
- Fixing from the inside of the enclosures.
- Material: Zinc-coated steel.

Supply:
4 reinforced connectors and fixing elements

Characteristics	Compatibility	References
Reinforced coupling	SFN	**NSYSFBKR**

Quick Coupling

SFN



NSYSFBKF

- Used for quickly joining 2 enclosures.
- Fixing from the inside of the enclosures.
- Material: Zinc-coated steel

Supply:
4 flat links and fixing elements

Characteristics	Compatibility	References
Quick coupling	SFN	**NSYSFBKF**

External Coupling

SFN



NSYSFBKE

- Allows two enclosures to be joined by their structure.
- To be used with the NSYSFBK standard coupling kit when the front and rear uprights are not accessible.
- The mounting plate or vertical uprights fixed to the back of the enclosure help prevent the assembly and dismantling of the kit.
- It can be combined with the reinforced or the quick coupling kit.
- Material: External connectors: Zinc-coated steel.
- The gasket and brackets from the standard coupling kit NSYSFBK still need to be installed.

Supply:
4 external connectors and fixing elements

Characteristics	Compatibility	References
External coupling	SFN	**NSYSFBKE**


Box Coupling Unit Piece

PLS





NSYPS2C27



DB300604_58_nb

- For coupling 2, 3 or 4 boxes, with optional wall-mounted.
- M6 x 8 mm screw with cylindrical head.

Supply:
To be ordered in multiples of 25

Characteristics	Compatibility	References
Box coupling unit piece for coupling 2 boxes	PLS	**NSYPS2C27**
Box coupling unit piece for coupling 3 or 4 boxes	PLS	**NSYPS4C27**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories


Pillars

Support Pillar

S3D


NSYCOCN80

- The support pillar is fixed directly to the bottom face of the PanelSeT steel enclosure by means of an adapter plate.
- The adapter plate, to be ordered in addition to the pillar, replaces the cable gland plate.
- Overall height of the support foot: 800 mm.
- Mounting possible on all enclosures with dimensions up to 600 x 400 x 250 mm (except 200 x 200 x 150 mm and 250 x 200 x 150 mm enclosures).
- Material: Extruded aluminum
- Finish: Epoxy polyester paint
- Color: RAL 7035 gray



Characteristics	Compatibility	Height (mm)	References
Support pillar	S3D	800	**NSYCOCN80**

Support Pillar Adaptation Plate

S3D


NSYAEFP42S3D

- Description: Plate for fixing the support pillar on the enclosure.
- This plate replaces the cable gland plate delivered with the enclosure.
- Material: Steel
- Finish: Polyester powder
- Color: RAL 7035 gray

Characteristics	Compatibility	For enclosure width (mm)	For enclosure depth (mm)	References
Support pillar adaptation plate	S3D	400	200-250	**NSYAEFP42S3D**

Support Bracket for Enclosure with Anti-Tilt Kit and Reinforcement

CRN S3D S3HF S3X PLM


NSYCOCNS1400


- The support bracket is used when the enclosure cannot be hung from a wall or a post.
- Maximum enclosure dimensions: 1000 x 800 x 300 mm.
- Floor attachment by standard M12 fastenings.
- Material: Steel
- Finish: Epoxy polyester paint
- Color: RAL 7035 gray
- Maximum load: 120 kg

Characteristics	Compatibility	Height (mm)	References
Support bracket for enclosure with anti-tilt kit and reinforcement	CRN, S3D, S3HF, S3X, PLM	1400	**NSYCOCNS1400**
Support bracket for enclosure with anti-tilt kit and reinforcement	CRN, S3D, S3HF, S3X, PLM	1800	**NSYCOCNS1800**

Floor-Mounted Pillar

PLM

To help protect cables entering the enclosure in outdoor installations.
Cable entry section: 165 x 100 mm.
For enclosures ref. **NSYPLM54G**, **NSYPLM54TG**, **NSYPLM64G** and **NSYPLM64TG**.




NSYSFSPLMG

- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray

Supply:
Delivered with steel frame for secure fixing to the floor


Characteristics	Compatibility	Reference
Floor-mounted pillar	PLM	**NSYSFSPLMG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Plinth as a Kit

The complete plinth consists of two elements, one is the front and rear kit, determined by the width of the enclosure, and the other consists of the side panels which determine the depth of the enclosure. The number of side panels required depends on the plinth combination.

- Robust design.
- The modular plinth system makes it possible to reduce the number of references in stock.


Characteristics	Front and rear kit	Side panels	Complete plinth
Plinth height 100 mm			
Plinth height 200 mm			

Floor

Examples of Solutions

Plinth Cross-Rail Fixed in Position B, Requires 2 Cross-Rails Fixed in Position A.

- They are fixed to the plinth cross-rails, both the universal and the quick-fixing types.
- Their depth is adjustable in increments of 25 mm.



Comment: Universal and quick-fixing cross-rail references, page 525


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Plinths


Possibility of Joining Plinths

PB500545_35_nb




The surfaces between corners are always in contact.
They are joined by a M8 screw and nut, not included in the standard supply.
⊕ Longitudinally free space for passing cables
⊕ Greater rigidity of the resulting assembly unit

PB500545_35_nb




PB500547_35_nb



Side panels
are secured by M6 screws and caged nuts, not included in the standard supply, reference **NSYSPM6** and reference **NSYCN9M625**, which can be mounted above and/or below.
⊕ Improves rigidity in the depthwise direction during transport


PB500548_35_nb



Vertical plinth assembly
are secured by means of M12 screws and nuts, not included in the standard supply.


Possibility of Fixing the Enclosure to the Plinth

PB500549_38_nb



Fixing from the inside of the enclosure
by means of an M12 screw, screwing directly into the corner of the plinth.
⊕ Fixing convenience and speed

PB500550_36_nb



Fixing from the outside of the enclosure
with a M12 screw, screwing directly onto the vertical upright.
⊕ Maximum rigidity of the enclosure-plinth assembly

6


Options to Fix the Plinth to the Floor

PB500551_22_NB




Fixing from the inside of the enclosure.
The machining angle varies according to the plinth model:
- Plinth height 100 mm φ = 18°.
- Plinth height 200 mm φ = 9°.

PB500552_27_NB



Fixing from the outside of the enclosure, optimal point for the rigidity of the assembly.
The machining angle varies according to the plinth model:
- Plinth height 100 mm φ = 22°.
- Plinth height 200 mm φ = 11°.


NSYSGF_nb



Floor-fixing supports can be used as well.
Brackets **NSYSGF** for fixing plinth to the floor if the drillholes made in the plinth cannot be used.
It can be to the corner, or between corner and panel.

Fixing the Enclosure to the Plinth


PB500555_33_NB



Fixing from the inside of the enclosure
by means of a M12 screw, screwing directly into the corner of the plinth
- Fixing convenience and speed.

Fixing the Enclosure Against a Wall

PB500555_33_NB



Enclosure against a wall.
Thanks to the design of the corners, when the enclosure is installed against the wall, the external fixing point can still be accessible by removing the plinth side panels and turning the back corners.

Assembly of the Plinth Panels


PB500556_23_NB




The panels are fixed with an M6 screw to the corner included in the standard supply of the side panels.
- The front and rear panels are delivered with the corners mounted.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Front and Rear Plinths



B: Width
C: Height



Installation:
It is necessary to order separately the plinth fixing kit (ref. **NSYAPFWM**) composed by fixing hardware and drilling jig.

Note:
For more information see page 467

Supply:
Height 100 mm: 4 corners, 2 panels (front and rear), 4 corner covers and fixing elements
Height 200 mm: 4 corners, 4 panels (2 front and 2 rear), 4 corner covers and fixing elements

CRN S3D SM SFN MCC SFN PC SD SFN IT

- The front and rear of the plinth consists of 4 corners with 2 or 4 panels.
- Material: Folded sheet steel, corner with a thickness of 25/10e mm
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7022 gray
- Ingress protection rating: IP20 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262


NSYSPF3100


NSYSPF3200

Characteristics	Compatibility	Width (mm)	Height (mm)	References
Front and rear plinths	SFN, MCC, SFN PC, SFN IT	300	100	**NSYSPF3100**
Front and rear plinths	SFN, MCC, SFN PC, SFN IT	400	100	**NSYSPF4100**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	600	100	**NSYSPF6100**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	800	100	**NSYSPF8100**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	1000	100	**NSYSPF10100**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	1200	100	**NSYSPF12100**
Front and rear plinths	SM, SFN, MCC, SFN PC, SFN IT	1600	100	**NSYSPF16100**
Front and rear plinths	SFN, MCC, SFN PC, SFN IT	300	200	**NSYSPF3200**
Front and rear plinths	SFN, MCC, SFN PC, SFN IT	400	200	**NSYSPF4200**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	600	200	**NSYSPF6200**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	800	200	**NSYSPF8200**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	1000	200	**NSYSPF10200**
Front and rear plinths	CRN, S3D, SM, SFN, MCC, SFN PC, SD, SFN IT	1200	200	**NSYSPF12200**
Front and rear plinths	SM, SFN, MCC, SFN PC, SFN IT	1600	200	**NSYSPF16200**


Plinth Side Panels

SM SFN MCC SFN IT

- They are fixed to the corner of the plinth by 2 fixing screws.
- Material: Folded sheet steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7022 gray
- Ingress protection rating: IP20 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Supply:
Height 100 mm: 2 side panels, 4 corner covers and fixing elements
Height 200 mm: 4 side panels (height of 100 mm, 2 for each side), 4 corner covers and fixing elements


NSYSPS3100


NSYSPS3200

Characteristics	Compatibility	Depth (mm)	Height (mm)	References
Side plinths	SM	300	100	**NSYSPS3100**
Side plinths	SM, SFN, MCC, SFN IT	400	100	**NSYSPS4100**
Side plinths	SM, SFN, MCC, SFN IT	500	100	**NSYSPS5100**
Side plinths	SM, SFN, MCC, SFN IT	600	100	**NSYSPS6100**
Side plinths	SFN, MCC, SFN IT	800	100	**NSYSPS8100**
Side plinths	SFN, MCC, SFN IT	1000	100	**NSYSPS10100**
Side plinths	SFN, MCC, SFN IT	1200	100	**NSYSPS12100**
Side plinths	SM	300	200	**NSYSPS3200**
Side plinths	SM, SFN, MCC, SFN IT	400	200	**NSYSPS4200**
Side plinths	SM, SFN, MCC, SFN IT	500	200	**NSYSPS5200**
Side plinths	SM, SFN, MCC, SFN IT	600	200	**NSYSPS6200**
Side plinths	SFN, MCC, SFN IT	800	200	**NSYSPS8200**
Side plinths	SFN, MCC, SFN IT	1000	200	**NSYSPS10200**
Side plinths	SFN, MCC, SFN IT	1200	200	**NSYSPS12200**

CRN S3D SD

Characteristics	Compatibility	Depth (mm)	Height (mm)	References
Side plinths	CRN, S3D	300	100	**NSYSPS3100SD**
Side plinths	CRN, S3D, SD	400	100	**NSYSPS4100SD**
Side plinths	SD	500	100	**NSYSPS5100SD**
Side plinths	SD	600	100	**NSYSPS6100SD**
Side plinths	CRN, S3D	300	200	**NSYSPS3200SD**
Side plinths	CRN, S3D, SD	400	200	**NSYSPS4200SD**
Side plinths	SD	500	200	**NSYSPS5200SD**
Side plinths	SD	600	200	**NSYSPS6200SD**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Plinths

Stainless-Steel Plinths

- Material: Stainless-steel, AISI 304L or AISI 316L
- Finish: Scotch-Brite® brushing, to help guarantee the durability in application where the contact with the floor increases the risk of corrosion
- Installation: Plinth fixing kit must be ordered separately (ref. **NSYAPFXWM**) composed by fixing elements and drilling jig

CRN S3X SMX SFX SFN SM S3HD SFN HD SD



NSYSPFX10100

Characteristics	Compatibility	W (mm)	H (mm)	References
Plinth H 100 mm, Kit (4 corners + front and back), AISI 304L	SMX, SFX, SFN, SM, S3HD, SFN HD, SD	600	100	**NSYSPFX6100**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 304L	CRN, S3X, SMX, SFX, SFN, SM, SFN HD, SD	800	100	**NSYSPFX8100**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 304L	CRN, S3X, SMX, SFX, SFN, SM, SFN HD, SD	1000	100	**NSYSPFX10100**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 304L	SMX, SFX, SFN, SM, SFN HD, SD	1200	100	**NSYSPFX12100**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 304L	SMX, SFN, SM, SFN HD	1600	100	**NSYSPFX16100**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 316L	CRN, S3X, SMX	800	100	**NSYSPFX8100H**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 316L	CRN, S3X, SMX	1000	100	**NSYSPFX10100H**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 316L	SMX	1200	100	**NSYSPFX12100H**
Plinth H 100 mm, Kit (4 corners + front and back), AISI 316L	SMX	1600	100	**NSYSPFX16100H**

CRN S3X SMX S3HD SD



NSYSPSX3100

Characteristics	Compatibility	D (mm)	H (mm)	References
Plinth H 100 mm, Set of 2 side panels, AISI 304L	S3X, SMX, CRN, S3HD	300	100	**NSYSPSX3100**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SMX, S3HD	400	100	**NSYSPSX4100**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SMX, SD	500	100	**NSYSPSX5100**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SMX	600	100	**NSYSPSX6100**
Plinth H 100 mm, Set of 2 side panels, AISI 316L	SMX	400	100	**NSYSPSX4100H**
Plinth H 100 mm, Set of 2 side panels, AISI 316L	SMX	500	100	**NSYSPSX5100H**
Plinth H 100 mm, Set of 2 side panels, AISI 316L	SMX	600	100	**NSYSPSX6100H**

SFX SFN SM SFN HD

Characteristics	Compatibility	D (mm)	H (mm)	References
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SFX, SFN, SM, SFN HD	400	100	**NSYSPSX4100SF**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SFX, SFN, SM, SFN HD	500	100	**NSYSPSX5100SF**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SFX, SFN, SM, SFN HD	600	100	**NSYSPSX6100SF**
Plinth H 100 mm, Set of 2 side panels, AISI 304L	SFN, SM, SFN HD	800	100	**NSYSPSX8100SF**

CRN S3X SMX SFX SFN SM S3HD SFN HD SD



NSYSPFX8200

Characteristics	Compatibility	W (mm)	H (mm)	References
Plinth H 200 mm, Kit (4 corners + front and back), AISI 304L	S3X, SMX, SFX, SD, S3HD, SFN HD	600	200	**NSYSPFX6200**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 304L	S3X, SMX, SFX, SD, CRN, S3HD, SFN HD	800	200	**NSYSPFX8200**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 304L	S3X, SMX, SFX, SD, CRN	1000	200	**NSYSPFX10200**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 304L	S3X, SMX, SFX, SD, SFN HD	1200	200	**NSYSPFX12200**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 304L	SMX	1600	200	**NSYSPFX16200**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 316L	S3X, SMX, CRN	800	200	**NSYSPFX8200H**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 316L	S3X, SMX, CRN	1000	200	**NSYSPFX10200H**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 316L	SMX	1200	200	**NSYSPFX12200H**
Plinth H 200 mm, Kit (4 corners + front and back), AISI 316L	SMX	1600	200	**NSYSPFX16200H**

CRN S3X SMX S3HD SD



NSYSPSX3200

Characteristics	Compatibility	D (mm)	H (mm)	References
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	S3X, SMX, S3HD, SFN HD, CRN	300	200	**NSYSPSX3200**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SMX, S3HD, SFN HD	400	200	**NSYSPSX4200**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SD, SMX	500	200	**NSYSPSX5200**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SMX	600	200	**NSYSPSX6200**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 316L	SMX	400	200	**NSYSPSX4200H**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 316L	SMX	500	200	**NSYSPSX5200H**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 316L	SMX	600	200	**NSYSPSX6200H**

SFX SFN SM SFN HD

Characteristics	Compatibility	D (mm)	H (mm)	References
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SFX, SFN HD	400	200	**NSYSPSX4200SF**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SFX	500	200	**NSYSPSX5200SF**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SFX, SFN HD	600	200	**NSYSPSX6200SF**
Plinth H 200 mm, Set of 2 side panels (x2), AISI 304L	SFN, SM, SFN HD	800	200	**NSYSPSX8200SF**

Stainless-steel plinths (standard plinths page 470, ventilated plinths page 471) are compatible with steel floor-standing enclosure SM and SFN using an earthing cable section 6 mm², length 220 mm, eyelet hole 13 mm. Not included in the delivery of the plinths.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Ventilated Plinths, Front and Rear Kit

S3HD SFN HD


NSYSPFVX6200

- The front and rear of the plinth consists of 4 corners with 2 panels.

Supply:
1 kit

Characteristics	Compatibility	Width (mm)	References
Ventilated plinths, front and rear kit	S3HD, SFN HD	600	**NSYSPFVX6200**
Ventilated plinths, front and rear kit	S3HD, SFN HD	800	**NSYSPFVX8200**
Ventilated plinths, front and rear kit	SFN HD	1200	**NSYSPFVX12200**

Ventilated Plinths, Lateral Kit

SFN HD


NSYSPLVX4200SF

- They are fixed to the corner of the plinth by fixing screws.

Supply:
1 kit

Characteristics	Compatibility	Depth (mm)	References
Ventilated plinths, for floor-standing enclosure	SFN HD	430	**NSYSPLVX4200SF**
Ventilated plinths, for floor-standing enclosure	SFN HD	630	**NSYSPLVX6200SF**

Ventilated Front Plinth

SM SFN
SFN IT


NSYSPFV6100

- The front and rear of the ventilated plinth is made up of 4 corners with 2 front panels.
- Material: Folded sheet steel, corner with a thickness of 25/10^{e} mm
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7022 gray
- Ingress protection rating: IP20 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Supply:
Height 100 mm: 4 corners, 2 ventilated panels (front and rear), 4 corner covers and fixing elements

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Ventilated front plinth	SFN, SM, SFN IT	100	600	**NSYSPFV6100**
Ventilated front plinth	SFN, SM, SFN IT	100	800	**NSYSPFV8100**

Ventilated Side Panels

SM SFN
SFN IT


NSYSPV6100


- They are fixed to the corner of the plinth by fixing screws.
- Material: Folded sheet steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7022 gray
- Ingress protection rating: IP20 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262


Supply:
Height 100 mm: 2 ventilated side panels, 4 corner covers and fixing elements

Characteristics	Compatibility	Height (mm)	Depth (mm)	References
Ventilated side panels	SM, SFN, SFN IT	100	600	**NSYSPV6100**
Ventilated side panels	SM, SFN, SFN IT	100	800	**NSYSPV8100**

Panels with Brush

SM SFN
SFN IT


NSYSPB6100



- They allow the entry and fixing of cables inside the enclosure, through the plinth.
- Material: Folded sheet steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7022 gray
- Ingress protection rating: IP20 according to IEC 60529
- Mechanical protection rating: IK10 according to IEC 62262

Supply:
Height 100 mm: 2 panels with brushes, 4 corner covers and fixing elements

Characteristics	Compatibility	Height (mm)	Depth (mm)	References
Panels with brush	SM, SFN, SFN IT	100	600	**NSYSPB6100**
Panels with brush	SM, SFN, SFN IT	100	800	**NSYSPB8100**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Plinths

Plinths

PLM

- Designed to support and raise enclosures **NSYPLM75G**, **NSYPLM86G** and **NSYPLM108G**.
- Plinth height of 200 mm; stackable to obtain a 400 mm plinth.
- Four floor attachment points; symmetry of the parts helps prevent incorrect assembly.
- The front parts of the plinth (front and rear) have two stainless-steel screws protected by a plastic cap; these screws make it possible (using an Allen key) to open and remove the front parts for easier cable installation. In stacked position, the bottom plinth can be partially buried. It is provided with one transverse reinforcement rail, adjustable to adapt to the position of the cables. The reference of the plinth contains all the accessories required for attaching the enclosure to the plinth and for stacking two plinths.
- Material: Polyester reinforced with fiberglass, molded by hot compression
- Ingress protection rating: IP44
- Mechanical protection rating: IK10
- Standards: Helps guarantee full insulation according to IEC 61439-1

PB502788_26_nb
PB502772_25_nb



Characteristics	Compatibility	PLM enclosure	Height (mm)	Width (mm)	Depth (mm)	Reference
Plinth	PLM	NSYPLM75G	200	456	302	**NSYZM253G**
Plinth	PLM	NSYPLM86G	200	556	302	**NSYZM263G**
Plinth	PLM	NSYPLM108G	200	772	352	**NSYZM283G**

Kit for IP54

PLM



NSYAEPZM

Required to obtain IP54 for the plinth and the plinth enclosure coupling.

Characteristics	Compatibility	Reference
Kit for IP54	PLM	**NSYAEPZM**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ZA Plinths

PLA PLAT PHDT


PB503709_nb
PB503696_nb

- The front parts of the plinth (front and rear) have two stainless-steel screws protected by a plastic cap; these screws, which can be accessed from the outside, make it possible (using an Allen key) to open and remove the front parts for easier cable installation.
- In stacked position, the bottom plinth can be partially buried.
- It is provided with one or two reinforcement cross-rails, adjustable to adjust to the position of the cables.
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray
- Ingress protection rating: IP44
- Mechanical protection rating: IK10
- Fixing: Four floor attachment points; symmetry of the parts helps prevent incorrect assembly
- Supply: The reference of the plinth contains all the accessories required for attaching the enclosure to the plinth and for stacking two plinths

For floor-standing enclosure			Plinth		Cable gland area		Height 200 mm	
W (mm)	D (mm)	References	W (mm)	D (mm)	W (mm)	D (mm)	References	Compatibility
500	320	**NSYPLA(T)●53G**	494	250	360	205	**NSYZA253G**	PLA, PLAT, PHDT
750	320	**NSYPLA(T)●73G**	744	250	610	205	**NSYZA273G**	PLA, PLAT, PHDT
1000	320	**NSYPLA(T)●103G**	994	250	860	205	**NSYZA2103G**	PLA, PLAT, PHDT
1250	320	**NSYPLA(T)●123G**	1244	250	1100	205	**NSYZA2123G**	PLA, PLAT, PHDT
500	420	**NSYPLA(T)●54G**	494	350	360	305	**NSYZA254G**	PLA, PLAT, PHDT
750	420	**NSYPLA(T)●74G**	744	350	610	305	**NSYZA274G**	PLA, PLAT, PHDT
1000	420	**NSYPLA(T)●104G**	994	350	860	305	**NSYZA2104G**	PLA, PLAT, PHDT
1250	420	**NSYPLA(T)●124G**	1244	350	1110	305	**NSYZA2124G**	PLA, PLAT, PHDT
750	620	**NSYPLA(T)●76G**	744	550	610	505	**NSYZA276G**	PLA, PLAT, PHDT
1250	620	**NSYPLA(T)●126G**	1244	550	1110	505	**NSYZA2126G**	PLA, PLAT, PHDT

ZZ Plinths

PLAZ PLAZT PHDZT


PB503698_nb
PB503697_nb

- The front parts (front and rear) are removed from the inside. Removing them makes it easier to install the cables.
- The 500-mm plinth can be partially buried.
- It is provided with one or two reinforcement cross-rails, adjustable to adapt to the position of the cables.
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray
- Ingress protection rating: IP44
- Mechanical protection rating: IK10
- Fixing: Four floor attachment points; symmetry of the parts helps prevent incorrect assembly
- Supply: The reference of the plinth contains all the accessories required for attaching the enclosure to the plinth

(1) For enclosures using ZZ or ZH type plinths the coupling kit to use is the **NSYMUPLA●●●W**.

For floor-standing enclosure			Plinth		Cable gland area		Height 200 mm		Height 500 mm	
W (mm) (B)	D (mm) (C)	References	W (mm)	D (mm)	W (mm)	D (mm)	References	Compatibility	References	Compatibility
500	320	**NSYPLAZ(T)●53G**	535	310	419	252	**NSYZZ253G**	PLAZ, PLAZT, PHDZT	**NSYZZ553G**	PLAZ, PLAZT, PHDZT
750	320	**NSYPLAZ(T)●73G**	785	310	669	252	**NSYZZ273G**	PLAZ, PLAZT, PHDZT	**NSYZZ573G**	PLAZ, PLAZT, PHDZT
1000	320	**NSYPLAZ(T)●103G**	1035	310	919	252	**NSYZZ2103G**	PLAZ, PLAZT, PHDZT	**NSYZZ5103G**	PLAZ, PLAZT, PHDZT
1250	320	**NSYPLAZ(T)●123G**	1285	310	1169	252	**NSYZZ2123G**	PLAZ, PLAZT, PHDZT	**NSYZZ5123G**	PLAZ, PLAZT, PHDZT
500	420	**NSYPLAZ(T)●54G**	535	410	419	352	**NSYZZ254G**	PLAZ, PLAZT, PHDZT	**NSYZZ554G**	PLAZ, PLAZT, PHDZT
750	420	**NSYPLAZ(T)●74G**	785	410	669	352	**NSYZZ274G**	PLAZ, PLAZT, PHDZT	**NSYZZ574G**	PLAZ, PLAZT, PHDZT
1000	420	**NSYPLAZ(T)●104G**	1035	410	919	352	**NSYZZ2104G**	PLAZ, PLAZT, PHDZT	**NSYZZ5104G**	PLAZ, PLAZT, PHDZT
1250	420	**NSYPLAZ(T)●124G**	1285	410	1169	352	**NSYZZ2124G**	PLAZ, PLAZT, PHDZT	**NSYZZ5124G**	PLAZ, PLAZT, PHDZT
750	620	**NSYPLAZ(T)●76G**	785	610	669	552	**NSYZZ276G**	PLAZ, PLAZT, PHDZT	-	-
1250	620	**NSYPLAZ(T)●126G**	1285	610	1169	552	**NSYZZ2126G**	PLAZ, PLAZT, PHDZT	-	-

N Plinths

PLA PLAT


NSYZNPLA53G

Designed to be installed under the closed bottom enclosures (version PLA or PLAT).
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray
- Height 60 mm

Supply:
Delivered with fixings required for installation

Characteristics	Compatibility	References
N plinths	PLA, PLAT	**NSYZNPLA53G**
N plinths	PLA, PLAT	**NSYZNPLA73G**
N plinths	PLA, PLAT	**NSYZNPLA103G**
N plinths	PLA, PLAT	**NSYZNPLA123G**
N plinths	PLA, PLAT	**NSYZNPLA54G**
N plinths	PLA, PLAT	**NSYZNPLA74G**
N plinths	PLA, PLAT	**NSYZNPLA104G**
N plinths	PLA, PLAT	**NSYZNPLA124G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Plinths

Connectors Between Plinths

PLA PLAT


Description: Designed to allow the adaptation of a closed bottom enclosure
+ N plinth on a H-type partially buried plinth.


NSYPLA or
NSYPLAT
not for
NSYPLAZ●●●

NSYZNPLA●●●

NSYAZ●●●

NSYZHPLA●●●





Supply:
Two parts for adapting the center-to-center distances.


NSYAZ3PLA

Characteristics	Compatibility	For floor-standing enclosure Depth (mm)	References
Linking parts for N plinth on 320 mm H plinth	PLA, PLAT	320	**NSYAZ3PLA**
Linking parts for N plinth on 420 mm H plinth	PLA, PLAT	420	**NSYAZ4PLA**


Buriable H Plinths

PLAZ PLAZT


NSYZHPLA53G


NSYZHPLA53G

- Front panel with a height of 170 mm, retractable, providing easy access to the inside.
- Fixed front panel with a height of 305 mm, corresponding to the finished floor height area.
- The height above the floor after built-in varies between 200 and 500 mm.
- A metal rail helps to fix the entry cables.
- Lateral uprights with knock-out auxiliary output with Ø Pg 36 (48 mm).
- A knock-out area is provided at the bottom of the lateral uprights for cable entry, if necessary.
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray



Supply:
Delivered with the fixings required for installation

Characteristics	Compatibility	References
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA53G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA73G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA103G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA123G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA54G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA74G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA104G**
Buriable H plinths	PLAZ, PLAZT	**NSYZHPLA124G**

Outside Opening Kit

PLAZ PLAZT

- Description: The 200 mm front part of the 200 and 500 mm plinths can be opened from the outside, after installing a set of two locks with double-bar insert.


NSYAELZ

Characteristics	Compatibility	References
Outside opening kit	PLAZ, PLAZT	**NSYAELZ**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Feet for Partially Buried Installation

PLM PLA PLAT PLAZ PLAZT

Description: Allows the partially buried installation of plinths before completion of the floor. The plinths are attached by four feet with a standard length of 750 mm. Option of horizontal adjustment of the plinth.


Supply:
Kit includes four feet and fixings.



Characteristics	Compatibility	References
Feet for partially buried installation	PLM, PLA, PLAT, PLAZ, PLAZT	**NSYAEBFZ**

Fixing to the Floor

CRN S3D SM SFN




NSYSGF

- Part for fixing the plinth to the floor if the drillholes made in the plinth cannot be used.
- Material: Steel
- Finish: Zinc-coated

Supply:
4 pieces, fixing element not supplied

Characteristics	Compatibility	References
Fixing to the floor	CRN, S3D, SM, SFN	**NSYSGF**

Plinth Cross-Rail Support

CRN S3D SM SFN



Comment:
Reference by unit Order by multiples of 12 (12, 24, 36…)


NSYSPCR


- Support for fixing a cross-rail inside the plinth.
- Material: Steel
- Finish: Zinc-coated

Supply:
12 pieces and fixing elements

Characteristics	Compatibility	References
Plinth cross-rail support, 100 mm	CRN, S3D, SM, SFN	**NSYSPCR**

Fixing Options, Levelling the Plinth

SFN SFN IT MCC


NSYSPLK

- The plinth allows levelling by means of a M12 screw.

Characteristics	Compatibility	References
Levelling the plinth	SFN, SFN IT, MCC	**NSYSPLK**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Composition Accessories

Other Accessories

Sealed Pressure Balance Valve

TBS TBP PLS PLM

Balances the pressure to avoid condensation and/or deformations of the boxes due to internal temperature changes. Protection of equipment for luminaires, industrial control, transportation, pumps, etc.

- Material: PA6-V2, acrylic co-polymer membrane, water and oil repellent
- Ingress protection rating: IP68
- Installation: The valve is installed by drilling a hole with Ø 12 mm in the box
- Operating temperature: -40...+105 °C
- Permeability: Air flow under ΔP = 0.7 bar
- Pressure difference: Condition for IP68

Supply:
10 valves, nuts and seals


NSYCAG12LPH1

Characteristics	Compatibility	Permeability	Pressure difference	Drilling Ø	Minor pack.	Reference
Sealed pressure balance valve IP68	TBS, TBP, PLS, PLM	16 litres/h	ΔP < 1 bar	12 mm	1	**NSYCAG12LPH1**
Sealed pressure balance valve IP68	TBS, TBP, PLS, PLM	120 litres/h	ΔP < 0.1 bar	12 mm	1	**NSYCAG12LPH2**

Airing Louvres

PLM

- They can be positioned inside the wall-mounted enclosures with heights from 430 to 846 mm, allowing airing through the channels of the enclosure.

Supply:
References by unit. Order by multiples of 2 units (2, 4, 6, etc.)


NSYCAG35LP

Characteristics	Compatibility	References
Airing louvres	PLM	**NSYCAG35LP**

Water Drain Plug

PLM

- For drainage of condensed water. (Condensation should be eliminated using ClimaSys solution.) It is placed in the Ø 8.5 mm (8.2 mm for wall-mounted enclosures **NSYPLM32G**, **NSYPLM32TG**, **NSYPLM32PG** and **NSYPLM32BG** diverse accessories) housing at the bottom of the enclosure.
- Ingress protection rating: IP53

Supply:
References by unit. Order by multiples of 10 units (10, 20, 30, etc.)


NSYVEA9

Characteristics	Compatibility	References
Water drain plug	PLM	**NSYVEA9**

Blanking Plates

PLM

Aesthetic Accessory. They are positioned on the rear surface of the enclosures to block the openings in the corners in order to improve their appearance or help prevent the entry of unwanted elements in the airing shaft. Supplied as standard for enclosure, ref. **NSYPLM108G**.

- Material: Thermoplastic
- Color: RAL 7035 gray
- Ingress protection rating: IP40


Accessory is mounted outside the IP66-protected area.



NSYCEPLMAG

Characteristics	Compatibility	For wall-mounted enclosure	Reference
Blanking plates	PLM	NSYPLM32G	**NSYCEPLMAG**
Blanking plates	PLM	NSYPLM43G and NSYPLM54G	**NSYCEPLMBG**
Blanking plates	PLM	NSYPLM64G, 75G and 86G	**NSYCEPLMCG**

Airing Elevators for Roof

SFN SFN IT MCC




NSYRE26_nb

- Allows the roof to be raised, providing natural airing.
- They are screwed onto the structure at the roof fixing point.
- Material: Zinc-coated steel.
- Can´t be used for lifting.

Supply:
4 elevators


NSYRE26

Characteristics	Compatibility	(H) Height (mm)	IP	References
Airing elevators for roof	SFN, SFN IT, MCC	23	10	**NSYRE26**
Airing elevators for roof	SFN, SFN IT, MCC	60	00	**NSYRE60**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Standard Wall Fixing Lugs


SBM CRN S3D SBX S3X SMX S3HD

PanelSeT SBM and SBX:

- Wall-mounted lugs to be mounted directly on the rear of the box, either in horizontal or vertical position. Their versatile design complies with the mounting dimensions of many other enclosures.
- Ingress protection rating: IP66 according to IEC 60529
- Installation: Horizontal or vertical position, distance between wall and enclosure: 12 mm, only requires a screw driver
- Maximum load: 70 kg

PanelSeT CRN, S3X, S3D, S3HD, SFN HD:

- Set of 4 wall-fixing lugs.
- Mounted directly on the rear of the enclosure, either in horizontal or vertical position.
- Wall-to-enclosure spacing separation of 12 mm.
- Maximum load: 250 kg
- Not suitable for dynamic loads.
- For weights of the PanelSeT CRN enclosures without mounting plate refer to the selection table



Supply:
4 wall-mounted lugs, screws and pre-mounted sealing gaskets


NSYAEFPFSB

Characteristics	Compatibility	References
Wall fixing lugs	SBM	**NSYAEFPFSB**
Wall fixing lugs for stainless-steel 304L	SBM, SBX	**NSYAEFPFSBX**
Wall fixing lugs	CRN	**NSYPFCR**
Wall fixing lugs for stainless-steel 304L	CRN, S3X	**NSYPFCX**
Wall fixing lugs in stainless-steel 316L	CRN, S3X	**NSYPFC2X**
Wall fixing lugs	S3D	**NSYAEFPFSC**
Wall fixing lugs for stainless-steel 304L	S3D, S3HD	**NSYAEFPFXSC**
Wall fixing lugs for stainless-steel 304L	SMX	**NSYFCMX**

Lugs and Cover

S3D


NSYAEFPFSC2

Supply:
4 fixing brackets + covers

Characteristics	Compatibility	References
Wall fixing lugs + cover, passivated zinc-coated steel, polyamide	S3D	**NSYAEFPFSC2**

CRN S3D


NSYCAEFPF


Supply:
Kit of 4 covers

Characteristics	Compatibility	References
Cover for wall fixing brackets, polyamide	CRN, S3D	**NSYCAEFPF**

Set of 4 Fixing Lugs

TBS TBP

- Plastic fixing lugs for installation on boxes with dimensions from 116 x 116 mm.
- Option of vertical or horizontal installation.
- Installation: Installation by a single screw at the last moment, with the box closed and equipped
- Maximum load: Body: 30 kg/m², Cover: 10 kg/m²




NSYAEFTB


Supply:
4 lugs + screws, minor pack 1

Characteristics	Compatibility	Reference
Set of 4 fixing lugs	TBS, TBP	**NSYAEFTB**


Wall Fixing Lugs

PLS


NSYPF27N


NSYPF27X

- Passivated zinc-coated steel
- Stainless-steel



Supply:
Set of 4 lugs and fixings

Characteristics	Compatibility	References
Wall fixing lug, passivated zinc-coated steel	PLS	**NSYPF27N**
Wall fixing lug, stainless-steel	PLS	**NSYPF27X**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

6

Fixing Accessories

Wall Fixing

Fixing Lugs

PLM

Set of 4 wall fixing lugs. Mounted directly on the enclosure, either in horizontal position or in vertical position.
- Material: Polyamide reinforced with fiberglass or stainless-steel
- Color: RAL 7035 gray
- **Maximum load:**
  On PLM32: Vertical or horizontal: 10 kg
  Other PLM models: Vertical position: 200 kg, horizontal position: 100 kg

Supply:
Delivered with fixings



NSYPFXPLM

Characteristics	Compatibility	Reference
Wall fixing lugs	PLM	**NSYPFPLMG**
Wall fixing lugs for NSYPLM32G and NSYPLM32TG	PLM	**NSYPFPLM32G**
Wall fixing lugs	PLM	**NSYPFXPLM**

PLA

Drilling positions and marks inside the side panels.
- Material: Passivated zinc-coated steel
- Maximum load: 180 kg including weight of enclosure

Fixing: Fixing on the sides by four or six lugs in horizontal position
(six lugs for enclosures with height ≥ 1000 mm)
10 mm fixing distance on the rear of the enclosure plane



Supply:
Set of six lugs and fixings


NSYFMPLA

Characteristics	Compatibility	References
Wall fixing lugs	PLA	**NSYFMPLA**

Wall Fixing Support

PHD

- Wall fixing support for polyester outdoor Heavy-Duty enclosure.
- No change in ingress protection rate.
- Maximum load per enclosure: 180 kg
- Material: Zinc-coated steel
- Finish: Zinc painting



Supply:
6



NSYFMPHD


Characteristics	Compatibility	References
Wall fixing support	PHD	**NSYFMPHD**

Wall Fixing Lugs with Wall-Enclosure Separation

S3D

- Set of 4 wall fixing lugs.
- Separation of 40 mm from the wall at the rear of the enclosure.
- Requires a drilled hole to help prevent rotation.
- Material: Passivated zinc-coated steel
- Maximum load: 100 kg





NSYAEFPF40SC

Characteristics	Compatibility	References
Wall fixing lugs with wall-enclosure separation	S3D	**NSYAEFPF40SC**

Full-Width Wall Fixing Lugs

S3D



- Kit made of 2 parts (top and bottom).
- Screwed from the inside.
- Material: Passivated zinc-coated steel
- Maximum load: 350 kg

Comment:
For more information see page 480


NSYAEFPFS3DW40

Characteristics	Compatibility	Width (mm)	A (mm)	References
Heavy load reinforcement	S3D	400	395	**NSYAEFPFS3DW40**
Heavy load reinforcement	S3D	600	595	**NSYAEFPFS3DW60**
Heavy load reinforcement	S3D	800	795	**NSYAEFPFS3DW80**
Heavy load reinforcement	S3D	1000	-	**NSYAEFPFS3DW100**

Kit For Heavy Loads

S3D

- Set of 2 reinforcement pieces.
- To be mounted before installing the mounting plate in top position with the standard lugs (to be ordered separately).
- This kit is mandatory for wall-mounted enclosures bigger than 800 x 800 mm.
- Material: Passivated zinc-coated steel
- Maximum load: 400 kg




Characteristics	Compatibility	References
Kit for heavy loads	S3D	**NSYAEFAHLBSC**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Wall Fixing Support

SFN



NSYSFWFIX

- Supports for fixing the enclosure on the wall and helping prevent it from turning over.
- They cannot be used for hanging the enclosure.
- They are installed using the roof mounting screws.
- Material: Zinc-coated steel sheet



Supply:
2 supports


Characteristics	Compatibility	References
Wall fixing support	SFN	**NSYSFWFIX**

SM



NSYSMWFIX

- Supports for fixing the enclosure on the wall and helping prevent it from turning over.
- They are installed using the drill holes in the back of the enclosure.
- Mounted directly on the rear of the enclosure, either in horizontal or vertical position
- Material: Zinc-coated steel sheet



Supply:
2 supports

Characteristics	Compatibility	References
Wall fixing support	SM	**NSYSMWFIX**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Fixing Accessories

Post Fixing

Post Fixing Device

SBM CRN S3D PLM

For CRN, S3D and SBM

- For indoor installations on posts with a maximum circumference of 675 mm (minimum diameter 150 mm and maximum diameter 215 mm).
- Material: Zinc-plated steel
- Rail mounted externally to the rear of the box with 8 mm screws for installation on posts with diameters between 150 mm and 215 mm.
- For steel boxes with widths of 150, 200, 300, 400, 500, 600 and 800 mm.
- Maximum load: 100 kg

For PLM:

- For outdoor installations on a post with a maximum circumference of 675 mm, Ø 215 mm.
- Support material: Steel with C4H treatment
- Maximum load: 100 kg
- Strap material: Stainless-steel
- C5H/C6H resistances available via customization services


Supply:
2 pieces





NSYSFPSC30





Characteristics	Compatibility	A (mm)	Height (mm)	Width (mm)	References
Post mounting	SBM, CRN, S3D	295	45	300	**NSYSFPSC30**
Post mounting	SBM, CRN, S3D	395	45	400	**NSYSFPSC40**
Post mounting	SBM, CRN, S3D	495	45	500	**NSYSFPSC50**
Post mounting	SBM, CRN, S3D	595	45	600	**NSYSFPSC60**
Post mounting	SBM, CRN, S3D	795	45	800	**NSYSFPSC80**
Post mounting	PLM	295	45	300	**NSYSFP300**
Post mounting	PLM	395	45	400	**NSYSFP400**
Post mounting	PLM	495	45	500	**NSYSFP500**
Post mounting	PLM	595	45	600	**NSYSFP600**











Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Levelling Feet

SM | SFN | SMX | SFX | SFN IT | MCC | SD



NSYSPSJ

- Height: 42 mm.
- Material: Steel.
- Maximum load: 400 kg per foot.

Supply:
Set of 4 floor feet

Characteristics	Compatibility	References
Levelling feet fixed	SM, SFN, SMX, SFX, SFN IT, MCC, SD	**NSYSPSJ**

Levelling Feet

SM | SFN | SMX | SFX | SFN IT | MCC | SD



NSYSPRJ

- Height: 22 mm.
- Maximum load: 400 kg per foot.

Supply:
Set of 4 floor feet

Characteristics	Compatibility	References
Levelling feet adjustable	SM, SFN, SMX, SFX, SFN IT, MCC, SD	**NSYSPRJ**

Hygienic Stainless-Steel Feet

SM | SFN | SMX | SFX | SFN IT | MCC | SD



NSYPHX200

- Recommended for applications that require special hygiene conditions.
- Material: 316L stainless-steel.
- Installation: Adjustable between 140 mm and 200 mm in height.
- Maximum load: 200 kg per foot.

Supply:
Set of 4 hygienic feet

Characteristics	Compatibility	References
Hygienic stainless-steel feet	SM, SFN, SMX, SFX, SFN IT, MCC, SD	**NSYPHX200**


Transport Casters

CRN | S3D | SM | SFN | SFN IT | MCC | SD



NSYSTW

- Quick installation on plinths with heights of 100 and 200 mm, except the plinth for enclosure sets.
- They can be installed in front or side position.
- Clipping and fixing to the corner by screws.
- For use on flat surfaces.
- Height: 110 mm.
- Maximum load: 200 kg per enclosure.



Supply:
4 transport casters
(2 with a blocking system)
and fixing elements

Characteristics	Compatibility	References
Transport casters	CRN, S3D, SM, SFN, SFN IT, MCC, SD	**NSYSTW**

Enclosure Casters

SM | SFN | SMX | SFX | SFN IT | MCC | SD



NSYSW

- Double casters.
- Height: 92 mm.
- Diameter: 64 mm.
- Maximum load:
  180 kg per caster
  720 kg per enclosure when it is installed directly on the upright,
  400 kg per enclosure when it is installed on the frame.



Supply:
4 casters and fixing elements

Characteristics	Compatibility	References
Enclosure casters	SM, SFN, SMX, SFX, SFN IT, MCC, SD	**NSYSW**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Lifting Accessories

Eyebolts

NSYAELYTCRG8	NSYAELYTCRXG8	NSYSFEB	NSYSMEB	NSYSMXEB	NSYPLHD
					
CRN S3D	CRN S3D S3X	SFN MCC SFN IT	SM	SMX SFX	PHD
• Set of two M8 eyebolts. They are fixed directly to the body of the floor-standing enclosure. Cannot be installed with the canopy in place or if it is planned to put one. • Material: Zinc-coated molded steel. • Maximum load: 200 kg per enclosure when slinging at 60°.	• Material: Stainless-steel 304L. • Maximum load: 210 kg per enclosure when slinging at 60°. • Supply reinforcing brackets attached to therings (these brackets also act as a drilling template).	• Set of M12 lifting eyebolts, which screw directly into the structure of the enclosure, in the axis of the uprights. • Material: Galvanized cast steel. • Maximum load: 1360 kg at 90° using 4 units (340 kg at 90° per unit). • Maximum amount of assembled enclosures to be lifted: 1.	• Set of M12 lifting eyebolts, fixed to the enclosure by fixing nuts. • Material: Galvanized cast steel. • Maximum load: 1360 kg at 90° using 4 units (340kg at 90° per unit) • Maximum amount of assembled enclosures to be lifted: 1.	• Material: Stainless-steel 304L. • Installation: By the fixing nuts supplied. • Maximum load: 340 kg for 1 eyebolt in vertical direction.	• Top lifting accessory for polyester outdoor Heavy-Duty enclosure. • Maximum load per enclosure: 500 kg. • Material: Galvanized cast steel.

Lifting Brackets



SFN SFN IT MCC


NSYSFELB

- Set of lifting and transport brackets, fixed to the structure between two coupled enclosures, in the axis of the uprights.
- Material: Zinc-coated steel
- Maximum load: 500 kg at 90° per unit
- Maximum amount of assembled enclosures to be lifted with 2 brackets: 2

Supply:
4 brackets and fixing elements (M12 screws)

Characteristics	Compatibility	Enclosures to be lifted	Max. load (kg)	References
Lifting brackets	SFN, MCC , SFN IT	2	500	**NSYSFELB**

SFX


NSYPUNX


- Material: Treated steel
- Installation: They are fixed instead of the eyebolts on two suitable enclosures side-by-side, helping guarantee the rigidity of the enclosure when lifted
- Maximum load: 1300 kg when slinging at 60°

Supply:
Set of four lifting brackets

Characteristics	Compatibility	References
Lifting bracket	SFX	**NSYPUNX**

Lifting Bar for SFN

SFN SFN IT MCC



- Set of bars for lifting and transporting enclosures suites.
- They are fixed to the structure of the enclosure, in the axis of the uprights.
- Material: Zinc-plated steel

Supply:
2 lifting bars and fixing elements (M12 screws)

Characteristics	Compatibility	B - Length (mm)	Enclosures to be lifted	Max. load (kg)	References
Lifting bar	SFN, MCC , SFN IT	1600	2	2000	**NSYSFTB16**
Lifting bar	SFN, MCC , SFN IT	1800	3	3000	**NSYSFTB18**
Lifting bar	SFN, MCC , SFN IT	2400	4	3000	**NSYSFTB24**
Lifting bar	SFN, MCC , SFN IT	3200	5	4000	**NSYSFTB32**



NSYSFTB16

Plastic Carrying Handle

PLS


NSYATM27

- Material: Plastic
- Ingress protection rating: IP43




Characteristics	Compatibility	References
Plastic carrying handle	PLS	**NSYATM27**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Cable Entries Key features

Key Features when Selecting a Cable Entry

1



Multiple



Single

Multiple Cable Entries or Single Cable Entries?

- This choice depends on the number of cables going through the cable entry: Generally, for 3 or more cables, choose a multiple cable entry.
  This will make your installation faster and more economical.
- In other words, your final costs will not necessarily be lower if you use single cable entry!
- Flexibility of installation: For high flexibility, multiple cable entry is the right choice.

2

Cable Entry Material

- **Soft membranes** allow cables to be easily pushed through, but still offer a good IP rating and protection from moisture and physical intrusion. Cable retention force, however, is lower than with other alternatives.



Push the Membrane into a Standard Hole



Make a Small Hole in the Membrane



Push the Cable or Tube through the Guide Hole





Pull the Cable or Tube Back Some 20 mm to Lock It


- **Hard-plastic cable entry plates** require tools to create the opening (drill or knife) but, thanks to the cable gland, they offer a very high retention force. Another use of this solution is for public places, since the hard surface helps prevent objects being pushed in.

- **Combined: The material of the cable entry plate is hard-plastic,** but the cable is pushed through a soft membrane. In this case you have the advantages of both soft membranes (easy and fast installation, flexibility) and hard-plastic membranes (high retention force when using specific cable clamps).










3



Cable Glands to Be Fitted

- Some multiple cable entries require a cable gland to be able to retain the cables and help ensure the degree of protection

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries Key features

Key Features when Selecting a Cable Entry

4


PB500305_30_nb


Installation Options

There are 4 ways to install your cable entries on the enclosure:


- **Using a cable entry:**
  The standard cable gland plate of your S3D wall-mounted enclosure is unscrewed and replaced by the cable entry.
  A gasket between enclosure and cable entry will help ensure good water and dust tightness.


PB500023_35_nb

- **Modifying the standard cable gland plate:**
  The standard cable gland plate is unscrewed and machined. A cut-out is made.


PB500462_44_nb

- **On cable gland plate adapter:**
  This plate, which has the outer dimensions of a standard cable gland plate, has one or more pre-cut cut-outs of standard dimensions (FL13 and FL21).
  On steel wall-mounted enclosures, the plate can replace the standard cable gland plate once the cable entry is fitted into it. On polyester enclosures, a cut-out must be created. Schneider Electric provides this service: a precise laser cut-out can be made at the factory upon request.
  On steel floor-standing enclosures, you may either use the specific cable gland roof or create a cut-out **(see expert's tip 1 - page 486)**.


PB500599_37_nb

Cable gland plate adapters		
Enclosure range	**1 membrane**	**2 membranes**
PanelSeT S3D	 PB500604_16_nb **NSYTL●FL**	 PB500604_15_nb **NSYTL●2FL**

- Drilling directly the enclosure: A cut-out is created on the enclosure's side according to the cable entry's dimensions **(see expert's tip 1 - page 486)**.


PB500358_108_nb

Spotlight On…
FL13 and FL21 are standard cut-out dimensions frequently used in northern European countries and also used by our enclosures for several years now.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries Key features

Key Features when Selecting a Cable Entry

PB502710_32_nb



Full Flexibility

PB500946_35_nb



Medium Flexibility

5 Flexibility of the installation

- **Full flexibility:**
  This means that cables can be added/removed easily, changing:
  - quantity
  - diameter
  - position

  (see expert's tip 2, page 486)
- **Medium flexibility:**
  - The amount, diameter or position of cables can be changed to a limited extent.
- **Low flexibility:**
  - It is not possible to change the above parameters.

6 Reversibility

- **Full reversibility:** This means that cables can be added/removed easily without losing their initial characteristics, such as water tightness.
- **Medium reversibility:** For soft membranes, once the cable has been removed, there may be a loss of IP degree depending on the size of the cable and the cut. For hard-plastic entries or combined material entries, initial characteristics are regained by adding plugs.
- **Low reversibility:** The cable entry must be completely replaced in order to regain the initial characteristics.

7 Degree of Protection (IP)

- If an enclosure is to be used in a clean, dry and well insulated environment, lower levels of IP may be acceptable (IP54 or IP55).
- In a dusty environment, a higher IP level such as IP65 or IP68 may be required **(see expert's tip 4, page 486)**.


8 Cable Retention

- Choose the right level of cable retention according to your needs. For locations accessible to the public, preferably choose a high level of cable retention.


9 Cable Diameter

- Choose the cable entry seal according to the cable diameter. Take into account cable diameter tolerances.

DB300404_42_nb




DB300406_41_nb



10 Cable Installation Time

- Each cable entry has different installation characteristics. Some can be installed easily and quickly thanks to the soft membrane. Take this into account depending on labour costs in your region.

DB300413_53_nb



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries Key features

Key Features when Selecting a Cable Entry






11 Number of Cables for a Given Surface

- For some installations, a large quantity of cables must go through the cable entry. Some cable entries can handle a high density of cables, which can result in a more economical installation (fewer cable entries to be purchased). For small enclosures, it may simply be impossible to install too many cable entries due to the available space on the enclosure's wall **(see expert's tip 3, page 486)**.



12 Cable Entries for Cables with Connectors

- Some cables have large connectors which cannot be pushed through tight cable clamps or cable seals. These cable entries have the unique advantage of not
requiring the cable to be cut, thanks to the snap-fitting system.




A High Cable Retention Force Is Provided Thanks to the Integrated Cable Fastener

Expert's Tip


Specific Configured



1 Some cable entries require cut-outs to be machined on the enclosure or cable gland plate. Our customized offer provides this service. The quality of your enclosure will therefore be improved since the painting operation is performed after creating the cut-outs.



2 Installing a cable entry with full flexibility is the solution when a large number of enclosures is being prepared for different types of installations. By using one combination of enclosure cable entries, you can cover a large variety of installations!



3 When the cable entry has been defined, the next step is cable management inside the enclosure. For correct thermal management, all cables must be fitted and attached so as not to create an obstacle for correct air flow. Consult our Universal Enclosures catalog for cable management accessories (such as cable ducts) and consumables (such as cable ties).



4 If your environment requires a high IP level for your installation, make sure you have an appropriate thermal management system to avoid condensation or overheating problems. Consult our Thermal Management offer in our Universal Enclosures catalog and our Control Panel Technical Guide related to this issue.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries

Single Entry

• For details enter the reference into the search engine of www.se.com

Characteristics	Simple-1	Simple-2	Simple-3	Simple-5
	 ISM71074	 NSYECPC15	 IMT36179	 ISM71503
	Mixed membrane entries for enclosure thickness 20/10ᵉ - 32/10ᵉ mm.	**PVC adjustable cone-shaped entries for enclosure thickness 30/10ᵉ - 32/10ᵉ mm.**	**Quick cable entries for enclosure thickness 10/10ᵉ - 40/10ᵉ mm (5/10ᵉ - 20/10ᵉ mm for ref. IMT36179).**	**ISO cable gland.**
Material	SBS	PVC	EPDM plastic	PA6 Polyamide, neoprene gasket
Color	RAL 7035 gray or RAL 9010 white	-	Gray cable entries: NCS 5500 Black cable entries: NCS 9000	RAL 7035 gray
Cable entry material	Soft membrane		Combined	
Cable glands to be fitted	Not applicable			
Installation options	On cable gland plate or directly on enclosure			
Flexibility of the installation	Low			
Reversibility	Medium			
Ingress protection rating	IP55 according to IEC 60529	IP55 according to IEC 60529	IP67 according to IEC 60529	IP66 o IP68-5BARS TYPE 4X (cULus) UL50E
Cable retention	Low	Low	Medium	High
Cable diameter (mm)	From 20 to 40	From 5 to 87	From 12 to 50	From 12 to 40
Cable Installation time	Fast	Fast	Fast	Slow
Quantity of cables to be fitted for a given surface	+	+	+	+
Cable entries for cables with connectors	No	No	No	No
Cut-out dimensions (mm)	Various circular hole diameters according to cable diameter			
External dimensions (mm)	From Ø 23 to 44	From Ø 25 to 98	From Ø 12.5 to 50.7	From Ø 15 to 46
Certificates	-	-	-	-
Standard	-	-	-	Compliance with UL
Flame resistance	750 °C	-	750 °C	750 °C
References	**See page 488 IMT36●●●/I SM71●●●**	**See page 488 NSYECPC●●**	**See page 489 IMT361●●**	**See page 489 ISM71●●●**

Characteristics	Synthetic snap-in cable gland	Stainless-steel cable gland with lamellar insert
	 NSYCGSP16	 NSYCGX12
	Without thread. Easy assembly and disassembly. Suitable for walls from 0.5 to 4 mm thick.	**Lamellar technology provides excellent resistance to traction as well as excellent torsional protection. For outdoor use, or for aggressive environments.**
Material	PA6 Polyamide, neoprene gasket	Stainless-steel AISI 304L or AISI 316L, neoprene gasket
Color	RAL 7035 gray, RAL 7001, RAL 9005. Other colors on demand	-
Cable entry material	Non armoured	Non armoured
Installation options	On cable gland plate or directly on enclosure	
Flexibility of the installation	Low	
Reversibility	Medium	
Ingress protection rating	IP68	IP68
Cable retention	High	High
Cable diameter (mm)	From 16 to 40	From 12 to 40
Cable Installation time	Slow	Slow
Quantity of cables to be fitted for a given surface	+	+
Cable entries for cables with connectors	No	No
Thread type	Metric EN 60423, other types are available on demand	Metric EN 60423
Cut-out dimensions (mm)	Various circular hole diameters according to cable diameter	
External dimensions (mm)	From Ø 22 to 46	From Ø 14 to 43
Certificates	UL recognized (cURus). Rated Type 4X according UL50E	UL recognized (cURus). Rated Type 4X according UL50E
Standard	DIN EN 62444, UL 514B, UL 514B§8.26.7	DIN EN 62444, UL 514
Temperature range	-20 °C to + 100 °C	-20 °C to + 100 °C
References	**See page 490, NSYCGSP●●**	**See page 490, NSYCGX●●●**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Cable Entries


Single Entry

Mixed Membrane Entries for IP55 Direct Cable Entries

Steel TBS TBP PLS

- Mixed membrane entries for enclosure thickness 20/10e - 32/10e mm.
- Material: SBS
- Color: RAL 7035 gray or RAL 9010 white
- Cable entry material: Soft membrane
- Cable glands to be fitted: Not applicable
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP55 according to IEC 60529
- Cable retention: Low
- Cable diameter (mm): From 20 to 40
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 23 to 44
- Flame resistance: 750 °C





Note:
Details see page 487

Supply:
Minimal packaging of 10 pieces



ISM71074

Characteristics	Compatibility	Drill hole Ø (mm)	Cable / conduit Ø (mm)	References
Mixed membrane entries for IP55 direct cable entries, RAL 7035	Steel, TBS, TBP, PLS	23	4 - 20	**ISM71071**
Mixed membrane entries for IP55 direct cable entries, RAL 7035	Steel, TBS, TBP, PLS	29	4 - 25	**ISM71072**
Mixed membrane entries for IP55 direct cable entries, RAL 7035	Steel, TBS, TBP, PLS	36	4 - 32	**ISM71073**
Mixed membrane entries for IP55 direct cable entries, RAL 7035	Steel, TBS, TBP, PLS	44	4 - 40	**ISM71074**

PVC Adjustable Cone-Shaped Entries

Steel TBS TBP PLS

- PVC adjustable cone-shaped entries for enclosure thickness 30/10e - 32/10e mm.
- Material: PVC
- Cable entry material: Soft membrane
- Cable glands to be fitted: Not applicable
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP55 according to IEC 60529
- Cable retention: Low
- Cable diameter (mm): From 5 to 87
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 25 to 98



Note:
* Drill-hole for mounting.
Details see page 487

Supply:
NSYECPC3 50 cable entries,
NSYECPC5 and **NSYECPC6** each 25 cable entries,
NSYECPC9 and **NSYECPC15** each 10 cable entries


NSYECPC15

Characteristics	Compatibility	Dimensions (mm)						Capacity		References
		Ø A	Ø B*	Ø C	Ø D	E	F	Cable (Ø mm)	Tube	
PVC adjustable cone-shaped entries	Steel, TBS, TBP, PLS	25	21.5	18	5	3.2	13	5-18	PG 9-11	**NSYECPC3**
PVC adjustable cone-shaped entries	Steel, TBS, TBP, PLS	33	29.5	26	5	3.2	20	5-26	PG 9-16	**NSYECPC5**
PVC adjustable cone-shaped entries	Steel, TBS, TBP, PLS	43	38.5	36	5	3.2	22	5-36	PG 9-21	**NSYECPC6**
PVC adjustable cone-shaped entries	Steel, TBS, TBP, PLS	70	63	60	28	3	20	28-60	PG 21-48	**NSYECPC9**
PVC adjustable cone-shaped entries	Steel, TBS, TBP, PLS	98	90	87	28	3	23	28-87	PG 21-48	**NSYECPC15**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ISO Cable Gland

All

- ISO cable gland.
- Material: PA6 Polyamide, neoprene gasket
- Color: RAL 7035 gray
- Cable entry material: Combined
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP68
- Cable retention: High
- Cable diameter (mm): From 12 to 40
- Cable Installation time: Slow
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 15 to 46
- Certificate: VDE, UL Recognized (UR)
- Flame resistance: 750 °C

- The cable gland (ref. **IMT36150**) is especially recommended for security circuits.



Note:
* In brackets: Tolerance.
Details see page 487

Supply:
The cable glands are supplied with nuts. Pack of 20 (M12 to M20), 10 (M25 and M32), 5 (M40)



ISM71503

Characteristics	Compatibility	Dimensions						References
		ISO	Cable Ø (mm)	Drill hole* Ø (mm)	TD	TL		
Cable gland	All	M12	3 / 6.5	12.2 (0 + 0.2)	12	6	15	**ISM71501**
Cable gland	All	M16	4 / 8	16.2 (0 + 0.2)	16	8	19	**ISM71502**
Cable gland	All	M20	6 / 12	20.2 (0 + 0.2)	20	10	24	**ISM71503**
Cable gland with high resistance to fire	All	M20	6 / 12	20.2 (0 + 0.2)	20	10	24	**IMT36150**
Cable gland	All	M25	11 / 17	25.2 (0 + 0.2)	25	8	29	**ISM71504**
Cable gland	All	M32	15 / 21	32.2 (0 + 0.3)	32	10	36	**ISM71505**
Cable gland	All	M40	19 / 28	40.5 (0 + 0.3)	40	10	46	**ISM71506**

Quick Cable Entries

All

- Quick cable entries for enclosure thickness 10/10e - 40/10e mm (5/10e - 20/10e mm for ref. **IMT36179**).
- Material: EPDM plastic
- Color: Gray cable entries: NCS 5500; Black cable entries: NCS 9000
- Cable entry material: Combined
- Cable glands to be fitted: Not applicable
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP67 according to IEC 60529
- Cable retention: Medium
- Cable diameter (mm): From 12 to 50
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 12.5 to 50.7
- Flame resistance: 750 ºC



Note:
Details see page 487

Supply:
50 (M12 to M32), 25 (M40 and M50)


IMT36179

Characteristics	Compatibility	Dimensions			References
		Ø	Drill hole Ø (mm)	Cable Ø (mm)	
Quick cable entries	All	M12	12.5	3 - 5	**IMT36179**
Quick cable entries	All	M16	16	5 - 7	**IMT36180**
Quick cable entries	All	M20	20.3	7 - 10	**IMT36181**
Quick cable entries	All	M25	25.3	10 - 14	**IMT36182**
Quick cable entries	All	M32	32.4	14 - 20	**IMT36183**
Quick cable entries	All	M40	40.7	20 - 26	**IMT36184**
Quick cable entries	All	M50	50.7	26 - 35	**IMT36185**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Cable Entries

Single Entry

Synthetic Snap-In Cable Gland

All

- Without thread.
- Easy assembly and disassembly.
- Suitable for walls from 0.5 to 4 mm thick.
- Material: PA6 Polyamide, neoprene gasket
- Color: RAL 7035 gray, RAL 7001, RAL 9005. Other colors on demand
- Cable entry material: Non-armoured
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP66
- Cable retention: High
- Cable diameter (mm): From 16 to 40
- Cable Installation time: Slow
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Thread type: Metric EN 60423. Other types are available on demand
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 22 to 46
- Certificates: UR (cURus) Type 4x except for the size M40
- Standard: DIN EN 62444, UL 514B, UL 514B§8.26.7
- Temperature range: -20 °C to + 100 °C



Note:
Details see page 487

Supply:
The cable glands are supplied with nuts. Pack of 20 (M16 and M20), of 10 (M25 and M32), of 5 (M40)



NSYCGSP16

Characteristics	Compatibility	Dimensions							References
		Ø	Ø min / max	Drill Ø	SL	SD	H		
Synthetic snap-in cable gland	All	M16	5/10	16.2 to 16.4	9	15.9	42.5	22	**NSYCGSP16**
Synthetic snap-in cable gland	All	M20	6/12	20.2 to 20.4	9	19.9	41.5	24	**NSYCGSP20**
Synthetic snap-in cable gland	All	M25	11/17	25.2 to 25.4	9	24.9	43.5	29	**NSYCGSP25**
Synthetic snap-in cable gland	All	M32	15/21	32.2 to 32.4	9	31.9	49.5	36	**NSYCGSP32**
Synthetic snap-in cable gland	All	M40	19/28	40.2 to 40.4	11.5	39.9	56	46	**NSYCGSP40**

Stainless-Steel Cable Gland with Lamellar Insert

Steel

- Lamellar technology provides excellent resistance to traction as well as excellent torsional protection. For aggressive environments.
- Material: Stainless-steel AISI 304L or AISI 316L, neoprene gasket
- Cable entry material: Non armoured
- Installation options: On cable gland plate or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP68
- Cable retention: High
- Cable diameter (mm): From 12 to 40
- Cable Installation time: Slow
- Quantity of cables to be fitted for a given surface: +
- Cable entries for cables with connectors: No
- Thread type: Metric EN 60423
- Cut-out dimensions (mm): Various circular hole diameters according to cable diameter
- External dimensions (mm): From Ø 14 to 43
- Certificates: UL recognized (cURus). Rated Type 4, 4X according UL50E
- Standard: DIN EN 62444, UL 514
- Temperature range: -20 °C to + 100 °C



Supply:
The cable glands are supplied with nuts
Pack of 5 (M12 and M16), of 4 (M20 and M25), of 2 (M32 and M40)


NSYCGX12


Characteristics	Compatibility	Dimensions							References
		Ø	Ø min-max mm	Thread Length TL mm	SW Cap mm	SW Body mm	Outer Ø D mm	max. Height H mm	
AISI 304L	Steel	M12x1.5	3.0 - 6.5	6	14	14	15.5	24	**NSYCGX12**
AISI 304L	Steel	M16x1.5	4.0 - 8.0	7	17	19	21	25.5	**NSYCGX16**
AISI 304L	Steel	M20x1.5	10.0 - 14.0	8	24	24	26.5	30	**NSYCGX20**
AISI 304L	Steel	M25x1.5	10.0 - 14.0	8	24	27	30	30	**NSYCGX25**
AISI 304L	Steel	M32x1.5	13.0 - 18.0	9	30	36	39.8	35	**NSYCGX32**
AISI 304L	Steel	M40x1.5	18.0 - 25.0	9	41	46	51.4	40.5	**NSYCGX40**
AISI 316L	Steel	M12x1.5	3.0 - 6.5	6	14	14	15.5	24	**NSYCGX12H**
AISI 316L	Steel	M16x1.5	4.0 - 8.0	7	17	19	21	25.5	**NSYCGX16H**
AISI 316L	Steel	M20x1.5	10.0 - 14.0	8	24	24	26.5	30	**NSYCGX20H**
AISI 316L	Steel	M25x1.5	10.0 - 14.0	8	24	27	30	30	**NSYCGX25H**
AISI 316L	Steel	M32x1.5	13.0 - 18.0	9	30	36	39.8	35	**NSYCGX32H**
AISI 316L	Steel	M40x1.5	18.0 - 25.0	9	41	46	51.4	40.5	**NSYCGX40H**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Management Accessories
Cable Entries
Multiple Entries

All

• For details enter the reference into the search engine of www.se.com

Characteristics	FlexiCable	Multi-A	Multi-C	Multi-R	Multi-CS	Multi-T
	 PB501965_16_nb	 PB501700_35_nb	 PB500024_33_nb	 PB500023_21_nb	 PB503490_nb	 NSYAECPFLT25
	Full membrane cable gland plate	**FL21 type membranes**	**Circular connector-free entries**	**Rectangular connector-free entries**	**Modular entry allowing the passing of up to 48 pre-assembled cables**	**FL21-type membranes**
Material	HCE for membrane. Steel for frame	TPE, SBS, SEBS and PP co-polymer - halogen-free	Polyamide	Polyamide	Reinforced polypropylene and TPE. halogen-free	TPE
Color	Frame: RAL 7035 gray	RAL 7035 gray	-	-	Black	RAL 7035 gray
Cable entry material	Soft membrane	Combined	Soft membrane			
Cable glands to be fitted	No	Optional: Specific cable clamp ref. **NSYAECPFLACA●●** to be used	No	No	No	No
Installation options	Replaces cable gland plate (S3D) or directly on enclosure	On cable gland plate adapter or directly on enclosure	On modified cable gland plate or directly on enclosure	On cable gland plate with special cut-out or directly on enclosure	On cable gland plate adapter or directly on enclosure	
Flexibility of the installation	Full	Medium	Medium	Medium	Full	Medium
Reversibility	Medium	Medium	Full	Full	Full	Medium
Ingress protection rating	IP55 according to IEC 60529	IP65 according to IEC 60529	IP65 according to IEC 60529	IP65 according to IEC 60529	IP65 according to IEC 60529	IP66 according to IEC 60529*
Cable retention	Low	High with cable clamp, (up to 18 daN)	Medium	Medium	Medium	Low
Cable diameter (mm)	Up to 26	From 16 to 30	From 3 to 15.9	From 4.3 to 15.9	Up to 22	From 5 to 60
Cable Installation time	Fast	Medium	Fast	Fast	Fast	Fast
Quantity of cables to be fitted for a given surface	+++	++	++	++	+++	++
Cable entries for cables with connectors	No	No	No	No	Yes	No
Cut-out dimensions (mm)	178 x 63 to 478 x 63	198 x 70 (FL21)	Ø 50.5 Ø 63.5	112 x 36	112 x 36	214 x 90 (FL21)
External dimensions (mm)	245 x 130 to 545 x 130 or 495 x 220	214 x 88	Ø 58 Ø 71	146 x 14 x 58	148 x 58 x 15 148 x 58 x 18	214 x 88
Certificates	Tested on short-circuit effect 250 A, 25 kA following IEC 61439-1	Cable anchorage pull test: EN 50262. Long term UV- resistance: ASTM G 154-06	UL recognized (UsR)	UL recognized (UsR)	-	-
Fire resistance	650 °C	750 °C	650 °C	650 °C	-	650 °C
Temperature range	-	-40 °C to +85 °C	-	-	-30 °C to +100 °C	-40 °C to +100 °C
References	**See page 493 NSYTL●●●**	**See page 493 NSYAECPFLA●●**	**See page 494 NSYTSAM●●●●●**	**See page 494 NSYTSA24●●●●**	**See page 496 NSYDCD24●●**	**See page 495 NSYAECPFL●●●**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries

Multiple Entries

All

- For further information please have a look on the next page

Characteristics	PrismaSeT	Multi-H
	 DB300733_24_nb	 PB500944_17_nb
	FL21 or rectangular	FL21 insulated flange with ISO knock-outs
Material	Insulated material	Polycarbonate glass-fiber reinforced
Color	RAL 9003	RAL 7035 gray
Cable entry material	Soft membrane	
Cable glands to be fitted	No	Yes
Installation options	On cable gland plate adapter or directly on enclosure	
Flexibility of the installation	Medium	Low
Reversibility	Medium	Medium
Ingress protection rating	IP55 according to IEC 60529	IP65 according to IEC 60529
Cable retention	Low	High (with cable clamp)
Cable diameter (mm)	From 28 to 60 (FL21) From 7 to 72 (rectangular)	From 12 to 25
Cable Installation time	Fast	Slow
Quantity of cables to be fitted for a given surface	++	++
Cable entries for cables with connectors	No	No
Cut-out dimensions (mm)	214 x 90 (FL21)	214 x 90 (FL21)
External dimensions (mm)	216 x 84	215 x 85
Certificates	-	-
Flame resistance	-	750 °C
Temperature range	-	• For normal operation: -40 °C to +80 °C • For a short time: -40 °C to +120 °C
References	See page 497 LVS088●●	See page 495 NSYTSAKFL

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

FlexiCable Cable Entries

S3D SFN


FlexiCable is an innovative cable gland plate for simple and fast cable entry. There is no need to drill holes: The creation of the cable entrances takes a few seconds.

- Installation options: Replaces cable gland plate (S3D) or directly on enclosure.
- Cable diameter: Up to 26 mm.
- Ingress protection rating: IP55 according to IEC 60529
- Fixing: By 4, 6, 8, 10 or 12 screws, according to the model.

Other characteristics:

- Exists in 5 sizes matching 46 sizes (132 models) of PanelSeT S3D steel wall-mounted enclosures
- Fire resistant 650 °C following IEC 60695-2-11
- Tested on short-circuit effect 250 A, 25 kA following IEC 61439-1.

Mount FlexiCable on Your S3D Enclosure



Create a Hole with a Screw Driver



Push the Cable through Flexicable and Complete Your Installation



Note:
Details see page 491

Supply:
1 metal frame with pre-mounted membrane, 1 gasket, fixing hardware



NSYTLGME


Characteristics	Compatibility	Type	Plate width (mm)	Plate depth (mm)	Effective cable entrance dimensions (mm)	References
FlexiCable cable entries	S3D, SFN	C	245	130	178 x 63	**NSYTLCME**
FlexiCable cable entries	S3D	D	345	130	278 x 63	**NSYTLDME**
FlexiCable cable entries	S3D	E	445	130	378 x 63	**NSYTLEME**
FlexiCable cable entries	S3D	F	545	130	478 x 63	**NSYTLFME**
FlexiCable cable entries	S3D	G	495	220	428 x 153	**NSYTLGME**
FlexiCable cable entries for enclosure with 2 cable gland plates	S3D	D	345	130	-	2x **NSYTLDME**
FlexiCable cable entries for enclosure with 2 cable gland plates	S3D	E	445	130	-	2x **NSYTLEME**

Multi-A

All

- Material: TPE, SBS, SEBS and PP co-polymer - halogen-free
- Color: RAL 7035 gray
- Cable entry material: Combined
- Cable glands to be fitted: Optional: Specific cable clamp ref. **NSYAECPFLACA●●** to be used
- Installation options:
  On cable gland plate adapter or directly on enclosure
- Flexibility of the installation: Medium
- Reversibility: Medium
- Ingress protection rating: IP55 according to IEC 60529
- Cable retention: High with cable clamp, (up to 18 daN)
- Cable diameter (mm): From 14 to 30
- Cable Installation time: Medium
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): 134 x 52 (FL13); 214 x 90 (FL21)
- External dimensions (mm): 216 x 84
- Certificates: Cable anchorage pull test: EN 50262. Long term UV resistance: ASTM G 154-06
- Flame resistance: 750 °C
- Temperature range: -40 °C to +85 °C

FL13 FL21



Note:
Details see page 491



NSYAECPFLA25



NSYAECPFLA33

Characteristics	Compatibility	Height (mm)	Width (mm)	Depth (mm)	Diameter of the cable entry (Ø mm) No.	13	14	15	16	18	21	30	References
Multi-A Type FL21	All	25	215	86	25	-	16	-	-	6	-	3	**NSYAECPFLA25**
Multi-A Type FL21	All	25	215	86	33	-	24	-	-	9	-	-	**NSYAECPFLA33**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries

Multiple Entries


Multi-C


All

- Order by multiples of 10 (10, 20, 30...)
- Material: Polyamide
- Cable entry material: Soft membrane
- Cable glands to be fitted: No
- Installation options:
  On modified cable gland plate or directly on enclosure
- Flexibility of the installation: Medium
- Reversibility: Full
- Ingress protection rating: IP55 according to IEC 60529, UL recognized (UR)
- Cable retention: Medium
- Cable diameter (mm): From 3 to 15.9
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): Ø 50.5; Ø 63.5
- External dimensions (mm): Ø 58; Ø 71
- Certificates: UL 94 V-0
- Flame resistance: 650 °C

Position of the holes on the circular cable entries with diameters 50 and 63 mm:







Note:
Details see page 491

Supply:
10 units.
Reference by unit.
Order by multiples of 10 (10, 20, 30...)



NSYTSAM508SE

Characteristics	Compatibility	Cut-out	Diameter of the cable entry (Ø mm)						References
		Ø (mm)	No.	3-5.5	3-6.5	3.6-6.5	5-9.2	6-10	9.6-15.9	
Multi-C	All	50.5	8	-	-	7	-	1	-	**NSYTSAM508SE**
Multi-C	All	63.5	8	-	2	-	4	-	2	**NSYTSAM638SE**

Multi-R

All

- Material: Polyamide
- Cable entry material: Soft membrane
- Cable glands to be fitted: No
- Installation options: On cable gland plate with special cut-out or directly on enclosure
- Flexibility of the installation: Medium
- Reversibility: Full
- Ingress protection rating: IP65 according to IEC 60529
- Cable retention: Medium
- Cable diameter (mm): From 4.3 to 15.9
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): 112 x 36
- External dimensions (mm): 146 x 14 x 58
- Certificates: UR Certified
- Flame resistance: 650 °C




Note:
Dimensions and positions of the holes on a rectangular cable entry see below.
Details see page 491

Supply:
1 unit


NSYTSA2414SE


Characteristics	Compatibility	Cut-out	Diameter of the cable entry (Ø mm)						References
		Ø (mm)	No.	4.3-8.1	3-6.5	5-9.2	8-12.5	9.6-15.9	
Multi-R	All	112 x 36	14	-	6	4	-	-	**NSYTSA2414SE**
Multi-R	All	112 x 36	17	-	-	17	-	-	**NSYTSA2417SE**
Multi-R	All	112 x 36	22	-	16	4	2	-	**NSYTSA2422SE**
Multi-R	All	112 x 36	23	23	-	-	-	-	**NSYTSA2423SE**
Multi-R	All	112 x 36	29	-	29	-	-	-	**NSYTSA2429SE**

NSYTSA2414SE




KDP 24/14

NSYTSA2417SE




KDP 24/17

NSYTSA2429SE




KDP 24/29

NSYTSA2422SE



KDP 24/22

NSYTSA2423SE



KDP 24/23

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Multi-T

All

- Material: TPE
- Color: RAL 7035 gray
- Cable entry material: Soft membrane
- Cable glands to be fitted: No
- Installation options:
  On cable gland plate adapter or directly on enclosure
- Flexibility of the installation: Medium
- Reversibility: Medium
- Ingress protection rating: IP66 according to IEC 60529
  (IP65 for **NSYAECPFLBP**)
- Cable retention: Low
- Cable diameter (mm): From 5 to 60
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): 214 x 90 (FL21)
- External dimensions (mm): 214 x 88
- Flame resistance: 650 °C
- Temperature range: -40 °C to +100 °C


Note:
Details see page 491

- Type FL21



NSYAECPFLT25

Characteristics	Compatibility	Diameter of the cable entry (Ø mm)												References
		No.	5-7	6-10	8-12	8-16	10-14	12-18	14-20	17-32	20-26	24-54	30-60	
Multi-T, metal plate	All	0	-	-	-	-	-	-	-	-	-	-	-	**NSYAECPFLBP**
Multi-T	All	7	-	-	-	4	-	-	-	-	-	2	1	**NSYAECPFLT7**
Multi-T	All	27	4	-	4	-	13	-	4	-	2	-	-	**NSYAECPFLT25**
Multi-T	All	37	-	4	14	-	16	2	-	1	-	-	-	**NSYAECPFLT35**


NSYAECPFLBP




NSYAECPFLT7



NSYAECPFLT25



NSYAECPFLT35



Multi-H

All


- Material: Fiberglass-reinforced polycarbonate
- Color: RAL 7035 gray
- Cable entry material: Hard-plastic
- Cable glands to be fitted: Yes
- Installation options:
  On cable gland plate adapter or directly on enclosure
- Flexibility of the installation: Low
- Reversibility: Medium
- Ingress protection rating: IP65 according to IEC 60529
- Cable retention: High (with cable clamp)
- Cable diameter (mm): From 12 to 25
- Cable Installation time: Slow
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): 214 x 90 (FL21)
- External dimensions (mm): 215 x 85
- Flame resistance: 750 °C
- Temperature range: For normal operation: -40 °C to +80 °C;
  For a short time: -40 °C to +120 °C

Note:
Details see page 492

- Type FL21


NSYTSAKFL

Characteristics	Compatibility	L1 (mm)	L2 (mm)	H (mm)	Diameter of the cable entry (Ø mm)			References
					M12	M12 or M20	M16 or M25	
Multi-H	All	10	215	85	4	4	4	**NSYTSAKFL**



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries

Multiple Entries

Multi-CS

All


- Material: Reinforced polypropylene and TPE. halogen-free
- Color: Black
- Cable entry material: Soft membrane
- Cable glands to be fitted: No
- Installation options:
  On cable gland plate adapter or directly on enclosure
- Flexibility of the installation: Full
- Reversibility: Full
- Ingress protection rating: IP65 according to IEC 60529
- Cable retention: Medium
- Cable diameter (mm): Up to 22
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: +++
- Cable entries for cables with connectors: Yes
- Cut-out dimensions (mm): 112 x 36
- External dimensions (mm): 148 x 58 x 15; 148 x 58 x 18
- Certificates: UL recognized (UR)
- Temperature range: -30 °C to +100 °C

Note:
Details see page 491

Supply:
1 unit


NSYDCD2412

Characteristics	Compatibility	Cut-out	Diameter of the cable entry (Ø mm)			References
		(mm)	Number	2-12	12-24	
Multi-CS	All	112 x 36	12	12	-	**NSYDCD2412**
Multi-CS	All	112 x 36	4	-	4	**NSYDCD244**
Multi-CS	All	112 x 36	8	6	2	**NSYDCD248**
Multi-CS	All	112 x 36	9	8	1	**NSYDCD249**



Grommets for Cable Entries

All

Supply:
Small … plugs: 12 units. Reference per unit. To be ordered in multiples of 12 (12,24,36, etc.).
Large … plugs: 4 units. Reference per unit. To be ordered in multiples of 4 (4,8,12, etc.)


NSYCEJDS2

Characteristics	Compatibility	Cable Ø (mm)	References
Grommets for cable entries, small	All	2-3	**NSYCEJDS2**
Grommets for cable entries, small	All	3-4	**NSYCEJDS3**
Grommets for cable entries, small	All	4-5	**NSYCEJDS4**
Grommets for cable entries, small	All	5-6	**NSYCEJDS5**
Grommets for cable entries, small	All	6-7	**NSYCEJDS6**
Grommets for cable entries, small	All	7-8	**NSYCEJDS7**
Grommets for cable entries, small	All	8-9	**NSYCEJDS8**
Grommets for cable entries, small	All	9-10	**NSYCEJDS9**
Grommets for cable entries, small	All	10-11	**NSYCEJDS10**
Grommets for cable entries, small	All	11-12	**NSYCEJDS11**
Grommets for cable entries, large	All	12-13	**NSYCEJDL12**
Grommets for cable entries, large	All	13-14	**NSYCEJDL13**
Grommets for cable entries, large	All	14-15	**NSYCEJDL14**
Grommets for cable entries, large	All	15-16	**NSYCEJDL15**
Grommets for cable entries, large	All	16-17	**NSYCEJDL16**
Grommets for cable entries, large	All	17-18	**NSYCEJDL17**
Grommets for cable entries, large	All	18-19	**NSYCEJDL18**
Grommets for cable entries, large	All	19-20	**NSYCEJDL19**
Grommets for cable entries, large	All	20-21	**NSYCEJDL20**
Grommets for cable entries, large	All	21-22	**NSYCEJDL21**

Blanking Plugs

All

Supply:
Small … plugs: 12 units. Reference per unit. To be ordered in multiples of 12 (12,24,36, etc.).
Large … plugs: 4 units. Reference per unit. To be ordered in multiples of 4 (4,8,12, etc.)


NSYCEJDS0

Characteristics	Compatibility	References
Blanking plugs, small	All	**NSYCEJDS0**
Blanking plugs, large	All	**NSYCEJDL0**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PrismaSeT

- Material: Insulated material
- Color: RAL 9003
- Cable entry material: Soft membrane
- Cable glands to be fitted: No
- Installation options:
  On cable gland plate adapter or directly on enclosure
- Flexibility of the installation: Medium
- Reversibility: Medium
- Ingress protection rating: IP55 according to IEC 60529
- Cable retention: Low
- Cable diameter (mm): From 28 to 60 (FL21), From 7 to 72 (rectangular)
- Cable Installation time: Fast
- Quantity of cables to be fitted for a given surface: ++
- Cable entries for cables with connectors: No
- Cut-out dimensions (mm): 214 x 90 (FL21)
- External dimensions (mm): 216 x 84

PrismaSeT, Plain

All


LVS08881

- Solid cable gland plates


Note:
Details see page 492


Characteristics	Compatibility	Type	References
PrismaSeT, plain	All	FL21	**LVS08881**


PrismaSeT, Pre-Drilled

All


LVS08892


LVS08895


LVS08898


LVS08899


- Suitable for receiving cable glands with metric pitch

Note:
Reference **LVS08898** is made up of:
3 cables with diameters from 14 to 26.
4 cables with diameters from 10 to 20.
32 cables with diameters from 7 to 16.
Details see page 492

Characteristics	Compatibility	Type	References
PrismaSeT, pre-drilled, with 4 entries 2 x M20 or M32 + 2 x M25 or M40	All	FL21	**LVS08892**
PrismaSeT, pre-drilledn, with 13 entries 5 x M16 or M25 + 8 x M20	All	FL21	**LVS08895**
PrismaSeT, pre-drilled, with 39 entries Ø 7 - 26 mm	All	opening 225 x 137 mm	**LVS08898**
PrismaSeT, pre-drilled, with 2 entries Ø 33 - 72 mm	All	opening 225 x 137 mm	**LVS08899**

PrismaSeT, Membrane

All


LVS08897

- Membrane to be drilled according to the required diameter

Note:
Details see page 492

Characteristics	Compatibility	Type	References
PrismaSeT, membrane, 2 entries, 2 x Ø 28 - 60 mm	All	FL21	**LVS08897**

Multi-cable Disc

Characteristics	Multi-cable disc		Cable gland gasket	Blanking plug	Transport plug
	 IMT36157		 IMT36151	 PB500269_23_nb	 PB500270_19_nb
	The multi-cable bushing permits several cables to be passed through a single cable gland.			**It is screwed into the cable gland's plate.**	**It is installed to block the cable gland during transport or during maintenance operations.**
Material	EDPM rubber		EDPM rubber	PA6	PA6
Color	Black		Black	RAL 7035 gray	Black
Ingress protection rating	-		IP68	-	-
Standards	-		-	-	-
Other characteristics	-		-	-	-
Supply	Set of 40 (M16 and M20), 20 (M25 and M32)		Set of 100 (M12 to M20), 50 (M25 and M32), 25 (M40)	Pack of 40 plugs (M12 to M20), 20 plugs (M25 and M32), 10 plugs (M40)	Pack of 40 plugs (M16 to M20), pack of 20 (M25 and M32), pack of 10 (M40)
Ø	**Number / Ø (mm)**	**References**	**References**	**References**	**References**
M12	-	-	**IMT36151**	**IMT36161**	-
M16	-	-	**IMT36152**	**IMT36162**	**IMT36167**
M20	3 x Ø 4	**IMT36158**	**IMT36153**	**IMT36163**	**IMT36168**
M25	-	-	**IMT36154**	**IMT36164**	**IMT36169**
M32	-	-	**IMT36155**	-	-

6


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries

Cable Gland Plates

Standard Cable Gland Plates

S3D SFN



- Plate delivered as standard with the PanelSeT S3D universal enclosure.
- Drilling marks with 25 mm spacing.
- Material: Steel, structured finish RAL 7035 gray
- Thickness: 15-20/10^{e} mm
- Ingress protection rating: IP66 according to IEC 60529
- Fixing: Fixing by 4, 6, 8, 10 or 12 screws, according to the model

Supply:
Delivered with sealing gasket and fixing hardware


NSYTLA

Characteristics	Compatibility	Enclosures (mm)		Type	Width (A)	Depth (B)	Number of Ø 6 holes	References
		Width	Depth					
Standard	S3D	200-250	150	A	140	80	4	**NSYTLA**
Standard	S3D	300-400	150	B	245	80	4	**NSYTLB**
Standard	S3D, SFN	300	200	C	245	130	6	**NSYTLC**
Standard	S3D	400	200-250	D	345	130	8	**NSYTLD**
Standard	S3D	500	200-250	E	445	130	8	**NSYTLE**
Standard	S3D	600	200-250	F	545	130	10	**NSYTLF**
Standard	S3D	600	300-400	G	495	220	12	**NSYTLG**
Standard	S3D	800	250-300-400	D	345	130	-	2x **NSYTLD**
Standard	S3D	1000-1200	300-400	E	445	130	-	2x **NSYTLE**

CRN

- The cable gland plate for PanelSeT CRN helps guarantee water and dust tightness.
- Material: Steel
- Color: RAL 7035 gray
- Installation: Fixing with screws, it is flattened with the body
- For type E cable entry, use two **NSYTLCRNC**.

Supply:
Included as a standard with the PanelSeT CRN enclosure It is delivered with a separate seal: It allows easy cut-outs with no risk of damaging the seal and can be easily repainted



NSYTLCRNO

Characteristics	Compatibility	Width (mm)	Depth (mm)	To be coupled with entry	References
Standard cable gland plate	CRN	200	150	0	**NSYTLCRNO**
Standard cable gland plate	CRN	250	150/200	A	**NSYTLCRNA**
Standard cable gland plate	CRN	300	150/200	B	**NSYTLCRNB**
Standard cable gland plate	CRN	400/500	150	B	**NSYTLCRNB**
Standard cable gland plate	CRN	400	200/250	C	**NSYTLCRNC**
Standard cable gland plate	CRN	500/600	200/250/300/400	D	**NSYTLCRND**
Standard cable gland plate	CRN	800	200/250/300	E	2 x **NSYTLCRNC**
Standard cable gland plate	CRN	800	400	C	2 x **NSYTLCRNC**
Standard cable gland plate	CRN	1000/1200	300/400	D	2 x **NSYTLCRND**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Aluminum Cable Gland Plate

S3D



- Suitable for non-magnetic applications.
- Material: Brushed-finish aluminum
- Thickness: 30/10[e] mm
- Ingress protection rating: IP66 according to IEC 60529
- Fixing: Fixing by 4, 10 or 12 screws, according to the model´

Supply:
Delivered with sealing gasket and fixing hardware


NSYTLBU

Characteristics	Compatibility	Enclosures (mm)		Type	Width (A)	Depth (B)	Number of Ø 6 holes	References
		Width	Depth					
Aluminum cable gland plate	S3D	300-400	150	B	245	80	4	**NSYTLBU**
Aluminum cable gland plate	S3D	600	200-250	F	545	130	10	**NSYTLFU**
Aluminum cable gland plate	S3D	600	300-400	G	495	220	12	**NSYTLGU**

Insulated Cable Gland Plates

CRN

- With a polyurethane sealing gasket.
- Excellent thermal resistance.
- Pre-marked holes for cable entrie plates.
- Material: Self-extinguishing ABS with 30% fiberglass
- Color: RAL 7035 gray
- Installation: Pre-marked holes with diameter Pg for coupling of cable glands, membrane glands, tubes, etc
- For type E cable entry, use two **NSYTSACRNC**.




NSYTSACRNB

Characteristics	Compatibility	Fig.	Width (mm)	Depth (mm)	To be coupled with entry	References
Insulated cable gland plate	CRN	2	300	150/200	B	**NSYTSACRNB**
Insulated cable gland plate	CRN	3	400/500	150	B	**NSYTSACRNB**
Insulated cable gland plate	CRN	3	400	200/250	C	**NSYTSACRNC**
Insulated cable gland plate	CRN	4	500/600	200/250/300	D	**NSYTSACRND**
Insulated cable gland plate	CRN	3	800	200/250/300	E	2 x **NSYTSACRNC**
Insulated cable gland plate	CRN	4	1000/1200	300/400	D	2 x **NSYTSACRNC**
Insulated cable gland plate	CRN	3	1000/1200	400	C	2 x **NSYTSACRND**

Fig. 1




Fig. 2




Fig. 3






Fig. 4





- PG 11 (18.6 mm)
- PG 16 (20.4 mm)
- PG 16 (22.5 mm)
- PG 21 / 11 (28.3 / 18.6 mm)
- PG 29 / 16 (37 / 22.5 mm)
- PG 36 / 29 (47 / 37 mm)

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Cable Entries

Cable Gland Plates


Steel Adapter Plate for FL21 Membranes

S3D SFN

FL21




NSYTLCFL
NSYTLDFL
NSYTLFEL
NSYTLFFL
NSYTLGFL



NSYTLF2FL
NSYTLG2FL

Application Example



Our membrane can be easily adapted to fit onto all our metal enclosures using the adapter plate.

- Allows the mounting of FL13 and FL21 membranes on every type of enclosure.
- Our membrane can be easily adapted to fit onto all our metal enclosures using the adapter plate.
- Ingress protection rating IP55 according to IEC 60529.
- Cut-outs for installation of membranes type FL 21 (Cut-out FL13 for depth 150 mm; And cut-out FL21 for other depths).
- Material: Steel, structured finish RAL 7035 gray
- Thickness: 15/10e mm
- Fixing: Fixing by 4, 6, 8, 10 or 12 screws, according to the model
- **NSYTLG2FL** with 2 FL21 cut-outs

Supply:
Delivered with fixing screws and gasket



NSYTLCFL


Characteristics	Compatibility	Type	Plate dimensions (mm)		Cut-out dimensions (mm)		References
			A	B	H	I	
Steel adapter plate for FL21 membranes	S3D, SFN	C	245	130	212	97	**NSYTLCFL**
Steel adapter plate for FL21 membranes	S3D	D	345	130	312	97	**NSYTLDFL**
Steel adapter plate for FL21 membranes	S3D	E	445	130	412	97	**NSYTLEFL**
Steel adapter plate for FL21 membranes	S3D	F	545	130	512	97	**NSYTLFFL**
Steel adapter plate for FL21 membranes	S3D	F	545	130	512	97	**NSYTLF2FL**
Steel adapter plate for FL21 membranes	S3D	G	495	220	462	187	**NSYTLGFL**
Steel adapter plate for FL21 membranes	S3D	G	495	220	462	187	**NSYTLG2FL**
Steel adapter plate for FL21 membranes	S3D	D	345	130	312	97	2x **NSYTLDFL**
Steel adapter plate for FL21 membranes	S3D	E	445	130	412	97	2x **NSYTLEFL**

Plain Cable Gland Plate

SM

- Cable-gland plate to be placed on top or bottom of the enclosure
- The design of the compact cable gland plate, coupled with the use of the sealing gasket **NSYCEK** enable maximum dust/water tightness
- Material: Steel painted with epoxy polyester resin
- Color: RAL 7035 gray
- Thicknesses: 10/10e mm

Supply:
Plain plate and fixing elements




NSYSMEC63


Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Plain cable gland plate	SM	600	300	**NSYSMEC63**
Plain cable gland plate	SM	600	400	**NSYSMEC64**
Plain cable gland plate	SM	600	500	**NSYSMEC65**
Plain cable gland plate	SM	800	300	**NSYSMEC83**
Plain cable gland plate	SM	800	400	**NSYSMEC84**
Plain cable gland plate	SM	800	500	**NSYSMEC85**
Plain cable gland plate	SM	800	600	**NSYSMEC86**
Plain cable gland plate	SM	1000	400	**NSYSMEC104**
Plain cable gland plate	SM	1200	300	2x **NSYSMEC63**
Plain cable gland plate	SM	1200	400	2x **NSYSMEC64**
Plain cable gland plate	SM	1200	500	2x **NSYSMEC65**
Plain cable gland plate	SM	1600	400	2x **NSYSMEC84**
Plain cable gland plate	SM	1600	500	2x **NSYSMEC85**
Plain cable gland plate	SM	1600	600	2x **NSYSMEC86**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Plain Cable Gland Plate

Possibilities of Cable Gland Plate Adjustment






SFN MCC SFN IT

- The design of the compact cable gland plate, coupled with the use of the sealing gasket **NSYCEK** provide IP55.
- Material: Galvanized steel
- Thicknesses: 15/10^{e} mm
- Ingress protection rating: IP55 according to IEC 60529 (with the gasket)

Supply:
Plain plate and fixing elements


NSYEC35

Characteristics	Compatibility	(B) Width (mm)	(C) Depth (mm)	References
Plain cable gland plate	SFN, MCC, SFN IT	300	500	**NSYEC35**
Plain cable gland plate	SFN, MCC, SFN IT	300	600	**NSYEC36**
Plain cable gland plate	SFN, MCC, SFN IT	400	400	**NSYEC44**
Plain cable gland plate	SFN, MCC, SFN IT	400	500	**NSYEC45**
Plain cable gland plate	SFN, MCC, SFN IT	400	600	**NSYEC64**
Plain cable gland plate	SFN, MCC, SFN IT	400	800	**NSYEC84**
Plain cable gland plate	SFN, MCC, SFN IT	600	400	**NSYEC64**
Plain cable gland plate	SFN, MCC, SFN IT	600	500	**NSYEC65**
Plain cable gland plate	SFN, MCC, SFN IT	600	600	**NSYEC66**
Plain cable gland plate	SFN, MCC, SFN IT	600	800	**NSYEC68**
Plain cable gland plate	SFN, MCC, SFN IT	600	1000	**NSYEC610**
Plain cable gland plate	SFN, MCC, SFN IT	800	400	**NSYEC84**
Plain cable gland plate	SFN, MCC, SFN IT	800	500	**NSYEC85**
Plain cable gland plate	SFN, MCC, SFN IT	800	600	**NSYEC86**
Plain cable gland plate	SFN, MCC, SFN IT	800	800	**NSYEC88**
Plain cable gland plate	SFN, MCC, SFN IT	800	1000	**NSYEC810**
Plain cable gland plate	SFN, MCC, SFN IT	1000	400	**NSYEC104**
Plain cable gland plate	SFN, MCC, SFN IT	1000	500	**NSYEC105**
Plain cable gland plate	SFN, MCC, SFN IT	1000	600	**NSYEC106**
Plain cable gland plate	SFN, MCC, SFN IT	1000	800	**NSYEC108**
Plain cable gland plate	SFN, MCC, SFN IT	1200	400	**NSYEC124**
Plain cable gland plate	SFN, MCC, SFN IT	1200	500	**NSYEC125**
Plain cable gland plate	SFN, MCC, SFN IT	1200	600	**NSYEC126**
Plain cable gland plate	SFN, MCC, SFN IT	1200	800	**NSYEC128**
Plain cable gland plate	SFN, MCC, SFN IT	1600	400	**NSYEC164**
Plain cable gland plate	SFN, MCC, SFN IT	1600	500	**NSYEC165**
Plain cable gland plate	SFN, MCC, SFN IT	1600	600	**NSYEC166**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Entries


Cable Gland Plates

Plate with 1 Entry

SFN | MCC | SFN IT



Enclosures of 300 and 400 mm width.



Enclosures of 600, 800, 1000 and 1200 mm width.

- Facilitates the entry of cables thanks to a longitudinal opening.
- Material: Galvanized steel
- Thicknesses: 15/10e mm
- The design of the compact cable gland plate, coupled with the use of the sealing gasket **NSYCEK** provides IP45


Supply:
Plate with 1 entry; Self-extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm (helps guarantee good sealing) and fixing elements


NSYEC351

Characteristics	Compatibility	(B) Width (mm)	(C) Depth (mm)	References
Plate with 1 entry	SFN, MCC, SFN IT	300	500	**NSYEC351**
Plate with 1 entry	SFN, MCC, SFN IT	300	600	**NSYEC361**
Plate with 1 entry	SFN, MCC, SFN IT	400	400	**NSYEC441**
Plate with 1 entry	SFN, MCC, SFN IT	400	500	**NSYEC451**
Plate with 1 entry	SFN, MCC, SFN IT	400	600	**NSYEC461**
Plate with 1 entry	SFN, MCC, SFN IT	400	800	**NSYEC481**
Plate with 1 entry	SFN, MCC, SFN IT	600	400	**NSYEC641**
Plate with 1 entry	SFN, MCC, SFN IT	600	500	**NSYEC651**
Plate with 1 entry	SFN, MCC, SFN IT	600	600	**NSYEC661**
Plate with 1 entry	SFN, MCC, SFN IT	600	800	**NSYEC681**
Plate with 1 entry	SFN, MCC, SFN IT	600	1000	**NSYEC6101**
Plate with 1 entry	SFN, MCC, SFN IT	800	400	**NSYEC841**
Plate with 1 entry	SFN, MCC, SFN IT	800	500	**NSYEC851**
Plate with 1 entry	SFN, MCC, SFN IT	800	600	**NSYEC861**
Plate with 1 entry	SFN, MCC, SFN IT	800	800	**NSYEC881**
Plate with 1 entry	SFN, MCC, SFN IT	800	1000	**NSYEC8101**
Plate with 1 entry	SFN, MCC, SFN IT	1000	400	**NSYEC1041**
Plate with 1 entry	SFN, MCC, SFN IT	1000	500	**NSYEC1051**
Plate with 1 entry	SFN, MCC, SFN IT	1000	600	**NSYEC1061**
Plate with 1 entry	SFN, MCC, SFN IT	1000	800	**NSYEC1081**
Plate with 1 entry	SFN, MCC, SFN IT	1200	400	**NSYEC1241**
Plate with 1 entry	SFN, MCC, SFN IT	1200	500	**NSYEC1251**
Plate with 1 entry	SFN, MCC, SFN IT	1200	600	**NSYEC1261**
Plate with 1 entry	SFN, MCC, SFN IT	1200	800	**NSYEC1281**
Plate with 1 entry	SFN, MCC, SFN IT	1600	400	**NSYEC1641**
Plate with 1 entry	SFN, MCC, SFN IT	1600	500	**NSYEC1651**
Plate with 1 entry	SFN, MCC, SFN IT	1600	600	**NSYEC1661**

Plate with 2 Entries

SFN | MCC | SFN IT



- Cable entry for very deep enclosures (600 and 800 mm).
- Two longitudinal openings allowing a large number of cables through.
- Material: Galvanized steel
- Thicknesses: 15/10e mm
- The design of the compact cable gland plate, coupled with the use of the sealing gasket **NSYCEK** provides IP45

Supply:
1 plate with 2 entries; Polyurethane adhesive gasket with cross-section of 15 x 25 mm (helps guarantee good sealing) and fixing elements


NSYEC662

Characteristics	Compatibility	(B) Width (mm)	(C) Depth (mm)	References
Plate with 2 entries	SFN, MCC, SFN IT	400	600	**NSYEC462**
Plate with 2 entries	SFN, MCC, SFN IT	400	800	**NSYEC482**
Plate with 2 entries	SFN, MCC, SFN IT	600	600	**NSYEC662**
Plate with 2 entries	SFN, MCC, SFN IT	600	800	**NSYEC682**
Plate with 2 entries	SFN, MCC, SFN IT	600	1000	**NSYEC6102**
Plate with 2 entries	SFN, MCC, SFN IT	800	600	**NSYEC862**
Plate with 2 entries	SFN, MCC, SFN IT	800	800	**NSYEC882**
Plate with 2 entries	SFN, MCC, SFN IT	800	1000	**NSYEC8102**
Plate with 2 entries	SFN, MCC, SFN IT	1000	600	**NSYEC1062**
Plate with 2 entries	SFN, MCC, SFN IT	1000	800	**NSYEC1082**
Plate with 2 entries	SFN, MCC, SFN IT	1200	600	**NSYEC1262**
Plate with 2 entries	SFN, MCC, SFN IT	1200	800	**NSYEC1282**
Plate with 2 entries	SFN, MCC, SFN IT	1600	600	**NSYEC1662**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Brush-Type Cable Entry Gasket

SFN

- For plates with 1 or 2 cable entries.
- The cables can have different diameters.
- No IP degree of protection



NSYBCE6

Characteristics	Compatibility	Width (mm)	References
PanelSeT SFN Brush-type cable entry gasket	SFN	600	**NSYBCE6**
PanelSeT SFN Brush-type cable entry gasket	SFN	800	**NSYBCE8**
PanelSeT SFN Brush-type cable entry gasket	SFN	1000	**NSYBCE10**
PanelSeT SFN Brush-type cable entry gasket	SFN	1200	**NSYBCE12**
PanelSeT SFN Brush-type cable entry gasket	SFN	1600	**NSYBCE16**

SM

- Brush-type gasket for installation on the cable gland plates.
- The cables can have different diameters.
- No IP degree of protection



NSYSMBCE6

Characteristics	Compatibility	Width (mm)	References
PanelSeT SM-Brush-type cable entry gasket	SM	600	**NSYSMBCE6**
PanelSeT SM-Brush-type cable entry gasket	SM	800	**NSYSMBCE8**
PanelSeT SM-Brush-type cable entry gasket	SM	1000	**NSYSMBCE10**
PanelSeT SM-Brush-type cable entry gasket	SM	1200	2x **NSYSMBCE6**
PanelSeT SM-Brush-type cable entry gasket	SM	1600	2x **NSYSMBCE8**

Foam Cable Entry Gasket

SFN

- Spare gasket, made from self-extinguishing expanded polyurethane with a cross-section of 15 x 25 mm, for fixing on cable gland plates.




NSYCEJ

Characteristics	Compatibility	References
PanelSeT SFN Foam cable entry gasket	SFN	**NSYCEJ**

Plain Cable Entry Plate

PLAZ PLAZT



- Easy drilling in specific customized version.
- Not compatible with: Adapter plates, step slides, internal door and chassis for modular distribution.
- Material: Polyester reinforced with fiberglass
- Thickness: 4 mm

Supply:
Delivered with the fixings required for installation



NSYECPLAZ53G

Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Plain cable entry plate	PLAZ, PLAZT	500	320	**NSYECPLAZ53G**
Plain cable entry plate	PLAZ, PLAZT	500	420	**NSYECPLAZ54G**
Plain cable entry plate	PLAZ, PLAZT	750	320	**NSYECPLAZ73G**
Plain cable entry plate	PLAZ, PLAZT	750	420	**NSYECPLAZ74G**
Plain cable entry plate	PLAZ, PLAZT	1000	320	**NSYECPLAZ103G**
Plain cable entry plate	PLAZ, PLAZT	1000	420	**NSYECPLAZ104G**
Plain cable entry plate	PLAZ, PLAZT	1250	320	**NSYECPLAZ123G**
Plain cable entry plate	PLAZ, PLAZT	1250	420	**NSYECPLAZ124G**

Sealing Gasket

SFN SFN IT

- Sealing gasket, made from ethylene-propylene with a cross-section of 3 x 10 mm, for mounting on the perimeter of the cable gland plates. Adhesive to help guarantee good sealing.



NSYCEK

Characteristics	Compatibility	References
Sealing gasket	SFN	**NSYCEK**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Holding


Cable Fixing


Lower Cable-Guide Cross-Rail

SM SFN SMX SFX

- It allows the quick fixing of cables entering and exiting the enclosure.
- Depth adjustable every 25 mm.
- Material: Galvanized steel

Fixing:
- PanelSeT SFN: for suitable enclosures with widths of 1200 and 1600 mm, use the adaptation kit for two-door suitable enclosures, see page 521
- PanelSeT SM: for floor-standing enclosures with a width of 1200 mm, a top/bottom mounting rail installed in central position is required
- PanelSeT SFX: no adaptation piece is required for the 1200 mm suitable enclosures
- PanelSeT SMX: no adaptation piece is required for the 1600 mm floor-standing enclosures





Supply:
1 cable-guide cross-rail and fixing elements


NSYCFP60


Characteristics	Compatibility	Width (mm)	References
Lower cable-guide cross-rail	SM, SFN, SMX, SFX	600	**NSYCFP60**
Lower cable-guide cross-rail	SM, SFN, SMX, SFX	800	**NSYCFP80**
Lower cable-guide cross-rail	SM, SFN, SMX, SFX	1000	**NSYCFP100**
Lower cable-guide cross-rail	SM, SFN, SMX, SFX	1200	2x **NSYCFP60**
Lower cable-guide cross-rail	SM, SFN, SMX, SFX	1600	2x **NSYCFP80**


Cable-Guide Cross-Rails for Framework

SM SFN SMX SFX

Support types:
- Angle support at 90°: For vertical cable fixing.
- Angle support at 120°: For fixing cables near the cable entry.
- Material: Galvanized steel

Fixing:
- PanelSeT SFN and SFX: support for direct mounting on the framework, cross-rails or rails
- PanelSeT SM: fixing on the bottom mounting rail, or on the floor-standing enclosure by means of adaptation rails and 40 mm universal cross-rails (1 row) in vertical position
- PanelSeT SMX: fixing on the bottom mounting rail and 40 mm universal cross-rails (1 row) in vertical position





Supply:
2 supports and fixing elements


NSYCFS96

Characteristics	Compatibility	Support angle	Width (mm)	Refere nces
Cable-guide cross-rails for framework	SM, SFN, SMX, SFX	90°	600	**NSYCFS96**
Cable-guide cross-rails for framework	SM, SFN, SMX, SFX	90°	800	**NSYCFS98**
Cable-guide cross-rails for framework	SM, SFN, SMX, SFX	120°	800	**NSYCFS128**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


L-Rail for Fixing Cables

SM SFN SMX SFX

- Rail for fixing cables entering from the bottom.
- Adjustable depth with a pitch of 25 mm.
- It is not possible to mount it on a plinth cross-rail.
- Material: Galvanized steel



Fixing:
- PanelSeT SFN and SFX: fixing to the bottom frame, above the cable entry, or else to the plinth, using the plinth cross-rails, see page 467
- PanelSeT SM/SMX: fixing to the bottom adjustment rails, above the cable entry, or else to the plinth, using the plinth cross-rails, see page 467
- The cables are fixed to the rail by means of metal clamps






Supply:
One rail, two mounting supports and fixing elements


NSYFCG60


Characteristics	Compatibility	Width (mm)	References
L-rail for fixing cables	SM, SFN, SMX, SFX	600	**NSYFCG60**
L-rail for fixing cables	SM, SFN, SMX, SFX	800	**NSYFCG80**
L-rail for fixing cables	SM, SFN, SMX, SFX	1000	**NSYFCG100**

Plastic Cable Support

SM SFN SMX SFX



Supply:
10 units. Reference by unit. Order by multiples of 10 (10, 20, 30...)


NSYSCCDINLG75

- It clips or screws onto 35-mm symmetric rails or a C-shaped rail.
- Fixing: Quick and easy fixing of cables using cable ties

Characteristics	Compatibility	Max. number of cables	Width (mm)	References
Plastic cable support	SM, SFN, SMX, SFX	5	75	**NSYSCCDINLG75**
Plastic cable support	SM, SFN, SMX, SFX	9	140	**NSYSCCDINLG140**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Cable Holding

Cable Ducts

Spiral Cable Duct

All

- Spiral strip for bundling cables.
- Allows cables to enter between the body and the door.
- Color: Colorless

Supply:
One 50 m reel


NSYTC12100

Characteristics	Compatibility	Tightening range (mm)	Ø Inner (mm)	Ø Outer (mm)	References
Corrugated cable tube	All	12 to 100	9	12	**NSYTC12100**

Cable-Duct


All

- Temperature resistance: -5 ... +60 °C
- Behaviour in fire: Material V0 according to UL 94
- Fire resistance: 960 °C according to IEC 60695-2-1/1
- Maximum capacity of H07.V.K 1.5 mm² flexible cable (filling factor: 0.6)
- With lateral through slots and rear perforations.
- Material: Rigid PVC
- Color: RAL 7030 gray or RAL 5000 blue
- Standards: Compliance with standards VDE 0660/506 and DIN 43659

Supply:
8 units. Supplied in lengths of 2 m


AK2GD7550

Characteristics	Compatibility	Width (mm)	Height (mm)	Color	References
Cable-duct	All	25	25	Gray	**AK2GD2525**
Cable-duct	All	25	50	Gray	**AK2GD2550**
Cable-duct	All	37.5	50	Gray	**AK2GD3750**
Cable-duct	All	37.5	75	Gray	**AK2GD3775**
Cable-duct	All	50	50	Gray	**AK2GD5050**
Cable-duct	All	50	75	Gray	**AK2GD5075**
Cable-duct	All	75	50	Gray	**AK2GD7550**
Cable-duct	All	75	75	Gray	**AK2GD7575**
Cable-duct	All	100	75	Gray	**AK2GD10075**
Cable-duct	All	125	75	Gray	**AK2GD12575**
Cable-duct	All	30	35	Blue	**AK2GA33**
Cable-duct	All	30	55	Blue	**AK2GA35**
Cable-duct	All	30	90	Blue	**AK2GA39**
Cable-duct	All	30	144	Blue	**AK2GA315**
Cable-duct	All	60	55	Blue	**AK2GA65**
Cable-duct	All	60	90	Blue	**AK2GA69**
Cable-duct	All	60	144	Blue	**AK2GA615**


AK2GA65

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Covers for Cable-Duct

All

- Temperature resistance: -5 ... +60 °C
- Behaviour in fire: Material V0 according to UL 94
- Fire resistance: 960 °C according to IEC 60695-2-1/1
- Maximum capacity of H07.V.K 1.5 mm² flexible cable (filling factor: 0.6)
- Replacement covers.
- Material: Rigid PVC
- Color: RAL 7030 gray or RAL 5000 blue
- Standards: Compliance with standards VDE 0660/506 and DIN 43659

Supply:
8 units. Supplied in lengths of 2 m



AK2CD75



AK2CA6

Characteristics	Compatibility	Width (mm)	Height (mm)	Color	For Cable-duct Ref.	References
Covers for cable-duct	All	25	25	Gray	AK2GD2525	**AK2CD25**
Covers for cable-duct	All	25	50	Gray	AK2GD2550	**AK2CD25**
Covers for cable-duct	All	37.5	50	Gray	AK2GD3750	**AK2CD37**
Covers for cable-duct	All	37.5	75	Gray	AK2GD3775	**AK2CD37**
Covers for cable-duct	All	50	50	Gray	AK2GD5050	**AK2CD50**
Covers for cable-duct	All	50	75	Gray	AK2GD5075	**AK2CD50**
Covers for cable-duct	All	75	50	Gray	AK2GD7550	**AK2CD75**
Covers for cable-duct	All	75	75	Gray	AK2GD7575	**AK2CD75**
Covers for cable-duct	All	100	75	Gray	AK2GD10075	**AK2CD100**
Covers for cable-duct	All	125	75	Gray	AK2GD12575	**AK2CD125**
Covers for cable-duct	All	30	35	Blue	AK2GA33	**AK2CA3**
Covers for cable-duct	All	30	55	Blue	AK2GA35	**AK2CA3**
Covers for cable-duct	All	30	90	Blue	AK2GA39	**AK2CA3**
Covers for cable-duct	All	30	144	Blue	AK2GA315	**AK2CA3**
Covers for cable-duct	All	60	55	Blue	AK2GA65	**AK2CA6**
Covers for cable-duct	All	60	90	Blue	AK2GA69	**AK2CA6**
Covers for cable-duct	All	60	144	Blue	AK2GA615	**AK2CA6**

Ø 22 mm Cable-Duct Support

CRN S3D SM SFN S3X SMX SFX PLM PLA S3CM SD




NSYSPCP


- Installed on the door of the wall-mounted or floor-standing enclosure combined with Ø 22 mm elements.
- Material: Treated steel


Supply:
10 units. Reference by unit.
Order by multiples of 10 (10, 20, 30...)

Characteristics	Compatibility	References
Ø 22 mm cable-duct support	CRN, S3D, SM, SFN, S3X, SMX, SFX, PLM, PLA, S3CM, SD	**NSYSPCP**

Cable-duct Support on Technical Upright

SM SFN SMX SFX PLA SD




NSYCDS

- Allows cable ducts to be installed on technical uprights, while increasing the usable surface of the equipment (up to 20% according to the width of the cable duct).
- Material: Galvanized steel

Supply:
10 units. Reference by unit.
Order by multiples of 10 (10, 20, 30...)

Characteristics	Compatibility	References
Cable-duct support on technical upright	SM, SFN, SFX, SMX, PLA, SD	**NSYCDS**

Plastic Cable-Duct Support

All


NSYSPC

- Clips onto the Telequick mounting plate or the 35-mm DIN rail.
- Includes a screw for fixing the cable ducts through the 6.5 x 14 mm drill holes made in the back.
- The 2 functions, clipping and bolting, provide considerable time savings.
- Respects electrical insulation.
- Material: Black polyamide.



Supply:
20 units. Reference by unit.
Order by multiples of 20 (20, 40, 60...)

Characteristics	Compatibility	References
Plastic cable-duct support	All	**NSYSPC**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

6


Equipment Assembly Accessories

Mounting Plates

Plain Mounting Plate

SBM SBX

- Material: Galvanized steel
- Installation: Mounting by means of 2* or 4 x Ø 5 mm self-tapping screws, Pozidriv head, ref. **NSYAMFSB**. Mounting plate installation points compatible with many other brands of accessories.




Comment:
* Only 2 screws for mounting plates with height of 150 mm

Supply:
1 unit, supplied without screws


NSYMM11SB

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Plain mounting plate	SBM, SBX	125	135	**NSYMM11SB**
Plain mounting plate	SBM	125	185	**NSYMM12SB**
Plain mounting plate	SBM, SBX	125	285	**NSYMM13SB**
Plain mounting plate	SBM	125	385	**NSYMM14SB**
Plain mounting plate	SBM, SBX	175	185	**NSYMM22SB**
Plain mounting plate	SBM, SBX	175	265	**NSYMM23SB**
Plain mounting plate	SBM, SBX	175	385	**NSYMM24SB**
Plain mounting plate	SBM	175	485	**NSYMM25SB**
Plain mounting plate	SBM	175	585	**NSYMM26SB**
Plain mounting plate	SBM	175	785	**NSYMM28SB**
Plain mounting plate	SBM, SBX	275	285	**NSYMM33SB**
Plain mounting plate	SBM	275	385	**NSYMM34SB**
Plain mounting plate	SBM	275	485	**NSYMM35SB**
Plain mounting plate	SBM	275	585	**NSYMM36SB**
Plain mounting plate	SBM	275	785	**NSYMM38SB**
Plain mounting plate	SBM	375	385	**NSYMM44SB**
Plain mounting plate	SBM	375	485	**NSYMM45SB**
Plain mounting plate	SBM	375	585	**NSYMM46SB**
Plain mounting plate	SBM	375	785	**NSYMM48SB**

TBS TBP




- Mounting plates made to adapt to all usage scenarios.
- Material: Galvanized steel
- Thickness: 15/10e mm
- Installation: Fixing by means of Ø 4 mm self-tapping screws, Pozidrive and slotted head, ref. **NSYAMFSTB**

Supply:
Plates supplied without screws


NSYAMPM1916TB

Characteristics	Compatibility	Box		Dimensions			References
		Height (mm)	Width (mm)	A (mm)	B (mm)	Minor pack.	
Mounting plate	TBS, TBP	192	164	168.5	140	1	**NSYAMPM1916TB**
Mounting plate	TBS, TBP	241	194	215	168.5	1	**NSYAMPM2419TB**
Mounting plate	TBS, TBP	291	241	265	215	1	**NSYAMPM2924TB**
Mounting plate	TBS, TBP	341	291	315	265	1	**NSYAMPM3429TB**



- Mounting plates made to adapt to all usage scenarios.
- Material: Insulated polyester plate reinforced with fiberglass, halogen-free: Glow wire resistance 750 °C.
- Thickness: 25/10e mm
- Installation: Fixing by means of Ø 4 mm self-tapping screws, Pozidrive and slotted head, ref. **NSYAMFSTB**

Supply:
Plates supplied without screws


NSYAMPA1916TB

Characteristics	Compatibility	Box		Dimensions			References
		Height (mm)	Width (mm)	A (mm)	B (mm)	Minor pack.	
Insulated mounting plate	TBS, TBP	192	164	168.5	140	1	**NSYAMPA1916TB**
Insulated mounting plate	TBS, TBP	241	194	215	168.5	1	**NSYAMPA2419TB**
Insulated mounting plate	TBS, TBP	291	241	265	215	1	**NSYAMPA2924TB**
Insulated mounting plate	TBS, TBP	341	291	315	265	1	**NSYAMPA3429TB**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Mounting Plates


Plain Mounting plate


CRN | S3D | S3X | PLM | S3DB | S3HD | S3DEX | S3HF

- Material: Galvanized steel
- Maximum load:PLM: 150 kg/m²
- S3D, S3X, CRN: 250 kg/m²
- Supply: One mounting plate without fixing elements




Characteristics	Compatibility	Height (mm)	width (mm)	References
Plain mounting plate	CRN	150	150	**NSYMM22**
Plain mounting plate	CRN	200	150	**NSYMM2520**
Plain mounting plate	CRN, S3D, S3X, PLM	250	200	**NSYMM3025**
Plain mounting plate	S3DB	200	350	**NSYMM2540**
Plain mounting plate	S3DB	200	450	**NSYMM2550**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	250	150	**NSYMM32**
Plain mounting plate	CRN, S3D, S3X, S3DEX	250	250	**NSYMM33**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	250	350	**NSYMM43**
Plain mounting plate	CRN	250	400	**NSYMM3045**
Plain mounting plate	S3D	450	250	**NSYMM53**
Plain mounting plate	S3DB	250	550	**NSYMM36**
Plain mounting plate	CRN, S3D, S3X, S3DEX	350	350	**NSYMM44**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	350	550	**NSYMM64**
Plain mounting plate	S3DB	350	750	**NSYMM48**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	450	350	**NSYMM54**
Plain mounting plate	CRN, S3D	450	450	**NSYMM55**
Plain mounting plate	CRN, S3D	550	450	**NSYMM65**
Plain mounting plate	CRN, S3D, S3X, S3HD, S3DEX, S3HF	550	550	**NSYMM66**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	650	450	**NSYMM75**
Plain mounting plate	S3DB	650	550	**NSYMM76**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	750	550	**NSYMM86**
Plain mounting plate	CRN, S3D, S3X, S3HD	750	750	**NSYMM88**
Plain mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	950	750	**NSYMM108**
Plain mounting plate	CRN, S3D, S3HD	950	550	**NSYMM106**
Plain mounting plate	CRN, S3D, S3X	950	950	**NSYMM1010**
Plain mounting plate	CRN, S3D	1150	550	**NSYMM126**
Plain mounting plate	CRN, S3D, S3X	1150	750	**NSYMM128**
Plain mounting plate	CRN, S3D, S3X	1150	950	**NSYMM1210**
Plain mounting plate	CRN, S3D	1150	1150	**NSYMM1212**
Plain mounting plate	CRN, S3D	1350	950	**NSYMM1410**





Exclusive to Sizes Equal to or Greater Than 1000 x 800 mm



From Size 1000 x 1000 mm


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories


Mounting Plates

Perforated Mounting Plate Telequick

CRN | S3D | S3X | PLM | S3HD | S3DEX | S3HF



- Grille with 11 x 26 mm drill holes, with a step of 15 x 30 mm, for direct installation, with clip nuts, of all the devices with fixing at 2, 3 or 4 points, by screws with diameters of 3, 4, 5 or 6 mm.
- Direct installation on M8 inserts at the rear of the enclosure or on step slides for depth adjustment (see page 521).
- The enclosures with height of ≥ 1000 mm have intermediate impressions for installing mounting plates of a lesser height (M8 inserts, ref. **NSYTEX8**, to be ordered separately).
- Material: Galvanized steel
- Maximum load: 150 kg/m²
- Supply: One mounting plate




Characteristics	Compatibility	Height (mm)	Width (mm)	Number of perforations		References
				height (mm)	width (mm)	
Telequick mounting plate	CRN, S3D, S3X, S3HD, S3DEX	250	150	16	5	**NSYMR32**
Telequick mounting plate	CRN, S3D, PLM, S3X	250	200	16	8	**NSYMR3025**
Telequick mounting plate	CRN, S3D, S3X, S3DEX	250	250	16	9	**NSYMR33**
Telequick mounting plate	CRN, S3D	250	350	18	11	**NSYMR34**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	250	350	22	9	**NSYMR43**
Telequick mounting plate	CRN, S3D, S3X, S3DEX	350	350	24	11	**NSYMR44**
Telequick mounting plate	CRN, S3D, S3X	350	350	24	19	**NSYMR46**
Telequick mounting plate	S3D	450	250	29	9	**NSYMR53**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX	450	350	31	11	**NSYMR54**
Telequick mounting plate	CRN, S3D	450	450	31	14	**NSYMR55**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	550	350	38	11	**NSYMR64**
Telequick mounting plate	CRN, S3D	550	450	38	14	**NSYMR65**
Telequick mounting plate	CRN, S3D, S3X, S3HD, S3HF	550	550	38	17	**NSYMR66**
Telequick mounting plate	CRN, S3D	550	750	36	24	**NSYMR68**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX	650	450	44	14	**NSYMR75**
Telequick mounting plate	PLM	650	550	44	17	**NSYMR76**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	750	550	51	17	**NSYMR86**
Telequick mounting plate	CRN, S3D, S3X, S3HD	750	750	51	24	**NSYMR88**
Telequick mounting plate	CRN, S3D, S3X	950	1150	49	31	**NSYMR810**
Telequick mounting plate	CRN, S3D, S3HD	950	550	64	17	**NSYMR106**
Telequick mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	950	750	64	24	**NSYMR108**
Telequick mounting plate	CRN, S3D, S3X	950	950	62	31	**NSYMR1010**
Telequick mounting plate	CRN, S3D	950	1150	62	37	**NSYMR1012**
Telequick mounting plate	CRN, S3D	1150	550	75	17	**NSYMR126**
Telequick mounting plate	CRN, S3D, S3X	1150	750	75	24	**NSYMR128**
Telequick mounting plate	CRN, S3D, S3X	1150	950	75	31	**NSYMR1210**
Telequick mounting plate	CRN, S3D	1350	950	88	31	**NSYMR1410**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Microperforated Mounting Plate

CRN | S3D | S3X | PLM | S3HD | S3DEX | S3HF




- They considerably reduce products installation time thanks to the holes prepared to receive the self-tapping screws. Holes with Ø 3.6 mm in steps of 12.5 mm. M4 self-tapping screws of class 6.8 minimum to be used.
- Material: Galvanized steel
- Maximum load:PLM: 150 kg/m²
- S3D, S3X, CRN: 250 kg/m²
- Supply: One mounting plate without fixing elements




Characteristics	Compatibility	Height (mm)	width (mm)	References
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	250	150	**NSYMF32**
Microperorated mounting plate	CRN, S3D, S3X, S3DEX	250	250	**NSYMF33**
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	250	350	**NSYMF43***
Microperorated mounting plate	CRN, S3D, S3X, S3DEX	350	350	**NSYMF44**
Microperorated mounting plate	S3D	450	250	**NSYMF53**
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	450	350	**NSYMF54**
Microperorated mounting plate	CRN, S3D	450	450	**NSYMF55**
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	550	350	**NSYMF64***
Microperorated mounting plate	CRN, S3D	550	450	**NSYMF65**
Microperorated mounting plate	CRN, S3D, S3X, S3HD, S3DEX, S3HF	550	550	**NSYMF66**
Microperorated mounting plate	CRN, S3D, S3X, PLM , S3HD, S3DEX	650	450	**NSYMF75**
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	750	550	**NSYMF86***
Microperorated mounting plate	CRN, S3D, S3X, S3HD	750	750	**NSYMF88**
Microperorated mounting plate	CRN, S3D, S3HD	950	550	**NSYMF106**
Microperorated mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	950	750	**NSYMF108***
Microperorated mounting plate	CRN, S3D, S3X	950	950	**NSYMF1010**
Microperorated mounting plate	CRN, S3D	1150	550	**NSYMF126**
Microperorated mounting plate	CRN, S3D, S3X	1150	750	**NSYMF128**
Microperorated mounting plate	CRN, S3D, S3X	1150	950	**NSYMF1210***

Joinable Telequick Mounting Plate

CRN | S3D | S3X | PLM



- 20/10e mm Telequick mounting plates.
- These mounting plates are suitable for mounting vertically multiple plates.
- 11 x 26 mm slots.
- Switchgear fixing by clip-on nuts.
- Material: Zinc-coated steel
- Supply: One mounting plate and fixing elements



Characteristics	Compatibility	Height (mm)	width (mm)	References
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	349	258	**AM1PA3020**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	360	734	**AM1PA3070**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	660	434	**AM1PA6040**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	660	534	**AM1PA6050**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	660	634	**AM1PA6060**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	960	634	**AM1PA9060**
Joinable telequick Mounting plate	CRN, S3D, S3X, PLM	960	734	**AM1PA9070**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Mounting Plates


Bakelite Mounting Plate

CRN S3D S3X PLM S3HD S3DEX S3HF



P = Height
S = Width


- They are coupled directly to the rear of the actual enclosure or to the sliding plate supports.
- Double-door enclosures offer the option of installing two plates.
- Material: Bakelite
- Color: RAL 9005 black
- Maximum load:100 kg/m²
- Supply: One mounting plate without fixing elements



Characteristics	Compatibility	Height (mm)	width (mm)	Thick.	References
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	265	150	4	**NSYMB32**
Bakelite mounting plate	CRN, S3D, S3X, PLM	265	200	4	**NSYMB3025**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	325	250	4	**NSYMB43**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	465	350	4	**NSYMB54**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	565	350	4	**NSYMB64**
Bakelite mounting plate	CRN, S3D	565	450	4	**NSYMB65**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX	665	450	4	**NSYMB75**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	765	550	4	**NSYMB86**
Bakelite mounting plate	CRN, S3D, S3X, PLM, S3HD, S3DEX, S3HF	965	750	4	**NSYMB108**
Bakelite mounting plate	CRN, S3D, S3X	1150	950	4	**NSYMB1210**

PLA

- Direct installation on M8 inserts at the rear of the enclosure or on step slides for depth adjustment (see page 521). The enclosures with height of ≥ 1000 mm have intermediate impressions for installing mounting plates of a lesser height (M8 inserts, ref. **NSYTEX8**, to be ordered separately).
- In the two door enclosures, it is possible to install one complete mounting plate or two individual mounting plates.
- Material: Bakelite
- Thickness: 4 mm
- Maximum load: 100 kg/m²
- Supply: One mounting plate




Characteristics	Compatibility	Height (A) (mm)	Width (B) (mm)	References
Bakelite mounting plate	PLA	500	500	**NSYPMB55**
Bakelite mounting plate	PLA	500	750	**NSYPMB75**
Bakelite mounting plate	PLA	500	1000	**NSYPMB510**
Bakelite mounting plate	PLA	500	500 + 750	**NSYPMB55** + **NSYPMB75**
Bakelite mounting plate	PLA	750	500	**NSYPMB75**
Bakelite mounting plate	PLA	750	750	**NSYPMB77**
Bakelite mounting plate	PLA	750	1000	**NSYPMB710**
Bakelite mounting plate	PLA	750	1250	**NSYPMB712**
Bakelite mounting plate	PLA	1000	500	**NSYPMB105**
Bakelite mounting plate	PLA	1000	750	**NSYPMB107**
Bakelite mounting plate	PLA	1000	1000	**NSYPMB1010**
Bakelite mounting plate	PLA	1000	1250	**NSYPMB1012**
Bakelite mounting plate	PLA	1250	500	**NSYPMB125**
Bakelite mounting plate	PLA	1250	750	**NSYPMB127**
Bakelite mounting plate	PLA	1250	1000	**NSYPMB1210**
Bakelite mounting plate	PLA	1250	1250	**NSYPMB1212**
Bakelite mounting plate	PLA	1500	500	**NSYPMB155**
Bakelite mounting plate	PLA	1500	750	**NSYPMB157**
Bakelite mounting plate	PLA	1500	1000	**NSYPMB1510**
Bakelite mounting plate	PLA	1500	1250	**NSYPMB1512**
Bakelite mounting plate	PLA	2 x 1000	750	2 x **NSYPMB107**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Polyester Mounting Plate

CRN S3D S3X PLM S3HD S3DEX S3HF



P = Height
S = Width

- They are coupled directly to the rear of the actual enclosure or to the sliding plate supports.
- Double-door enclosures offer the option of installing two plates.
- Material: Polyester reinforced with fiberglass
- Color: RAL 7035 gray
- Maximum load:150 kg/m²
- Supply: One mounting plate without fixing elements

NSYMPP32

Characteristics	Compatibility	Height (mm)	width (mm)	Thick.	References
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX	265	150	4	**NSYMPP32**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	325	250	4	**NSYMPP43**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX	465	350	4	**NSYMPP54**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	565	350	4	**NSYMPP64**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX	665	450	4	**NSYMPP75**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	765	550	5	**NSYMPP86**
Polyester mounting plate	CRN, S3D, PLM, S3X, S3HD, S3DEX, S3HF	965	750	5	**NSYMPP108**

PLA

- Direct installation on M8 inserts at the rear of the enclosure or on step slides for depth adjustment (see page 521).
  The enclosures with height of ≥ 1000 mm have intermediate impressions for installing mounting plates of a lesser height (M8 inserts, ref. NSYTEX8, to be ordered separately).
- In the two door enclosures, it is possible to install one complete mounting plate or two individual mounting plates.
- Material: Polyester
- Thickness:
  - 4 mm up to 700 mm height
  - 5 mm from 800 mm height
- Maximum load: 100 kg/m²
- Supply: One mounting plate

NSYMPP32

Characteristics	Compatibility	Height (A) (mm)	Width (B) (mm)	References
Polyester mounting plate	PLA	500	500	**NSYPMA55**
Polyester mounting plate	PLA	500	750	**NSYPMA75**
Polyester mounting plate	PLA	500	500 + 750	**NSYPMA55** + **NSYPMA75**
Polyester mounting plate	PLA	750	500	**NSYPMA75**
Polyester mounting plate	PLA	750	750	**NSYPMA77**
Polyester mounting plate	PLA	1000	500	**NSYPMA105**
Polyester mounting plate	PLA	1000	750	**NSYPMA107**
Polyester mounting plate	PLA	1250	750	**NSYPMA127**
Polyester mounting plate	PLA	2 x 1000	750	2 x **NSYPMA107**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Mounting Plates

Plain Mounting Plate

SM | SFN | SMX | SFX | SFN HD | SFN 6G



- Depth adjustable with a pitch of 25 mm, provided with plastic shoe for easier sliding.
- Once the plate is fixed, in advanced position, the sliding shoe can be easily removed to increase the available plate surface.
- In sets made up of two or more enclosures with mounting plates, it is possible to obtain a continuous plate surface using intermediate mounting plates (see page 518).
- Load: 300 kg/ m²
- Maximum load: 600 kg in the back of the enclosure and 500 kg in the intermediate position
- Material: Galvanized steel

Fixing options:
- At the sides of the enclosure with the orthogonal brackets (see page 520)
- Back-to-back, with the brackets for fixing the mounting plates in back-to-back position (see page 520)
- For 400 mm wide plates: with sliding rails and brackets, orthogonal brackets when mounted at back position, or with standard fixing brackets when mounted at middle position.

Note:
Accesories must be purchased separately (depending on the fixation at the back or in the mid position).

NSYSMPS rails always needed
NSYSMNPB brackets for intermediate position
NSYSMPSB brackets for back position

Supply:
One mounting plate and sliding shoes.


NSYMP184


Characteristics	Compatibility	Width of the enclosure (mm)	Height of the enclosure (mm)	Width (mm)	Height (mm)	References
Plain mounting plate	SFN	400	1800	296	1697	**NSYMP184**
Plain mounting plate	SFN	400	2000	296	2097	**NSYMP204**
Plain mounting plate	SFN, SFX	400	2200	296	1897	**NSYMP224**
Plain mounting plate	SFN	600	1200	496	1097	**NSYMP126**
Plain mounting plate	SM, SFN	600	1400	496	1297	**NSYMP146**
Plain mounting plate	SM, SFN	600	1600	496	1497	**NSYMP166**
Plain mounting plate	SM, SFN, SMX, SFX, SFN HD	600	1800	496	1697	**NSYMP186**
Plain mounting plate	SM, SFN, SFX, SFN HD	600	2000	496	1897	**NSYMP206**
Plain mounting plate	SFN, SFX	600	2200	496	2097	**NSYMP226**
Plain mounting plate	SM, SFN	800	1200	696	1097	**NSYMP128**
Plain mounting plate	SM, SFN	800	1400	696	1297	**NSYMP148**
Plain mounting plate	SM, SFN, SMX	800	1600	696	1497	**NSYMP168**
Plain mounting plate	SM, SFN, SMX, SFX, SFN HD	800	1800	696	1697	**NSYMP188**
Plain mounting plate	SM, SFN, SMX, SFX, SFN HD, SFN 6G	800	2000	696	1897	**NSYMP208**
Plain mounting plate	SFN, SFX	800	2200	696	2097	**NSYMP228**
Plain mounting plate	SM	1000	1200	896	1097	**NSYMP1210**
Plain mounting plate	SM, SMX	1000	1400	896	1297	**NSYMP1410**
Plain mounting plate	SM	1000	1600	896	1497	**NSYMP1610**
Plain mounting plate	SM, SFN	1000	1800	896	1697	**NSYMP1810**
Plain mounting plate	SM, SFN, SMX, SFX	1000	2000	896	1897	**NSYMP2010**
Plain mounting plate	SFN, SFX	1000	2200	896	2097	**NSYMP2210**
Plain mounting plate	SM	1200	1200	1096	1097	**NSYMP1212**
Plain mounting plate	SM	1200	1400	1096	1297	**NSYMP1412**
Plain mounting plate	SM	1200	1600	1096	1497	**NSYMP1612**
Plain mounting plate	SM, SFN, SMX, SFX	1200	1800	1096	1697	**NSYMP1812**
Plain mounting plate	SM, SFN, SMX, SFX	1200	2000	1096	1897	**NSYMP2012**
Plain mounting plate	SFN	1200	2200	1096	2097	**NSYMP2212**
Plain mounting plate	SM, SFN, SMX	1600	1800	1496	1697	**NSYMP1816**
Plain mounting plate	SM, SFN, SMX	1600	2000	1496	1897	**NSYMP2016**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Plain Mounting Plate


PLA PHD

- Direct installation on M8 inserts at the rear of the enclosure or on step slides for depth adjustment (see page 521). The enclosures with height of ≥ 1000 mm have intermediate impressions for installing mounting plates of a lesser height (M8 inserts, ref. **NSYTEX8**, to be ordered separately).
- In the two door enclosures, it is possible to install one complete mounting plate or two individual mounting plates.
- Material: Galvanized sheet steel
- Thickness: 2.5 mm
- Maximum load: 150 kg/m²
- Supply: One mounting plate





Characteristics	Compatibility	Height (A) (mm)	Width (B) (mm)	Surface (dm²)	References
Plain mounting plate	PLA, PHD	500	500	14	**NSYPMM55**
Plain mounting plate	PLA, PHD	500	750	24	**NSYPMM75**
Plain mounting plate	PLA, PHD	500	1000	32	**NSYPMM510**
Plain mounting plate	PLA, PHD	500	1250	38	**NSYPMM55** + **NSYPMM75**
Plain mounting plate	PLA, PHD	750	500	24	**NSYPMM75**
Plain mounting plate	PLA, PHD	750	750	40	**NSYPMM77**
Plain mounting plate	PLA, PHD	750	1000	54	**NSYPMM710**
Plain mounting plate	PLA, PHD	750	1250	70	**NSYPMM712**
Plain mounting plate	PLA, PHD	1000	500	33	**NSYPMM105**
Plain mounting plate	PLA, PHD	1000	750	55	**NSYPMM107**
Plain mounting plate	PLA, PHD	1000	1000	74	**NSYPMM1010**
Plain mounting plate	PLA, PHD	1000	1250	96	**NSYPMM1012**
Plain mounting plate	PLA, PHD	1250	500	42	**NSYPMM125**
Plain mounting plate	PLA, PHD	1250	750	70	**NSYPMM127**
Plain mounting plate	PLA, PHD	1250	1000	96	**NSYPMM1210**
Plain mounting plate	PLA, PHD	1250	1250	124	**NSYPMM1212**
Plain mounting plate	PLA, PHD	1500	500	51	**NSYPMM155**
Plain mounting plate	PLA, PHD	1500	750	85	**NSYPMM157**
Plain mounting plate	PLA, PHD	1500	1000	118	**NSYPMM1510**
Plain mounting plate	PLA, PHD	1500	1250	152	**NSYPMM1512**
Plain mounting plate	PLA, PHD	2000	750	115	**NSYPMM207**



PLA PHD

- Plate for fixing non-modular devices.
- Depth-adjustable fixing on the supports from 40 to 85 mm.
- Material: Galvanized steel 2 mm thick

Supply:
Order by multiples of 2 (2, 4, 6...)



NSYPMP500DLP

Characteristics	Compatibility	For enclosure - Width (mm)	Height - A (mm)	Thickness (mm)	References
Plain mounting plate	PLA, PHD	500	149	2	**NSYPMP500DLP**
Plain mounting plate	PLA, PHD	500	298	2	**NSYPMP5002DLP**
Plain mounting plate	PLA, PHD	750	149	2	**NSYPMP750DLP**
Plain mounting plate	PLA, PHD	750	298	2	**NSYPMP7502DLP**

Extra Large Mounting Plate

SFN

- Extended mounting plates for PanelSeT SFN, to use the maximum space available.
- Mounting plates can be coupled for a continuous mounting surface.
- Easy installation by side-entry rails, see page 521
- Material: Galvanized steel
- Supply: One mounting plate



Characteristics	Compatibility	Height (mm)	Width (mm)	References
Extra large mounting plate	SFN	1800	800	**NSYMP188L**
Extra large mounting plate	SFN	2000	800	**NSYMP208L**
Extra large mounting plate	SFN	2000	1000	**NSYMP2010L**
Extra large mounting plate	SFN	2000	1200	**NSYMP2012L**

Further dimensions available on demand.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories


Mounting Plates

Perforated Mounting Plate Telequick

PLA



- Grille with 11 x 26 mm drill holes, with a step of 15 x 30 mm, for direct installation, with clip nuts, of all the devices with fixing at 2, 3 or 4 points, by screws with diameters of 3, 4, 5 or 6 mm.
- Direct installation on M8 inserts at the rear of the enclosure or on step slides for depth adjustment (see page 521).
- The enclosures with height of ≥ 1000 mm have intermediate impressions for installing mounting plates of a lesser height (M8 inserts, ref. **NSYTEX8**, to be ordered separately).
- Material: Galvanized steel
- Maximum load: 150 kg/m²
- Supply: One mounting plate




Characteristics	Compatibility	Height (E) (mm)	Width (D) (mm)	Surface (dm²)	References
Telequick mounting plate	PLA	350	350	13	**NSYPMR55**
Telequick mounting plate	PLA	350	600	23	**NSYPMR57**
Telequick mounting plate	PLA	350	2 x 350	26	2 x **NSYPMR55**
Telequick mounting plate	PLA	350	350 + 600	36	**NSYPMR55** + **NSYPMR57**
Telequick mounting plate	PLA	600	350	23	**NSYPMR75**
Telequick mounting plate	PLA	600	600	38	**NSYPMR77**
Telequick mounting plate	PLA	600	2 x 350	46	2 x **NSYPMR75**
Telequick mounting plate	PLA	600	600	61	**NSYPMR75** + **NSYPMR77**
Telequick mounting plate	PLA	850	350	32	**NSYPMR105**
Telequick mounting plate	PLA	850	600	54	**NSYPMR107**
Telequick mounting plate	PLA	850	2 x 350	64	2 x **NSYPMR105**
Telequick mounting plate	PLA	850	350 + 600	86	**NSYPMR105** + **NSYPMR107**
Telequick mounting plate	PLA	1100	350	42	**NSYPMR125**
Telequick mounting plate	PLA	1100	600	70	**NSYPMR127**
Telequick mounting plate	PLA	1100	2 x 350	84	2 x **NSYPMR125**
Telequick mounting plate	PLA	1100	350 + 600	112	**NSYPMR125** + **NSYPMR127**
Telequick mounting plate	PLA	1350	350	51	**NSYPMR155**
Telequick mounting plate	PLA	1350	600	85	**NSYPMR157**
Telequick mounting plate	PLA	1350	2 x 350	102	2 x **NSYPMR155**
Telequick mounting plate	PLA	1350	350 + 600	136	**NSYPMR155** + **NSYPMR157**
Telequick mounting plate	PLA	2 x 850	2 x 600	108	2 x **NSYPMR107**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Perforated Mounting Plate Telequick

SM SFN SMX SFX

- Allows the installation of switchgear without drilling or screwing.
- Plate designed for quick-fixing of switchgear by means of clip-on nuts ref. **AF1EA3** to **AF1EA6**.
- To help ensure vertical continuity, multiple Telequick plates can be installed consecutively in a stacked arrangement.
- The top plate must be fixed in the third hole, 80 mm from the top frame.
- Load: 150 kg/m²
- Material: Zinc-coated steel




1 Cut-outs 11 x 26 with a pitch of 15 x 30.

Fixing options:
- Directly to the vertical uprights of the structure, by means of self-tapping screws (only PanelSeT SFN)
- To the technical vertical uprights, by means of sliding nuts, see page 530;
- To standard uprights by means of flat nuts, see page 523 or self-tapping screws, and to cross-rails

Comment:
Examples of combination see below.

Supply:
One perforated mounting plate and fixing elements for technical uprights and screws for fixing to the structure or cross-rails.




NSYSTMP4560

Characteristics	Compatibility	Width	Plate height (mm)				Useful surface	References
		(mm)	D	E	F	G	(dm²)	
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	600	450	200	-	100	11.4	**NSYSTMP2260**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	600	450	425	-	325	22.8	**NSYSTMP4560**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	600	450	575	125	475	30.4	**NSYSTMP6060**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	600	450	800	250	700	11.9	**NSYSTMP8260**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	800	650	200	-	100	15.9	**NSYSTMP2280**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	800	650	425	-	325	31.8	**NSYSTMP4580**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	800	650	575	125	475	42.4	**NSYSTMP6080**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	800	650	800	250	700	58.4	**NSYSTMP8280**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1000	850	200	-	100	20.4	**NSYSTMP22100**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1000	850	425	-	325	40.8	**NSYSTMP45100**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1000	850	575	125	475	54.4	**NSYSTMP60100**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1000	850	800	250	700	74.9	**NSYSTMP82100**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1200	1050	200	-	100	24.9	**NSYSTMP22120**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1200	1050	425	-	325	49.9	**NSYSTMP45120**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1200	1050	575	125	475	66.5	**NSYSTMP60120**
Perforated mounting plate Telequick	SM, SFN, SMX, SFX	1200	1050	800	250	700	91.5	**NSYSTMP82120**


Examples of perforated mounting plate installation



- Perforated plate mounted on structure.



- Perforated plate mounted on technical vertical uprights.



- Perforated plate mounted on standard vertical uprights.



- Perforated plate mounted on cross-rails.

Examples of Mounting Plates Combination

Length of joined PanelSeT SFN enclosures (mm)	Example of PanelSeT SFN enclosure combination width (mm) (B)	Example of combining mounting plates by width (mm)	Useful length (mm)
1200	1200	600 + 800	1192
1400	600 + 800	600 + 1000	1392
1600	2 x 800	800 + 1000	1592
1800	3 x 600	800 + 1200	1792
2000	2 x 1000	1000 + 1200	1992
2200	600 + 2 x 800	1200 + 1200	2192
2400	3 x 800	1600 + 1000	2392
2400	3 x 800	3 x 600 + 1000	2384
2600	2 x 1000 + 600	1600 + 1200	2592
2600	2 x 1000 + 600	3 x 600 + 1200	2584
2800	2 x 1000 + 800	4 x 800	2784
3000	3 x 1000	3 x 800 + 1000	2984
3200	2 x 1000 + 1200	3 x 800 + 1200	3184
3400	3 x 800 + 1000	800 + 3 x 1000	3384
3600	3 x 1200	4 x 1000	3584
3800	800 + 3 x 1000	600 + 3 x 1200	3784
4000	4 x 1000	800 + 3 x 1200	3984

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Mounting Plates


Partial Mounting Plate

SM | SFN | SMX | SFX | PLA

- Partial mounting plate, provided with reinforcement flange on its four sides.
- Load: 250 kg/m²
- Material: Galvanized steel

Fixing options:
PanelSeT SFN and SFX:
- Fixing to the vertical uprights of the structure
- Fixing to the technical or standard vertical uprights, see page 530
- For installations in advanced position, fixing to cross-rails, see page 525

PanelSeT SM:
- Fixing by means of adaptation profiles and 40 mm universal cross-rails (one row) in vertical position, or also on horizontal universal cross-rails
- It can be mounted horizontally, as a tray, by means of depthwise cross-rails, see page 525



Supply:
Partial mounting plate and fixing elements



NSYSPMP2560

Characteristics	Compatibility	Width (mm) B	Plate height (mm) H	Plate length (mm) B-100	References
Partial mounting plate	SM, SFN, SMX, SFX, PLA	600	247	500	**NSYSPMP2560**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	600	397	500	**NSYSPMP4060**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	600	597	500	**NSYSPMP6060**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	750	247	500	**NSYSPMP2575**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	800	247	700	**NSYSPMP2580**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	800	397	700	**NSYSPMP4080**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	800	597	700	**NSYSPMP6080**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	1000	247	900	**NSYSPMP25100**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	1000	397	900	**NSYSPMP40100**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	1200	247	1100	**NSYSPMP25120**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	1200	397	1100	**NSYSPMP40120**
Partial mounting plate	SM, SFN, SMX, SFX, PLA	1200	597	1100	**NSYSPMP60120**

Intermediate Mounting Plate


SM | SFN | SMX | SFX

- Obtains a continuous surface of the mounting plate at enclosure suites.
- Adjustable depth with a pitch of 25 mm. When the mounting plates are located in the back of the enclosure, the vertical profiles of the structure are flush with the plates, acting as an intermediate mounting plate. In this case the intermediate plate cannot be installed.
- Material: Galvanized steel





Supply:
One intermediate plate and fixing elements


NSYSIMP12

Characteristics	Compatibility	Height (mm)	References
Intermediate mounting plate	SM, SFN	1200	**NSYSIMP12**
Intermediate mounting plate	SM, SFN, SFX	1400	**NSYSIMP14**
Intermediate mounting plate	SM, SFN, SFX	1600	**NSYSIMP16**
Intermediate mounting plate	SM, SFN, SMX, SFX	1800	**NSYSIMP18**
Intermediate mounting plate	SM, SFN, SMX, SFX	2000	**NSYSIMP20**
Intermediate mounting plate	SFN	2200	**NSYSIMP22**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Accessories for Mounting Plates


Intermediate Fixing of the Mounting Plate, Located in the Back of the Enclosure

SM SFN SFX



- Support for additional fixing of the mounting plate, at any height of the plate when the plate is mounted in the back of the enclosure.
- The supports minimize the vibration of the plate during the transport and operation of the panel.
- Material: Zinc-coated steel
- **Fixing:** The supports are fixed to the structure when the plate is already located in the back of the enclosure PanelSeT SM: Fixing to 40 mm universal cross-rails (one row), installed vertically in the back of the enclosure, see page 525

Supply:
Ten units and fixing elements. Reference by unit. Order by multiples of 10 (10, 20, 30…)



NSYSMPFB

Characteristics	Compatibility	References
Intermediate fixing of the mounting plate, located in the back of the enclosure	SM, SFN, SFX	**NSYSMPFB**


Intermediate Fixing of the Mounting Plate, in Advanced Position

SM SFN SFX



- Support for additional fixing of the mounting plate, at any height of the plate when the plate is mounted in advanced position.
- The supports minimize the vibration of the plate during the transport and operation of the panel.
- Material: Zinc-coated steel
- **Fixing:** The supports are mounted on light cross-rails or on 40 mm (one row) universal or quick-fixing cross-rails (not supplied), see page 525

Supply:
Ten units and fixing elements. Reference by unit. Order by multiples of 10 (10, 20, 30…)




NSYSMPFA

Characteristics	Compatibility	References
Intermediate fixing of the mounting plate, in advanced position	SM, SFN, SFX	**NSYSMPFA**

Reinforcement for Mounting Plate

SM SFN SMX SFX SFN HD



- Reinforcement kit for transversal mounting plate.
- Provides extra rigidity to the mounting plates and absorbs vibrations.
- Not compatible with extra-large mounting plates
- Can be used as a support for fixing very heavy elements.
- Material: Zinc-coated steel
- Thickness: 15/10^{e} mm

Supply:
Two profiles, four supports for fixing to the mounting plate and fixing elements



NSYMPRK8

Characteristics	Compatibility	Width (mm)	References
Reinforcement for mounting plate	SM, SFN, SMX, SFX, SFN HD	800	**NSYMPRK8**
Reinforcement for mounting plate	SM, SFN, SMX, SFX, SFN HD	1000	**NSYMPRK10**
Reinforcement for mounting plate	SM, SFN, SMX, SFX, SFN HD	1200	**NSYMPRK12**
Reinforcement for mounting plate	SM, SFN, SMX, SFX, SFN HD	1600	**NSYMPRK16**

Elevator for Microperforated Mounting Plate

CRN S3D S3X PLM S3HD

- Mounting plate elevator to mount the microperforated mounting plate on the same level as the other Telequick system components.

Supply:
Four units



AZ1CA04

Characteristics	Compatibility	Reference
Elevator for microperforated mounting plate	CRN, S3D, S3X, PLM, S3HD	**AZ1CA04**

Mounting Plate Sliding Rails

SFN SFN HD



- Rail in which the mounting plate slides along when inserted in the enclosure.
- Once the mounting plate is installed and fixed to the brackets, the sliding rails can be removed to maximize the cable passage surface, and can be installed depthwise in other positions.
- Material: Galvanized steel

Supply:
Two rails and fixing elements



NSYSMPS4

Characteristics	Compatibility	Depth (mm)	References
Mounting plate sliding rails	SFN, SFN HD	400	**NSYSMPS4**
Mounting plate sliding rails	SFN, SFN HD	500	**NSYSMPS5**
Mounting plate sliding rails	SFN, SFN HD	600	**NSYSMPS6**
Mounting plate sliding rails	SFN, SFN HD	800	**NSYSMPS8**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Accessories for Mounting Plates

Mounting Plate Fixing Brackets

SM | SFN | SMX | SFX

PB503880



NSYSFNPB

- For direct mounting on the structure of the enclosure.
- Adjustable depth with a pitch of 25 mm.
- Material: Zinc-coated steel
- Maximum load: Four brackets: 600 kg

Supply:
Four brackets and fixing elements

Characteristics	Compatibility	References
Mounting plate fixing brackets	SFN	**NSYSFNPB**
Mounting plate fixing brackets	SM, SMX, SFX	**NSYSMNPB**

Orthogonal Brackets


SFN | SFX | SFN HD



NSYSMPSB

Designed for the installation of mounting plates on the sides of the enclosure.
- When installing one plate in the back of the enclosure and one plate at the side, they must both be installed using orthogonal brackets.
- PanelSeT SFX: Mounting the lateral mounting plate requires the removal of the one on the back and its fixing brackets.
- Material: Zinc-coated steel
- Maximum load: Four brackets: 600 kg

PB500791_31_nb




Supply:
Four brackets and fixing elements

Characteristics	Compatibility	References
Orthogonal brackets	SFN, SFX, SFN HD	**NSYSMPSB**


Brackets for Fixing Mounting Plates in Back-to-Back Position

SFN | SFN HD

DB300571EN_53_nb



PB500796_37_nb





NSYSBTB

- Doubling the mounting surface.
- Adjustable with a pitch of 25 mm.
- Material: Zinc-coated steel


Supply:
Four brackets for fixing back-to-back and fixing elements

Characteristics	Compatibility	References
Brackets for fixing mounting plates in back-to-back position	SFN, SFN HD	**NSYSBTB**

Brackets for Fixing Intermediate Mounting Plates in Back-to-Back Position


SM | SFN | SMX | SFX | SFN HD

DB300572EN_53_nb



PB500798_30_nb





NSYSIBTB

- Doubling the mounting surface.
- Adjustable with a pitch of 25 mm.
- Material: Zinc-coated steel


Supply:
2 brackets for fixing intermediate plates back-to-back and fixing elements

Characteristics	Compatibility	References
Brackets for fixing intermediate mounting plates in back-to-back position	SM, SFN, SMX, SFX, SFN HD	**NSYSIBTB**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Side Entry Rails for the Mounting Plate

SFN SFX SFN HD



- Side entry device for the mounting plates when coupling PanelSeT SFN enclosures or SFX.
- The mounting plates can be coupled with one another, and are fixed to the side entry guide by pressure.
- Material: Zinc-coated steel


Supply:
Two rails (top and bottom) and fixing elements



NSYSMPSE6

Characteristics	Compatibility	Width (mm)	References
Side entry rails for the mounting plate	SFN, SFX, SFN HD	600	**NSYSMPSE6**
Side entry rails for the mounting plate	SFN, SFX, SFN HD	800	**NSYSMPSE8**
Side entry rails for the mounting plate	SFN, SFX, SFN HD	1000	**NSYSMPSE10**
Side entry rails for the mounting plate	SFN, SFX, SFN HD	1200	**NSYSMPSE12**

Top/Bottom Adjustment Rails

SM





- Allows the installation of two mounting plates or vertical uprights in enclosures with a width of 1200 mm and 1600 mm, as if in two independent enclosures.
- A set of mounting plate fixing brackets ref. **NSYSMNPB** is required.
- Optional installation of an intermediate mounting plate.
- Material: Galvanized steel

Supply:
Two top rails and two bottom rails



NSYSTBR3


Characteristics	Compatibility	Depth (mm)	References
Top/bottom adjustment rails	SM	300	**NSYSTBR3**
Top/bottom adjustment rails	SM	400	**NSYSTBR4**
Top/bottom adjustment rails	SM	500	**NSYSTBR5**
Top/bottom adjustment rails	SM	600	**NSYSTBR6**

Kit for Adapting Two-Door Enclosures

SFN

- Allows the installation of two mounting plates as if in two independent enclosures.
- A set of brackets for fixing mounting plates ref. **NSYSMNPB** is required.
- Option of installing an intermediate mounting plate.
- Valid for enclosures with widths of 1200 and 1600 mm.
- If installing a cable gland plate for a width of 1200 mm, it is necessary to install two with a width of 600 mm, and for widths of 1600 mm, two with a width of 800 mm.




NSYSMP2D4


Characteristics	Compatibility	Depth (mm)	References
Kit for adapting two-door enclosures	SFN	400	**NSYSMP2D4**
Kit for adapting two-door enclosures	SFN	500	**NSYSMP2D5**
Kit for adapting two-door enclosures	SFN	600	**NSYSMP2D6**
Kit for adapting two-door enclosures	SFN	800	**NSYSMP2D8**

Step Slides for Mounting Plate

CRN S3D S3X S3HD S3HF


NSYSDCR200

- Set of four supports intended for installation in enclosures with depths of 200 and 250 mm.
- The rail allows the depth of the plate and other accessories to be adjusted in steps of 12.5 mm.



Supply:
Four step slides

Characteristics	Compatibility	Enclosure depth (mm)	Reference
Step slides for mounting plate	CRN, S3D, S3X, S3HD, S3HF	200	**NSYSDCR200**
Step slides for mounting plate	CRN, S3D, S3X, S3HD, S3HF	250	**NSYSDCR250**
Step slides for mounting plate	CRN, S3D, S3X, S3HD, S3HF	300	**NSYSDCR300**
Step slides for mounting plate	CRN, S3D, S3HD	400	**NSYSDCR400**

Step slides for 2 mounting plates in one enclosure

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Accessories for Mounting Plates

Step Slides

PLM

Kit allowing depth adjustment with a pitch of 12.5 mm, and the fixings required for the installation.
Incompatible with the modular distribution chassis.




Supply:
4 step slides with brackets


NSYDPLM200


Characteristics (Material: Galvanized steel)	Compatibility	For wall-mounted enclosure depth (mm)	Depth adjustment A (mm)	Depth adjustment B (mm)	References
Step slides	PLM	200	156	94	**NSYDPLM200**
Step slides	PLM	250	200	100	**NSYDPLM250**
Step slides	PLM	300	250	100	**NSYDPLM300**
Step slides	PLM	350	306	106	**NSYDPLM350**

PLA **PHD**

- Set of four step slides with brackets allowing continuous depth adjustment of the mounting plate, with a pitch of 25 mm.
- Designed for direct installation in the enclosures with sealed bottom part (versions PLA or PLAT).
- In the enclosures with open bottom part (versions PLAZ or PLAZT), installation is made possible by adding the relevant adapter plates.
- Incompatibility with: Internal door, modular distribution chassis, 19" chassis, cable entry plate and door retainer, ref. **NSYRETPLAU**.
- Material: Bracket with steel M8 stud on aluminum rail.
- Fixing: Fixing on the top and bottom parts of the enclosure by means of M8 inserts and screws (supplied).



Installation of step slide ref. **NSYDPLA●●●**, 1 57 mm with one transparent door.



Installation of step slide ref. **NSYDPLA●●●**, with adapter plate ref. **NSYPTZ●●●**, 1 57 mm with one transparent door.






NSYDPLA3

Characteristics	Compatibility	Depth (mm)	Number of doors	References
Step slides	PLA, PHD	320	1	**NSYDPLA3**
Step slides	PLA, PHD	320	2	2 x **NSYDPLA3**
Step slides	PLA, PHD	420	1	**NSYDPLA4**
Step slides	PLA, PHD	420	2	2 x **NSYDPLA4**
Step slides	PLA, PHD	620	1	**NSYDPLA6**
Step slides	PLA, PHD	620	2	2 x **NSYDPLA6**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Accessories for Mounting Plates

Additional Support

PLA



NSYEDPLA

- Set of four additional brackets, to be slid into the step slides, for the installation of an additional mounting plate.


Characteristics	Compatibility	Reference
Additional support	PLA	**NSYEDPLA**

Clicked Support Plate



AX2DL01

- For screw mounted equipment.
- For mounting on 35 mm symmetric and double profile DIN rails or Telequick mounting plate.
- Material: Zinc-plate coated



AX2DL0_16

Supply:
Ten units and fixing elements. Reference by unit. Order by multiples of 10 (10, 20, 30...)

Characteristics	Compatibility	References
Clicked support plate, 44 x 65 - 9 screws	All	**AX2DL01**

Clip-On Nuts for Telequick Mounting Plate



AF1EA3

- Used to easily fix devices on the Telequick mounting plate with the option of converting the layout as much as needed.


Supply:
100 units. Reference by unit. Order by multiples of 100 (100, 200, 300...)

Characteristics	Compatibility	Reference
Clip-on nuts for Telequick mounting plate, Model M3	All	**AF1EA3**
Clip-on nuts for Telequick mounting plate, Model M4	All	**AF1EA4**
Clip-on nuts for Telequick mounting plate, Model M5	All	**AF1EA5**
Clip-on nuts for Telequick mounting plate, Model M6	All	**AF1EA6**

Bracket for Fixing Control Units (Ø 22)



DX1AP52



DX1AP5_10

Supply:
Ten units and fixing elements. Reference by unit. Order by multiples of 10 (10, 20, 30...)

- To mount any 22 mm diameter device directly on mounting plates.

Characteristics	Compatibility	References
Bracket for fixing control units (Ø 22)	All	**DX1AP52**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Cross Rails

SM | SFN | SMX | SFX | SFN PC | SFN HD | SFN HF

It is possible to create a fixing at any point of the inner volume, providing mounting planes with different widths, heights and depths. In the case of the PanelSeT SM, it may be necessary to install vertical/horizontal adaptation profiles and 40-mm universal cross-rails (one row).


PB503915



Four types of cross-rails are available to create fixing points:
- Universal cross-rails (see page 525)
- Quick-fixing cross-rails (see page 526)
- Integrated cross-rails (see page 527)
- Light cross-rails (see page 526)


Universal, quick-fixing and integrated cross-rails are available in 3 sizes:
- 40 mm (1 row)
- 65 mm (2 rows)
- 90 mm (3 rows)

PB503463_75_nb




Cross-rails for specific applications are also available:
- Cross-rails for heavy loads (see page 537) to be fixed on the bottom part of the enclosure or to be combined with a "heavy load kit" (see page 537) to be used at any height in the enclosure

PB503916




PB503465_83_nb




Combination Examples

PB500486_29_nb



PanelSeT SFN and SFX:
The cross-rails can be fixed to the structure and among each other, offering multiple options.

PB500838_26_nb




The quick-fixing cross-rails can be fixed directly to the structure, quickly and easily.
PanelSeT SFN and SFX*:
- They clip onto the structure and are fixed by M6 self-tapping screws, or optionally with M6 caged nuts.

PanelSeT SM:
- Option of clipping onto the adaptation profile or another cross-rail.
- Fixing by means of M6 self-tapping screws.
- Fixing by means of M6 caged nuts.


* In PanelSeT SFX enclosures, it cannot be mounted depthwise.

PB500835_27_nb




Universal cross-rails and integrated cross-rails can be simultaneously mounted at the same height, on all the sides of the enclosure.
To perform this type of installation in a PanelSeT SM enclosure, the vertical adaptation profile and the vertical 40 mm universal cross-rail (one row) are required, mounted in the back of the enclosure.

PB500839_30_nb



Quick-fixing cross-rails can be used to support equipments at the back of the enclosure or be fixed every 25 mm on two cross-rails (universal or integrated) in vertical position.

PB500841_24_nb




40 mm wide universal and integrated cross-rails can be used as uprights, adjustable every 25 mm in depth. They enable the fixing of diverse equipment supports and are adjustable every 25 mm in height.

PB500837_27_nb



PanelSeT SFN:
Universal cross-rails and integrated cross-rails can be mounted in vertical position.

PB500842_30_nb




The main fixing point to the quick-fixing cross-rails is the 5.2 mm drill hole for M6 self-tapping screw, although they can also receive M6 and M8 caged nuts.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Universal Cross-Rails

SM | SFN | SMX | SFX | SFN PC | SFN HD | SFN HF

40 mm (1 Row) | 65 mm (2 Rows) | 90 mm (3 Rows)



- Used for the creation of structures inside the enclosure.
- Cross-rails available in three sizes:
  40 mm (one row), 65 mm (two rows) and 90 mm (three rows).
- Each row is perforated every 25 mm with a 5.2 mm diameter hole and a 11x13 mm cutout which enables fixing by means of M6 self-tapping screws, ref **NSYST30M6S**.
- Equipment is fixed by means of caged nuts or self-tapping screws.
- Material: Galvanized steel
- Thickness: 15/10^{e} mm


Fixing to the structure:
Fixing accordingly to uprights axis.
Option to mount cross-rails simultaneously on all sides, at the same height of the enclosure.

Fixing to the plinths:
They are fixed across the width and/or depth between the corners of the plinth.
The plinth cross-rail supports are required for its assembly.


Fixing to the trays:
Allow the installation of fixed trays and telescopic rails.

Comment:
(1) For vertical assembly only.
(2) Cross-rails only for fixing cables.
(3) These cross-rails have not been sized to be used in the width, depth or height of the enclosure, but to be mounted in other positions or in between cross-rails.

Supply:
Two cross-rails, four supports for cross-rails and fixing elements


NSYSUCR4030

Tray fixing


NSYSQCR4040_nb


NSYSUCR4040_nb

Plinth fixing


NSYSUCR4030

Characteristics	Compatibility	Fixing possibility	Width of the cross-rails (mm)	H / W / D (Dn) of enclosure (mm)	Maximum load by rail (kg)	References
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinths	40 (1 row)	300	70	**NSYSUCR4030**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure, plinths and tray	40 (1 row)	400	60	**NSYSUCR4040**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure, plinths and tray	40 (1 row)	500	60	**NSYSUCR4050**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	600	50	**NSYSUCR4060**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	40 (1 row)	700 (3)	50	**NSYSUCR4070**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	800	40	**NSYSUCR4080**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	40 (1 row)	900 (3)	40	**NSYSUCR4090**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1000	30	**NSYSUCR40100**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	40 (1 row)	1100 (3)	30	**NSYSUCR40110**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1200	20	**NSYSUCR40120**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1400	(1)	**NSYSUCR40140**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1600	(1)	**NSYSUCR40160**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1800	(1)	**NSYSUCR40180**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	2000	(1)	**NSYSUCR40200**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	2200	(1)	**NSYSUCR40220**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	300	110	**NSYSUCR6530**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	400	100	**NSYSUCR6540**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	500	90	**NSYSUCR6550**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	600	80	**NSYSUCR6560**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	800	70	**NSYSUCR6580**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1000	50	**NSYSUCR65100**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1200	50	**NSYSUCR65120**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1400	(1)	**NSYSUCR65140**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1600	(1)	**NSYSUCR65160**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1800	(1)	**NSYSUCR65180**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	2000	(1)	**NSYSUCR65200**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	90 (3 rows)	300	130	**NSYSUCR9030**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	90 (3 rows)	400	120	**NSYSUCR9040**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	90 (3 rows)	500	120	**NSYSUCR9050**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	600	110	**NSYSUCR9060**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and plinth	90 (3 rows)	700 (3)	110	**NSYSUCR9070**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	800	100	**NSYSUCR9080**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1000	70	**NSYSUCR90100**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1200	70	**NSYSUCR90120**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1400	(1)	**NSYSUCR90140**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1600	(1)	**NSYSUCR90160**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1800	(1)	**NSYSUCR90180**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	2000	(1)	**NSYSUCR90200**
Universal cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	2200	(1)	**NSYSUCR90220**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Cross Rails

Quick-Fixing Cross-Rails

SM | SFN | SMX | SFX | SFN PC | SFN HD | SFN HF

40 mm (1 Row) | 65 mm (2 Rows) | 90 mm (3 Rows)



- Used for the creation of structures inside the enclosure.
- Cross-rails available in three sizes:
  40 mm (one row), 65 mm (two rows) and 90 mm (three rows).
- Each row is perforated every 25 mm with a 5.2 mm diameter hole and a 11x13 mm cutout which enables fixing by means of M6 self-tapping screws, ref **NSYST30M6S**.
- Equipment are fixed by means of caged nuts or self-tapping screws.
- Material: Galvanized steel
- Thickness: 15/10e mm

Fixing to the structure:
Fixing accordingly to uprights axis.
It is not possible to mount two cross-rails on one level with an upright.


Fixing to the trays:
Allow the installation of fixed trays and telescopic rails.

Comment:
(1) For vertical assembly only.
(2) Cross-rails only for fixing cables.
(3) These cross-rails have not been sized to be used in the width, depth or height of the enclosure, but to be mounted in other positions or in between cross-rails.

Supply:
Two cross-rails and fixing elements


NSYSQCR4040

Tray fixing



NSYSQCR4040_nb



NSYSUCR4040_nb

Characteristics	Compatibility	Fixing possibility	Width of the cross-rails (mm)	H / W / D (Dn) of enclosure (mm)	Maximum load by rail (kg)	References
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	400	60	**NSYSQCR4040**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	500	60	**NSYSQCR4050**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	600	50	**NSYSQCR4060**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure and tray	40 (1 row)	800	40	**NSYSQCR4080**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1000	30	**NSYSQCR40100**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	40 (1 row)	1200	20	**NSYSQCR40120**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	400	100	**NSYSQCR6540**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	500	90	**NSYSQCR6550**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	600	80	**NSYSQCR6560**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	800	70	**NSYSQCR6580**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1000	50	**NSYSQCR65100**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	65 (2 rows)	1200	50	**NSYSQCR65120**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	400	120	**NSYSQCR9040**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	500	120	**NSYSQCR9050**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	600	110	**NSYSQCR9060**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	800	100	**NSYSQCR9080**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1000	70	**NSYSQCR90100**
Quick-fixing cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	90 (3 rows)	1200	70	**NSYSQCR90120**
Set of 2 quick cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	120 (4 rows)	400	120	**NSYSQCR12040**
Set of 2 quick cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	120 (4 rows)	500	120	**NSYSQCR12050**
Set of 2 quick cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	120 (4 rows)	600	110	**NSYSQCR12060**
Set of 2 quick cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	Structure	120 (4 rows)	800	100	**NSYSQCR12080**

Light Cross-Rails

SM | SFN | SMX | SFX | SFN PC | SFN HD | SFN HF




PB500854_35_nb

- **PanelSeT SFN and SFX:** Direct fixing to the structure or between cross-rails.
- **PanelSeT SM:** Fixing by means of adaptation profiles and 40 mm universal cross-rails (one row), or between cross-rails in any other position.
- Adjustable with a pitch of 25 mm.
- The light cross-rails are equipped with a row of drill holes with a diameter of 5.2 mm and a pitch of 25 mm, which allows fixing with an M6 self-tapping screw, ref. **NSYST30M6S**.
- Material: Galvanized steel

Supply:
Two light cross-rails and fixing elements



Characteristics	Compatibility	Width/Depth (mm)	References
Light cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	400	**NSYSLCR40**
Light cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	500	**NSYSLCR50**
Light cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	600	**NSYSLCR60**
Light cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	800	**NSYSLCR80**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Cross Rails


Integrated Cross-Rails

SM | SFN | SMX | SFX | SFN PC | SFN HD | SFN HF

- Used for the creation of structures inside the enclosure.
- Cross-rails available in three sizes:
  40 mm (one row), 65 mm (two rows) and 90 mm (three rows).
- Each row is perforated every 25 mm with a 5.2 mm diameter hole and a 11x13 mm cutout which enables fixing by means of M6 self-tapping screws, ref **NSYST30M6S**.
- Equipment are fixed by means of caged nuts or self-tapping screws
- Material: Galvanized steel
- Thickness: 15/10e mm



30 mm space saving thanks to new fixation mode



Quick mounting, at same level, on all enclosure perimeter

Fixing to the structure:
Fixing is shifted by 30 mm relatively to uprights axis.
Option to mount cross-rails simultaneously on all sides, at the same height of the enclosure.


Supply:
Two cross-rails and fixing elements


NSYSICR4040

Characteristics	Compatibility	Width of the cross-rails (mm)	H / W / D (Dn) of enclosure (mm)	Maximum load by rail (kg)	References
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	40 (1 row)	400	60	**NSYSICR4040**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	40 (1 row)	500	60	**NSYSICR4050**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	40 (1 row)	600	50	**NSYSICR4060**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	40 (1 row)	800	40	**NSYSICR4080**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	65 (2 rows)	600	80	**NSYSICR6560**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	65 (2 rows)	800	70	**NSYSICR6580**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	65 (2 rows)	1000	50	**NSYSICR65100**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	90 (3 rows)	400	120	**NSYSICR9040**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	90 (3 rows)	600	110	**NSYSICR9060**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	90 (3 rows)	800	100	**NSYSICR9080**
Integrated cross-rails	SM, SFN, SMX, SFX, SFN PC, SFN HD, SFN HF	90 (3 rows)	1000	70	**NSYSICR90100**


Door Cross-Rails

SM | SFN | SMX | SFX



- Direct mounting cross-rails on the profiles of the reinforcement frame of the door.
- Adjustable height with a pitch of 25 mm.
- Material: Galvanized steel
- Thickness: 20/10e mm

Supply:
2 cross-rails and bag of fixings


NSYSDCR4

Characteristics	Compatibility	Width (B)	References
Door cross-rails	SM, SFN, SMX, SFX	400	**NSYSDCR4**
Door cross-rails	SM, SFN, SMX, SFX	500	**NSYSDCR5**
Door cross-rails	SM, SFN, SMX, SFX	600	**NSYSDCR6**
Door cross-rails	SM, SFN, SMX, SFX	800	**NSYSDCR8**
Door cross-rails	SM, SFN, SMX, SFX	1000	**NSYSDCR10**

Adapter Plates

PLA | PHD

- The enclosures with open bottom part (versions PLAZ and PLAZT) require a set of adapter plates for mounting: An internal door, step slides, modular chassis and 19" chassis.
- **NSYPTZ●●●** for one door enclosures
- **NSYPTX●●●** 2P for two door enclosures
- Material: Galvanized steel
- Fixing: Fixing on the bottom part of the enclosure by means of M8 inserts and screws (supplied)




NSYPTZ3

Characteristics	Compatibility	Depth (mm)	Number of doors	References
Adapter plates	PLA, PHD	320	1	**NSYPTZ3**
Adapter plates	PLA, PHD	320	2	**NSYPTZ32P**
Adapter plates	PLA, PHD	420	1	**NSYPTZ4**
Adapter plates	PLA, PHD	420	2	**NSYPTZ42P**
Adapter plates	PLA, PHD	620	1	**NSYPTZ6**
Adapter plates	PLA, PHD	620	2	**NSYPTZ62P**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Rails

Aluminum Vertical Rails

CRN S3D S3X PLM PLA


NSYMDVR12



- Fixing in the enclosure with M8 nuts, ref. **NSYAMCSF** (set of 4 adapters to be ordered separately).

Characteristics	Compatibility	Height (mm)	Supply (units)	References
Aluminum vertical rail	CRN, S3D, S3X, PLM, PLA	1200	2	**NSYMDVR12**
Aluminum vertical rail	CRN, S3D, S3X, PLM, PLA	3000	10	**NSYMDVR3M**

Sliding Nuts

CRN S3D S3X PLM PLA

Supply:
100 Sliding nuts

- Sliding nuts to be used on aluminum vertical rails.


NSYNM5


Characteristics	Compatibility	Type	References
Sliding Nut	CRN, S3D, S3X, PLM, PLA	M4	**NSYNM4**
Sliding Nut	CRN, S3D, S3X, PLM, PLA	M5	**NSYNM5**
Sliding Nut	CRN, S3D, S3X, PLM, PLA	M6	**NSYNM6**


Mounting Rail

CRN S3D



- Accessory designed to optimize the available space in the enclosure.
- It is intended for the installation of switchgear complementing the chassis.
- Mounting possible after installing the mounting plate.
- It is mounted horizontally, with a single screw, on the side panels.
- Door switch mounting option.
- It is possible to vertically fasten **NSYSLCR●●** light cross-rails (description on page 526) and **NSYSQCR●●** quick-fixing cross-rails (description on page 526).
- Material: Galvanized steel
- Maximum load: Static load: 6 kg (sides) and 1,5 kg (top); Dynamic load (transport horizontally): 2 kg according to ASTM D-4169-16
- Installation: In order to ensure the electrical continuity in all cases we recommend using an earthing cable **NSYEL●●●D6** or **NSYEL●●●D8**, see page 540




Supply:
Set of 2 cross-rails


NSYSUCR200WM

Characteristics	Compatibility	Enclosure depth (mm)	References
Mounting rail for wall-mounted enclosure	CRN, S3D	200	**NSYSUCR200WM**
Mounting rail for wall-mounted enclosure	CRN, S3D	250	**NSYSUCR250WM**
Mounting rail for wall-mounted enclosure	CRN, S3D	300	**NSYSUCR300WM**
Mounting rail for wall-mounted enclosure	CRN, S3D	400	**NSYSUCR400WM**

Symmetrical DIN Rails

SBM SBX



- Material: Galvanized steel
- Installation: Mounting by means of 2 x Ø 5 mm self-tapping screws, Pozidriv head, ref. **NSYAMFSB**
- All boxes are delivered with 5 x Ø 5 mm self-tapping screws.

Supply:
10 rails, supplied without screws



NSYAMRD15357SB

Characteristics	Compatibility	Height (mm)	Width (mm)	DIN rail lenght A (mm)	References
Symmetrical DIN rail	SBM, SBX	35	150	135	**NSYAMRD15357SB**
Symmetrical DIN rail	SBM, SBX	35	200	185	**NSYAMRD20357SB**
Symmetrical DIN rail	SBM, SBX	35	300	285	**NSYAMRD30357SB**
Symmetrical DIN rail	SBM, SBX	35	400	385	**NSYAMRD40357SB**
Symmetrical DIN rail	SBM	35	500	485	**NSYAMRD50357SB**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Symmetrical DIN Rails

TBS TBP



- Installation: Fixing of the rails with Ø 4 mm self-tapping screws, (not included), Pozidrive and slotted head, ref. **NSYAMFSTB**

Supply:
Supplied without screws


NSYAMRD11357TB

Characteristics	Compatibility	Height (mm)	Depth (mm)	Length (mm)	Box (mm)	References
Symmetric DIN rail	TBS, TBP	35	7.5	97	105	**NSYAMRD11357TB**
Symmetric DIN rail	TBS, TBP	35	7.5	140	150	**NSYAMRD16357TB**
Symmetric DIN rail	TBS, TBP	35	7.5	168	175	**NSYAMRD19357TB**
Symmetric DIN rail	TBS, TBP	35	7.5	214	225	**NSYAMRD24357TB**
Symmetric DIN rail	TBS, TBP	35	7.5	264	275	**NSYAMRD29357TB**
Symmetric DIN rail	TBS, TBP	35	7.5	316	325	**NSYAMRD34357TB**

35-mm Symmetrical DIN Rails

PLM

They are fixed to the rear of the enclosure without uprights, with a pitch of 25 mm for the notches on the rear of the enclosure using direct-fixing nuts ref. **NSYTCSPLM** or **NSYTCSM6PLM**.

- Material: Galvanized steel

Supply:
References by unit. Order by multiples of 2 units (2, 4, 6, etc.)



NSYCS200PLM

Characteristics	Compatibility	For wall-mounted enclosure width (mm)	Rail length (mm)	References
35 mm symmetrical DIN rails	PLM	215	180	**NSYCS200PLM**
35 mm symmetrical DIN rails	PLM	330	280	**NSYCS300PLM**
35 mm symmetrical DIN rails	PLM	430 / 436	380	**NSYCS400PLM**
35 mm symmetrical DIN rails	PLM	536	480	**NSYCS500PLM**
35 mm symmetrical DIN rails	PLM	636	580	**NSYCS600PLM**
35 mm symmetrical DIN rails	PLM	852	795	**NSYCS800PLM**

20/10e mm Zinc-Coated Pre-Drilled Uprights

CRN S3D S3X PLM S3HD


DZ6MZ211




- Ø 11 mm holes enable to adjust the rows of equipment by 20 mm steps.

Characteristics	Compatibility	Height (mm)	Weight (g)	References
20/10e mm zinc-coated pre-drilled uprights	CRN, S3D, S3X, PLM, S3HD	1920	4000	**DZ6MZ211**

Brass Nuts to Fix the Upright to the Enclosures

CRN S3D S3X PLM S3HD S3HF




Supply:
Four Brass nuts


NSYAMCSF

Characteristics	Compatibility	References
Brass nuts for screws M8 to fix the upright to the enclosures	CRN, S3D, S3X, PLM, S3HD, S3HF	**NSYAMCSF**

Notched Clamp Nuts for Uprights

CRN S3D S3X PLM S3HD



DZ5MF6

- Specially designed for pre-drilled uprights.

Supply:
100 units. References per unit.
To be ordered in multiples of 100 (100, 200, 300, etc).

Characteristics	Compatibility	Type	Weight (g)	References
Notched clamp nuts	CRN, S3D, S3X, PLM, S3HD	M6	7.0	**DZ5MF6**
Notched clamp nuts	CRN, S3D, S3X, PLM, S3HD	M8	8.0	**DZ5MF8**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Rails

Standard Uprights

SM | SFN | SMX | SFX | SFN HD | SFN HF

- Vertical uprights for fixing plates and rails.
- They can be fixed on the mounting plate fixing brackets or on the upright fixing bracket, ref. **NSYMFB**.
- Adjustable height with a pitch of 25 or 50 mm.
- Material: Galvanized steel
- Thickness: 20/10[e] mm



Supply:
Set of two uprights



NSYVR18

Characteristics	Compatibility	Height (mm)	A (mm)	References
Standard uprights	SM, SFN, SMX, SFX, SFN HD, SFN HF	1800	1696	**NSYVR18**
Standard uprights	SM, SFN, SMX, SFX, SFN HD, SFN HF	2000	1896	**NSYVR20**
Standard uprights	SM, SFN, SMX, SFX, SFN HD, SFN HF	2200	2096	**NSYVR22**

Technical Uprights

SM | SFN | SMX | SFX | PLA

- Vertical uprights for fixing plates and rails.
- They can be fixed to the fixing brackets of the mounting plate or to the uprightfixing bracket (ref. **NSYMFB**).
- Adjustable height in steps of 2.5 mm (with quarter-turn nuts, ref. **NSYSNM6** or **NSYSNM8**) or 25 mm (with cage nuts, ref. **NSYCNM6** or **NSYCNM8**).
- Material: Galvanized steel
- Thickness: 20/10[e] mm



Comment:
NSYTVR20 is not compatible with PLA or PHD 2000 mm high enclosures. Use 2 x **NSYTVR10**.

Supply:
Set of two uprights


NSYTVR7

Characteristics	Compatibility	Height (mm)	A (mm)	References
Technical uprights	PLA	750	625	**NSYTVR7**
Technical uprights * Control desk	PLA	1000*	675	**NSYTVR8**
Technical uprights	PLA	1000	875	**NSYTVR10**
Technical uprights	SM, SFN, PLA	1200	1075	**NSYTVR12**
Technical uprights	PLA	1250	1125	**NSYTVR125**
Technical uprights	SM, SFN, SMX, PLA	1400	1275	**NSYTVR14**
Technical uprights	PLA	1500	1375	**NSYTVR15**
Technical uprights	SM, SFN, SMX	1600	1475	**NSYTVR16**
Technical uprights	SM, SFN, SMX, SFX	1800	1675	**NSYTVR18**
Technical uprights	SM, SFN, SMX, SFX	2000	1875	**NSYTVR20**
Technical uprights	SFN	2200	2075	**NSYTVR22**

Bracket for Fixing Uprights

SM | SFN | SMX | SFX | PLA | SFN HD | SFN HF

- Brackets for fixing the uprights, standard or technical, at the same level as the structure, obtaining a greater working surface inside the enclosure.
- They allow two pairs of uprights to be fixed back-to-back, doubling the working surface.
- The brackets are fixed to the structure by means of M6 self-tapping screws.
- Adjustable depth with a pitch of 25 mm.
- Material: Zinc-coated steel.

Supply:
Four brackets for fixing uprights and fixing elements.


NSYMFB

Characteristics	Compatibility	References
Bracket for fixing uprights	SM, SFN, SMX, SFX, PLA, SFN HD, SFN HF	**NSYMFB**

Screws for Uprights

All



AF1VA612

Characteristics	Compatibility	Supply (units)	References
M6 x 12 screw	All	100	**AF1VA612**
M6 x 18 screw	All	100	**AF1VA618**
M8 x 20 screw	All	100	**AF1VC820**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Vertical Adaptation Profiles

SM



- The vertical adaptation profiles provide fixing points at the entrance to the enclosure.
- Fixing on the screws of the hinge and catches of the lock.
- Allows the depthwise fixing of cross-rails, etc.
- Thickness: 15/10e mm
- Material: Galvanized steel



Supply:
Two vertical adaptation profiles and fixing screws




NSYSMVR12


Characteristics	Compatibility	Height (mm)	References
Vertical adaptation profiles	SM	1200	**NSYSMVR12**
Vertical adaptation profiles	SM	1400	**NSYSMVR14**
Vertical adaptation profiles	SM	1600	**NSYSMVR16**
Vertical adaptation profiles	SM	1800	**NSYSMVR18**
Vertical adaptation profiles	SM	2000	**NSYSMVR20**

Horizontal Adaptation Profiles

SM



- The horizontal adaptation profiles provide fixing points at the entrance to the enclosure.
- Thickness: 15/10e mm
- Material: Galvanized steel



Supply:
Two horizontal adaptation profiles and fixing screws




NSYSMHR6

Characteristics	Compatibility	Width (mm)	References
Horizontal adaptation profiles	SM	600	**NSYSMHR6**
Horizontal adaptation profiles	SM	800	**NSYSMHR8**
Horizontal adaptation profiles	SM	1000	**NSYSMHR10**
Horizontal adaptation profiles	SM	1200	**NSYSMHR12**
Horizontal adaptation profiles	SM	1600	**NSYSMHR16**

Symmetric Mounting Rail

CRN S3D PLM

- 2 types: Type A: 35 x 15 mm, Type B: 35 x 7.5 mm
- Material: Zinc-coated steel
- Standards: DIN 715
- Thickness: Type A: 15/10e mm, Type B: 10/10e mm
- Fixing: Fixed to mounting plates or another fixing elements, uprights not included in the supply



Supply:
10 rails and fixings for direct assembling to the structure. References by unit. Order by multiples of 10 units(10, 20, etc.)



NSYSDR30B

Characteristics	Compatibility	Type	Enclosure width (mm)	Rail length (mm)	References
Symmetric mounting rail	CRN, S3D, PLM	B	300	250	**NSYSDR30B**
Symmetric mounting rail	CRN, S3D, PLM	B	400	350	**NSYSDR40B**
Symmetric mounting rail	CRN, S3D, PLM	A	500	450	**NSYSDR50A**
Symmetric mounting rail	CRN, S3D, PLM	A	600	550	**NSYSDR60A**
Symmetric mounting rail	CRN, S3D, PLM	A	800	750	**NSYSDR80A**
Symmetric mounting rail	CRN, S3D, PLM	A	1000	950	**NSYSDR100A**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Rails

Symmetric Rails

All



- Material: Galvanized steel, zinc-coated steel or aluminum
- Length: 2000 mm



NSYSDR200D

Characteristics	Compatibility	Type	Order by Multiples	Perforations	References
Symmetric rail, Galvanized steel	All	A	10	Perforated	**NSYSDR200D**
Symmetric rail, Galvanized steel	All	B	10	Perforated	**NSYSDR200BD**
Symmetric rail, Galvanized steel	All	A	10	Not perforated	**NSYSDR200**
Symmetric rail, Galvanized steel	All	B	10	Not perforated	**NSYSDR200B**
Symmetric rail, Zinc-coated steel	All	C	6	Not perforated	**AM1DL201**
Symmetric rail, Aluminum	All	D	10	Not perforated	**AM1EA200**

Symmetric C-Shaped Rails

All

- Rails for supporting and fixing switchgear on panels and enclosures, formation of chassis, racks and panel reinforcements.
- Material: Galvanized steel
- Fixing: They are fixed to the structure and to one another by means of fixing elements
- Length: 2000 mm




Supply:
References by unit. Order by multiples of 10 units(10, 20, etc.)


NSYCN20

Characteristics	Compatibility	Dimensions (mm)								Perforations	References
		A	J	C	D	E	F	G	H		
Symmetric C-shaped rails 21x11x10	All	21	11	10	1.5	5.5	-	-	-	Not perforated	**NSYCN20**
Symmetric C-shaped rails 21x11x10	All	21	11	10	1.5	5.5	5	6.2	15	Perforated	**NSYCNT20**
Symmetric C-shaped rails 40x20x24	All	40	20	24	1.5	8	-	-	-	Not perforated	**NSYCN40**
Symmetric C-shaped rails 40X20X24	All	40	20	24	1.5	8	10	8.5	30	Perforated	**NSYCNT40**


Asymmetric DIN Rails

All



Supply:
10 rails with a length of 2 m.
References by unit. Order by multiples of 10 units (10, 20, etc.)


- Material: Galvanized steel
- Length: 2000 mm


NSYADR200D

Characteristics	Compatibility	Perforations	References
Asymmetric DIN rail	All	Perforated	**NSYADR200D**
Asymmetric DIN rail	All	Not perforated	**NSYADR200**

Double-Profile DIN Rails

All



Supply:
10 rails with a length of 2 m.
References by unit. Order by multiples of 10 units (10, 20, etc.)
ref. **NSYDPR200T** multiples 20

- Material: Galvanized steel
- Length: 2000 mm


NSYDPR200D

Characteristics	Compatibility	Thickness (mm)	Perforations	Order by Multiples	References
Double-profile DIN rail	All	15/10[e]	Perforated	10	**NSYDPR200D**
Double-profile DIN rail	All	10/10[e]	Perforated	20	**NSYDPR200T**
Double-profile DIN rail	All	15/10[e]	Not perforated	10	**NSYDPR200**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Combiplas Nut for Symmetric C-Shaped Rails

All


NSYBN206

Characteristics	Compatibility	Rail type	Nuts type	Supply	References
Combiplas nut for symmetric C-shaped rails	All	C20	M4	100	**NSYBN204**
Combiplas nut for symmetric C-shaped rails	All	C20	M6	100	**NSYBN206**
Combiplas nut for symmetric C-shaped rails	All	C40	M4	50	**NSYBN404**
Combiplas nut for symmetric C-shaped rails	All	C40	M6	50	**NSYBN406**
Combiplas nut for symmetric C-shaped rails	All	C40	M8	50	**NSYBN408**
Combiplas nut for symmetric C-shaped rails	All	C60	M6	20	**NSYBN606**

Metal Sliding Nut for Symmetric C-Shaped Rails

All


NSYB406

Characteristics	Compatibility	Rail type	Nuts type	Supply	References
Metal sliding nut for symmetric C-shaped rails	All	C40	M6	-	**NSYB406**

Screws for Rails

TBS TBP

- Ø 4 x 10 mm

Supply:
Pack of 100 screws


NSYAMFSTB

Characteristics	Compatibility	References
Screws Ø4 mm, height 10 mm	TBS, TBP	**NSYAMFSTB**

Plastic Nuts for Rail Fixing

PLM

They slide directly into the notches, with a pitch of 25 mm, which are located on the rear of the enclosures, except enclosure ref. **NSYPLM3025G/TG**. They allow direct fixing of symmetrical DIN rails by self-tapping screws. Option of raising the rails with an M6 spacer using a plastic nut containing an M6 nut.

Supply:
References by unit. Order by multiples of 20 units (20, 40, 60, etc.)


NSYTCSPLM

Characteristics	Compatibility	References
Plastic nut with self- tapping screw	PLM	**NSYTCSPLM**
Plastic nut containing an M6 metal nut	PLM	**NSYTCSM6PLM**

Nuts for Symmetric Rails


PB500863_25_nb

Supply:
100 nuts


AF1CG4

- Clip-on nut.

Characteristics	Compatibility	Type	References
Nuts for symmetric rails	All	M4	**AF1CG4**
Nuts for symmetric rails	All	M5	**AF1CG5**
Nuts for symmetric rails	All	M6	**AF1CG6**

Nuts for Asymmetric DIN Rails, 2000 mm Version


PB500866_24_nb

Supply:
100 nuts


DZ5ME5

- Quarter-turn sliding nut.

Characteristics	Compatibility	Type	References
Nuts for asymmetric DIN rails, 2000 mm version	All	M4	**DZ5ME5**
Nuts for asymmetric DIN rails, 2000 mm version	All	M5	**DZ5ME8**
Nuts for asymmetric DIN rails, 2000 mm version	All	M6	**DZ5ME9**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Accessories for Rails

Nuts for Double-Profile DIN Rails


PB500886_24_nb


AF1CF34

Supply:
100 nuts

- Quarter-turn sliding nut.

Characteristics	Compatibility	Type	References
Nuts for double-profile DIN rails	All	M3 + M4	**AF1CF34**
Nuts for double-profile DIN rails	All	M5 + M6	**AF1CF56**


Connectors for Symmetric C-Shaped Rails

- The connectors enable the formation of chassis or frames and structures for fixing switchgear, in any position inside the enclosures, allowing the fixing of DIN rails or other elements.
- See symmetric C-shaped rails.

EVA Connectors

Steel


NSYEVA20



- To join two symmetric C-shaped rails, C20 and C40 types, forming an overlapping assembly with plane change, or also at right angles for the formation of spacers or supports at a different level.
- Material: Zinc-coated steel


Supply:
20 units. References by unit. Order by multiples of 20 units (20, 40, 60, etc.)

Characteristics	Compatibility	Dimensions (mm)					References
		A	B	C	D	E	
EVA connectors	Steel	43	19	2	6.2	15	**NSYEVA20**

EN Connectors

Steel


NSYEN20




- To create L-shaped assemblies with plane change in the symmetric C-shaped rails, between them or with any other section.
- Material: Zinc-coated steel

Supply:
20 units. References by unit. Order by multiples of 20 units (20, 40, 60, etc.)

Characteristics	Compatibility	References
EN connectors	Steel	**NSYEN20**
EN connectors	Steel	**NSYEN40**

Examples


PB500509_73_nb


Combinations with connectors for symmetric C-shaped rails

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Connectors for Symmetric C-Shaped Rails

Hexagonal Spacers

All



- Hexagonal spacers for raising switchgear, mounting plates, etc. They can be linked to achieve variable heights with gradual elevation.
- Their assembly requires M6 or M8 caged nuts.
- Material: Zinc-coated steel
- Installation: If used to raise a mounting plate, the maximum load of the mounting plate is decreased

Supply:
100 hexagonal connectors.
References by unit.
Order by multiples of 100 units (100, 200, 300, etc.)


NSYE1025

Characteristics	Compatibility	Thread type	Spacer height (mm)	References
Hexagonal spacers	All	M5	10	**NSYE1025**
Hexagonal spacers	All	M5	15	**NSYE1525**
Hexagonal spacers	All	M5	20	**NSYE2025**
Hexagonal spacers	All	M6	10	**NSYEX106**
Hexagonal spacers	All	M6	14	**NSYEX146**
Hexagonal spacers	All	M6	16	**NSYEX166**
Hexagonal spacers	All	M6	20	**NSYEX206**
Hexagonal spacers	All	M6	30	**NSYEX306**
Hexagonal spacers	All	M6	40	**NSYEX406**
Hexagonal spacers	All	M6	50	**NSYEX506**
Hexagonal spacers	All	M6	100	**NSYEX1006**
Hexagonal spacers	All	M8	15	**NSYEX158**
Hexagonal spacers	All	M8	20	**NSYEX208**
Hexagonal spacers	All	M8	30	**NSYEX308**
Hexagonal spacers	All	M8	40	**NSYEX408**
Hexagonal spacers	All	M8	50	**NSYEX508**
Hexagonal spacers	All	M8	60	**NSYEX608**
Hexagonal spacers	All	M8	100	**NSYEX1008**

Rail Support Bracket

SM SFN SMX SFX SD


NSYFB45

- Bracket for fixing rails at an angle of 45°.
- Material: Zinc-coated steel
- Insallation: PanelSeT SFN: Mounted on the structure and/or mounting plates
  PanelSeT SM: Mounted on the bottom mounting rail and/or mounting plates



Supply:
Ten units and fixing elements.
Reference by unit. Order by multiples of 10 (10, 20, 30...)


Characteristics	Compatibility	References
Rail support bracket	SM, SFN, SMX, SFX, SD	**NSYFB45**

Combined Support Bracket

SM SFN SMX SFX SD


NSYETF

- Allows the installation of a DIN rail and an earthing strip on different planes to minimize the cable radiuses.
- Material: Zinc-coated steel
- Insallation: PanelSeT SFN: Directly on the structure and/or using mounting plates
  PanelSeT SM: On the bottom adjustment rails and/or on mounting plates



Supply:
Ten combined support brackets and fixing elements.
Reference by unit. Order by multiples of 10 (10, 20, 30...)


Characteristics	Compatibility	References
Combined support bracket	SM, SFN, SMX, SFX, SD	**NSYETF**

Terminal-Block Support Bracket

SM SFN SMX SFX SD


NSYEDCO

- Allow the mounting of a DIN rail.
- Tilted to 30°.
- Material: Treated steel



Supply:
Two lugs and fixings

Characteristics	Compatibility	References
Terminal-block support bracket	SM, SFN, SMX, SFX, SD	**NSYEDCO**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Accessories for Rails

Combined Support Bracket (Vertical)

SM | SFN | SMX | SFX | SD


DZ5MS10

- Allow the installation of a DIN rail and an earthing strip on different planes, to minimize the cable radiuses.
- Material: Zinc-coated steel
- Installation: PanelSeT SFN and SM: Directly on the vertical structure and/or using mounting plates


PB502727_68_nb

Supply:
10 brackets

Characteristics	Compatibility	References
Combined support bracket (vertical)	SM, SFN, SMX, SFX, SD	**DZ5MS10**

Nuts for Uprights and Serrated C-Shaped Rails

All


PB500818_31_nb


NSYSNSM6


NSYSNM6


NSYCNM6


NSYFNM6

Characteristics	Compatibility	Supply (units)	References
M6 quarter-turn sliding nut	All	10	**NSYSNM6**
M8 quarter-turn sliding nut	All	10	**NSYSNM8**
M6 quarter-turn serrated sliding nut	All	10	**NSYSNSM6**
M8 quarter-turn serrated sliding nut	All	10	**NSYSNSM8**
M6 renovable nut	All	50	**NSYCNM6**
M8 renovable nut	All	50	**NSYCNM8**
M6 flat nut	All	50	**NSYFNM6**
M8 flat nut	All	50	**NSYFNM8**

Intermediate Support in the Two Door Enclosures

PLA


- Required accessory for installing support plates, ref. **NSYBANPLA●●●** or uprights, ref. **NSYSPLA●●●** in the two door enclosures
- Material: Galvanized steel

Supply:
Two support kits


NSYSBPLA

Characteristics	Compatibility	References
Intermediate support in the two door enclosures	PLA	**NSYSBPLA**

Recommendation


DB300659_33_grau_001

Intermediate support
Accessory required for installing uprights, ref. **NSYSPLA●●●**.
Only for two door enclosures.
Supply: one (including two supports)
ref. **NSYSBPLA**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Equipment Assembly Accessories

Heavy Loads

Rails for Heavy Loads

SFN | SFN 6G


- Mounted with a cable gland plate (directly fixed on the bottom frame of the enclosure) or with a previously mounted mounting plate. Furthermore, they can be fixed anywhere in the enclosure with a heavy load kit.
- Laterally adjustable with a pitch of 25 mm.
- Elongated holes for adjusting the center-to-center distance of the switchgear.
- The nominal width of cross-rails must be 100 mm shorter than the associated heavy load kit width.
- Thickness is 30/10e mm.
- Material used is galvanized steel.


PB500855_29_nb


PB503536_68_nb


NSYHLCR40

+


NSYSHLT6040


Supply:
Two rails for heavy loads and fixing elements

Characteristics	Compatibility	Associated heavy load kit references	Maximum load (kg)	Nominal width (mm)	References
Rail for heavy loads	SFN, SFN 6G	Not usable with heavy load kit	575	400	**NSYHLCR40**
Rail for heavy loads	SFN, SFN 6G	NSYSHLT6040 / NSYSHLT6060 / NSYSHLT6080	525	500	**NSYHLCR50**
Rail for heavy loads	SFN, SFN 6G	Not usable with heavy load kit	500	600	**NSYHLCR60**
Rail for heavy loads	SFN, SFN 6G	Not usable with heavy load kit	475	800	**NSYHLCR80**


Heavy Load Supports


PB503918

Combination Examples


PB503533_42_nb

- Heavy Load Kit + Ventilated Shelf


PB503534_42_nb

- Heavy Load Kit + Partially Ventilated Shelf


PB503535_42_nb

- Heavy Load Kit + Plain Shelf For Battery


PB503536_68_nb


- Heavy Load Kit + Heavy Load Cross-Rails

Serrated C-Shaped Rail for Heavy Loads

All


AM1EC200

- Marked in steps of 25 mm to facilitate switchgear positioning.
- Material: Zinc-coated steel
- Thickness: 20/10e mm




DB300343_69_nb

Supply:
Two rails with a length of 2 m

Characteristics	Compatibility	Rail length (mm)	References
Serrated C-shaped rail for heavy loads	All	2000	**AM1EC200**

Ventilated Shelf

SM | SFN | SFN HD


NSYDHLT8080

- Airing is ensured by two cut-out sizes: 11 x 13 mm rectangles for fixation on both sides with self- tapping screws, 40 x 8.5 mm rectangles.
- The ventilated shelf must be fixed in the enclosure with a heavy load kit.
- Material: Steel
- Color: RAL 7035 gray
- Maximum load: 350 kg


PB503466_42_nb

Supply:
1 tray and fixing elements

Characteristics	Compatibility	Tray dimensions W x D x H (mm)	Width (mm)	Depth (mm)	References
Ventilated shelf	SM, SFN, SFN HD	700 x 759 x 50	800	800	**NSYDHLT8080**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Trays and Shelves

Fixed Tray


SM SFN SFX SFN PC SFN HD

- Provided with cut-outs for improving air circulation inside.
- Material: Steel
- Finish: Painted with epoxy polyester resin
- Color: RAL 7035 gray
- Maximum load: 150 kg direct fixed to the structure, 40 kg when universal cross-rails are used

Options for fixing the tray to the enclosure:
If the tray has the same dimensions as the enclosure:
- PanelSeT SFN: Direct fixing to the structure.
- PanelSeT SFX: Installation possible only with universal cross-rails, see page 525.
- PanelSeT SM: Fixing by means of adaptation profiles and 40 mm universal cross-rails (1 row) in vertical position.

If the tray is smaller than the dimensions of the enclosure:
- Fixing on depth cross-rails.
- Depth-adjustable tray with a pitch of 25 mm.

Supply:
1 fixed tray and fixing elements


NSYFXT6040

Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	600	400	**NSYFXT6040**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	800	400	**NSYFXT8040**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	600	500	**NSYFXT6050**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	800	500	**NSYFXT8050**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	600	600	**NSYFXT6060**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	800	600	**NSYFXT8060**
Fixed tray	SM, SFN, SFX, SFN PC, SFN HD	800	800	**NSYFXT8080**

Telescopic Rails

SM SFN SFX SFN PC SFN HD

- Mechanical stop of the rails in open and closed position.
- Material: Galvanized steel
- Finish: Painted with epoxy polyester resin
- Maximum load: 25 kg evenly distributed

Options for fixing the tray to the enclosure:
- PanelSeT SFN: Installation directly on the structure of the enclosure or on universal cross-rails.
- PanelSeT SFX: Instalation possible only with universal cross-rails, see page 525.
- PanelSeT SM: Installation by means of adaptation profiles and 40 mm universal cross-rails (1 row) in vertical position, or on horizontal universal cross-rails.

The installation of a telescopic tray consists of the following:
- 1 fixed tray.
- 2 telescopic rails.

Supply:
2 telescopic rails and fixing elements


NSYTTG40

Characteristics	Compatibility	Width (mm)	Depth (mm)	References
Telescopic rails	SM, SFN, SFX, SFN PC, SFN HD	600/800	400	**NSYTTG40**
Telescopic rails	SM, SFN, SFX, SFN PC, SFN HD	600/800	500	**NSYTTG50**
Telescopic rails	SM, SFN, SFX, SFN PC, SFN HD	600/800	600/800	**NSYTTG60**

Handle for Telescopic Trays

SM SFN SFX SFN PC SFN HD

- Designed for easy extraction of the sliding trays.
- Material: Polyamide 6 (black).

Supply:
2 units and fixing elements


NSY1TH

Characteristics	Compatibility	References
Handle for telescopic trays	SM, SFN, SFX, SFN PC, SFN HD	**NSY1TH**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Support Plate


PLA



NSYSPLA75

Installation:
It is installed directly on the bottom part of the enclosure.
For the installation of one or several support plates, use two sets of two uprights suitable for the height (to be ordered separately). These uprights offer the option of adjusting the height with a step of 50 mm.





- Designed to support assorted equipment or simply to install a separation.
- In the two door enclosures, the installation of the plate or the uprights requires the prior installation of an intermediate support, ref. **NSYSBPLA**, presented beside.
- Material: Galvanized steel

Supply:
Delivered with the fixings required for installation

Characteristics	Compatibility	Height	Depth	Upright Number of adjustments	References
Support plate	PLA	750	320/420/620	2	2 x **NSYSPLA75**
Support plate	PLA	1000	320/420	3	2 x **NSYSPLA100**
Support plate	PLA	1250	320/420/620	4	2 x **NSYSPLA125**
Support plate	PLA	1500	320/420/620	5	2 x **NSYSPLA150**
Support plate	PLA	2000	420	6	2 x **NSYSPLA100**

Characteristics	Compatibility	Depth (C)	Width (B)	Plate Max. load	References
Support plate	PLA	320	500	60 kg	**NSYBANPLA53**
Support plate	PLA	420	500	50 kg	**NSYBANPLA54**
Support plate	PLA	420	750	50 kg	**NSYBANPLA74**
Support plate	PLA	620	750	50 kg	**NSYBANPLA76**

6

Folding Support Tray

CRN S3D SM SFN SMX SFX




NSYSDT5



NSYSDT8

- Adjustable horizontal support for laptop computers, documents or any other element.
- Installation on the reinforcement frame of the door.
- Can also be installed on the door cross-rails, see page 527.
- 4 positions: 45°, 60°, 75° and 90°.
- Maximum load: 30 kg
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray



Supply:
1 folding support tray and fixing elements

Characteristics	Compatibility	Width of enclosure (mm)	Width of tray (mm)	References
Folding support tray	CRN, S3D, SM, SFN, SMX, SFX	500	325	**NSYSDT5**
Folding support tray	CRN, S3D, SM, SFN, SMX, SFX	600	425	**NSYSDT6**
Folding support tray	CRN, S3D, SM, SFN, SMX, SFX	800	625	**NSYSDT8**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Earthing

Earthing Strip

Steel

- Perforated brass bar, 15 x 3 mm.
- 1 m long.
- 87 connection points, M5 drill holes

Supply:
1 earthing stripand fixing elements


NSYECB1M153

Characteristics	Compatibility	References
Earthing strip	Steel	**NSYECB1M153**

Earth Braids

Steel

- They help guarantee the earth connection for high frequencies, avoiding the disturbing electric currents that are produced.
- Material: Tinned copper.

Supply:
10 earth braids
(nuts and washers not included)


NSYEB156D6

Characteristics	Compatibility	Section (mm²)	Terminal Ø (mm)	Length (mm)	Width (mm)	References
Earth braids	Steel	6	7	150	12	**NSYEB156D6**
Earth braids	Steel	10	6.5	150	17	**NSYEB1510D6**
Earth braids	Steel	16	8.5	155	17	**NSYEB1516D8**
Earth braids	Steel	25	8.5	200	27	**NSYEB2025D8**
Earth braids	Steel	50	8.5	200	33	**NSYEB2050D8**

Earth Cables

Steel

- Make it easier to install a safe earth connection, with a contact, with optimized length.
- Material: Brass and copper alloy terminal, green and yellow PVC insulated sheath


Supply:
10 earth cables (nuts and washers not included). Reference by unit. Order by multiples of 10 (10, 20, 30...)


NSYEL136D6

Characteristics	Compatibility	Section (mm²)	Terminal Ø (mm)	Length (mm)	References
Earth cables	Steel	6	6.4	130	**NSYEL136D6**
Earth cables	Steel	6	6.4	160	**NSYEL166D6**
Earth cables	Steel	6	8.3	160	**NSYEL166D8**
Earth cables	Steel	6	6.4	220	**NSYEL226D6**
Earth cables	Steel	25	8.3	220	**NSYEL2225D8**
Earth cables	Steel	10	6.4	250	**NSYEL2510D6**
Earth cables	Steel	25	8.3	350	**NSYEL3525D8**

Fixing Lugs for the Earthing Strip

CRN S3D S3X




PB501000_42_nb


NSYEDCOS


- They allow the mounting of an earth collector rail or a DIN rail at the top and bottom of an enclosure.
- Mounting incompatible with certain accessories. Please consult us.
- Fixing: On holes made in the gutter of the enclosure.

Supply:
2 lugs and fixings.

Characteristics	Compatibility	References
Fixing lugs for the earthing strip	CRN, S3D, S3X	**NSYEDCOS**

Combined Fixing Lugs for the Earthing Strip

Steel


PB500833_35_nb

- Allows the mounting of an earth collector rail and a DIN rail.
- Tilted to 30°.
- Earthing strip, ref. **NSYECB1M153**. See page 540.

Supply:
Two fixing lugs and fixing elements


NSYEDCOC

Characteristics	Compatibility	References
Combined fixing lugs for the earthing strip	Steel	**NSYEDCOC**

Central Earthing Point

SM SFN SMX SFX SD


NSYCEP

- Connects earthing braids and cables to the structure of the enclosure.
- The earth connection is made by means of the M8 x 18 mm screw.
- Fixing: Fixing to the structure by means of self-tapping screws

Supply:
1 central earthing point, elements for fixing to the structure, and fixings for fixing to the screw

Characteristics	Compatibility	References
Central earthing point	SM, SFN, SMX, SFX, SD	**NSYCEP**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Equipment Assembly Accessories

Inserts and Screws

Self-Tapping Screws

SBM SBX


NSYAMFSB

All

- Same reference for all enclosure dimensions
- Self-tapping, Pozidriv head, screws, for Ø 5 mm holes.

Supply:
100 units

Characteristics	Compatibility	References
Self-tapping screws	SBM, SBX	**NSYAMFSB**


NSYS13M5HS

Supply:
100 units. To be ordered in multiples of 100 (100, 200, 300, etc.)


NSYS16M5HS

- Hexagonal head, 4.8 x 16 mm thread.
- Drilling capacity: Thicknesses between 17.5/10e and 40/10e mm.

Characteristics	Compatibility	References
Plain mounting plate screw, self-tapping screw M5 x 13	All	**NSYS13M5HS**
Plain mounting plate screw, Self-tapping screw M5 x 16	All	**NSYS16M5HS**
Plain mounting plate screw, Self-tapping screw M6 x 16	All	**NSYS16M6HS**

Sealing Kit

SBM SBX


NSYPPSB

- The sealing kit helps to set up a lead-sealed cable of cover opening.
- Color: Green
- Ingress protection rating: IP66 according to IEC 60529
- Installation: Replaces the standard sealing washer on the box
- Same reference for all enclosure dimensions

Supply:
1 unit

Characteristics	Compatibility	References
Sealing kit	SBM, SBX	**NSYPPSB**

Fixing Options, Screw M6

SFN


NSYSPM6

- M6 x 10 mm

Supply:
50 screws

Characteristics	Compatibility	References
Screw M6	SFN	**NSYSPM6**

Fixing Inserts

PLM

Expanding inserts for addition to the M6 bosses of the enclosure, the M5 or M6 bosses of the door and the M8 bosses of the external rear part of the enclosure.

Supply:
References by unit. Order by multiples of 8 units (8, 16, 24, etc.). M5 and M6 inserts to be ordered in multiples of 20


NSYTEX5 NSYTEX6 NSYTEX8PLM

Characteristics	Compatibility	Insert size	For wall-mounted enclosure	References
Fixing inserts	PLM	M5	NSYPLM43G and NSYPLM54G	**NSYTEX5**
Fixing inserts	PLM	M6	NSYPLM64G to NSYPLM108G	**NSYTEX6**
Fixing inserts	PLM	M8	For the rear of the enclosure	**NSYTEX8PLM**

M8 Inserts

PLA


NSYTEX8

- To be placed in the bosses molded on the doors, uprights, rear panels and bottom and top parts, for fixing accessories and assorted devices.
- Material: Brass

Supply:
References by unit. Order by multiples of 8 units (8, 16, 24, etc.)

Characteristics	Compatibility	References
Fixing inserts	PLA	**NSYTEX8**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electrical Distribution and IT

Modular Chassis

DLM Modular Chassis

CRN | S3D | S3X | S3DM | S3HD | S3DEX

- The chassis consists of metal cut-out front panels, which can be clipped on without screws.
- The depth of the chassis can be adjusted from 40 to 85 mm, between the rail and the front panel, allowing the installation of all types of devices.
- Material: Rigid galvanized steel structure
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray


Note:
1 module = 2 steps = 18 mm



NSYDLM24


Characteristics	Compatibility	Number of modules	Height (mm)	Width (mm)(B)	References
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	24	400	300	**NSYDLM24**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	48	500	400	**NSYDLM48**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	48	600	400	**NSYDLM48P**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	84	600	600	**NSYDLM84P**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	66	700	500	**NSYDLM66** *
DLM modular chassis	CRN, S3D, S3X, S3DM S3HD, S3DEX	88	700	500	**NSYDLM88**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	84	800	600	**NSYDLM84** *
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	112	800	600	**NSYDLM112**
DLM modular chassis	CRN, S3D, S3DM, S3HD	168	1000	600	**NSYDLM168**
DLM modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	234	1000	800	**NSYDLM240**

* Chassis with a plain front plate includes a partial mounting plate.




Front Panel Cut-Out

B: Enclosure width
C: Enclosure depth



Detail A
Rail Adjustment: 45 mm

Number of Modules per Chassis (Every 18 mm)



Chassis reference	NSYDLM24	NSYDLM48	NSYDLM48P	NSYDLM84P	NSYDLM66*	NSYDLM88	NSYDLM84*	NSYDLM112	NSYDLM168	NSYDLM240
Enclosure height (mm)	400	500	600	600	700	700	800	800	1000	1000
Enclosure width (mm)	300	400	400	600	500	500	600	600	600	800
Number of rows	2	3	3	3	3	4	3	4	6	6
Modules per row	12	16	16	28	22	22	28	28	28	39
Total n. of modules	24	48	48	84	66	88	84	112	168	234

Note:
References **NSYDLM48**, **NSYDLM48P** and **NSYDLM84P**: the central row cannot receive modules at the height of the lock (check our technical instructions) when installed at the front of the enclosure. In this case, 1 module is sealed up. DLM modular chassis. The dimensions provided include the modular chassis which is the most commonly used accessory with this enclosure.

* Chassis with a plain front plate includes a partial mounting plate.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

DLA Modular Chassis for Distribution

CRN | S3D | S3X | PLM | S3HD | S3DEX



PB502875_60_nb

NSYDLA24G

- Front panels and covers installed in the front part, not depth adjustable
- Rigid structure for the installation of modular devices
- Open front panels with 35-mm DIN rail and plain front panels with mounted plate, according to the model
- Front plates are quickly installed with no fixings
- Rail depth adjustable from 40 to 85 mm
- System for standard circuit marking
- Incompatible with the internal doors and the step slides
- Neutral/earth strip: 2 x 16 mm² + 5 x 6 mm²
- Material:
  - Front panels and finish covers: Polystyrene
  - Rigid structure: Galvanized steel
- Color: Front panels and finish covers: RAL 7035 gray

Characteristics	Compatibility	No. of rows	No. of 18 mm modules per row	No. of 18 mm modules	No. of plates	PLM enclosure References		S3D enclosure (depth ≥ 200 mm)		References
								Height (mm)	Width (mm)	
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	2	12	24	-	NSYPLM43G	NSYPLM43TG	400	300	**NSYDLA24G**
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	3	16	48	-	NSYPLM54G	NSYPLM54TG	500	400	**NSYDLA48G**
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	3	16	48	-	NSYPLM64G	NSYPLM64TG	600	400	**NSYDLA48PG**
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	3	22	66	1	NSYPLM75G	NSYPLM75TG	700	500	**NSYDLA66G** *
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	4	22	88	-	NSYPLM75G	NSYPLM75TG	700	500	**NSYDLA88G**
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	3	28	84	1	NSYPLM86G	NSYPLM86TG	800	600	**NSYDLA84G** *
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	4	28	112	-	NSYPLM86G	NSYPLM86TG	800	600	**NSYDLA112G**
DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	6	39	234	-	NSYPLM108G	NSYPLM108TG	1000	800	**NSYDLA234G**


DB300620_SE



NSYDLA24G **NSYDLA48G** **NSYDLA48PG** **NSYDLA66G** **NSYDLA88G** **NSYDLA84G** **NSYDLA112G** **NSYDLA234G**

* Chassis with a plain front plate includes a partial mounting plate.

DB300621_72_nb



★★ Models **NSYDLA48PG**, **66G**, **88G**, **84G** and **112G**.
★★★ Models **NSYDLA234G**.

Plain Front Panels for DLA Modular Chassis

CRN | S3D | S3X | PLM | S3HD | S3DEX

- Front panel for non-modular device protection on one row.
- To be ordered in multiples of two.
- Material: Polystyrene
- Color: RAL 7035 gray


NSYCTL300DLAG

Characteristics	Compatibility	Width (mm)	For installing on the chassis	References
Plain front panels for DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	456	NSYDLA66G and NSYDLA88G	**NSYCTL500DLAG**
Plain front panels for DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	555	NSYDLA84G and NSYDLA112G	**NSYCTL600DLAG**
Plain front panels for DLA modular chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	755	NSYDLA234G	**NSYCTL800DLAG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electrical Distribution and IT

Modular Chassis

Modular Distribution Chassis

PLM

- For mounted modular devices on two rows of nine 18-mm modules.
- Material:
  Chassis: Metal Protective
  Plate: Insulated material



NSYDLPLM18G

Characteristics	Compatibility	For enclosure	Reference
Modular distribution chassis	PLM	NSYPLM3025G/TG	**NSYDLPLM18G**

PLA PHD

- Chassis for modular switchgear, installed directly in the sealed enclosures (PLA version).
  For installation in enclosures with open bottom part (PLAZ version)
  it is necessary to use a set of adapter plates (ref. **NSYPTZ●●●**).
- Chassis made up of cover plates on a rigid structure.
- Quick installation without fixings.
- Distance between rail and front panel with adjustable depth from 40 to 85 mm.
- System for identifying electrical circuits supplied.
- Neutral/earth strip: 2 x 16 mm² + 5 x 6 mm² included in the standard offer.
- Incompatibility with: Cable entry plate, internal door,
  door switch and door retainer (ref. **NSYRETPLAU**).
- Material: Rigid structure: Galvanized steel, Cover plates: Self-extinguishing insulated
- Color: Cover plates: RAL 7035 gray

Note:
For dimensions see page 545
Other modular distribution accessories on page 521



PB502917_22_nb

Dimensions (mm) Height (A)	Width (B)	Compatibility	No. of doors	No. of rows	Rows for module	No. of modules 18 mm	No. of plates	References
750	500	PLA, PHD	1	4	4	76	-	**NSYDLP76G**
750	500	PLA, PHD	1	4	3	57	1	**NSYDLP57G** *
750	750	PLA, PHD	1	4	4	132	-	**NSYDLP132G**
750	750	PLA, PHD	1	4	3	99	1	**NSYDLP99G** *
750	1000	PLA, PHD	2	4 + 4	4 + 4	152	-	2 x **NSYDLP76G**
750	1000	PLA, PHD	2	4 + 4	3 + 3	114	1 + 1	2 x **NSYDLP57G** *
750	1250	PLA, PHD	2	4 + 4	4 + 4	208	-	**NSYDLP76G** + **NSYDLP132G**
750	1250	PLA, PHD	2	4 + 4	3 + 3	156	1 + 1	**NSYDLP57G** * + **NSYDLP99G** *
1000	500	PLA, PHD	1	6	6	114	-	**NSYDLP114G**
1000	500	PLA, PHD	1	6	5	95	1	**NSYDLP95G** *
1000	750	PLA, PHD	1	6	6	198	-	**NSYDLP198G**
1000	750	PLA, PHD	1	6	5	165	1	**NSYDLP165G** *
1000	1000	PLA, PHD	2	6 + 6	6 + 6	228	-	2 x **NSYDLP114G**
1000	1000	PLA, PHD	2	6 + 6	5 + 5	190	1 + 1	2 x **NSYDLP95G** *
1000	1250	PLA, PHD	2	6 + 6	6 + 6	312	-	**NSYDLP114G** + **NSYDLP198G**
1000	1250	PLA, PHD	2	6 + 6	5 + 5	260	1 + 1	**NSYDLP95G** * + **NSYDLP165G** *
1250	500	PLA, PHD	1	7	7	133	-	**NSYDLP133G**
1250	500	PLA, PHD	1	7	6	114	1	**NSYDLP114PG** *
1250	750	PLA, PHD	1	7	7	231	-	**NSYDLP231G**
1250	750	PLA, PHD	1	7	6	198	1	**NSYDLP198PG** *
1250	1000	PLA, PHD	2	7 + 7	7 + 7	266	-	2 x **NSYDLP133G**
1250	1000	PLA, PHD	2	7 + 7	6 + 6	228	1 + 1	2 x **NSYDLP114PG** *
1250	1250	PLA, PHD	2	7 + 7	7 + 7	364	-	**NSYDLP133G** + **NSYDLP231G**
1250	1250	PLA, PHD	2	7 + 7	6 + 6	312	1 + 1	**NSYDLP114PG** * + **NSYDLP198PG** *
1500	500	PLA, PHD	1	9	9	171	-	**NSYDLP171G**
1500	500	PLA, PHD	1	9	8	152	1	**NSYDLP152G** *
1500	750	PLA, PHD	1	9	9	297	-	**NSYDLP297G**
1500	750	PLA, PHD	1	9	8	264	1	**NSYDLP264G** *
1500	1000	PLA, PHD	2	9 + 9	9 + 9	342	-	2 x **NSYDLP171G**
1500	1000	PLA, PHD	2	9 + 9	8 + 8	304	-	2 x **NSYDLP152G** *
1500	1250	PLA, PHD	2	9 + 9	9 + 9	468	1 + 1	**NSYDLP171G** + **NSYDLP297G**
1500	1250	PLA, PHD	2	9 + 9	8 + 8	416	1 + 1	**NSYDLP152G** * + **NSYDLP264G** *

* Chassis with a plain front plate includes a partial mounting plate.


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Modular Distribution Chassis

PB502918_55_NB




DB300660_71_nb




NSYDLP76G **NSYDLP114G** **NSYDLP133G** **NSYDLP171G**

PB501388_41_nb



Details of the Depth Adjustment




NSYDLP57G **NSYDLP95G** **NSYDLP114PG** **NSYDLP152G**

PB502919_37_nb



Detail from Front Panel Mounting




NSYDLP132G **NSYDLP198G** **NSYDLP231G** **NSYDLP297G**

PB502920_32_nb




Detail from the Circuit Marking System



NSYDLP99G **NSYDLP165G** **NSYDLP198PG** **NSYDLP264G**

DB300661_nb



1 Dimensions of 42 or 67 mm or a pitch of 25 mm, according to the M8 boss chosen for the installation. See details in the enlarged image on the right. In enclosures with glazed doors, the two dimensions are reduced by 5 mm.
2 C = Depth of the enclosure.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electrical Distribution and IT

Modular Chassis

DL Modular Chassis

CRN | S3D | S3X | S3DM | S3HD | S3DEX


- Modular chassis designed for devices with heights of 53 and 68 mm, which can be coupled directly to the enclosure plate-support screws.
- Distance between device rail and protective cover plate: 45 mm.
- One-piece modular chassis
- The depth of the chassis can't be adjustable
- Material: Steel
- Finish: Metal protective cover plate
- Color: RAL 7035 gray

Note:
For PanelSeT S3D please consult us
Depth 150 mm: For coupling to enclosures with a depth of 200 mm, the stand-offs (ref. **NSYEX608**) are to be ordered separately (4 per chassis).



Characteristics	Compatibility	Height (mm)	Width (mm)	Depth (mm)	References
DL modular chassis	CRN, S3D, S3X, S3DM	300	250	150	**NSYDLCR18**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	400	300	150	**NSYDLCR24**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	400	300	150	**NSYDLCR36**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	500	400	150	**NSYDLCR48**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	600	400	150/200	**NSYDLCR64**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD	600	500	150/200	**NSYDLCR88**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	700	500	200	**NSYDLCR110**
DL modular chassis	CRN, S3D, S3X, S3DM, S3HD, S3DEX	800	600	200	**NSYDLCR135**

* Chassis with a plain front plate includes a partial mounting plate



Dimension F: Distance from the protective cover plate to the inside of the door.
Dimension G: Distance from the device-support rail to the rear of the enclosure.

For coupling to the enclosures with normal or transparent door	Dimensions (mm)						Number of 18 mm modules	Number of rows	Approx. weight (kg)
References	A	B	D	E	F	G			
NSYDLCR18	255	205	162	120	41	51	18	2	1.2
NSYDLCR24	355	255	216	160	41	51	24	2	1.7
NSYDLCR36	355	255	216	110	41	51	36	3	1.7
NSYDLCR48	455	355	288	130	41	51	48	3	2.4
NSYDLCR64	555	355	288	130	41	51/101	64	4	3.3
NSYDLCR88	555	455	396	130	41	51/101	88	4	4.5
NSYDLCR110	655	455	396	125	41	101	110	5	5.1
NSYDLCR135	755	555	486	140	41	101	135	5	7.5


Note: For enclosures with transparent door, the F dimension is reduced by 4 mm

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

DIN rail chassis

CRN | S3D | S3X | PLM | S3HD | S3DEX

- Components supplied with a DIN rail chassis:
  - Aluminum uprights.
  - DIN rails (symmetric section A or B, according to the reference).
  - Screws, washers and nuts need to mount the DIN rails to the uprights.
  - Set of four adapters, ref. **NSYAMCSF**, needed to fix the uprights to the enclosure. They are coupled directly to the rear of the actual enclosure or to the sliding plate supports.
  - Double-door enclosures offer the option of installing two plates.
- Material: Aluminum - Zinc-coated steel
- Supply: One DIN rail chassis





Characteristics	Compatibility	Height (mm)	Width (mm)	Type of rails	No. of rails	References
DIN rail chassis	CRN, S3D, S3X, PLM	300	300	B	4	**NSYMD33**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	400	300	B	4	**NSYMD43**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	500	400	B	4	**NSYMD54**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	600	400	B	6	**NSYMD64**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	600	600	A	6	**NSYMD66**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	700	500	B	6	**NSYMD75**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	800	600	A	6	**NSYMD86**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	800	600	A	6	2 x **NSYMD86**
DIN rail chassis	CRN, S3D, S3X, PLM, S3HD, S3DEX	1000	800	A	6	**NSYMD108**
DIN rail chassis	CRN, S3D, S3X, PLM	1200	800	A	7	**NSYMD128**

Blanking Plate

All


- Blanking plate for full or partial covering of the circuit-breaker windows; it can easily be cut to the required size.
- Material: PVC (polyvinyl chloride)




Characteristics	Compatibility	Number of modules	Color	Length (mm)	References
Blanking plate	All	4	RAL 7035 gray	72	**NSYATP72M**
Blanking plate	All	24	RAL 7035 gray	432	**NSYATP24DTM**
Blanking plate	All	61	RAL 7035 gray	1100	**NSYATPUND**

Plain Cover Plate

PLA





- Plain cover plate for non-modular switchgear protection.
- Can be cutted out according to needs.
- Material: Polystyrene (PS) (for 146 mm high)
- Fiberglass reinforced polyester (for 298 mm high)
- Color: RAL 7035 gray

Supply:
Order by multiples of 2 (2, 4, 6...)



Characteristics	Compatibility	For enclosure - Width (mm)	Height A (mm)	Thickness (mm)	References
Plain cover plate	PLA	500	146	2	**NSYCTL500DLPG**
Plain cover plate	PLA	500	298	4	**NSYCTL500DLP2**
Plain cover plate	PLA	750	146	2	**NSYCTL750DLPG**
Plain cover plate	PLA	750	298	4	**NSYCTL750DLP2**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Electrical Distribution and IT

19" Racks

19" Fixed Chassis for Wall-Mounted Enclosure

CRN | S3D | S3X | S3D IT | S3HD | S3DEX

- 19" fixed chassis comprising 2 19" uprights with fixing.
- Adjustable in depth by fixing on the step slides available as accessory.
- Material: Galvanized steel
- Thickness: 20/10^{e} mm
- Maximum load: 3 kg per unit


NSYVDM8UF

Characteristics	Compatibility	Enclosure dimensions (mm)		Unit number	References
		Height	Width		
19" fixed chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	400	600	8	**NSYVDM8UF**
19" fixed chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	600	600	12	**NSYVDM12UF**
19" fixed chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	800	600	17	**NSYVDM17UF**
19" fixed chassis	CRN, S3D, S3D IT, S3HD	1000	600	21	**NSYVDM21UF**

19" Swing Chassis for Wall-Mounted Enclosure

CRN | S3D | S3X | S3D IT | S3HD | S3DEX

- 19" swing chassis opening to 120° with locking system by 3-mm double-bar insert.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray
- Maximum load: 3 kg per unit


NSYVDM11UP

Characteristics	Compatibility	Enclosure dimensions (mm)		Unit number	References
		Height	Width		
19" swing chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	600	600	11	**NSYVDM11UP**
19" swing chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	800	600	16	**NSYVDM16UP**
19" swing chassis	CRN, S3D, S3D IT, S3HD	1000	600	20	**NSYVDM20UP**
19" swing chassis	CRN, S3D, S3X, S3D IT, S3HD, S3DEX	1000	800	20	**NSYVDM20U8P**
19" swing chassis	CRN, S3D, S3X, S3D IT	1200	800	25	**NSYVDM25U8P**

Fixings for 19" Rack

All

- They allow 19" accessories to be mounted.
- Caged nut compatible with 8.5 x 8.5 mm and 9.5 x 9.5 mm holes.


PB600189_28_nb


NSYGFR95M63

Characteristics	Compatibility	Set of	References
M6 screws + washers + nuts 8.5 mm	All	30	**NSYGFR95M63**
M6 x 16 screws and washers	All	50	**NSYGFR166P**
M6 caged nuts 9.5 mm	All	100	**NSYCN9M625**
M6 screws + washers + nuts 9.5 mm	All	50	**NSYGFR95M65**
M5 screws + washers + nuts 9.5 mm	All	50	**NSYGFR95M55**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

19'' Fixed Chassis

PLA PHD

Installation: For heights from 750 to 1500 mm, the installation requires ordering one set of two matching uprights. If a chassis is installed in an enclosure with a greater height, it is necessary to use the suitable uprights for the size of the enclosure


- Very sturdy 19" metal chassis, designed for installation in enclosures with a width of 750 and 1250 mm.
  In enclosures with a width of 1250 mm, the chassis is installed in the 750-mm part with an intermediate support, ref. **NSYSBPLA**.
- These chassis can be used as partial mounting plates in enclosures with a height greater than the nominal height.
- Incompatible with the internal doors and the step slides.
- Fixed chassis made up of two uprights with fixings
- Material: Galvanized steel
- Color: RAL 7035 gray
- Maximum load: 3 kg per unit




NSYBRF8PLAG

Characteristics	Compatibility	Height (mm)	Width (mm)	# of units	References
19" fixed chassis	PLA	500	750	8	**NSYBRF8PLAG**
19" fixed chassis	PLA, PHD	750	750	12	**NSYBRF12PLAG**
19" fixed chassis	PLA, PHD	1000	750	17	**NSYBRF17PLAG**
19" fixed chassis	PLA, PHD	1250	750	21	**NSYBRF21PLAG**
19" fixed chassis	PLA, PHD	1500	750	26	**NSYBRF26PLAG**
19" fixed chassis	PLA, PHD	2000	750	2 x 17	2 x **NSYBRF17PLAG** + **NSYPTZ4**
Set of two uprights	PLA, PHD	750	750	12	**NSYSPLA75**
Set of two uprights	PLA, PHD	1000	750	17	**NSYSPLA100**
Set of two uprights	PLA, PHD	1250	750	21	**NSYSPLA125**
Set of two uprights	PLA, PHD	1500	750	26	**NSYSPLA150***
Set of two uprights	PLA, PHD	2000	750	2 x 17	2 x **NSYSPLA100**

* Not compatible with **NSYCAAPVHD**.





6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Internal Doors

Internal Door

CRN S3D S3X S3HD



NSYPIN43




NSYPIN43


- Locking with 3-mm double-bar lock.
- The internal door can be installed directly on the front face of the enclosure or on the step slides (not supplied as standard).
- To mount an internal door and a mounting plate at the same time on the step slides is possible as standard.
- Incompatible with the installation of the door stop and door switch.
- For further details, please consult us.
- Material: Steel
- Color: RAL 7035 gray
- Maximum load: 30 kg/m²

Note:
(1) Equipped with welded vertical profiles in order to facilitate cable management.

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Internal door	CRN, S3D, S3X, S3HD	400	300	**NSYPIN43**
Internal door	CRN, S3D, S3X, S3HD	500	400	**NSYPIN54**
Internal door	CRN, S3D, S3X, S3HD	600	400	**NSYPIN64**
Internal door	CRN, S3D, S3X, S3HD	700	500	**NSYPIN75**
Internal door	CRN, S3D, S3X, S3HD	800	600	**NSYPIN86** (1)
Internal door	CRN, S3D, S3X, S3HD	1000	600	**NSYPIN106** (1)
Internal door	CRN, S3D, S3X, S3HD	1000	800	**NSYPIN108** (1)
Internal door	CRN, S3D, S3X	1200	600	**NSYPIN126**
Internal door	CRN, S3D, S3X	1200	800	**NSYPIN128** (1)



1 **Installation on the front of the enclosure or**
2 **Installation on step slides**
3 Dimension resulting from installation on step slides: B-83 mm.
Dimension resulting from direct installation (without step slides): B-91 mm



1 **NSYPIN** internal door fixed directly to the enclosure.


2 **NSYPIN** internal door fixed to the adjustable **NSYSDCR●●** support. In this case, internal door and mounting plate can be adjusted in depth.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Internal Door

PLM

- Reversible door.
- Grid pattern with a pitch of 25 mm for easier marking before drilling.
- Closes with 2 double-bar locks.
- Door handle.
- Steel internal door, without grid pattern and locking by a screw, for enclosures ref. **NSYPLM3025G**.
- Incompatible with the modular distribution chassis.
- Material: Polyester reinforced with fiberglass, self-extinguishing
- Color: RAL 7035 gray



Supply:
Delivered with fixings and brass inserts


NSYPA3025PLMG


Characteristics	Compatibility	Height (mm)	Width (mm)	A (mm)	B (mm)	C (mm)	D Plain door (mm)	D Transp. door (mm)	Reference
Internal door	PLM	308	255	248	165	62	76	71	**NSYPA3025PLMG**
Internal door	PLM	430	330	315	205	152	26	21	**NSYPAP43G**
Internal door	PLM	530	430	415	305	152	26	21	**NSYPAP54G**
Internal door	PLM	645	435	515	305	194	32	27	**NSYPAP64G**
Internal door	PLM	745	535	615	405	244	32	27	**NSYPAP75G**
Internal door	PLM	845	635	715	505	244	32	27	**NSYPAP86G**
Internal door	PLM	1055	850	850	650	269	37	32	**NSYPAP108G**


PLA **PHD**


PB502906_22_nb


PB502912_25_nb

- Designed for direct installation in enclosures with sealed bottom part. In the enclosures with the bottom part open, installation can be Performed by ordering the necessary adapter plates, ref. **NSYPTZ●●●**.
- Two depthwise mounting positions (two positions for depthwise installation) according to the chosen M8 impressions, on the top and bottom parts of the enclosure, for fixing.
- Lock with 5-mm double-bar inserts.
- Not compatible with: Modular distribution chassis, 19" chassis, cable entry plate and door retainer, ref. **NSYRETPLAU**.
- Material: Aluminum
- Color: RAL 7035 gray





1 Two positions for depthwise installation
2 The 2nd position moves the position of the internal door back by 25 mm

Supply:
Delivered with M8 brass inserts and fixings

Characteristics	Compatibility	Dimensions		Internal door dimensions		References
		Height (mm)	Width (mm)	D (mm)	E (mm)	
Internal door	PLA, PHD	500	500	398	398	**NSYPAPLA55G**
Internal door	PLA	500	750	398	648	**NSYPAPLA57G**
Internal door	PLA	500	1000	398	796 (2 x 398)	2 x **NSYPAPLA55G**
Internal door	PLA	500	1250	398	1046 (398 + 648)	**NSYPAPLA55G** + **NSYPAPLA57G**
Internal door	PLA, PHD	750	500	648	398	**NSYPAPLA75G**
Internal door	PLA, PHD	750	750	648	648	**NSYPAPLA77G**
Internal door	PLA	750	1000	648	796 (2 x 398)	2 x **NSYPAPLA75G**
Internal door	PLA	750	1250	648	1046 (398 + 648)	**NSYPAPLA75G** + **NSYPAPLA77G**
Internal door	PLA, PHD	1000	500	898	398	**NSYPAPLA105G**
Internal door	PLA, PHD	1000	750	898	648	**NSYPAPLA107G**
Internal door	PLA	1000	1000	898	796 (2 x 398)	2 x **NSYPAPLA105G**
Internal door	PLA	1000	1250	898	1046 (398 + 648)	**NSYPAPLA105G** + **NSYPAPLA107G**
Internal door	PLA, PHD	1250	500	1148	398	**NSYPAPLA125G**
Internal door	PLA, PHD	1250	750	1148	648	**NSYPAPLA127G**
Internal door	PLA	1250	1000	1148	796 (2 x 398)	2 x **NSYPAPLA125G**
Internal door	PLA, PHD	1250	1250	1148	1046 (398 + 648)	**NSYPAPLA125G** + **NSYPAPLA127G**
Internal door	PLA	1500	500	1398	398	**NSYPAPLA155G**
Internal door	PLA, PHD	1500	750	1398	648	**NSYPAPLA157G**
Internal door	PLA	1500	1000	1398	796 (2 x 398)	2 x **NSYPAPLA155G**
Internal door	PLA, PHD	1500	1250	1398	1046 (398 + 648)	**NSYPAPLA155G** + **NSYPAPLA157G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Internal Doors


Internal Door

SM | SFN | SMX | SFX | SFN HD



NSYID166

- Door for additional protection. Helps prevent the switchgear from being manipulated by unauthorised personnel.
- Allows the installation of switchgear mounted directly on the door.
- Mounting on the top and bottom frame of the enclosure.
- Depth adjustable with a pitch of 25 mm, from the first fixing point.
- Opening to right or left, with two locks, 3-mm double-bar, with central handle.
- Reinforcement frames on the rear, cut-outs with a 25 mm pitch, for equipping the door.
- Maximum acceptable load: 15 kg.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray



Comment:
For dimensions see page 68

Supply:
One internal door and fixing elements



NSYID166

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Internal door	SFN, SM	1600	600	**NSYID166**
Internal door	SFN, SM, SMX	1600	800	**NSYID168**
Internal door	SFN, SM, SMX, SFX, SFN HD	1800	600	**NSYID186**
Internal door	SFN, SM, SMX, SFX, SFN HD	1800	800	**NSYID188**
Internal door	SFN, SM	1800	1000	**NSYID1810**
Internal door	SFN, SM, SFX, SFN HD	2000	600	**NSYID206**
Internal door	SFN, SM, SMX, SFX, SFN HD	2000	800	**NSYID208**
Internal door	SFN, SM, SMX, SFX	2000	1000	**NSYID2010**

Partial Doors

NOTICE

PROTECTION RATING DECREASE

Enclosure ingress protection rating decreases to IP54 according to IEC 60529 when installing any type of partial door.

Failure to follow these instructions can result in equipment damage.

Front Fix Panel for Modularity

SFN | MCC

- Top and bottom fix panel to obtain modularity required to install partial doors.
- It is needed to purchase **NSYMICN6** and **NSYMICN8**.
- Height 100 mm fixed panels are delivered as standard for PanelSeT SFN compartmentalized enclosures for Motor Control Centers.
- Option to order it separately for PanelSeT SFN framework in kit supply.
- Available in 2 heights (mm).
- Color: RAL 7035 gray.
- Finish: Epoxy-polyester powder.

Supply:
2 crossbars with 2 front fix panels



NSYMFP2M6

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Front Fix panel for modularity	SFN, MCC	100	600	**NSYMFP2M6**
Front Fix panel for modularity	SFN, MCC	250	600	**NSYMFP5M6**
Front Fix panel for modularity	SFN, MCC	100	800	**NSYMFP2M8**
Front Fix panel for modularity	SFN, MCC	250	800	**NSYMFP5M8**

Frontal Transparent Partial Doors

SFN | MCC

- Glazed (Securit glass) partial door with lock 5-mm double-bar insert.
- They are fixed to the uprights of the framework by means of hinges.
- Opening to right or left.
- 1 or 2 locking points according different heights.
- Available in following heights (mm).
- Color: RAL 7035 gray.
- Finish: Epoxy-polyester powder.



NSYMPD46T

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Frontal Transparent partial doors	SFN, MCC	400	600	**NSYMPD46T**
Frontal Transparent partial doors	SFN, MCC	600	600	**NSYMPD66T**
Frontal Transparent partial doors	SFN, MCC	800	600	**NSYMPD86T**
Frontal Transparent partial doors	SFN, MCC	1000	600	**NSYMPD106T**
Frontal Transparent partial doors	SFN, MCC	400	800	**NSYMPD48T**
Frontal Transparent partial doors	SFN, MCC	600	800	**NSYMPD68T**
Frontal Transparent partial doors	SFN, MCC	800	800	**NSYMPD88T**
Frontal Transparent partial doors	SFN, MCC	1000	800	**NSYMPD108T**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Frontal Partial Doors

SFN MCC

- Plain partial door with lock 5-mm double-bar insert.
- They are fixed to the uprights of the framework by means of hinges.
- Drilling template for uprights ref. **NSYMDT** (only one drilling template required per order).
- Opening to right or left.
- 1, 2 or 4 locking points depending on height.
- Option to replace locking insert.
- Available in following heights (mm).
- Color: RAL 7035 gray.
- Finish: Epoxy-polyester powder.


NSYMPD3M6

Characteristics	Compatibility	Height (mm)	Width (mm)	References
Frontal partial door	SFN, MCC	150	600	**NSYMPD3M6**
Frontal partial door	SFN, MCC	200	600	**NSYMPD4M6**
Frontal partial door	SFN, MCC	250	600	**NSYMPD5M6**
Frontal partial door	SFN, MCC	300	600	**NSYMPD6M6**
Frontal partial door	SFN, MCC	400	600	**NSYMPD8M6**
Frontal partial door	SFN, MCC	450	600	**NSYMPD9M6**
Frontal partial door	SFN, MCC	600	600	**NSYMPD12M6**
Frontal partial door	SFN, MCC	800	600	**NSYMPD16M6**
Frontal partial door	SFN, MCC	900	600	**NSYMPD18M6**
Frontal partial door	SFN, MCC	1000	600	**NSYMPD20M6**
Frontal partial door	SFN, MCC	1200	600	**NSYMPD24M6**
Frontal partial door	SFN, MCC	150	800	**NSYMPD3M8**
Frontal partial door	SFN, MCC	200	800	**NSYMPD4M8**
Frontal partial door	SFN, MCC	250	800	**NSYMPD5M8**
Frontal partial door	SFN, MCC	300	800	**NSYMPD6M8**
Frontal partial door	SFN, MCC	400	800	**NSYMPD8M8**
Frontal partial door	SFN, MCC	450	800	**NSYMPD9M8**
Frontal partial door	SFN, MCC	600	800	**NSYMPD12M8**
Frontal partial door	SFN, MCC	800	800	**NSYMPD16M8**
Frontal partial door	SFN, MCC	900	800	**NSYMPD18M8**
Frontal partial door	SFN, MCC	1000	800	**NSYMPD20M8**
Frontal partial door	SFN, MCC	1200	800	**NSYMPD24M8**

Intermediate Crossbar

SFN MCC

- Mounted between partial doors or between doors and control desk, helping guarantee IP54 according to IEC 60529.
- Crossbar with direct fixing to the structure.
- Available in 2 widths (mm).
- Color: RAL 7035 gray.
- Finish: Epoxy-polyester powder.


NSYMIC6


PB500639_17_nb

Supply:
2 crossbars with fixing elements.

Characteristics	Compatibility	Width (mm)	References
PanelSeT SFN-Intermediate Crossbar	SFN, MCC	600	**NSYMICN6**
PanelSeT SFN-Intermediate Crossbar	SFN, MCC	800	**NSYMICN8**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Side Doors

Side Door

SFN SFN IT


PB124779

- Door for the side of the enclosure, can replace the panels.
- Installation directly on the structure of the enclosure, opening 120°.
- Lock with handle and 5-mm double-bar insert. 4 locking points.
- Reinforcement frame, cut-out with a pitch of 25 mm.
- Opening to right or left.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray

Supply:
One side door, four hinges, four catches, bottom trim and handle lock


NSYSFND188

Characteristics	Compatibility	Height (mm)	Depth (mm)	References
Side door	SFN, SFN IT	1200	600	**NSYSFND126**
Side door	SFN, SFN IT	1200	800	**NSYSFND128**
Side door	SFN, SFN IT	1400	600	**NSYSFND146**
Side door	SFN, SFN IT	1400	800	**NSYSFND148**
Side door	SFN, SFN IT	1600	600	**NSYSFND166**
Side door	SFN, SFN IT	1600	800	**NSYSFND168**
Side door	SFN, SFN IT	1800	400	**NSYSFND184**
Side door	SFN, SFN IT	1800	500	**NSYSFND185**
Side door	SFN, SFN IT	1800	600	**NSYSFND186**
Side door	SFN, SFN IT	1800	800	**NSYSFND188**
Side door	SFN, SFN IT	2000	400	**NSYSFND204**
Side door	SFN, SFN IT	2000	500	**NSYSFND205**
Side door	SFN, SFN IT	2000	600	**NSYSFND206**
Side door	SFN, SFN IT	2000	800	**NSYSFND208**
Side door	SFN, SFN IT	2200	400	**NSYSFND224**
Side door	SFN, SFN IT	2200	500	**NSYSFND225**
Side door	SFN, SFN IT	2200	600	**NSYSFND226**
Side door	SFN, SFN IT	2200	800	**NSYSFND228**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Hinges

S3D


NSYAEDH180S3D


NSYAEDH120S3D



- Captive pin, indexed by a spring.
- Material: Zamak body for ref. **NSYAEDH180S3D**, treated sheet steel body for ref. **NSYAEDH120S3D**, aluminum pin
- Maximum load: For the 180° hinge, the maximum admissible load on the door is 20 kg/m²
- For the 120° hinge, the maximum admissible load on the door is 50 kg/m²

Supply:
Set of 1 hinge, delivered with fixings

Characteristics	Compatibility	References
180° hinge	S3D	**NSYAEDH180S3D**
Standard 120° hinge	S3D	**NSYAEDH120S3D**

SBM


NSYAEDHSB

- The hinges allow the cover to be opened by more than 180°.
- They can be installed on all covers of the range.
- Ingress protection rating: IP66 according to IEC 60529

Installation:

- The box must be drilled before installing the 2 or 3 hinges on the body.
- 3 hinges are required for boxes of width more than 500 mm
- A specific mark on the body helps to locate where the hole should be drilled
- Maximum load: 30 kg/m² on the hinged cover
- Same reference for all enclosure dimensions

Supply:
Set of 6 hinges delivers with fixing hardware

Characteristics	Compatibility	References
Hinges	SBM	**NSYAEDHSB**

SM SFN MCC SFN IT




- Hinge with opening of 180°.
- Intended to replace the 120° hinges installed as standard.
- They are compatible with the transparent door and can be installed even with enclosure suites.
- Maximum load: 60 kg on the door
- Material: galvanized steel and painting
- Finish: Painted RAL 9005 black
- UL-certified (cULus):
  - SFN: Types 1, 3R, 12 according UL50E
  - SM: Types 1, 2, 3R, 5 and 13 for single-door enclosures

Supply:
4 hinges

Characteristics	Compatibility	References
180° hinge	SM, SFN, MCC, SFN IT	**NSYSH180NC**

TBS TBP


NSYAEDH20TB



- The hinges can be adapted to all covers with a height of 20 and 40 mm with dimensions from 138 x 93 mm.
- The hinge allows the lid to open fully to 200°.
- Ingress protection rating: IP66 according to IEC 60529
- Installation: The hinge does not require any machining and is installed
- Easily even with the box already equipped
- Maximum load: Hinged cover: 10 kg/m²

Supply:
The hinges (2 per set) are delivered with the fixings, minor pack 1

Characteristics	Compatibility	Height of the lid (mm)	References
Set of 2 hinges	TBS, TBP	20	**NSYAEDH20TB**
Set of 2 hinges	TBS, TBP	40	**NSYAEDH40TB**

PLS


NSYBE27G


NSYBL27

Comment:
IP level cannot be guaranteed due to type of application and installation

- To open the door to 180°.
- External Hinges material: Plastic
- Internal Hinges material: Brass

Supply:
Set of 2 hinges

Characteristics	Compatibility	References
External hinges	PLS	**NSYBE27G**
Internal hinges	PLS	**NSYBL27**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Door Accessories

Closing

Lock for Panel**SeT** CRN Enclosure Three-Point Lock


- Standard 5-mm double-bar lock for CRN for heights from 1200 mm and widths from 1000 mm.
- Operation using: Key **NSYLDB5** (according to DIN 43668)





Handle Locks for Transformation of the Standard Lock to Standardized Variations in Enclosures with Three-Point Locks

CRN S3X




NSYTSML


- Protection rating: IP66
- Compatible with PanelSeT S3X double-door enclosures
- Compatible with large-sized CRN enclosures, defined by a height H ≥ 1200 mm or a width L ≥ 1000 mm
- Compatible with double door S3X enclosures


Characteristics	Compatibility	References
Handle lock	CRN, S3X	**NSYTSML**
Handle lock operated using key 405 (included)	CRN, S3X	**NSYTL405SML**


Simple lock for Panel**SeT** CRN Enclosure

- **NSYCDB3** 3 mm Ø standard double-bar lock for heights below 1200 mmand widths below 1000 mm.
- By fixing the wing nut to the lock, the double-bar lock becomes a handle lock.
- Operation using:
  wing key ref.: **NSYDBP**
  key **NSYLDB5** (according to DIN 43668)
- **NSYTDBCRN** delivered with 1 metal key









Complete Locks

CRN


NSYCL405CRN


NSYCLL405CRN

Characteristics	Compatibility	References
Complete manual handle lock, operated with key 405	CRN	**NSYCL405CRN**
Complete manual handle lock, operated with key 220	CRN	**NSYCL220CRN**
Complete metal lock, operated with key 405E	CRN	**NSYCLL405CRN**
Lock TJIS	CRN	**NSYTJIS**

Double-Bar Lock for Polyester

PLM

Characteristics	Compatibility	References
Double-bar lock for PLM enclosures from 430 to 847 mm height with new aspect	PLM	**NSYCDBPLMN**
Double-bar lock for PLM enclosure of 308 mm height with new aspect	PLM	**NSYCDB3N**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Standard Locks

S3D

- PanelSeT S3D wall-mounted enclosures are supplied with a 3-mm double-bar lock as **standard**.
- Spare lock: Order ref. **NSYAEDLS3DRL** (escutcheon + cam + washer).
- Large range of standardised inserts covering all the most common needs.
- Installation and removal with a single screw.
- Material: Zamack + polyamide
- Ingress protection rating: IP66 according to IEC 60529

Supply:
Delivered with 1 plastic key


NSYAEDLS6S3D

Characteristics	Compatibility	References
7 mm square	S3D	**NSYAEDLS7S3D**
8 mm square	S3D	**NSYAEDLS8S3D**
3-mm double-bar	S3D	**NSYAEDLB3S3D**
5-mm double-bar	S3D	**NSYAEDLB5S3D**
CNOMO 6.5 mm triangular	S3D	**NSYAEDLT6S3D**
8 mm triangular	S3D	**NSYAEDLT8S3D**

Barrel DIN Kit

S3D

- Mounting of half-cylinder according to DIN 18252 (EN1303). Cam can be turned every 45°.
- Easy mounting instead of standard lock.
- Compatible with PLM barrels offer. See page 563. (Example: **NSYTL1242EME**).
- Material: Polyamide GF
- Ingress protection rating: IP66 according to IEC 60529

Supply:
Delivered with metal cam 1 point and metal cam 3 points


NSYAEDDINS3D

Characteristics	Compatibility	References
Barrel DIN kit	S3D	**NSYAEDDINS3D**

Double-Bar 3 mm Metal Lock

S3D

- Easy mounting instead of standard lock.
- Material: Zamak
- Ingress protection rating: IP66 according to IEC 60529

Supply:
Delivered with metal cam 1 point and metal cam 3 points


NSYAEDLB3MS3D

Characteristics	Compatibility	References
Double-bar 3 mm metal lock	S3D	**NSYAEDLB3MS3D**

Metal Cam Kit 1 Point and 3 Points

S3D

- To adapt other locks.
- Material: Zinc-coated metal

Supply:
Delivered with metal cam 1 point and metal cam 3 points




NSYAEDLMETS3D

Characteristics	Compatibility	References
Metal cam kit 1 point and 3 points	S3D	**NSYAEDLMETS3D**


Flat escutcheon lock

SM SFN MCC SFN IT




NSYSFLOCKT7

- Optional flat escutcheon lock. Replaces the handle lock.
- Easy to change the opening direction of the door, right/ left.
- Option of changing the turning direction of the insert.
- Handle material: Polyamide 6 with 30% fiberglass
- Color: RAL 9005
- Mechanical protection rating: IK10 according to IEC 62262
- Fire resistance: 650 °C



Supply:
Flat lock, shape insert, key and fixing elements

Characteristics	Compatibility	References
Flat lock + 7 mm triangular insert	SM, SFN, MCC, SFN IT	**NSYSFLOCKT7**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Closing

Standard Handle

S3D


NSYAEDLS3DKDB3


- Operating handle delivered with the enclosure.
- It can be attached to the locking system by means of a fixing element.
- It can also be used to loosen the caps helping protect the studs when painting.

Characteristics	Compatibility	References
Standard handle	S3D	**NSYAEDLS3DKDB3**

Standard Handles with Key

S3D

- Attractive and ergonomic bi-material handle.
- Large range of barrels covering all the most common needs.
- The installation of the standard handle does not require the escutcheon to be removed.
- Locks may only be operated using the supplied keys.
- Delivery: Delivered with 2 keys




NSYAEDL1242S3D

Characteristics	Compatibility	References
405	S3D	**NSYAEDL405S3D**
421	S3D	**NSYAEDL421S3D**
455	S3D	**NSYAEDL455S3D**
610E	S3D	**NSYAEDL610S3D**
1242	S3D	**NSYAEDL1242S3D**
2124E	S3D	**NSYAEDL2124S3D**
2131A	S3D	**NSYAEDL2131S3D**
2132A	S3D	**NSYAEDL2132S3D**
2241A	S3D	**NSYAEDL2241S3D**
2331A	S3D	**NSYAEDL2331S3D**
2432E	S3D	**NSYAEDL2432S3D**
2433A	S3D	**NSYAEDL2433S3D**
3113A	S3D	**NSYAEDL3113S3D**
3123E	S3D	**NSYAEDL3123S3D**
3131A	S3D	**NSYAEDL3131AS3D**
3132A	S3D	**NSYAEDL3132S3D**
3432E	S3D	**NSYAEDL3432S3D**
3524E	S3D	**NSYAEDL3524S3D**
4324E	S3D	**NSYAEDL4324S3D**
5124A	S3D	**NSYAEDL5124S3D**

Other Locks with Keys

S3D

- Material: Zamak
- Ingress protection rating: IP66 (IEC 60529)

Supply:
Delivered with metal cam 1 point
and metal cam 3 points


NSYAEDLEDF13S3D

Characteristics	Compatibility	References
EDF 900	S3D	**NSYAEDLEDF9S3D**
EDF 1300	S3D	**NSYAEDLEDF13S3D**
EDF 1400	S3D	**NSYAEDLEDF14S3D**

Padlocks

S3D S3HD


S3D 6G


NSYAEDLPADS3D

For NSYAEDLPADS3D
- Easy mounting instead of the standard lock.
- Padlockable, diameter 8 mm
- Material: Zamak
- Ingress protection rating: IP66 (IEC 60529)

For NSYAEDLPADS3DHD
- Easy mounting instead of the standard lock.
- Material: Zamak
- Finish: Anti-corrosive painting

For NSYAEDLPADS3DK3
- Securing of enclosure access.
- Material: White galvanized steel




Supply:
NSYAEDLPADS3D: Delivered with metal key
NSYAEDLPADS3DHD: Delivered with 3-mm double-bar metal key

Characteristics	Compatibility	References
Padlock	S3D	**NSYAEDLPADS3D**
Heavy-Duty padlockable double lock	S3D, S3HD	**NSYAEDLPADS3DHD**
Padlocking lug	S3D, S3D 6G	**NSYAEDLPADS3DK3**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

1-Point-Lock Options

S3X




NSYSTDNCSX


NSYSTDCX2H


NSYCBXHCRN


NSYCL610CSX

- Protection rating: IP66
- For locks for double-door enclosures please contact us

Characteristics	Compatibility	Type	Material	References
Double-bar lock	S3X	Escutcheon with insert, 3 mm	Chrome-plated zamak	**NSYSTDNCSX**
Insert	S3X	Triangular, 8 mm	304L stainless-steel	**NSYTT8CSX**
Insert	S3X	Square, 7 mm	304L stainless-steel	**NSYTC7CSX**
Insert	S3X	Square, 6 mm	304L stainless-steel	**NSYTC6CSX**
Round lock	S3X	Round, 3 mm (spare)	Chrome-plated zamak	**NSYSTDCSX**
Round lock	S3X	Round, 3 mm	304L stainless-steel	**NSYSTDCXH**
Round lock	S3X	Round	316 stainless-steel, please contact us for availability	**NSYSTDCX2H**
Handle lock	S3X	Padlock	316 stainless-steel, please contact us for availability	**NSYCBXHCRN**
Handle lock	S3X	1242E	Chrome-plated zamak	**NSYCL1242ECSX**
Handle lock	S3X	405	Polyamide	**NSYCL405CSX**
Handle lock	S3X	610	Chromed zamak	**NSYCL610CSX**

Padlocks

CRN PLM


NSYKPLM NSYCBCCRN

Characteristics	Compatibility	References
Padlock device Ø 8 mm, stainless-steel	PLM	**NSYKPLM**
Padlock Ø 7.5 mm / Ø 10 mm	CRN	**NSYCBCCRN**

Padlocking Accessories

CRN


NSYBCPL

- Padlocking system, positioned around the long rectangular escutcheon of the enclosures, to block access to the lock, for a Ø 9 mm padlock.

Characteristics	Compatibility	References
Padlock device for large rectangular escucheon	CRN	**NSYBCPL**

CRN S3X SMX SFX PLM


NSYBCME

- Padlocking system, to block access to the retractable handle, for a Ø 9 mm padlock
- Compatible with large-sized CRN enclosures, defined by a height H ≥ 1200 mm or a width L ≥ 1000 mm
- Compatible with double door S3X enclosures

Characteristics	Compatibility	References
Padlocking device for retractable handle	CRN, S3X, SMX, SFX, PLM	**NSYBCME**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Closing

Closing Locks

PLS


NSYCL27M


NSYCL27L405

- Option of installing a side lock on the opposite side to where the hinges are installed
- Ingress protection rating: IP43

Characteristics	Compatibility	Tool	References
Double-bar side lock and handle	PLS	NSYDBP	**NSYCL27M**
Side lock with key 405	PLS	Key 405	**NSYCL27L405**

Lock and key


PLM


NSYTL405PLM

Characteristics	Compatibility	References
Lock and key 405	PLM	**NSYTL405PLM**
Lock and key 220	PLM	**NSYTL220PLM**

Locks and Inserts for Enclosures NSYPLM108/T

PLM



NSYTDB5PL

- Options to convert the insert
- The standard insert can be replaced with other shaped inserts according to the following table.

Characteristics	Compatibility	References
Double-bar insert	PLM	**NSYTDB5PL**

Locks and Inserts for Enclosures NSYPLM108/T

PLM



NSYTEDB5PL

- Options to convert to a retractable handle
- The escutcheon and rosette assembly can be replaced with a lock with retractable handle equipped with inserts or barrels according to the following table.

Characteristics	Compatibility	References
5-mm double-bar	PLM	**NSYTEDB5PL**
8 mm triangle insert	PLM	**NSYTET8PL**
Lock key 1242 E	PLM	**NSYTEL1242EPL**
Barrel and key 405	PLM	**NSYTEL405PL**
JIS key and barrel	PLM	**NSYTELJISPL**
Manual	PLM	**NSYTEMPL**

Options to Convert the Locks to Double-Bar Inserts NSYPLM43G to NSYPLM86G

PLM


NSYTHL1242EPLM

- Replacement for locking handle with cylindrical barrel, delivered with all the parts required to change the lock.

Characteristics	Compatibility	References
Key 1242 E	PLM	**NSYTHL1242EPLM**
Key 405	PLM	**NSYTHL405PLM**
Key 421	PLM	**NSYTHL421PLM**
Key 455	PLM	**NSYTHL455PLM**
Key 2433 A	PLM	**NSYTHL2433APLM**
Key 3113 A	PLM	**NSYTHL3113APLM**
Manual	PLM	**NSYTHPLM**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Transformation of the Standard Lock to a Retractable Three-Point Lock with Various Types of Inserts

CRN SFN IT

- Compatible with large-sized CRN enclosures, defined by a height H ≥ 1200 mm or a width L ≥ 1000 mm
- Compatible with double door S3X enclosures
- For SFN IT: compatible only with Swing Rack


NSYTEL405ML

Characteristics	Compatibility	Key references	References
Key operated bar lock	CRN, SFN IT	NSYLDB5	**NSYTEDB5ML**
Lock operated with key type 405	CRN		**NSYTEL405ML**

Handle for Shaped Inserts and Cylindrical Barrels

SM SFN MCC SFN IT


NSYSFNHS1

- Easy to change the opening direction of the door, right/left.
- Space reserved for enclosure identification, 21 x 27 mm, protected by a label frame.
- Handle material: Polyamide 6 with 30% fiberglass
- Color: RAL 9005
- Mechanical protection rating: IK10 according to IEC 62262
- Fire resistance: 650 °C

Supply:
Standard handle and fixing elements (insert not included)

Characteristics	Compatibility	References
Handle for shaped inserts and cylindrical barrels	SM, SFN, MCC, SFN IT	**NSYSFNHS1**

Handles for Insert Types DIN, KABA, ASSA, Insert Handle

SM SFN MCC SFN IT


NSYSFHD2

- The inserts are easily and quickly mounted without any screws and allow the installation of profiled DIN, KABA and ASSA locks.
- To install shaped inserts or cylindrical barrels, it is necessary to add adapter ref. **NSYLADP**.
- Easy to change the opening direction of the door, right/left.
- Space reserved for enclosure identification, 21 x 27 mm, protected by a label frame.
- Handle material: Polyamide 6 with fiberglass
- Color: RAL 9005 black
- Mechanical protection rating: IK10 according to IEC 62262
- Glow wire resistance: 650 °C

Supply:
One handle for DIN, KABA and ASSA inserts and fixing elements (insert not included)

Characteristics	Compatibility	References
Insert handle	SM, SFN, MCC, SFN IT	**NSYSFHD2**

Handles for Insert Types DIN, KABA, ASSA, Double-Insert Handle

SM SFN MCC SFN IT


NSYSFHD3

- The double-insert handle can perform the "AND" and "OR" functions (are supplied with the handle).
  - "AND" function: One insert blocks the activation of the other insert.
  - "OR" function: Either insert can release the handle.
- Easy to change the opening direction of the door, right/left.
- Space reserved for enclosure identification, 21 x 27 mm, protected by a label frame.
- To install shaped inserts or cylindrical barrels, it is necessary to add adapter ref. **NSYLADP**.
- Handle material: Polyamide 6 with fiberglass
- Color: RAL 9005 black
- Mechanical protection rating: IK10 according to IEC 62262
- Glow wire resistance: 650 °C.

Supply:
One handle for DIN, KABA and ASSA inserts and fixing elements (insert not included)

Characteristics	Compatibility	References
Double-insert handle	SM, SFN, MCC, SFN IT	**NSYSFHD3**

Padlock Locking

Coming soon

SM SFN MCC SFN IT


NSYBLKHN123

- Padlock locking system, for installation in all the handles of the PanelSeT SFN and PanelSeT SM enclosures.
- Screw with 7.5 mm drill hole.

Supply:
One cut-out handle, screw for padlock and screw fixing screw

Characteristics	Compatibility	References
Padlock locking	SM, SFN, MCC, SFN IT	**NSYBLKHN123**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories


Closing

Push-button handle with 3524E key

SM | SFN | MCC | SFN IT


NSYSFHPB

- Push-button handle with 3524E key for Spacial SF and Spacial SM enclosures.
- Locking and unlocking by key and opening by pushing the insert.
- Handle material: Polyamide 6 with 30% fiberglass
- Color: RAL 9005
- Fire resistant: 650 °C





Supply:
Push-button handle, two 3524E keys and fixing elements (insert included)


Characteristics	Compatibility	References
Spacial SF/SM Push-button handle with 3524E key	SM, SFN, MCC, SFN IT	**NSYSFHPB**

Lock System: DIN, KABA and ASSA

SM | SFN | PLA | SD | MCC | SFN IT




NSYINDIN2


NSYIN1242E2

Comment:
NSYINKBA2: Adapter for receiving the KABA8, KABA20 and KABA start cylinders.

Characteristics	Compatibility	References
Adapter for DIN cylinder	SM, SFN, PLA, MCC, SFN IT, SD	**NSYINDIN2**
Adapter for KABA cylinder	SM, SFN, MCC, SFN IT	**NSYINKBA2**
Adapter for ASSA cylinder	SM, SFN, MCC, SFN IT	**NSYINASSA2**
1242E key lock	SM, SFN, PLA, MCC, SFN IT, SD	**NSYIN1242E2**
Reinforced key lock	SM, SFN, PLA, MCC, SFN IT, SD	**NSYINKR2**
JIS key lock	SM, SFN, PLA, MCC, SFN IT, SD	**NSYINKJIS2**
FAC key lock	SM, SFN, PLA, MCC, SFN IT, SD	**NSYINKFAC2**

Options for Converting the Handle Lock

PLA | PHD


NSYCBCMPLAG

- Changing the handle for a handle including a padlocking device (Ø 10 mm) allowing the handle to be locked. The handle is delivered without barrel or insert block.

Characteristics	Compatibility	References
Options for converting the handle lock	PLA, PHD	**NSYCBCMPLAG**

Options for Converting the Handle Lock

PLA


NSYEBMPLAG

- Spare handle lock without barrel or insert blocks.
  The insert or barrel are to be chosen from the option table.

Characteristics	Compatibility	References
Options for converting the handle lock	PLA	**NSYEBMPLAG**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Inserts

CRN PLM


NSYTDBCRN


NSYTC6CRN


NSYTT6CRN


NSYTC7CRN



NSYTC8CRN


NSYTT8CRN

Characteristics	Compatibility	Key references	References
3-mm double-bar	CRN, PLM	NSYLDB5	**NSYTDBCRN**
6 mm square	CRN, PLM	NSYLC7	**NSYTC6CRN**
7 mm square	CRN, PLM	NSYLC7	**NSYTC7CRN**
8 mm square	CRN, PLM	NSYLC8	**NSYTC8CRN**
6.5 mm triangular	CRN, PLM	NSYLT8	**NSYTT6CRN**
8 mm triangular	CRN, PLM	NSYLT8	**NSYTT8CRN**
Screw driver lock	CRN, PLM		**NSYAEDLSD**

Shape Inserts

SM SFN PLA SD



NSYINS61

Characteristics	Compatibility	References
6 mm square insert	SM, SFN, PLA, SD	**NSYINS61**
7 mm square insert	SM, SFN, PLA, SD	**NSYINS71**
8 mm square insert	SM, SFN, PLA, SD	**NSYINS81**
6.5 mm triangular insert	SM, SFN, PLA, SD	**NSYINT61**
7 mm triangular insert	SM, SFN, PLA, SD	**NSYINT71**
8 mm triangular insert	SM, SFN, PLA, SD	**NSYINT81**
9 mm triangular insert	SM, SFN, PLA, SD	**NSYINT91**
3-mm double-bar insert	SM, SFN, PLA, SD	**NSYINDB31**
5-mm double-bar insert	SM, SFN, PLA, SD	**NSYINDB51**

Barrels

SM SFN PLA SD


- The enclosures PanelSeT SMX and SFX are delivered as standard with a retractable handle made from
- Painted zamak with 5-mm double-bar insert, ref. **NSYMCSX**
- Standard inserts can be replaced by shaped inserts or barrels according the following table.
- Conversion of the standard insert (barrel for key 1242E, ref. **NSYTL1242EME**) to other shaped
- Inserts or barrels according to the following table


NSYIN405E1

Characteristics	Compatibility	References
405E key lock	SM, SFN, PLA, SD	**NSYIN405E1**
421E key lock	SM, SFN, PLA, SD	**NSYIN421E1**
455 key lock	SM, SFN, PLA, SD	**NSYIN4551**
1242E key lock	SM, SFN, PLA, SD	**NSYIN1242E1**
2131A key lock	SM, SFN, PLA, SD	**NSYIN2131A1**
2132A key lock	SM, SFN, PLA, SD	**NSYIN2132A1**
2433A key lock	SM, SFN, PLA, SD	**NSYIN2433A1**
2452E key lock	SM, SFN, PLA, SD	**NSYIN2452E1**
3113A key lock	SM, SFN, PLA, SD	**NSYIN3113A1**
EDF1300 key lock	SM, SFN, PLA, SD	**NSYINF1301**
Michelin 8133 keyless lock	SM, SFN, PLA, SD	**NSYINICHEL8131**
Michelin 8376 keyless lock	SM, SFN, PLA, SD	**NSYINICHEL8371**
E1 keyless lock	SM, SFN, PLA, SD	**NSYINE11**

Other Locks with Keys

CRN S3X SMX SFX PLM


PB501338

Characteristics	Compatibility	References
Manual	CRN, SMX, SFX, PLM	**NSYTMME**
Barrel and key 405E	CRN, SMX, SFX, PLM	**NSYTCL405ME**
Barrel and key 1242E	CRN, SMX, SFX, PLM	**NSYTL1242EME**

Characteristics	Compatibility	References
5-mm double bar insert	CRN, S3X, SMX, SFX, PLM	**NSYTDB5ME**

Adapter for Shaped Inserts and Cylindrical Barrels

SM SFN PLA SD

- Plastic adapter for installing shaped inserts and cylindrical barrels in handle lock types DIN, KABA, ASSA.
- See shaped inserts and cylindrical barrels.
- See insert types DIN, KABA, ASSA.

Supply:
1 unit


NSYLADP

Characteristics	Compatibility	References
Adapter for shaped inserts and cylindrical barrels	SM, SFN, PLA, SD	**NSYLADP**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Closing

Closures for PLS Boxes

PLS

- Slotted screw: Included in the standard references of boxes **NSYPLS●●●**.
- Wing screw: Included in the standard references of modular distribution boxes **NSYPLS●●●DLS●●●**.

Supply:
Set of 4, 6 or 8 screws.
The references also include 4 M6 screws for fixing mounting plates and 2 steel sealing accessories



NSYTCD274


NSYTCM274

Characteristics	Compatibility	Tool	References
Set of 4 slotted screws	PLS	Flat-blade screwdriver	**NSYTCD274**
Set of 6 slotted screws	PLS	Flat-blade screwdriver	**NSYTCD276**
Set of 8 slotted screws	PLS	Flat-blade screwdriver	**NSYTCD278**
Set of 4 wing screws	PLS	Manual	**NSYTCM274**

Cover Accessories Set

TBS TBP


NSYAEDST620TB_nb

- The TBS/TBP boxes are delivered as standard with slotted-head screws for flat-bladed screwdriver from 4 to 5.5 mm.

Supply:
Set of 4 shape screws


NSYAEDSB520TB

Characteristics	Compatibility	Minor pack.	Reference
Spare standard plastic screw - Height of the lid 20 mm	TBS, TBP	1	**NSYAEDS20TB**
Spare standard plastic screw - Height of the lid 40 mm	TBS, TBP	1	**NSYAEDS40TB**
Spare standard plastic screw - Height of the lid 60 mm	TBS, TBP	1	**NSYAEDS60TB**

Head Screws

SBM

- The standard Pozidriv head screws can be replaced with the double-bar or triangular shaped head screws, to discourage unauthorised opening of the cover with normal screwdrivers.
- Ingress protection rating: IP66 according to IEC 60529
- Installation: Simply replace the standard screw on the box
- Same reference for all enclosure dimensions

Supply:
1 unit


NSYAEDSBSB

Characteristics	Compatibility	References
Double-bar shaped head 3 mm screw	SBM	**NSYAEDSBSB**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Keys

All


NSYLDB5


NSYLC8


NSYLT8

- Insert without keys (unless indicated)

Characteristics	Compatibility	References
Metal key for 5-mm double-bar insert	All	**NSYLDB5**
Metal key for 7 mm square insert	All	**NSYLC7**
Metal key for 8 mm square insert	All	**NSYLC8**
Metal key for 8 mm triangle insert	All	**NSYLT8**

CNOMO Kit

SM | SFN | MCC | SFN IT


NSYCNOH123

- Locking system to be installed on the central locking bar of the door.
- It works as a locking bar immobiliser, helping prevent the handle from closing while the door is still open.
- It is compatible with all handle lock versions, except the flat lock and the small flat lock.



Supply:
One mechanism and fixing elements

Characteristics	Compatibility	References
CNOMO kit	SM, SFN, MCC, SFN IT	**NSYCNOH123**

Push-Button

SM | SFN | PLA | MCC | SFN IT | SD


NSYINPULS1

Characteristics	Compatibility	References
Push-button	SM, SFN, MCC, SFN IT, SD	**NSYINPULS1**
Push-button	PLA	**NSYTSPLA**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Viewing

Window for Modular Equipment

All

Fig. 1





Fig. 2



- Material: Transparent polycarbonate
- For indoor use only, except for outdoor ranges

Supply:
1 window


NSYVA278M

Characteristics	Compatibility	N.° of modules	Fig. n.°	A	B	C	References
Window for modular equipment, Low cover	All	2	1	78	60	15	**NSYVA272M**
Window for modular equipment, Low cover	All	4	1	78	95	15	**NSYVA274M**
Window for modular equipment, Low cover	All	6	1	78	130	15	**NSYVA276M**
Window for modular equipment, Low cover	All	8	1	78	165	15	**NSYVA278M**
Window for modular equipment, Low cover	All	10	1	78	200	15	**NSYVA2710M**
Window for modular equipment, Low cover	All	12	1	78	235	15	**NSYVA2712M**
Window for modular equipment, High cover	All	2	1	78	60	25	**NSYVA272MA**
Window for modular equipment, High cover	All	4	1	78	95	25	**NSYVA274MA**
Window for modular equipment, High cover	All	6	1	78	130	25	**NSYVA276MA**
Window for modular equipment, High cover	All	8	1	78	165	25	**NSYVA278MA**
Window for modular equipment, High cover	All	10	1	78	200	25	**NSYVA2710MA**
Window for modular equipment, High cover	All	12	1	78	235	25	**NSYVA2712MA**
Window for modular equipment, Low cover	All	16	2	195	165	13	**NSYVA2716M**
Window for modular equipment, Low cover	All	24 in 2 rows	2	196	235	13	**NSYVA2724M**


NSYVA2724M

Plastic Window

All

- Plastic window with hinged cover for installation in front panel.
- External dimensions: 213 x 133 mm.
- Internal dimensions of the window: 180 x 78 mm.
- Material:
  - Cover: Polycarbonate
  - Body: PVC
- For indoor use only, except for outdoor ranges

Supply:
1 plastic window delivered with a drilling template


NSYMW10M

Characteristics	Compatibility	References
Plastic window	All	**NSYMW10M**

Plastic Window for Modular Equipment

All

- Frame with transparent hinged cover for mounting modular switchgear on the front panel.
- Opening: 46 x 180 mm (10 modules).
- Material:
  - Cover: Polycarbonate
  - Body: PVC
- For indoor use only, except for outdoor ranges

Supply:
1 modular front panel


NSYMW10MK

Characteristics	Compatibility	References
Plastic window for modular equipment	All	**NSYMW10MK**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Kit for Fixing the Switchgear

All



NSYMW10MR


- The unit is delivered assembled
- For indoor use only, except for outdoor ranges

Supply:
1 DIN rail and two supports.

Characteristics	Compatibility	References
Kit for fixing the switchgear	All	**NSYMW10MR**


Mounting Example

NSYMW10MK + NSYMW10MR.



Control Window

All



- To help prevent accidental operation of the control units by any unauthorised person.
- Allows the displayed information to be read without opening the door.
- Equipped with hinges for opening (180°).
- Locked by a n° 2233X lock.
- Indoor installation.
- Material: Aluminum frame and 3 mm acrylic window
- For indoor use only, except for outdoor ranges

Supply:
1 window, fixings
and instruction sheet



NSYCW33

Characteristics	Compatibility	Dimensions A (mm)	Dimensions B (mm)	References
Control window	All	300	300	**NSYCW33**
Control window	All	400	400	**NSYCW44**
Control window	All	400	500	**NSYCW45**
Control window	All	400	600	**NSYCW46**
Control window	All	500	400	**NSYCW54**
Control window	All	500	500	**NSYCW55**
Control window	All	500	600	**NSYCW56**
Control window	All	600	500	**NSYCW65**
Control window	All	600	600	**NSYCW66**
Control window	All	800	600	**NSYCW86**


Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Door Accessories

Cable Guides, retainers and Switches

Door Cable-Guide Cross-Rail

SM | SFN | SMX | SFX | MCC | SFN IT | SFN HD





- Recommended for fixing cables in the internal equipment of the door.
- Height adjustable every 25-mm.
- Material: Galvanized steel
- Fixing: Direct fixing on the reinforcement frame


Supply:
2 cable-guide cross-rails and fixing elements


NSYSDGCR5

Characteristics	Compatibility	Width (mm)	References
Door cable-guide cross-rail	SM, SFN, SMX, SFX, MCC, SFN IT, SFN HD	600	**NSYSDGCR5**
Door cable-guide cross-rail	SM, SFN, SMX, SFX, MCC, SFN IT, SFN HD	600	**NSYSDGCR6**
Door cable-guide cross-rail	SM, SFN, SMX, SFX, MCC, SFN IT, SFN HD	800	**NSYSDGCR8**

Door Cable-Guide Cross-Rails for Wall-Mounted Enclosures

CRN | S3D | S3X | S3HD | S3DEX





- They are installed on wall-mounted enclosures with heights from 400 mm for PanelSeT S3D and 500 mm for PanelSeT S3X.
- They make it easy to equip the inside of the door.
- Installation cable ties.
- Fixing: They are fixed to the door reinforcement frame by 2 self-tapping screws. The angle can be directed towards the body of the enclosure or towards the door

Supply:
2 cable-guide cross-rails and fixing elements



NSYTFPCRN4

Characteristics	Compatibility	Width (mm)	References
Door cable-guide cross-rails for wall-mounted enclosures	CRN, S3D, S3X, S3HD, S3DEX	400	**NSYTFPCRN4**
Door cable-guide cross-rails for wall-mounted enclosures	CRN, S3D, S3X, S3HD, S3DEX	500	**NSYTFPCRN5**
Door cable-guide cross-rails for wall-mounted enclosures	CRN, S3D, S3X, S3HD, S3DEX	600	**NSYTFPCRN6**
Door cable-guide cross-rails for wall-mounted enclosures	CRN, S3D, S3X, S3HD, S3DEX	800	**NSYTFPCRN8**
Door cable-guide cross-rails for wall-mounted enclosures	CRN, S3D, S3X, S3HD	1000	**NSYTFPCRN10**

Wall-Mounted Door Retainer Steel

CRN | S3D | S3X

To block the door in the open position.
- It is installed on enclosures with heights from 400 mm and widths from 300 mm.
- Door opening angle: 120°.
- Earthing connection of the enclosure by means of the reinforcement rail.
- Earthing accessories supplied with the enclosure (earth-connection cable to be ordered separately), for more information see page 540
- Material: Steel

Comment:
It is not compatible with installing the 19" swing rack and the internal door.


NSYAEDRSCST

Characteristics	Compatibility	References
Wall-mounted door retainer Steel	CRN, S3D, S3X	**NSYAEDRSCST**

Wall-Mounted Door Retainer Polyamide

S3D | S3HD

To block the door in the open position.
- It is installed on the perforated rails of the enclosure doors at the required height.
- Material: Polyamide 6 (PA6)

Comment:
It can only be installed enclosures with a height from 400 mm and above (including perforated rails).


NSYAEDRS3DPA6

Characteristics	Compatibility	References
Wall-mounted door retainer polyamide	S3D, S3HD	**NSYAEDRS3DPA6**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Retainer

PLA PLAZ PLAT PLAZT


NSYRETPLA


NSYRETPLAU

- Designed to adapt directly to the enclosure
- Can be installed on a door opening to the left or right indistinctly
- Material: Galvanized steel

Supply:
Delivered with the fixings required for installation

Note:
ref. **NSYRETPLAU** is incompatible with internal doors, modular distribution chassis, step slides, adapter plates and cable entry plates. If not compatible, use ref. **NSYRETPLA**.

Characteristics	Compatibility	References
Door retainer opening to 110°	PLA, PLAZ, PLAT	**NSYRETPLA**
Door retainer with 2 positions, 90° and 120°	PLA, PLAZ, PLAT, PLAZT	**NSYRETPLAU**

Door Retainer for Floor-Standing Enclosure

SM SFN


NSYSFNDR_rb

- Door retainer locking the door in open position.
- It is fixed directly to the front frame of them enclosure and to the reinforcement frame of the door.
- It can be installed on doors that open both to the right and to the left.
- If the total weight (door plus accessories) is less than 40 kg, use the mechanical door retainer.

Supply:
Door stop and fixing elements



NSYSMDR


NSYSFNDR

Characteristics	Compatibility	Type	Limit	References
Door retainer for floor-standing enclosure	SM	Mechanical	90°	**NSYSMDR**
Door retainer for floor-standing enclosure	SM	Pneumatic	90° and 120°	**NSYSMNDR**
Door retainer for floor-standing enclosure	SFN	Mechanical	90° and 120°	**NSYSFMDR**
Door retainer for floor-standing enclosure	SFN	Pneumatic	90° and 120°	**NSYSFNDR**

Door-Centering Caster

SM SFN


NSYSDRC

- Allows the door to be raised when closing.
- Direct mounting on the reinforcement frame.
- Maximum load: 92 kg
- PanelSeT SM: installation only possible with horizontal adaptation profile NSYSMHR• (see page 531)

Supply:
One centering roller and fixing elements

Characteristics	Compatibility	References
Door-centering caster	SM, SFN	**NSYSDRC**

Door Switch

CRN S3D S3X


NSYINLCRN

- Switch/commutator unit equipped with support and fixings for direct fixing to the enclosure.
- Can be used to control lighting, air-conditioning units, etc.
- It is not compatible with installing the 19" swing rack and the internal door.
- NC + NO contact, 240 V AC / 3 A (IEC 60947-5-1) 250 V DC / 0,1 A (IEC 0947-5-1).

Supply:
1 door switch and fixing elements

Characteristics	Compatibility	References
Door switch	CRN, S3D, S3X	**NSYINLCRN**

PLA


NSYSNLPLA

- NC + NO switch.
- Incompatible with the inner door and modular distribution chassis

Supply:
Switch, fixing bracket and fixings

Characteristics	Compatibility	References
Door switch	PLA	**NSYSNLPLA**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Door Accessories

Cable Guides, retainers and Switches

Door Switch



Supply:
1 door switch and fixing elements

SM SFN SFX

- The switch is fixed to the structure of the enclosure.
- Drilled M20 cable entry for cable gland.
- NC + NO contact, 240 V AC / 3 A (IEC 60947-5-1)
  250 V DC / 0,1 A (IEC 60947-5-1)



NSYDCM20

Characteristics	Compatibility	References
Door switch	SFN, SFX	**NSYDCM20**
Door switch	SM	**NSYMDCM20**

Metal Document Pocket

SM SFN SMX SFX

- Direct mounting on the reinforcement frame of the door.
- Adjustable depth with a pitch of 25 mm.
- Material: Steel
- Finish: Structured finish, epoxy polyester powder
- Color: RAL 7035 gray



Supply:
1 metal document pocket and fixing elements



NSYSDP6M

Characteristics	Compatibility	(D) Width (mm)	References
Metal document pocket	SM, SFN, SMX, SFX	600	**NSYSDP6M**
Metal document pocket	SM, SFN, SMX, SFX	800	**NSYSDP8M**

Plastic Document Pocket

All

- Attachment by adhesive tape.
- Material: Polystyrene (PS)
- Color: RAL 7035 gray (**NSYDPA4**: RAL 9001 white)
- Operating Temperature: -10°C to +50°C
- Operating humidity: < 50% HR



Comment:
NSYDPA44 not compatible with 19" chassis or modular distribution.

Supply:
1 plastic document pocket


NSYDPA5

Characteristics	Compatibility	Doc. format	A (mm)	B (mm)	C (mm)	References
Plastic document pocket	All	A5	174	188	22	**NSYDPA5**
Plastic document pocket	All	A4	230	247	23	**NSYDPA4**
Plastic document pocket	All	A4	234	278	40	**NSYDPA44**
Plastic document pocket	All	A3	285	476	35	**NSYDPA3**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Aerosol Paint Can

Steel



NSYBPA7032

- Air-drying paint.
- Content: 150 g.

Note:
Not available for destinations outside Europe.
NSYBPA703• expires 10 years after its production.

Characteristics	Compatibility	References
Aerosol paint can, RAL 7032	Steel	**NSYBPA7032**
Aerosol paint can, RAL 7035 gray	Steel	**NSYBPA7035**

Touch-Up Paint

Steel


NSYTUP7035

- Paint for touching up with a brush.
- Air-drying paint.

Characteristics	Compatibility	References
Touch-up paint, RAL 7035 gray	Steel	**NSYTUP7035**

Renovation and Anti-Graffiti Paint

Polyester


NSYAUPG1G

- Paint kit with 2 components (base 80% + hardener 20%)
- Specially designed for polyester enclosures, for their renovation and/or as prevention to allow easy removal of graffiti.
- Color: RAL 7035 gray

Supply: NSYAUPG1G
The 1 kg reference includes 1 pot with 800 g of base paint and 200 g of hardener (It is enough to paint a surface of around 5 m²).

Characteristics	Compatibility	References
Renovation and anti-graffiti paint	Polyester	**NSYAUPG1G**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Maintenance Accessories

Lighting

Characteristics	Multi-Fixing LED Lamps	
Note: For dimensions see below		
	These LED lamps are designed to optimize the life time, consumption, space and accessibility inside the enclosure, they are available with three fixing options as standard.	
Color	Black RAL 9005	
Ingress protection rating	IP20 according to IEC60529	
Standards	• IEC 60598 • UL 94: For plastic components • UL508A: Control Panel	• UL153: Lamps • UL8750: LED for lighting • EN55015: EMC
Other characteristics	• Built-in switch • Power consumption: 10 W • Frequency: 50/60 Hz • Power factor: V AC lamps: 0.9 V DC lamps: 1 • Luminosity: 1020 lm* • Light temperature: 4000 K • LED service life: 25000 h	• Casing: Plastic UL94 • Degree of insulation: Class I - Lamps with socket according to ENEC certificate Class II - Lamps without socket according to ENEC certificate **NSYLAMLDVDC** is Class III according to ENEC Certificate • Compliant with RoHS and Reach • Ambient temperature: Operation: -16 °C to +65 °C (-3 °F to +149 °F) Storage: -10 °C to +60 °C (-14 °F to +140 °F) • Max. 2 Apms and 5 lamps in serial connection
Connections	• 3 m power black or orange cable with quick connector (Not supplied. See reference below) • 1.5 m interconnection black or orange cable with quick connectors (Not supplied. See reference below) According to the directive IEC 60204-1: • Black cables: Power circuits for switch or DC voltage. • Orange cables: External voltage that may be present even if the cabinet is turned off.	
Supply	• 1 lamp and fixing elements	


Lamp model	Lamps			Cables		
	Socket			Black cables		Orange cables
			References	Power (3 m) References	Interconnection (1.5 m) References	Power (3 m) References
With socket 120 / 230 V AC	SCHUKO		**NSYLAMLDS**	NSYLAM3M	**NSYLAM1M**	**NSYLAM3MN**
With socket 120 / 230 V AC	UTE		**NSYLAMLDF**	NSYLAM3M	**NSYLAM1M**	**NSYLAM3MN**
With socket 120 / 230 V AC	British		**NSYLAMLDB**	NSYLAM3M	**NSYLAM1M**	**NSYLAM3MN**
With socket 120 V AC	USA		**NSYLAMLDU**	NSYLAM3MUL	-	-
Without socket 120 / 230 V AC	–	–	**NSYLAMLD**	NSYLAM3M	**NSYLAM1M**	**NSYLAM3MN**
Without socket 120 / 230 V AC		–		NSYLAM3MUL	-	-
Without socket - With presence detection 120/230 V AC	–	–	**NSYLAMLDD**	NSYLAM3M	**NSYLAM1M**	**NSYLAM3MN**
Without socket - With presence detection 230 V AC				NSYLAM3MUL	-	-
Without socket - DC 24-48 V DC	–	–	**NSYLAMLDVDC**	NSYLAM3MDC	-	-
Without socket - DC 24-48 V DC				NSYLAM3MDCUL	-	-

* For reference NSYLAMLDVDC luminosity is 1020 ml.



Fixing Options


Fixing by Sliding Brackets



Magnetic Fixing



Fixing to DIN Rail



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

3-Pole Connectors

All

- Designed to connect Multi-Fixing LED Lamps.
- Color:
  AC: Black
  DC: Black (body) and brown (head)
- Ingress protection rating: IP20
- Rated current: 16 A
- Rated voltage: 250 V
- Strain relief: Yes
- Connection type for cabling: Screw connection
- Material: Polyamide
- Dimensions:
  Length: 53.2 mm
  Width: 23 mm
  Height: 13.8 mm

- **Connection data:**
  Cable diameter: 9 mm
  Cable diameter 2: 5.5 mm
  Cross section solid: 2.5 mm²
  Cross section solid 2: 0.5 mm²
  Connection cross section stranded (max.): 2.5 mm²
  Cross section stranded 2: 0.5 mm²


NSYLAMACF


NSYLAMACM

Characteristics	Compatibility	References
3-pole socket type connectors AC model	All	**NSYLAMACF**
3-pole plug type connectors AC model	All	**NSYLAMACM**

6

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.


Maintenance Accessories

Lighting

Cost-Effective LED Lamps

All

- This LED lamp is designed to optimize costs and can be used in almost all enclosures respecting the dimensions. It can be interconnected using a single power source: 5 W lamps: Max. 10 lamps interconnected, 10 W lamps: Max. 5 lamps interconnected.
- Built-in switch
- Light temperature: 4000 K*
- LED service life: 25000 h*
- Casing: Plastic for transparent cover and connectors Aluminum for body
- Degree of insulation: Class I
- Compliant with RoHS and Reach
- Ambient temperature: Operating: -10 °C to +60 °C (-14 °F to +140 °F) / Storage: -16 °C to +65 °C (-3 °F to +149 °F)
- Color: Aluminum
- Ingress protection rating: IP20 according to IEC60529
- Standards: IEC 60598



Supply:
1 lamp and fixing elements
3 m connection cable with quick connector
1 m interconnection cable with quick connectors

* Approximate values.



NSYLAMT5LD1

Characteristics	Compatibility	Voltage (V)	Power (W)	Power factor	Frequency (Hz)	Luminous flux (lm)*	References
Cost-effective LED lamps	All	120/230 V AC	5	0.8	50-60	500	**NSYLAMT5LD1**
Cost-effective LED lamps	All	120/230 V AC	10	0.9	50-60	1100	**NSYLAMT5LD2**
Cost-effective LED lamps	All	24/48 V DC	5	1	-	470	**NSYLAMT5LD1VDC**

Portable LED Lamp

All

- This LED portable lamp is designed to be installed as
- Enclosure lamp or maintenance lamp providing mobility,
- Resistance, versatility and durability.
- Double function: internal enclosure lamp, maintenance lamp.
- E27 LED lamp
- Built-in recessed switch
- Light temperature: 4000 K*
- LED service life: 25000 h*
- Power cable 3 m long with a plug (European standard type)
- Casing: Plastic
- Degree of insulation: Class II
- Compliant with RoHS and Reach
- Ambient temperature: Operating: -16 °C to +65 °C (-3 °F to +149 °F) / Storage: -10 °C to +60 °C (-14 °F to +140 °F)
- Color: Black RAL 9005
- Ingress protection rating: IP20 according to IEC60529
- Standards: IEC 60598 UL 94: For plastic components



Supply:
1 lamp with 3 m power cable with European universal plug
1 fix base
Fixing elements

* Approximate values.


NSYLAMPORTLD


Characteristics	Compatibility	Voltage (V)	Power (W)	Power factor	Frequency (Hz)	Luminous flux (lm)*	References
Portable LED lamp	All	120/230 V AC	10	0.5	50-60	1100	**NSYLAMPORTLD**

Fixing Options

Magnetic Fixing



Fixing by Adapter Brackets



Possible uses

Fixing by Adhesive or by Screws



Used on Workbench



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Spare Parts

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Spare Parts

PanelSeT Steel Enclosures	**578**
PanelSeT Stainless-Steel Enclosures	**583**
PanelSeT Insulated Enclosures	**584**
Specific Application and Customized Solutions	**585**
ClimaSys Thermal Management	**590**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT Steel Enclosures

PanelSeT SBM: Industrial Boxes


NSYSBMABS4

Accessories	References
Bag of acces. SBM boxes 4 screws	NSYSBMABS4
Bag of acces. SBM boxes 6 screws	NSYSBMABS6

PanelSeT S3D: Wall-Mounted Enclosures


PB500199_48_nb
NSYDS3D32

Single doors	References
Plain door 300 x 200	NSYDS3D32
Plain door 300 x 250	NSYDS3D325
Plain door 300 x 300	NSYDS3D33
Plain door 300 x 400	NSYDS3D34
Plain door 400 x 300	NSYDS3D43
Plain door 400 x 400	NSYDS3D44
Plain door 400 x 600	NSYDS3D46
Plain door 500 x 300	NSYDS3D53
Plain door 500 x 400	NSYDS3D54
Plain door 500 x 500	NSYDS3D55
Plain door 600 x 400	NSYDS3D64
Plain door 600 x 500	NSYDS3D65
Plain door 600 x 600	NSYDS3D66
Plain door 600 x 800	NSYDS3D68
Plain door 700 x 500	NSYDS3D75
Plain door 800 x 600	NSYDS3D86
Plain door 800 x 800	NSYDS3D88
Plain door 800 x 1000	NSYDS3D810
Plain door 1000 x 600	NSYDS3D106
Plain door 1000 x 800	NSYDS3D108
Plain door 1000 x 1000	NSYDS3D1010
Plain door 1200 x 1000	NSYDS3D1210
Plain door 1200 x 600	NSYDS3D126
Plain door 1200 x 800	NSYDS3D128

Door accessories	References
Gasket double-door enclosure (previous version before May 2023)	NSYGDD
Set of 5 taps and latches	NSYS3DTL
Hinge 120°	NSYAEDH120S3D
Hinge 180°	NSYAEDH180S3D

Earthing accessories	References
Set of 500 earthing labels	NSYSWMEL

Fixing hardware cable Gland plate	References
100 screws	NSYS3DCGSB
standard screw bag	NSYS3DCGPSTDSB

Locking accessories	References
Set of 10 linkage guides	NSYS3DLG
Standard key DB3	NSYAEDLS3DKDB3
Lock + standard key DB3 neutral	NSYAEDLS3DRLN
3 point lock linkage H 600 mm	NSYBTAS3D60
3 point lock linkage H 700 mm	NSYBTAS3D70
3 point lock linkage H 800 mm	NSYBTAS3D80
3 point lock linkage H 1000 mm	NSYBTAS3D100
3 point lock linkage H 1200 mm	NSYBTAS3D120
3 point lock linkage H 1400 mm	NSYBTAS3D140
3 point lock linkage (H = 650 mm)	NSYBTAS3D65
3 point lock linkage (H = 900 mm)	NSYBTAS3D90

Panels	References
50 caps for holes of hinges WM	NSYSWMCH
Set of 50 back plugs WM	NSYSWMBP

Sealing	References
Adhesive sealing gasket 18 x 10 2M	NSYADG2M
Adhesive sealing gasket 18 x 10 3M	NSYADG3M
Adhesive sealing gasket 18 x 10 5M	NSYADG5M
Adhesive sealing gasket 18 x 10 20M	NSYADG20M

Double door (new design from April 2023)	References
Plain door 800 x 500 right	NSYDNS3D85R
Plain door 800 x 500 left	NSYDNS3D85L
Plain door 800 x 600 right	NSYDNS3D86R
Plain door 800 x 600 left	NSYDNS3D86L
Plain door 1000 x 500 right	NSYDNS3D105R
Plain door 1000 x 500 left	NSYDNS3D105L
Plain door 1000 x 600 right	NSYDNS3D106R
Plain door 1000 x 600 left	NSYDNS3D106L
Plain door 1200 x 500 right	NSYDNS3D125R
Plain door 1200 x 500 left	NSYDNS3D125L
Plain door 1200 x 600 right	NSYDNS3D126R
Plain door 1200 x 600 left	NSYDNS3D126L
Plain door 1400 x 500 right	NSYDNS3D145R
Plain door 1400 x 500 left	NSYDNS3D145L

Double door (previous design before April 2023)	References
Plain door 800 x 500 right	NSYDS3D85R
Plain door 800 x 500 left	NSYDS3D85L
Plain door 800 x 600 right	NSYDS3D86R
Plain door 800 x 600 left	NSYDS3D86L
Plain door 1000 x 500 right	NSYDS3D105R
Plain door 1000 x 500 left	NSYDS3D105L
Plain door 1000 x 600 right	NSYDS3D106R
Plain door 1000 x 600 left	NSYDS3D106L
Plain door 1200 x 500 right	NSYDS3D125R
Plain door 1200 x 500 left	NSYDS3D125L
Plain door 1200 x 600 right	NSYDS3D126R
Plain door 1200 x 600 left	NSYDS3D126L
Plain door 1400 x 500 right	NSYDS3D145R
Plain door 1400 x 500 left	NSYDS3D145L

See page 9 for details or consult our web site www.se.com

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT S3DM: Wall-Mounted Enclosures


NSYS3DM10615T

Fixing hardware	References
100 screws for cable gland plate	NSYS3DCGSB
Standard screw bag cable gland plate	NSYS3DCGPSTDSB
Earthing accessories	**References**
Set of 500 earthing labels	NSYSWMEL
Locking accessories	**References**
Set of 10 linkage guides	NSYS3DLG
Standard key DB3	NSYAEDLS3DKDB3
3 point lock linkage H 600 mm	NSYBTAS3D60
3 point lock linkage H 700 mm	NSYBTAS3D70
3 point lock linkage H 800 mm	NSYBTAS3D80
3 point lock linkage H 1000 mm	NSYBTAS3D100
Panels WM	**References**
50 caps for holes of hinges	NSYSWMCH
Set of 50 back plugs	NSYSWMBP

PanelSeT S3DB: Wall-Mounted Enclosures


PB500200-42

NSYSWMEL

Earthing accessories	References
Set of 500 earthing labels	NSYSWMEL
Locking accessories	**References**
Standard key DB3	NSYAEDLS3DKDB3
Panels	**References**
50 caps for holes of hinges WM	NSYSWMCH
Set of 50 back plugs WM	NSYSWMBP

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT Steel Enclosures

PanelSeT CRN: Wall-Mounted Enclosures



NSYDCRN22

Doors	References
Plain door H 200 x W 200	**NSYDCRN22**
Plain door H 200 x W 300	**NSYDCRN23**
Plain door H 250 x W 200	**NSYDCRN2520**
Plain door H 300 x W 250	**NSYDCRN3025**
Plain door H 300 x W 300	**NSYDCRN33**
Plain door H 300 x W 400	**NSYDCRN34**
Plain door H 300 x W 450	**NSYDCRN3045**
Plain door H 400 x W 300	**NSYDCRN43**
Plain door H 400 x W 400	**NSYDCRN44**
Plain door H 400 x W 600	**NSYDCRN46**
Plain door H 500 x W 400	**NSYDCRN54**
Plain door H 500 x W 500	**NSYDCRN55**
Plain door H 600 x W 400	**NSYDCRN64**
Plain door H 600 x W 500	**NSYDCRN65**
Plain door H 600 x W 600	**NSYDCRN66**
Plain door H 600 x W 800	**NSYDCRN68**
Plain door H 700 x W 500	**NSYDCRN75**
Plain door left H 800 x W 500	**NSYDCRN85L**
Plain door right H 800 x W 500	**NSYDCRN85R**
Plain door H 800 x W 600	**NSYDCRN86**
Plain door left H 800 x W 600	**NSYDCRN86L**
Plain door right H 800 x W 600	**NSYDCRN86R**
Plain door H 800 x W 800	**NSYDCRN88**
Plain door left H 1000 x W 500	**NSYDCRN105L**
Plain door right H 1000 x W 500	**NSYDCRN105R**
Plain door H 1000 x W 600	**NSYDCRN106**
Plain door right H 1000 x W 600	**NSYDCRN106R**
Plain door left H 1000 x W 600	**NSYDCRN106L**
Plain door H 1000 x W 800	**NSYDCRN108**
Plain door right H 1200 x W 500	**NSYDCRN125R**
Plain door left H 1200 x W 500	**NSYDCRN125L**
Plain door H 1200 x W 600	**NSYDCRN126**
Plain door right H 1200 x W 600	**NSYDCRN126R**
Plain door left H 1200 x W 600	**NSYDCRN126L**
Plain door H 1200 x W 800	**NSYDCRN128**
Plain door right H 1400 x W 500	**NSYDCRN145R**
Plain door left H 1400 x W 500	**NSYDCRN145L**

Door Accessories	References
Standard PanelSeT hinge	**NSYBICRN**
Earthing accessories	**References**
Set of 500 earthing labels	**NSYSWMEL**
Panels	**References**
Set of 50 back plugs WM	**NSYSWMBP**
Fixing hardware	**References**
Screw bag for CRN cable gland plate	**NSYCRNCGPSTDSB**
Sealing	**References**
Adhesive sealing gasket 18 x 10 2M	**NSYADG2M**
Adhesive sealing gasket 18 x 10 3M	**NSYADG3M**
Adhesive sealing gasket 18 x 10 5M	**NSYADG5M**
Adhesive sealing gasket 18 x 10 20M	**NSYADG20M**

7

PanelSeT CRNG: Wall-Mounted Enclosures



NSYDCRNG86

Doors	References
Plain door H 800 x W 600	**NSYDCRNG86**
Plain door left H 800 x W 500	**NSYDCRNG85L**
Plain door right H 800 x W 500	**NSYDCRNG85R**
Plain door left H 800 x W 600	**NSYDCRNG86L**
Plain door right H 800 x W 600	**NSYDCRNG86R**
Plain door left H 1000 x W 500	**NSYDCRNG105L**
Plain door right H 1000 x W 500	**NSYDCRNG105R**
Plain door H 1000 x W 600	**NSYDCRNG106**
Plain door right H 1000 x W 600	**NSYDCRNG106R**
Plain door left H 1000 x W 600	**NSYDCRNG106L**
Plain door H 1000 x W 800	**NSYDCRNG108**
Plain door right H 1200 x W 500	**NSYDCRNG125R**
Plain door left H 1200 x W 500	**NSYDCRNG125L**
Plain door H 1200 x W 600	**NSYDCRNG126**
Plain door H 1200 x W 600	**NSYDCRNG126R**
Plain door left H 1200 x W 600	**NSYDCRNG126L**
Plain door H 1200 x W 800	**NSYDCRNG128**
Plain door right H 1400 x W 500	**NSYDCRNG145R**
Plain door left H 1400 x W 500	**NSYDCRNG145L**

Door Accessories	References
Hinge 120°	**NSYAEDH120S3D**
Hinge 180°	**NSYAEDH180S3D**
Locking accessories	**References**
3 point lock linkage for PanelSeT CRNG (H = 800 mm)	**NSYBTACRNG80**
3 point lock linkage for PanelSeT CRNG (H = 1000 mm)	**NSYBTACRNG100**
3 point lock linkage for PanelSeT CRNG (H = 1200 mm)	**NSYBTACRNG120**
3 point lock linkage for PanelSeT CRNG (H = 1400 mm)	**NSYBTACRNG140**
Earthing accessories	**References**
Set of 500 earthing labels	**NSYSWMEL**
Fixing hardware cable gland plate	**References**
100 screws	**NSYS3DCGSB**
Standard screw bag	**NSYS3DCGPSTDSB**
Panels	**References**
50 caps for holes of hinges WM	**NSYSWMCH**
Set of 50 back plugs WM	**NSYSWMBP**
Others accessories	**References**
Screw bag for CRN cable gland plate	**NSYCRNCGPSTDSB**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT SFN: Floor-Standing Enclosures

PB124775



NSYSFD207



NSYTDSSFN2D

Door accessories	References
Set of 4 Hinges and fixing elements	NSYDHSF
Double-door stoppers (2 pieces)	NSYTDSSFN2D
Locking accessories	**References**
Locking system for enclosures, single-door version 1200H (right side door for double-door version)	NSYLCK12SF
Locking system for enclosures 1 single-door version 1400H	NSYLCK14SF
Locking system for enclosures, single-door version 1600H (right side door for double-door version)	NSYLCK16SF
Locking system for enclosures, single-door version 1800H (right side door for double-door version)	NSYLCK18SF
Locking system for enclosures, single-door version 2000H (right side door for double-door version)	NSYLCK20SF
Locking system for enclosures, single-door version 2200H (right side door for double-door version)	NSYLCK22SF
Door locking plastic fastening clip	NSYLCKWSF
Handle neutral trim	NSYSFHNTRIM
Handle SF	NSYSFNHS1

Roof	References
Std roof W 1000 x D 400 mm	NSYRSFN104L
Std roof W 1000 x D 500 mm	NSYRSFN105L
Std roof W 1000 x D 600 mm	NSYRSFN106L
Std roof W 1000 x D 800 mm	NSYRSFN108L
Std roof W 1200 x D 400 mm	NSYRSFN124L
Std roof W 1200 x D 500 mm	NSYRSFN125L
Std roof W 1200 x D 600 mm	NSYRSFN126L
Std roof W 600 x D 400 mm	NSYRSFN64L
Std roof W 600 x D 600 mm	NSYRSFN66L
Std roof W 800 x D 400 mm	NSYRSFN84L
Std roof W 800 x D 500 mm	NSYRSFN85L
Std roof W 800 x D 600 mm	NSYRSFN86L
Std roof W 800 x D 800 mm	NSYRSFN88L
Fixing hardware	**References**
Captive screws for panels external fixing	NSYCSSF
Plinth accessories	**References**
H 100 mm Plastic covers for plinth corners	NSYPC100
H 200 mm Plastic covers for plinth corners	NSYPC200
Panels	**References**
Back panel H 2000 x W 700 mm	NSYBPN207
Doors	**References**
Plain door PrismaSeT RAL9003 2000 x 700 mm	NSYSFND207ED
Plain door PrismaSeT RAL7035 2000 x 700 mm	NSYSFND207G
Glazed door PrismaSeT RAL9003 2000 x 700 mm	NSYSFND207TED
Glazed door PrismaSeT RAL7035 2000 x 700 mm	NSYSFND207TG
Plain door PrismaSeT RAL9003 2000 x 300	NSYSFND203ED
Two door stop double door	NSYTDSSFN2D

Spacial SF: Floor-Standing Enclosures

PB502412-55



PB503841



NSYRSF64L


Door accessories	References
Set of 4 Hinges and fixing elements	NSYDHSF
Double-door stoppers (2 pieces)	NSYTDSSF2D
Locking accessories	**References**
Locking system for enclosures, single-door version 1200H (right side door for double-door version)	NSYLCK12SF
Locking system for enclosures 1 single-door version 1400H	NSYLCK14SF
Locking system for enclosures, single-door version 1600H (right side door for double-door version)	NSYLCK16SF
Locking system for enclosures, single-door version 1800H (right side door for double-door version)	NSYLCK18SF
Locking system for enclosures, single-door version 2000H (right side door for double-door version)	NSYLCK20SF
Locking system for enclosures, single-door version 2200H (right side door for double-door version)	NSYLCK22SF
Door locking plastic fastening clip	NSYLCKWSF
Handle neutral trim	NSYSFHNTRIM
Handle SF	NSYSFHS1

Fixing hardware	References
Captive screws for panels external fixing	NSYCSSF
Plinth accessories	**References**
H 100 mm Plastic covers for plinth corners	NSYPC100
H 200 mm Plastic covers for plinth corners	NSYPC200
Panels	**References**
PrismaSeT back panel H 2000 x W 700 mm	NSYBP207
Doors	**References**
Simple doors of PanelSeT SFN are compatible with Spacial SF. Bottom trim not to be mounted	NSYSFND•
Double doors of PanelSeT SFN can be used in Spacial SF by replacing the double-door stopper. Bottom trim not to be mounted	NSYSFND•2D + NSYTDSSFN2D
Roof	**References**
Roof W 600 x D 400 mm	NSYRSF64L
Roof W 600 x D 600 mm	NSYRSF66L
Roof W 800 x D 400 mm	NSYRSF84L
Roof W 800 x D 500 mm	NSYRSF85L
Roof W 800 x D 600 mm	NSYRSF86L
Roof W 800 x D 800 mm	NSYRSF88L
Roof W 1000 x D 400 mm	NSYRSF104L
Roof W 1000 x D 500 mm	NSYRSF105L
Roof W 1000 x D 600 mm	NSYRSF106L
Roof W 1000 x D 800 mm	NSYRSF108L
Roof W 1200 x D 400 mm	NSYRSF124L
Roof W 1200 x D 500 mm	NSYRSF125L
Roof W 1200 x D 600 mm	NSYRSF126L

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Spacial SF: Floor-Standing Enclosures

PB503272-56



NSYRSF35L

Roof	References
Roof W 300 x D 500 mm	**NSYRSF35L**
Roof W 300 x D 600 mm	**NSYRSF36L**
Roof W 300 x D 800 mm	**NSYRSF38L**
Roof W 400 x D 400 mm	**NSYRSF44L**
Roof W 400 x D 500 mm	**NSYRSF45L**
Roof W 600 x D 400 mm	**NSYRSF64L**
Roof W 600 x D 500 mm	**NSYRSF65L**
Roof W 600 x D 600 mm	**NSYRSF66L**
Roof W 800 x D 400 mm	**NSYRSF84L**
Roof W 800 x D 500 mm	**NSYRSF85L**
Roof W 800 x D 600 mm	**NSYRSF86L**
Roof W 800 x D 800 mm	**NSYRSF88L**
Roof W 1000 x D 400 mm	**NSYRSF104L**
Roof W 1000 x D 500 mm	**NSYRSF105L**
Roof W 1000 x D 600 mm	**NSYRSF106L**
Roof W 1000 x D 800 mm	**NSYRSF108L**
Roof W 1200 x D 400 mm	**NSYRSF124L**
Roof W 1200 x D 500 mm	**NSYRSF125L**
Roof W 1200 x D 600 mm	**NSYRSF126L**
Roof W 1200 x D 800 mm	**NSYRSF128L**
Roof W 1600 x D 400 mm	**NSYRSF164L**
Roof W 1600 x D 500 mm	**NSYRSF165L**
Roof W 1600 x D 600 mm	**NSYRSF166L**

PanelSeT SM: Floor-Standing Enclosures



NSYSMEC1041

Cable gland plates	References
1 entry W 1000 x D 400 mm	**NSYSMEC1041**
1 entry W 1000 x D 300 mm	**NSYSMEC1031**
1 entry W 1000 x D 500 mm	**NSYSMEC1051**
1 entry W 600 x D 300 mm	**NSYSMEC631**
1 entry W 600 x D 400 mm	**NSYSMEC641**
1 entry W 600 x D 600 mm	**NSYSMEC661**
1 entry W 800 x D 300 mm	**NSYSMEC831**
1 entry W 800 x D 400 mm	**NSYSMEC841**
1 entry W 800 x D 500 mm	**NSYSMEC851**
1 entry W 800 x D 600 mm	**NSYSMEC861**

Doors	References
Single plain door H 1200 x W 800 mm	**NSYSFD128**
Double plain door H 1200 x W 1000 mm	**NSYSMDN12102D**
Double plain door H 1200 x W 1200 mm	**NSYSMDN12122D**
Single plain door H 1400 x W 600 mm	**NSYSFD146**
Single plain door H 1400 x W 800 mm	**NSYSFD148**
Double plain door H 1400 x W 1000 mm	**NSYSMDN14102D**
Double plain door H 1400 x W 1200 mm	**NSYSMDN14122D**
Single plain door H 1600 x W 600 mm	**NSYSFD166**
Single plain door H 1600 x W 800 mm	**NSYSFD168**
Double plain door H 1600 x W 1000 mm	**NSYSMDN16102D**
Double plain door H 1600 x W 1200 mm	**NSYSMDN16122D**
Single plain door H 1800 x W 600 mm	**NSYSFD186**
Single plain door H 1800 x W 800 mm	**NSYSFD188**
Single plain door H 1800 x W 1000 mm	**NSYSFD1810**
Double plain door H 1800 x W 1000 mm	**NSYSFD18102D**
Double plain door H 1800 x W 1200 mm	**NSYSFD18122D**
Double plain door H 1800 x W 1600 mm	**NSYSMDN18162D**
Single plain door H 2000 x W 600 mm	**NSYSFD206**
Single plain door H 2000 x W 800 mm	**NSYSFD208**
Single plain door H 2000 x W 1000 mm	**NSYSFD2010**
Double plain door H 2000 x W 1200 mm	**NSYSFD20122D**
Double plain door H 2000 x W 1600 mm	**NSYSFD20162D**

Door accessories	References
Set of 4 hinges and fixing elements	**NSYDHSF**
PanelSeT SM hinges and 2D door stop	**NSYDHSM2D**
Double-door stoppers (2 pieces) for SM before February 2026	**NSYTDSSF2D**
PanelSeT SM hinges and 2D door stop for new SM	**NSYDHSMN2D**

Locking accessories	References
Locking system for enclosures, single-door version 1200H (right side door for double-door version)	**NSYLCK12SF**
Locking system for enclosures, single-door version 1600H (right side door for double-door version)	**NSYLCK16SF**
Locking system for enclosures, single-door version 1800H (right side door for double-door version)	**NSYLCK18SF**
Locking system for enclosures, single-door version 2000H (right side door for double-door version)	**NSYLCK20SF**
Locking system for enclosures, single-door version 2200H (right side door for double-door version)	**NSYLCK22SF**
Locking system for enclosures 1, single-door version 1400H	**NSYLCK14SF**
Door locking plastic fastening clip	**NSYLCKWSF**
Handle neutral trim	**NSYSFHNTRIM**

Plinth accessories	References
H 100 mm Plastic covers for plinth corners	**NSYPC100**
H 200 mm Plastic covers for plinth corners	**NSYPC200**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

PanelSeT Stainless-Steel Enclosures

PanelSeT S3X: Wall-Mounted Enclosures

PB500075_40_nb.tif



Doors	References
Left door 304L for enclosure H1000 x W1000 mm	**NSYDS3X1010L**
Left door 316L for enclosure H1000 x W1000 mm	**NSYDS3X1010LH**
Right door 304L for enclosure H1000 x W1000 mm	**NSYDS3X1010R**
Right door 316L for enclosure H1000 x W1000 mm	**NSYDS3X1010RH**
Plain door 304L for enclosure H1000 x W800 mm	**NSYDS3X108**
Plain door 316L for enclosure H1000 x W800 mm	**NSYDS3X108H**
Left door 304L for enclosure H1200 x W1000 mm	**NSYDS3X1210L**
Left door 316L for enclosure H1200 x W1000 mm	**NSYDS3X1210LH**
Right door 304L for enclosure H1200 x W1000 mm	**NSYDS3X1210R**
Right door 316L for enclosure H1200 x W1000 mm	**NSYDS3X1210RH**
Plain door 304L for enclosure H1200 x W800 mm	**NSYDS3X128**
Plain door 316L for enclosure H1200 x W800 mm	**NSYDS3X128H**
Plain door 304L for enclosure H300 x W200 mm	**NSYDS3X32**
Plain door 304L for enclosure H300 x W250 mm	**NSYDS3X325**
Plain door 316L for enclosure H300 x 250 mm	**NSYDS3X325H**
Plain door 316L for enclosure H300 x W200 mm	**NSYDS3X32H**
Plain door 304L for enclosure H300 x W300 mm	**NSYDS3X33**
Plain door 316L for enclosure H300 x W300 mm	**NSYDS3X33H**
Plain door 304L for enclosure H400 x W300 mm	**NSYDS3X43**
Plain door 316L for enclosure H400 x W300 mm	**NSYDS3X43H**
Plain door 304L for enclosure H400 x W400 mm	**NSYDS3X44**
Plain door 316L for enclosure H400 x W400 mm	**NSYDS3X44H**
Plain door 304L for enclosure H400 x W600 mm	**NSYDS3X46**

Doors	References
Plain door 316L 400 x 600 mm	**NSYDS3X46H**
Plain door 304L 500 x 400 mm	**NSYDS3X54**
Plain door 316L 500 x 400 mm	**NSYDS3X54H**
Plain door 304L 600 x 400 mm	**NSYDS3X64**
Plain door 316L 600 x 400 mm	**NSYDS3X64H**
Plain door 304L 600 x 600 mm	**NSYDS3X66**
Plain door 316L 600 x 600 mm	**NSYDS3X66H**
Plain door 304L 700 x 500 mm	**NSYDS3X75**
Plain door 316L 700 x 500 mm	**NSYDS3X75H**
Plain door 304L 800 x 600 mm	**NSYDS3X86**
Plain door 316L 800 x 600 mm	**NSYDS3X86H**
Plain door 304L 800 x 800 mm	**NSYDS3X88**
Plain door 316L 800 x 800 mm	**NSYDS3X88H**
Transp. door 304L 1000 x 800 mm	**NSYDS3X108T**
Transp. door 304L 400 x 300 mm	**NSYDS3X43T**
Transp. door 304L 500 x 400 mm	**NSYDS3X54T**
Transp. door 304L 600 x 400 mm	**NSYDS3X64T**
Transp. door 304L 700 x 500 mm	**NSYDS3X75T**
Transp. door 304L 800 x 600 mm	**NSYDS3X86T**
Door accessories	**References**
Set of 2 hinges	**NSYHS3X**
Locking accessories	**References**
Locking system 1000 mm	**NSYLSS3X10**
Locking system 1200 mm	**NSYLSS3X12**

PanelSeT SMX and SFX: Wall-Mounted Enclosures

PB500138_26_nb



PB503684



Doors	Related Offer	References
Left door 304L for enclosure H1400 x W1000 mm	SMX	**NSYDSFX1410L**
Right door 304L for enclosure H1400 x W1000 mm	SMX	**NSYDSFX1410R**
Door 304L for enclosure H1600 x W800 mm	SMX	**NSYDSFX168**
Door 304L for enclosure H1800 x W600 mm	SMX, SFX	**NSYDSFX186**
Left door for enclosure H1800 x W1200 mm	SMX, SFX	**NSYDSFX1812L**
Left door 316L for enclosure H1800 x W1200 mm	SMX	**NSYDSFX1812LH**
Right door for enclosure H1800 x W1200 mm	SMX, SFX	**NSYDSFX1812R**
Right door 316L for enclosure H1800 x W1200 mm	SMX	**NSYDSFX1812RH**
Door 304L for enclosure H1800 x W800 mm	SMX, SFX	**NSYDSFX188**
Door 316L for enclosure H1800 x W800 mm	SMX	**NSYDSFX188H**
Left door 304L for enclosure H1800 x W1600 mm	SMX	**NSYDSFX1816L**
Left door 316L for enclosure H1800 x W1600 mm	SMX	**NSYDSFX1816LH**
Right door 304L for enclosure H1800 x W1600 mm	SMX	**NSYDSFX1816R**
Right door 316L for enclosure H1800 x W1600 mm	SMX	**NSYDSFX1816RH**
Left door for enclosure H2000 x W1000 mm	SMX, SFX	**NSYDSFX2010L**
Left door 316L for enclosure H2000 x W1000 mm	SMX	**NSYDSFX2010LH**
Right door for enclosure H2000 x W1000 mm	SMX, SFX	**NSYDSFX2010R**
Right door 316L for enclosure H2000 x W1000 mm	SMX	**NSYDSFX2010RH**
Door for enclosure H1800 x W800 mm	SMX, SFX	**NSYDSFX206**
Left door for enclosure H2000 x W1200 mm	SMX, SFX	**NSYDSFX2012L**
Left door 316L for enclosure H2000 x W1200 mm	SMX	**NSYDSFX2012LH**
Right door for enclosure H2000 x W1200 mm	SMX, SFX	**NSYDSFX2012R**
Right door 316L for enclosure H2000 x W1200 mm	SMX	**NSYDSFX2012RH**
Door for enclosure H2000 x W800 mm	SMX, SFX	**NSYDSFX208**
Left for enclosure door H2000 x W1600 mm	SMX, SFX	**NSYDSFX2016L**
Left door 316L for enclosure H2000 x W1600 mm	SMX	**NSYDSFX2016LH**
Right door for enclosure H2000 x W1600 mm SMX	SMX, SFX	**NSYDSFX2016R**
Right door 316L for enclosure H2000 x W1600 mm	SMX	**NSYDSFX2016RH**

Locking system	Related Offer	References
Locking system H = 1400 mm	SMX, SFX	**NSYLSSFX14**
Locking system H = 1600 mm	SMX, SFX	**NSYLSSFX16**
Locking system H = 1800 mm	SMX, SFX	**NSYLSSFX18**
Locking system H = 2000 mm	SMX, SFX	**NSYLSSFX20**
Door accessories	**Related Offer**	**References**
Set of 3 hinges	SFX	**NSYHSMX**

7

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Panel**SeT** Insulated Enclosures

Panel**SeT** PLM: Wall-Mounted Enclosures


PB600147SE_19_nb

• For RAL 7035

Complete door (door + lock system)	References
Door with locking for PLM32	**NSYDPLM32G**
Door with locking for PLM3025	**NSYDPLM3025G**
Door with locking for PLM43	**NSYDPLM43G**
Door with locking for PLM54	**NSYDPLM54G**
Door with locking for PLM64	**NSYDPLM64G**
Door with locking for PLM75	**NSYDPLM75G**
Door with locking for PLM86	**NSYDPLM86G**
Door with locking for PLM108	**NSYDPLM108G**
Glazed door with locking for PLM3025T	**NSYDPLM3025TG**
Glazed door with locking for PLM43T	**NSYDPLM43TG**
Glazed door with locking for PLM54T	**NSYDPLM54TG**
Glazed door with locking for PLM64T	**NSYDPLM64TG**
Glazed door with locking for PLM75T	**NSYDPLM75TG**
Glazed door with locking for PLM86T	**NSYDPLM86TG**
Glazed door with locking for PLM108T	**NSYDPLM108TG**

Door accessories	References
Door hinge for NSYPLM32	**NSYAEDHPLM32**
Door hinge for NSYPLM3025 for 2 locks door	**NSYAEDHPLM3025**
Door hinge for NSYPLM43 to 86	**NSYAEDHPLM**
Door hinge for NSYPLM108	**NSYAEDHPLM108**
Rod guides (4 pieces) for PLM108	**NSYAEDPLM108**
Door hinge for NSYPLM810 (3 pieces)	**NSYAEDPLM810**
Fixing hardware	**References**
Acc. bag NSYPLM43 to 86	**NSYASPLM**
Locking accessories	**References**
Locking and rods for NSYPLM108	**NSYVPLM108**
Double-bar lock for PLM enclosures from 430 to 847 mm height with old aspect	**NSYCDBPLM**

Panel**SeT** PLA: Floor-Standing Enclosures


PB503694

• For RAL 7035

Doors	References
Door 500 x 500 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA55G**
Door 500 x 750 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA57G**
Door 750 x 500 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA75G**
Door 750 x 750 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA77G**
Door 1000 x 500 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA105G**
Door 1000 x 750 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA107G**
Door 1250 x 500 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA125G**
Door 1250 x 750 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA127G**
Door 1500 x 500 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA155G**
Door 1500 x 750 Lock handle type. Door opening 120°. For PLA, PLAT and PLAZ	**NSYDPLA157G**
Door 500 x 500 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA55HG**
Door 500 x 750 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA57HG**
Door 750 x 500 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA75HG**
Door 750 x 750 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA77HG**
Door 1000 x 500 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA105HG**

• For RAL 7035

Doors	References
Door 1000 x 750 Lock handle type. Door opening 180° + Accessory bag 120° hinge	**NSYDPLA107HG**
Door 1250 x 500 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA125HG**
Door 1250 x 750 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA127HG**
Door 1500 x 500 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA155HG**
Door 1500 x 750 Lock handle type. Door opening 180° + Accessory bag 120° hinge. For PLAZT	**NSYDPLA157HG**
Door accessories	**References**
One hinge + axe for PLA (120° opening)	**NSYAEDPLA004**
Kit of axes of door PLAZT (180° opening)	**NSYAEDPLA005**
Rod guide inside the door PLA (set of 2)	**NSYAEDPLA001**
Rod guide on 1 door PLA (set of 2)	**NSYAEDPLA002G**
Rod guide on 2 doors PLA (set of 2)	**NSYAEDPLA003G**
Fixing hardware	**References**
Acc. bag for 1 door H = 500-1000 mm	**NSYASPLA001**
Acc. bag for 1 door H = 1250-1500 mm	**NSYASPLA002**
Acc. bag for 2 door	**NSYASPLA003**
Locking accessories	**References**
5mm double bar insert for large escucheon for old PLA without handle	**NSYTDB5PLA**
Handle locking and rods H = 500 mm	**NSYVPLA5MG**
Handle locking and rods H = 750 mm	**NSYVPLA7MG**
Handle locking and rods H = 1000 mm	**NSYVPLA10MG**
Handle locking and rods H = 1250 mm	**NSYVPLA12MG**
Handle locking and rods H = 1500 mm	**NSYVPLA15MG**

Panel**SeT** TBS TBP: Plastic Industrial Boxes


NSYTBS19168

Accessories bag	References
Accessories bag for enclosure TBS/TBP	**NSYTBPASBS**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Application and Customized Solutions

Human Machine Interface: SD



NSYCCSDF8

Doors	References
Desk lid W 600 mm	**NSYDLSD6**
Desk lid W 800 mm	**NSYDLSD8**
Desk lid W 1000 mm	**NSYDLSD10**
Desk lid W 1200 mm	**NSYDLSD12**
Desk lid for w/console W 800 mm	**NSYDLSDF8**
Desk lid for w/console W 1000 mm	**NSYDLSDF10**
Desk lid for w/console W 1200 mm	**NSYDLSDF12**
Desk lid for w/console W 1600 mm	**NSYDLSDF16**
Folding console cover W 800 mm	**NSYCCSDF8**
Folding console cover W 1000 mm	**NSYCCSDF10**
Folding console cover W 1200 mm	**NSYCCSDF12**
Folding console cover W 1600 mm	**NSYCCSDF16**

Door accessories	References
Hinges compact control desk	**NSYHSD**
Hinges control desk w/console	**NSYHSDF**
Locking accessories	**References**
Standard handle in RAL 7011 (previous version)	**NSYSDH**
Handle rear door (new version)	**NSYBTACRNG140**
Lock w/DB 3 mm for frontal doors	**NSYFDLSD**
Lock w/DB 3 mm desk lids and covers	**NSYDLLSDF**
Flat escutcheon with DB 5 mm	**NSYSDFLOCKDB5**

Human Machine Interface

Door accessories	References
Locking system	**NSYLSSDX**

PanelSeT S3CM: Control Enclosure with Suspension Rack

Doors	References
Plain door H 200 x W 200	**NSYDCRN22**
Plain door H 200 x W 300	**NSYDCRN23**
Plain door H 250 x W 200	**NSYDCRN2520**
Plain door H 300 x W 250	**NSYDCRN3025**
Plain door H 300 x W 300	**NSYDCRN33**
Plain door H 300 x W 400	**NSYDCRN34**
Plain door H 300 x W 450	**NSYDCRN3045**
Plain door H 400 x W 300	**NSYDCRN43**
Plain door H 400 x W 400	**NSYDCRN44**
Plain door H 400 x W 600	**NSYDCRN46**
Plain door H 500 x W 500	**NSYDCRN55**
Plain door H 600 x W 600	**NSYDCRN66**
Plain door H 600 x W 800	**NSYDCRN68**
Plain door H 800 x W 600	**NSYDCRN86**

Door accessories	References
Standard PanelSeT hinge	**NSYBICRN**
Earthing accessories	**References**
Set of 500 earthing labels	**NSYSWMEL**

Applicative and Customized Solutions: EMC, S3HF



PB500205_46_nb

Earthing accessories	References
Set of 500 earthing labels	**NSYSWMEL**
Locking accessories	**References**
Standard Locking system	**NSYAEDLS3HFDB3**

7

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Application and Customized Solutions

PanelSeT S3DEX: Explosive Atmospheres



Doors	References
Plain door 300 x 200	**NSYDS3D32**
Plain door 300 x 300	**NSYDS3D33**
Plain door 400 x 300	**NSYDS3D43**
Plain door 400 x 400	**NSYDS3D44**
Plain door 500 x 400	**NSYDS3D54**
Plain door 600 x 400	**NSYDS3D64**
Plain door 600 x 600	**NSYDS3D66**
Plain door 700 x 500	**NSYDS3D75**
Plain door 800 x 600	**NSYDS3D86**
Plain door 1000 x 800	**NSYDS3D108**
Earthing accessories	**References**
Set of 500 earthing labels	**NSYSWMEL**

Locking accessories	References
Set of 10 linkage guides	**NSYS3DLG**
Standard key DB3	**NSYAEDLS3DKDB3**
3 point lock linkage H 600 mm	**NSYBTAS3D60**
3 point lock linkage H 700 mm	**NSYBTAS3D70**
3 point lock linkage H 800 mm	**NSYBTAS3D80**
3 point lock linkage H 1000 mm	**NSYBTAS3D100**
Panels	**References**
50 caps for holes of hinges WM	**NSYSWMCH**
Set of 50 back plugs WM	**NSYSWMBP**

PanelSeT PHD: Outdoor Heavu-Duty Enclosures



Plain doors (door + lock + hinges + door retainer)	Unic door or right door References	Left door References
H 538 x W 500	**NSYDPHD55P**	-
H 788 x W 500	**NSYDPHD75P**	-
H 843 x W 750	**NSYDPHD77P**	-
H 1093 x W 500	**NSYDPHD105P**	-
H 1093 x W 750	**NSYDPHD107P**	-
H 1343 x W 500	**NSYDPHD125P**	-
H 1343 x W 750	**NSYDPHD127P**	-
H 1343 x W 1250	**NSYDPHD127P**	**NSYDPHD125LP**
H 1593 x W 750	**NSYDPHD157P**	-
H 1593 x W 1250	**NSYDPHD157P**	**NSYDPHD155LP**
H 2093 x W 750	2 x **NSYDPHD107P**	-
Ribbed doors (door + lock + hinges + door retainer)	**References**	**References**
H 538 x W 500	**NSYDPHD55R**	-
H 788 x W 500	**NSYDPHD75R**	-
H 843 x W 750	**NSYDPHD77R**	-
H 1093 x W 500	**NSYDPHD105R**	-
H 1093 x W 750	**NSYDPHD107R**	-
H 1343 x W 500	**NSYDPHD125R**	-
H 1343 x W 750	**NSYDPHD127R**	-
H 1343 x W 1250	**NSYDPHD127R**	**NSYDPHD125LR**
H 1593 x W 750	**NSYDPHD157R**	-
H 1593 x W 1250	**NSYDPHD157R**	**NSYDPHD155LR**
H 2093 x W 750	2 x **NSYDPHD107R**	-

Aluminum cable gland plate	References
For enclosure W 750 x D 420	**NSYPPC74HD**
For enclosure W 750 x D 620	**NSYPPC76HD**
For enclosure W 500 x D 420	**NSYPPC54HD**
For enclosure W 1250 x D 420	**NSYPPC54HD** + **NSYPPC74HD**
For enclosure W 1250 x D 620	**NSYPPC56HD** + **NSYPPC76HD**
Screws and nuts for PHD gland plate (10 units)	**NSYPPCPHDSN**
Door accessories	**References**
Set of 4 complete hinges for PHD	**NSYAEDPHD**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Application and Customized Solutions

PanelSeT S3HD: Outdoor Heavy-Duty Enclosures



Heavy-Duty cable gland plate for enclosure	References
H 343 x W 200 x D 180	**NSYTLAUHD**
H 448 x W 300 x D 230	**NSYTLCUHD**
H 548 x W 400 x D 230	**NSYTLDUHD**
H 653 x W 400 x D 280	**NSYTLDUHD**
H 658 x W 600 x D 330	**NSYTLGUHD**
H 753 x W 500 x D 280	**NSYTLEUHD**
e H 858 x W 600 x D 330	**NSYTLGUHD**
H 862 x W 800 x D 430	2 x **NSYTLDUHD**
H 1062 x W 600 x D 430	**NSYTLGUHD**
H 1062 x W 800 x D 430	2 x **NSYTLDUHD**
Door	**References**
Door 300 x 200 S3HD, without handle	**NSYDS3HD32**
Door 400 x 300 S3HD, without handle	**NSYDS3HD43**
Door 500 x 400 S3HD, without handle	**NSYDS3HD54**
Door 600 x 400 S3HD + linkage locking syst	**NSYDS3HD64**
Door 600 x 600 S3HD + linkage locking syst	**NSYDS3HD66**
Door 700 x 500 S3HD + linkage locking syst	**NSYDS3HD75**
Door 800 x 600 S3HD + linkage locking syst	**NSYDS3HD86**
Door 800 x 800 S3HD + linkage locking syst	**NSYDS3HD88**
Door 1000 x 600 S3HD + linkage locking syst	**NSYDS3HD106**
Door 1000 x 800 S3HD + linkage locking syst	**NSYDS3HD108**

Hinge	References
S3HD hinge	**NSYAEDH120S3HD**
Canopy	**References**
Canopy for S3HD 200 (W) x 150 (P)	**NSYTJ2015HD**
Canopy for S3HD 300 (W) x 200 (P)	**NSYTJ3020HD**
Canopy for S3HD 400 (W) x 200 (P)	**NSYTJ4020HD**
Canopy for S3HD 400 (W) x 250 (P)	**NSYTJ4025HD**
Canopy for S3HD 600 (W) x 300 (P)	**NSYTJ6030HD**
Canopy for S3HD 500 (W) x 250 (P)	**NSYTJ5025HD**
Canopy for S3HD 800 (W) x 400 (P)	**NSYTJ8040HD**
Canopy for S3HD 600 (W) x 400 (P)	**NSYTJ6040HD**
Lock	**References**
Lock S3HD DB 3 mm (Escutcheon+cam+washer)	**NSYAEDLS3HDRL**

PanelSeT SFN HD: Outdoor Heavy-Duty Enclosures



Heavy-Duty cable gland plate for enclosure	References
H 1262 x W 600 x D 430	**NSYSFECA64HD**
H 1262 x W 800 x D 430	**NSYSFECA64HD**
H 1262 x W 1200 x D 430	2 x **NSYSFECA64HD**
H 1281 x W 600 x D 630	**NSYSFECA66HD**
H 1281 x W 800 x D 630	**NSYSFECA66HD**
H 1281 x W 1200 x D 630	2 x **NSYSFECA66HD**
H 1662 x W 800 x D 430	**NSYSFECA64HD**
H 1662 x W 1200 x D 430	2 x **NSYSFECA64HD**
H 1681 x W 600 x D 630	**NSYSFECA66HD**
H 1681 x W 800 x D 630	**NSYSFECA66HD**
H 1681 x W 1200 x D 630	2 x **NSYSFECA66HD**
H 2062 x W 800 x D 430	**NSYSFECA64HD**

Handle with 1242E cylindrical barrel	References
Handle SFHD 1242E	**NSYSFHS1HD**
Captive screws	**References**
Captive screws for PanelSeT SFHD panels	**NSYCSSFHD**

Note: For PanelSeT SFN HD Spare doors, handle, side and back panels and canopy are available on demand.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Specific Application and Customized Solutions

Spacial SF HD: Outdoor Heavy Duty Enclosures

NSYSFECA64HD



Heavy-Duty cable gland plate for enclosure	References
H 1262 x W 600 x D 430	**NSYSFECA64HD**
H 1262 x W 800 x D 430	**NSYSFECA64HD**
H 1262 x W 1200 x D 430	2 x **NSYSFECA64HD**
H 1281 x W 600 x D 630	**NSYSFECA66HD**
H 1281 x W 800 x D 630	**NSYSFECA66HD**
H 1281 x W 1200 x D 630	2 x **NSYSFECA66HD**
H 1662 x W 800 x D 430	**NSYSFECA64HD**
H 1662 x W 1200 x D 430	2 x **NSYSFECA64HD**
H 1681 x W 600 x D 630	**NSYSFECA66HD**
H 1681 x W 800 x D 630	**NSYSFECA66HD**
H 1681 x W 1200 x D 630	2 x **NSYSFECA66HD**
H 2062 x W 800 x D 430	**NSYSFECA64HD**
Door	**References**
Plain door SFHD 1200 x 600 mm	**NSYSFDHD126**
Plain door SFHD 1200 x 800 mm	**NSYSFDHD128**
Plain door SFHD 1200 x 1200 mm	**NSYSFDHD12122D**
Plain door SFHD 1600 x 600 mm	**NSYSFDHD166**
Plain door SFHD 1600 x 800 mm	**NSYSFDHD168**
Plain door doble SFHD 1600 x 1200 mm	**NSYSFDHD16122D**
Plain door SFHD 2000 x 800 mm	**NSYSFDHD208**

Back Panel	References
SFHD 1200 x 600 mm	**NSYBPHD126**
SFHD 1200 x 800 mm	**NSYBPHD128**
SFHD 1200 x 1200 mm	**NSYBPHD12122D**
SFHD 1600 x 600 mm	**NSYBPHD166**
SFHD 1600 x 800 mm	**NSYBPHD168**
SFHD 1600 x 1200 mm	**NSYBPHD1612**
SFHD 2000 x 800 mm	**NSYBPHD208**
Canopy	**References**
SFHD 600 x 400 mm	**NSYSC64HD**
SFHD 600 x 600 mm	**NSYSC66HD**
SFHD 800 x 400 mm	**NSYSC84HD**
SFHD 800 x 600 mm	**NSYSC86HD**
SFHD 1200 x 400 mm	**NSYSC124HD**
SFHD 1200 x 600 mm	**NSYSC126HD**
Handle with 1242E cylindrical barrel	**References**
Handle SFHD 1242E	**NSYSFHS1HD**
Captive screws	**References**
Captive screws for PanelSeT SFHD panels	**NSYCSSFHD**

Spacial SF PC: Suitable Control PC Rack

NSYSF16660PC



Locks for Partial Doors	References
With 6.5 mm triangular insert for partial and hinged door	**NSYMLT6**
With 6 mm square insert for partial and hinged door	**NSYMLS6**
With 2233X key for partial door	**NSYML23**
With 2233X key for hinged keyboard door	**NSYMLCD23**

7

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys Thermal Management

ClimaSys CE: Exchangers

Exchangers							
							
Exchanger Battery	Fan (Fan + Capacitor)	Frontal Cover RAL 7035 gray	Thermostat	Mounting Kit (instruction + full seal + screws)	Transformer	Solenoid Valve	
Air-AIR exchangers							
References	**References**	**References**	**References**	**References**	**References**	**References**	**References**
NSYCEA22E	**NSYCUSP0177**	**NSYCUSP0042**	**NSYCUSP0181**	-	**NSYCUSP0184**	-	-
NSYCEA36	**NSYCUSP0031**	**NSYCUSP0044**	**NSYCUSP0077**	**NSYCUSP0100**	**NSYCUSP0112**	-	-
NSYCEA50	**NSYCUSP0032**	**NSYCUSP0044**	**NSYCUSP0077**	**NSYCUSP0100**	**NSYCUSP0112**	-	-
NSYCEA80	**NSYCUSP0033**	**NSYCUSP0138**	**NSYCUSP0078**	**NSYCUSP0100**	**NSYCUSP0113**	-	-
Air-WATER exchangers							
References	**References**	**References**	**References**	**References**	**References**	**References**	**References**
NSYCEW1K	**NSYCUSP0034**	**NSYCUSP0043**	**NSYCUSP0079**	**NSYCUSP0100**	**NSYCUSP0114**	-	**NSYCUSP0108**
NSYCEWX1K	-	-	-	**NSYCUSP0100**	**NSYCUSP0114**	-	**NSYCUSP0108**
NSYCEW1K8	**NSYCUSP0035**	**NSYCUSP0044**	**NSYCUSP0080**	**NSYCUSP0100**	**NSYCUSP0124**	-	**NSYCUSP0109**
NSYCEWX1K8	-	-	-	**NSYCUSP0100**	**NSYCUSP0124**	-	**NSYCUSP0109**
NSYCEW2K5	**NSYCUSP0036**	**NSYCUSP0136**	**NSYCUSP0080**	**NSYCUSP0100**	**NSYCUSP0124**	-	**NSYCUSP0109**
NSYCEWX2K5	-	-	-	**NSYCUSP0100**	**NSYCUSP0124**	-	**NSYCUSP0109**
NSYCEW3K5	**NSYCUSP0037**	**NSYCUSP0138**	**NSYCUSP0081**	**NSYCUSP0100**	**NSYCUSP0115**	-	**NSYCUSP0109**
NSYCEW4K5	**NSYCUSP0038**	**NSYCUSP0137**	**NSYCUSP0081**	**NSYCUSP0100**	**NSYCUSP0115**	-	**NSYCUSP0109**
NSYCEW6K	**NSYCUSP0039**	**NSYCUSP0137**	**NSYCUSP0082**	**NSYCUSP0100**	**NSYCUSP0125**	-	**NSYCUSP0109**
NSYCEW6K2P4	**NSYCUSP0040**	**NSYCUSP0137**	**NSYCUSP0082**	**NSYCUSP0100**	**NSYCUSP0125**	**NSYCUSP0107**	**NSYCUSP0109**
NSYCEW2K5R	**NSYCUSP0041**	**NSYCUSP0053**	**NSYCUSP0084**	**NSYCUSP0100**	**NSYCUSP0117**	-	**NSYCUSP0109**

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

ClimaSys CU: Cooling Units

Cooling units: Side-mounted models							
 NSYCUSP001DG	 NSYCUSP003DG	 NSYCUSP002DG	 NSYCUSP004DG	 NSYCUSP010DG	 NSYCUACC041DG	 NSYCUACC042DG	
Condenser Fan Kit	Condenser Fan Kit	Evaporator Fan Kit	Evaporator Fan Kit	Controller Kit	Accessory box	Reduced Noise Condenser Fan Kit*	
References	**References**	**References**	**References**	**References**	**References**	**References**	**References**
NSYCU350DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUX350DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU600DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUX600DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU800DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU8002P4DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1KDG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCUX1KDG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1K2P4DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCUX1K2P4DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1K2DG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1K22P4DG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1K6DG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCUX1K6DG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU1K62P4DG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU2KDG	-	**NSYCUSP005DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCU2K3P4DG	-	**NSYCUSP007DG**	-	**NSYCUSP006DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	**NSYCUACC042DG**
NSYCUX2K3P4DG	-	**NSYCUSP007DG**	-	**NSYCUSP006DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU3K2DG	-	**NSYCUSP008DG**	-	**NSYCUSP005DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU3K23P4DG	-	**NSYCUSP009DG**	-	**NSYCUSP007DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU4K3P4DG	-	**NSYCUSP009DG**	-	**NSYCUSP007DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU600RDG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU800RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU8002P4RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU1K2RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU1K22P4RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU1K5RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU1K52P4RDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU2KRDG	-	**NSYCUSP003DG**	-	**NSYCUSP003DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU2K3P4RDG	-	**NSYCUSP006DG**	-	**NSYCUSP006DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU3K3P4RDG	-	**NSYCUSP009DG**	-	**NSYCUSP007DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCU4K3P4RDG	-	**NSYCUSP009DG**	-	**NSYCUSP007DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD350DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD600DG	**NSYCUSP001DG**	-	**NSYCUSP002DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD800DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD1KDG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD1K2P4DG	-	**NSYCUSP003DG**	-	**NSYCUSP004DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD1K6DG	-	**NSYCUSP005DG**	**NSYCUSP003DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD1K62P4DG	-	**NSYCUSP005DG**	**NSYCUSP003DG**	-	**NSYCUSP010DG**	**NSYCUACC041DG**	-
NSYCUHD2K3P4DG	-	**NSYCUSP007DG**	-	**NSYCUSP006DG**	**NSYCUSP010DG**	**NSYCUACC041DG**	-

* Compatible with NSYCU••DG cooling units from 800w to 2kw

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Useful Technical Information

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Useful Technical Information

Enclosures and Thermal Management Systems Certifications	594
International Enclosure Standards	595
Selection of Enclosures	597
Degrees of Protection Provided by Enclosures	598
Classification of Electrical Equipment	599
Painting Properties	600
Properties of Plastic Materials	601
Description of Marking Label Affixed	603

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Enclosures and Thermal Management Systems Certifications

Range	Empty assemblies					Equipped assemblies
	Empty assemblies for low-voltage switchgear	Standards for industrial equipment and UL classification	Marine environment classification or approval for protection and resistance to vibrations	Enclosures installed in a potentially explosive atmosphere	Outdoor heavy-duty enclosures	Low-voltage switchgear and controlgear assemblies
	Standard/Directive					
	IEC 62208	UL508A and CAN CSA C22-2 no. 14	Compliance with requirements of certified bodies	European directive no. 2014/34/UE EN60079-0 / EN60079-7 EN60079-3 / EN60529	IEC 61439-5 (7) ISO 12944-6	IEC61439-1 and 2
PanelSeT - Steel and Stainless Steel Enclosures						
SBM	●	●	●			
S3D	● ●	●	●			
CRN	●	●	●			
S3DEX		●		●		
S3HF		●				
S3HD	●	●			●	
S3CM		●				
SM	● ●	●	●			
SFN	● ●	●	●			●
SFHD	● ●	●			●	●
PrismaSeT HD	●					●
SBX	●	●	●			
S3X	●	●	●			
SMX	●	●	● (3)			
SFX	● (3)	●	● (3)			
PanelSeT - Polyester Enclosures						
TBS/TBP	●	● (1)				
PLS	●	●				
PLM	● ●	●	●			
PLA	● ●	●	●			● (6)
PLAT	● ●					
PLAZ	● ●					
PLAZT	● ●					
PHD	●	●			● (2)	
ClimaSys (4)						
CV		●				
CU		●				
CE		●				
CR		● (5)				
CC		●				

(1) Only TBP.
(2) ISO 12944-6 only applies to the PanelSeT enclosures.
(3) Only for single-door versions
(4) EAC-compliant
(5) The insulated and aluminum resistance heaters of 12-24 V DC and 270-420 V AC are not certified
(6) Valid for specific architectures
(7) Only for mechanical strength test
For other certifications and declarations of conformity please consult us.

Official Certification Body

Bureau Veritas	LCIE (Bureau Veritas)	Bureau Veritas Marine Division	TUV Rheinland Group	Underwriters Laboratories	Laboratorio Oficial J.M. Madariaga	DNV-GL	Dekra	Asefa
●	●	●	●	●	●	●	●	●

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

The Main 10 Functions of Standard IEC 61439

For each of the following 10 functions, the standard IEC 61439 requires design verifications from the system manufacturer - mainly through type-tests defined in IEC 62208 - and routine verifications on each panel from the panel builder to achieve 3 basic goals: Safety, continuity of service and compliance with end-user requirements.

Safety

Voltage stresses withstand capability

- To withstand long term voltages, and transient and temporary overvoltages according to the insulation coordination principles and requirements.

Current-carrying capability

To help protect against fire and to withstand temperature rise:

- When any circuit is continuously loaded, alone, to the specified current
- When the assembly is loaded to the specified current according to the specified load pattern (between circuits and/or as a function of the time).

Short-circuit withstand capability

- To withstand the stresses resulting from the prospective short-circuit current and from the associated data (high forces between conductors, temp. rise in a very short time, air ionization, overpressure).

Protection against electric shock

- Hazardous live parts not to be accessible (basic protection).
- Accessible conductive parts not to become hazardous-live (fault protection).

Protection against risk of fire or explosion

- Resistance to internal glowing elements.

Comment: Protection of people, and optional protection of the assembly, against arcing due to internal fault can be specified through a "special test" according to IEC 61641.

Continuity of Service

Maintenance and modification capability

Capability to preserve continuity of supply without impairing safety during assembly, maintenance or modification.

- Electrical condition of the assembly or various circuits.
- Speed of exchange of the functional units.
- Test facilities…

Electro-Magnetic Compatibility

To properly function (immunity) and not to generate EM interference (emission) in specified environmental conditions:

- Industrial networks or locations (Environment A).
- Domestic, commercial, and light industrial locations (Environment B).

Compliance with End-User Requirements

Capability to operate the electrical installation

To properly function, according to:

- The electrical diagram of the overall system and related information (voltages, coordination…),
- The specified operating facilities (e.g. free or restricted access to man-machine interfaces, isolation of the outgoing circuits…).

Capability to be installed on site

- To withstand handling, transport, storage and installation constraints.
- Capability to be set up and connected (type of enclosure, type, material and cross-sectional areas of external conductors).

Protection of the assembly against mechanical and atmospheric ambient conditions

- Presence of water or solid foreign bodies (IP according to IEC 60529).
- External mechanical impacts (optional IK according to IEC 62262).
- Indoor or outdoor installation (humidity, UV).

Both the Point of Arrival of Energy and a Device for Distribution to the Site Applications, the LV Switchboard Is the Intelligence of the System, Central to the Electrical Installation.

It plays an essential role in the availability of electric power, while meeting the needs of personal and property safety. Its definition, design and installation are based on precise rules; There is no space for improvisation. The IEC 61439 standard aims to better define "low-voltage switchgear and controlgear assemblies", helping ensure that the specified performances are reached. It specifies in particular:

- The responsibilities of each player, distinguishing those of the original equipment manufacturer; the organization that performed the original design and associated verification of an assembly in accordance with the standard, and of the assembly manufacturer - the organization taking responsibility for the finished assembly
- The design and verification rules, constituting a benchmark for product certification All the component parts of the electrical switchboard are concerned by the IEC 61439 standard. Equipment produced in accordance with the requirements of this switchboard standard helps ensure the safety and reliability of the installation.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

International Enclosure Standards

Standards IEC 62208,

PB500056_57_nb



Comment:
European standard EN 62208 is identical to IEC 62208. European countries publish this standard according to the body in each country (for example BS EN 62208 in the UK).

Empty Enclosures for Low-Voltage Switchgear and Controlgear Assemblies. General Rules.

Application
For empty enclosures before adding the user's switchgear, in the condition as supplied by the manufacturer.

Field of application
Demands for testing the enclosures to be used as part of the switchgear assemblies for voltages of less than 1000 V alternating current and 1500 V direct current in accordance with IEC 61439.

Information supplied by the manufacturer
- Commercial trademark of the manufacturer: Schneider Electric.
- Mechanical characteristics, materials, conditions for use.
- Conditions for use: Ambient air temperature for outdoor installations: -25 to +40 °C.
- Atmospheric conditions for outdoor installations: The humidity may temporarily reach 100% at a temperature of 25 °C.
- Transport and storage conditions: From -25 to +55 °C; For limited periods not exceeding 24 h: Up to +70 °C.

PB500057_57_nb



Standard Tests of Standard IEC 62208

- Static loads: Test 1.25 x maximum admissible load during 1 hour.
- Lifting: Applicable to enclosures with lifting accessories.
- Axial loads of metal inserts: 500 N for 10 seconds for M8 inserts.
- IK code: Test according to standard IEC 62262 with pendulum impact tester. The enclosure must maintain its IP rating after the test.
- IP rating: Test according to standard IEC 60529. Degree of protection against access to dangerous parts and the penetration of solid bodies and against the penetration of water.
- Thermal stability at a temperature of 70 °C: 7 days.
- Resistance to heat: Ball test at 70 °C.
  Information required for enclosures made from insulated material.
- Resistance to abnormal heat and to fire: Glow wire test according to IEC 60695-2-10 and IEC 60695-2-11.
  Information required for enclosures made from insulated material.
- Dielectric strength: 5000 V
  Information required for enclosures made from insulated material.
- Protection circuit continuity for metal enclosures: Resistance not to exceed 0.1 ohm.
- Weather resistance: Duration 500 h (cycle: Rain 5 minutes + UV lamp 25 minutes).

Corrosion resistance:
Severity Test A:
- 6 cycles of 24 hours of the damp heat test at 40 °C and relative humidity of 95%.
- 2 cycles of 24 hours of the salt mist test at 35 °C.

Severity Test B:
2 identical 12 day periods. Each one with:
- 5 cycles of 24 hours of the damp heat test at 40 °C and relative humidity of 95%.
- 7 cycles of 24 hours of the salt mist test at 35 °C.

Our empty enclosures are CE-marked according to the Low-Voltage Directive (LVD). It is the responsibility of the final equipment manufacturer to respect regulations in force.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Selection According to the IP Protection Degrees

The degrees of protection, explained on the next page, is an important element when selecting the enclosures. The following table shows the protection degrees of the enclosures.

Name	Range	IP43	IP44	IP54	IP55	IP65 [7]	IP66
Metal industrial boxes	PanelSeT SBM						●
Metal derivation boxes	PanelSeT SDB				●		
Stainless-steel boxes	PanelSeT SBX						●
Steel wall-mounted enclosures	PanelSeT S3D				● [1]		●
Steel modular distribution wall-mounted enclosures	PanelSeT S3DM						●
Terminal wall-mounted enclosures	PanelSeT S3DB						●
Steel wall-mounted enclosures	PanelSeT S3HF				●		
Steel wall-mounted enclosures	PanelSeT CRN				● [1]		●
EMC steel floor-standing enclosures	PanelSeT SFHF				●		
HMI control enclosures	PanelSeT S3CM			●			
ATEX steel wall-mounted enclosures	PanelSeT S3DEX						●
Steel outdoor wall-mounted enclosures	PanelSeT S3HD						●
Stainless-steel wall-mounted enclosures	PanelSeT S3X				● [1]		●
Seismic and nuclear enclosures	PanelSeT S3D6G / PanelSeT S3D6GK3					●	
Terminal enclosures with FL21 cut-out	PanelSeT S3DBFL					● [6]	
Steel floor-standing enclosures	PanelSeT SM				●		
Steel suitable enclosures	PanelSeT SFN				●		
Steel outdoor floor-standing enclosures	PanelSeT SFN HD				●		
Stainless-steel floor-standing enclosures	PanelSeT SMX						● [7]
Stainless-steel suitable enclosures	PanelSeT SFX						● [7]
Functional steel floor-standing enclosures	PrismaSeT HD				●		
Steel control desks	PanelSeT SD				●		
Thermoplastic industrial boxes	PanelSeT TBS-TBP				● [4]		● [5]
Polyester modular boxes	PanelSeT PLS						●
Polyester wall-mounted enclosures	PanelSeT PLM						●
Polyester outdoor wall-mounted enclosures	PanelSeT PHD					●	
Polyester floor-standing enclosures	PanelSeT PLA [2]		●	●		●	
Polyester outdoor wall-mounted enclosures	PanelSeT PHD					●	
Polyester outdoor floor-standing enclosures	PanelSeT PHD				●		

[1] Double-door.
[2] Different IP depending on the version. See introduction in PanelSeT section: PLA: IP65, PLAT / PLAZT: IP44, PLAZ: IP54, PLAT / PLAZT only with grille: IP54.
[3] With gasket.
[4] Button boxes.
[5] Universal boxes.
[6] With membrane mounted.
[7] Single-door enclosure.

The Universal Offer

> 3 Material Options

Steel

Stainless-Steel

Plastic and Polyester

Selection According to Ambient Conditions

The location of the enclosures and the physical, chemical and climatic conditions to which they are exposed will determine the model to be used.

Steel enclosures are particularly well suited to indoor use in industrial environments.
Stainless-steel enclosures are particularly well suited to corrosive environments or areas where specific hygiene demands are applicable.
Polyester enclosures are particularly well suited to severe corrosive atmospheres, indoors or outdoors.

Enclosures made from insulated materials that helps ensure total insulation, reducing electric hazards for people.
The main characteristics of the plastic materials of our enclosures and their chemical strength are given on page 601.









Further help for making the selection is given by the NEMA or UL classification of the enclosure, see page 599.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Degrees of Protection Provided by Enclosures

- The degrees of protection provided by the enclosures are defined by standards IEC 60529 (IP) and IEC 62262 (IK).
- Degrees of protection are indicated by the letters IP followed by two characteristic numerals. The numerals show the degree of protection offered by the enclosure against access to hazardous parts, the penetration by solid bodies (1st numeral), and against the penetration of liquids (2nd numeral).
- The protection against external mechanical impact is indicated by the letters IK followed by a characteristic group numeral.

Comment:
Many EN European standards are harmonized with international IEC standards.
This is the case with enclosure protection standards:
- EN 60529 = IEC 60529
- EN 62262 = IEC 62262

	IP	IK
First numeral Protection against solid bodies	**Second numeral Protection against liquids**	**Mechanical protection**
0 No protection	**0** No protection	**0** No protection
1  Protected against solid bodies larger than 50 mm (e.g.: Incidental contact with the hand)	**1**  Protected against vertically falling water droplets (condensation)	**1**  Impact energy: 0.150 Joules
2  Protected against solid bodies larger than 12 mm (e.g.: Finger contact)	**2**  Protected against water droplets deflected at up to 15° from vertical	**2**  Impact energy: 0.200 Joules
3  Protected against solid bodies larger than 2.5 mm (tools, cables)	**3**  Protected against rainwater at up to 60° from vertical	**3**  Impact energy: 0.350 Joules
4  Protected against solid bodies larger than 1 mm (fine tools, small cables)	**4**  ⚠ Protection against water spray from all directions	**4**  Impact energy: 0.500 Joules
5  ❖ Protected against dust (no harmful deposits)	**5**  ⚠⚠ Protected against low-pressure water jets from all directions	**5**  Impact energy: 0.700 Joules
6  ❖ Totally dust tight	**6**  Protected against powerful water jets from all directions	**6**  Impact energy: 1.00 Joules
	7  ⬍⬍ Protected against the effects of immersion	**7**  Impact energy: 2.00 Joules
	8  ⬍⬍ ... m Protected against prolonged effects of immersion under pressure	**8**  Impact energy: 5.00 Joules
		9  Impact energy: 10.00 Joules
		10  Impact energy: 20.00 Joules

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Classification of Electrical Equipment

Classification of Electrical Equipment Enclosures According to NEMA and UL

NEMA and UL are standardization bodies, commonly recognized in North America, which have issued classifications of enclosures according to the protection offered in various environments. These classifications are similar.

Enclosures		Type of protection [1]													
Name	Range	1	2	3	3R	3S	3X	3RX	3SX	4	4X	5	6	12	13
Metal industrial boxes	SBM									●	●				
Stainless-steel industrial boxes	SBX									●	●				●
HMI control enclosures	S3CM	●	●		●									●	●
Steel wall-mounted enclosures	S3D [1]	●	● [2]	● [2]	● [2]					● [2]	● [2]	● [2]		●	● [2]
Steel wall-mounted enclosures	S3HF	●	●	●	●									●	●
Steel outdoor wall-mounted enclosures	S3HD	●	●	●	●					●	●	●		●	●
Steel wall-mounted enclosures	CRN	●	● [2]	● [2]	● [2]					● [2]		● [2]		●	●
Stainless-steel wall-mounted enclosures	S3X	●	● [2]	● [2]	● [2]					● [2]	● [2]	● [2]		●	● [2]
Steel floor-standing enclosures	SM	●	● [2]	● [2]	●							● [2]		●	●
Polyester heavy-duty	PHD	●	●	●	●					● [2]	● [2]	●		●	●
Steel suitable enclosures	SFN	●			●									●	
Steel outdoor floor-standing enclosures	SFN HD	●			●									●	
Stainless-steel floor-standing enclosures	SMX	●	● [2]	● [2]	● [2]					● [2]	● [2]	● [2]		●	●
Stainless-steel floor-standing enclosures	SFX	●	● [2]	● [2]	● [2]					● [2]	● [2]	● [2]			● [2]
Thermoplastic boxes	TBP	●		●		●				●	●				
Polyester modular boxes	PLS	●	●	●	●	●				●	●			●	●
Polyester wall-mounted enclosures	PLM	●	●	●	●	●				●	●	●		●	●
Polyester floor-standing enclosures	PLA	●	●	● [2]	●	● [2]	● [2]	●	● [2]			●		●	●

[1] Also S3DM, S3DC.
[2] 1 door.

Components		Type of protection [5]											
Name	Range	1	2	3	3R	3S	4	4X	5	6	6P	12	13
Airing system	CV											● [3]	
Thermal control system	CC	● [3]											

[3] In some ranges the classification depends on the model and version. The detailed protection types are indicated in the UL certifications.

8

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Painting Properties

Polyester Base-Painting Properties

Product type
Thermosetting polyester resins based powder painting modified by epoxy resins and designed for decoration and to help prevent corrosion. The performance of this painting is superior to conventional epoxy powders in terms of color stability, temperature resistance and weather resistance. RAL 7035 gray; Surface finish: Structured.

Mechanical properties
Testing conditions: Steel samples with a thickness of 10/10^{e} mm. Degreasing using biodegradable surface-active agents. Film thickness: 60 microns.

Bonding (scratching and adhesive tape)	ISO 2409	≥ to Class 1
Ericksen stamping	ISO 1520	≥ 7 mm
Direct impact resistance	ISO 6272	> 1 kg/70 cm
Indirect impact resistance	ISO 6272	> 1 kg/20 cm
Bending around conical mandrel	ISO 6860 - ASTM D 522-88	Maximum cracking of 70 mm, without the paint coming loose

Chemical properties
Tests conducted at ambient temperature on phosphated samples covered with a 70 to 100 micron film:

Film intact.
Film attacked (blistering, yellowing, loss of gloss).

Number of months			2	4	6	8	10	12
Acid	Acetic	20%						
	Sulphuric	30%						
	Nitric	30%						
	Phosphoric	30%						
	Hydrochloric	30%						
	Lactic	10%						
	Citric	10%						
Base	Soda	10%						
	Ammonia	10%						
Water	Distilled water							
	Sea water							
	Tap water							
	Diluted chloride bleach							
Solvents	Petrol							
	Higher-grade alcohols							
	Aliphatics							
	Aromatics							
	Ketone-ester							
	Tri-perchlorethylene							

Physical properties
Temperature resistance: -40 °C and 100 hours at +150 °C (color: White). Gloss retention: Good.


Resistance to corrosion
Compliance with standard IEC 62208 for outdoor installations: 288 h of humid heat and 336 h of salt mist.

Nuclear decontamination
Applicable to colors RAL 7035 gray and AFNOR A550.
Standard NFT 30901. Percentage of decontamination for contamination by fission products. Please consult us for further details.

Accelerated aging
Standard IEC 62208: 500 h UV according to ISO 4892 (method A) (adherence of the painting with minimum retention of 50% on the grid according to ISO 2409).

Fire behaviour
Class M1 (self-extinguishing material).
Class M0 (for painting on a metal base).

Manufacturing process



Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Properties of Plastic Materials

Properties of Plastic Materials - Mechanical, Electrical, Physical and Fire-Resistance Properties

Plastic materials generally used to manufacture our products:

- ABS.
- Polycarbonate.
- PVC (polyvinyl chloride).
- Bayblend® = PC + ABS.
- Polyester reinforced with fiberglass.
- Altuglas.
- Polypropylene.
- Polystyrene.
- Polyamide 6 and 12.
- SBS.

Comment:
For other chemical agents, please contact us.
All information provided here is taken from the sources and provided for information purposes only, with no commitment on our behalf.

Specifications	Standards	Units	ABS	Polycarbonate	PVC	Bayblend®	Polyester	SBS
Mechanical properties								
Tensile strength	ISO 257	MPa	44	> 65	45	35	85	5
Tensile strain	ISO 527	%	12	> 110	120 bis 150	40	0	600
Impact resistance	ISO 179	kJ/m²	125	No breakage	25	No breakage	60	No breakage
Notching resistance	ISO 179	kJ/m²	19	25	20	25	50	-
Electrical properties								
Stress point	IEC 60112	-	-	250-300	> 600	> 550	> 600	-
Surface strength	IEC 60093	Ω	1015	> 1015	> 1013	> 1014	≥1012	> 1013
Dielectric strength	IEC 60243	kV/mm	16.5	> 30	30	24	18-20	20
Specific resistivity	IEC 60093	Ω³cm	1015	> 1016	≥ 1015	1016	≥ 1012	> 1016
Physical properties								
Softening temperature (Vicat B)	ISO 306	°C	95	145-150	79-80	115	(1)	80
Temperature resistance	-	°C	-40...+90	-50...+125	-20...+65	-35...+90	-50...+150	-40...+120
Water absorption	ISO 62	%	0.2 - 0.45	0.15	< 0.1	0.2	0.2	-
Specific weight	ISO 1183	kg/dm³	1.04	1.21	1.4	1.12	1.85	0.3 in 24 h
Fire resistance								
Oxygen index	ISO 4589	%	19	26	45-50	22	24.4	18
Glow wire resistance, 2 mm	IEC 60695-2-10	°C	650	960	960	750	960	750° (1.5 mm)
Glow wire resistance, 3 mm	IEC 60695-2-10	°C	650	960	960	750	960	NA

(1) No softening of the polyester.

Specifications	Standards	Units	Altuglas	Polypropylene	Polystyrene	Polyamide 6	Polyamide 12
Mechanical properties							
Tensile strength	ISO 257	MPa	30	35	24	40	30
Tensile strain	ISO 527	%	5	400	36	200	300
Impact resistance	ISO 179	kJ/m²	20	20	63	No breakage	No breakage
Notching resistance	ISO 179	kJ/m²	3	5	50	31.2	15
Electrical properties							
Stress point	IEC 60112	-	-	-	KB175	KB175	KB180
Surface strength	IEC 60093	Ω	≥ 1014	-	> 1013	1012	5 x 1010
Dielectric strength	IEC 60243	kV/mm	13-15	20	≤ 40	23	55
Specific resistivity	IEC 60093	Ω³cm	> 1015	> 1016	> 1015	1011	3 x 1011
Physical properties							
Softening temperature (Vicat B)	ISO 306	°C	120-122	75 (vicat A)	79	230	140
Temperature resistance	-	°C	-20...+80	-10...+80	-15...+60	-20...+100	-50...+125
Water absorption	ISO 62	%	< 0.5	0.1 in 24 h	0.1 in 24 h	1.6	1.5
Density	ISO 1183	kg/dm³	1.18	0.91	1.06	1.14	1.03
Fire resistance							
Oxygen index	ISO 4589	%	18.5	18	18	24	22
Glow wire resistance, 2 mm	IEC 60695-2-10	°C	-	650	650	750	650
Glow wire resistance, 3 mm	IEC 60695-2-10	°C	960	650	650	850	650

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Properties of Plastic Materials

Properties of Plastic Materials - Resistance to Chemical Agents

Plastic materials generally used to manufacture our products:

- ABS.
- Polycarbonate.
- PVC (polyvinyl chloride).
- Bayblend® = PC + ABS.
- Polyester.
- Altuglas.
- Polypropylene.
- Polystyrene.
- Polyamide 6 and 12.
- SBS.

The table shows:

The concentration of the chemical agent in %;

- Sat = saturation.

The resistance of the material:

- +: Resistant.
- O: Limited resistance.
- –: Not resistant.

Resistance to	ABS		Polycarbonate		PVC		Bayblend®		Polyester		Altuglas		Polypropylene		Polystyrene		Polyamide 6		Polyamide 12		SBS	
Acetone		–		–		–		–		–		O	100	+		–	100	+		+		+
Hydrochloric acid	15	+	10	+	30	+	20	+	30	+	sat	+	10	+		O	10	–	10	+	10	+
Citric acid			10	+	sat	+	10	+	100	+	sat	+	sat	+		+	10	O		+	10	+
Lactic acid	80	+	10	+	90	+	10	–	100	+	20	+	90	+		O	50 90	O –		+ +	sat	+
Nitric acid	30	+	10 100	+ –	50	+	10	+	20	+ +	10 100	+ –	25/ 50			O	2 10	O –		–	50	+
Phosphoric acid	85	+	100	+	sat	+		+	100	+	10 95	+ –	sat	+		O	2 10	O –	50	+		+
Sulphuric acid	50	+	50 100	+ –	96	+	30	+	70	+	30	+	96	+		O	3	–	10	+	96	+
Alcohol		O	96	+	96	+		–	50	O	50	O	96	+		+	96	O	96	+		+
Pure aniline		O		–	100	–		–		O		–	100	+			100	O	100	O		
Benzene		+	100	–		–		+		–		O	100	O			100	+		+		–
Liquid bromine			100	–		–		–					100	–					100	–		–
Liquid chlorine				-	100	-		-	sat	+		–	100	–			100	O		–	50	+
Sea water		+	100	+	100	+		+	100	+	100	+		–	100	+			100	+	sat	+
Petrol		+	100	+	100	O		–	100	+	100	O		–		–	100	+		+		–
Ether		–	100	O	100	–		–	100	O		+					100	+	100	+		–
Hexane		O		+		O		O		–			100	+			100	+	100	+		–
Oil and greases		+	100	+	100	+		O	100	+	100	O	100	+		–		+	100	+		–
Aromatic hydrocarbon		O		–		–		–		–		+	–			–		–		+		–
Fuel oil		O	100	O	100	+		–	100	+	100	–	100	+			100	+	100	+		–
Naphthalene					100	O		–	100	+	100	–	100	+			100	+	100	+		
Nitrobenzene		–		–	100	–		–				–	100	O				–		O		–
Phenol		–		–	sat	O		–	20	O		–	sat	+				–		–	10	O
Mineral salts				+		+		+		+		+		+						+		+
Iodine solution				O		–		+				–						+				
Toluene		–		–	100	–		–		+		O	100	O		–	100	+	100	+		–
Trichloroethylene		–		–	100	–		–		–		–	100	O		–	100	–	100	O		–
Urea			sat	+	sat	+		+					sat	+			10	+	sat	+	sat	O

Comment:
For other chemical agents please contact us.
All information provided here is taken from the sources and provided for information purposes only, with no commitment on our behalf.


8

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Description of Marking Label Affixed

Description of Marking Labels on ATEX-Certified Wall-Mounted Enclosures

Panel**SeT** S3DEX



1
Range of the product with its dimensions

2
100123456 71: exemple of the serial number
1711: exemple of the year and the month of the manufacturing

3
Address of manufacturer

4
0081: identification number of the notified body for the application of the ATEX directive
Ex: distinctive mark indicating that the product is authorized in an explosive atmosphere
II: Industry group (II = surface industries)
2: device category (2 = occasional presence, Zone 1 or 21)
G: atmosphere type (G = gases and vapors)
D: atmosphere type (D = dust)

5
Ex: symbol that indicates the product complies with one or several protection modes
eb: protection level of type of protection "e" for increased safety (EN 60079-7)
II C: group of gaz (hydrogen/acetylene)
Gb: type of protection for non-electric material (control of power supply)
G = gaz

6
Ex: symbol indicating that the product complies with one or several protection types
tb: protection level of type of protection "t" per enclosure (EN 60079-31)
III C: type of dust (conductive dust)
Db: type of protection for non-electric material (control of power supply)
D = dust

7
Number of the EC type examination certificate
(Included the name of the certification body)

Download our ATEX certificates from our site.

Technical changes reserved. Information provided without guarantee. Images are for illustrative purposes only.

Index of References

13...	Page
13934	124, 125, 464
AF...	Page
AF1CF34	534
AF1CF56	534
AF1CG4	533
AF1CG5	533
AF1CG6	533
AF1EA3	517, 523
AF1EA4	523
AF1EA5	523
AF1EA6	517, 523
AF1VA612	530
AF1VA618	530
AF1VC820	530
AK...	Page
AK2CA3	507
AK2CA6	507
AK2CD25	507
AK2CD37	507
AK2CD50	507
AK2CD75	507
AK2CD100	507
AK2CD125	507
AK2GA33	506
AK2GA35	506
AK2GA39	506
AK2GA65	506
AK2GA69	506
AK2GA315	506
AK2GA615	506
AK2GD2525	506
AK2GD2550	506
AK2GD3750	506
AK2GD3775	506
AK2GD5050	506
AK2GD5075	506
AK2GD7550	506
AK2GD7575	506
AK2GD10075	506
AK2GD12575	506
AM...	Page
AM1DL201	532
AM1EA200	532
AM1EC200	537
AM1PA3020	511
AM1PA3070	511
AM1PA6040	511
AM1PA6050	511
AM1PA6060	511
AM1PA9060	511
AM1PA9070	511
ATV...	Page
ATV630D11M3	383
ATV630D15M3	383
ATV630D18M3	383
ATV630D22M3	383
ATV630D30M3	383
ATV630D37M3	383
ATV630D45M3	383
ATV930D11M3	383
ATV930D15M3	383
ATV930D18M3	383
ATV930D22M3	383

ATV...	Page
ATV930D30M3	383
ATV930D37M3	383
ATV930D45M3	383
ATV630D11N4	383
ATV630D15N4	383
ATV630D18N4	383
ATV630D22N4	383
ATV630D30N4	383
ATV630D37N4	383
ATV630D45N4	383
ATV630D55N4	383
ATV630D75N4	383
ATV630D90N4	383
ATV930D11N4	383
ATV930D15N4	383
ATV930D18N4	383
ATV930D22N4	383
ATV930D30N4	383
ATV930D37N4	383
ATV930D45N4	383
ATV930D55N4	383
ATV930D75N4	383
ATV930D90N4	383
ATV340D30N4E	383
ATV340D37N4E	383
ATV340D45N4E	383
ATV340D55N4E	383
ATV340D75N4E	383
ATV630U07M3	383
ATV630U15M3	383
ATV630U22M3	383
ATV630U30M3	383
ATV630U40M3	383
ATV630U55M3	383
ATV630U75M3	383
ATV930U07M3	383
ATV930U15M3	383
ATV930U22M3	383
ATV930U30M3	383
ATV930U40M3	383
ATV930U55M3	383
ATV930U75M3	383
ATV630U07N4	383
ATV630U15N4	383
ATV630U22N4	383
ATV630U30N4	383
ATV630U40N4	383
ATV630U55N4	383
ATV630U75N4	383
ATV930U07N4	383
ATV930U15N4	383
ATV930U22N4	383
ATV930U30N4	383
ATV930U40N4	383
ATV930U55N4	383
ATV930U75N4	383
AX...	Page
AX2DL01	523
AZ...	Page
AZ1CA04	519
DX...	Page
DX1AP52	523

DZ...	Page
DZ5ME5	533
DZ5ME8	533
DZ5ME9	533
DZ5MF6	529
DZ5MF8	529
DZ5MS10	536
DZ6MZ211	529
IMT...	Page
IMT36150	489
IMT36151	497
IMT36152	497
IMT36153	497
IMT36154	497
IMT36155	497
IMT36158	497
IMT36161	497
IMT36162	497
IMT36163	497
IMT36164	497
IMT36167	497
IMT36168	497
IMT36169	497
IMT36179	489
IMT36180	489
IMT36181	489
IMT36182	489
IMT36183	489
IMT36184	489
IMT36185	489
ISM...	Page
ISM71071	488
ISM71072	488
ISM71073	488
ISM71074	488
ISM71501	489
ISM71502	489
ISM71503	489
ISM71504	489
ISM71505	489
ISM71506	489
LVS...	Page
LVS01109	188, 191, 219
LVS01130	193, 248
LVS01215	249, 251
LVS03583	195
LVS04229	193, 248
LVS04502	188, 191, 219, 222
LVS04503	188, 191, 219, 222
LVS04504	188, 191, 219
LVS04505	188, 191, 219, 222
LVS04506	188, 191, 219
LVS04509	189
LVS04510	189
LVS04512	222
LVS04515	222
LVS04516	190, 192, 221, 246
LVS04518	190, 192, 221, 246
LVS04525	190, 192, 221, 246
LVS04526	190, 192, 221, 246
LVS04528	190, 192, 221, 246
LVS04550	190, 221
LVS04560	186, 189, 217, 220, 244, 245

LVS...	Page
LVS04561	186, 189, 217, 220, 244, 245
LVS04562	186, 189, 217, 220, 244, 245
LVS04563	186, 189, 217, 220, 244, 245
LVS04564	186, 189, 217, 220, 244, 245
LVS04565	186, 189, 217, 220, 244, 245
LVS04566	186, 189, 217, 220, 244, 245
LVS04567	186, 217, 220, 244, 245
LVS04568	186, 217, 220, 244, 245
LVS04602	188, 191, 219, 222
LVS04603	188, 219
LVS04604	189, 220, 244
LVS04605	189, 220, 244
LVS04607	189, 220, 244
LVS04620	186, 217, 245
LVS04621	186, 217, 245
LVS04623	186, 217, 245
LVS04624	186, 187
LVS04634	188, 219
LVS04635	188, 191, 192, 219
LVS04636	188, 190-192, 219, 221, 222, 246
LVS04637	190, 221, 246
LVS04638	188, 190, 219, 221
LVS04640	187, 218, 247
LVS04641	187, 218, 247
LVS04642	188, 190-192, 219, 221, 246
LVS04643	187, 218
LVS04645	190, 221, 246
LVS04646	186, 217, 218, 220, 244, 245
LVS04651	188, 219
LVS04652	191
LVS04653	192
LVS04656	222
LVS04658	189, 220, 244
LVS04659	189, 220, 244
LVS04664	186, 187
LVS04669	192
LVS04671	186, 187, 189, 190
LVS04672	222
LVS04678	189, 190, 211
LVS04742	223
LVS04743	223
LVS04746	223
LVS04751	223
LVS04753	223
LVS04759	193, 248
LVS04766	193, 222, 248
LVS04767	193, 248
LVS04768	193, 248
LVS04769	193, 248
LVS04772	193, 248
LVS04773	193, 248
LVS04774	193, 248
LVS04775	193, 248
LVS04782	193, 248
LVS04783	193, 248
LVS04784	193, 248

Index of References

LVS...	Page
LVS04785	193, 248
LVS04786	193, 248
LVS04787	193, 248
LVS04788	193, 248
LVS04794	193, 248
LVS04901	195
LVS04924	194
LVS04943	195
LVS04946	196
LVS04951	196
LVS04952	196
LVS04955	195
LVS04956	195
LVS06461	198
LVS06540	194, 249
LVS06541	194
LVS06543	194
LVS06545	194
LVS06555	194
LVS06560	194
LVS06561	194, 249
LVS06563	194, 249
LVS06567	194
LVS06568	194, 249
LVS06570	194
LVS06600	196
LVS06601	196
LVS06604	196
LVS06605	196
LVS06606	196
LVS06607	196
LVS08566	197
LVS08881	497
LVS08892	497
LVS08895	497
LVS08897	497
LVS08898	497
LVS08899	497
LVS08911	198

NSY...	Page
NSY17990	402
NSY17991	402
NSY17992	402
NSY17996	399
NSY17997	399
NSY17998	399
NSY1TH	538
NSY2SPINHD184	327
NSY2SPINHD186	327
NSY2SPINHD188	327
NSY2SPINHD204	327
NSY2SPINHD206	327
NSY2SPN124	75, 76, 461
NSY2SPN125	76, 461
NSY2SPN126	75, 76, 293, 461
NSY2SPN128	76, 293, 461
NSY2SPN144	75, 76, 461
NSY2SPN145	76, 461
NSY2SPN146	76, 293, 461
NSY2SPN148	76, 293, 461
NSY2SPN164	76, 461
NSY2SPN165	76, 461

NSY...	Page
NSY2SPN166	75, 76, 260, 293, 461
NSY2SPN168	75, 76, 260, 293, 461
NSY2SPN184	75, 76, 213, 461
NSY2SPN185	75, 76, 213, 461
NSY2SPN186	75, 76, 213, 260, 293, 461
NSY2SPN188	75, 76, 260, 293, 461
NSY2SPN2010	77, 293
NSY2SPN204	75, 77, 213, 461
NSY2SPN205	75, 77, 197, 213, 461
NSY2SPN205ED	197
NSY2SPN206	75, 77, 197, 213, 252, 293, 461
NSY2SPN208	75, 77, 197, 213, 252, 293, 461
NSY2SPN208ED	197
NSY2SPN2210	293
NSY2SPN224	77, 461
NSY2SPN225	77, 461
NSY2SPN226	75, 77, 213, 293, 461
NSY2SPN228	75, 77, 293, 461
NSY2SPX184	461
NSY2SPX204	461
NSY2SPX205	461
NSY2SPX206	461
NSY6G2SPN206	350

NSYA...	Page
NSYADC16	205, 208
NSYADC18	208
NSYADG20M	578, 580
NSYADG2M	578, 580
NSYADG3M	578, 580
NSYADG5M	578, 580
NSYADR200	532
NSYADR200D	532
NSYAEBFZ	475
NSYAEBP2F4F	310
NSYAEBP2F610	305
NSYAEBP2F68	305
NSYAEBP2F810	305
NSYAEBP2F88	305
NSYAEBP2FS10	305
NSYAEBP2FS6	305
NSYAEBP2FS8	305
NSYAECPFLA25	493
NSYAECPFLA33	493
NSYAECPFLBP	495
NSYAECPFLT25	495
NSYAECPFLT35	495
NSYAECPFLT7	495
NSYAEDDINS3D	557
NSYAEDH120S3D	555, 578, 580
NSYAEDH120S3HD	587
NSYAEDH180S3D	555, 578, 580
NSYAEDH20TB	555
NSYAEDH40TB	555
NSYAEDHPLM	584
NSYAEDHPLM108	584
NSYAEDHPLM3025	584
NSYAEDHPLM32	584
NSYAEDHSB	21, 555

NSYA...	Page
NSYAEDL1242K31	339
NSYAEDL1242K33	339, 351
NSYAEDL1242S3D	558
NSYAEDL2124S3D	558
NSYAEDL2131S3D	558
NSYAEDL2132S3D	558
NSYAEDL2241S3D	558
NSYAEDL2331S3D	558
NSYAEDL2432S3D	558
NSYAEDL2433S3D	558
NSYAEDL3113S3D	558
NSYAEDL3123S3D	558
NSYAEDL3131AS3D	558
NSYAEDL3132S3D	558
NSYAEDL3432S3D	558
NSYAEDL3524S3D	558
NSYAEDL405K31	339
NSYAEDL405K33	339, 351
NSYAEDL405S3D	558
NSYAEDL421S3D	558
NSYAEDL4324S3D	558
NSYAEDL455K31	339
NSYAEDL455K33	339, 351
NSYAEDL455S3D	558
NSYAEDL5124S3D	558
NSYAEDL610S3D	558
NSYAEDLB3MS3D	557
NSYAEDLB3S3D	557
NSYAEDLB5S3D	557
NSYAEDLEDF13S3D	558
NSYAEDLEDF14S3D	558
NSYAEDLEDF9S3D	558
NSYAEDLMETS3D	557
NSYAEDLPADS3D	558
NSYAEDLP-ADS3DHD	558
NSYAEDLPADS3DK3	339, 558
NSYAEDLS3DKDB3	558, 578, 579, 586
NSYAEDLS3DRL	557
NSYAEDLS3DRLN	578
NSYAEDLS3HDRL	587
NSYAEDLS3HFDB3	585
NSYAEDLS7S3D	557
NSYAEDLS8S3D	557
NSYAEDLSD	563
NSYAEDLT6S3D	557
NSYAEDLT8S3D	557
NSYAEDPHD	586
NSYAEDPLA001	584
NSYAEDPLA002G	584
NSYAEDPLA003G	584
NSYAEDPLA004	584
NSYAEDPLA005	584
NSYAEDPLM108	584
NSYAEDPLM810	584
NSYAEDRS3DPA6	568
NSYAEDRSCST	568
NSYAEDS20TB	564
NSYAEDS40TB	564
NSYAEDS60TB	564
NSYAEDSBSB	21, 564
NSYAEDSTSB	21
NSYAEEC1UN	305

NSYA...	Page
NSYAEECS	305
NSYAEFAHLBSC	47, 478
NSYAEFP42S3D	50, 466
NSYAEFPF40SC	478
NSYAEFPFS3DW100	48, 478
NSYAEFPFS3DW40	48, 478
NSYAEFPFS3DW60	48, 478
NSYAEFPFS3DW80	48, 478
NSYAEFPFSB	21, 477
NSYAEFPFSBX	91, 477
NSYAEFPFSC	47, 369, 477
NSYAEFPFSC2	477
NSYAEFPFXSC	47, 369, 477
NSYAEFTB	124, 125, 477
NSYAELYTCRG8	339, 482
NSYAELYTCRXG8	482
NSYAELZ	474
NSYAEPZM	472
NSYAEUBU41SC	463
NSYAEUBU61SC	463
NSYAEUBUSC	463
NSYAMCSF	528, 529, 547
NSYAMFSB	21, 508, 528, 541
NSYAMFSTB	124-126, 508, 529, 533
NSYAMPA1916TB	126, 508
NSYAMPA2419TB	126, 508
NSYAMPA2924TB	126, 508
NSYAMPA3429TB	126, 508
NSYAMPM1916TB	126, 508
NSYAMPM2419TB	126, 508
NSYAMPM2924TB	126, 508
NSYAMPM3429TB	126, 508
NSYAMRD11357TB	529
NSYAMRD15357SB	21, 91, 528
NSYAMRD16357TB	529
NSYAMRD19357TB	529
NSYAMRD20357SB	21, 91, 528
NSYAMRD24357TB	529
NSYAMRD29357TB	529
NSYAMRD30357SB	21, 91, 528
NSYAMRD34357TB	529
NSYAMRD40357SB	21, 91, 528
NSYAMRD50357SB	21, 528
NSYAMRD60357SB	21
NSYAMRD80357SB	21
NSYAPFWM	34, 49, 469
NSYAPFXWM	470
NSYAPU19F6CB	308
NSYAPU19F8S	308
NSYAPU19F9	308
NSYAPU19S8S	308
NSYAPU19S9	308
NSYAPUB	308
NSYAPUBV	308
NSYAPUF10S	308
NSYAPUF12CB	308
NSYAS500	189, 190, 214
NSYAS600	189, 190, 214, 246
NSYAS800	189, 190, 214, 246
NSYAS800L	189, 190, 214
NSYASPLA001	584
NSYASPLA002	584

Index of References

NSYA...	Page
NSYASPLA003	584
NSYASPLM	584
NSYATM27	482
NSYATP24DTM	209, 547
NSYATP72M	35, 209, 547
NSYATPUND	209, 547
NSYAUPG1G	571
NSYAZ3PLA	474
NSYAZ4PLA	474

NSYB...	Page
NSYB406	533
NSYBANPLA53	539
NSYBANPLA54	539
NSYBANPLA74	539
NSYBANPLA76	539
NSYBBF1U40	305
NSYBBF1U40P	305
NSYBBF1U60	305
NSYBBF1U60P	305
NSYBBF1U80	305
NSYBBF1U80P	305
NSYBBT1U40	306
NSYBBT1U40P	306
NSYBBT1U60	306
NSYBBT1U60P	306
NSYBBT1U80	306
NSYBBT1U80P	306
NSYBCE10	503
NSYBCE12	503
NSYBCE16	503
NSYBCE6	503
NSYBCE8	503
NSYBCME	559
NSYBCPL	559
NSYBE27G	143, 555
NSYBF1U25P	306
NSYBF2U25P	306
NSYBF2U40P	306
NSYBF4B3M	251
NSYBF4B4M	251
NSYBF4B5M	251
NSYBF4B6M	251
NSYBF4B8M	251
NSYBF4B9M	251
NSYBHNT600	211
NSYBHNT800	211
NSYBHNW600	211
NSYBHNW800	211
NSYBHS500	187, 215
NSYBHS600	187, 215, 245, 247
NSYBHS800	187, 215, 245, 247
NSYBHS800L	215
NSYBICRN	580, 585
NSYBL27	555
NSYBLKHN123	561
NSYBN204	533
NSYBN206	533
NSYBN404	533
NSYBN406	533
NSYBN408	533
NSYBN606	533
NSYBP207	581
NSYBPA7032	571

NSYB...	Page
NSYBPA7035	571
NSYBPHD12122D	588
NSYBPHD126	588
NSYBPHD128	588
NSYBPHD1612	588
NSYBPHD166	588
NSYBPHD168	588
NSYBPHD208	588
NSYBPN126	76, 293
NSYBPN128	76, 293
NSYBPN146	76, 293
NSYBPN148	76, 293
NSYBPN166	76, 293
NSYBPN168	76, 293
NSYBPN1810	76
NSYBPN1812	76
NSYBPN184	76
NSYBPN186	76, 293
NSYBPN188	76, 293
NSYBPN2010	77
NSYBPN2012	77
NSYBPN2016	77
NSYBPN203	77, 253
NSYBPN204	77, 253
NSYBPN206	77, 252, 293
NSYBPN207	581
NSYBPN208	77, 252, 293
NSYBPN2210	77
NSYBPN2212	77
NSYBPN224	77
NSYBPN226	77, 293
NSYBPN228	77, 293
NSYBRF12PLAG	549
NSYBRF17PLAG	549
NSYBRF21PLAG	549
NSYBRF26PLAG	549
NSYBRF8PLAG	549
NSYBSA	186, 187, 189, 190, 192, 215, 217, 218, 220, 221, 244-247
NSYBSA70	211
NSYBT2U25P	306
NSYBTACRNG100	580
NSYBTACRNG120	580
NSYBTACRNG140	580, 585
NSYBTACRNG80	580
NSYBTAS3D100	578, 579, 586
NSYBTAS3D120	578
NSYBTAS3D140	578
NSYBTAS3D60	578, 579, 586
NSYBTAS3D65	578
NSYBTAS3D70	578, 579, 586
NSYBTAS3D80	578, 579, 586
NSYBTAS3D90	578
NSYBVS400	214
NSYBVS500	189, 190, 214
NSYBVS600	189, 190, 214, 246
NSYBVS800	189, 190, 214, 244, 246
NSYBVS800L	189, 190, 214

NSYC...	Page
NSYCAAPV	403, 415
NSYCAAPVHD	333, 408, 549
NSYCAC228RMB	399

NSYC...	Page
NSYCAC228RMF	399
NSYCAEFPF	477
NSYCAF104X95X	398
NSYCAF108	402
NSYCAF125	404
NSYCAF125DG	415
NSYCAF125L55	404, 405
NSYCAF125M	404
NSYCAF125O	404
NSYCAF125T	404
NSYCAF130X110X	398
NSYCAF170X190X	398
NSYCAF190	224
NSYCAF223	404
NSYCAF223DG	415
NSYCAF223L55	404, 405
NSYCAF223M	404
NSYCAF223O	404
NSYCAF223T	404, 408
NSYCAF228R	399
NSYCAF291	404
NSYCAF291DG	415
NSYCAF291L55	404, 405
NSYCAF291M	404
NSYCAF291O	404
NSYCAF291T	404
NSYCAF92	404
NSYCAF92DG	415
NSYCAF92M	404
NSYCAG104X95LM	398
NSYCAG108LP	402
NSYCAG110X46M	398
NSYCAG114LPF	403
NSYCAG125DG	414
NSYCAG125LPF	160, 161, 243, 399
NSYCAG12LPH1	399, 476
NSYCAG12LPH2	399, 476
NSYCAG130X110LM	398
NSYCAG170X190LM	398
NSYCAG180X62M	398
NSYCAG19LP	399
NSYCAG216X62M	398
NSYCAG223DG	414
NSYCAG223LFHD	333, 404, 408
NSYCAG223LPF	242, 243, 399
NSYCAG291DG	414
NSYCAG291LPF	224, 399
NSYCAG317X120M	398
NSYCAG317X91M	398
NSYCAG33LP	399
NSYCAG35LP	399, 476
NSYCAG38LP	399
NSYCAG417X120M	398
NSYCAG45LP	399
NSYCAG78LPF	403
NSYCAG92DG	414
NSYCAG92LPF	242, 399
NSYCAP125LE	405
NSYCAP125LXF	404, 405
NSYCAP125LZF	404, 405
NSYCAP223LE	405
NSYCAP223LXF	404, 405
NSYCAP223LZF	404, 405

NSYC...	Page
NSYCAP291LE	405
NSYCAP291LXF	404, 405
NSYCAP291LZF	404, 405
NSYCBCCRN	559
NSYCBCMPLAG	562
NSYCBXHCRN	559
NSYCCA500MFST	414
NSYCCAFSDUST	415
NSYCCARPM	415
NSYCCASTE	427
NSYCCOFR55	414
NSYCCOFSEM8U2	414
NSYCCOFST30V	414
NSYCCOFST90250V	414
NSYCCOHY230VID	427
NSYCCOHYT120VID	427
NSYCCOHYT230VID	427
NSYCCOHYT30VID	427
NSYCCOTH120VID	427
NSYCCOTH230VID	427
NSYCCOTH30VID	427
NSYCCOTHC	426
NSYCCOTHCF	426
NSYCCOTHD	426
NSYCCOTHDF	426
NSYCCOTHI	426
NSYCCOTHO	426
NSYCCOTHOF	426
NSYCCSDF10	585
NSYCCSDF12	585
NSYCCSDF16	585
NSYCCSDF8	585
NSYCDB3	556
NSYCDB3N	556
NSYCDBPLM	148, 584
NSYCDBPLMN	556
NSYCDS	507
NSYCEA22E	430, 434, 590
NSYCEA36	430, 434, 590
NSYCEA50	430, 434, 590
NSYCEA80	430, 434, 590
NSYCEJ	503
NSYCEJDL0	496
NSYCEJDL12	496
NSYCEJDL13	496
NSYCEJDL14	496
NSYCEJDL15	496
NSYCEJDL16	496
NSYCEJDL17	496
NSYCEJDL18	496
NSYCEJDL19	496
NSYCEJDL20	496
NSYCEJDL21	496
NSYCEJDS0	496
NSYCEJDS10	496
NSYCEJDS11	496
NSYCEJDS2	496
NSYCEJDS3	496
NSYCEJDS4	496
NSYCEJDS5	496
NSYCEJDS6	496
NSYCEJDS7	496
NSYCEJDS8	496

NSYC...	Page
NSYCEJDS9	496
NSYCEK	500, 501, 503
NSYCEP	540
NSYCEPLMAG	476
NSYCEPLMBG	476
NSYCEPLMCG	476
NSYCEW1K	431, 590
NSYCEW1K8	431, 590
NSYCEW2K5	431, 590
NSYCEW2K5R	432, 590
NSYCEW3K5	431, 590
NSYCEW4K5	431, 590
NSYCEW6K	432, 590
NSYCEW6K2P4	432, 590
NSYCEWX1K	590
NSYCEWX1K8	590
NSYCEWX2K5	590
NSYCFP100	504
NSYCFP60	504
NSYCFP80	504
NSYCFS128	504
NSYCFS96	504
NSYCFS98	504
NSYCGSP16	490
NSYCGSP20	490
NSYCGSP25	490
NSYCGSP32	490
NSYCGSP40	490
NSYCGX12	490
NSYCGX12H	490
NSYCGX16	490
NSYCGX16H	490
NSYCGX20	490
NSYCGX20H	490
NSYCGX25	490
NSYCGX25H	490
NSYCGX32	490
NSYCGX32H	490
NSYCGX40	490
NSYCGX40H	490
NSYCL1242ECSX	559
NSYCL220CRN	556
NSYCL27L405	560
NSYCL27M	560
NSYCL405CRN	556
NSYCL405CSX	559
NSYCL610CSX	559
NSYCLL405CRN	378, 556
NSYCMACS50	283
NSYCMBPT	281
NSYCMT2560110	281
NSYCMT5005	279, 282
NSYCMT5010	279, 282
NSYCMT5015	279, 282
NSYCMT5020	279, 282
NSYCMUCC50	279, 283, 285
NSYCMUCR50	279, 283, 285
NSYCMUIA50	279, 282, 285
NSYCMUMA50	279, 282, 285
NSYCMUMA80	285
NSYCMUMC50	279, 282, 285
NSYCMUMR50	279, 282, 285
NSYCMUTC50	279, 283, 285

NSYC...	Page
NSYCN20	532
NSYCN40	532
NSYCN9M625	304, 468, 548
NSYCNM6	530, 536
NSYCNM8	530, 536
NSYCNOH123	565
NSYCNT20	532
NSYCNT40	532
NSYCOCN80	50, 466
NSYCOCNS1400	36, 50, 466
NSYCOCNS1800	36, 50, 466
NSYCR100WU1	423
NSYCR100WU1C	422
NSYCR100WU2	423
NSYCR100WU2C	422
NSYCR100WU3	423
NSYCR100WU3C	422
NSYCR10WU1	423
NSYCR10WU1C	422
NSYCR10WU2	423
NSYCR10WU2C	422
NSYCR150WU1	423
NSYCR150WU1C	422
NSYCR150WU2	423
NSYCR150WU2C	422
NSYCR150WU3	423
NSYCR170W230VVC	422
NSYCR20WU1	423
NSYCR20WU1C	422
NSYCR20WU2	423
NSYCR20WU2C	422
NSYCR20WU3	423
NSYCR250W230VV	423
NSYCR400W230VV	423
NSYCR50WU1C	422
NSYCR50WU2C	422
NSYCR50WU3C	422
NSYCR55WU1	423
NSYCR55WU2	423
NSYCR55WU3	423
NSYCRN1010300D	33
NSYCRN1010300T	33
NSYCRN1012300D	33
NSYCRN1012400D	33
NSYCRN106250	33
NSYCRN106250P	33
NSYCRN106250T	33
NSYCRN106300	33
NSYCRN106300P	33
NSYCRN106300T	33
NSYCRN106400	33
NSYCRN106400T	33
NSYCRN108250	33
NSYCRN108250P	33
NSYCRN108250T	33
NSYCRN108300	33
NSYCRN108300P	33
NSYCRN108300T	33
NSYCRN108400	33
NSYCRN108400T	33
NSYCRN1210300D	33
NSYCRN1210400D	33
NSYCRN1212300D	33

NSYC...	Page
NSYCRN1212400D	33
NSYCRN126300	33
NSYCRN126300T	33
NSYCRN126400	33
NSYCRN126400T	33
NSYCRN128300	33
NSYCRN128300T	33
NSYCRN128400	33
NSYCRN128400T	33
NSYCRN1410300D	33
NSYCRN22150	33
NSYCRN23150	33
NSYCRN252150	33
NSYCRN252150P	33
NSYCRN325150	33
NSYCRN325150P	33
NSYCRN325150T	33
NSYCRN325200	33
NSYCRN325200P	33
NSYCRN325200T	33
NSYCRN33150	33
NSYCRN33150P	33
NSYCRN33150T	33
NSYCRN33200	33
NSYCRN33200P	33
NSYCRN33200T	33
NSYCRN34200	33
NSYCRN34200T	33
NSYCRN345150	33
NSYCRN43150	33
NSYCRN43150P	33
NSYCRN43150T	33
NSYCRN43200	33
NSYCRN43200P	33
NSYCRN43200T	33
NSYCRN44200	33
NSYCRN44200P	33
NSYCRN44200T	33
NSYCRN46250	33
NSYCRN46250P	33
NSYCRN46250T	33
NSYCRN46300	33
NSYCRN54150	33
NSYCRN54150P	33
NSYCRN54150T	33
NSYCRN54200	33
NSYCRN54200P	33
NSYCRN54200T	33
NSYCRN54250	33
NSYCRN54250P	33
NSYCRN54250T	33
NSYCRN55250	33
NSYCRN55250P	33
NSYCRN55250T	33
NSYCRN64150	33
NSYCRN64150P	33
NSYCRN64150T	33
NSYCRN64200	33
NSYCRN64200P	33
NSYCRN64200T	33
NSYCRN64250	33
NSYCRN64250P	33
NSYCRN64250T	33

NSYC...	Page
NSYCRN65150	33
NSYCRN65150P	33
NSYCRN65200	33
NSYCRN65200P	33
NSYCRN65200T	33
NSYCRN65250	33
NSYCRN65250P	33
NSYCRN65250T	33
NSYCRN66200	33
NSYCRN66200P	33
NSYCRN66200T	33
NSYCRN66250	33
NSYCRN66250P	33
NSYCRN66250T	33
NSYCRN66300	33
NSYCRN66300P	33
NSYCRN66300T	33
NSYCRN68300	33
NSYCRN68300T	33
NSYCRN75200	33
NSYCRN75200P	33
NSYCRN75200T	33
NSYCRN75250	33
NSYCRN75250P	33
NSYCRN75250T	33
NSYCRN810300D	33
NSYCRN812300D	33
NSYCRN86200	33
NSYCRN86200P	33
NSYCRN86200T	33
NSYCRN86250	33
NSYCRN86250P	33
NSYCRN86250T	33
NSYCRN86300	33
NSYCRN86300P	33
NSYCRN86300T	33
NSYCRN86400	33
NSYCRN86400T	33
NSYCRN88200	33
NSYCRN88200P	33
NSYCRN88300	33
NSYCRN88300P	33
NSYCRN88300T	33
NSYCRNCGPSTDSB	580
NSYCRP1W120VTVC	423
NSYCRP1W230VTVC	423
NSYCRS100W240V	419
NSYCRS10W240V	419
NSYCRS200W230V	423
NSYCRS200W240V	419
NSYCRS25W240V	419
NSYCRS50W240V	419
NSYCRTA1U	310
NSYCRTM10U	310
NSYCRTM12U	310
NSYCRTM1U	310
NSYCRTM1U1P	309
NSYCRTM1U1PS	318
NSYCRTM1U2	309
NSYCRTM1U40B	309
NSYCRTM1U5GCA	309
NSYCRTM2U	310
NSYCRTM2US	309

Index of References

NSYC...	Page
NSYCRTM3U	310
NSYCRTM3UD	308
NSYCRTM4U	310
NSYCRTM5U	310
NSYCRTM6U	310
NSYCRTM9U	310
NSYCRTMR1U	310
NSYCRTMR3U	310
NSYCS200PLM	148, 529
NSYCS300PLM	529
NSYCS400PLM	529
NSYCS500PLM	529
NSYCS600PLM	529
NSYCS800PLM	529
NSYCSA57	149
NSYCSA68	149
NSYCSA810	149
NSYCSH166	204
NSYCSH168	204
NSYCSH186	204, 205
NSYCSH188	204
NSYCSH206	204
NSYCSH208	204
NSYCSP	461
NSYCSP6G	350
NSYCSSF	581
NSYCSSFHD	587, 588
NSYCTL500DLAG	543
NSYCTL500DLM	35
NSYCTL500DLP2	547
NSYCTL500DLPG	547
NSYCTL600DLAG	543
NSYCTL600DLM	35
NSYCTL750DLP2	547
NSYCTL750DLPG	547
NSYCTL800DLAG	543
NSYCTL800DLM	35
NSYCU1K22P4DG	441, 448, 450, 591
NSYCU1K22P4RDG	444, 448, 453, 591
NSYCU1K2DG	441, 448, 450, 591
NSYCU1K2P4DG	441, 448, 450, 591
NSYCU1K2RDG	444, 448, 453, 591
NSYCU1K52P4RDG	444, 448, 453, 591
NSYCU1K5RDG	444, 448, 453, 591
NSYCU1K62P4DG	441, 448, 450, 591
NSYCU1K6DG	441, 448, 450, 591
NSYCU1KDG	441, 448, 450, 591
NSYCU2K3P4DG	443, 448, 450, 591
NSYCU2K3P4RDG	444, 448, 453, 591
NSYCU2KDG	441, 448, 450, 591
NSYCU2KRDG	444, 448, 453, 591
NSYCU350DG	441, 448, 450, 591
NSYCU3K23P4DG	443, 448, 451, 591
NSYCU3K2DG	443, 448, 451, 591
NSYCU3K3P4RDG	444, 448, 453, 591
NSYCU4K3P4DG	443, 448, 451, 591
NSYCU4K3P4RDG	444, 448, 453, 591
NSYCU600DG	441, 448, 450, 591
NSYCU600RDG	444, 448, 453, 591
NSYCU8002P4DG	441, 448, 450, 591
NSYCU8002P4RDG	444, 448, 453, 591
NSYCU800DG	441, 448, 450, 591
NSYCU800RDG	444, 448, 453, 591

NSYC...	Page
NSYCUACC001DG	448
NSYCUACC002DG	448
NSYCUACC003DG	448
NSYCUACC004DG	448
NSYCUACC005DG	448
NSYCUACC006DG	448
NSYCUACC007DG	448
NSYCUACC008DG	448
NSYCUACC009DG	445, 448
NSYCUACC010DG	448
NSYCUACC011DG	448
NSYCUACC013DG	448
NSYCUACC014DG	448
NSYCUACC015DG	448
NSYCUACC017DG	448
NSYCUACC018DG	448
NSYCUACC019DG	448
NSYCUACC020DG	448
NSYCUACC021DG	448
NSYCUACC022DG	448
NSYCUACC023DG	448
NSYCUACC024DG	448
NSYCUACC025DG	448
NSYCUACC026DG	448
NSYCUACC027DG	448
NSYCUACC028DG	448
NSYCUACC029DG	448
NSYCUACC030DG	448
NSYCUACC031DG	448
NSYCUACC032DG	448
NSYCUACC033DG	448
NSYCUACC034DG	448
NSYCUACC035DG	448
NSYCUACC036DG	448
NSYCUACC037DG	448
NSYCUACC038DG	448
NSYCUACC039DG	448
NSYCUACC040DG	448
NSYCUACC041DG	591
NSYCUACC042DG	591
NSYCUH600DG	448
NSYCUHD1K2P4DG	447, 448, 452, 591
NSYCUHD1K62P4DG	447, 448, 452, 591
NSYCUHD1K6DG	447, 448, 452, 591
NSYCUHD1KDG	447, 448, 452, 591
NSYCUHD2K3P4DG	447, 448, 452, 591
NSYCUHD350DG	447, 448, 452, 591
NSYCUHD600DG	447, 452, 591
NSYCUHD800DG	447, 448, 452, 591
NSYCUSP001DG	591
NSYCUSP002DG	591
NSYCUSP0031	590
NSYCUSP0032	590
NSYCUSP0033	590
NSYCUSP0034	590
NSYCUSP0035	590
NSYCUSP0036	590
NSYCUSP0037	590
NSYCUSP0038	590
NSYCUSP0039	590
NSYCUSP003DG	591
NSYCUSP0040	590
NSYCUSP0041	590

NSYC...	Page
NSYCUSP0042	590
NSYCUSP0043	590
NSYCUSP0044	590
NSYCUSP004DG	591
NSYCUSP0053	590
NSYCUSP005DG	591
NSYCUSP006DG	591
NSYCUSP0077	590
NSYCUSP0078	590
NSYCUSP0079	590
NSYCUSP007DG	591
NSYCUSP0080	590
NSYCUSP0081	590
NSYCUSP0082	590
NSYCUSP0084	590
NSYCUSP008DG	591
NSYCUSP009DG	591
NSYCUSP0100	590
NSYCUSP0107	590
NSYCUSP0108	590
NSYCUSP0109	590
NSYCUSP010DG	591
NSYCUSP0112	590
NSYCUSP0113	590
NSYCUSP0114	590
NSYCUSP0115	590
NSYCUSP0117	590
NSYCUSP0124	590
NSYCUSP0125	590
NSYCUSP0136	590
NSYCUSP0137	590
NSYCUSP0138	590
NSYCUSP0177	590
NSYCUSP0181	590
NSYCUSP0184	590
NSYCUX1K2P4DG	441, 448, 450, 591
NSYCUX1K6DG	441, 448, 450, 591
NSYCUX1KDG	441, 448, 450, 591
NSYCUX2K3P4DG	443, 448, 450, 591
NSYCUX350DG	441, 448, 450, 591
NSYCUX600DG	441, 448, 450, 591
NSYCVA114M	403
NSYCVAC200	403
NSYCVF156M	403
NSYCVF156M115	403
NSYCVF156M230	403
NSYCVF165M115PF	400
NSYCVF165M230DG	413
NSYCVF165M230PF	242, 243, 400
NSYCVF165M24DPF	400
NSYCVF165M48DPF	400
NSYCVF170M115	403
NSYCVF170M230	403
NSYCVF300M115PF	400
NSYCVF300M230DG	413
NSYCVF300M230PF	242, 400
NSYCVF300M24DPF	400
NSYCVF300M48DPF	400
NSYCVF35M	403
NSYCVF35M115	403
NSYCVF35M230	403
NSYCVF38M115PF	400, 401
NSYCVF38M230DG	413

NSYC...	Page
NSYCVF38M230PF	242, 400, 401
NSYCVF38M24DPF	400
NSYCVF38M48DPF	400
NSYCVF54M230MM2	402
NSYCVF550M115FB	408
NSYCVF550M230FB	224, 408
NSYCVF550M24FB	408
NSYCVF560M115PF	400
NSYCVF560M230DG	413
NSYCVF560M230PF	400
NSYCVF570M115MF	402
NSYCVF575M230MF	402
NSYCVF65M115PF	402
NSYCVF65M230PF	402
NSYCVF850M115PF	400
NSYCVF850M230DG	413
NSYCVF850M230PF	400
NSYCVF850M400DG	413
NSYCVF850M400PF	400
NSYCVF85FM230PF	243
NSYCVF85M115PF	400
NSYCVF85M230DG	413
NSYCVF85M230PF	400
NSYCVF85M24DPF	400
NSYCVF85M48DPF	400
NSYCW33	567
NSYCW44	567
NSYCW45	567
NSYCW46	567
NSYCW54	567
NSYCW55	567
NSYCW56	567
NSYCW65	567
NSYCW66	567
NSYCW86	567

NSYD...	Page
NSYDB1010M	18
NSYDB1510M	18
NSYDB2015M	18
NSYDB88M	18
NSYDBN1010	18
NSYDBN1510	18
NSYDBN2015	18
NSYDBN2520	18
NSYDBN3025	18
NSYDBN88	18
NSYDBP	556
NSYDCD2412	496
NSYDCD244	496
NSYDCD248	496
NSYDCD249	496
NSYDCM20	570
NSYDCRN105L	580
NSYDCRN105R	580
NSYDCRN106	580
NSYDCRN106L	580
NSYDCRN106R	580
NSYDCRN108	580
NSYDCRN125L	580
NSYDCRN125R	580
NSYDCRN126	580
NSYDCRN126L	580
NSYDCRN126R	580

NSYD...	Page
NSYDCRN128	580
NSYDCRN145L	580
NSYDCRN145R	580
NSYDCRN22	580, 585
NSYDCRN23	580, 585
NSYDCRN2520	580, 585
NSYDCRN3025	580, 585
NSYDCRN3045	580, 585
NSYDCRN33	580, 585
NSYDCRN34	580, 585
NSYDCRN43	580, 585
NSYDCRN44	580, 585
NSYDCRN46	580, 585
NSYDCRN54	580
NSYDCRN55	580, 585
NSYDCRN64	580
NSYDCRN65	580
NSYDCRN66	580, 585
NSYDCRN68	580, 585
NSYDCRN75	580
NSYDCRN85L	580
NSYDCRN85R	580
NSYDCRN86	580, 585
NSYDCRN86L	580
NSYDCRN86R	580
NSYDCRN88	580
NSYDCRNG105L	580
NSYDCRNG105R	580
NSYDCRNG106	580
NSYDCRNG106L	580
NSYDCRNG106R	580
NSYDCRNG108	580
NSYDCRNG125L	580
NSYDCRNG125R	580
NSYDCRNG126	580
NSYDCRNG126L	580
NSYDCRNG126R	580
NSYDCRNG128	580
NSYDCRNG145L	580
NSYDCRNG145R	580
NSYDCRNG85L	580
NSYDCRNG85R	580
NSYDCRNG86	580
NSYDCRNG86L	580
NSYDCRNG86R	580
NSYDCSH2012	204, 205
NSYDHLT8080	537
NSYDHSF	581, 582
NSYDHSM2D	582
NSYDHSMN2D	582
NSYDLA112G	35, 47, 543
NSYDLA234G	35, 47, 543
NSYDLA24G	35, 47, 543
NSYDLA48G	35, 47, 543
NSYDLA48PG	35, 47, 543
NSYDLA66G	35, 47, 543
NSYDLA84G	35, 47, 543
NSYDLA88G	35, 543
NSYDLCR110	35, 546
NSYDLCR135	35, 546
NSYDLCR18	35, 546
NSYDLCR24	35, 546
NSYDLCR36	35, 546

NSYD...	Page
NSYDLCR48	35, 546
NSYDLCR64	35, 546
NSYDLCR88	35, 546
NSYDLLSDF	585
NSYDLM112	35, 47, 101, 542
NSYDLM168	35, 47, 542
NSYDLM24	35, 47, 101, 542
NSYDLM240	35, 47, 101, 542
NSYDLM48	35, 47, 101, 542
NSYDLM48P	35, 47, 101, 542
NSYDLM66	35, 47, 101, 542
NSYDLM84	35, 47, 101, 542
NSYDLM84P	35, 47, 101, 542
NSYDLM88	35, 101, 542
NSYDLP114G	544, 545
NSYDLP114PG	544, 545
NSYDLP132G	544, 545
NSYDLP133G	544, 545
NSYDLP152G	544, 545
NSYDLP165G	224, 544, 545
NSYDLP171G	544, 545
NSYDLP198G	544, 545
NSYDLP198PG	544, 545
NSYDLP231G	544, 545
NSYDLP264G	224, 544, 545
NSYDLP297G	544, 545
NSYDLP57G	544, 545
NSYDLP76G	544, 545
NSYDLP95G	544, 545
NSYDLP99G	544, 545
NSYDLPLM18G	544
NSYDLS12	137, 139
NSYDLS24	139
NSYDLS242	139
NSYDLS36	139
NSYDLS48	139
NSYDLSD10	585
NSYDLSD12	585
NSYDLSD6	585
NSYDLSD8	585
NSYDLSDF10	585
NSYDLSDF12	585
NSYDLSDF16	585
NSYDLSDF8	585
NSYDNS3D105L	578
NSYDNS3D105R	578
NSYDNS3D106L	578
NSYDNS3D106R	578
NSYDNS3D125L	578
NSYDNS3D125R	578
NSYDNS3D126L	578
NSYDNS3D126R	578
NSYDNS3D145L	578
NSYDNS3D145R	578
NSYDNS3D85L	578
NSYDNS3D85R	578
NSYDNS3D86L	578
NSYDNS3D86R	578
NSYDPA3	570
NSYDPA4	570
NSYDPA44	570
NSYDPA5	570
NSYDPHD105P	586

NSYD...	Page
NSYDPHD105R	586
NSYDPHD107P	586
NSYDPHD107R	586
NSYDPHD125LP	586
NSYDPHD125LR	586
NSYDPHD125P	586
NSYDPHD125R	586
NSYDPHD127P	586
NSYDPHD127R	586
NSYDPHD155LP	586
NSYDPHD155LR	586
NSYDPHD157P	586
NSYDPHD157R	586
NSYDPHD55P	586
NSYDPHD55R	586
NSYDPHD75P	586
NSYDPHD75R	586
NSYDPHD77P	586
NSYDPHD77R	586
NSYDPLA105G	584
NSYDPLA105HG	584
NSYDPLA107G	584
NSYDPLA107HG	584
NSYDPLA125G	584
NSYDPLA125HG	584
NSYDPLA127G	584
NSYDPLA127HG	584
NSYDPLA155G	584
NSYDPLA155HG	584
NSYDPLA157G	584
NSYDPLA157HG	584
NSYDPLA3	522
NSYDPLA4	522
NSYDPLA55G	584
NSYDPLA55HG	584
NSYDPLA57G	584
NSYDPLA57HG	584
NSYDPLA6	522
NSYDPLA75G	584
NSYDPLA75HG	584
NSYDPLA77G	584
NSYDPLA77HG	584
NSYDPLM108G	584
NSYDPLM108TG	584
NSYDPLM200	522
NSYDPLM250	522
NSYDPLM300	522
NSYDPLM3025G	584
NSYDPLM3025TG	584
NSYDPLM32G	584
NSYDPLM350	522
NSYDPLM43G	584
NSYDPLM43TG	584
NSYDPLM54G	584
NSYDPLM54TG	584
NSYDPLM64G	584
NSYDPLM64TG	584
NSYDPLM75G	584
NSYDPLM75TG	584
NSYDPLM86G	584
NSYDPLM86TG	584
NSYDPR200	532
NSYDPR200D	532

NSYD...	Page
NSYDPR200T	532
NSYDS3D1010	578
NSYDS3D105L	578
NSYDS3D105R	578
NSYDS3D106	578
NSYDS3D106L	578
NSYDS3D106R	578
NSYDS3D108	578, 586
NSYDS3D1210	578
NSYDS3D125L	578
NSYDS3D125R	578
NSYDS3D126	578
NSYDS3D126L	578
NSYDS3D126R	578
NSYDS3D128	578
NSYDS3D145L	578
NSYDS3D145R	578
NSYDS3D32	578, 586
NSYDS3D325	578
NSYDS3D33	578, 586
NSYDS3D34	578
NSYDS3D43	578, 586
NSYDS3D44	578, 586
NSYDS3D46	578
NSYDS3D53	578
NSYDS3D54	578, 586
NSYDS3D55	578
NSYDS3D64	578, 586
NSYDS3D65	578
NSYDS3D66	578, 586
NSYDS3D68	578
NSYDS3D75	578, 586
NSYDS3D810	578
NSYDS3D85L	578
NSYDS3D85R	578
NSYDS3D86	578, 586
NSYDS3D86L	578
NSYDS3D86R	578
NSYDS3D88	578
NSYDS3HD106	587
NSYDS3HD108	587
NSYDS3HD32	587
NSYDS3HD43	587
NSYDS3HD54	587
NSYDS3HD64	587
NSYDS3HD66	587
NSYDS3HD75	587
NSYDS3HD86	587
NSYDS3HD88	587
NSYDS3X1010L	583
NSYDS3X1010LH	583
NSYDS3X1010R	583
NSYDS3X1010RH	583
NSYDS3X108	583
NSYDS3X108H	583
NSYDS3X108T	583
NSYDS3X1210L	583
NSYDS3X1210LH	583
NSYDS3X1210R	583
NSYDS3X1210RH	583
NSYDS3X128	583
NSYDS3X128H	583
NSYDS3X32	583

Index of References

NSYD...	Page
NSYDS3X325	583
NSYDS3X325H	583
NSYDS3X32H	583
NSYDS3X33	583
NSYDS3X33H	583
NSYDS3X43	583
NSYDS3X43H	583
NSYDS3X43T	583
NSYDS3X44	583
NSYDS3X44H	583
NSYDS3X46	583
NSYDS3X46H	583
NSYDS3X54	583
NSYDS3X54H	583
NSYDS3X54T	583
NSYDS3X64	583
NSYDS3X64H	583
NSYDS3X64T	583
NSYDS3X66	583
NSYDS3X66H	583
NSYDS3X75	583
NSYDS3X75H	583
NSYDS3X75T	583
NSYDS3X86	583
NSYDS3X86H	583
NSYDS3X86T	583
NSYDS3X88	583
NSYDS3X88H	583
NSYDSFX1410L	583
NSYDSFX1410R	583
NSYDSFX168	583
NSYDSFX1812L	583
NSYDSFX1812LH	583
NSYDSFX1812R	583
NSYDSFX1812RH	583
NSYDSFX1816L	583
NSYDSFX1816LH	583
NSYDSFX1816R	583
NSYDSFX1816RH	583
NSYDSFX186	583
NSYDSFX188	583
NSYDSFX188H	583
NSYDSFX2010L	583
NSYDSFX2010LH	583
NSYDSFX2010R	583
NSYDSFX2010RH	583
NSYDSFX2012L	583
NSYDSFX2012LH	583
NSYDSFX2012R	583
NSYDSFX2012RH	583
NSYDSFX2016L	583
NSYDSFX2016LH	583
NSYDSFX2016R	583
NSYDSFX2016RH	583
NSYDSFX206	583
NSYDSFX208	583
NSYE...	Page
NSYE1025	535
NSYE1525	535
NSYE2025	535
NSYEB1510D6	379, 540
NSYEB1516D8	379, 540
NSYEB156D6	379, 540

NSYE...	Page
NSYEB2025D8	379, 540
NSYEB2050D8	379, 540
NSYEBMPLAG	562
NSYEC104	75, 501
NSYEC1041	75, 502
NSYEC105	75, 501
NSYEC1051	75, 502
NSYEC106	75, 501
NSYEC1061	75, 502
NSYEC1062	75, 502
NSYEC108	75, 501
NSYEC1081	75, 502
NSYEC1082	75, 502
NSYEC124	75, 501
NSYEC1241	75, 502
NSYEC125	75, 501
NSYEC1251	75, 502
NSYEC126	75, 501
NSYEC1261	75, 502
NSYEC1262	75, 502
NSYEC128	75, 501
NSYEC1281	75, 502
NSYEC1282	75, 502
NSYEC164	75, 501
NSYEC1641	75, 502
NSYEC165	75, 501
NSYEC1651	75, 502
NSYEC166	75, 501
NSYEC1661	75, 502
NSYEC1662	75, 502
NSYEC35	75, 501
NSYEC351	75, 197, 502
NSYEC36	75, 501
NSYEC361	75, 197, 502
NSYEC381	75, 197
NSYEC44	75, 501
NSYEC440	296
NSYEC441	75, 502
NSYEC45	75, 501
NSYEC451	75, 502
NSYEC461	75, 502
NSYEC462	75, 502
NSYEC481	75, 502
NSYEC482	75, 502
NSYEC610	293, 501
NSYEC6101	293, 502
NSYEC6102	293, 502
NSYEC64	75, 501
NSYEC641	75, 502
NSYEC65	75, 501
NSYEC651	75, 502
NSYEC66	75, 293, 501
NSYEC661	75, 260, 293, 502
NSYEC662	75, 293, 502
NSYEC68	75, 293, 501
NSYEC681	75, 260, 293, 502
NSYEC682	75, 293, 502
NSYEC751	197
NSYEC761	197
NSYEC781	197
NSYEC810	293, 501
NSYEC8101	293, 502
NSYEC8102	293, 502

NSYE...	Page
NSYEC84	75, 501
NSYEC841	75, 502
NSYEC85	75, 501
NSYEC851	75, 502
NSYEC86	75, 293, 501
NSYEC861	75, 293, 502
NSYEC862	75, 293, 502
NSYEC88	75, 293, 501
NSYEC881	75, 293, 502
NSYEC882	75, 293, 502
NSYECAV440	296
NSYECB1M153	540
NSYECP300	314-317
NSYECP440	296
NSYECPC15	488
NSYECPC3	488
NSYECPC5	488
NSYECPC6	488
NSYECPC9	488
NSYECPLAZ103G	503
NSYECPLAZ104G	503
NSYECPLAZ123G	503
NSYECPLAZ124G	503
NSYECPLAZ53G	503
NSYECPLAZ54G	503
NSYECPLAZ73G	503
NSYECPLAZ74G	503
NSYECPT300	317
NSYECVT2V440	297
NSYECVT300	314-317
NSYECVT3V440	297
NSYEDCO	535
NSYEDCOC	540
NSYEDCOS	540
NSYEDPLA	523
NSYEL136D6	540
NSYEL166D6	540
NSYEL166D8	198, 540
NSYEL2225D8	540
NSYEL226D6	540
NSYEL2510D6	540
NSYEL3525D8	198, 540
NSYEMR	32, 46, 57
NSYENU	310
NSYETF	535
NSYEVA20	534
NSYEX1006	535
NSYEX1008	535
NSYEX106	535
NSYEX146	535
NSYEX158	535
NSYEX166	535
NSYEX206	296, 535
NSYEX208	535
NSYEX306	535
NSYEX308	535
NSYEX406	535
NSYEX408	535
NSYEX506	535
NSYEX508	535
NSYEX608	535, 546
NSYF...	Page
NSYFB45	251, 535

NSYF...	Page
NSYFCG100	505
NSYFCG60	505
NSYFCG80	505
NSYFCMX	477
NSYFDLSD	585
NSYFMPHD	478
NSYFMPLA	478
NSYFNM6	536
NSYFNM8	536
NSYFPLS1827G	139
NSYFPLS2727G	139
NSYFPLS2736G	139
NSYFPLS2754G	139
NSYFPLS3636G	139
NSYFPLS3654G	139
NSYFPLS3672G	139
NSYFPLS5454G	139
NSYFPLS5472G	139
NSYFXMNT60F	210
NSYFXMNT80F	210
NSYFXMNT80W	210
NSYFXMNW80F	210
NSYFXMNW80W	210
NSYFXMNWT60FW	210
NSYFXT6040	538
NSYFXT6050	538
NSYFXT6060	260, 538
NSYFXT8040	538
NSYFXT8050	538
NSYFXT8060	260, 538
NSYFXT8080	538
NSYG...	Page
NSYGB140	303
NSYGCA410	309
NSYGDD	578
NSYGF356	307
NSYGF356H5	307
NSYGF456	307
NSYGF556	307
NSYGF656	307
NSYGF756	307
NSYGFR12M65	310
NSYGFR166P	304, 548
NSYGFR95M55	304, 548
NSYGFR95M63	304, 548
NSYGFR95M65	304, 548
NSYGT60	307
NSYGT80	307
NSYH...	Page
NSYHATVSK	242
NSYHLCR40	537
NSYHLCR50	537
NSYHLCR60	346, 350, 537
NSYHLCR80	537
NSYHPF2B3M4	249
NSYHPF2B3M64	249
NSYHPF2B3M65	249
NSYHPF2B3M84	249
NSYHPF2B3M85	249
NSYHPF2B4M65	249
NSYHS3X	583
NSYHSD	585
NSYHSDF	585

Index of References

NSYH...	Page
NSYHSMX	583
NSYI...	Page
NSYID166	65, 552
NSYID168	65, 552
NSYID1810	65, 552
NSYID186	65, 552
NSYID188	65, 552
NSYID2010	65, 552
NSYID206	65, 552
NSYID208	65, 552
NSYIN1242E1	563
NSYIN1242E2	562
NSYIN2131A1	563
NSYIN2132A1	563
NSYIN2433A1	563
NSYIN2452E1	563
NSYIN3113A1	563
NSYIN405E1	563
NSYIN421E1	563
NSYIN4551	563
NSYINASSA2	562
NSYINDB31	563
NSYINDB51	563
NSYINDIN2	562
NSYINE11	563
NSYINF1301	563
NSYINICHEL8131	563
NSYINICHEL8371	563
NSYINKBA2	562
NSYINKFAC2	562
NSYINKJIS2	562
NSYINKR2	562
NSYINLCRN	339, 569
NSYINPULS1	565
NSYINS61	563
NSYINS71	563
NSYINS81	563
NSYINT61	563
NSYINT71	563
NSYINT81	563
NSYINT91	563
NSYJ...	Page
NSYJPSVD	317
NSYK...	Page
NSYKDB12U6F	318
NSYKDB15U6F	318
NSYKDB6U4F	318
NSYKDB9U4F	318
NSYKPLM	559
NSYL...	Page
NSYLADP	561, 563
NSYLAM1M	572
NSYLAM3M	572
NSYLAM3MDC	572
NSYLAM3MDCUL	572
NSYLAM3MN	572
NSYLAM3MUL	572
NSYLAMACF	573
NSYLAMACM	573
NSYLAMLD	572
NSYLAMLDB	572
NSYLAMLDD	572
NSYLAMLDF	572

NSYL...	Page
NSYLAMLDS	572
NSYLAMLDU	572
NSYLAMLDVDC	572
NSYLAMPORTLD	574
NSYLAMT5LD1	574
NSYLAMT5LD1VDC	574
NSYLAMT5LD2	574
NSYLC7	565
NSYLC8	565
NSYLCK12SF	581, 582
NSYLCK14SF	581, 582
NSYLCK16SF	581, 582
NSYLCK18SF	581, 582
NSYLCK20SF	581, 582
NSYLCK22SF	581, 582
NSYLCKWSF	581, 582
NSYLDB5	556, 565
NSYLSS3X10	583
NSYLSS3X12	583
NSYLSSDX	585
NSYLSSFX14	583
NSYLSSFX16	583
NSYLSSFX18	583
NSYLSSFX20	583
NSYLT8	565
NSYM...	Page
NSYMB108	33, 47, 512
NSYMB1210	33, 47, 512
NSYMB3025	33, 47, 512
NSYMB32	33, 47, 512
NSYMB33	33
NSYMB43	33, 47, 512
NSYMB54	33, 47, 512
NSYMB64	33, 47, 512
NSYMB65	33, 47, 512
NSYMB75	33, 47, 512
NSYMB86	33, 47, 512
NSYMBC206	249
NSYMBC208	249
NSYMBHS4	245, 247
NSYMBHS5	245, 247
NSYMBHS54	245
NSYMBR19	300
NSYMCDFIX	209
NSYMCSX	563
NSYMD108	33, 47, 547
NSYMD128	33, 47, 547
NSYMD33	33, 47, 547
NSYMD43	33, 47, 547
NSYMD54	33, 47, 547
NSYMD64	33, 47, 547
NSYMD66	33, 47, 547
NSYMD75	33, 47, 547
NSYMD86	33, 47, 547
NSYMDCM20	570
NSYMDT	553
NSYMDVR12	528
NSYMDVR3M	528
NSYMF1010	33, 47, 101, 511
NSYMF106	33, 47, 101, 511
NSYMF108	33, 47, 101, 511
NSYMF1210	33, 47, 101, 511
NSYMF126	33, 47, 101, 511

NSYM...	Page
NSYMF128	33, 47, 101, 511
NSYMF2PLAZ4	325
NSYMF2PLAZ6	325
NSYMF32	33, 47, 101, 511
NSYMF33	33, 47, 101, 511
NSYMF43	33, 47, 101, 511
NSYMF44	33, 47, 101, 511
NSYMF53	47, 511
NSYMF54	33, 47, 101, 511
NSYMF55	33, 47, 511
NSYMF64	33, 47, 101, 511
NSYMF65	33, 47, 511
NSYMF66	33, 47, 101, 511
NSYMF75	33, 47, 101, 511
NSYMF86	33, 47, 101, 511
NSYMF88	33, 47, 101, 511
NSYMFB	530
NSYMFP2M6	252, 260, 552
NSYMFP2M8	252, 552
NSYMFP5M6	252, 552
NSYMFP5M8	252, 552
NSYMFP6M6	252
NSYMFSC60	208
NSYMFSC60D	208
NSYMFSC80	208
NSYMFSC80D	208
NSYMICN6	250, 260, 552, 553
NSYMICN8	250, 552, 553
NSYML23	588
NSYML405SD	272
NSYMLCD23	588
NSYMLS6	588
NSYMLT6	588
NSYMM1010	33, 47, 101, 509
NSYMM106	33, 47, 101, 509
NSYMM108	33, 47, 101, 509
NSYMM11SB	21, 91, 508
NSYMM1210	33, 47, 101, 509
NSYMM1212	33, 47, 509
NSYMM126	33, 47, 101, 509
NSYMM128	33, 47, 101, 509
NSYMM12SB	21, 508
NSYMM13SB	21, 91, 508
NSYMM1410	33, 47, 509
NSYMM14SB	21, 508
NSYMM22	33, 509
NSYMM22SB	21, 91, 508
NSYMM23SB	21, 91, 508
NSYMM24SB	21, 91, 508
NSYMM2520	33, 509
NSYMM2540	509
NSYMM2550	509
NSYMM25SB	21, 508
NSYMM26SB	21, 508
NSYMM28SB	21, 508
NSYMM3025	33, 47, 101, 509
NSYMM3045	33, 509
NSYMM32	33, 47, 101, 509
NSYMM33	33, 47, 101, 509
NSYMM33SB	21, 91, 508
NSYMM34SB	21, 508
NSYMM35SB	21, 508
NSYMM36	509

NSYM...	Page
NSYMM36SB	21, 508
NSYMM38SB	21, 508
NSYMM43	33, 47, 101, 509
NSYMM44	33, 47, 101, 509
NSYMM44SB	21, 508
NSYMM45SB	21, 508
NSYMM46SB	21, 508
NSYMM48	509
NSYMM48SB	21, 508
NSYMM53	47, 509
NSYMM54	33, 47, 101, 509
NSYMM55	33, 47, 509
NSYMM64	33, 47, 101, 509
NSYMM65	33, 47, 509
NSYMM66	33, 47, 101, 509
NSYMM75	33, 47, 101, 509
NSYMM76	509
NSYMM86	33, 47, 101, 509
NSYMM88	33, 47, 101, 509
NSYMP1210	65, 514
NSYMP1212	65, 514
NSYMP126	75, 76, 514
NSYMP128	65, 75, 76, 514
NSYMP12M6	233, 236, 237, 240-242
NSYMP12M8	233, 236, 237, 240, 241
NSYMP1410	65, 514
NSYMP1412	65, 514
NSYMP146	65, 75, 76, 514
NSYMP148	65, 75, 76, 514
NSYMP1610	65, 514
NSYMP1612	65, 514
NSYMP166	65, 75, 76, 514
NSYMP168	65, 75, 76, 514
NSYMP16M6	233, 237, 240-242
NSYMP16M8	233, 237, 240, 241
NSYMP1810	65, 75, 76, 514
NSYMP1812	65, 75, 76, 514
NSYMP1816	65, 75, 514
NSYMP184	75, 76, 514
NSYMP186	65, 75, 76, 514
NSYMP188	65, 75, 76, 514
NSYMP188L	515
NSYMP18M6	233, 242, 243
NSYMP18M8	233
NSYMP2010	65, 75, 77, 514
NSYMP2010L	515
NSYMP2012	65, 75, 77, 514
NSYMP2012L	515
NSYMP2016	65, 75, 77, 514
NSYMP204	75, 77, 514
NSYMP206	65, 75, 77, 514
NSYMP208	65, 75, 77, 346, 350, 514
NSYMP208L	515
NSYMP20M6	233, 241
NSYMP20M8	233, 241
NSYMP2210	75, 77, 514
NSYMP2212	75, 77, 514
NSYMP224	75, 77, 514
NSYMP226	75, 77, 514
NSYMP228	75, 77, 514
NSYMP24M6	233, 241

Index of References

NSYM...	Page
NSYMP24M8	233, 241
NSYMP3M6	233, 236, 238, 240
NSYMP3M8	233, 236, 238, 240
NSYMP4M6	233, 236-239
NSYMP4M8	233, 236-239
NSYMP5M6	233, 237, 239
NSYMP5M8	233, 237, 239
NSYMP6M6	233, 236, 240
NSYMP6M8	233, 236, 240
NSYMP8M6	233
NSYMP8M8	233
NSYMP9M6	233, 236, 240-242
NSYMP9M8	233, 236, 240, 241
NSYMPB6SD	272
NSYMPBSD	272
NSYMPC156	206
NSYMPC158	206
NSYMPC206	206
NSYMPC208	206
NSYMPC306	206
NSYMPC308	206
NSYMPC406	206
NSYMPC408	206
NSYMPC456	206
NSYMPC458	206
NSYMPC606	206
NSYMPC608	206
NSYMPCH156	206
NSYMPCH158	206
NSYMPCH206	206
NSYMPCH208	206
NSYMPCH306	206
NSYMPCH308	206
NSYMPCH406	206
NSYMPCH408	206
NSYMPCH456	206
NSYMPCH458	206
NSYMPCH606	206
NSYMPCH608	206
NSYMPD106T	252, 552
NSYMPD108T	252, 552
NSYMPD12M6	252, 553
NSYMPD12M8	252, 553
NSYMPD16M6	252, 553
NSYMPD16M8	252, 553
NSYMPD18M6	252, 553
NSYMPD18M8	252, 553
NSYMPD20M6	252, 553
NSYMPD20M8	252, 553
NSYMPD24M6	252, 553
NSYMPD24M8	252, 553
NSYMPD3M6	252, 553
NSYMPD3M8	252, 553
NSYMPD46T	252, 552
NSYMPD48T	252, 552
NSYMPD4M6	252, 260, 553
NSYMPD4M8	252, 553
NSYMPD5M6	252, 553
NSYMPD5M8	252, 553
NSYMPD66T	252, 552
NSYMPD68T	252, 552
NSYMPD6M6	252, 553
NSYMPD6M8	252, 553

NSYM...	Page
NSYMPD86T	252, 552
NSYMPD88T	252, 552
NSYMPD8M6	252, 553
NSYMPD8M8	252, 553
NSYMPD9M6	252, 553
NSYMPD9M8	252, 553
NSYMPFIX	233, 236-243
NSYMPP108	513
NSYMPP32	513
NSYMPP43	513
NSYMPP54	513
NSYMPP64	513
NSYMPP75	513
NSYMPP86	513
NSYMPR12M6	243
NSYMPRK10	519
NSYMPRK12	519
NSYMPRK16	519
NSYMPRK8	519
NSYMPS60	209
NSYMPS80	209
NSYMR1010	33, 101, 510
NSYMR1012	33, 47, 510
NSYMR106	33, 47, 101, 510
NSYMR108	33, 47, 101, 510
NSYMR1210	33, 47, 101, 510
NSYMR126	33, 510
NSYMR128	33, 47, 101, 510
NSYMR1410	33, 47, 510
NSYMR3025	33, 47, 101, 510
NSYMR32	47, 101, 510
NSYMR33	33, 47, 101, 510
NSYMR34	33, 47, 510
NSYMR43	33, 47, 101, 510
NSYMR44	33, 47, 101, 510
NSYMR46	33, 47, 101, 510
NSYMR53	47, 510
NSYMR54	33, 47, 101, 510
NSYMR55	33, 47, 510
NSYMR64	33, 47, 101, 510
NSYMR65	33, 47, 510
NSYMR66	33, 47, 101, 510
NSYMR68	33, 47, 510
NSYMR75	33, 47, 101, 510
NSYMR76	510
NSYMR810	33, 47, 510
NSYMR86	33, 47, 101, 510
NSYMR88	33, 47, 101, 510
NSYMSC202	249
NSYMSC206	249
NSYMTRN64	250
NSYMTRN65	250
NSYMTRN84	250
NSYMTRN85	250
NSYMUC156	207
NSYMUC158	207
NSYMUC206	207
NSYMUC208	207
NSYMUC306	205, 207
NSYMUC308	207
NSYMUC406	207
NSYMUC408	207
NSYMUCH156	207

NSYM...	Page
NSYMUCH158	207
NSYMUCH206	207
NSYMUCH208	207
NSYMUCH306	207
NSYMUCH308	207
NSYMUCH406	207
NSYMUCH408	207
NSYMUPLA103G	464
NSYMUPLA103W	465
NSYMUPLA104G	464
NSYMUPLA104W	465
NSYMUPLA123G	464
NSYMUPLA123W	465
NSYMUPLA124G	464
NSYMUPLA124W	465
NSYMUPLA153G	464
NSYMUPLA153W	465
NSYMUPLA154G	464
NSYMUPLA154W	465
NSYMUPLA204G	224, 464
NSYMUPLA53G	464
NSYMUPLA54G	464
NSYMUPLA73G	464
NSYMUPLA74G	464
NSYMW10M	566
NSYMW10MK	566
NSYMW10MR	567
NSYN...	Page
NSYNM4	528
NSYNM5	528
NSYNM6	528
NSYO...	Page
NSYOPB12U4F	315, 316
NSYOPB12U4FR	315, 316
NSYOPB12U5F	315, 316
NSYOPB12U5P	314, 316
NSYOPB12U6F	315, 316
NSYOPB12U6P	314, 316
NSYOPB12UTPN	314, 315, 317
NSYOPB15U4F	315, 316
NSYOPB15U5F	315, 316
NSYOPB15U5FR	315, 316
NSYOPB15U6F	315, 316
NSYOPB15UTPN	314, 315, 317
NSYOPB18U4F	315, 316
NSYOPB18U5F	315, 316
NSYOPB18U5FR	315, 316
NSYOPB18U5P	314, 316
NSYOPB18UTPN	314, 315, 317
NSYOPB21U5F	315, 316
NSYOPB21U6F	315, 316
NSYOPB21UTPN	315, 317
NSYOPB6U4F	315, 316
NSYOPB6U5F	315, 316
NSYOPB6UTPN	314, 315, 317
NSYOPB9U4F	315, 316
NSYOPB9U4FR	315, 316
NSYOPB9U5F	315, 316
NSYOPB9U5P	314, 316
NSYOPB9U6F	315, 316
NSYOPB9UTPN	314, 315, 317
NSYP...	Page
NSYPA3025PLMG	551

NSYP...	Page
NSYPAP108G	551
NSYPAP43G	551
NSYPAP54G	551
NSYPAP64G	551
NSYPAP75G	551
NSYPAP86G	551
NSYPAPLA105G	551
NSYPAPLA107G	551
NSYPAPLA125G	551
NSYPAPLA127G	551
NSYPAPLA155G	224, 551
NSYPAPLA157G	551
NSYPAPLA55G	551
NSYPAPLA57G	551
NSYPAPLA75G	551
NSYPAPLA77G	551
NSYPC100	581, 582
NSYPC200	581, 582
NSYPCVDN126	293, 296
NSYPCVDN128	293, 296
NSYPCVDN188	293, 296
NSYPCVDN206	293, 296
NSYPCVDN208	293, 296
NSYPCVDN226	293, 296
NSYPCVDN228	293, 296
NSYPCVR124HD	224, 407, 460
NSYPCVR126HD	407
NSYPCVR54HD	407
NSYPCVR74HD	224, 407, 460
NSYPCVR76HD	407
NSYPF27N	477
NSYPF27X	477
NSYPFC2X	477
NSYPFCR	35, 378, 477
NSYPFCX	477
NSYPFPLM32G	478
NSYPFPLMG	478
NSYPFXPLM	478
NSYPHDT553P	325, 407
NSYPHDT753P	325, 407
NSYPHDZT1054	325, 407
NSYPHDZT1054P	325, 407
NSYPHDZT1074	325, 407
NSYPHDZT1074P	325, 407
NSYPHDZT12124	325, 407
NSYPHDZT12124P	325, 407
NSYPHDZT12126	325, 407
NSYPHDZT12126P	325, 407
NSYPHDZT1254	325, 407
NSYPHDZT1254P	325, 407
NSYPHDZT1274	325, 407
NSYPHDZT1274P	325, 407
NSYPHDZT1276	325, 407
NSYPHDZT1276P	325, 407
NSYPHDZT15124	325, 407
NSYPHDZT15124P	325, 407
NSYPHDZT15126	325, 407
NSYPHDZT15126P	325, 407
NSYPHDZT1574	325, 407
NSYPHDZT1574P	325, 407
NSYPHDZT1576	325, 407
NSYPHDZT1576P	325, 407
NSYPHDZT2074	325, 407

NSYP...	Page
NSYPHDZT2074P	325, 407
NSYPHDZT774	325, 407
NSYPHDZT774P	325, 407
NSYPHDZT776	325, 407
NSYPHDZT776P	325, 407
NSYPHX200	481
NSYPIN106	35, 48, 550
NSYPIN108	35, 48, 550
NSYPIN126	35, 48, 550
NSYPIN128	35, 48, 550
NSYPIN43	35, 48, 550
NSYPIN54	35, 48, 550
NSYPIN64	35, 48, 550
NSYPIN75	35, 48, 550
NSYPIN86	35, 48, 550
NSYPLA10103G	162
NSYPLA10103TG	162
NSYPLA10104G	162
NSYPLA10104TG	162
NSYPLA10123G	162
NSYPLA10123TG	162
NSYPLA10124G	162
NSYPLA10124TG	162
NSYPLA1053G	162
NSYPLA1053TG	162
NSYPLA1054G	162
NSYPLA1054TG	162
NSYPLA1073G	162
NSYPLA1073TG	162
NSYPLA1074G	162
NSYPLA1074TG	162
NSYPLA12103G	162
NSYPLA12103TG	162
NSYPLA12104G	162
NSYPLA12104TG	162
NSYPLA12123G	162
NSYPLA12123TG	162
NSYPLA12124G	162
NSYPLA12124TG	162
NSYPLA12126G	162
NSYPLA12126TG	162
NSYPLA1253G	162
NSYPLA1253TG	162
NSYPLA1254G	162
NSYPLA1254TG	162
NSYPLA1273G	162
NSYPLA1273TG	162
NSYPLA1274G	162
NSYPLA1274TG	162
NSYPLA1276G	162
NSYPLA1276TG	162
NSYPLA15103G	162
NSYPLA15103TG	162
NSYPLA15104G	162
NSYPLA15104TG	162
NSYPLA15123G	162
NSYPLA15123TG	162
NSYPLA15124G	162
NSYPLA15124TG	162
NSYPLA15126G	162
NSYPLA15126TG	162
NSYPLA1553G	162
NSYPLA1553TG	162

NSYP...	Page
NSYPLA1554G	162
NSYPLA1554TG	162
NSYPLA1573G	162
NSYPLA1573TG	162
NSYPLA1574G	162
NSYPLA1574TG	162
NSYPLA1576G	162
NSYPLA1576TG	162
NSYPLA2074G	162
NSYPLA2074TG	162
NSYPLA5103G	162
NSYPLA5104G	162
NSYPLA5123G	162
NSYPLA5124G	162
NSYPLA553G	162
NSYPLA553TG	162
NSYPLA554G	162
NSYPLA554TG	162
NSYPLA573G	162
NSYPLA573TG	162
NSYPLA574G	162
NSYPLA574TG	162
NSYPLA7103G	162
NSYPLA7103TG	162
NSYPLA7104G	162
NSYPLA7104TG	162
NSYPLA7123G	162
NSYPLA7123TG	162
NSYPLA7124G	162
NSYPLA7124TG	162
NSYPLA753G	162
NSYPLA753TG	162
NSYPLA754G	162
NSYPLA754TG	162
NSYPLA773G	162
NSYPLA773TG	162
NSYPLA774G	162
NSYPLA774TG	162
NSYPLA776G	162
NSYPLA776TG	162
NSYPLAT10103G	163
NSYPLAT10104G	163
NSYPLAT10123G	163
NSYPLAT10124G	163
NSYPLAT1053G	163
NSYPLAT1054G	163
NSYPLAT1073G	163
NSYPLAT1074G	163
NSYPLAT12103G	163
NSYPLAT12104G	163
NSYPLAT12123G	163
NSYPLAT12124G	163
NSYPLAT12126G	163
NSYPLAT1253G	163
NSYPLAT1254G	163
NSYPLAT1273G	163
NSYPLAT1274G	163
NSYPLAT1276G	163
NSYPLAT15103G	163
NSYPLAT15104G	163
NSYPLAT15123G	163
NSYPLAT15124G	163
NSYPLAT15126G	163

NSYP...	Page
NSYPLAT1553G	163
NSYPLAT1554G	163
NSYPLAT1573G	163
NSYPLAT1574G	163
NSYPLAT1576G	163
NSYPLAT2074G	163
NSYPLAT553G	163
NSYPLAT554G	163
NSYPLAT573G	163
NSYPLAT574G	163
NSYPLAT7103G	163
NSYPLAT7104G	163
NSYPLAT7123G	163
NSYPLAT7124G	163
NSYPLAT753G	163
NSYPLAT754G	163
NSYPLAT773G	163
NSYPLAT774G	163
NSYPLAT776G	163
NSYPLAZ10103G	162
NSYPLAZ10104G	162
NSYPLAZ10123G	162
NSYPLAZ10124G	162
NSYPLAZ1053G	162
NSYPLAZ1054G	162
NSYPLAZ1073G	162
NSYPLAZ1074G	162
NSYPLAZ12103G	162
NSYPLAZ12104G	162
NSYPLAZ12123G	162
NSYPLAZ12124G	162
NSYPLAZ12126G	162
NSYPLAZ1253G	162
NSYPLAZ1254G	162
NSYPLAZ1273G	162
NSYPLAZ1274G	162
NSYPLAZ1276G	162
NSYPLAZ15103G	162
NSYPLAZ15104G	162
NSYPLAZ15123G	162
NSYPLAZ15124G	162
NSYPLAZ15126G	162
NSYPLAZ1553G	162
NSYPLAZ1554G	162
NSYPLAZ1573G	162
NSYPLAZ1574G	162
NSYPLAZ1576G	162
NSYPLAZ2074G	162
NSYPLAZ553G	162
NSYPLAZ554G	162
NSYPLAZ573G	162
NSYPLAZ574G	162
NSYPLAZ7103G	162
NSYPLAZ7104G	162
NSYPLAZ7123G	162
NSYPLAZ7124G	162
NSYPLAZ753G	162
NSYPLAZ754G	162
NSYPLAZ773G	162
NSYPLAZ774G	162
NSYPLAZ776G	162
NSYPLAZT10103G	163
NSYPLAZT10104G	163

NSYP...	Page
NSYPLAZT10123G	163
NSYPLAZT10124G	163
NSYPLAZT1053G	163
NSYPLAZT1054G	163
NSYPLAZT1073G	163
NSYPLAZT1074G	163
NSYPLAZT12103G	163
NSYPLAZT12104G	163
NSYPLAZT12123G	163
NSYPLAZT12124G	163
NSYPLAZT12126G	163
NSYPLAZT1253G	163
NSYPLAZT1254G	163
NSYPLAZT1273G	163
NSYPLAZT1274G	163
NSYPLAZT1276G	163
NSYPLAZT15103G	163
NSYPLAZT15104G	163
NSYPLAZT15123G	163
NSYPLAZT15124G	163
NSYPLAZT15126G	163
NSYPLAZT1553G	163
NSYPLAZT1554G	163
NSYPLAZT1573G	163
NSYPLAZT1574G	163
NSYPLAZT1576G	163
NSYPLAZT2074G	163
NSYPLAZT553G	163
NSYPLAZT554G	163
NSYPLAZT573G	163
NSYPLAZT574G	163
NSYPLAZT7103G	163
NSYPLAZT7104G	163
NSYPLAZT7123G	163
NSYPLAZT7124G	163
NSYPLAZT753G	163
NSYPLAZT754G	163
NSYPLAZT773G	163
NSYPLAZT774G	163
NSYPLAZT776G	163
NSYPLHD	333, 482
NSYPLM108BG	151
NSYPLM108G	150, 155, 472, 476
NSYPLM108TG	150, 155
NSYPLM3025BG	151
NSYPLM3025G	150, 551
NSYPLM3025PG	151
NSYPLM3025TG	150
NSYPLM32BG	151, 476
NSYPLM32G	150, 476
NSYPLM32PG	151, 476
NSYPLM32TG	150, 476
NSYPLM43BG	151
NSYPLM43G	150, 155
NSYPLM43PG	151
NSYPLM43TG	150, 155
NSYPLM43TVG	150, 155
NSYPLM43VG	150
NSYPLM54BG	151
NSYPLM54G	150, 155, 466
NSYPLM54PG	151
NSYPLM54TG	150, 155, 466
NSYPLM54TVG	150, 155

Index of References

NSYP...	Page
NSYPLM54VG	150
NSYPLM57G	149
NSYPLM64BG	151
NSYPLM64G	150, 155, 466
NSYPLM64PG	151
NSYPLM64TG	150, 155, 466
NSYPLM64TVG	150, 155
NSYPLM64VG	150
NSYPLM68G	149
NSYPLM75BG	151
NSYPLM75G	150, 155, 472
NSYPLM75PG	151
NSYPLM75TG	150, 155
NSYPLM75TVG	150, 155
NSYPLM75VG	150
NSYPLM810G	149
NSYPLM86BG	151
NSYPLM86G	150, 155, 472
NSYPLM86PG	151
NSYPLM86TG	150, 155
NSYPLM86TVG	150, 155
NSYPLM86VG	150
NSYPLMRS108GA	150
NSYPLS1827G	136, 139
NSYPLS2727AG	139
NSYPLS2727G	139
NSYPLS2736AG	139
NSYPLS2736G	139
NSYPLS2754AG	139
NSYPLS2754G	139
NSYPLS30	271
NSYPLS3636G	139
NSYPLS3654AG	139
NSYPLS3654G	139
NSYPLS3672AG	139
NSYPLS5454AG	136, 139
NSYPLS5454G	139
NSYPLS5472AG	139
NSYPLSC1827G	136, 139
NSYPLSC2727AG	139
NSYPLSC2727G	139
NSYPLSC2736AG	139
NSYPLSC2736G	139
NSYPLSC2754AG	139
NSYPLSC2754G	139
NSYPLSC3636G	139
NSYPLSC3654AG	139
NSYPLSC3654G	139
NSYPLSC3672AG	139
NSYPLSC5454AG	139
NSYPLSC5454G	139
NSYPLSC5472AG	136, 139
NSYPLSP1827G	136, 139
NSYPLSP2727G	139
NSYPLSP2736G	139
NSYPLSP2754G	139
NSYPLSP3636G	139
NSYPLSP3654G	139
NSYPLSP5454G	139
NSYPMA105	513
NSYPMA107	513
NSYPMA127	513
NSYPMA1827G	139

NSYP...	Page
NSYPMA2727G	139
NSYPMA2736G	139
NSYPMA2754G	139
NSYPMA3636G	139
NSYPMA3654G	139
NSYPMA3672G	139
NSYPMA5454G	139
NSYPMA5472G	139
NSYPMA55	513
NSYPMA75	513
NSYPMA77	513
NSYPMB1010	512
NSYPMB1012	512
NSYPMB105	512
NSYPMB107	512
NSYPMB1210	512
NSYPMB1212	512
NSYPMB125	512
NSYPMB127	512
NSYPMB1510	512
NSYPMB1512	512
NSYPMB155	512
NSYPMB157	512
NSYPMB510	512
NSYPMB55	512
NSYPMB710	512
NSYPMB712	512
NSYPMB75	512
NSYPMB77	512
NSYPMD1510	18
NSYPMD2015	18
NSYPMD2520	18
NSYPMD3025	18
NSYPMM1010	515
NSYPMM1012	515
NSYPMM105	515
NSYPMM107	515
NSYPMM1210	515
NSYPMM1212	515
NSYPMM125	515
NSYPMM127	515
NSYPMM1510	515
NSYPMM1512	515
NSYPMM155	515
NSYPMM157	515
NSYPMM1827	139
NSYPMM207	515
NSYPMM2727	139
NSYPMM2736	139
NSYPMM2754	139
NSYPMM3636	139
NSYPMM3654	139
NSYPMM3672	139
NSYPMM510	515
NSYPMM5454	139
NSYPMM5472	139
NSYPMM55	515
NSYPMM710	515
NSYPMM712	515
NSYPMM75	515
NSYPMM77	515
NSYPMP45100	272
NSYPMP45120	272

NSYP...	Page
NSYPMP45160	272
NSYPMP4580	272
NSYPMP5002DLP	515
NSYPMP500DLP	515
NSYPMP600DLM	35
NSYPMP7502DLP	515
NSYPMP750DLP	515
NSYPMP800DLM	35
NSYPMP85100	272
NSYPMP85120	272
NSYPMP85160	272
NSYPMP8560	272
NSYPMP8580	272
NSYPMR105	516
NSYPMR107	516
NSYPMR125	516
NSYPMR127	516
NSYPMR155	516
NSYPMR157	516
NSYPMR1827	139
NSYPMR2727	139
NSYPMR2736	139
NSYPMR2754	139
NSYPMR3654	139
NSYPMR55	516
NSYPMR57	516
NSYPMR75	516
NSYPMR77	516
NSYPPC54HD	586
NSYPPC56HD	586
NSYPPC74HD	586
NSYPPC76HD	586
NSYPPCPHDSN	586
NSYPPS184	461
NSYPPS185	461
NSYPPS186	461
NSYPPS204	461
NSYPPS205	461
NSYPPS206	461
NSYPPS208	461
NSYPPSB	21, 91, 541
NSYPS2C27	143, 465
NSYPS4C27	465
NSYPTDS1	383
NSYPTDS2	383
NSYPTDS3	383
NSYPTDS4	383
NSYPTDS5	383
NSYPTZ3	527
NSYPTZ32P	527
NSYPTZ4	527, 549
NSYPTZ42P	527
NSYPTZ6	527
NSYPTZ62P	527
NSYPUNX	482

NSYR...	Page
NSYR19DN	309
NSYRBL216146M	216
NSYRBL216296M	216
NSYRBL21656M	216
NSYRBL21686M	216
NSYRC12	293, 299
NSYRC14	293

NSYR...	Page
NSYRC16	293
NSYRC18	293, 299
NSYRC1U	303
NSYRC20	293, 299
NSYRC22	293, 299
NSYRCDFIX	303
NSYRCDR12	301, 304
NSYRCDR18	304
NSYRCINT	304
NSYRCK19KIT	293, 298, 299
NSYRCK19KIT6G	346, 351
NSYRCK19KITN6G	346, 351
NSYRCK24	293, 298
NSYRCK29	293, 298
NSYRCK33	293, 298
NSYRCK38	293, 298
NSYRCK42	293, 298, 346, 351
NSYRCK47	293, 298
NSYRCKP12	298
NSYRCKP17	298
NSYRCKP21	298
NSYRCKP26	298
NSYRCKP4	298
NSYRCKP8	298
NSYRCKS10	293, 299
NSYRCKS6	293, 299
NSYRCKS8	293, 299
NSYRCLOCK	304
NSYRCSUP15	303
NSYRCSUP25	303
NSYRE26	398, 476
NSYRE60	398, 476
NSYRETPLA	569
NSYRETPLAU	522, 544, 551, 569
NSYRP2	271, 273
NSYRS12M	243
NSYRSF104L	581, 582
NSYRSF105L	581, 582
NSYRSF106L	581, 582
NSYRSF108L	581, 582
NSYRSF124L	581, 582
NSYRSF125L	581, 582
NSYRSF126L	581, 582
NSYRSF128L	582
NSYRSF164L	582
NSYRSF165L	582
NSYRSF166L	582
NSYRSF35L	582
NSYRSF36L	582
NSYRSF38L	582
NSYRSF44L	582
NSYRSF45L	582
NSYRSF64L	581, 582
NSYRSF65L	582
NSYRSF66L	581, 582
NSYRSF84L	581, 582
NSYRSF85L	581, 582
NSYRSF86L	581, 582
NSYRSF88L	581, 582
NSYRSFN104L	581
NSYRSFN105L	581
NSYRSFN106L	581
NSYRSFN108L	581

Index of References

NSYR...	Page
NSYRSFN124L	581
NSYRSFN125L	581
NSYRSFN126L	581
NSYRSFN64L	581
NSYRSFN66L	581
NSYRSFN84L	581
NSYRSFN85L	581
NSYRSFN86L	581
NSYRSFN88L	581
NSYRSW27	293, 301
NSYRSW31	293, 301
NSYRSW36	293, 301
NSYRSW40	293, 301
NSYRSW45	293, 301
NSYRSW636	293, 301
NSYRSW640	293, 301
NSYRSW645	293, 301
NSYRSWC36	293, 302
NSYRSWC40	293, 302
NSYRSWC45	293, 302
NSYRSWH180	302
NSYRSWP12	300
NSYRSWP15	300
NSYRSWP18	300
NSYRSWP21	300
NSYRSWP6	300
NSYRSWP9	300
NSYRSWSP6	300
NSYRSWSP8	300

NSYS...	Page
NSYS04	216
NSYS06	216
NSYS10	216
NSYS13M5HS	47, 541
NSYS16	216
NSYS16M5HS	541
NSYS16M6HS	541
NSYS2535	216
NSYS3CM303020	279, 281, 284
NSYS3CM304020	279, 281, 284
NSYS3CM404020	279, 281, 284
NSYS3CM406025	279, 281, 284
NSYS3CM505025	279, 281, 284
NSYS3CM606020	279, 281, 284
NSYS3CM608030	284
NSYS3D101030	47
NSYS3D101030D	47, 57
NSYS3D101030DP	47
NSYS3D101030DT	47
NSYS3D101030P	47
NSYS3D101030T	47
NSYS3D101230D	47
NSYS3D101230DP	47
NSYS3D101240D	47
NSYS3D101240DP	47
NSYS3D10625	47, 57, 290
NSYS3D10625P	47
NSYS3D10625T	47, 290
NSYS3D10630	47, 290
NSYS3D10630P	47
NSYS3D10630T	47, 290
NSYS3D10640	47, 290
NSYS3D10640P	47

NSYS...	Page
NSYS3D10640T	47, 290
NSYS3D10825	47, 290
NSYS3D10825P	47
NSYS3D10825T	47, 290
NSYS3D10830	47, 57, 290
NSYS3D10830P	47
NSYS3D10830T	47, 290
NSYS3D10840	47, 290
NSYS3D10840P	47
NSYS3D10840T	47, 290
NSYS3D121030	47
NSYS3D121030D	47
NSYS3D121030DP	47
NSYS3D121030DT	47
NSYS3D121030P	47
NSYS3D121030T	47
NSYS3D121040D	47
NSYS3D121040DP	47
NSYS3D121230D	47
NSYS3D121230DP	47
NSYS3D121240D	47
NSYS3D121240DP	47
NSYS3D12630	47
NSYS3D12630P	47
NSYS3D12630T	47
NSYS3D12640	47
NSYS3D12640P	47
NSYS3D12640T	47
NSYS3D12830	47, 290
NSYS3D12830P	47
NSYS3D12830T	47, 290
NSYS3D12840	47, 290
NSYS3D12840P	47
NSYS3D12840T	47, 290
NSYS3D141030D	47, 57
NSYS3D141030DP	47
NSYS3D3215	47, 57
NSYS3D3215P	47
NSYS3D32515	47
NSYS3D32515P	47
NSYS3D32515T	47
NSYS3D3315	47
NSYS3D3315P	47
NSYS3D3315T	47
NSYS3D3320	47
NSYS3D3320P	47
NSYS3D3320T	47
NSYS3D3415	47
NSYS3D3415P	47
NSYS3D3415T	47
NSYS3D3420	47
NSYS3D3420P	47
NSYS3D3420T	47
NSYS3D4315	47
NSYS3D4315P	47
NSYS3D4315T	47
NSYS3D4320	47
NSYS3D4320P	47
NSYS3D4320T	47
NSYS3D4420	47
NSYS3D4420P	47
NSYS3D4420T	47
NSYS3D4620	47, 290

NSYS...	Page
NSYS3D4620P	47
NSYS3D4620T	47, 290
NSYS3D4625	47, 290
NSYS3D4625P	47
NSYS3D4625T	47, 290
NSYS3D5320	47, 57
NSYS3D5320P	47
NSYS3D5320T	47
NSYS3D5420	47, 57
NSYS3D5420P	47
NSYS3D5420T	47
NSYS3D5425	47
NSYS3D5425P	47
NSYS3D5425T	47
NSYS3D5520	47
NSYS3D5520P	47
NSYS3D5520T	47
NSYS3D5525	47
NSYS3D5525P	47
NSYS3D5525T	47
NSYS3D6420	47
NSYS3D6420P	47
NSYS3D6420T	47
NSYS3D6425	47, 57
NSYS3D6425P	47
NSYS3D6425T	47
NSYS3D6525	47
NSYS3D6525P	47
NSYS3D6525T	47
NSYS3D6620	47, 57, 290
NSYS3D6620P	47
NSYS3D6620T	47, 290
NSYS3D6625	47, 290
NSYS3D6625P	47
NSYS3D6625T	47, 290
NSYS3D6630	47, 290
NSYS3D6630P	47
NSYS3D6630T	47, 290
NSYS3D6640	47, 290
NSYS3D6640P	47
NSYS3D6640T	47, 290
NSYS3D6830	47
NSYS3D6830P	47
NSYS3D6830T	47
NSYS3D6G12840P	338
NSYS3D6G32515P	338
NSYS3D6G4320P	338
NSYS3D6G7525P	338
NSYS3D6G8630P	338
NSYS3D7525	47
NSYS3D7525P	47
NSYS3D7525T	47
NSYS3D81030	47
NSYS3D81030D	47
NSYS3D81030DP	47
NSYS3D81030P	47
NSYS3D81230D	47
NSYS3D81230DP	47
NSYS3D8620	47, 290
NSYS3D8620P	47
NSYS3D8620T	47, 290
NSYS3D8625	47, 290
NSYS3D8625P	47

NSYS...	Page
NSYS3D8625T	47, 290
NSYS3D8630	47, 57, 290
NSYS3D8630P	47
NSYS3D8630T	47, 290
NSYS3D8640	47, 290
NSYS3D8640P	47
NSYS3D8640T	47, 290
NSYS3D8825	47
NSYS3D8825P	47
NSYS3D8825T	47
NSYS3D8830	47
NSYS3D8830P	47
NSYS3D8830T	47
NSYS3DB25315	229
NSYS3DB25415	229
NSYS3DB25515	229
NSYS3DB3415	229
NSYS3DB3515	229
NSYS3DB3615	229
NSYS3DB4815	229
NSYS3DB6415	229
NSYS3DCGPSTDSB	578-580
NSYS3DCGSB	578-580
NSYS3DEX10830	369
NSYS3DEX3215	369
NSYS3DEX3320	369
NSYS3DEX4320	369
NSYS3DEX4420	369
NSYS3DEX5420	369
NSYS3DEX6425	369
NSYS3DEX6625	369
NSYS3DEX7525	369
NSYS3DEX8630	369
NSYS3DLG	578, 579, 586
NSYS3DM10615T	228
NSYS3DM10815T	228
NSYS3DM4315T	228
NSYS3DM5415T	228
NSYS3DM6415T	228
NSYS3DM6615T	228
NSYS3DM7515T	228
NSYS3DM8615T	228
NSYS3DTL	578
NSYS3HD10640	326, 407
NSYS3HD10840	326, 407
NSYS3HD3215	326
NSYS3HD4320	326
NSYS3HD5420	326
NSYS3HD6425	326
NSYS3HD6630	326
NSYS3HD7525	326
NSYS3HD8630	326, 407
NSYS3HD8840	326, 407
NSYS3HF10830P	378
NSYS3HF4320P	378
NSYS3HF6420P	378
NSYS3HF6625P	378
NSYS3HF8630P	378
NSYS3X101030	101
NSYS3X101030H	101
NSYS3X10830	101
NSYS3X10830H	101
NSYS3X10830T	101

Index of References

NSYS...	Page
NSYS3X121030	101
NSYS3X121030H	101
NSYS3X12830	101
NSYS3X12830H	101
NSYS3X302515	101
NSYS3X302515H	101
NSYS3X3215	101
NSYS3X3215H	101
NSYS3X3315	101
NSYS3X3315H	101
NSYS3X4315	101
NSYS3X4315H	101
NSYS3X4320	101
NSYS3X4320H	101
NSYS3X4320T	101
NSYS3X4420	101
NSYS3X4420H	101
NSYS3X4620	101
NSYS3X4620H	101
NSYS3X5420	101
NSYS3X5420H	101
NSYS3X5420T	101
NSYS3X601030	101
NSYS3X601230	101
NSYS3X6420	101
NSYS3X6420H	101
NSYS3X6420T	101
NSYS3X6625	101
NSYS3X6625H	101
NSYS3X7525	101
NSYS3X7525H	101
NSYS3X7525T	101
NSYS3X801030	101
NSYS3X801230	101
NSYS3X8625	101
NSYS3X8625H	101
NSYS3X8625T	101
NSYS3X8830	101
NSYS3X8830H	101
NSYS50	216
NSYS70	216
NSYS95100	216
NSYSBM151512	21
NSYSBM15158	21
NSYSBM152012	21
NSYSBM15208	21
NSYSBM153012	21
NSYSBM15308	21
NSYSBM154012	21
NSYSBM15408	21
NSYSBM202012	21
NSYSBM20208	21
NSYSBM203012	21
NSYSBM20308	21
NSYSBM204012	21
NSYSBM20408	21
NSYSBM205012	21
NSYSBM20508	21
NSYSBM206012	21
NSYSBM20608	21
NSYSBM208012	21
NSYSBM303012	21
NSYSBM304012	21

NSYS...	Page
NSYSBM305012	21
NSYSBM306012	21
NSYSBM308012	21
NSYSBM404012	21
NSYSBM405012	21
NSYSBM406012	21
NSYSBM408012	21
NSYSBMABS4	578
NSYSBMABS6	578
NSYSBPLA	536, 539
NSYSBTB	520
NSYSBX15158	91, 94
NSYSBX15308	91, 94
NSYSBX20208	91, 94
NSYSBX20308	91, 94
NSYSBX204012	91, 94
NSYSBX303012	91, 94
NSYSC1030	458
NSYSC1040	458
NSYSC1050	458
NSYSC1060	458
NSYSC1230	458
NSYSC1240	458
NSYSC124HD	588
NSYSC1250	458
NSYSC1260	458
NSYSC126HD	588
NSYSC1640	458
NSYSC1650	458
NSYSC630	458
NSYSC640	458
NSYSC64HD	588
NSYSC660	458
NSYSC66HD	588
NSYSC830	458
NSYSC840	458
NSYSC84HD	588
NSYSC850	458
NSYSC860	458
NSYSC86HD	588
NSYSCCDINLG140	505
NSYSCCDINLG75	505
NSYSCMX10030	459
NSYSCMX10040	459
NSYSCMX12040	459
NSYSCMX16060	459
NSYSCMX8040	459
NSYSCMX8050	459
NSYSCX10060	459
NSYSCX12040	459
NSYSCX12050	459
NSYSCX12060	459
NSYSCX16040	459
NSYSCX16060	459
NSYSCX6040	459
NSYSCX8040	459
NSYSCX8060	459
NSYSD10	266, 270, 271
NSYSD10R	266, 270, 271, 273
NSYSD12	266, 270, 271
NSYSD12R	266, 270, 271, 273
NSYSD6	266, 270, 271
NSYSD6R	266, 270, 271, 273

NSYS...	Page
NSYSD8	266, 270, 271
NSYSD8R	266, 270, 271, 273
NSYSDC42	271, 273
NSYSDC43	271, 273
NSYSDC62	271, 273
NSYSDC63	271, 273
NSYSDCR10	527
NSYSDCR200	35, 48, 101, 521
NSYSDCR250	35, 48, 101, 521
NSYSDCR300	35, 48, 101, 521
NSYSDCR4	527
NSYSDCR400	35, 48, 521
NSYSDCR5	527
NSYSDCR6	527
NSYSDCR8	527
NSYSDF1010	267, 270, 271
NSYSDF108	267, 270, 271
NSYSDF1210	267, 270, 271
NSYSDF128	267, 270, 271
NSYSDF1610	267, 270, 271
NSYSDF168	267, 270, 271
NSYSDF810	267, 270, 271
NSYSDF88	267, 270, 271
NSYSDFLOCKDB5	585
NSYSDGCR5	568
NSYSDGCR6	568
NSYSDGCR8	568
NSYSDH	585
NSYSDP6M	570
NSYSDP8M	570
NSYSDR100A	531
NSYSDR200	532
NSYSDR200B	532
NSYSDR200BD	532
NSYSDR200D	532
NSYSDR30B	531
NSYSDR40B	531
NSYSDR50A	531
NSYSDR60A	531
NSYSDR80A	531
NSYSDRC	569
NSYSDT5	539
NSYSDT6	539
NSYSDT8	539
NSYSFBK	464
NSYSFBK19	198, 346, 361, 464
NSYSFBKE	465
NSYSFBKF	465
NSYSFBKR	346, 361, 465
NSYSFD128	582
NSYSFD146	582
NSYSFD148	582
NSYSFD166	582
NSYSFD168	582
NSYSFD1810	582
NSYSFD18102D	582
NSYSFD18122D	582
NSYSFD186	582
NSYSFD188	582
NSYSFD2010	582
NSYSFD20122D	582
NSYSFD20162D	582
NSYSFD206	582

NSYS...	Page
NSYSFD208	582
NSYSFDHD12122D	588
NSYSFDHD126	588
NSYSFDHD128	588
NSYSFDHD16122D	588
NSYSFDHD166	588
NSYSFDHD168	588
NSYSFDHD208	588
NSYSFEB	198, 482
NSYSFECA64HD	587, 588
NSYSFECA66HD	587, 588
NSYSFELB	198, 482
NSYSFHD2	561
NSYSFHD3	561
NSYSFHFBK206	379
NSYSFHNTRIM	581, 582
NSYSFHPB	562
NSYSFHS1	581
NSYSFHS1HD	587, 588
NSYSFLOCKT7	557
NSYSFMDR	569
NSYSFN12640	75
NSYSFN12640P	75
NSYSFN12660	75
NSYSFN12660P	75
NSYSFN12840	75
NSYSFN12840P	75
NSYSFN12860	75
NSYSFN12860P	75
NSYSFN14640	75
NSYSFN14640P	75
NSYSFN14840	75
NSYSFN14840P	75
NSYSFN16660	75
NSYSFN16660P	75
NSYSFN16680	75
NSYSFN16680P	75
NSYSFN16860	75
NSYSFN16860P	75
NSYSFN16880	75
NSYSFN16880P	75
NSYSFN181040	75
NSYSFN1810402D	75
NSYSFN1810402DP	75
NSYSFN181040P	75
NSYSFN181050	75
NSYSFN181050P	75
NSYSFN181060	75
NSYSFN1810602D	75
NSYSFN1810602DP	75
NSYSFN181060P	75
NSYSFN1812402D	75
NSYSFN1812402DP	75
NSYSFN1812502D	75
NSYSFN1812502DP	75
NSYSFN1812602D	75
NSYSFN1812602DP	75
NSYSFN1816402D	75
NSYSFN18440	75, 213
NSYSFN18450	75, 213
NSYSFN18460	75, 213
NSYSFN18640	75
NSYSFN18640P	75

Index of References

NSYS...	Page
NSYSFN18640T	75
NSYSFN18650	75
NSYSFN18650P	75
NSYSFN18650T	75
NSYSFN18660	75
NSYSFN18660P	75
NSYSFN18680T	75
NSYSFN18840	75
NSYSFN18840P	75
NSYSFN18840T	75
NSYSFN18850	75
NSYSFN18850P	75
NSYSFN18850T	75
NSYSFN18860	75
NSYSFN188602D	75
NSYSFN188602DP	75
NSYSFN18860P	75
NSYSFN18860T	75
NSYSFN201040	75
NSYSFN2010402D	75
NSYSFN2010402DP	75
NSYSFN201040P	75
NSYSFN201040T	75
NSYSFN201050	75
NSYSFN2010502D	75
NSYSFN2010502DP	75
NSYSFN201050P	75
NSYSFN201050T	75
NSYSFN201060	75
NSYSFN2010602D	75
NSYSFN2010602DP	75
NSYSFN201060P	75
NSYSFN201060T	75
NSYSFN201080	75
NSYSFN201080P	75
NSYSFN2012402D	75
NSYSFN2012402DP	75
NSYSFN2012502D	75
NSYSFN2012502DP	75
NSYSFN2012602D	75
NSYSFN2012602DP	75
NSYSFN2012802D	75
NSYSFN2012802DP	75
NSYSFN2016402D	75
NSYSFN2016402DP	75
NSYSFN2016502D	75
NSYSFN2016502DP	75
NSYSFN2016602D	75
NSYSFN2016602DP	75
NSYSFN20350	75, 197, 213
NSYSFN20350ED	197
NSYSFN20360	75, 197, 213, 253
NSYSFN20380	75, 197, 213, 253
NSYSFN20380ED	197
NSYSFN20440	75, 213
NSYSFN20450	75, 213
NSYSFN20460	75, 213, 253
NSYSFN20480	75, 213, 253
NSYSFN20640	75
NSYSFN20640P	75
NSYSFN20640T	75
NSYSFN20650	75
NSYSFN20650P	75
NSYSFN20650T	75
NSYSFN20660	75
NSYSFN20660P	75
NSYSFN20680	75
NSYSFN20680P	75
NSYSFN20840	75
NSYSFN20840P	75
NSYSFN20840T	75
NSYSFN20850	75
NSYSFN20850P	75
NSYSFN20850T	75
NSYSFN20860	75
NSYSFN208602D	75
NSYSFN208602DNU	361
NSYSFN208602DP	75
NSYSFN20860NUC	361
NSYSFN20860P	75
NSYSFN20860T	75
NSYSFN20880	75
NSYSFN20880P	75
NSYSFN20880T	75
NSYSFN221060	75
NSYSFN221060P	75
NSYSFN2212602D	75
NSYSFN2212602DP	75
NSYSFN2212802D	75
NSYSFN2212802DP	75
NSYSFN22460	75, 213
NSYSFN22660	75
NSYSFN22660P	75
NSYSFN22680	75
NSYSFN22680P	75
NSYSFN22860	75
NSYSFN22860P	75
NSYSFN22880	75
NSYSFN22880P	75
NSYSFN22880T	75
NSYSFN6G20860	346
NSYSFNC104	76, 77
NSYSFNC105	76, 77
NSYSFNC106	76, 77
NSYSFNC108	76, 77
NSYSFNC124	76, 77
NSYSFNC125	76, 77
NSYSFNC126	76, 77
NSYSFNC128	76, 77
NSYSFNC164	77
NSYSFNC165	77
NSYSFNC166	77
NSYSFNC35	77, 197
NSYSFNC35ED	197
NSYSFNC36	77, 253
NSYSFNC38	77, 253
NSYSFNC44	76, 77
NSYSFNC45	76, 77
NSYSFNC46	76, 77, 253
NSYSFNC48	76, 77, 253
NSYSFNC610	77, 293
NSYSFNC64	76, 77
NSYSFNC65	76, 77
NSYSFNC66	76, 77, 252, 260, 293
NSYSFNC68	76, 77, 252, 260, 293
NSYSFNC75	197
NSYSFNC75ED	197
NSYSFNC810	77, 293
NSYSFNC84	76, 77
NSYSFNC85	76, 77
NSYSFNC86	76, 77, 252, 293
NSYSFNC88	76, 77, 252, 293
NSYSFNCVR64HD	327, 407
NSYSFNCVR66HD	327, 407
NSYSFNCVR84HD	327, 407
NSYSFNCVR86HD	327, 407
NSYSFNCVR88HD	327, 407
NSYSFND126	76, 293, 554
NSYSFND126T	76, 293
NSYSFND128	76, 293, 554
NSYSFND128T	76, 293
NSYSFND146	76, 293, 554
NSYSFND146T	76, 293
NSYSFND148	76, 293, 554
NSYSFND148T	76, 293
NSYSFND166	76, 260, 293, 554
NSYSFND166T	76, 293
NSYSFND168	76, 293, 554
NSYSFND168T	76, 293
NSYSFND1810	76
NSYSFND18102D	76
NSYSFND1810T	76
NSYSFND18122D	76
NSYSFND18122DT	76
NSYSFND184	76, 554
NSYSFND185	554
NSYSFND186	76, 260, 293, 554
NSYSFND186T	76, 293
NSYSFND188	76, 293, 554
NSYSFND1882D	76
NSYSFND188T	76, 293
NSYSFND2010	77
NSYSFND20102D	77
NSYSFND20102DI	388
NSYSFND2010T	77
NSYSFND20122D	77
NSYSFND20122DI	388
NSYSFND20122DT	77
NSYSFND20162D	77
NSYSFND203	77, 253
NSYSFND203ED	581
NSYSFND204	77, 253, 554
NSYSFND205	554
NSYSFND206	77, 293, 554
NSYSFND206T	77, 293
NSYSFND207ED	581
NSYSFND207G	581
NSYSFND207TED	581
NSYSFND207TG	581
NSYSFND208	77, 293, 554
NSYSFND20802DI	388
NSYSFND2082D	77
NSYSFND208T	77, 293
NSYSFND2210	77
NSYSFND22102DI	388
NSYSFND2210T	77
NSYSFND22122D	77
NSYSFND22122DI	388
NSYSFND22122DT	77
NSYSFND224	77, 554
NSYSFND225	554
NSYSFND226	77, 293, 554
NSYSFND226T	77, 293
NSYSFND228	77, 293, 554
NSYSFND22802DI	388
NSYSFND228T	77, 293
NSYSFNDR	569
NSYSFNHD18640	327, 407
NSYSFNHD18840	327, 407
NSYSFNHD18860	327, 407
NSYSFNHD18880	327, 407
NSYSFNHD20660	327, 407
NSYSFNHD20840	327, 407
NSYSFNHD20860	327, 407
NSYSFNHF20860	378
NSYSFNHS1	561, 581
NSYSFNPB	520
NSYSFNPCMK600	260
NSYSFNPCPD600	260
NSYSFNPCPD600T	260
NSYSFNRB3G	354
NSYSFNRB6003G	357
NSYSFNRB8003G	357
NSYSFNV12	76, 293
NSYSFNV14	76, 293
NSYSFNV16	76, 260, 293
NSYSFNV18	76, 260, 293
NSYSFNV20	77, 197, 252, 253, 293
NSYSFNV20ED	197
NSYSFNV22	77, 293
NSYSFP300	480
NSYSFP400	480
NSYSFP500	480
NSYSFP600	480
NSYSFPAED	188, 197, 219
NSYSFPB6G	346, 350
NSYSFPN20750ED	197
NSYSFPN20750G	197
NSYSFPN20750TED	197
NSYSFPN20750TG	197
NSYSFPN20760G	197
NSYSFPN20760TG	197
NSYSFPN20780ED	197
NSYSFPN20780G	197
NSYSFPN20780TED	197
NSYSFPN20780TG	197
NSYSFPSC30	21, 36, 48, 480
NSYSFPSC40	21, 36, 48, 480
NSYSFPSC50	21, 36, 48, 480
NSYSFPSC60	21, 36, 48, 480
NSYSFPSC80	21, 36, 48, 480
NSYSFSPLMG	466
NSYSFTB16	482
NSYSFTB18	482
NSYSFTB24	482
NSYSFTB32	482
NSYSFWFIX	479
NSYSFX181240	111
NSYSFX18640	111
NSYSFX18840	111

Index of References

NSYS...	Page
NSYSFX201060	111
NSYSFX201260	111
NSYSFX20650	111
NSYSFX20840	111
NSYSFX20860	111
NSYSFXJG	464
NSYSGF	468, 475
NSYSH180NC	555
NSYSIBTB	520
NSYSICR4040	527
NSYSICR4050	527
NSYSICR4060	527
NSYSICR4080	527
NSYSICR65100	527
NSYSICR6560	527
NSYSICR6580	527
NSYSICR90100	527
NSYSICR9040	527
NSYSICR9060	527
NSYSICR9080	527
NSYSIMP12	75, 518
NSYSIMP14	75, 518
NSYSIMP16	75, 518
NSYSIMP18	75, 518
NSYSIMP20	75, 518
NSYSIMP22	75, 518
NSYSLCKP	388
NSYSLCKS10	388
NSYSLCKS6	388
NSYSLCKS8	388
NSYSLCR40	526
NSYSLCR50	526
NSYSLCR60	526
NSYSLCR80	526
NSYSLINK1000	388
NSYSLINK1200	388
NSYSLINK800	388
NSYSM1210302D	65
NSYSM1210302DP	65
NSYSM1212402D	65
NSYSM1212402DP	65
NSYSM12830	65
NSYSM12830P	65
NSYSM1410402D	65
NSYSM1410402DP	65
NSYSM1412402D	65
NSYSM1412402DP	65
NSYSM14630	65
NSYSM14630P	65
NSYSM14640	65
NSYSM14640P	65
NSYSM14830	65
NSYSM14830P	65
NSYSM14840	65
NSYSM14840P	65
NSYSM14840T	65
NSYSM1610302D	65
NSYSM1610302DP	65
NSYSM1610402D	65
NSYSM1610402DP	65
NSYSM1612302D	65
NSYSM1612302DP	65
NSYSM1612402D	65
NSYSM1612402DP	65
NSYSM16630	65
NSYSM16630P	65
NSYSM16640	65
NSYSM16640P	65
NSYSM16640T	65
NSYSM16830	65
NSYSM16830P	65
NSYSM16840	65
NSYSM16840P	65
NSYSM16840T	65
NSYSM181040	65
NSYSM1810402D	65
NSYSM1810402DP	65
NSYSM181040P	65
NSYSM1810502D	65
NSYSM1810502DP	65
NSYSM1812402D	65
NSYSM1812402DP	65
NSYSM1812502D	65
NSYSM1812502DP	65
NSYSM1816402D	65
NSYSM1816402DP	65
NSYSM1816502D	65
NSYSM1816502DP	65
NSYSM18630	65
NSYSM18630P	65
NSYSM18640	65
NSYSM18640P	65
NSYSM18640T	65
NSYSM18650	65
NSYSM18650P	65
NSYSM18830	65
NSYSM18830P	65
NSYSM18830T	65
NSYSM18840	65
NSYSM18840P	65
NSYSM18840T	65
NSYSM18850	65
NSYSM18850P	65
NSYSM18850T	65
NSYSM18860	65
NSYSM18860P	65
NSYSM2010402D	65
NSYSM2010402DP	65
NSYSM2010502D	65
NSYSM2010502DP	65
NSYSM2012402D	65
NSYSM2012402DP	65
NSYSM2012502D	65
NSYSM2012502DP	65
NSYSM2012602D	65
NSYSM2012602DP	65
NSYSM2016402D	65
NSYSM2016402DP	65
NSYSM2016502D	65
NSYSM2016502DP	65
NSYSM2016602D	65
NSYSM2016602DP	65
NSYSM20630	65
NSYSM20630P	65
NSYSM20640	65
NSYSM20640P	65
NSYSM20640T	65
NSYSM20650	65
NSYSM20650P	65
NSYSM20830	65
NSYSM20830P	65
NSYSM20830T	65
NSYSM20840	65
NSYSM20840P	65
NSYSM20840T	65
NSYSM20850	65
NSYSM20850P	65
NSYSM20850T	65
NSYSM20860	65
NSYSM20860P	65
NSYSM20860T	65
NSYSMBCE10	503
NSYSMBCE6	503
NSYSMBCE8	503
NSYSMBK	464
NSYSMDN12102D	582
NSYSMDN12122D	582
NSYSMDN14102D	582
NSYSMDN14122D	582
NSYSMDN16102D	582
NSYSMDN16122D	582
NSYSMDN18162D	582
NSYSMDR	569
NSYSMEB	482
NSYSMEC1031	582
NSYSMEC104	500
NSYSMEC1041	582
NSYSMEC1051	582
NSYSMEC63	500
NSYSMEC631	582
NSYSMEC64	500
NSYSMEC641	582
NSYSMEC65	500
NSYSMEC661	582
NSYSMEC83	500
NSYSMEC831	582
NSYSMEC84	500
NSYSMEC841	582
NSYSMEC85	500
NSYSMEC851	582
NSYSMEC86	500
NSYSMEC861	582
NSYSMHR10	531
NSYSMHR12	531
NSYSMHR16	531
NSYSMHR6	531
NSYSMHR8	531
NSYSMNDR	569
NSYSMNPB	514, 520, 521
NSYSMP2D4	521
NSYSMP2D5	205, 521
NSYSMP2D6	521
NSYSMP2D8	521
NSYSMPFA	519
NSYSMPFB	519
NSYSMPS	514
NSYSMPS4	519
NSYSMPS5	519
NSYSMPS6	519
NSYSMPS8	519
NSYSMPSB	514, 520
NSYSMPSE10	521
NSYSMPSE12	521
NSYSMPSE6	521
NSYSMPSE8	521
NSYSMVR12	531
NSYSMVR14	531
NSYSMVR16	531
NSYSMVR18	531
NSYSMVR20	531
NSYSMWFIX	479
NSYSMX141030	111
NSYSMX16840	111
NSYSMX181240	111
NSYSMX181640	111
NSYSMX181640H	111
NSYSMX18640	111
NSYSMX18840	111
NSYSMX18840H	111
NSYSMX201040	111
NSYSMX201040H	111
NSYSMX201250	111
NSYSMX201250H	111
NSYSMX201660	111
NSYSMX201660H	111
NSYSMX20850	111
NSYSMXEB	482
NSYSNLPLA	569
NSYSNM6	530, 536
NSYSNM8	530, 536
NSYSNSM6	536
NSYSNSM8	536
NSYSODS	388
NSYSPB6100	471
NSYSPB8100	471
NSYSPBCN35	212
NSYSPBCN36	212
NSYSPBCN38	212
NSYSPC	507
NSYSPCP	507
NSYSPCR	475
NSYSPF10100	35, 48, 65, 75, 270, 293, 469
NSYSPF10200	35, 48, 65, 75, 270, 293, 469
NSYSPF12100	35, 48, 65, 75, 270, 469
NSYSPF12200	35, 48, 65, 75, 270, 469
NSYSPF16100	65, 75, 270, 469
NSYSPF16200	65, 75, 270, 469
NSYSPF3100	75, 197, 469
NSYSPF3200	75, 197, 469
NSYSPF4100	75, 469
NSYSPF4200	75, 469
NSYSPF6100	35, 48, 65, 75, 270, 293, 469
NSYSPF6200	35, 48, 65, 75, 270, 293, 469
NSYSPF7100	197
NSYSPF7200	197
NSYSPF8100	35, 48, 65, 75, 270, 293, 469
NSYSPF8200	35, 48, 65, 75, 270, 293, 469

Index of References

NSYS...	Page
NSYSPFV6100	471
NSYSPFV8100	471
NSYSPFVX12200	471
NSYSPFVX6200	407, 471
NSYSPFVX8200	407, 471
NSYSPFX10100	470
NSYSPFX10100H	470
NSYSPFX10200	470
NSYSPFX10200H	470
NSYSPFX12100	470
NSYSPFX12100H	470
NSYSPFX12200	470
NSYSPFX12200H	470
NSYSPFX16100	470
NSYSPFX16100H	470
NSYSPFX16200	470
NSYSPFX16200H	470
NSYSPFX6100	470
NSYSPFX6200	470
NSYSPFX8100	470
NSYSPFX8100H	470
NSYSPFX8200	470
NSYSPFX8200H	470
NSYSPLA100	539, 549
NSYSPLA125	539, 549
NSYSPLA150	408, 539, 549
NSYSPLA75	539, 549
NSYSPLK	475
NSYSPLVX4200SF	471
NSYSPLVX6200SF	471
NSYSPM6	468, 541
NSYSPMP25100	518
NSYSPMP25120	518
NSYSPMP2560	518
NSYSPMP2575	518
NSYSPMP2580	518
NSYSPMP40100	518
NSYSPMP40120	518
NSYSPMP4060	518
NSYSPMP4080	518
NSYSPMP60120	518
NSYSPMP6060	518
NSYSPMP6080	518
NSYSPRJ	481
NSYSPS10100	469
NSYSPS10200	469
NSYSPS12100	469
NSYSPS12200	469
NSYSPS3100	65, 469
NSYSPS3100SD	35, 48, 469
NSYSPS3200	65, 469
NSYSPS3200SD	35, 48, 469
NSYSPS4100	65, 75, 469
NSYSPS4100SD	35, 48, 270, 469
NSYSPS4200	65, 75, 469
NSYSPS4200SD	35, 48, 270, 469
NSYSPS5100	65, 75, 197, 469
NSYSPS5100SD	270, 469
NSYSPS5200	65, 75, 197, 469
NSYSPS5200SD	270, 469
NSYSPS6100	65, 75, 197, 293, 469
NSYSPS6100SD	270, 469
NSYSPS6200	65, 75, 197, 293, 469
NSYSPS6200SD	270, 469
NSYSPS8100	75, 197, 293, 469
NSYSPS8200	75, 197, 293, 469
NSYSPSJ	481
NSYSPSX3100	470
NSYSPSX3200	407, 470
NSYSPSX4100	470
NSYSPSX4100H	470
NSYSPSX4100SF	470
NSYSPSX4200	470
NSYSPSX4200H	470
NSYSPSX4200SF	470
NSYSPSX5100	470
NSYSPSX5100H	470
NSYSPSX5100SF	470
NSYSPSX5200	470
NSYSPSX5200H	470
NSYSPSX5200SF	470
NSYSPSX6100	470
NSYSPSX6100H	470
NSYSPSX6100SF	470
NSYSPSX6200	470
NSYSPSX6200H	470
NSYSPSX6200SF	470
NSYSPSX8100SF	470
NSYSPSX8200SF	470
NSYSPV6100	471
NSYSPV8100	471
NSYSQCR12040	526
NSYSQCR12050	526
NSYSQCR12060	526
NSYSQCR12080	526
NSYSQCR40100	526
NSYSQCR40120	526
NSYSQCR4040	526
NSYSQCR4050	526
NSYSQCR4060	526
NSYSQCR4080	526
NSYSQCR65100	526
NSYSQCR65120	526
NSYSQCR6540	526
NSYSQCR6550	526
NSYSQCR6560	526
NSYSQCR6580	526
NSYSQCR90100	526
NSYSQCR90120	526
NSYSQCR9040	526
NSYSQCR9050	526
NSYSQCR9060	526
NSYSQCR9080	526
NSYST30M6S	525-527
NSYSTBR3	521
NSYSTBR4	521
NSYSTBR5	521
NSYSTBR6	521
NSYSTDCSX	559
NSYSTDCX2H	559
NSYSTDCXH	559
NSYSTDNCSX	559
NSYSTMP22100	517
NSYSTMP22120	517
NSYSTMP2260	517
NSYSTMP2280	517
NSYSTMP45100	517
NSYSTMP45120	517
NSYSTMP4560	517
NSYSTMP4580	517
NSYSTMP60100	517
NSYSTMP60120	517
NSYSTMP6060	517
NSYSTMP6080	517
NSYSTMP82100	517
NSYSTMP82120	517
NSYSTMP8260	517
NSYSTMP8280	517
NSYSTW	481
NSYSUCR200WM	528
NSYSUCR250WM	528
NSYSUCR300WM	528
NSYSUCR400WM	528
NSYSUCR40100	525
NSYSUCR40110	525
NSYSUCR40120	525
NSYSUCR40140	525
NSYSUCR40160	525
NSYSUCR40180	525
NSYSUCR40200	197, 249, 525
NSYSUCR40220	525
NSYSUCR4030	525
NSYSUCR4040	525
NSYSUCR4050	525
NSYSUCR4060	525
NSYSUCR4070	525
NSYSUCR4080	525
NSYSUCR4090	525
NSYSUCR65100	525
NSYSUCR65120	525
NSYSUCR65140	525
NSYSUCR65160	525
NSYSUCR65180	525
NSYSUCR65200	525
NSYSUCR6530	525
NSYSUCR6540	525
NSYSUCR6550	525
NSYSUCR6560	525
NSYSUCR6580	525
NSYSUCR90100	525
NSYSUCR90120	525
NSYSUCR90140	525
NSYSUCR90160	525
NSYSUCR90180	525
NSYSUCR90200	525
NSYSUCR90220	525
NSYSUCR9030	525
NSYSUCR9040	525
NSYSUCR9050	525
NSYSUCR9060	525
NSYSUCR9070	525
NSYSUCR9080	525
NSYSUPLA3G	464
NSYSUPLA3TG	464
NSYSUPLA4G	464
NSYSUPLA4TG	464
NSYSW	481
NSYSWMBP	578-580, 586
NSYSWMCH	578-580, 586
NSYSWMEL	578-580, 585, 586

NSYT...	Page
NSYTBCN3105	212
NSYTBCN3106	212
NSYTBCN3108	212
NSYTBCN3125	212
NSYTBCN3126	212
NSYTBCN3128	212
NSYTBCN345	212
NSYTBCN346	212
NSYTBCN348	212
NSYTBCN365	212
NSYTBCN366	212
NSYTBCN368	212
NSYTBCN385	212
NSYTBCN386	212
NSYTBCN388	212
NSYTBP11116	126
NSYTBP1176	126
NSYTBP1397	126
NSYTBP1397T	126
NSYTBP16128	126
NSYTBP16128T	126
NSYTBP191210H	126
NSYTBP191210HT	126
NSYTBP19128	126
NSYTBP19128T	126
NSYTBP191610H	126
NSYTBP191610HT	126
NSYTBP19168	126
NSYTBP19168T	126
NSYTBP241910	126
NSYTBP241910H	126
NSYTBP241910HT	126
NSYTBP241910T	126
NSYTBP241912H	126
NSYTBP241912HT	126
NSYTBP24198	126
NSYTBP24198T	126
NSYTBP292412	126
NSYTBP292412H	126
NSYTBP292412HT	126
NSYTBP292412T	126
NSYTBP292416H	126
NSYTBP292416HT	126
NSYTBP29248	126
NSYTBP29248T	126
NSYTBP342912	126
NSYTBP342912T	126
NSYTBP342916H	126
NSYTBP342916HT	126
NSYTBP775	126
NSYTBP885	126
NSYTBPASBS	584
NSYTBS111113H	126
NSYTBS11116	126
NSYTBS1176	126
NSYTBS1179H	126
NSYTBS1397	126
NSYTBS1397T	126
NSYTBS16128	126

Index of References

NSYT...	Page
NSYTBS16128T	126
NSYTBS191210H	126
NSYTBS191210HT	126
NSYTBS19128	126
NSYTBS19128T	126
NSYTBS191610H	126
NSYTBS191610HT	126
NSYTBS19168	126
NSYTBS19168T	126
NSYTBS241910	126
NSYTBS241910H	126
NSYTBS241910HT	126
NSYTBS241910T	126
NSYTBS241912H	126
NSYTBS241912HT	126
NSYTBS24198	126
NSYTBS24198T	126
NSYTBS292412	126
NSYTBS292412H	126
NSYTBS292412HT	126
NSYTBS292412T	126
NSYTBS292416H	126
NSYTBS292416HT	126
NSYTBS29248	126
NSYTBS29248T	126
NSYTBS342912	126
NSYTBS342912T	126
NSYTBS342916H	126
NSYTBS342916HT	126
NSYTBS775	126
NSYTBS885	126
NSYTC12100	506
NSYTC6CRN	563
NSYTC6CSX	559
NSYTC7CRN	563
NSYTC7CSX	559
NSYTC8CRN	563
NSYTCD274	564
NSYTCD276	564
NSYTCD278	564
NSYTCL405ME	563
NSYTCM274	564
NSYTCSM6PLM	529, 533
NSYTCSPLM	148, 529, 533
NSYTDB5ME	563
NSYTDB5PL	560
NSYTDB5PLA	584
NSYTDBCRN	556, 563
NSYTDSSF2D	581, 582
NSYTDSSFN2D	581
NSYTEDB5ML	301, 561
NSYTEDB5PL	560
NSYTEL1242EPL	560
NSYTEL405ML	561
NSYTEL405PL	560
NSYTELJISPL	560
NSYTEMPL	560
NSYTET8PL	560
NSYTEX5	142, 541
NSYTEX6	541
NSYTEX8	166, 167, 510, 512, 515, 516, 541
NSYTEX8PLM	541

NSYT...	Page
NSYTFPCRN10	47, 568
NSYTFPCRN4	47, 568
NSYTFPCRN5	47, 568
NSYTFPCRN6	47, 568
NSYTFPCRN8	47, 568
NSYTHL1242EPLM	560
NSYTHL2433APLM	560
NSYTHL3113APLM	560
NSYTHL405PLM	560
NSYTHL421PLM	560
NSYTHL455PLM	560
NSYTHPLM	560
NSYTJ10030	36, 48, 458
NSYTJ10040	36, 48, 458
NSYTJ12030	36, 48, 458
NSYTJ12040	36, 48, 458
NSYTJ2015	36, 48, 458
NSYTJ2015HD	587
NSYTJ2515	48
NSYTJ3015	36, 48, 458
NSYTJ3020	36, 48, 458
NSYTJ3020HD	587
NSYTJ4015	36, 48, 458
NSYTJ4020	36, 48, 458
NSYTJ4020HD	587
NSYTJ4025	36, 48, 458
NSYTJ4025HD	587
NSYTJ5020	36, 48, 458
NSYTJ5025	36, 48, 458
NSYTJ5025HD	587
NSYTJ6020	36, 48, 458
NSYTJ6025	36, 48, 458
NSYTJ6030	36, 48, 458
NSYTJ6030HD	587
NSYTJ6040	36, 48, 458
NSYTJ6040HD	587
NSYTJ8025	36, 48, 458
NSYTJ8030	36, 48, 458
NSYTJ8040	36, 48, 458
NSYTJ8040HD	587
NSYTJIS	556
NSYTJPLA103G	460
NSYTJPLA104G	460
NSYTJPLA123G	460
NSYTJPLA124G	224, 460
NSYTJPLA126G	460
NSYTJPLA53G	460
NSYTJPLA54G	460
NSYTJPLA73G	460
NSYTJPLA74G	224, 460
NSYTJPLA76G	460
NSYTL1242EME	557, 563
NSYTL220PLM	560
NSYTL27270G	143, 462
NSYTL27360G	462
NSYTL405PLM	560
NSYTL405SML	556
NSYTLA	48, 54, 498
NSYTLAUHD	48, 587
NSYTLB	48, 54, 498
NSYTLBU	48, 499
NSYTLC	48, 54, 498
NSYTLCFL	48, 500

NSYT...	Page
NSYTLCME	48, 493
NSYTLCRNA	33, 498
NSYTLCRNB	33, 498
NSYTLCRNC	33, 498
NSYTLCRND	33, 498
NSYTLCRNO	33, 498
NSYTLCUHD	48, 587
NSYTLD	48, 54, 498
NSYTLDFL	48, 500
NSYTLDME	48, 493
NSYTLDUHD	48, 587
NSYTLE	48, 54, 498
NSYTLEFL	48, 500
NSYTLEME	48, 493
NSYTLEUHD	48, 587
NSYTLF	48, 54, 498
NSYTLF2FL	500
NSYTLFFL	48, 500
NSYTLFME	48, 493
NSYTLFU	48, 499
NSYTLG	48, 54, 498
NSYTLG2FL	48, 500
NSYTLGFL	48, 500
NSYTLGME	48, 493
NSYTLGU	48, 499
NSYTLGUHD	587
NSYTMME	301, 563
NSYTPLS1827	139
NSYTPLS2727	139
NSYTPLS2727A	139
NSYTPLS2736	139
NSYTPLS2736A	139
NSYTPLS2754	139
NSYTPLS2754A	139
NSYTPLS3636	139
NSYTPLS3654	139
NSYTPLS3654A	139
NSYTPLS3672A	139
NSYTPLS5454	139
NSYTPLS5454A	139
NSYTPLS5472A	139
NSYTPLSC1827G	139
NSYTPLSC2727AG	139
NSYTPLSC2727G	139
NSYTPLSC2736AG	139
NSYTPLSC2736G	139
NSYTPLSC2754AG	139
NSYTPLSC2754G	139
NSYTPLSC3636G	139
NSYTPLSC3654AG	139
NSYTPLSC3654G	139
NSYTPLSC3672AG	139
NSYTPLSC5454AG	139
NSYTPLSC5454G	139
NSYTPLSC5472AG	139
NSYTPLSP2727G	139
NSYTPLSP2754G	139
NSYTPLSP3654G	139
NSYTPV	305
NSYTSA2414SE	494
NSYTSA2417SE	494
NSYTSA2422SE	494
NSYTSA2423SE	494

NSYT...	Page
NSYTSA2429SE	494
NSYTSACRNB	33, 499
NSYTSACRNC	33, 499
NSYTSACRND	33, 499
NSYTSAKFL	492, 495
NSYTSAM508SE	494
NSYTSAM638SE	494
NSYTSML	556
NSYTSPLA	565
NSYTT6CRN	563
NSYTT8CRN	563
NSYTT8CSX	559
NSYTTG40	538
NSYTTG50	538
NSYTTG60	538
NSYTUP7035	571
NSYTVR10	530
NSYTVR12	65, 75, 530
NSYTVR125	530
NSYTVR14	65, 75, 530
NSYTVR15	530
NSYTVR16	65, 75, 530
NSYTVR18	65, 75, 530
NSYTVR20	65, 75, 530
NSYTVR22	75, 530
NSYTVR7	530
NSYTVR8	530
NSYTX10030	459
NSYTX2015	459
NSYTX2515	459
NSYTX3015	459
NSYTX3020	459
NSYTX4020	459
NSYTX5025	459
NSYTX6020	459
NSYTX6025	459
NSYTX8030	459

NSYU...	Page
NSYUCC270	463
NSYUCC360	463
NSYUM27180	463
NSYUM27270	143, 463
NSYUM27360	463
NSYUVPLA	465

NSYV...	Page
NSYVA2710M	566
NSYVA2710MA	566
NSYVA2712M	566
NSYVA2712MA	566
NSYVA2716M	566
NSYVA2724M	566
NSYVA272M	566
NSYVA272MA	566
NSYVA274M	566
NSYVA274MA	566
NSYVA276M	566
NSYVA276MA	566
NSYVA278M	566
NSYVA278MA	566
NSYVDM11UP	35, 48, 290, 291, 548
NSYVDM12UF	35, 48, 290, 291, 548

NSYV...	Page
NSYVDM16UP	35, 48, 290, 291, 548
NSYVDM17UF	35, 48, 290, 291, 548
NSYVDM20U8P	35, 48, 290, 548
NSYVDM20UP	35, 48, 290, 291, 548
NSYVDM21UF	35, 48, 290, 291, 548
NSYVDM25U8P	35, 48, 290, 291, 548
NSYVDM8UF	35, 48, 290, 291, 548
NSYVEA9	476
NSYVMICN18	253
NSYVMICN20	253
NSYVMICN22	253
NSYVPFN2B4	249
NSYVPLA10MG	584
NSYVPLA12MG	584
NSYVPLA15MG	584
NSYVPLA5MG	584
NSYVPLA7MG	584
NSYVPLM108	148, 584
NSYVR18	65, 75, 530
NSYVR20	65, 75, 530
NSYVR22	75, 530
NSYVSP18M	242
NSYZ...	Page
NSYZA2103G	473
NSYZA2104G	473
NSYZA2123G	473
NSYZA2124G	473
NSYZA2126G	473
NSYZA253G	473
NSYZA254G	473
NSYZA273G	473
NSYZA274G	224, 473
NSYZA276G	473
NSYZHPLA103G	474
NSYZHPLA104G	474
NSYZHPLA123G	474
NSYZHPLA124G	474
NSYZHPLA53G	474
NSYZHPLA54G	474
NSYZHPLA73G	474
NSYZHPLA74G	474
NSYZM253G	472
NSYZM263G	472
NSYZM283G	472
NSYZNPLA103G	473
NSYZNPLA104G	473
NSYZNPLA123G	473
NSYZNPLA124G	473
NSYZNPLA53G	473
NSYZNPLA54G	473
NSYZNPLA73G	473
NSYZNPLA74G	473
NSYZZ2103G	473
NSYZZ2104G	473
NSYZZ2123G	473
NSYZZ2124G	473
NSYZZ2126G	473
NSYZZ253G	473
NSYZZ254G	473

NSYZ...	Page
NSYZZ273G	473
NSYZZ274G	473
NSYZZ276G	473
NSYZZ5103G	473
NSYZZ5104G	473
NSYZZ5123G	473
NSYZZ5124G	473
NSYZZ553G	473
NSYZZ554G	473
NSYZZ573G	473
NSYZZ574G	473
XALE...	Page
XALE2	127
XALE3	127
XALE3255	127
XALEK170	127
XALEK1702	127

Schneider Electric Industries SAS
1884 Boulevard de la Défense
92000 Nanterre
France

RCS Nanterre 954 503 439
Capital social 896 313 776
se.com

© 2026 Schneider Electric. All Rights Reserved. Life Is On Schneider Electric is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies.
All other trademarks are the property of their respective owners. **UEMKCAT012EN** · 07/2026