

UK Declaration of Conformity

UK1007288-2

1.0 Product Identification

Object of the declaration: Direct Current electrical vehicle fast charging station

Product: EVlink Pro DC 180 V2
EVlink Pro DC 320

Reference: See Annex

2.0 This declaration of conformity is issued under the sole responsibility of the manufacturer.

Manufacturer: SCHNEIDER eSTAR
1884 Boulevard de la Défense,
92000 Nanterre, FRANCE

UK Representative Schneider Electric Limited
Stafford Part 5
Telford, TF3 3BL – United Kingdom

3.0 We Undersigned Schneider eStar declare that Schneider Electric branded products, when subject to correct installation, Maintenance and use confirming their intended purpose, according to applicable regulations and standards in the country where they are installed, to the supplier's instructions and to accept rules of the art comply with essential requirements of following Statutory Inventories and is also in conformity with the relevant union harmonization legislation.

4.0

Statutory Inventory with Amendments	Harmonized Standards/Other Technical Specification
SI 2012 No. 3032 - The RoHS Regulation	BS EN IEC 63000: 2018
SI 2017 No. 1206 - The Radio Equipment Regulations	BS EN IEC 61851-1: 2019, BS EN 61851-23: 2014, BS EN 61851-24: 2014, BS EN IEC 62311: 2020
	BS EN 61000-6-2: 2005 and BS EN IEC 61000-6-2: 2019, BS EN 61000-6-4: 2007+ A1: 2011 and BS EN IEC 61000-6-4: 2019, BS EN IEC 61851-21-2: 2021, EN 301 489-1 V1.9.2 (2011-09) and EN 301 489-1 V2.2.3 (2019-11), EN 301 489-3 V2.3.2 (2023-01), EN 301 489-17 V3.3.1 (2024-09), EN 301 489-52 V1.3.1 (2024-11),
	EN 300 330 V2.1.1 (2017-02), EN 301 511 V12.5.1 (2017-03), EN 301 908-1 V15.2.1 (2023-01), EN 301 908-2 V13.1.1 (2020-06), EN 301 908-13 V13.2.1 (2022-02) + EN 301 908-13 V13.3.1 (2024-10), EN 300 328 V2.2.2 (2019-07)
	BS EN 18031-1: 2024, BS EN 18031-2: 2024, BS EN 18031-3: 2024



UK Declaration of Conformity

UK1007288-2

5.0 Signed for on behalf of:
Place and Date:
Signature:

Name / Title:

Schneider Electric Industries SAS
Telford, UK, 30.06.2026

Signed by:

David Williams

A578D60923D7459...

David Williams

Vice President Transactional Business & Major
Pursuits UK&I Zone

UK Declaration of Conformity

UK1007288-2

Annex

Product	Short Description	Ratings
EVD2cxTyBzab	EVlink Pro DC 180 V2 EVlink Pro DC 320	Input: 380-415Vac, 3P+N+PE, 50/60Hz, Output: 150-1000 Vdc; Max output current: 380A; Overvoltage category: OVC III before SPD, OVC II after SPD IP55/IK10, -30°C to +50°C (up to 55°C with derating)
EVD2S120TBB-AN	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Australia/New Zealand
EVD2S120TBB-IEC	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for rest of world
EVD2S120TBB-T	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Turkey
EVD2S120TBBC10-IEC	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, 10m without cable management, without payment terminal, for rest of world
EVD2S120TBBC10-T	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, 10m without cable management, without payment terminal, for Turkey
EVD2S120TBBC7-AN	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, 7.5m without cable management, without payment terminal, for Australia/New Zealand

UK Declaration of Conformity

UK1007288-2

EVD2S120TBBC7-IEC	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, 7.5m without cable management, without payment terminal, for rest of world
EVD2S120TBBC7-T	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, 7.5m without cable management, without payment terminal, for Turkey
EVD2S120TBBCC1-T	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Turkey
EVD2S120TBBCC-AN	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Australia/New Zealand
EVD2S120TBBCC-IEC	EVlink Pro DC 180 V2	Rated output power: 120kW; Rated input current: 190A; Max input current: 211A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world
EVD2S150TBB-AN	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Australia/New Zealand
EVD2S150TBB-IEC	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for rest of world
EVD2S150TBB-T	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Turkey

UK Declaration of Conformity

UK1007288-2

EVD2S150TBBC10-IEC	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, 10m without cable management, without payment terminal, for rest of world
EVD2S150TBBC10-T	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, 10m without cable management, without payment terminal, for Turkey
EVD2S150TBBC7-AN	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, 7.5m without cable management, without payment terminal, for Australia/New Zealand
EVD2S150TBBC7-IEC	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, 7.5m without cable management, without payment terminal, for rest of world
EVD2S150TBBC7-T	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, 7.5m without cable management, without payment terminal, for Turkey
EVD2S150TBCC1-T	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Turkey
EVD2S150TBCC-AN	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Australia/New Zealand
EVD2S150TBCC-IEC	EVlink Pro DC 180 V2	Rated output power: 150kW; Rated input current: 238A; Max input current: 268A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world

UK Declaration of Conformity

UK1007288-2

EVD2S180TBB-AN	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Australia/New Zealand
EVD2S180TBB-IEC	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for rest of world
EVD2S180TBB-T	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, without payment terminal, for Turkey
EVD2S180TBBC10-IEC	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, 10m without cable management, without payment terminal, for rest of world
EVD2S180TBBC10-T	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, 10m without cable management, without payment terminal, for Turkey
EVD2S180TBBC7-AN	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, 7.5m without cable management, without payment terminal, for Australia/New Zealand
EVD2S180TBBC7-IEC	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, 7.5m without cable management, without payment terminal, for rest of world
EVD2S180TBBC7-T	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, 7.5m without cable management, without payment terminal, for Turkey

UK Declaration of Conformity

UK1007288-2

EVD2S180TBBCC1-T	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Turkey
EVD2S180TBBCC-AN	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Australia/New Zealand
EVD2S180TBBCC-IEC	EVlink Pro DC 180 V2	Rated output power: 180kW; Rated input current: 285A; Max input current: 316A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world
EVD2S240TBB-AN	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Australia/New Zealand
EVD2S240TBB-IEC	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world
EVD2S240TBB-T	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Turkey
EVD2S240TBBC10-IEC	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, 10m without cable management, without payment terminal, for rest of world
EVD2S240TBBC10-T	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, 10m without cable management, without payment terminal, for Turkey

UK Declaration of Conformity

UK1007288-2

EVD2S240TBBC7-AN	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, 7.5m without cable management, without payment terminal, for Australia/New Zealand
EVD2S240TBBC7-IEC	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, 7.5m without cable management, without payment terminal, for rest of world
EVD2S240TBBC7-T	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, 7.5m without cable management, without payment terminal, for Turkey
EVD2S240TBBCC1-T	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Turkey
EVD2S240TBBCC-AN	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Australia/New Zealand
EVD2S240TBBCC-IEC	EVlink Pro DC 320	Rated output power: 240kW; Rated input current: 380A; Max input current: 422A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world
EVD2S320TBB-AN	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Australia/New Zealand
EVD2S320TBB-IEC	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world

UK Declaration of Conformity

UK1007288-2

EVD2S320TBB-T	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Turkey
EVD2S320TBBC10-IEC	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, 10m without cable management, without payment terminal, for rest of world
EVD2S320TBBC10-T	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, 10m without cable management, without payment terminal, for Turkey
EVD2S320TBBC7-AN	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, 7.5m without cable management, without payment terminal, for Australia/New Zealand
EVD2S320TBBC7-IEC	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, 7.5m without cable management, without payment terminal, for rest of world
EVD2S320TBBC7-T	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, 7.5m without cable management, without payment terminal, for Turkey
EVD2S320TBCC1-T	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (PAX), for Turkey
EVD2S320TBCC-AN	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for Australia/New Zealand

UK Declaration of Conformity

UK1007288-2

EVD2S320TBBCC-IEC	EVlink Pro DC 320	Rated output power: 320kW; Rated input current: 507A; Max input current: 563A; CCS2 connector, Default usable length is 5m with cable management, with payment terminal (Payter), for rest of world
-------------------	-------------------	--

Photograph

