



**Note:**  
- Drawings Not To Scale  
- Drawings Subject to Change Without Notice  
- Dimensions are inches next to [Millimeters]

Part No.:  
**LC1D65AF7**

**Schneider Electric**  
Schneider Electric United States  
North American Division  
Boston One Campus  
800 Federal Street  
Andover, MA 01810, USA  
Phone: +1 8773425173  
Email: CCC@us.schneider-electric.com

Technical Information:	
Rating:	600V / 65A
UL File/CCN:	E164862 / NLDX
CSA File:	LR43364 3211 04
Meets Standards:	IEC 60647-4
Weight:	2.30 lb (0.860 kg)
Termination Method:	Screw Clamp
Wire Size:	Power: #2 - #16 AWG Control: #12 - #20 AWG
Terminal torque:	Power: 70 lb-in (8 Nm) Control: 8 lb-in (0.9 Nm)
Mounting Hwd.:	35mm DIN Rail, #8 screw

Specification:

Description	TeSys D IEC Contactor New Type with Everlink® - 65A - Vac Coil																		
Type	TeSys D IEC Contactor - 65A - 110Vac Coil																		
Voltages Code:	F7 at 110Vac 50/60 Hz																		
Coil Consumption: Inrush 160 VA Sealed 15 VA																			
<table><tr><th colspan="2">Single Phase</th><th colspan="4">Three Phase</th></tr><tr><td>115V</td><td>230V</td><td>200V</td><td>230V</td><td>460V</td><td>575V</td></tr><tr><td>5 HP</td><td>10 HP</td><td>20 HP</td><td>20 HP</td><td>40 HP</td><td>50 HP</td></tr></table>		Single Phase		Three Phase				115V	230V	200V	230V	460V	575V	5 HP	10 HP	20 HP	20 HP	40 HP	50 HP
Single Phase		Three Phase																	
115V	230V	200V	230V	460V	575V														
5 HP	10 HP	20 HP	20 HP	40 HP	50 HP														