# Form of Material Declaration

**<Date of declaration>**

| | |
|---|---|
| Date | 2026-10-21 |

**<MD ID number>**

| | |
|---|---|
| MD-ID-No. | 963778 |

**<Other information>**

| | |
|---|---|
| Remark 1 | |
| Remark 2 | |
| Remark 3 | |

**<Supplier (respondent) information>**

| | |
|---|---|
| Company name | |
| Division name | |
| Address | |
| Contact person | |
| Telephone number | |
| Fax number | |
| E-mail address | |
| SDoC ID-No. | |

**<Product information>**

| Product name | Product number | Delivered unit | | Product information |
|---|---|---|---|---|
| | | Amount | Unit | |
| Multi9 C60H-DC 2P 3A C 10kA 500 | M9U21203 | | | |

**<Materials information>**

This materials information shows the amount of hazardous materials contained in 1 (Unit: ) of the product.

| Table | Material name | | Threshold level | Present above threshold value | If yes, material mass: Mass | If yes, material mass: Unit | If yes, information on where it is used |
|---|---|---|---|---|---|---|---|
| **Table A* (materials listed in appendix 1 of the Convention)** | Asbestos | | 0.1%** | No | | | |
| | Polychlorinated biphenyls (PCBs) | | 50 mg/kg | No | | | |
| | **Ozone-depleting substances** | Chlorofluorocarbons (CFCs) | no threshold level | No | | | |
| | | Halons | | No | | | |
| | | Other fully halogenated CFCs | | No | | | |
| | | Carbon tetrachloride | | No | | | |
| | | 1,1,1-Trichloroethane | | No | | | |
| | | Hydrochlorofluorocarbons | | No | | | |
| | | Hydrobromofluorocarbons | | No | | | |
| | | Methyl bromide | | No | | | |
| | | Bromochloromethane | | No | | | |
| | Anti-fouling systems containing organotin compounds as a biocide | | 2,500 mg total tin/kg | No | | | |
| | Anti-fouling systems containing cybutryne | | 200 mg/kg*** | No | | | |
| **Table B* (Materials listed in appendix 2 of the Convention)** | Cadmium and cadmium compounds | | 100 mg/kg | No | | | |
| | Hexavalent chromium and hexavalent chromium compounds | | 1,000 mg/kg | No | | | |
| | Lead and lead compounds | | 1,000 mg/kg | No | | | |
| | Mercury and mercury compounds | | 1,000 mg/kg | No | | | |
| | Polybrominated biphenyls (PBBs) | | 50 mg/kg | No | | | |
| | Polybrominated diphenyl ethers (PBDEs) | | 1,000 mg/kg | No | | | |
| | Polychloronaphthalenes (Cl >= 3) | | 50 mg/kg | No | | | |
| | Radioactive substances | | no threshold level | No | | | |
| | Certain short-chain chlorinated paraffins | | 1% | No | | | |
| **Annex II**** (Additional materials)** | Perfluorooctane sulfonic acid (PFOS) and its derivatives | | no threshold level | NA | | | |
| | Brominated Flame Retardant (HBCDD) | | no threshold level | NA | | | |

* Hong Kong International Convention for the Safe and Environmentally Sound Recycling of Ships, 2009 (SR/CONF/45).

** Please refer to footnote 19 on the "Form of Material Declaration" in Appendix 6 of IMO Resolution MEPC.379(80).

*** Please refer to footnote 20 on the “Form of Material Declaration” amendment by IMO Resolution MEPC.405(83).

**** Regulation EU No. 1257/2013 of the European Parliament and of the Council of 20 November 2013 on Ship Recycling and amending Regulation EC No. 1013/2006 and Directive 2009/16/EC